



Tap Splice and Barrel Terminal

Power Factor Capacitor
.095 [2.41]
Aluminum Foil Thickness
Related Product Data:
Application Tooling — page 9
Technical Documents — page 1

Type 10
Splice




Type 11
Terminal




Material and Finish	Type	Wire Barrel Range		Part Number	Foil Crimp Tooling	Wire Barrel Crimp Tooling	
		AWG	mm ²		Jaws for Tool 68068, 68068-3	Jaws for Tool 68068, 68068-3	Head for Pneu. Tool 69010
Steel, tin-plated	10	—	—	53612-4	68257-1	—	—
Brass, tin-plated	11	8	7.0–8.0	53660-4	68257-1	68135	38394

Shield Connector for Telephone and Power Cable

Material and Finish:
Brass, tin-plated
Related Product Data:
Application Tooling — page 9
Technical Documents — page 1




Part No. 53490-1



Ring Tongue Terminal

.030 [0.76] Max.
Aluminum Foil Thickness

Material and Finish:
Copper, tin-plated
Foil Crimp Tooling:
Hand Tool — 68026
Die for Pneu. Tool — 69010
with Head 69263-1 — 69177-1
Related Product Data:
Application Tooling — page 9
Technical Document — page 1



Part No. 276959-2