


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION			
© COPYRIGHT - By -		ALL RIGHTS RESERVED.			


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	8	REVISED	10NOV2016	D.Z	S.L



- NOTES:
- PRODUCT MEET CONTROLLED SUBSTANCES SPEC. ROHS 2.0
- MATERIAL:
 - HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94 V-0
 - LATCH: HIGH TEMPERATURE THERMOPLASTIC, UL94 V-0
 - CONTACT: COPPER ALLOY
 - BOARD LOCK: STAINLESS STEEL
 - INTERFACE FINISH:
 - 0.00038 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
 - GOLD FLASH OVER 0.00127 MIN THK NICKEL.
 - 0.00076 MIN THK GOLD OVER 0.00127 MIN THK NICKEL
 - WAVE SOLDER CAPABLE TO 270°C 10S.
 - KEEP OUT AREA RESERVED FOR SOCKET EXTRACTORS, BOTH ENDS.

DUAL LONG LATCH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	DAVID ZHAO	15AUG2016	TE Connectivity	
		CHK	SIMON LI	15AUG2016		
		APVD	COREL WANG	15AUG2016	NAME	
		PRODUCT SPEC			SOCKET ASSEMBLY	
		108-115124			DDR4 DIMM,T/H TYPE	
		APPLICATION SPEC			288 POSITION	
		—			SIZE	CAGE CODE
		WEIGHT			A2	00779
		CUSTOMER DRAWING			SCALE	1:1
					SHEET	1 of 6
					REV	8



DUAL SHORT LATCH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 15AUG2016	 TE Connectivity			
DIMENSIONS: mm		CHK SIMON LI 15AUG2016				
		APVD COREL WANG 15AUG2016	NAME			
		PRODUCT SPEC	SOCKET ASSEMBLY			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		108-115124	DDR4 DIMM,T/H TYPE			
0 PLC ± -		APPLICATION SPEC	288 POSITION			
1 PLC ± 0.25		—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± 0.15		WEIGHT 7.0g	A2	00779	C=2308107	—
3 PLC ± -0.10		CUSTOMER DRAWING	SCALE 1:1		SHEET 2 of 6	REV 8
4 PLC ± -						
ANGLES ± -						
FINISH						

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

SHORT LATCH TYPE

NATURAL	BLUE(2935U)	15u"	3.85	3.18	6-2308107-5
NATURAL	BLACK	15u"	3.85	3.18	6-2308107-4
NATURAL	BLACK	30u"	3.57	2.67	6-2308107-3
NATURAL	NATURAL	30u"	3.85	3.18	6-2308107-2
GREEN (375C)	BLACK	30u"	3.85	3.18	6-2308107-1
NATURAL	BLACK	30u"	3.85	3.18	6-2308107-0
BLACK	BLACK	30u"	3.85	3.18	5-2308107-9
NATURAL	NATURAL	30u"	3.57	2.10	5-2308107-8
BLACK	BLACK	30u"	3.57	2.10	5-2308107-7
BLACK	BLACK	30u"	3.57	2.67	5-2308107-6
NATURAL	NATURAL	30u"	3.57	2.67	5-2308107-5
BLACK	BLACK	15u"	3.57	2.67	5-2308107-4
NATURAL	NATURAL	15u"	3.57	2.67	5-2308107-3
NATURAL	BLUE(2935U)	15u"	3.57	2.67	5-2308107-2
NATURAL	BLACK	15u"	3.57	2.67	5-2308107-1
LATCH COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE		DIM H	DIM L
					PART NUMBER

LONG LATCH TYPE

NATURAL	BLUE(2935U)	15u"	3.57	2.67	2-2308107-4
NATURAL	BLACK	30u"	3.57	2.40	2-2308107-3
NATURAL	BLACK	30u"	3.85	3.18	2-2308107-2
NATURAL	BLACK	15u"	3.57	2.40	2-2308107-1
BLUE(2935U)	BLUE(2935U)	15u"	3.85	3.18	2-2308107-0
GREEN (375C)	GREEN (375C)	15u"	3.85	3.18	1-2308107-9
NATURAL	NATURAL	15u"	3.85	3.18	1-2308107-8
BLACK	BLACK	15u"	3.85	3.18	1-2308107-7
BLACK	BLACK	30u"	3.57	2.10	1-2308107-6
NATURAL	BLACK	30u"	3.57	2.10	1-2308107-5
GREEN (375C)	BLACK	30u"	3.57	2.10	1-2308107-4
BLACK	BLACK	30u"	3.57	2.67	1-2308107-3
NATURAL	BLACK	30u"	3.57	2.67	1-2308107-2
GREEN (375C)	BLACK	30u"	3.57	2.67	1-2308107-1
NATURAL	BLACK	15u"	3.57	2.10	1-2308107-0
NATURAL	BLUE(2935U)	15u"	3.57	2.10	2308107-9
NATURAL	GREEN (375C)	15u"	3.57	2.10	2308107-8
NATURAL	BLACK	15u"	3.85	3.18	2308107-7
NATURAL	BLUE(2935U)	15u"	3.85	3.18	2308107-6
NATURAL	NATURAL	30u"	3.57	2.40	2308107-5
BLACK	BLACK	30u"	3.57	2.40	2308107-4
NATURAL	GREEN (375C)	15u"	3.57	2.40	2308107-3
NATURAL	BLUE(2935U)	15u"	3.57	2.40	2308107-2
BLACK	BLACK	15u"	3.57	2.40	2308107-1
LATCH COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE		DIM H	DIM L
					PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± 0.25

2 PLC ± 0.15

3 PLC ± -0.10

4 PLC ± -

ANGLES ± -

MATERIAL

FINISH

DWN DAVID ZHAO 15AUG2016

CHK SIMON LI 15AUG2016

APVD COREL WANG 15AUG2016

PRODUCT SPEC 108

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A2 00779 C=2308107 -

SCALE 1:1 SHEET 3 OF 6 REV 8

1471-9 (1/15)

D

C

B









A

D

C


B

A




LEFT ACTIVITY LATCH


NATURAL	NATURAL	BLUE(2935U)	15u" MIN.	3.85	2.67	9-2308107-2
		BLACK		3.85	2.67	9-2308107-1
FIXED LATCH COLOR	ACTIVITY LATCH COLOR	HOUSING COLOR	CONTACT GOLD INTERFACE	DIM H	DIM L	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN DAVID ZHAO 15AUG2016	TE Connectivity		
DIMENSIONS: mm			CHK SIMON LI 15AUG2016			
TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD COREL WANG 15AUG2016	NAME		
0 PLC ± -			PRODUCT SPEC			
1 PLC ± 0.25			108-115124	SOCKET ASSEMBLY DDR4 DIMM,T/H TYPE 288 POSITION		
2 PLC ± 0.15			APPLICATION SPEC			
3 PLC ± -0.10			-	SIZE CAGE CODE DRAWING NO		
4 PLC ± -			WEIGHT 7.6g			
ANGLES ± -			CUSTOMER DRAWING	A2 00779 C=2308107		
FINISH			SCALE 1:1			
			SHEET 4 of 6	REV 8		



FOR LONG LATCH, X IS 162 MM;
FOR SHORT LATCH, X IS 152 MM;
FOR SINGLE LATCH, X IS 152.70 MM;



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



5.4kg	3.5kg	50	10	500
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAY/ BOX	PCS/ BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 15AUG2016	TE Connectivity		
		CHK SIMON LI 15AUG2016			
		APVD COREL WANG 15AUG2016	NAME		
DIMENSIONS: mm		PRODUCT SPEC 108	SOCKET ASSEMBLY		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	DDR4 DIMM,T/H TYPE		
0 PLC ± -			288 POSITION		
1 PLC ± 0.25			SIZE A2	CAGE CODE 00779	DRAWING NO C=2308107
2 PLC ± 0.15			RESTRICTED TO		
3 PLC ± -0.10					
4 PLC ± -					
ANGLES ± -					
MATERIAL -		FINISH -			
		WEIGHT -			
		CUSTOMER DRAWING	SCALE 1:1	SHEET 6 of 6	REV 8