

[Connectors](#) > [Terminal Blocks & Strips](#) > [Terminal Blocks](#)

2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

✓ ACTIVE

[Buchanan](#) | [Din Rail Terminal Block Systems](#)TE Part # **2271556-5**TE Internal #: **2271556-5**Terminal Block Type : **Spring Terminal Block**Block Type : **Standard**Connector System : **Cable-to-Cable**Number of Positions : **1**Centerline (Pitch) : **5.15 mm [.202 in]**[Add to List](#) ▾[Similar Products](#)**ORDER SAMPLES****Compatible Parts & Tooling**

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

CONTACT US

We are here to help!

Get in touch with our product experts.

**CHAT WITH US****EMAIL US****CALL US**

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

 [2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK](#)

English

CAD Files

3D PDF

 [3D_CVM_CVM_2271556-5_A.pdf](#) 3D

Customer View Model

 [ENG_CVM_CVM_2271556-5_A.2d_dxf.zip](#)

English

 [ENG_CVM_CVM_2271556-5_A.3d_igs.zip](#)

English

 [ENG_CVM_CVM_2271556-5_A.3d_stp.zip](#)

English

Product Specifications

Application Specification

 [ENG_SS_114-137138_A3.pdf](#) English

Product Specification

 [ENG_SS_108-137138_A3.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features	Terminal Block Type : Spring Terminal Block Block Type : Standard Connector System : Cable-to-Cable Sealable : No Product Type : Terminal Block
Configuration Features	Number of Positions : 1 Number of Circuits : 2 Ground Function : Without Fuse Function : Without Switch Function : Without Number of Contacts : 1
Electrical Characteristics	Current Rating (A): 20 Voltage Rating (VAC): 600 Continuous Current Rating (A): 20
Contact Features	Contact Base Material : Copper Contact Configuration : Quick Connect Contact Current Rating (Max) (A): 20 Contact Plating Material : Matte Tin
Mechanical Attachment	Connector Mounting Type : DIN Rail
Housing Features	Centerline (Pitch) : 5.15 mm [.202 in] Housing Color : Black Housing Material : Nylon
Dimensions	Wire Size : 28 – 12 AWG [.08 – 2.5 kcmil]
Usage Conditions	Operating Temperature Range (°C): -40 – 105
Operation/Application	Circuit Application : Power
Industry Standards	UL Flammability Rating : UL 94V-0

Statement of
Compliance

[Statement of Compliance pdf](#)

Compatible Parts

[Contact Product Support](#)

Also in the Series | [Din Rail Terminal Block Systems](#)



Terminal Block
Hardware (26)



Terminal Block
Marking (4)



Terminal Blocks (158)

Customers Also Bought



TE Part # 68085
DIE COPALUM IP
69099 6



TE Part # 52746
SPLICE, COPALUM
PARA 6



TE Part # 52791
SPLICE, COPALUM
PARA 16-14



TE Part # 52792
SPLICE, COPALUM
PARA 12-10

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

[CALL US](#)

[LIVE CHAT](#)

[United States](#)

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)

[Investors](#)

[Corporate Responsibility](#)

[Terms and Conditions of
Sale](#)

[Distributors](#)

[Suppliers](#)

[Email or Call Us](#)

[Find Authorized Distributors](#)

[What's New on TE.com](#)

[Product FAQs](#)

[Select Country & Language](#)

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#)

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)

© 2018 TE Connectivity. All Rights Reserved.

