



+ CONNECTORS

TERMINAL BLOCKS



✓ Active

TE CONNECTIVITY (TE)

4MM^2,TWO LEVEL SPRING TERMINAL BLOCK

2271580-2

TE Internal Number: 2271580-2

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Terminal Block Type Spring Terminal Block

Centerline (Pitch) 6.15 mm [.242 in]

Operating Temperature Range (°C) -40 – 105

Connector Mounting Type DIN Rail

Block Type Standard

↓ **PRODUCT DRAWING**

English

DOCUMENTATION

Product Drawings

4mm^2,Double Level Spring Clamp Type Terminal Block

PDF

English

Product Specifications

Product Specification

Product Specification For Spring Terminal Block Connector

PDF

English

Application Specification

Application Specification For Spring Terminal Block Connectors

PDF

English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Block Type Spring Terminal Block
Block Type Standard
Product Type Terminal Block

Configuration Features

Number of Circuits 2
Ground Function Without
Fuse Function Without
Switch Function Without
Number of Contacts 2

Electrical Characteristics

Current Rating (A) 30
Voltage Rating (VAC) 600
Continuous Current Rating (A) 30

Contact Features

Contact Configuration Quick Connect
Contact Plating Material Matte Tin
Contact Base Material Copper

Mechanical Attachment

Connector Mounting Type DIN Rail

Housing Features

Centerline (Pitch) 6.15 mm [.242 in]
Housing Color Blue
Housing Material Nylon

Dimensions

Wire Size 28 – 10 AWG [.08 – 4 kcmil]

Usage Conditions

Operating Temperature Range (°C) -40 – 105

Industry Standards

UL Flammability Rating UL 94V-0

Statement of Compliance

