

For more Information  
please call

1-800-Belden1



### General Description:

The insulation is cross-linked polyethylene applied in a single extrusion. This construction has excellent thermal aging characteristics, moisture resistance, and solvent resistance. The 356-series of XL-DUR is recommended for class 130(B) as motor leads

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	20	10x30	TC - Tinned Copper

Total Number of Conductors: 1

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
XLPE - Cross Linked Polyethylene	0.762

#### Overall Insulation

#### Overall Cable

Overall Nominal Diameter: 2.565 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

UL AWM Style:	3173
UL Rating:	600 V, 125°C
CSA Rating:	600 V, 125°C
CSA Type:	CL1251
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Plenum/Non-Plenum

Plenum (Y/N): No

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
35620 0065000	5,000 FT	40.000 LB	BLUE, LIGHT	C I U Z	#20STRXLPE125C600VLBLU
35620 010500	500 FT	4.500 LB	BLACK	F	#20 STR XLPE 125C 600V
35620 0105000	5,000 FT	40.000 LB	BLACK	C	#20 STR XLPE 125C 600V

#### Notes:

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

I = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'

U = TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10000' PER COLORCOMBINATION. (SEE TOPCOAT ADDER TABLE)

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

### 35620 Hook-up/Lead - UL AWM Style 3173 - XL-DUR®

Revision Number: 1    Revision Date: 05-14-2007

© 2015 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.