

TRF600-150-RB-B-0.5 Product Details



TRF600-150-RB-B-0.5

TE Internal Number: A71956-000

 [Active](#)

PolySwitch Resettable Devices

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Telecom Application
- Family Name = TRF600
- Through Hole Construction
- IH (Room Temperature) = .15 Amps.
- IT (Room Temperature) = .30 Amps.

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

 [Add to My Part List](#)

 [Request Sample](#)

 [Find Similar Products](#)

 [Buy Product](#)

Documentation & Additional Information	
Product Drawings: TRF600-150-RB-B-0.5 (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available List all Documents	Additional Information: Product Line Information Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - UL Recognized = File No. E74889 - CSA File No. = 78165C - Comment = Devices are available with 0.5 ohm resistance matching.; Designed for equipment required to meet UL60950 and TIA968; can be used for ITU applications. Electrical Characteristics: IH (Room Temperature) (Amps.) = 0.15 IT (Room Temperature) (Amps.) = 0.30 Vmax Operating (V) = 250 Rmin (?) = 9.00 Rmax (?) = 12.000 R1 Max [Post Trip] (?) = 22.00 Vmax Interrupt (V rms) = 600 - Power Dissipation (Typical) (W) = 1.00 - R (Typical) (?) = 8.00 - Resistance Matching (?) = 0.5 - UL Rated Voltage (V) = 250 Termination Related Features: - Construction = Through Hole Body Related Features: - Lead Type = Kinked	Contact Related Features: - Family Name = TRF600 Configuration Related Features: - Coating = Coated Industry Standards: RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: Operating Temperature (Max.) (°C) = 85 Operation/Application: - Application = Telecom Packaging Related Features: - Packaging Method = Bulk, Tape & Reel Other: - Brand = Raychem