


1761664 -2 Product Details



1761664 -2

[Active](#)

Pin and Pinless Headers (AMP -LATCH)

[RoHS Compliant \(Statement of Compliance\)](#)

Product Highlights:

- ? Connector Type = Pin Headers
- ? Low Profile
- ? Number of Positions = 34
- ? 2.54 x 2.54 mm Centerline, Matrix
- ? PCB Mount Angle = Vertical

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [HEADER ASSEMBLY, VERTICAL, 34 POS, LOW PROFILE, SELE...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? Connector Type = Pin Headers
- ? [Profile](#) = Low
- ? [Number of Positions](#) = 34
- ? [PCB Mount Angle](#) = Vertical
- ? [PCB Retention Feature](#) = No
- ? [Mating Polarization Method](#) = Center, Dual Polarizing Bar
- ? [Mating Connector Lock](#) = Without
- ? [Housing Style](#) = 4 -Sided
- ? [Ejection Latches](#) = Without
- ? Post Size (mm [in]) = 0.64 [.025]
- ? Shrouded = Yes
- ? Comment = Post # Omitted - Row T None, Row S 15

Termination Related Features:

- ? [Termination Post Length \(mm \[in\]\)](#) = 2.79 [0.110]

Body Related Features:

- ? [Centerline, Matrix \(mm \[in\]\)](#) = 2.54 x 2.54 [.100 x .100]
- ? Daisy Chain = With

Contact Related Features:

- ? [Contact Mating Area Plating](#) = Gold (15)
- ? Contact Shape = Square
- ? Contact Termination Area Plating = Tin

Housing Related Features:

- ? Housing Material = Nylon
- ? Housing Flammability Rating = UL 94V -0
- ? Housing Color = Black

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Temperature Rating](#) = Standard

Other:

- ? Brand = AMP