



Circuit Board Indicators	Circuit Board Indicators - Through Hole Indicators	
Panel Mount Indicators		
Solid State Lighting	P/N# 5219488F	3 mm Lens
Traffic Signals	Description	Discrete LED Lamp
Vehicle Lighting	Package Options	100 pieces per bag
Rail	Product Type	Through Hole Indicators
Obstruction Lighting	Sub Product Type	Discrete LED
Hazardous Area Lighting	Configuration	3 mm Lens
Heliport Lighting	Viewing Angle	60 degrees
	Absolute Maximum Ratings (Ta = 25 °)	
	Solder Temp	260Â° for 6 sec
	Operating Temp	-55~+100° C
	Storage Temp	-55~+100° C

Distributor Stock Check

Check stock with our distributors now.

5219488F

[check stock](#)

- how to purchase
- sales contacts
- stock check



search

Product Line Search

Please select a Product Line to search.

[find](#)

☐ Part # / Text Search

Part No.:

Text Search:

[search](#)

quick links

- Dialight Corporate Video**
- Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)
- Application Notes**
- FAQs**
- Dialight Ltd (UK)**
- Dialight Garufo**
- Dialight BLP**
- LumiDrives**

Operating Characteristics	
LED Position	
Color	Green / Red
Lamp Type	Bi-Color / Bi-Color
LED Type	
Intensity Min (mcd)	3.7 / 2.5
Intensity Typ (mcd)	10.0 / 4.7
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	2.1 / 2.0
Fwd Voltage Max	2.8 / 2.8
Dom Wavelength Min (nm)	
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	