


[Home](#) > [Search Tools](#) > [Part Number](#)

Part Number Search

 You Searched For:

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS. *ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Global Sales Locator" located either to the right of this data or at the top of every page.*

- [Sales Support](#)
- [Product Overview](#)
- [Stock Check](#)

Our Descriptive Part Number: DM537401

Our Global Manufacturing Part Number: 053740-0001

<input type="checkbox"/>	CONSULT FACTORY	RoHS compliant =	material restrictions of lead, cadmium, hexavalent chromium, mercury, poly bromated biphenyl ether (PBB) and poly bromide diphenyl ether (PBDE) according to directive 2002/95/EC
<input type="checkbox"/>	CONSULT FACTORY	RoHS compatible =	Compatible with lead free soldering process

Export Compliance

<input type="checkbox"/>	Country of Compliance	United States
<input type="checkbox"/>	Export Compliance Notes	Commercial Shipments "C" Controlled by the US Department of Commerce.

Product Datasheet	
Where Sold	Europe, Americas, Asia Pacific
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Size 8 Contact
Application Type	Commercial
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	0
Number of Size 8 contacts	1
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Other Features	50 Ohm Coax
Contact Termination	Solder Crimp RG316
Temperature Rating	-55°C to +125°C
Current Capacity	5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1000 V AC at Sea Level
Insulator Material	Teflon
Contact Material	Copper Alloy
Shell Material	Copper Alloy
Other Information	Coax VSWR less than 1.3:1 up to 500 MHz, Coax Insertion Loss less than .3 dB, See Tooling Section for Crimp Tooling