Product Data Sheet

TERMINAL BLOCK

15XX ST

Replace XX with 02, 04, 06, 08 or 12 for number of poles Connector is Removable

Wire Range

• For use with prepared wire only

Electrical Ratings

• Amps

- 75 Amps (when wired with crimp type ring, spade or fork terminal)
- 600 Volts AC/DC (UL 1059 Class C, User Group General Industrial)
- Short Circuit Current Rated for 10,000 Amps
- Factory & Field Wiring

Agency Compliance

- UL Recognized, UL 1059 Terminal Block Standard, File No. XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766
- CE compliant to IEC 60947-7-1
- RoHS Compliant

Material Information

- Connector: Brass, nickel plated
- Insulator base:
 - Phenolic
 - Flammability rating of insulator base: UL 94 V-0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Stud: Plated Brass
- Marking Strips: Vinyl (White)
- Anchor screws: Steel, zinc plated





Termination Specifications

	Wire Range/ Terminal Type	Torque	Max Lug Width
	Listed Lug, Ring, Fork Ter- minals	20 in-Ibs	.50″

Installation & Accessories

Mounting

- For use with #10 fastener
- Recommended mounting torque not to exceed 25-30 in lbs

• Jumper

- MCJ (Multi-Circuit Jumper) Bar Available: Only sold seperately and the marking strip must be removed to assemble MCJ bar on part.

Cover

- Clear cover: Thermoplastic, UL Recognized QMFZ2 order CC 15XX (XX representing number of poles).
- Printed Marker Strips Consult factory for custom printed applications

STYLE 01	A	В	С	D
Example	1 2 3 4 5	54321	- 0 ω 4 Ω	Ω4 00 F


marathon®

——— Special Products

Product Data Sheet



Drawing



Catalog #	# of Poles	А	В
1504	4	3.25	2.88
1508	8	4.50	4.12
1508	8	5.75	5.38
1512	12	8.25	7.88