


208 Series Lead-Free 2AG, Fast-Acting Fuse











Agency Approvals

Agency	Agency File Number	Ampere Range
c FL °us	E10480	375mA - 10A
PS E	NBK200405-E10480 A/B/C/D NBK110512-E10480 A/B	1A - 3.5A 4A - 5A
C€		375mA - 10A

Additional Information







Resources



Samples

Description

Littelfuse 208 Series (2AG) 350V Fast-Acting Fuses are available in cartridge form or with axial leads. This series provides the same performance characteristics as its 3AG counterpart, while occupying one-third the space. Sleeved fuses are available.

Features

- In accordance with Underwriter's Laboratories Standard UL 248-14
- Available in cartridge and axial lead form and with
- various lead forming dimensions
- RoHS compliant and Lead-free

Applications

· Electrical ballasts used in fluorescent lighting and other applications

Electrical Characteristics for Series


% of Ampere Rating	Opening Time
100%	4 Hours, Min .
135%	1 Hour, Max .
200%	1 Second, Max .

Electrical Characteristic Specifications by Item


	Amp Rating Voltage Rating Rating Rating Rating Rominal Cold Resistance (Ohms) I²t (A² sec)	Voltage	Interrupting			А	gency Approva	ls
Amp Code			c FL ° us	PSE	Œ			
.375	0.375	350		0.395	0.171	Х		Х
.500	0.500	350		0.265	0.365	х		X
.750	0.750	350		0.152	1.050	х		Х
001.	1.0	350	100A @ 350V AC	0.103	2.220	×	×	X
01.5	1.5	350		0.0712	0.800	×	×	X
002.	2.0	350		0.0497	1.50	×	×	X
02.5	2.5	350		0.0372	2.68	×	×	X
003.	3.0	350		0.0317	4.62	×	×	X
03.5	3.5	350		0.0265	6.70	х	×	х
004.	4	350		0.0240	9.40	×	×	х
005.	5	350		0.0186	17.00	×	×	х
006.	6	350		0.0154	22.10	х	×	х
007.	7	350		0.0130	40	х	×	х
008.	8	350		0.0107	56	х	×	х
010.	10	350		0.0075	116	X	X	х




Temperature Rerating Curve



Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation		
Preheat:			
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)		
Temperature Minimum:	100° C		
Temperature Maximum:	150° C		
Preheat Time:	60-180 seconds		
Solder Pot Temperature:	260° C Maximum		
Solder DwellTime:	2-5 seconds		

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350° C +/- 5°C

Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.




Product Characteristics

Materials	Body: Glass Cap: Nickel-plated brass Leads: Tin-plated Copper		
Terminal Strength	MIL-STD-202G, Method 211A, Test Condition A		
Solderability	Reference IEC 60127 Second Edition 2003-01 Annex A		
Product Marking	Cap1 : Brand logo, current and voltage ratings Cap2 : Series and agency approval marks		


Operating Temperature:	−55°C to 125°C.
Thermal Shock:	MIL-STD-202G, Method 107G, Test Condition B (5 Cycles -65°C to +125°C).
Vibration	MIL-STD-202G, Method 201A
Humidity	MIL-STD-202G, Method 103B, Test Condition A: High RH (95%) and elevated temp (40°C) for 240 hours
Salt Spray	MIL-STD-202G, Method 101D, Test Condition B

Dimensions

208 000P Series 208 000EP Series



Part Numbering System



Packaging

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code	Taping Width		
208 Series						
Bulk	N/A	1000	MX	N/A		
Bulk	N/A	1000	MXE	N/A		
Reel and Tape	EIA 296-E	1500	DRT1	T1=53mm (2.087")		