




## MINISMDC150F/12-2 Product Details

[Share](#) | [Print](#) | [Email](#)


**MINISMDC150F/12-2**

TE Internal Number: RF1336-000

 Active

### PolySwitch Resettable Devices

 Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Surface Mount Application
- Vmax = 12 V
- Imax = 100 A
- Family Name = miniSMD
- Surface Mount Construction

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [miniSMDC150F/12 \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- [CP CATALOG 2011 - SURFACE-MOUNT \(PDF, English\)](#)

#### Product Specifications:

- [miniSMDC150F/12 \(PDF, English\)](#)

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Family Name = miniSMD
- UL File Number = E74889
- CSA File Number = CA78165

#### Electrical Characteristics:

- Vmax (V) = 12
- Imax (A) = 100
- IH (Room Temperature) (A) = 1.5
- IT (Room Temperature) (A) = 2.80
- Rmin (Ω) = 0.04
- R1 Max [Post Trip] (Ω) = 0.11

#### Termination Features:

- Construction = Surface Mount

#### Configuration Features:

- Form Factor (inches) = 1812
- Form Factor (mm) = 4532

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- TUV Certificate No. = R72111045

#### Environmental:

- [Operating Temperature \(Max.\) \(°C\)](#) = 85

#### Operation/Application:

- [Application](#) = Surface Mount

#### Packaging Features:

- [Packaging Method](#) = Tape & Reel

#### Other:

- [Brand](#) = Raychem

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed

