



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  sales contacts
-  stock check

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

find

Part # / Text Search

Part No.:

Text Search:


search

quick links

- Dialight Corporate Video
 - Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)
- Application Notes
 - FAQs
- Dialight Ltd (UK)
 - Dialight Garufo
 - Dialight BLP
 - LumiDrives

Circuit Board Indicators - Through Hole Indicators		
P/N# 56801433333F	3 mm Lens Single Color	
Description	3 mm Quad X 3 Backlighting Y-Y-Y-Y	
Package Options	5 Pieces Per Bag	
Product Type	Through Hole Indicators	
Sub Product Type	with Quad Level Housing	
Configuration	3 mm Lens	
Lamp Type	Single Color	
Viewing	Right Angle	
Viewing Angle	60	
Test Current (mA)	10mA	
Forward Current (mA)	20mA	
LED Centerline	3.53	
Polarity	Cathode Right	

Absolute Maximum Ratings (Ta = 25 °)		
Reverse Current	100 @ Vr = 5V	
Derating	from 50Â° @ .25 mA/Â°C	
Reverse Voltage	5 V	
Solder Temp	260Â° for 5 sec	
Operating Temp	-55 to +100° C	
Storage Temp	-55 to +100° C	



Operating Characteristics		
LED Position	1-4	
Color	Yellow	
Lamp Type	Single Color	
LED Type	Standard Efficiency	
Intensity Min (mcd)	7.4	
Intensity Typ (mcd)	10.0	
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)	60	
Backlighting	Yes	
Pitch Between Vertical	4.50	
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

56801433333F

check stock