

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [502380-0400](#)
Status: **Active**
Overview: [CLIK-Mate™ Wire-to-Board Connectors](#)
Description: 1.25mm Pitch CLIK-Mate™ Wire-to-Board Housing, Single Row, 4 Circuits

Documents:
[3D Model](#) [Application Specification AS-502380-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [Application Specification AS-502380-002 \(PDF\)](#)
[Product Specification PS-502382-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


General
Product Family Crimp Housings
Series [502380](#)
Application Signal, Wire-to-Board
MolexKits Yes
Overview [CLIK-Mate™ Wire-to-Board Connectors](#)
Product Name CLIK-Mate™
UPC 822350894869

Physical
Breakaway No
Circuits (maximum) 4
Color - Resin White
Gender Plug
Glow-Wire Compliant No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Resin Polyester
Net Weight 149.000/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 1.25mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -25°C to +85°C

Electrical
Current - Maximum per Contact 1A

Material Info

Reference - Drawing Numbers
Application Specification AS-502380-001, AS-502380-002
Product Specification PS-502382-001, RPS-502382-003, RPS-502382-004, RPS-502382-005, RPS-502382-006, RPS-502382-008, RPS-502382-010, RPS-502382-011, RPS-502382-012, RPS-502382-013, RPS-502382-016, RPS-502382-017, RPS-502382-018, RPS-502382-019, RPS-502386-001, RPS-502386-002
Sales Drawing SD-502380-001, SD-502380-002



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[502380Series](#)

Mates With
[502382](#) PCB Receptacle, [502386](#) PCB Receptacle

Use With
[502381](#) Crimp Terminal