

GFSMCB240202P -- Ground Fault Sensing Module Circuit Breaker, 240V AC, 20A, Two Pole



This hydraulic magnetic circuit breaker, in the event of a ground fault will interrupt the load by means of a shunt trip coil.

Product Specifications	
GFCI Product Type	 GFCI Sensing Module and Breaker
GFCI Sensing Module Item	Sensing Module Circuit Breaker
Sensing Module Circuit Breaker Voltage	240V AC
Sensing Module Circuit Breaker Amperage	20A
Sensing Module Circuit Breaker Poles	2 Pole
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Max Humidity	0.95
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)
UPC Number	78358569241
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

