


GSD

M39012/26-0011



NOTES:

1. FOR USE WITH RG-142, 223 & 400/U CABLES.
2. FOR CABLING INSTRUCTIONS SEE CP-465.
3. FOR CABLE TRIMMING USE KTJ-113 & KTD-166.
4. FOR CRIMPING USE DIE KTH-2001.
5. INTERFACE PER MIL-STD-348, FIG. 313-1.
6. CENTER CONTACT TO BE SUPPLIED UNASSEMBLED.
7. MATERIALS:
 - INSULATOR: TEFLON, ASTM-D-1457
 - GASKET: SIL. RUB., ZZ-R-765
 - K-GRIP SLEEVE: COM. BRONZE TUBE, ALLOY 220
 - OUTER CONTACT: BER. COP., ASTM-B-196
 - ALL OTHER PARTS: BRASS, ASTM-B16
8. FINISHES:
 - CENTER CONTACT: HARD GOLD PLATE PER MIL-G-45204
 - ALL OTHER METAL PARTS: SILVER PLATE PER QQ-S-365
9. ELECTRICAL CHARACTERISTICS:
 - NOMINAL IMPEDANCE: 50 OHMS
 - VOLTAGE RATING: 500 VRMS
 - FREQUENCY RANGE: DC TO 11 GHz

REVISIONS

ISSUE	CHANGES
7	CN 33600 E REDRAWN JCA 12/13/91
8	CN 35686 A KVH 08/02/94

JCA2294

SCALE 4:1

APPROX SURFACE AREA

KA-59-230

USED ON

REF:

PLUG, TNC

DRAWN	JCA	DATE	12/13/91
DESIGN	MJB	DATE	12/16/91
APPR.		DATE	

KINGS
ELECTRONICS CO., INC.
TUCKAHOE, NEW YORK 10707

M39012/26-0011

GSD