



Search

- [United States](#) [[Change](#) [Change](#)]
- [All 3M Products](#)
- [Newsroom](#)
- [About 3M](#)

[Electrical Commercial and Industrial](#)

- [Products](#)
 - [Aerosols, Coatings, and Adhesives](#)
 - [Cable Ties and Accessories](#)
 - [Cold Shrink Products](#)
 - [Electrical Tapes and Mastics](#)
 - [Electrical Wire Connectors and Tools](#)
 - [Fire Protection Products](#)
 - [Heat Shrink Products](#)
 - [Identification Systems](#)
 - [Lugs and Connectors](#)
 - [Cable Accessory Products](#)
 - [Motor Lead Connections and Kits](#)
 - [Safety and Protection Products](#)
 - [Separable Connectors](#)
 - [Splices](#)
 - [Terminals, Kits and Tools](#)
 - [Terminations](#)
 - [Underground Cable Locating and Marking Products](#)
 - [Wire Pulling Lubricants](#)
 - [Commercial LED Lamps](#)
- [Documentation & Literature](#)
- [News & Tradeshow](#)
 - [News](#)
 - [Tradeshow](#)
- [Support](#)
 - [Where to Buy \(Find a Distributor\)](#)
 - [Find an Account Rep](#)
 - [Product Support](#)
 - [Industry Standards & Compliance](#)
 - [Training](#)
 - [Industry Links](#)
 - [Contact Us](#)
 - [Construction Services](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Heat Shrink](#) > [Dual Wall \(Adhesive Lined\)](#) > 3M™ Heat Shrink Multiple-Wall Polyolefin Tubing EPS400-.450-48"-Black-75 Pcs, 48 in length sticks, 75 pieces/case

[Contact Us](#) [Where to Buy \(Find a Distributor\)](#) [Find an Account Rep](#)

3M™ Heat Shrink Multiple-Wall Polyolefin Tubing EPS400-.450-48"-Black-75 Pcs, 48 in length sticks, 75 pieces/case

3M ID 80611601982 UPC# 00051128599372 Part Number EPS400-.450-48"-Black-75 Pcs

3M™ EPS-400 Heat Shrink Tubing is a dual-wall tubing provides the advantage of [Print](#)



integral, adhesive-lined construction. This flame-retardant tubing with a 4:1 shrink ratio offers insulation for 600V-rated applications. The semi-rigid polyolefin construction has an internal layer of thermoplastic adhesive which offers moisture-seal protection in automotive and marine applications.

- Dual-wall construction provides abrasion resistance and moisture-seal protection
- Offers the advantage of integral, adhesive-lined construction
- Offers protection for sealing voids in multiple wire bundles for automotive and marine applications
- Expanded I.D. of 0.45 in
- 4-ft stick
- Made of black semi-rigid polyolefin
- Withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C)
- Flame-retardant tubing is rated for 600V applications
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 75 sticks/case

[Need Help?](#)

Questions?
We can help

[Contact Us](#)

- [Overview](#)
- [Documents](#)

3M™ Heat Shrink Tubing EPS-400 is color-coded for quick and easy identification of the wire. It provides a skintight fit and strain-relief protection for electronic components, truck wire splices, wire bundles and harness breakouts. This flame-retardant tubing has a heat shrinkable outer wall that is cross-linked for abrasion resistance. The inner adhesive helps to maintain high flow and superior adhesion characteristics. When the tubing cools down, it forms a permanent, water-resistant barrier. It withstands temperatures of -67 to 230 degrees F (-55 to 110 degrees C). UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

Specifications

Color	Black
Family	3M™ Heat Shrink EPS-400
Length	48 Inch
Material	Polyolefin
Size	0.450 Inch
Trademark	3M

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.

3M:

[News](#)
[Careers](#)
[Partners & Suppliers](#)
[Investor Relations](#)
[SDS Search](#)
[Transport Information Search](#)
[Help Center](#)

© 3M 2018. All Rights Reserved.

- [Legal Information](#)
- [Privacy Policy](#)

- [Share](#)