





# KU series

**KUP Enclosed Relay KUIP 8mm Coil to Contacts KUGP 3mm Contact Gap, 8mm Coil to Contacts KUEP 10 Amp 150VDC Load Switching** KUMP 15 Amp 277VAC

**File E22575** 

(File LR15734)

Users should thoroughly review the technical data before selecting a product part number. It is recommended that users also seek out the pertinent approvals files of the agencies/laboratories and review them to ensure the product meets

#### **Features**

- AC coils: 6-240VAC, 50/60 Hz. DC: 6-110VDC.
- Contact arrangement up to 4PDT.
- Wide selection of termination and mounting styles.
- PC terminals available.
- Push to test button and indicator lamps.
- KUEP incorporates a blow out magnet for high voltage DC switching.
- KUIP offers 8mm contact-to-coil spacing for a higher degree of isolation.
- KUGP provides 3mm contact gap and 8mm contact-to-coil spacing.
- Complete line of sockets and DIN rail.
- Class B coil insulation.

#### Contact Data @ 25°C

Arrangements: See respective ordering information table. Materials: Fine silver (5 amp) silver-cadmium oxide (10 amp).

Gold flash available as standard.

Gold diffused and gold alloy on special order.

#### **Expected Mechanical Life:**

#### **Contact Ratings**

Material	Arrangement	UL/CSA Ratings	Expected Life
Fine Silver	All	5 amps @ 28VDC or 240VAC 80% PF, 2.5 amp tungsten @120VAC, 1/2 amp @ 120VDC. 1/6 HP @120VAC, 1/3 HP @ 240VAC, 5 FLA, 15 LRA @ 250VAC (FLA covered by 30,000 operations).	100,000
Silver- Cadmium Oxide	1-2 Pole KUP KUIP KUGP KUEP All KUMP	10 amps @ 28VDC or 240VAC, 80% PF, 5 amp tungsten @ 120VAC, 3A 600VAC, 1/2 amp @ 120VDC. 1/3 HP @ 120VAC, 1/2 HP @ 240, 480, and 600VAC, 10 FLA 30 LRA @ 120VAC, 5 FLA, 15 LRA @ 250VAC.(FLA ratings covered by 30,000 operations)	100,000
	KUMP	15 amp @ 277VAC, 80% PF KUM KUMP	100,000
	3 Pole KUP KUIP 4 Pole	10 amp @ 28VDC or 120VAC, 80% PF, 6 2/3 amp @ 240VAC, 80% PF 10 amp per pole not to exceed 30 amp total @ 28VDC, 120VAC, 80% PF, 6 2/3 amp @ 240VAC,	100,000
	KUEP SPST-NO KUEP 2PST-NO KUEP 2PDT	80% PF  10 amp @ 150VDC  5 amp @ 150VDC  3 amp @ 150VDC	100,000

(All other AC ratings apply KUEP.)

### **Initial Dielectric Strength**

Between Open Contacts: 1,200V rms; KUGP, 3,500V rms.

Between Adjacent Contacts: 2,200V rms.

Between Contacts and Coil: 2,200V rms; KUGP, KUIP, 3,750V rms.

the requirements for a given application.

#### Coil Data @ 25°C

Voltage: 6 to 110VDC and 6 to 240VAC.

**Nominal Coil Power:** 

DC Coils: 1.2 Watts - KUP, KUIP, KUMP, 1 - 3 pole; KUEP, 1 pole. DC Coils: 1.8 Watts - KUP, 4 pole; KUEP, 2 pole; KUGP. AC Coils: 2.0VA - KUP, KUIP, 1 - 2 pole; KUEP, 1 pole.

AC Coils: 2.7VA - KUP, KUIP, 3 pole; KUEP, 2 pole; KUGP, KUMP.

#### **Coil Data**

DC Volts	1.2 Wa	att	1.8 Watt		
Nominal	DC Ohms ± 10%	Nom. I ma	DC Ohms ± 10%	Nom. I ma	
5	21	238	14	360	
6	32.1	187	20	300	
12	120	100	80	150	
24	472	51	320	75	
48	1,800	26.7	1,260	38	
110	10,000	11	6,720	16	
AC Volts	2VA		2.7V	1	
Nominal	DC Ohms ± 15%	Nom. I ma	DC Ohms ± 15%	Nom. I ma	
6	6	335	4.2	460	
12	24	168	18	230	
24	85	84	72	115	
120	2,250	17.5	1,700	24	
240	9,110	8.75	7,200	12	

#### Operate Data @ 25°C

Must Operate Voltage:

**DC Coils:** 75% of nominal voltage or less. **AC Coils:** 85% of nominal voltage or less.

Operating Time (Excluding Bounce):

15 milliseconds, typical, at nominal voltage.

Release Time (Excluding Bounce): 10 milliseconds, typical, at nominal voltage.

### **Environmental Data**

Temperature Range:


Operating: Enclosed Relays: -45°C to maximum listed in table below. Open Relays: Add 15°C to maximum listed.


Max C°	+45°C	+50°C	+55°C	+70°C	+75°C	+80°C	+95°C
KUP	AC	DC	AC	DC			
	3-4 pole	4 pole	1-2 pole	1-3 pole			
KUIP				AC		AC	DC
				3 pole		1-2 pole	1-3 pole
KUGP				AC	DC		
				2 pole	2 pole		
KUEP	AC	DC	AC	DC			
	2 pole	2 pole	1 pole	1 pole			
KUMP	AC		AC	DC			
	3 pole		1-2 pole	1-3 pole			

Catalog 1308242 Issued 3-03 (PDF Rev. 1-06) tyco P&B Electronics

### **Environmental Data (Continued)**

### Maximum Allowable Ambient Temperature vs. Voltage (KUP enclosed)





#### **Mechanical Data**

Termination: Quick connect, solder and PC board. Enclosure: Clear polycarbonate dust cover. Weight: 3.0 oz. (85g) approximately.

### **Ordering Information**

Typical Part No. ▶

KU **KUP**  -14

Α

1

5

F -120

Basic Series & Type:

KU = Basic open relay. KUP = Basic enclosed relay

**Contact Arrangement:** 

14 = 3C (3PDT) 17 = 4C (4PDT) 1 = 1A (SPST-NO)5 = 1C (SPDT)11 = 2C (DPDT)

**Coil Input:** 

A = AC 50/60 Hz.D = DC

4.

ŀ.	Mountings:				
	Туре	KU		KUP (through 3 poles)	KUP (4 pole models)
	Codes Available	1,3,4		1,2,3,4,5, A,E,T	1,3,5,A,E
	3 = #6-32  tap	d, .218" (5.54mm) locatin ped core, .125" (3.18mm) ped core, .218" (5.54mm	locating tab.	1 = PLAIN CASE; 2 = with test button. 3 = with indicator lam 4 = with test button of the second o	x indicator lamp.* IT CASE. 32 stud, locating tab. ped core, locating tab. SE. models with the following coils: 20-240VAC. Only models with

#### Terminal & Contact Material:

Type	1 & 2 Pole Models	3 Pole Models	4 Pole Models
Codes Available	1, 5, 7, K	1, 5, 7	1**, 5**,7, 9

- \*\*4 pole KUP with .187" (4.75mm) quick connect/solder terminals will not plug into sockets. Must use .110" (2.79 mm) quick connect solder terminals for socket mounting.
- 1 = .187" (4.75mm) quick-connect/solder; silver, 5 amps.
- 5 = .187" (4.75mm) quick connect/solder; silver-cadmium oxide, 10 amps.
- 7 = .047" (1.19mm) printed circuit; silver-cadmium oxide, 10 amps. 9 = 4 pole KU, KUP: .110" (2.79mm) quick connect/solder; silver-cadmium oxide, 10 amps. K = .250" (6.35mm) quick connect; silver-cadmium oxide, 10 amps.

### 5A. Gold Flashed Contact Option:

F = Optional gold flashing for silver and silver-cadmium oxide contacts.

**Coil Voltage:** 

To 240VAC, 50/60 Hz. or 110VDC.

## Our authorized distributors are more likely to stock

KUP-11A15-12	KUP-11D15-5	KUP-11D55-110	KUP-14A55-24	KUP-14D25-24
KUP-11A15-24	KUP-11D15-12	KUP-14A11-120	KUP-14A55-120	KUP-14D35-24
KUP-11A15-120	KUP-11D15-24	KUP-14A15-12	KUP-14A55-240	KUP-14D55-12
KUP-11A15-240	KUP-11D15-110	KUP-14A15-24	KUP-14D11-24	KUP-14D55-24
KUP-11A35-120	KUP-11D35-24	KUP-14A15-120	KUP-14D15-6	KUP-17A19-120
KUP-11A55-24	KUP-11D55-6	KUP-14A15-240	KUP-14D15-12	KUP-17A55-24
KUP-11A55-120	KUP-11D55-12	KUP-14A25-120	KUP-14D15-24	KUP-17D19-24
KUP-11AT5-120	KUP-11D55-24	KUP-14A35-120	KUP-14D15-48	KUP-17D55-24
KUP-11D11-24	KUP-11D55-48	KUP-14A45-120	KUP-14D15-110	
	KUP-11A15-24 KUP-11A15-120 KUP-11A15-240 KUP-11A35-120 KUP-11A55-24 KUP-11A55-120 KUP-11AT5-120	KUP-11A15-24       KUP-11D15-12         KUP-11A15-120       KUP-11D15-24         KUP-11A15-240       KUP-11D15-110         KUP-11A55-120       KUP-11D35-24         KUP-11A55-24       KUP-11D55-12         KUP-11A75-120       KUP-11D55-24	KUP-11A15-24         KUP-11D15-12         KUP-14A11-120           KUP-11A15-120         KUP-11D15-24         KUP-14A15-12           KUP-11A15-240         KUP-11D15-110         KUP-14A15-24           KUP-11A35-120         KUP-11D35-24         KUP-14A15-120           KUP-11A55-24         KUP-11D55-6         KUP-14A15-240           KUP-11A55-120         KUP-11D55-12         KUP-14A25-120           KUP-11AT5-120         KUP-11D55-24         KUP-14A35-120	KUP-11A15-24         KUP-11D15-12         KUP-14A11-120         KUP-14A55-120           KUP-11A15-120         KUP-11D15-24         KUP-14A15-12         KUP-14A55-240           KUP-11A15-240         KUP-11D15-110         KUP-14A15-24         KUP-14D11-24           KUP-11A35-120         KUP-11D35-24         KUP-14A15-120         KUP-14D15-6           KUP-11A55-24         KUP-11D55-6         KUP-14A15-240         KUP-14D15-12           KUP-11A55-120         KUP-11D55-12         KUP-14A25-120         KUP-14D15-24           KUP-11AT5-120         KUP-11D55-24         KUP-14A35-120         KUP-14D15-48



tyco Catalog 1308242 Issued 3-03 (PDF Rev. 1-06) P&B

**Ordering Information High Isolation Design** 

**KUIP** -5 A 5 5 -120 Typical Part No. ▶ **KUGP** 

**Basic Series & Type:** 

KUIP = Enclosed relay with 8mm contact to coil spacing. KUGP = Enclosed relay with 3mm open contact spacing and

8mm contact to coil spacing. (Form A and Form X arrangements only)

**Contact Arrangement:** 

5 = 1 Form C (SPDT)\*11 = 2 Form C (DPDT)\*7 = 2 Form A (DPST-NO)14 = 3 Form C (3PDT)\*

\* Not offered on KUGP model.

**Coil Input:** 

A = AC, 50/60 Hz. D = DC

Mountings:

1 = PLAIN CASE, SOCKET MOUNT. T = TOP FLANGE CASE

5 = BRACKET MOUNT CASE

**Terminal & Contact Material:** 3 = .047" (1.19mm) printed circuit board; silver. 5 = .187" (4.75mm) quick connect/solder; silver-cadmium oxide.

Coil Voltage:

To 240VAC, 50/60 Hz. or 110VDC. (For 277VAC, consult factory.) See coil data tables.

Our authorized distributors are more likely to stock the following items for immediate delivery.

KUIP-14A15-120 KUGP-7D55-24 KUIP-14D15-12 KUIP-5A55-120 KUIP-14D15-24 KUIP-11D55-12

KUIP-11D55-24

**Ordering Information** 

**High Voltage DC Switching KUEP** -3 Α 1 5 -120 Typical Part No. ▶

Basic Series & Type:

KUEP = Enclosed relay with magnetic blow-outs

2. **Contact Arrangement:** 

3 = 1X (SPST-NO-DM)7 = 2A (DPST-NO)11 = 2C (DPDT)

3. Coil Input:

A = AC 50/60 Hz.D = DC

Mountings:

1 = PLAIN CASE;

3 = with indicator lamp.\* \*Indicator lamps are available on models with the following coils: 5 = BRACKET MOUNT CASE 6-24VAC and DC, 110VDC and 120-240VAC. Only models with

T = TOP FLANGE CASE 120-240VAC coils are UL recognized.

**Terminal & Contact Material:** 

5 = .187" (4.75mm) quick connect/solder; silver-7 = .047' (1.19mm) printed circuit; silver-cadmium-oxide.

cadmium-oxide.

Coil Voltage:

To 240VAC, 50/60 Hz. or 110VDC. (For 277VAC, consult factory.)

Our authorized distributors are more likely to stock the following items for immediate delivery.

KUEP-3A15-120 KUEP-3D15-110 KUEP-11D15-12 KUEP-3D15-12 KUEP-7D15-24 KUEP-11D15-24

KUEP-3D15-24 KUEP-11A15-120



Catalog 1308242 Issued 3-03 (PDF Rev. 1-06) tyco P&B

### **Ordering Information**

15 Amp Switching **KUM** -14 A 1 8 -120 Typical Part No. ▶ **KUMP** Basic Series & Type: KUM = 15 amp open relay KUMP = 15 amp enclosed relay **Contact Arrangement:** 1 = 1A (SPST-NO)2 = 1B (SPST-NC)

3 = 1X (SPST-NO-DM)

4 = 1Y (SPST-NC-DB)

5 = 1C (SPDT)

6 = 1Z (SPDT-NC-NO [DB-DM])

7 = 2A (DPST-NO)

8 = 2B (DPST-NC)

11 = 2C (DPDT)

12 = 3A (3PST-NO)

13 = 3B (3PST-NC) 14 = 3C (3PDT)

**Coil Input:** A = AC, 50/60 Hz. D = DC

### Mountings:

Туре	KUM		KUMP
OPEN S	STYLE	1 = PLAIN CASE;	A = PLAIN CASE, #6-32 STUD LOCATING TAB;
1 = #6-3	32 stud, .218"	2 = with test button.	B = with test button.
(5.5	4mm) locating	3 = with indicator lamp.*	C = with indicator lamp.*
tab.	-	4 = with test button & indicator lamp.*	D = with test button & indicator lamp.*
2 = 2-hc	ole bracket,	5 = BRACKET MOUNT CASE;	E = PLAIN CASE, TAPPED CORE, LOCATING TAB;
	32 tapped.	6 = with test button.	F = with test button.
	32 tapped core,	7 = with indicator lamp.*	G = with indicator lamp.*
	" (3.18mm)		H = with test button & indicator lamp.*
	ting tab.	9 = STUD ON END OF PLAIN CASE.	T = TOP FLANGE CASE.
	32 tapped core,		
	3" (5.54mm)		
		*Indicator lamps are available on model	
5 = #6-32 tapped core,		6-24VAC and DC, 110VDC and 120-240	VAC. Only models with
no lo	ocating tab.	120-240VAC coils are UL recognized.	

#### Terminal & Contact Material:

Type	1 & 2 Pole Models	3 Pole Models
Codes Available	6,8,9,G	6,8,9

6 = .205" (5.21mm) quick connect/solder; silver-cadmium-oxide.

8 = .187" (4.75mm) quick connect/solder; silver-cadmium-oxide. 9 = .047" (1.19mm) printed circuit; silver-cadmium-oxide.

G = .250" (6.35mm) quick connect; silver-cadmium-oxide. (Not available on 3 pole models.)

### Coil Voltage:

To 240VAC, 50/60 Hz. or 110VDC (For 277VAC, consult factory.)

### Our authorized distributors are more likely to stock the following items for immediate delivery.


KUMP-11A18-24 KUMP-11D18-12 KUMP-14A18-24 KUMP-11A18-120 KUMP-11D18-24 KUMP-14A18-120 KUMP-11A18-240 KUMP-11D18-110 KUMP-14D18-12

KUMP-14D18-24


tyco Catalog 1308242 Issued 3-03 (PDF Rev. 1-06) P&B Electronics

### **Outline Dimensions**

### **Open Relays**



X Is For Terminal Dimensions See Terminal Drawings



## **Seated Heights For Open Relays**



#### 1.52" (38.6mm) for bracket with 2-#6 32 tapped holes.


#### 1.282" (32.56mm) for #6-32 tapped core with .125" (3.18mm) or .218" (5.54mm) locating tab.


#### 2.046" (51.97mm) for relay with printed circuit terminals.

#### STUD TYPE also available with .125" (3.18mm) tab, as well as without stud and locating tab. Models without stud have core tapped #6-32 THREAD, .25" (6.4mm) minimum depth.

- \*Dimensions with .250" (6.35mm) terminals.
- \*\*Dimensions with .110" (2.79mm) or .205"(5.21mm) terminals.
- \*\*\*Dimensions with .187" (4.75mm) terminals.


### Stud Type






## **Enclosed Relays**


#### **Plain Case**




### **Top Flange Case**



### **Bracket Mount Case**




#### Core and Stud Mount Cases



- †Dimensions with .250" (6.35mm) terminals.
- ‡Dimensions with .110" (2.79mm), .187" (4.75mm and .205" 5.21mm) terminals
- \*Dimensions with .250" (6.35mm) terminals.
- \*\*Dimensions with .110" (2.79mm) or .205" (5.21mm) terminals
- \*\*\*Dimensions with .187" (4.75mm) terminals

### Stud on End Case






tyco

Catalog 1308242 Issued 3-03 (PDF Rev. 1-06)


P&B

### **Outline Dimensions (Continued) Relay Front Diagrams**


#### 1-3 Pole Relays








#### 4 Pole Relays




#### **Terminal Dimensions**


.110" (2.79mm) Quick ConnectQuick Connect




#### .205" (5.21mm) **Quick Connect**




.250" (6.35mm)



#### Printed Circuit



.187" (4.75mm) **Quick Connect** 



Note: All drawings shown oversize

## **Wiring Diagrams**

\*1 Form X

1 Form C

\*2 Form A

\*2 Form C

3 Form C

4 Form C
















### PC Board Layouts (Bottom Views)


#### 1 Form X



### 3 Pole Models



### 4 Pole Models



<sup>\*</sup>Recommended Load Polarity for Optimum Arc Suppression.



**tyco** Catalog 1308242

 Electronics
 Issued 3-03 (PDF Rev. 1-06)
 **P&B**

### Sockets For KU Series Relays Through 3 Poles

#### Socket Selection Table Stock items are boldfaced.

For KUP, KUEP, KUGP, KUIP, and KUMP relays, through 3 poles, with .187" (4.75mm) quick connect termination.


Socket	Socket Termination	Hold-Down Spring
27E043	Solder eyelet	20C228 or 20C254*
27E046	PC board, .144" (3.66mm) terminals	20C228 or 20C254
27E067	.187" (4.75mm) quick connect	20C228 or 20C254
27E121	Screw terminals	20C314 (2 per socket required)
27E305	PC board, .184" (4.67mm) terminals	20C228 or 20C254
<b>27E396</b> .187" (4.75mm) quick connect*		20C254
27E893	Screw terminals†	20C318

- \* 20C228 held in place by socket hold-down screw where as 20C254 snaps onto socket.
- \*\* Snap-in mounting
- † DIN rail mounting

### **Hard Mount Sockets For Relays Through 3 Poles**


Nylon sockets with .187" (4.75mm) quick connect, solder or printed circuit terminals are available for KUEP, KUGP, KUIP, KUMP, and KUP relays, through 3 poles, with .187" (4.75mm) quick connect terminals. All are rated 15 amps and UL recognized, File E59244 and CSA certified File LR15734

27E043—with solder eyelet terminals. 27E067—with .187" (4.75mm) quick connect terminals.




**Suggested Socket** 

**PC Board Layout** 



The 27E043 and 27E067 use chassis cutout shown on this page.

#### 27E046, 27E305 Socket With Printed Circuit Terminals




#### 27E396 Snap-In Socket For Relays Through 3 Poles


Nylon snap-in socket with .187" (4.75mm) quick connect terminals is available for KUEP, KUGP, KUIP, KUMP, and KUP relays, through 3 poles, with .187" (4.75mm) quick connect terminals. Snap-in sockets reduce labor by eliminating time consuming screw or rivet mounting. Preassembled wiring harnesses may also be used as the sockets are designed to snap into the chassis from either front or back. All are rated 15 amps and UL recognized, File E59244. The 27E396 uses chassis cutout shown on this page.

27E396-with .187" (4.75mm) quick connect terminals.


# Recommended Chassis Cutout For Hard Mount Sockets



# Recommeded Chassis Cutout For Snap-In Sockets



Recommended chassis thickness .031" (.79mm) to .062" (1.57mm).



P&B

Catalog 1308242 Issued 3-03 (PDF Rev. 1-06) tyco Electronics

### Sockets For KU Series Relays Through 3 Poles (continued)


#### **Screw Terminal Socket**

The 27E121 socket offers screw termination for KUEP, KUGP, KUIP, KUL, KUMP and KUP relays, through 3 poles, with .187" (4.75mm) quick connect terminals. This socket stacks on 1.700" (43.18mm) centers. When surface mounting, two #6-32 screws of suitable length are required. When track mounting, two 24A071 retainer clips (not shown) are required. The 27E121 is rated 15 amps and is UL recognized, File E59244, CSA certified. File LR15734.

#### Screw Terminal, Din Rail Snap-Mount Socket

(use with mounting track 24A110)

The 27E893 DIN rail, snap-mount socket offers screw termination for KUEP, KUGP, KUIP, KUL, KUMP and KUP relays, through 3 poles, with .187" (4.75mm) quick connect terminals. This socket is constructed with a spring-loaded latch which allows it to be quickly snapped onto or removed from a "top hat" style mounting track. No special tools or extra hardware is required for installation. The 27E893 is UL rated 15 amps, 94V-0, File E59244 and CSA rated 10 amps, File LR15734.



#### **Sockets For KU Series 4 Pole Relays**

#### **Socket Selection Table** Stock items are boldfaced

For 4 pole KUP relays with .110" (2.79mm) quick connect termination.


Socket	Socket Termianation	Hold-Down Spring
27E415	.187" (4.75mm) quick connect	20C228 or 20C254
27E419	PC board	20C228 or 20C254
27E867*	Screw terminals	20C254

<sup>\*</sup> Use 40G432 insulator pad or customer supplied alternative.


### Hard Mount Sockets For 4 Pole Relays

27E415-with .187" (4.75mm) guick connect/solder terminals. 27E419-with printed circuit terminals. See PC board lavout at right.

**Note:** Only 4 pole KUP relays with .110" (2.79mm) quick connect terminals can be used with 4 pole hard



#### **Suggested Socket PC Board Layout**



### **Screw Terminal Socket For 4 Pole Relays**

27E867 offers screw termination for 4 pole KUP relays with .110" (2.79mm) quick connect/socket mount terminals. Rated 10 amps and is UL recognized, File E59244.

