

Philips screwdriver - SF-PHSL 2-100 VDE - 1212288

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screwdriver, positive/negative PH slot, VDE insulated, size: PH 2 x 100, 2-component grip, with non-slip grip

Product Features

- VDE approval
- Screwdrivers for Phillips screws with Pozidriv and Phillips Recess screw head



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	100.0 g
Custom tariff number	82054000
Country of origin	Czech Republic

Technical data

Dimensions

Length (b)	205 mm
Width (a)	37 mm
Blade height	100 mm

General

Type	Phillips
	Straight
Material	Alloyed tool steel
Test standard	IEC 60900:2004

Standards and Regulations

Test standard	IEC 60900:2004
---------------	----------------

Philips screwdriver - SF-PHSL 2-100 VDE - 1212288

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301
eCl@ss 5.0	21040301
eCl@ss 5.1	21040301
eCl@ss 6.0	21043811
eCl@ss 7.0	21043811
eCl@ss 8.0	21040406

ETIM

ETIM 4.0	EC000144
ETIM 5.0	EC000144

UNSPSC

UNSPSC 6.01	27112118
UNSPSC 7.0901	27111518
UNSPSC 11	23171604
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518

Approvals

Approvals

Approvals

VDE Zeichengenehmigung / EAC

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung 
--

Philips screwdriver - SF-PHSL 2-100 VDE - 1212288

Approvals

EAC

Drawings

Pictogram

