


REV	DOCUMENT	CHANGED BY	CHECK
1	204327	WJC 07NOV01	SAV



- NOTES
- 1 - EXPLOSION PROOF - UNDERWRITERS LAB INC LISTING FOR HAZARDOUS LOCATIONS CLASS 1, GROUPS C AND D; CLASS 2 GROUPS E, F AND G
 - 2 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: EExd IIC T6 CATEGORY II 2 GD
 - 3 - ALUMINUM ENCLOSURE FINISHED WITH BLUE AND BLACK EPOXY PAINT
 - 4 - 6-32 UNC X (7.92) PAN HEAD TERMINAL SCREW AND LOCKWASHER (SEMS TERMI-LOX) (3 PER BASIC)
 - 5 - CAMS MAY BE REPOSITIONED IN 7°20' INCREMENTS
 - 6 - 1 BASIC; OPERATES CLOCKWISE AND COUNTER CLOCKWISE
 - 7 - FOR USE IN TEMPERATURES UP TO 85°C
 - 8 - SEE 7CX CHARTS 1 AND 2 (1 DRAWING) FOR LEVER ACTUATORS
 - 9 - WEIGHT: 2.49 LB (1.13 Kg) APPROX

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN		WJC		07NOV01		Honeywell Sensing and Control					
OPERATING TORQUE----- .922 LB FT (1.25 Nm) MAX		CONTACT ARRANGEMENT S P D T		NO PLACE X ±.040 ±1		CHECK		SAV		07NOV01							
RELEASE TORQUE----- .083 LB FT (0.113 Nm) MIN		L96 15A 125, 250 OR 480 VAC 1/8HP 125 VAC, 1/4HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC		ONE PLACE .X ±.030 ±0,4		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL SENSING AND CONTROL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.											
PRETRAVEL----- 15° MAX				TWO PLACE .XX ±.015 ±0,15													
DIFFERENTIAL TRAVEL----- 10° MAX				THREE PLACE .XXX ±.005 ±		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED											
OVERTRAVEL----- 90° MIN		ANGLES ± ±		RAW MATERIAL-COMMERCIAL STANDARD													
Ex CE UL CS		THIRD ANGLE PROJECTION				3D PTC		ASME Y14.5M-1994		SIZE		DWG TYPE		DRAWING NAME		REV	
						C		I		11CX1E		1					
										SCALE		FULL		WEIGHT		SHEET 1 OF 1	