

HONEYWELL

See full Datasheet below...






onlinecomponents.com
THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS

BUY NOW

 **MASTER**TM
ELECTRONICS

BUY NOW

masterelectronics.com & onlinecomponents.com
are **authorized** e-commerce distributors
of electronic components.



REVISION HISTORY					
REV	DOCUMENT	DESCRIPTION	CHGD BY	DATE	APPROVED
15	0129443	REDRAWN WITH CHANGE	RKA	2016-05-02	M. MANTUA

- NOTES:
- EXPLOSION PROOF - UNDERWRITER'S LAB INC. LISTED FOR HAZARDOUS NEMA 7, LOCATIONS CLASS I, GROUPS C AND D, NEMA 9, CLASS II, GROUPS E, F AND G
 - 8X MOUNTING SCREW HOLE 10-32 UNF-2B THREAD X (.219) DEEP
 - 8-32 UNC X (.219) TERMINAL SCREWS AND CUPWASHERS
 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: Ex d IIB+H2 T6 CATEGORY II 2G
 - SEAL RATING: NEMA I
 - EXTERNAL GROUND SCREW MAY BE ASSEMBLED TO ANY UNUSED MOUNTING SCREW HOLE
 - ASSEMBLE PROVIDED SPLIT LOCKWASHER BETWEEN GROUND LUG AND HOUSING
 - BRAZILIAN HAZARDOUS LOCATION DESIGNATION: Ex d IIB+H2 T6 Gb -40°C ≤ T_{amb} ≤ +70°C

CHARACTERISTICS	ELECTRICAL DATA
OPERATING FORCE----- 3 LB MAX	CONTACT ARRANGEMENT S P D T
RELEASE FORCE----- 3/4 LB MIN	
DIFFERENTIAL TRAVEL----- .004 MAX	-L9- 10A-125, 250, OR 480VAC 1/2A-125VDC; 1/4A-250VDC
OVERTRAVEL----- .188 MIN	
SWITCH-BASIC REPLACEMENT-- BZ-2R15-P4	

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES DECIMAL TOL NO PLACE --- ±.030 1 PLACE --- ±.015 2 PLACE --- ±.010 3 PLACE --- ±.005 ANGULAR TOL --- CHAMFER -		THIRD ANGLE PROJECTION			Honeywell SWITCH - ENCLOSED	
MATERIAL	FINISH	SIZE D				
APPLICABLE DOCUMENTS: ASME Y14.100-2013 ASME Y14.5-2009		SCALE 3:2	REF. WT.	SHEET 1 of 1	HONEYWELL CONFIDENTIAL <small>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSES WITHOUT WRITTEN PERMISSION FROM HONEYWELL</small>	
COMPUTER GENERATED DRAWING: PRO/ENGINEER		RELEASE DATE	DRW: OMW	RDE: -	OA: -	CHK: GCH