




Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

1TP33-7



Actual product appearance may vary.

TP Series Rocker Switch, 1 pole, 3 position, Screw terminal, Above Panel Mounting

Features

Environmentally sealed
Two and three-position pushbutton action
Various button colors
1, 2, and 4-pole circuitry
Flush panel and above panel mountings
Temperature range: -54 ° C to +71° C [- 65 ° F to +160° F]
UL recognized, CSA certified
CE approved

Potential Applications

Industrial machinery and equipment
Military and commercial aviation
Marine applications
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™ TP Rocker switches may be mounted flush with panel for a low-button profile or above panel for a distinct button appearance. Buttons measure 22,1 mm x 37,1 mm [.87 in x 1.46 in]. They are removable and interchangeable, and come in transparent plastic, translucent plastic, and six colors of opaque plastic. Switches without buttons are also available, as well as separate buttons.

Supporting Documentation

- Accessory: Rocker Operator
- Engineering Drawing

Product Specifications		
Circuitry/Operating action	Keyway Momentary Position Center Position Opposite Keyway Momentary Position	
Product Type	MICRO SWITCH™ Rocker	
Ampere/Voltage Range (Resistive Load)	0.75 A at 115 Vdc,0.5 A at 250 Vdc,0.5 A to 15 A at 0.5 Vdc to 28 Vdc,0.5 A to 10 A at 0.5 Vac to 7 Vac	
Circuitry	SPDT	
Action	3 position	
Mounting	Above Panel	
Termination	Screw	
Button Type	Colored	
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 250, 277 Vac; 3 A - 125 Vac "L"	
Comment	No mounting threads	
Availability	Global	
UNSPSC Code	302119	
UNSPSC Commodity	302119 Switches and controls and relays	
Series Name	TP	

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search