
Features

- Single or Polyphase Service
- Buzz-Free, Shaded AC Coil
- **High Dielectric Strength**
- Arc-Over Barrier Between Each Contact



4PDT, 4 Form "C"




AC OPERATED								
NTE Type No.	Nom. Volt.	Contact Arr.	Coil Res. Ohms (Typ)	Approx. Nom. Power	Max. Contact Cur. @ 277VAC	Diag No.		
RLY1663	24VAC	4PDT	5	14 VA	25A	D76		
RLY1665	120VAC	4PDT	120	14 VA	25A	D76		
RLY1666	240VAC	4PDT	600	14 VA	25A	D76		
DC OPERATED								
RLY1762	12VDC	4PDT	30	4.4W	25A	D76		
RLY1763	24VDC	4PDT	130	4.4W	25A	D76		

	ACCESSORIES						
STYLES	DESCRIPTION	CONTACT ARR.	NTE TYPE NO.				
DUST COVER	PLASTIC	4PDT	RLY9166				

RLY16/17 Series 51 (1)

Heavy Duty, Open Frame, 25 Amp, 4PDT, AC & DC Power Relays.

D76



Electrical Specifications

Contact

Rating: 25 Amp @ 277 VAC max, 10 Amp @ 28 VDC

1 HP @ 120/240 VAC, Single Phase

Material: Silver-cadmium oxide Resistance: 100mΩ Max

Coil Voltages: See Chart **Duty Cycle:** Continuous Resistance: See Chart

Operational Characteristics

Must Operate Voltage

AC Coil: 85% of nominal voltage @ +25°C DC Coil: 75% of nominal voltage @ +25°C Timing Value: ... Operate Time: 25 mS max

Release Time: 25 mS max

Insulation Characteristics

Dielectric Strength

Between All Elements and GND: 2000Vrms Min.

Insulation Resistance: $1000M\Omega$ Min.

Environmental Characteristics Operating

AC: -55°C to +45°C @ nominal coil power **DC:** -55°C to +55°C @ nominal coil power

Life

Mechanical: 10,000,000 operations (under rated load) Electrical: 100,000 operations (under rated load)

Mounting

Std: One front key-hole and two rear channel slots for #8-32 screws

Weight

Std: 14 oz (397 grams) approx.