

## D-SUB coaxial contact - VS-ST-KX-50-RG174 - 1655548

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Coaxial contact, for D-SUB combination inserts, solder cup, pin, straight, for cable RG 174, gold-plated

### Key Commercial Data

Packing unit	10 STK
GTIN	 4 046356 029476

### Technical data

#### Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
Connection method	Solder cup
Type of contact	Coaxial
Conductor cross section	0.5 mm <sup>2</sup>
Connection cross section AWG	20
External cable diameter	3.2 mm
Insertion force per signal contact	≤ 7.00 N
Extraction force per signal contact	≤ 7 N

#### Ambient conditions

Ambient temperature (operation)	-55 °C ... 135 °C
---------------------------------	-------------------

#### Material data

Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel

#### Electrical characteristics

Rated current	2 A
---------------	-----

### Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701

# D-SUB coaxial contact - VS-ST-KX-50-RG174 - 1655548

## Classifications

### eCl@ss

eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27261202
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204

### ETIM


ETIM 2.0	EC000796
ETIM 3.0	EC000796
ETIM 4.0	EC000796
ETIM 5.0	EC000796

### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	39121522
UNSPSC 11	39121522
UNSPSC 12.01	39121522
UNSPSC 13.2	39121522

## Drawings

Dimensional drawing



D-SUB coaxial contact pin

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>