

# Ethernet module - FL PSE 2TX - 2891013

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Factoryline Power-over-Ethernet modules (PSE) for midspan power supply according to IEEE 802.3af, two PoE supply ports, no configuration required, function possible with 10 and 100 Mbps networks

## Product Description

Power-over-Ethernet-Module (PSE) for midspan power supply according to IEEE 802.3af. The industrial Power-over-Ethernet modules enable the common transmission of power and data according to IEEE 802.3af via the Ethernet medium. Consequently, terminal equipment, such as WLAN or Bluetooth access points, IP telephones or IP cameras can be connected to the network quickly and economically. The FL PSE 2TX is a compact stand-alone solution that converts the two standard Ethernet ports to Power-over-Ethernet ports. The FL PSE 2TX is a Plug & Play device and generates the 48 V DC required for Power-over-Ethernet from the 24 V module supply according to IEEE 802.3af.

## Why buy this product

- Can be combined with Fast Ethernet switch
- Compact housing
- IEEE 802.3af

## Ethernet

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 076043

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	45 mm
Height	99 mm
Depth	112 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	30 % ... 95 % (non-condensing)

# Ethernet module - FL PSE 2TX - 2891013

## Technical data

### Ambient conditions

Permissible humidity (storage/transport)	30 % ... 95 % (non-condensing)
Air pressure (operation)	86 kPa ... 108 kPa (2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (3500 m above sea level)

### Interfaces

Interface 1	Ethernet
No. of ports	2 (PoE ports)
Connection method	8-pos. RJ45 socket
Transmission physics	Ethernet RJ45
Transmission speed	10/100 MBit/s
Transmission length	100 m (Between transmitter / receiver)
Signal LEDs	PoE detection

### Function

Basic functions	PSE/midspan, complies with IEEE 802.3af
Status and diagnostic indicators	LEDs: US, PoE detection per port

### Network expansion parameters

Maximum conductor length (twisted pair)	100 m
---	-------

### Supply voltage

Supply voltage	24 V DC (via COMBICON; max. conductor cross section 2.5 mm <sup>2</sup> )
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Supply voltage range	18.5 V DC ... 30.5 V DC
Typical current consumption	typ. 100 mA (During no load; approx. 1800 mA at 24 V at the input with maximum load and 25°C ambient temperature)

### General

Mounting type	DIN rail
Type AX	Stand-alone
Net weight	320 g
Housing material	Polyamide (PA 6.6)

### Standards and Regulations

Electromagnetic compatibility	Conformance with EMC Directive 2004/108/EC
Developed in acc. with standard	IEC 61000-6.2
Test standard	IEC 61000-4-2 (ESD)
Test result	Criterion B
Test standard	IEC 61000-4-3 (immunity to radiated interference)
Test result	Criterion A
Test standard	IEC 61000-4-4 (burst)
Test result	Criterion A
Test standard	IEC 61000-4-5 (surge)
Test result	Criterion B

# Ethernet module - FL PSE 2TX - 2891013

## Technical data

### Standards and Regulations

Test standard	IEC 61000-4-6 (immunity to conducted interference)
Test result	Criterion A
Test standard	IEC 61000-4-8 (immunity to magnetic fields)
Test result	Criterion A
Test standard	EN 55022 (emitted interference)
Test result	Criterion A
Test section	For one minute 1500 V AC 1 min.
Noise emission	EN 61000-6-4
Noise immunity	EN 61000-6-2:2005
Vibration (storage/transport)	5g, 150 Hz, in acc. with IEC 60068-2-6
Free from substances that could impair the application of coating	In acc. with VW specification
Connection in acc. with standard	CUL
Vibration (operation)	In acc. with IEC 60068-2-6: 5g, 150 Hz

## Classifications

### eCl@ss

eCl@ss 4.0	27250501
eCl@ss 4.1	27250501
eCl@ss 5.0	27250501
eCl@ss 5.1	27250501
eCl@ss 6.0	27250501
eCl@ss 7.0	19170190
eCl@ss 8.0	19170106

### ETIM

ETIM 2.0	EC000734
ETIM 3.0	EC000734
ETIM 4.0	EC000734
ETIM 5.0	EC000734

### UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201410
UNSPSC 13.2	43201410

## Approvals

### Approvals

# Ethernet module - FL PSE 2TX - 2891013

## Approvals

Approvals

UL Recognized / cUL Recognized / EAC / EAC / cULus Recognized

---

Ex Approvals


UL Listed / cUL Listed / cULus Listed


---

Approvals submitted

---


## Approval details

UL Recognized 

cUL Recognized 

EAC

EAC

cULus Recognized 

---

Phoenix Contact 2016 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>