

LED machine light - PLD M 260 W-85/95 365/D40 - 2702481

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



LED machine light, 24 V DC, Degree of protection IP67, Emission angle 85 °/95 °, Color temperature 5000 K, Length 365 mm, Diameter 40 mm, M12 connector, Light housing: Anodized aluminum, Pane: Single-pane safety glass (ESG, thermally toughened float glass), pivoting, Resistant to coolants and lubricants

Product Description

This LED machine light is designed to provide illumination inside or on machinery.

You can use the light in harsh environments.

This is possible thanks to:

- The high degree of protection
- Resistance to common cooling agents and lubricants
- Resistance to vibrations and shock
- The 4 mm thick safety glass

The small diameter of just 40 mm enables mounting even where space is at a premium.

Mounting is by means of holders or brackets (neither of which are supplied as standard) in which the light can swivel and the lighting can therefore be optimally aligned.

Why buy this product

- ✓ Space saving, thanks to the small diameter
- ✓ Plug-in supply line enables free choice of the cable length as well as quick and easy installation
- ✓ Focused illumination, thanks to swivel action
- ✓ IP67 protection and resistance to cooling agents and lubricants enables use in machine tools
- ✓ Can be used at high temperatures and can be subjected to strong vibrations and shocks
- ✓ Safety glass enables use even in environments with potential mechanical strain
- ✓ ETL approval permits use on the North American market
- ✓ Particularly economical thanks to energy-efficient LED technology and an LED service life of at least 60,000 h

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 247809
GTIN	4055626247809
Weight per Piece (excluding packing)	700.000 g

LED machine light - PLD M 260 W-85/95 365/D40 - 2702481

Custom tariff number	94054099
Country of origin	Germany

Technical data

Dimensions

Width	40 mm
Height	30 mm
Length	365 mm
Note on dimensions	Length without M12 flush-type connector

Ambient conditions

Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	95 %
Permissible humidity (storage/transport)	95 % (non-condensing)
Air pressure (operation)	69 kPa ... 102 kPa
Air pressure (storage/transport)	69 kPa ... 102 kPa
Degree of protection	IP67

General

Note	The PLD M-ME MC/D40 mounting holder (Order No. 2702491) or the PLD M-ME MB/D40 mounting bracket (Order No. 2702527) is required in order to mount the light.
Net weight	500 g
Mounting type	Screw mounting
Assembly instructions	Mounting with mounting holders or mounting brackets, please observe the notes in the package slip.

Power supply for module electronics

Connection method	M12 connector, (A-coded)
	M12 connector, (A-coded)
Number of positions	4
Permissible conductor cross section	min. 0.34 mm²
Supply voltage	24 V DC
Supply voltage range	20 V DC ... 28 V DC
Current consumption	typ. 0.44 A (at 24 V DC)
Power consumption	approx. 10.5 W (at 24 V DC)
Type of protection	Surge protection

Connection data

Connection method	M12 connector, (A-coded)
-------------------	--------------------------

Light properties

LED machine light - PLD M 260 W-85/95 365/D40 - 2702481

Technical data

Light properties

Source of light type	LED
Number of LEDs	27
Service life, lighting appliance	60000 h (L70)
Light color	Neutral white
Color temperature	5000 K
Color rendering index	80
Luminous flux	approx. 1080 lm (Net luminous flux)
Illumination	max. 477 lx (Distance of 1 m)
Average illumination	348 lx (Distance of 1 m over 1 m² area)
Emission angle	85 ° (C0-C180)

Standards and Regulations


Mechanical tests	Vibration resistance in acc. with EN 60068-2-6/IEC 60068-2-6 4g
	Shock in acc. with EN 60068-2-27/IEC 60068-2-27 50g
Protection class	III, IEC 61140, EN 61140, VDE 0140-1

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Approvals

Approvals

Approvals

ETLus / cETL / cETLus

Ex Approvals

LED machine light - PLD M 260 W-85/95 365/D40 - 2702481

Approvals

Approval details

ETLus		http://www.intertek.com	LV-Lighting-Systems
cETL		http://www.intertek.com	Luminaires
cETLus		http://www.intertek.com	