




### Turn-Tell® Labels



- Allows labels to rotate for visibility from any angle, and allows repositioning on the wire/cable to align legends for improved aesthetics
- Ideal for use in high-density or space-constrained cable applications
- Use thermal transfer hybrid ribbon
- Temperature range: -40°F to 200°F (-40°C to 107°C)

Part Number	Part Description	Width		Length		Print-On Area Height		Min. Cable O.D.		Max. Wire O.D.		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm		
R050X075V1T	Thermal Transfer, Vinyl, 0.50" W x 0.75" H, 0.25" POA, Clear/White, 3" Core, 18 – 14 AWG wire/cable.	0.50	12.7	0.75	19.1	0.25	6.4	0.12	3.1	0.16	4.1	5000	20000
R050X125V1T	Thermal Transfer, Vinyl, 0.50" W x 1.25" H, 0.38" POA, Clear/White, 3" Core, 12 – 10 AWG wire/cable, Cat. 3 UTP cable.	0.50	12.7	1.25	31.8	0.38	9.7	0.12	3.1	0.16	4.1	5000	20000
R050X150V1T	Thermal Transfer, Vinyl, 0.50" W x 1.50" H, 0.50" POA, Clear/White, 3" Core, 10 – 6 AWG wire/cable, Cat. 5e/6/6e UTP and Cat. 5e FTP cable.	0.50	12.7	1.50	38.1	0.50	12.7	0.16	4.0	0.32	8.1	5000	20000
R100X075V1T	Thermal Transfer, Vinyl, 1.00" W x 0.75" H, 0.25" POA, Clear/White, 3" Core, 18 – 14 AWG wire/cable.	1.00	25.4	0.75	19.1	0.25	6.4	0.12	3.1	0.16	4.1	2500	10000
R100X125V1T	Thermal Transfer, Vinyl, 1.00" W x 1.25" H, 0.38" POA, Clear/White, 3" Core, 12 – 10 AWG wire/cable, Cat. 3 UTP cable.	1.00	25.4	1.25	31.8	0.38	9.7	0.16	4.1	0.22	5.6	2500	10000
R100X150V1T	Thermal Transfer, Vinyl, 1.00" W x 1.50" H, 0.50" POA, Clear/White, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	2500	10000
R100X150V2T	Thermal Transfer, Vinyl, 1.00" W x 1.50" H, 0.50" POA, Clear/Blue, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	2500	10000
R100X150V3T	Thermal Transfer, Vinyl, 1.00" W x 1.50" H, 0.50" POA, Clear/Green, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	2500	10000
R100X150V7T	Thermal Transfer, Vinyl, 1.00" W x 1.50" H, 0.50" POA, Clear/Red, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	2500	10000
R100X150V8T	Thermal Transfer, Vinyl, 1.00" W x 1.50" H, 0.50" POA, Clear/Yellow, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.	1.00	25.4	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	2500	10000
R100X225V1T	Thermal Transfer Vinyl, 1.00" W x 2.25" H, 0.75" POA, Clear/White, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	1.00	25.4	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	2500	10000
R100X225V2T	Thermal Transfer, Vinyl, 1.00" W x 2.25" H, 0.75" POA, Clear/Blue, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	1.00	25.4	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	2500	10000
R100X225V3T	Thermal Transfer, Vinyl, 1.00" W x 2.25" H, 0.75" POA, Clear/Green, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	1.00	25.4	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	2500	10000
R100X225V7T	Thermal Transfer, Vinyl, 1.00" W x 2.25" H, 0.75" POA, Clear/Red, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	1.00	25.4	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	2500	10000
R100X225V8T	Thermal Transfer, Vinyl, 1.00" W x 2.25" H, 0.75" POA, Clear/Yellow, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	1.00	25.4	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	2500	10000


Order number of labels required, in multiples of Standard Package Quantity.

Table continues on page O.20

**Turn-Tell<sup>®</sup> Labels (continued)**

Part Number	Part Description	Width		Length		Print-On Area Height		Min. Cable O.D.		Max. Wire O.D.		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	In.	mm	In.	mm	In.	mm		
<b>R100X400V1T</b>	Thermal Transfer, Vinyl, 1.00" W x 4.00" H, 1.00" POA, Clear/White, 3" Core, 2 AWG – 250 MCM wire/cable.	1.00	25.4	4.00	101.6	1.00	25.4	0.39	9.9	0.95	24.1	1000	4000
<b>R200X150V1T</b>	Thermal Transfer, Vinyl, 2.00" W x 1.50" H, 0.50" POA, Clear/White, 3" Core, Cat. 5e/6/6A UTP/Cat. 5e FTP cable.5/5e/6 cable.	2.00	50.8	1.50	38.1	0.50	12.7	0.22	5.6	0.28	7.1	1000	4000
<b>R200X225V1T</b>	Thermal Transfer, Vinyl, 2.00" W x 2.25" H, 0.75" POA, Clear/White, 3" Core, 8 – 4 AWG wire/cable, Cat. 6A UTP, FTP/Cat. 6 FTP cable.	2.00	50.8	2.25	57.2	0.75	19.1	0.28	7.1	0.39	9.9	1000	4000
<b>R200X400V1T</b>	Thermal Transfer, Vinyl, 2.00" W x 4.00" H, 1.00" POA, Clear/White, 3" Core, 2 AWG – 250 MCM wire/cable.	2.00	50.8	4.00	101.6	1.00	25.4	0.39	9.9	0.95	24.1	1000	4000


Order number of labels required in multiples of Standard Package Quantity.

**Thermal Transfer Marker Plates**

- Non-adhesive halogen-free marker plates used to identify wires, cables, equipment, and many other applications
- Offers crisp, clear legend with superior legibility and engineered to withstand high temperatures, harsh solvents, oils, and chemicals without over-lamination
- Attachable in horizontal or vertical orientation
- Available in a variety of colors and sizes
- Temperature range: -58°F to 221°F (-50°C to 105°C)
- Use with Panduit thermal transfer resin ribbons

Part Number	Color							Width In. (mm)	Height In. (mm)	Print-On Area Width In. (mm)	Labels Per Roll	Std. Pkg. Qty.
	Yellow	White	Blue	Green	Gray	Orange	Red					
<b>M200X050*</b>	Y6T	Y7T	ACT	AET	AFT	AGT	AIT	2.00 (50.8)	0.50 (12.7)	1.07 (27.2)	500	1 Roll
<b>M200X100*</b>	Y6T	Y7T	ACT	AET	AFT	AGT	AIT	2.00 (50.8)	1.00 (25.4)	0.80 (20.3)	500	1 Roll
<b>M300X050*</b>	Y6T	Y7T	ACT	AET	AFT	AGT	AIT	3.00 (76.2)	0.50 (12.7)	2.07 (52.6)	500	1 Roll
<b>M300X100*</b>	Y6T	Y7T	ACT	AET	AFT	AGT	AIT	3.00 (76.2)	1.00 (25.4)	1.80 (45.7)	500	1 Roll

Replace the asterisk in part numbers above with the desired color code.

**Thermal Transfer Flag Labels**

- Halogen-free, polyester flag-style marker for wire/cable labeling
- Improved legibility and more information on small wires and cables provide clearer, more complete identification
- Innovative design allows the product to be applied as a permanent adhesive label or as a repositionable non-adhesive label
- Temperature range: -40°F to 302°F (-40°C to 150°C)
- UL969 recognized, File # MH14576 and File # MH14979; cUL recognized C22.2 No 0.15-01, File # MH14979
- Use with Panduit thermal transfer resin ribbons

Part Number	Color	Width		Height		Min. Cable O.D.		Max. Cable O.D.		Wire Range	Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm	In.	mm	In.	mm			
<b>F100X150AJT</b>	White	1.00	25.4	1.50	38.1	0.12	3.1	0.20	5.1	12 – 10 AWG	2500	10000
<b>F100X213AJT</b>	White	1.00	25.4	2.13	54.1	0.32	8.1	0.38	9.7	3 – 2 AWG	2500	10000
<b>F100X300AJT</b>	White	1.00	25.4	3.00	76.2	0.90	2.3	0.28	7.1	8 – 4 AWG	2500	10000
<b>F100X363AJT</b>	White	1.00	25.4	3.63	92.2	0.20	5.1	0.46	11.7	2 – 1 AWG	2500	10000

Order number of pieces required, in multiples of Standard Package Quantity.

Prime items appear in **BOLD**.