




HARNESSING

HEAT SHRINK BOOTS



✓ Active

TE CONNECTIVITY (TE)

202A163-25/225-0

Raychem | CAP , CRPS

202A163-25/225-0

TE Internal Number: 891199-000

Alias ID: 8-1196931-5

EU RoHS Compliant

EU ELV Compliant

Lipped No

Operating Temperature Range (°C) -75 – 150

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /225 Precoat, -75 – 150°C (-103 – 302°F)

Material Systems Code 10

[↓](#) **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

Boot, Straight, Overexpanded

PDF

English

Product Specifications

Product Specification

Thermofit Elastomeric Molded Components Flame-Retarded, Semi-Rigid, Heat-Shrinkable

PDF

English

-25 MOULDED PARTS

PDF

English

Product Environmental Compliance

Safety Data Sheet

Unicure 225 Adhesive

PDF

English

Unicure 225 Adhesive

PDF

French

Unicure 225 Adhesive

PDF

German

Unicure 225 Adhesive

PDF

Italian

Unicure 225 Adhesive

PDF

Spanish

Unicure 225 Adhesive

PDF

Swedish

Unicure 225 Adhesive

PDF

Dutch

Unicure 225 Adhesive

PDF

Danish

EPS Heat Shrinkable Polymeric Products

PDF

English

EPS Heat Shrinkable Polymeric Products

PDF

French

EPS Heat Shrinkable Polymeric Products

PDF

German

EPS Heat Shrinkable Polymeric Products

PDF

Italian

EPS Heat Shrinkable Polymeric Products

PDF

Norwegian

EPS Heat Shrinkable Polymeric Products

PDF

Spanish

EPS Heat Shrinkable Polymeric Products

PDF

Swedish

EPS Heat Shrinkable Polymeric Products

PDF

Dutch

EPS Heat Shrinkable Polymeric Products

PDF

Danish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type Molded Boot

Configuration Features

Lipped No

Body Features

Material Systems Code 10

Adhesive Pre-Coat Yes

Material Modified Polyolefin

Dimensions

Cable Diameter Range 9.4 – 27.2 mm [.37 – 1.071 in]

Wire/Cable Outside Diameter .43 in, .433 in, .47 in, .55 in, .63 in, .7 in, .71 in, .787 in, 11 mm, 12 mm, 14 mm, 16 mm, 18 mm, 20 mm

Usage Conditions

Operating Temperature Range (°C) -75 – 150

Operation/Application

Power Cable Accessory No

Industry Standards

Government Qualified No

Approved Standards BS-G-198-5-DE, DEF Std 59-97 Issue 3 Type DE, IEC 62329-3-102, MIS-34867

Other

Fluid/Chemical Resistance Suitable for long term fluid exposure at elevated temperatures

Adhesive Options /225 Precoat, -75 – 150°C (-103 – 302°F)

Adhesive Type High Performance Pre-Coat Adhesive

Statement of Compliance

Statement of Compliance

PDF