

Protective hose - WP-PA HF 15,8 BK - 3240682

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Polyamide protective hose, inflammability class V0, UV resistant

Image shows WP-PA HF 13.0 BK version

Key Commercial Data

Packing unit	1 M
Minimum order quantity	50 M
Weight per Piece (excluding packing)	1.0 g
Custom tariff number	39173200
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	12.00 mm
Outside diameter	15.80 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 115 °C
Short-term temperature	150 °C

General

Color	black
Type	Helically corrugated plastic hose
Components	free from silicone, halogen, and cadmium
Flammability rating according to UL 94	V0
Material	PA
Bending radius, static	35.00 mm
Bending radius, dynamic	55.00 mm

Standards and Regulations

Resistance to UV radiation	yes
----------------------------	-----

Protective hose - WP-PA HF 15,8 BK - 3240682

Technical data

Standards and Regulations

Halogen-free	yes
Connection in acc. with standard	UL
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Approvals

Approvals

UL Recognized / VDE Zeichengenehmigung / LR / DNV

Ex Approvals

Protective hose - WP-PA HF 15,8 BK - 3240682

Approvals

Approvals submitted

Approval details

UL Recognized 

VDE Zeichengenehmigung 

LR

DNV