





MLF1608DR33KTA00

Applications	 Commercial Grade
Feature	 Multilayer
	 Magnetic Shield
	 Ferrite Core
Series	MLF Series / MLF1608 Type
Status	Production



Size	
Length(L)	1.60mm +/-0.15mm
Width(W)	0.80mm +/-0.15mm
Thickness(T)	0.80mm +/-0.15mm
Recommended Land Pattern (A)	0.60mm Nom.
Recommended Land Pattern (B)	0.80mm Nom.
Recommended Land Pattern (C)	0.80mm Nom.


Electrical Characteristics	
Inductance	330nH +/-10% at 25MHz
Rated Current	100mA
Self-Resonant Frequency [Min.]	230MHz
Self-Resonant Frequency [Typ.]	320MHz
Q [Min.]	15 at 25MHz
Q [Typ.]	25 at 25MHz
DC Resistance [Nom.]	400mΩ
DC Resistance [Max.]	750mΩ

Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	4000Pcs Min.
Weight	0.004g


•This PDF document was created based on the data listed on the TDK Corporation website.
 •All specifications are subject to change without notice.

MLF1608DR33KTA00

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLF1608DR33KTA00



MLF1608DR33KTA00



MLF1608DR33KTA00




MLF1608DR33KTA00

- This PDF document was created based on the data listed on the TDK Corporation website.
- All specifications are subject to change without notice.

MLF1608DR33KTA00

Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



•This PDF document was created based on the data listed on the TDK Corporation website.
•All specifications are subject to change without notice.