## **HOME THEATRE** connectors & adaptors

				HOME THEAT	TRE PLUGS 8	& JACKS		
fig. 1	fig. fig fig. fig.	1 1 1 1	45-142G 45-162G 45-163G 45-166G	RCA Jack, Bulkhead .375" mounting hole. (2) Pack = (1) ea. Red + White, Gold plated RCA Jack, Bulkhead .375" mounting hole. (1) ea. Red + White + Yellow, Gold plated RCA Jack, Bulkhead .375" mounting hole; (2) Pack Orange, Gold plated RCA Jack, Bulkhead .375" mounting hole; (1) each Red, Green & Blue, Gold plated				
J	fig. fig	1	42-342 42-362	RCA Jack, Bulkhead .375" mounting hole. (2) Pack = (1) ea. Red + White Nickel Plated RCA Jack, Bulkhead .375" mounting hole. (1) ea. Red + White + Yellow Nickel Plated				
Silver.	fig fig.	1 1 2	42-352 42-366 45-109G	RCA Jack, Bulkhead .375" mounting hole. (2) Pack Yellow Nickel Plated RCA Jack, Bulkhead .375" mounting hole; (1) each Red, Green & Blue Nickel Plated RCA Jack, panel mounting with Teflon insulator. Package 1 red and 1 black.				
	fig. fig. fig.	3	45-270 45-273	RCA Jack, panel mounting, standard insulator. Pkg. of 1 ea. red, yellow, white.  Component Video RCA Jack Mt. in .25" Hole w/Std insulator. (3) Pack = (1) Red + Blue + Green				
fig. 2	fig.	3	45-276	RCA Jack Mt. in .25" Hole w/Std insulator. (6) Pack = (1) ea. Red, White, Yellow, Black, Green, Blue				
	fig.	4	45-229G	Binding Post, insulated. Accepts wire or banana plug. Pkg. 1 ea. red & black.				
En SCO	fig. fig.	5 6	45-230G 45-232G	Binding Post, all metal. Gold w/color bands. Package 1 ea. red and black.  Solderless Metal Binding Post, .375" mounting hole. Red and black color band.				
fig. 3	fig.	7	45-239G	Package of Two.  Low profile Banana Jacks with set screw terminal. Will accept up to 12 Ga. speaker wire.  Package 1 each Red & Black.				
_	fig.	8	45-235G	Banana Jacks. Mount in .25" hole. Package of 1 each red and black.				
	fig.		45-120G	Mono (2 conductor) Standard 1/4" Phone Plug; with strain relief spring. Package 1 each red and black.				
	fig.	10 11	<ul> <li>45-121G Mono (2 conductor) mini-1/8" Phone Plug; w/rubber strain relief. Pkg. of 2.</li> <li>45-123G Mono (2 conductor) mini-1/8" in-line Phone Jack; w/strain relief. Pkg. of 2.</li> </ul>					
fig. 4	fig.	12	45-132G	Stereo Phone Plug (3 conductor), standard 1/4" with spring strain relief.  Package of 1 red & 1 black.				
- 05 1 5 1 1 1 mm	fig. 13 45-122 Mono (2 conductor) Phone Jack , standard 1/4" in-line type with spring strain relief. Package 1 re and 1 black.						ain relief. Package 1 red	
	fig.	14	45-135	Stereo (3 conductor) Phone Jack, standard 1/4" in-line type with spring strain relief. Package 1 red and 1 black.				
fig. 5	fig.	15	45-133G	Stereo (3 conductor) Phone Plug, mini 1/8" with rubber strain relief. Pkg. of 2.				
	fig. fig.	16 17	45-134G 45-136G	Stereo (3 conductor) Phone Jack, 1/4" - panel mounting, open circuit.  Stereo (3 conductor) Phone Jack, mini 1/8" in-line type with rubber strain relief. Package of 2.				
	fig.	18	45-310G	Double RCA male adaptor; plug on each end. Package of 1 red and 1 black.				
	fig.	19	45-810G	Spade Lugs, handles up to 10 ga. wire. Package 1 black & 1 red.				
- 34 Missi Birk	fig.	20	45-811G	Single Banana Plug 1 Pair red & black. Plastic handle				
fig. 6	fig.	21 22	45-812G 45-813G	Banana Plugs, for wire up to 10 gauge. Package 1 red & 1 black.				
	fig. fig.	23	45-814G	Speaker Pin Plug 1 Pair red & black Pin Plugs, for wire up to 10 gauge. Package 1 red & 1 black. Plastic handle				
	fig.	24	45-816G	Ring Terminals for wire up to 10 gauge.				
9 9	fig.	25	45-820G	Ring Terminals for 12 to 10 ga. wire; hole size #10. Package 2 red & 2 black. Plastic handle				
	fig.	26	45-818G	Gold Coupler for perfectly joining two wires up to 10 gauge.				
	fig.	27	45-280	Gold Spade Terminal. Attach under a speaker screw (etc.) and permits connecting wires up to 10 gauge with no loss in fidelity.				
fig. 7	fig.	28	45-822G	Spade Terminals for 12 to 10 ga. wire; hole size #10. Package 2 red & 2 black. Plastic handle				
- Bio	annune.	time-	-0	THE RESERVE		***************************************	Manual Control of the	
					The state of the s	0		
fig. 8	fig. 9		. 9	fig. 10	fig. 11		fig. 12	
fig. 13	fig. 14		fig. 14	fig. 15	fig. 16	fig. 17	fig. 18	
				The state of the s				

fig. 22

fig. 26

fig. 23

fig. 28

fig. 27

66

fig. 19

fig. 20

fig. 24

fig. 21

fig. 25