



### enabling technologies

[10 Gig Ethernet](#)  
[Data Centers](#)  
[Fiber System Deployment](#)  
[Grounding System for Data Centers](#)  
[Industrial Ethernet](#)  
[Managing the Physical Layer](#)  
[Network Security](#)  
[Power Over Ethernet](#)

### product information

[Products](#)  
[Bill of Material](#)  
[My Catalog](#)  
[Part Search](#)  
[Cross Reference](#)  
[FAQ's](#)  
[Download / Request Literature](#)  
[Downloads](#)

### resources to help you

[Evaluate Technologies](#)  
[Design a Solution](#)  
[How to Buy](#)  
[Evaluate, Design & Install Products](#)  
[Download Panduit Logo](#)  
[White Papers](#)  
[RoHS Compliance](#)

### value added services

[Strategic Alliance Program](#)  
[Consultants](#)  
[Distributors](#)  
[Installers](#)  
[System Integrators](#)  
[Warranties](#)

### Product Information: Products

[USA](#) | [Heat Shrink & Abrasion Protection](#) | [Heat Shrink](#) | [General Purpose, Flexible Polyolefin for Dry Locations](#) | **Heat Shrink in 6 In. Pieces; Yellow/Green Stripe, Multiple Diameters**



- Small package fits easily in tool box
- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes
- Cross-linked, UV resistant material improves flame retardancy, chemical, and temperature resistance
- Available in various colors for permanent, cost effective color coding

\*\*\* Meets Mil Spec AMS-DTL-23053/5 Class 1.

Part Number	HSTT-YK2-45
Product Family	Heat Shrink in 6 In. Pieces; Yellow/Green Stripe, Multiple Diameters
RoHS Compliant	Compliant
Part Description	Yellow/Green 6" Pieces Thin Wall Polyolefin Heat Shrink
Material	Flame retardant polyolefin cross-linked*
Color	Yellow/Green
Military Specification	AMS-DTL-23053/5 Class 1
Length (In.)	6.00
Length (mm)	152.4
Flammability Rating	Flame Retardant
Max. Recovered I.D. (In.)	—
Max. Recovered I.D. (mm)	—
Min. Expanded I.D. (In.)	—
Min. Expanded I.D. (mm)	—
Nominal Diameter / Size	Various - Larger Range
Nominal Recovered Wall Thickness (In.)	—
Nominal Recovered Wall Thickness (mm)	—
Shrink Ratio	2:1
Std. Pkg. UOM	PK
Temperature Range	-67°F to 275°F (-55°C to 135°C)
UOM	PK
Std. Pkg. Qty.	1

### evaluate

[FAQs](#)

### design a solution

### install & maintain

[Installation Instructions](#)

Min. Order Qty

1

BOM Qty. (# of Pkgs.)

Add to My Catalog

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2005, PANDUIT CORP. All rights reserved.