



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

## Internet Office 120V 50/60Hz 300VA 150W Standby UPS, Ultra-Compact Desktop 6 Outlets, Tel/DSL/Ethernet Protection, TAA

MODEL NUMBER: INTERNETOFFICE300



### Highlights

- 300VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets
- TAA Compliant

### Package Includes

- INTERNETOFFICE300 UPS System
- Phone cable
- Instruction manual

### Description

Tripp Lite's INTERNETOFFICE300 UPS System provides complete power protection for your entire computer set-up. 300 VA power capacity maintains your Internet connection allowing you to work online through short blackouts or safely shut down during longer ones. Unique design features 6 outlets (3 UPS & surge + 3 surge-only outlets) and diagnostic LEDs. Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment. A 6-ft. telephone cord is also included. \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment.

### Features

- 300 VA output power rating (150 watts)
- Up to 11 minutes backup time (single PC; 15-in monitor)
- Battery run time: 10 minutes half load/4 minutes full load
- 6 protected outlets (3 UPS & surge + 3 surge-only outlets); 6-ft. cord
- Built-in RJ45 jacks prevent surges from damaging your modem/fax/10BT equipment; 6-ft. telephone cord included
- Complete surge protection and EMI/RFI noise filtering
- \$100,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- 5 diagnostic LEDs indicate AC present, line fault, on battery, overload and battery low/replace
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

## Specifications

| OVERVIEW                                        |                                     |
|-------------------------------------------------|-------------------------------------|
| UPC Code                                        | 037332096654                        |
| UPS Type                                        | Standby                             |
| OUTPUT                                          |                                     |
| Output Volt Amp Capacity (VA)                   | 300                                 |
| Output Watt Capacity (Watts)                    | 150                                 |
| Nominal Voltage Details                         | 120v nominal output in battery mode |
| Frequency Compatibility                         | 50 / 60 Hz                          |
| Frequency Compatibility Details                 | Automatic frequency selection       |
| Output Voltage Regulation (Battery Mode)        | +/- 5%                              |
| UPS Output Receptacles (Surge Suppression Only) | 3 UPS outlets, 3 surge-only outlets |
| Output Circuit Breakers                         | 15A                                 |
| Hot-Swap PDU options                            | PDUB15 (2U / 8 5-15R outlets)       |
| Output AC Waveform (AC Mode)                    | Sine wave                           |
| Output AC Waveform (Battery Mode)               | PWM sine wave                       |
| Nominal Output Voltage(s) Supported             | 110V; 115V; 120V                    |
| Output Receptacles                              | (6) 5-15R                           |
| Individually Controllable Load Banks            | No                                  |
| INPUT                                           |                                     |
| Rated input current (Maximum Load)              | 12A                                 |
| Nominal Input Voltage(s) Supported              | 120V AC                             |
| UPS Input Connection Type                       | 5-15P                               |
| UPS Input Cord Length (ft.)                     | 6                                   |
| UPS Input Cord Length (m)                       | 1.8                                 |
| Recommended Electrical Service                  | 15A 120V                            |
| Input Phase                                     | Single-Phase                        |
| BATTERY                                         |                                     |
| Full Load Runtime (min.)                        | 4 min. (150w)                       |
| Half Load Runtime (min.)                        | 10 min. (75w)                       |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                                               |                                                            |
|---------------------------------------------------------------|------------------------------------------------------------|
| DC System Voltage (VDC)                                       | 12                                                         |
| Expandable Runtime                                            | No                                                         |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b>                  |                                                            |
| Switches                                                      | Power off / on switch                                      |
| LED Indicators                                                | 5 LEDs indicate complete UPS operational status            |
| <b>SURGE / NOISE SUPPRESSION</b>                              |                                                            |
| UPS AC Suppression Joule Rating                               | 380                                                        |
| UPS AC Suppression Response Time                              | Instantaneous                                              |
| UPS Dataline Suppression                                      | 1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet       |
| EMI / RFI AC Noise Suppression                                | Yes                                                        |
| AC Suppression Joule Rating                                   | 380                                                        |
| AC Suppression Response Time                                  | Instantaneous                                              |
| Dataline Suppression                                          | 1 line TEL / DSL or 10Base T Ethernet protection           |
| <b>PHYSICAL</b>                                               |                                                            |
| Installation Form Factors Supported with Included Accessories | Tower; Ultra-compact desktop; Wallmount                    |
| Primary Form Factor                                           | Desktop                                                    |
| Primary UPS Depth (mm)                                        | 114                                                        |
| Primary UPS Height (mm)                                       | 66                                                         |
| Primary UPS Width (mm)                                        | 279                                                        |
| Shipping Dimensions (hwd / cm)                                | 10.41 x 20.32 x 32.77                                      |
| Shipping Dimensions (hwd / in.)                               | 4.10 x 8.00 x 12.90                                        |
| Shipping Weight (kg)                                          | 2.40                                                       |
| Shipping Weight (lbs.)                                        | 5.30                                                       |
| UPS Housing Material                                          | ABS                                                        |
| UPS Power Module Dimensions (hwd, cm)                         | 6.60 x 27.94 x 11.43                                       |
| UPS Power Module Dimensions (hwd, in.)                        | 2.6 x 11 x 4.5                                             |
| UPS Power Module Weight (kg)                                  | 1.81                                                       |
| UPS Power Module Weight (lbs.)                                | 4                                                          |
| <b>ENVIRONMENTAL</b>                                          |                                                            |
| Operating Temperature Range                                   | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |
| Storage Temperature Range                                     | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                                            |                                                                                                                           |
|------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Relative Humidity                                          | 0 to 95%, non-condensing                                                                                                  |
| AC Mode Efficiency Rating (100% Load)                      | 94%                                                                                                                       |
| <b>COMMUNICATIONS</b>                                      |                                                                                                                           |
| Communications Interface                                   | None                                                                                                                      |
| <b>LINE / BATTERY TRANSFER</b>                             |                                                                                                                           |
| Transfer Time                                              | 2-4 milliseconds                                                                                                          |
| Low Voltage Transfer to Battery Power (Setpoint)           | 99V                                                                                                                       |
| High Voltage Transfer to Battery Power (Setpoint)          | 141V                                                                                                                      |
| <b>CERTIFICATIONS</b>                                      |                                                                                                                           |
| UPS Certifications                                         | Meets FCC Part 15 Category B (EMI); TAA Compliant; Tested to CSA (Canada); Tested to NOM (Mexico); Tested to UL1778 (USA) |
| <b>WARRANTY</b>                                            |                                                                                                                           |
| Product Warranty Period (U.S. & Canada)                    | 3-year limited warranty                                                                                                   |
| Product Warranty Period (Latin America)                    | 3-year limited warranty                                                                                                   |
| Product Warranty Period (International)                    | 2-year limited warranty                                                                                                   |
| Product Warranty Period (Mexico)                           | 3-year limited warranty                                                                                                   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$100,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>    |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>