

**Multipin terminal strip
D 2 MK5/2 PA/NA**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	D 2 MK5/2 PA/NA
Order No.	0244060000
Version	Multipin terminal strip, Single- and multi-pole terminal strip, Rated cross-section: Screw connection, Direct mounting
GTIN (EAN)	4008190071844
Qty.	50 pc(s).

Creation date August 21, 2020 5:13:01 PM CEST

Catalogue status 14.08.2020 / We reserve the right to make technical changes.

**Multipin terminal strip
D 2 MK5/2 PA/NA**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Width	18 mm	Width (inches)	0.709 inch
Height	4,000 mm	Height (inches)	157.48 inch
Depth	7.7 mm	Depth (inches)	0.303 inch
Net weight	1.72 g		

Temperatures

Storage temperature, max.	55 °C	Storage temperature, min.	-25 °C
Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Material data

Material	PA 66	Colour	white
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails	End cover plate required	No
---------	------------------------	--------------------------	----

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of mounting	Direct mounting		

Conductors for clamping (rated connection)

Blade size	0.6 x 3.5 mm	Connection direction	on side
Number of connections	4	Type of connection	Screw connection

Rating data

Pollution severity	3
--------------------	---

Classifications

ETIM 6.0	EC001284	ETIM 7.0	EC001284
eClass 9.0	27-14-11-06	eClass 9.1	27-14-11-06
eClass 10.0	27-14-11-06	UNSPSC	30-21-18-11

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks