

**VPMS (blanking plug in brass)  
VP 16-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



For sealing surplus threaded holes to maintain the IP class of protection

**General ordering data**

Type	VP 16-MS65
Order No.	<a href="#">0295000000</a>
Version	VPMS (blanking plug in brass), Blanking plug, PG 16, 6 mm, Brass, nickel-plated
GTIN (EAN)	4008 19000 1032
Qty.	100 pc(s).

Creation date August 16, 2020 6:21:35 AM CEST

Catalogue status 24.07.2020 / We reserve the right to make technical changes.

**Data sheet**

**VPMS (blanking plug in brass)  
VP 16-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Length	9 mm	Length (inches)	0.354 inch
Height	9 mm	Height (inches)	0.354 inch
Net weight	10.55 g	Diameter	26 mm

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**General information**

Material	Brass, nickel-plated	Cable glands	PG
External thread	PG 16	Length of thread	6 mm
Protection degree	IP68 - 5 bar (30 min.)	Operating temperature range, min.	-40 °C
Operating temperature range, max.	100 °C	Head diameter	26 mm
Halogen	No	O-Ring	NBR
Sealing	NBR		

**Classifications**

ETIM 6.0	EC000451	ETIM 7.0	EC000451
eClass 9.0	27-14-44-25	eClass 9.1	27-14-44-33
eClass 10.0	27-14-44-25	UNSPSC	30-21-18-01

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>
Engineering Data	<a href="#">STEP</a>

**Data sheet**

**VPMS (blanking plug in brass)  
VP 16-MS65**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

