



NEOZED, fuse base, D02, 1-pole, 63 A, Un AC: 400 V, Un DC: 250 V with twofold frame terminal

Model	
product brand name	NEOZED
product designation	Fuse base
design of the product	NEOZED fuse base installation
General technical data	
number of poles	1
size of fuse system / acc. to DIN EN 60269-1	D02
Supply voltage	
operating voltage / rated value	400 V
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1 W
operational current	
• at 35 °C / rated value	60.48 A
• at 40 °C / rated value	59.22 A
• at 45 °C / rated value	57.96 A
• at 50 °C / rated value	56.7 A
• at 55 °C / rated value	55.44 A
• at 60 °C / rated value	54.18 A
• at 65 °C / rated value	52.29 A
• at 70 °C / rated value	51.03 A
Main circuit	
operational current / rated value	63 A
Product details	
product component / cover	Yes
Mechanical Design	
height	83 mm
width	27 mm
depth	64 mm
fastening method	DIN rail
net weight	126 g
material / of D fuse base	plastic
General Product Approval Declaration of Conformity Test Certificates	



[Type Test Certificates/Test Report](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SG1701>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SG1701>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1701

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



