

| D-HR SERIES

HIGH INSULATION RESISTANCE, HIGH VOLTAGE RELAYS, 5KV, 7.5KV, 10KV & 15KV



Very high isolation voltages, up to 15kV, are achieved through the use of high vacuum reed switches. Rhodium or tungsten contacts make these relays suitable for high reliability applications, such as cardiac defibrillators, test equipment and high voltage power supplies.

The rhodium contact relays have low contact resistance, whilst the tungsten contact relays can switch higher voltages.

Features

- 5kV, 7.5kV,10kV or 15kV isolation
- Low contact resistance
- 1x10¹⁴ Ohms minimum insulation resistance
- PCB or flying leads connections
- Ideal for sensitive test and measurement circuits which require low leakage current losses

SPECIFICATIONS

Contact	Unit Condition	5kV SPNO		5kV SPNC		7.5kV SPNO		7.5kV SPNC		10kV SPNO		10kV SPNC		15kV SPNO*
Contact Material		Rhodium	Tungsten	Tungsten										
Isolation across contacts	kV DC or AC peak	5	5	5	5	7.5	7.5	7.5	7.5	10	10	10	10	15
Switching Power Max.	W	50	50	50	50	50	50	50	50	50	50	50	50	50
Switching Voltage Max.	V DC or AC peak	1000	3500	1000	3500	1000	5000	1000	5000	1000	7000	1000	7000	10000
Switching Current Max.	A DC or AC peak	3	2	3	2	3	2	3	2	3	2	3	2	2
Carry Current Max	A DC or AC peak	4	3	4	3	4	3	4	3	4	3	4	3	2
Capacitance across contacts	pF coil to screen grounded	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2	<0.2
Lifetime	dry switching	10 ⁹												
Operations	50W switching	10 ⁶												
Contact Resistance	mΩ max (typical)	50(15)	250(100)	50(15)	250(100)	50(15)	250(100)	50(15)	250(100)	50(15)	250(100)	50(15)	250(100)	250(100)
Insulation Resistance	Ω min	1x10 ¹⁴												

^{*} Form B (n/c) is not available on 15kV models.




Contact	Unit Condition	5kV SPNO	5kV SPNC	7.5kV SPNO	7.5kV SPNC	10kV SPNO	10kV SPNC	15kV SPNO*
Coil		5V 12V 24V						
Must Operate Voltage	V DC	3.7 9 20	3.7 9 20	3.7 9 20	3.7 9 20	3.7 9 20	3.7 9 20	3.7 9 20
Must Release Voltage	V DC	0.5 1.25 4	0.5 1.25 4	0.5 1.25 4	0.5 1.25 4	0.5 1.25 4	0.5 1.25 4	0.5 1.25 4
Operate Time	ms diode fitted	3.0 3.0 3.0	2.0 2.0 2.0	3.0 3.0 3.0	2.0 2.0 2.0	3.0 3.0 3.0	2.0 2.0 2.0	3.0 3.0 3.0
Release Time	ms diode fitted	2.0 2.0 2.0	3.0 3.0 3.0	2.0 2.0 2.0	3.0 3.0 3.0	2.0 2.0 2.0	3.0 3.0 3.0	2.0 2.0 2.0
Resistance	Ω	28 150 780	38 240 925	28 150 780	38 240 925	28 150 780	38 240 925	16 95 350
Note. The operate / release voltage and ceil resistance will change at a rate of 0.4% per degree C. Values are stated at room temporature (20 degrees C).								

Note. The operate / release voltage and coil resistance will change at a rate of 0.4% per degree C. Values are stated at room temperature (20 degrees C)


Relay		
Isolation contact/coil	kV DC or AC peak	17
Insulation resistance contact to all terminals	Ω min	1x10 ¹⁴
Environmental Operating Temp range	°C	-20 to +70



STANDARD




FLYING LEAD



NOTE: PINS WHICH ARE NOT NUMBERED HAVE NO ELECTRICAL CONNECTION.

Please refer to this document for circuit design notes:https://www.cynergy3.com/blog/reed-relay-application-notes



^{*} Form B (n/c) is not available on 15kV models.

Please refer to this document for circuit design notes: https://www.cynergy3.com/blog/reed-relay-application-notes

Made in the UK

Datasheets provided by Sensata Technologies, Inc., its subsidiaries and/or affiliates ("Sensata") are solely intended to assist third parties ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, valuation, and judgment in designing Buyer's systems and products. Sensata datasheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular datasheet. Sensata may make corrections, enhancements, improvements, and other changes to its datasheets or components without notice. Buyers are authorized to use Sensata datasheets with the Sensata component(s) identified in each particular datasheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATASHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATASHEETS OR USE OF THE DATASHEETS, EXPRESS, IMPLIED, OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATASHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at www.sensata.com. SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY, AND SAFETY-RELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA.

CONTACT US

+44 (0)1202 897969 support@sensata.com Cynergy3 Components Ltd. 7 Cobham Road, Ferndown Industrial Estate, Wimborne, Dorset, BH21 7PE, United Kingdom