




Features

- Shielded construction
- Metal alloy powder core
- High saturation current
- Inductance range 0.15 to 10 μ H
- AEC-Q200 compliant
- RoHS compliant* and halogen free**

Applications


- Selected automotive applications:
 - Driver assistant
 - Infotainment
 - Lighting
- DC/DC converters
- Power supplies

SRP3012TA Series – Shielded Power Inductors

Electrical Specifications @ 25 °C

Bourns Part Number	Inductance @ 100 kHz / 1 V		SRF (MHz) Typ.	DCR (m Ω) Typ.	DCR (m Ω) Max.	I rms (A) Typ.	I sat (A) Typ.
	L (μ H)	Tol. %					
SRP3012TA-R15Y	0.15	± 30 %	195	9.6	11	10	14
SRP3012TA-R22M	0.22	± 20 %	170	14	17	6.5	10
SRP3012TA-R33M	0.33	± 20 %	150	16	20	6.2	9.2
SRP3012TA-R36M	0.36	± 20 %	125	18.5	23	6.0	8.5
SRP3012TA-R47M	0.47	± 20 %	107	25	30	5.0	7.2
SRP3012TA-R56M	0.56	± 20 %	90	31	36	4.5	6.6
SRP3012TA-R68M	0.68	± 20 %	85	34	40	4.0	6.1
SRP3012TA-R82M	0.82	± 20 %	71	41	48	3.5	5.8
SRP3012TA-1R0M	1.0	± 20 %	65	50	60	3.3	5.5
SRP3012TA-1R5M	1.5	± 20 %	55	71	85	3.0	4.0
SRP3012TA-2R2M	2.2	± 20 %	45	98	115	2.7	3.4
SRP3012TA-3R3M	3.3	± 20 %	40	191	210	2.0	3.1
SRP3012TA-4R7M	4.7	± 20 %	35	266	293	1.6	2.8
SRP3012TA-5R6M	5.6	± 20 %	32	310	360	1.5	2.2
SRP3012TA-6R8M	6.8	± 20 %	29	360	400	1.4	2.0
SRP3012TA-8R2M	8.2	± 20 %	26	420	463	1.2	1.7
SRP3012TA-100M	10	± 20 %	23	498	550	1.0	1.4

Product Dimensions



BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Email: asiacus@bourns.com

EMEA: Tel: +36 88 520 390 • Email: eurocus@bourns.com

The Americas: Tel: +1-951 781-5500 • Email: americus@bourns.com

www.bourns.com

* RoHS Directive 2015/863, Mar 31, 2015 and Annex.

**Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

General Specifications

Operating Temperature

.....-40 °C to +150 °C
(Temperature rise included)

Storage Temperature (Component)

.....-40 °C to +150 °C

Rated Current

..... Inductance drops 30 % at Isat

Temperature Rise ... 40 °C at rated Irms¹

MSL 1

ESD Classification (HBM)..... N/A

Note 1: Circuit design, component, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application.

Materials

Core..... Metal alloy powder

Wire Enameled copper

Terminal Finish Sn/Ni


Packaging..... 4000 pcs. per 13-inch reel

How to Order


SRP3012TA - 1R0M

Model
Value Code (see table)

Schematic



Recommended Layout




DIMENSIONS: MM (INCHES)










SRP3012TA Series – Shielded Power Inductors

BOURNS®

Soldering Profile



L vs. I Charts











Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

SRP3012TA Series – Shielded Power Inductors

BOURNS®

L vs. I Charts (Continued)



Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

BOURNS®

[illegible]