

REV. Status


REVISION -
12/10/01 MPENCAPSULATED TELECOMMUNICATION MODEM COUPLING TRANSFORMER
COMPATIBLE WITH V.90 TECHNOLOGIES

A. Electrical Specifications (@ 25°C)

1. Pri Source Impedance; 600Ω
2. Sec Load Impedance; 374Ω
3. Insertion Loss;
2.5dB MAX, 1KHz, 0dBm
4. Frequency Response (relative to 1 KHz)
±0.20dB 200Hz to 4KHz @ 0dBm
5. Longitudinal Balance;
60dB MIN @ 200Hz to 1KHz
40dB MIN @ 1KHz to 4KHz
6. Return Loss; 25dB MIN @ 1KHz, 0dBm (29dB TYP)
7. DC Resistance;
(1-2)= 108Ω ±15%
(3-4)= 120Ω ±15%
8. Turns Ratio; (1-2):(4-3) = 1:1.00±2%
9. Dielectric Strength;
3750Vrms 1 second Pri to Sec
10. Total Harmonic Distortion:
-86dB MAX @ 600Hz, -10dBm (-90 dB TYP)



UL #E208555




MODEL NUMBER

TTC-5006


B. Marking; TTC-5006, TAMURA, date code and country of origin

C. Safety: UL 1950 3rd Edition, UL60950, EN60950

D. Schematic Diagram



E. Mechanical Specifications



PREPARED BY:

D. Rund

ENGINEER:

M. Pitchai

QUALITY CONTROL:

D. Kelley

APPROVED:

J. Coleman

DWG CONTROL NO.
P-A1-12727
ACAD\TTC\A1127271.DWGREV
—MODEM COUPLING
TRANSFORMERTAMURA CORPORATION OF AMERICA
43352 BUSINESS PARK DRIVE, TEMECULA, CA. 92590-6624
(909) 699-1270 FAX 9096769482

TTC-5006

MODEL SPECIFICATION

DIM: mm(in) SCL: 1/1 SH: 1 OF 1

PROPRIETARY NOTICE: THIS DRAWING PRINT OR DOCUMENT AND SUBJECT MATTER DISCLOSED HEREIN ARE PROPRIETARY ITEMS TO WHICH TAMURA RETAINS THE EXCLUSIVE RIGHT OF DISSEMINATION, REPRODUCTION, MANUFACTURE AND SALE. THIS DRAWING, PRINT OR DOCUMENT IS SUBMITTED IN CONFIDENCE FOR CONSIDERATION BY THE RECIPIENT ALONE UNLESS PERMISSION FOR FURTHER DISCLOSURE IS EXPRESSLY GRANTED IN WRITING.