




- Steep pressure-volume-performance curve
- 100% speed controllable through auto transformers
- Easy air volume control via large range of control products based on pressure and temperature
- Motor protection through thermal contacts as standard



Type	U [Volt]	f [Hz]	Curve	P ₁ [kW]	I _N [A]	n [min ⁻¹]	t _R [°F]	t _R [°C]	C [μF]	ΔI [%]	I _A /I _N	▲	*	I [kg]
DRAD 200-4 B	3~460Y	60	A	0.62	0.98	1470	104	40	-	-	2.3	54	01.005	11
DRAD 200-4 B	3~230D	60	B	0.57	1.65	1400	104	40	-	-	2.3	54	01.006	11
DRAD 200-4 B	3~400Y	50	C	0.56	0.98	1170	104	40	-	-	2.4	54	01.005	11

