



Actual

Catalog Number: SRPE-375F-9-C
Product ID: 7TAG009960R0053
UPC Number: 72849409154
EAN Number: 05414363053491
Status: Active

Forward Cut Spiral Wrap, Natural Polyethylene for Temperatures up to 50 Degrees Celsius (122 F), Outside Diameter of 9.53mm (0.375 Inches), Pitch of 11.13mm (0.438 Inches), Nominal Wall Thickness of 1.32mm (0.052 Inches), 30.48m Reel (100 Feet)

- Perfect for protection of bundles from .063 to 7 inch diameters.
- Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.
- Available in 3 materials.
- Application Tools: SR-100

North American Specifications (UNSPSC)

UNSPSC	39131604 Spiral wrapping
IGCC	5395 Spiral wrapping
Brand Name	Catamount
Type	Spiral Wrap
Special Features	Perfect for protection of bundles from .063 to 7 inch diameters.
Color	Natural
Outside Diameter	0.375 Inches/9.53mm
Maximum Bundle Diameter	3.0 Inches/76.2mm
Minimum Bundle Diameter	0.313 Inches/7.9mm
Length	111 Feet/30.48mm
Material	Polyethylene
Wall Thickness	0.052 Inches/1.32mm

European Specifications (ETIM)

ETIM	EC002604 Cable bundle hose
Model	Spiral hose
Nominal diameter	9.53mm
Material	Plastic
Material quality	Polyethylene
Colour	Natural colour
Transparent	N
Fire resistant properties	According to UL94 HB
Wall thickness	1.32mm

Packaging

Inner Quantity	1
Inner Dimensions (inches)	11x11x3.5
Outer Quantity	6
Outer Dimensions (inches)	19.7x14.4x13.1
Weight Uom	2.94 lbs. Each

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

