

2-Port HDMI Splitter for Video with Audio 1920x1200 at 60Hz/1080p (HDMI F/2xF)

MODEL NUMBER: **B118-002**



Transmit a HDMI signal from a single source to two displays

Description

Tripp Lite's B118-002 HDMI Splitter allows the digital signal from a Blu-Ray player or other HDMI device to be displayed on two HDMI displays, or, connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's P566-Series cables. Installation is quick and simple, with no software or drivers to install. Locate your HDMI source up to 13 ft. (4 m.) from the splitter, and the splitter up to 16 ft. (5 m.) from a display, for a max distance of 29 ft. (9 m.) between source and display. Multiple splitters can be cascaded together to connect additional monitors, with no more than 6 levels of splitters in all. Supports HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200. High Speed HDMI v1.4 and 3D compliant, with support for 36-bit Deep Color (12-bits per channel). Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio. HDCP v1.4 and EDID compliant.

Features

- Transmit a HDMI signal from a single source to two displays
- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI v1.4 and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP v1.4 and EDID compliant
- Plug and play; No software or drivers required
- Locate a monitor up to 29 ft. (9 m.) from a HDMI source; up to 13 ft. (4 m.) between the source and the switch; up to 16 ft. (5 m.) between the switch and a monitor
- Cascade multiple levels of splitters together to increase the number of connected monitors, with no more than 6 levels of splitters in all
- Connect a DVI-D Single Link display using an HDMI to DVI adapter, such as Tripp Lite's P566-Series

Highlights

- Display HD video resolutions up to 1080p, and computer video resolutions up to 1920 x 1200
- Supports up to 36-bit Deep Color (12-bits per channel)
- High Speed HDMI v1.4 and 3D compliant
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio
- HDCP v1.4 and EDID compliant
- Plug and play; No software or drivers required

System Requirements

- TV's with an available HDMI port and a HDMI peripheral device (e.g. Blu-Ray player, DVR, etc.)
- The cable connecting the HDMI source to the splitter must be no longer than 13 ft. (4 m.)
- The cable connecting the splitter to a HDMI monitor must be no longer than 16 ft. (5 m.)

Package Includes

- B118-002 2-Port HDMI Splitter
- External Power Supply with NEMA 1-15P Plug (Input:100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.9 ft.)
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

cables.

Specifications

OVERVIEW	
UPC Code	037332180520
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 127; 200; 208; 220; 230; 240
External Power Supply Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.8A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	5
External Power Supply Cord Length (m.)	1.5
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 10mm, Positive Pin, Negative Sleeve
External Power Supply Plug(s)	NEMA 1-15P North America
External Power Supply Certifications	CE; FCC; UL; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power, Input, Output 1, Output 2)
PHYSICAL	
Color	Black
Material of Construction	Iron
Shipping Dimensions (hwd / cm)	5.31 x 20.50 x 14.50
Shipping Dimensions (hwd / in.)	2.09 x 8.07 x 5.71
Shipping Weight (kg)	0.40
Shipping Weight (lbs.)	0.88
Unit Dimensions (hwd / cm)	2.4 x 11.1 x 7.5
Unit Dimensions (hwd / in.)	0.9 x 4.4 x 3
Unit Packaging Type	Box
Unit Weight (kg)	0.23
Unit Weight (lbs.)	0.5
ENVIRONMENTAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 158 F (-20 to 70 C)
Relative Humidity	5% to 90% RH, Non-Condensing
BTUs	34.1 BTU/Hr
Power Consumption (Watts)	10
COMMUNICATIONS	
Signal Range (ft.)	16
Signal Range (m)	5
Latency	80ms
CONNECTIONS	
Ports	2
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
Connector Plating	Gold
PORT EXPANSION	
Max Distance (Between any 2 Units)	16ft (5m)
Max Number of Ports (Entire Chain)	2048
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	1080p @60Hz
HDMI Specification	1.4a
HDCP Specification	1.4
Audio Specification	7.1 Surround Sound, Dolby True HD, DTS-HD, DSD
Driver Required	No
Max Supported Color Depth	12-bit
EDID Compatible	Yes
3D Video Supported	Yes
Consumer Electronics Control (CEC) Supported	Yes
Technology	HDMI
CERTIFICATIONS	
Certifications	Tested to CE, FCC, RoHS, REACH
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>