





#### **Features**


- ♦ For surface mounted application
- ♦ Glass passivated junction chip
- Built-in strain relief, ideal for automated placement
- Plastic material used carries Underwriters Laboratory Classification 94V-0
- ♦ Fast switching for high efficiency
- $\Rightarrow$  High temperature soldering: 260°C / 10 seconds at terminals
- Green compound with suffix "G" on packing code & prefix "G" on datecode


#### **Mechanical Data**

- ♦ Case: Molded plastic
- ♦ Terminals: Pure tin plated, Lead free
- ♦ Polarity: Indicated by cathode band
- ♦ Packing: 12mm tape per EIA STD RS-481
- ♦ Weight: 0.064 grams

# 1.0 AMP. Surface Mount Fast Recovery Rectifiers

## SMA/DO-214AC





#### **Dimensions in inches and (millimeters)**

#### **Marking Diagram**



RS1X = Specific Device Code G = Green Compound

Y = Year M = Work Month

### **Maximum Ratings and Electrical Characteristics**

Rating at 25  $^{\circ}$ C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, denate current by 20%

For capacitive load, derate current by 20%									
Type Number	Symbol	RS 1A	RS 1B	RS 1D	RS 1G	RS 1J	RS 1K	RS 1M	Unit
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	$V_{RMS}$	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	$V_{DC}$	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current .375 (9.5mm) Lead Length @ $T_L$ =90 $^{\circ}$ C	I <sub>F(AV)</sub>	1							Α
Peak Forward Surge Current, 8.3 ms Single Half Sinewave Superimposed on Rated Load (JEDEC method)	I <sub>FSM</sub>	30							Α
Maximum Instantaneous Forward Voltage (Note 1) @ 1 A	V <sub>F</sub>	1.3							٧
Maximum Reverse Current @ Rated VR $T_A$ =25 $^{\circ}$ C $T_A$ =125 $^{\circ}$ C	I <sub>R</sub>	5 50							uA
Maximum Reverse Recovery Time (Note 2)	Trr	150			250	500		nS	
Typical Junction Capacitance (Note 3)	Cj	10						pF	
Typical Thermal Resistance	$R_{\theta jA} \ R_{\theta jC}$	105 32						°C/W	
Operating Temperature Range	TJ	- 55 to + 150							οС
Storage Temperature Range	T <sub>STG</sub>	- 55 to + 150							°С


Note 1: Pulse Test with PW=300 usec, 1% Duty Cycle


Note 2: Reverse Recovery Test Conditions:  $I_F$ =0.5A,  $I_R$ =1.0A,  $I_{RR}$ =0.25A


Note 3: Measured at 1 MHz and Applied Reverse Voltage of 4.0V D.C.





#### RATINGS AND CHARACTERISTIC CURVES (RS1A THRU RS1M)











REVERSE VOLTAGE (V)

FIG. 4 TYPICAL JUNCTION CAPACITANCE



