




## FIRE TRIANGLE



All three elements of the fire triangle must be present for ignition to occur.

This Hoffman ATEX Reference Guide explains European hazardous location protection methods and markings.


### PROTECTION CONCEPTS

Protection Concepts	Symbol	How it Works	Category
Increased Safety	Ex e	No arcs, sparks or hot surfaces	2 & 3
Non-sparking	Ex nA		3
Flameproof Enclosed Break*	Ex d Ex nC	Contain the explosion and quench flame	2 & 3 3
Quartz/Sand Filled	Ex q		2 & 3
Intrinsic Safety	Ex ia	Limit energy of sparks; limit the temperature	1, 2 & 3
	Ex ib		2 & 3
	Ex ic		3
Energy Limitation	Ex nL		3
Pressurized	Ex px	Keep the flammable gas away from any hot surfaces and ignition capable equipment	1, 2 & 3
	Ex py		2 & 3
	Ex pz		3
Encapsulation	Ex ma		1, 2 & 3
	Ex mb		2 & 3
Oil Immersion Restricted Breathing	Ex o		2 & 3
	Ex nR		3
Special	Ex s	Any proven method	1, 2 & 3

### PROTECTION METHODS

Protection Methods	IEC
Intrinsic Safety	ia 60079-11
Intrinsic Safety	ib 60079-11
Intrinsic Safety	ic 60079-11
Flameproof	d 60079-1
Pressurization	p 60079-2
Increased Safety	e 60079-7
Encapsulation	m 60079-18
Oil Immersion	o 60079-6
Powder Filling	q 60079-5
Non-sparking	n 60079-15
General Requirement	60079-0
Inspection & Maintenance	60079-17

### Atex Marking Directive (94/9/EC)



**ATEX**

### MODULES [ATEX (94/9/EC)]

[ANNEX I (1)] CLASSIFICATION OF EQUIPMENT GROUPS INTO CATEGORIES

Equipment shall be classified into the following categories				
Equipment Group	Equipment Category	Atmosphere	Protection Level	Required Protection Performance & Operation
I (Mines)	M1	Methane & Dust	Very High	Two faults, remain energized and functioning
I (Mines)	M2	Methane & Dust	High	Severe normal operation, De-energize in exp. atm.
II (Above Ground)	1	Gas, Vapor, Mist, Dust	Very High	Two faults
II (Above Ground)	2	Gas, Vapor, Mist, Dust	High	One faults
II (Above Ground)	3	Gas, Vapor, Mist, Dust	Low	Normal operation

### GAS GROUPS

Typical Material	
Methane	I
Propane	IIA
Ethylene	IIB
Hydrogen	IIC
Acetylene	IIC
All Gases	II

Highlighted items represent protection provided by Hoffman ZONEX™ Enclosures, certified to meet ATEX Directive 94/9/EC and IEC Ex, Exe IIC, Gb/Ex tb IIC Db IP66


\*Applies to component populated Hoffman ZONEX™ Enclosures only.

### TEMPERATURE CLASSES

Max. Surface Temperature	Fahrenheit	T-Class
450° C	(842° F)	T1
300° C	(572° F)	T2
200° C	(392° F)	T3
135° C	(275° F)	T4
100° C	(212° F)	T5
85° C	(185° F)	T6*

# ATEX REFERENCE GUIDE

## Zones and Divisions



## COMPARING DIVISIONS, ZONES & CATEGORIES

Frequency of Occurrence	CEC, NEC Editions Division System	Zone System Class I, CEC, NEC	Category System ATEX
Continuous		Zone 0, 20	Category 1
Intermittent	Class I, Division 1	Zone 1, 21	Category 2
Periodically	Class II, Division 1		
Abnormal	Class I, Division 2	Zone 2, 22	Category 3
Condition	Class II, Division 2		

## INGRESS PROTECTION (IP) CODES

First Number <sup>1</sup>		Second Number <sup>1</sup>	
0	No Protection	0	No Protection
1	Objects Greater than 50mm	1	Vertically Dripping Water
2	Objects Greater than 12 mm	2	75° to 90° F Dripping Water
3	Objects Greater than 2.5 mm	3	Sprayed Water
4	Objects Greater than 1 mm	4	Splashed Water
5	Dust Protected	5	Water Jets
6	Dust Tight	6	Powerful Water Jets
		7	Effects of Immersion
		8	Indefinite Immersion

## ENCLOSURE TYPES

Enclosure Type <sup>2,3</sup>	Intended Use
1	Indoor use, limited amounts of falling dirt
2	Indoor use, limited amounts of falling water and dirt
3	Outdoor use, rain, sleet, wind blown dust, external formation of ice
3R	Outdoor use, rain, sleet, external formation of ice
3S	Outdoor use, rain, sleet, wind blown dust, external mechanisms operable when ice laden
4	Indoor or outdoor use, wind blown dust and rain, splashing water, hose directed water, external formation of ice
4X	Indoor or outdoor use, wind blown dust and rain, splashing water, hose directed water, corrosion, external formation of ice
5	Indoor use, settling airborne dust, falling dirt, non-corrosive liquids
6	Indoor or outdoor use, hose directed water, temporary submersion, external formation of ice
6P	Indoor or outdoor use, hose directed water, prolonged submersion, external formation of ice
7	Indoor use, Class I, Division 1, Groups A, B, C, and D hazardous locations, air-break equipment
8	Indoor use, Class I, Division 1, Groups A, B, C, and D hazardous locations, oil-immersed equipment
9	Indoor use, Class II, Division 1 Groups E, F, and G hazardous locations, air-break equipment
10	Mining applications
12	Indoor use, circulating dust, falling dirt, dripping noncorrosive liquids
12K	Indoor use, circulating dust, falling dirt, dripping noncorrosive liquids, provided with knockouts
13	Indoor use, lint, dust, spraying of water, oil, and noncorrosive coolant

Note:

<sup>1</sup> Numbers can be replaced by 'X' when the characteristic number is not required

<sup>2</sup> Enclosure Types for US only

<sup>3</sup> Enclosure Type can be converted to IP code rating; however, IP classified enclosures cannot be converted to Enclosure Type

### Regional Headquarters

#### North America

Pentair Technical Products  
2100 Hoffman Way  
Anoka, Minnesota 55303-1745  
U.S.A.  
Tel: +1-763-421-2240

#### Brazil

Pentair Technical Products  
(Taurus Metalurgica LTDA)  
Rua Joao Marcon, 165  
18550.000 – Centro  
Boituva – SP  
Tel: +55 15 3363 9100

#### Europe

Pentair Technical Products  
Langenalber Straße 96-100  
75334 Straubenhardt, Germany  
Tel: +49 (0) 7082 794-0

#### China

Pentair Technical Products  
21st Floor of Cloud Nine Plaza  
No. 1118 West Yan'an Road  
Changning District, Shanghai  
P.R. China  
Tel: +86 400 820 1133

#### Singapore

Pentair Technical Products  
Hoffman Schroff Pte Ltd.  
18 Boon Lay Way  
TradeHub 21, #04-110/111  
Singapore 609966  
Tel: +65 6795 2213

For worldwide locations, see [pentairtechnicalproducts.com](http://pentairtechnicalproducts.com)

