

RF Coax Products





Introduction

Product Facts

- Listed under the Component Program of Underwriters Laboratories Inc., (U_L) File No. E-81956 as indicated by Product Family
- Recognized under the **Component Program of** Underwriters R Laboratories Inc., File No. E-81956 as indicated by Product Family
- Certified by Canadian Standards **S₽**® Association File No. LR 7189 as indicated by Product Family
- Produced under a Quality Management System certified to ISO 9001

A copy of the certificate is available upon request



The Tyco Electronics RF Coaxial catalog combines the best products from industry leading brand names like M/A-COM and AMP. We have integrated these into one cohesive set of RF products focused specifically on wireless, wireline carrier, and enterprise networking sectors of the world telecom equipment market.

Tyco Electronic's broadest selection of RF connectors and coaxial cable assemblies provides you with a solution for every interconnection requirement. Type N and 7/16 connectors are used where high power and rugged reliability are required, typically as antenna feeds, filter/ combiner I/O's, and power amplifier outputs. SMA, SMB, and TNC connectors are the primary cable interface for inner cabinet routing and are available in panel mount, board mount, and cable terminations. Subminiature connectors

such as MCX, SMP, DIN, and BlindMate provide panel to board and backplane connections. Finally, our micro miniature SSMT, and MMCX series provide excellent board to board and card edge to board solutions.

All of these interfaces are supported with cable terminating tools and between series adapters to meet all your requirements for trouble free terminations at the lowest applied cost. The appendices hold a wealth of information including a Theory and Application tutorial, RG/U cable specification tables, Application notes on White Bronze plating and intermodulation distortion.

Whether you need rugged external RF power cables, panel mount, board to board, blindmate, or DIN, Tyco Electronics has the connection.

How to Use This Catalog

Based on the communications gear that you are designing:

- Wireless Basestations
- Carrier Rack Equipment
- Chassis Set Top Box
- NIC Card

Typical equipment drawings on pages 306-309 guide you to the interconnect section(s) in this catalog.

Selection guides will direct you to products based on performance and mechanical requirements such as impedance, VSWR, max. frequency, power handling, etc.

There are other guides to help you find the right connection: A table of contents listed by interface type, a complete connector type selector describes each interface with typical applications, and a miniselection guide shows key parameters to quickly pinpoint the right connector type.

Need more information?

Call Technical Support at the numbers listed below.

Technical Support is staffed with specialists well versed in all Tyco Electronics products. They can provide you with:

- Technical Support
- Catalogs
- Technical Documents
- Product Samples
- Tyco Electronics
- Authorized Distributor Locations

Restriction on the use of Hazardous Substances (RoHS)

At Tyco Electronics, we're ready to support your RoHS requirements. We've assessed more than 1.5 million end items/components for RoHS compliance, and issued new part numbers where any change was required to eliminate the restricted materials. Part numbers in this catalog are identified as:

RoHS Compliant — Part numbers in this catalog are RoHS Compliant, unless marked otherwise. These products comply with European Union Directive 2002/95/EC as amended 1 January 2006 that restricts the use of lead, mercury, cadmium, hexavalent chromium, PBB, and PBDE in certain electrical and electronic products sold into the EU as of 1 July 2006.

NOTE: For purposes of this Catalog, included within the definition of RoHS Compliant are products that are clearly "Out of Scope" of the RoHS Directive such as hand tools and other non-electrical accessories.

Non-RoHS Compliant — These part numbers are identified with a " \blacklozenge " symbol. These products do not comply with the material restrictions of the European Union Directive 2002/95/EC

NOTE: Information regarding RoHS compliance is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information provided by our suppliers. This information is subject to change. For latest compliance status, refer to our website referenced at right.

Getting the Information You Need

Our comprehensive on-line RoHS Customer Support Center provides a forum to answer your questions and support your RoHS needs. A RoHS FAQ (Frequently Asked Questions) is available with links to more detailed information. You can also submit RoHS questions and receive a response within 24 hours during a normal work week. The Support Center also provides:

- Cross-Reference from Non-compliant to Compliant Products
- Ability to browse RoHS Compliant Products in our on-line catalog
- Downloadable Technical Data Customer Information Presentation
- Support Center More detailed information regarding the definitions used above
- So whatever your questions when it comes to RoHS, we've got the answers at www.tycoelectronics.com/leadfree



2

Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RoHS

Customer

Disclaimer

While Tyco Electronics Corporation and its affiliates referenced herein ("Tyco Electronics") have made every reasonable effort to ensure the accuracy of the information in this catalog, Tyco Electronics does not guarantee that it is error-free, nor does Tyco Electronics make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. Tyco Electronics reserves the right to make any adjustments to the information contained herein at any time without notice. Tyco Electronics expressly disclaims all implied warranties regarding the information contained herein, includ-ing, but not limited to, any implied war-ranties of merchantability or fitness for a particular purpose. Tyco Electronics' only obligations are those in the Tyco Electronics Standard Terms and Conditions of Sale, and in no case will Tyco Electronics be responsible for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of its products. Users should independently evaluate the suitability of, and test each product for, their application.

The dimensions, specifications, designs, construction, materials and processes in this catalog are for reference purposes only and are subject to change without notice. Please consult Tyco Electronics for the met aurent needuat information for the most current product information. The export of certain Tyco Electronics products is restricted by the Arms Export Control Act (Title 22, U.S.C. Sec 2751, et seq.) or the Export Administration Act of 1979, as amended (Title 50, U.S.C., App. 2401 et seq.). Orders may be subject to export approval by the U.S. Government. Buyer must comply with all applicable export laws of all applicable jurisdictions. © Copyright 2007, 2000, 1998, 1994, 1992, 1990, and 1982 by Tyco Electronics Corporation. All International Rights Reserved. ACTION PIN, AMP, AMP-HDI, AMPLIMITE, AMP-O-LECTRIC, CERTI-CRIMP, COAXICON, M/A-COM, OSP, OSSP, PIDG, PRO-CRIMPER, RAYCHEM, SIEMAX, SMT/QuickGrip, SOLISTRAND, STAX, TE LOGO, TYCO ELECTRONICS and Z-PACK are trademarks. AT&T is a trademark of AT&T Corporation. BELDEN is a trademark of Belden Wire and Cable Company. BERK-TEK is a trademark of Nexans, Inc. COMM/SCOPE is a trademark of Commscope, Inc. DANIELS is a trademark of Daniels Manufacturing Corporation. GPO is a trademark of Corning Gilbert, Inc. HIROSE is a trademark of Hirose Electric. MURATA is a trademark of Murata Electronics, Inc. ROLM is a trademark of the Rolm Corp. TEFLON is a trademark of E.I. Dupont de Nemours and Company. TPX is a trademark of Mitsui Chemicals America, Inc TROMPETER is a trademark of Trompeter Electronics, Inc.

VALOX is a trademark of General Electric Company.

Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

See inside back cover for Global Contacts and phone numbers.

Catalog 1307191

Revised 3-07

RF Catalog Table of Contents

Miniature Connectors	
7-16 Series Connectors	
Lightning Protection Connectors Surge Protectors	
$\lambda/4$ Wave Stub Tuners	
N Series Connectors	
Quick Lock N (QLN) Series Connectors	
TNC Connectors	
BNC Connectors	
Mini BNC Connectors	
Decoupled Connectors	
Self-Terminating PC Board Connectors	
Twin BNC Connectors	
F Series and G Series Connectors	93-99
Subminiature Connectors	
SMA Connectors	
QMA Connectors	124-128
DIN Connectors	
Series 1.0/2.3	
Series 1.6/5.6	
Measurement Accessories	
Coaxial Cables	
SMP Connectors	
Blind Mate Connectors	
OSP Miniature Blind Mate Connectors OSSP Subminiature Blind Mate Connectors	
SMB Connectors	
SMC Connectors	
MCX Connectors	
Compression Coax Board-to-Board Connectors	204
STAX Coax Connectors	
Micro Miniature RF Coax Connectors	
SMT/QuickGrip Connectors	207-211
SSMT Connectors	212-217
MMCX Connectors	
UMCC Connectors	
Switching Coax Connectors	
Quick Snap Stripline (QSL) Connectors	
Multi Position Connectors	
DIN Inserts	238-241
Size 8 Contacts	
COAXICON Contacts	
SIEMAX Connectors	249, 250
Between Series Adapters	251-260
•	
Coaxial Terminations	
Application Tooling	
Cable Assembly Capabilities	
Appendix	
A - Theory and Application	
B - White Bronze Application Note	
C - Intermodulation Application Note	
D - Typical Coaxial Cable Specifications	
E - Maximum Power Handling Capabilities for Cables	
F - Nominal Loss Characteristics for Cables	
G - Glossary of Terms	
RF Coaxial Solutions for Communications Equipment Overview	
RoHS Compliant to Non-RoHS Compliant Part Number Cross Reference	
M/A-COM Part Number Cross Reference	
Part Number Index	315-318

Dimensions are shown for Dimensions are in millimeters reference purposes only. Specifications subject to change.

and inches unless otherwise specified. Values in brackets

are standard equivalents.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

3

www.tycoelectronics.com

Connector Selection

Connector Types

7-16 Series connectors are designed for medium to high power applications such as cellular base stations, control components, antenna and broadcast. The 7-16 Series minimizes intermodulation distortion by white bronze or silver plating the electrical path. Combined hex/knurl coupling nuts allow for manual or torque tightening, further reducing distortion by providing a strong butt joint.

Lightning Protection devices have an integral surge arrestor capsule which is designed to protect equipment from high current pulses. It is effective against very fast rise times as induced by electromagnetic pulses from nuclear explosions (NEMP) and the slower pulses arising from lightning strikes (LEMP).

N Series threaded connectors have an air dielectric interface and are low cost. These connectors operate to 11 GHz and are commonly used in cable-based local-area networks (LAN's) medium power transmitters, and base station antenna applications.

TNC connectors have an interface similar to BNC except for a threaded coupling nut. The tighter fit provided by this screw-on connection improves interface control allowing connectors to operate up to 11 GHz. TNC connectors are excellent for mobile units where top-notch performance is required under vibration.

BNC connectors offer easy engagement and disengagement using bayonet couplings and overlapping dielectrics. They are most useful for frequently coupled and uncoupled RF connections with frequencies below 4 GHz. BNC connectors find applications in flexible networks, instrumentation, and computer peripheral interconnections.

F & G Series connectors offer enhanced performance beyond 1 GHz. Designed to meet the rigorous requirements of Bellcore TA-NWT-001503 and SCTE specifications, the F & G series provides high current carrying capabilities in both sealed and un-sealed configurations. Plugs, jacks and adapters are available in threaded and push-on versions. These connectors meet the evolving needs of the communications industry for increased reliability and performance.

SMA threaded connectors are widely used in microwave communications. Connectors operate to at least 12.4 GHz on flexible coax cables, and up to 26.5 GHz on semi-rigid coax cables. Crimp-on SMA connectors that operate to 26.5 GHz are available.

Blind Mate connectors operate to 22 GHz for OSP connectors, 28 GHz for OSSP connectors, and 40 GHz for SMP style connectors. These connectors offer easy slide-on connection and require less alignment between the cable and the equipment than other connectors with comparable band width. Blind Mate connectors are widely used as coaxial interconnects between plug-in modules and motherboards when axial and radial misalignments are necessary.

SMB connectors feature a snap coupling for fast connection. A self centering outer spring and overlapping dielectric allows easy snap-on and excellent performance even in moderate vibration. The SMB is smaller in size than the SMA and excellent where engineers are concerned about circuit miniaturization. Typical application is inter- or intra-board connection of RF or digital signals. Commercial 50 ohm versions operate to 4 GHz, and 75 ohm versions reach 2 GHz.

MCX connectors offer a high reliability, space saving sub-miniature coaxial cable to cable and cable to board interconnection system. The MCX connectors impedance types are applicable up to 6 GHz.

Surface Mount (SMT) connectors. The RF solution to the communication and information age. Tyco Electronics' SSMT and SMT Quick Grip connectors are designed to meet the growing demand for surface mount RF connector technology. These connectors operate up to 6 GHz utilizing cable assembly design to terminate to SMT connectors. Surface mount connectors contribute to high density packaging and high volume manufacturing requirements.

Multi Position connectors. These connector series, including the 1.0/2.3 (CECC 22230), 1.6/5.6 (CECC 22240), Subminiature D (DIN 41652 and CECC 75 301-082), and Tyco Electronics' own SIEMAX multi coax connector series offer the customer a broad choice of options where density and performance are a major concern. The 1.0/2.3 series contacts are available in both 50 and 75 Ohm versions and are designed for use to 10 GHz. The different types of coupling mechanisms, such as screw on, slide-in and latching coupling provide for a variety of space-saving installations. The connector series 1.6/5.6 has been modified to incorporate improved technical advantages. A 75 Ohm design for use up to 8 GHz, it offers excellent screening effectiveness and is a most suitable component for those applications where the transmission of high bit rates is required. In Subminiature D type connectors these interfaces provide good electrical grounding and electromagnetic shielding in a small package size. These plug connectors address the increasing demands related to EMC (electromagnetic compatibility) and RFI (immunity to radiated noise), and are widely used as interface connectors in office and data systems, telecommunications equipment, and in measurement and control systems. Tyco Electronics' SIEMAX connectors combine the benefits of surface mount technology and modular design. This 75 Ohm connector series operates up to 2 GHz and offers a compact grid pitch of 10mm. Its uses include multiplex and high-density systems, and Base Station applications.

Miscellaneous connector types include multiple-circuit connectors that use coaxial contacts in a pin-and-socket configuration, crimp-on ferrules that offer fast, reliable connections for attaching one or more ground taps to shielded wire and braided shield terminations for connecting cable shields to pc boards. Also available are network/premises interconnect products for Ethernet/IEEE 802.3 systems and coaxial taps for simple, dependable connections from transceiver to LAN without cutting the cable.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

4

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Connector Selection Guide

Product	Nominal Impedance	Maximum Frequency	Temperature Rating	Cable Retent		Coupling Mechanism	Maximum Peak	Durability Cycles	Connector Body	Page No.
	Öhms	ĠHz	c	lb	[N]		Voltage	-	Finish	
7-16 Series	50	7	-55° to +155°	RG8A/U	_	Threaded	4000	500	White Bronze	7
Lightning Protection N Series	50	2.5	-45° to +85°	Adapter 90	_	Threaded	650	500	White Bronze	12
Commercial TNC	50	11	-65° to +85°	(RG-214/U) 60	400.3	Threaded	1000	500	Nickel	20
Single Crimp	50	7	-65° to +165°	(RG-58C/U)	266.9	Threaded	500	500	Silver	29
TNC Dual Crimp	50	11	-65° to +165°	60 (RG-58C/U)	266.9	Threaded	500	500	Silver or Nickel	29
TNC Commercial	50	7	-55° to +85°	60 (RG-58C/U)	266.9	Threaded	500	500	Nickel	29
TNC 75 Ohm	75	2	-55° to +85°	60 (RG-59B/U)	266.9	Threaded	500	500	Nickel	29
BNC Single Crimp	50	2.5	-65° to +165°	60 (RG-58C/U)	266.9	Bayonet	500	500	Silver or Nickel	44
BNC Dual Crimp	50	4	-65° to +165°	60 (RG-58C/U)	266.9	Bayonet	500	500	Silver or Nickel	44
BNC Dual Crimp Commercia	al 50	4	-55° to +85°	60 (RG-58C/U)	266.9	Bayonet	500	500	Nickel	44
BNC Hex Crimp	50	4	-55° to +85°	60 (RG-58C/U)	266.9	Bayonet	500	500	Nickel	44
BNC Field Serviceable	50	4	-65° to +165°	40 (RG-142B/U)	177.9	Bayonet	500	500	Nickel	44
BNC 75 Ohm	75	2	-65° to +85°	60 (RG-59B/U)	266.9	Bayonet	500	500	Nickel	44
Twin BNC	Non- constant	_	-55° to +85°	25 (RG-108/U)	111.2	Bayonet	500	200	Silver or Nickel	89
F Series	75	_	-55° to +85°	40 (Series 59, 6, 7 Single Braid)	_	Threaded (F)	500	200	Nickel	93
G Series	75	_	-55° to +85°	40 (Series 59, 6, 7 Single Braid)	_	Push-On (G)	500	200	Nickel	93
SMA Semi-Rigid	50	26.5	-65° to +105°	60 (RG-402/U)	266.9	Threaded	500	500	Gold or Passivated Stainless Steel	100
SMA Flexible	50	12.4	-65° to +165°	40 (RG-58C/U)	177.9	Threaded	500	500	Gold or Passivated Stainless Steel	100
SMP	50	40	-65° to +165°	20 (RG-405/U)	89	Snap-On	500	100	Gold	152
OSP Semi-Rigid	50	22	-65° to +125°	60 (RG-402/U)	267.02	Push-On	500	5000	Gold or Passivated Stainless Steel	157
OSP Flexible	50	12.4	-65° to +125°	40 (RG-58/U)	178	Push-On	335	5000	Gold or Passivated Stainless Steel	157
OSSP Semi-Rigid	50	28	-65° to +125°	20 (RG-405/U)	89	Push-On	335	5000	Gold or Passivated Stainless Steel	169
OSSP Flexible	50	_	-65° to +125°	20 (RG-316/U)	89	Push-On	250	5000	Gold or Passivated Stainless Steel	169
SMB	50	4	-65° to +85°	20 (RG-316/U)	89	Snap-On	335	500	Nickel	176
SMC	50	10	-65° to +85°	20 (RG-174/U)	89	Threaded	250	500	Gold	193
MCX	50	6	-65° to +165°	20 (RG-316/U)	32	Snap-On	500	500	Nickel	196
Connectors	75	6	-65° to +165°	20 (RG-187/U)	32	Snap-On	500	500	Nickel	196
SMT Quick Grip	50	3	-40° to +125°	Omni-Flex	_	Snap-On	250	5	Gold	207
SSMT	50	6	-40° to +125°	Omni-Flex	_	Snap-On	250	100	Gold	212
MMCX	50	6	-55° to +155°	10 (RG-178/U)	44.5	Snap-On	500	500	Gold	218
Mini BNC	75	2	-40° to +85°	20 (735A)	_	Bayonet	300	500	Nickel	78
QMA	50	6	-40° to +125°	20 (RG-316/U)	_	Quick Lock	335	100	Nickel	124
Comp. Coax	50	4	-40° to +125°	N/A	_	N/A	125	25	Gold	204
	50	10	-40° to +85°	_	_	Thread/ Snap/Slide	500	500	_	129
DIN 1.0/2.3	75	2	-40° to +85°	_	_	Thread/ Snap/Slide	500	500	_	129
Switching Coax	50	2.4	_	N/A	_	N/A	_	30,000	_	229

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Connector Selection (Continued)

Method of Termination

Electronics

₹ Tyco

Tyco Electronics provides connectors that can be terminated to coaxial cable, printed circuit boards or other connector interfaces.

Selection of the proper connector to terminate to an RG cable is simplified by using the format of this catalog. Experience has proven that certain connector types lend themselves to termination of particular coax cable sizes. For example, miniature cables such as RG 188 are most practically terminated to subminiature connectors such as SMB and SMC styles. Figure 3 illustrates the interface diameters of each connector type and the dielectric outside diameter (DOD) of popular RG cables. It is most economical to select a connector that terminates to a cable with a dielectric diameter close in size to the connector's interface diameter. The product information sections of this catalog have been organized so that all connector construction types are grouped together by cable size. This allows easy selection of the connector construction best suited for the application.

Tyco Electronics continually looks at new cable types and will release new part numbers based upon general market or specific customer needs. If you cannot find a Tyco Electronics part number for a specific cable type, please contact one of our sales locations or your local distributor to make an inquiry.

Tyco Electronics offers a wide range of connector configurations for terminating to printed circuit boards. Also available are connectors which allow the interconnection of one interface type to another.




Figure 3

By reviewing this catalog, a connector can be found to match most any application. Since the RF connector is a part of a transmission line system, make sure when selecting a new connector design, that it is compatible with the overall system's performance.

Construction

The construction of a connector will greatly affect the purchase price. The connector tables in this catalog include construction details that allow you to select connectors that meet your requirements at the lowest price. Commercial designs use lower cost materials, such as zinc diecast bodies, polypropylene insulators and silver-plated contacts. Specific details of connector construction are listed in each product section of this catalog.

The materials used affect both performance and cost. Common base metals include brass, beryllium copper and stainless steel. The most common plating used for the center contact is gold because of its low contact resistance, superior mating properties and corrosion resistance.

TEFLON, polypropylene and polymethylpentene (TPX) are the most common connector dielectrics. TEFLON offers the lowest loss, the most stable electrical properties and highest operating temperature. But since it cannot be injection molded, manufacturing is more costly than other materials. Be certain, when specifying connectors, that the temperature and voltage limitations are taken into consideration.

Assembly

There are several methods of assembly or termination, but they can be categorized into two major areas: (1) Solder center conductor and clamp braid (Category A) and (2) Crimp center conductor and crimp braid. Other methods are derived from combinations of the above, (e.g., solder center conductor and crimp braid. Method (1) (Category A) is generally used where no specialized tools are available, such as with field installations. With the development of low cost assembly tools, method (2) is becoming more popular for field installation.

Crimping is preferred in most manufacturing environments where assembly tooling is available because terminations can be made in the least amount of time and with the greatest reliability. The design of crimp tools assures that every termination is made the same; this cannot be done with a clamp design without further testing or inspection. Figure 4 illustrates the difference between braid crimping using AMP "O" crimp and the industry-standard hex crimp. The AMP "O" crimp gives a more consistent pressure on the outer collar. In addition, the crimp of the center conductor provides superior VSWR as shown in Figure 5.

Benefits derived by using AMP "O" crimp:

- No soldering of center contact is required. This alleviates all prospective problems associated with the soldering process such as excess solder, cold solder joints and overheating the dielectric.
- Fewer parts resulting in less assembly errors
- Braid crimping which eliminates the need for the combing, screwing and torquing associated with the braid clamp.

TEFLON is a trademark of E.I. Dupont de Nemours and Company. TPX is a trademark of Mitsui Chemicals America, Inc.

6

Catalog 1307191 Revised 3-07

spe www.tycoelectronics.com are

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

7-16 Series Connectors

Product Facts

₹тусо

 Designed for cellular basestations, control component, antenna and broadcast applications

Electronics

- Available in White Bronze plating
- Minimizes Intermodulation Distortion by the use of non-ferrous materials
- Hex knurl for wrench tightening
- Available for several popular RG cable sizes in solder-clamp and crimpcrimp attachment styles

Related Product Data

N Connectors — Pages 20-25

Application Notes — White Bronze — Appendix B Intermodulation — Appendix C

Between Series Adapters

For 7-16 Series Between Series Adapters, see pages 251-260.



Tyco Electronics offers a comprehensive range of 7-16 Connectors to suit today's challenging Wireless Infrastructure Market. This market demands reliable, intermodulation sensitive connectors that accommodate higher power.

Tyco Electronics 7-16 Coaxial Connector Series provides reliable, intermodulation- minimizing solutions that also provide a logical alternative to N Series connectors in high power applications where a more rugged interface design is required. Typical examples of this include transmitter to antenna links and channel switching networks.

The 7-16 Series conforms to CECC 22190 and IEC 169-4 specification standards and has a 2.7kV working voltage at the connector interface and maximum power handling capability of 4kW.

The series has been designed for these demanding environments and can withstand a minimum of 500 mating cycles. Popular RG cable sizes are covered in both solder/clamp and crimp attachment styles. Two piece combination connectors adapt to straight or right-angle configurations, minimizing the number of different part codes needed by the customer. Series N to 7-16 between series adapters facilitate the transition between system interfaces as well as providing a test interface.

The increased customer demand for greater channel capacity combined with increased sensitivity of receivers has exposed the IMD (Intermodulation Distortion) phenomenon. To address this problem 7-16 Connectors have been

designed to reduce IMD through the use of nonferrous base materials and by silver plating of the electrical path. The proprietary White Bronze plating technique is standard, providing high corrosion resistance, low porosity, scratch resistance, low RF loss and a non-magnetic finish. Incorporation of hex-knurl coupling nuts allow for hand or wrench tightening of connectors, depending upon the application.

Tyco Electronics is a global ISO 9001 certified manufacturer and maintains a complete in-house Intermodulation Testing facility. Connector part numbers shown form just a small part of the extensive interconnect package that Tyco Electronics offers for the professional wireless and telecom markets.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

7-16 Series Connectors (Continued)

General Specifications

Materials	
Female Contacts (inner and outer)	Beryllium Copper
Other Metal Parts	Brass
Insulators	Fluorocarbon Polymer
Gaskets	Silicone Rubber
Finishes Parts in the electrical path Other Metal Parts	Silver over copper White Bronze
Electrical	
Frequency Range	DC-7GHz
Impedance	50 Ohms
Insulation Resistance	10,000 Megohms Minimum 2.7kV (connector)
Maximum Working Voltage rms (sea level)	1.4kV (versions for RG 213, 214 and 393)
Maximum Proof Voltage rms (sea level)	2.7kV (connector) 1.4kV (versions for RG 213, 214 and 393)
Center Contact Resistance	0.8 milliohm (max.) after conditioning
Insertion Loss	<1.5dB to 5 GHz
VSWR	1.02 + 0.03f up to 7 GHz where f is measured in GHz
Intermodulation	Better than -150dBc
Mechanical	
Coupling Torque	18.5 – 22 ftlbs.
Proof Torque	25 ftlbs.
Mechanical Endurance	500 mating cycles
Environmental	
Temperature Rating	–55°C to +155°C

Catalog 1307191 D Revised 3-07 ar www.tycoelectronics.com ar


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Electronics

RF Coax Connectors


7-16 Series Connectors (Continued)






Cable Type	Body Plating	Part No.
1/2" Corrugated	White Bronze/ Gold	1460159-1


Straight Cable Plug Crimp/Crimp




	Cable Type	Body Plating	Part No.
	RG 8A/U, RG 213/U	White Bronze	6331959-1
a.	RG 9B/U, RG 214/U	White Bronze	6362765-1

Right-Angle Cable Plug Solder/Crimp







are standard equivalents.

Dimensions are in millimeters	Dimensions are shown for
and inches unless otherwise	reference purposes only.
specified. Values in brackets	Specifications subject

to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


9

www.tycoelectronics.com


Catalog 1307191 Revised 3-07

7-16 Series Connectors (Continued)

Right-Angle Cable Plug Solder/Clamp




Cable Type	Body Plating	Part No.
RG 55B/U, RG 58C/U, RG 141A/U, RG 142B/U, RG 223/U, RG 400/U	White Bronze	6408026-1
T-Flex 402	Silver	6328873-1



Cable Type	Body Plating	Part No.
RG 213/U, RG 214/U, RG 393/U	White Bronze	6408027-1
RG 8A/U, RG 9B/U, RG 213/U, RG 214/U	White Bronze	6408038-1


Straight Panel Mount Cable Jacks Crimp/Crimp




Cable Type	Body Plating	Part No.
RG 8A/U, RG 213/U	White Bronze	6408032-1
RG 9B/U, RG 214/U	White Bronze	6408033-1

Panel Socket Launcher

Mounting Detail





Catalog 1307191 Revised 3-07 www.tycoelectronics.com


10

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

7-16 Series Connectors (Continued)

Right-Angle Panel Jack Solder/Clamp




Mounting Detail




Cable Type	Body Plating	Part No.
RG 213/U, RG 214/U, RG 393	White Bronze	6408036-1
RG 58C/U, RG 142B/U, RG 223/U, RG 400/U	White Bronze	6363527-1

Combination Panel Jack Solder/Crimp



Cable Type	Body Plating	Part No.
RG 55B/U, RG 142B/U, RG 233/U, RG 400/U	White Bronze	6363524-1
RG 8A/U, RG 213/U	White Bronze	6363525-1
RG 9B/U, RG 214/U	White Bronze	6363526-1

Bulkhead Adapter Jack/Jack



Body Plating	Part No.
White Bronze	6408037-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Lightning and EMP Protection Devices

Product Facts

₹ Тусо

Cellular operator protection against EMP (electromagnetic pulses) caused by lightning strikes

Electronics

- Two different categories: Surge protectors and Quarter wave stub tuners
- For use in cellular infrastructure including GSM, DCS 1800, and PCS 1900 systems
- Incorporates Gas Discharge Tube (GDT) technology

Tvco Electronics has developed a unique series of Lightning and EMP protection devices for use in cellular infrastructure including GSM, DCS 1800, and PCS 1900 systems. These devices are designed to offer the cellular operator protection against EMP (electro-magnetic pulses) caused by lightning strikes. Direct or even near strikes produce fast rising electric fields within micro-seconds. These fields generate high voltage pulses through unprotected antennas and transmission lines which lead to the primary communication equipment. High voltage pulses can cause extensive damage leading to costly repairs as well as significant loss of service to

subscribers. These protective devices come in two different categories: surge protectors and quarter wave stub tuners.

To ensure that proper, low level contact resistance is established between the LP device and mounting wall, it is recommended that a minimum torque of 50 in/lbs / 5.65 n/m be applied to tighten the connector mounting nut. A recommended minimum torque of 35 in/lbs / 3.95 n/m should also be applied for installation of replacement surge protector capsules to ensure proper protection performance.

In order to ensure that resultant currents from lightning or EMP strikes do not

interfere with parallel transmission lines within protected electronic equipment, surge protector devices must be installed with proper orientation. The surge protector side of the device should be mounted in the unprotected side of the equipment while the mounting nut is positioned internally in the protected area.

It is important when planning lightning protection, that the user can estimate the potential number of direct strikes. This information may influence the type of device selected or the requirement for routine maintenance checks. Significant attention must be paid to the height of supporting structure as this, when related to the typical number of thunderstorms in a particular region, allows us to estimate the probability of a direct strike taking place. To assist our customers in this, the following table and chart has been included in this note. This should enable lightning protection planners to establish the likelihood of direct strikes across a network anywhere in the world.

Detailed application notes are available for proper selection of lightning protection devices (surge protectors & stub tuners) as well as intermodulation and White Bronze plating.

Selecting your RF Coaxial **Lightning Protection Device**

Between Series Adapters

For 7-16 Series and N Series Between Series Adapters, please see pages 251-260.

Number of Thunderstorm Days per year	hmax/m 10%	hmax/m 20%	hmax/m 50%
05	28	39	61
10	18	26	40
15	14	20	31
20	12	17	26
30	9.4	13	20
40	7.9	11	17
50	6.9	9.5	15
70	5.6	8.0	12
90	4.8	7.0	10.6
130	3.9	5.5	8.5
150	3.5	5.0	7.7
180	3.1	4.4	6.9

Table 1: Maximum height of supporting building for a given number of thunderstorm days (when hmax is exceeded, probability of direct strike to supporting building within 15 years is greater than 10% for hmax values given in second column, 20% for hmax values given in third column and 50% for hmax values given in the fourth column).

12

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Surge Protectors

Product Facts

₹ Тусо

 Excellent for Broadband Frequency Applications

Electronics

- Field Replaceable Gas Discharge Tube
- Available Interfaces Facilitate Retrofit Capabilities
- Low VSWR up to 2.5GHz
- Specialized White Bronze Finish



Selection of a Lightning Protection Device

At right are the basic advantages and limitations for both types of protection to use in the proper selection for your application.

Advantages

- Broadband
- Allows DC bias on the transmission line. (critical for applications using mast top electronics.)
- No harmonic passband
- Ease of retrofitting antenna sights
- GDT easily accessible for replacement
- Limitations
- Routine maintenance recommended
- 3 GHZ maximum frequency
- Initial pass-through voltage

These devices incorporate Gas Discharge Tube (GDT) technology. A GDT is a hermetically sealed tube containing an inert gas. The tube is inserted in the side of the device through an easily accessible weather sealed port. During normal operation the tube is inactive. When an installation is struck by lightning, a high voltage impulse will appear on the coaxial line. As the impulse amplitude rises, a level is reached where the impulse surpasses the dynamic voltage threshold of the tube and the electrodes arc over to discharge the energy to ground. Prior to activation of the tube, there will be a short period of time where energy will be present on the line. This residual pulse is equal to the dynamic voltage threshold of the tube. The maximum impulse voltage a tube can handle without discharging is referred to as the impulse sparkover voltage. This capacity of the GDT is guoted as follows:

Characteristic	Symbol	Definition	Impulse	Typical Value
Impulse sparkover voltage	U _{zdyn}	Dynamic voltage threshold	1kV/μS	650V

In the case of the referenced chart, the voltage will rise at one kilovolt per microsecond and the tube will fire after 650 nanoseconds. During activation a small percentage of voltage (called arc voltage) will still pass through. This will be approximately 30 volts. When the pulse subsides, the tube again becomes inactive leaving a small residual voltage on the line. A direct lightning strike results in an impulse current of high amplitude. The capability of a device to protect a system is defined as the impulse discharge current rating. This is defined as the peak current of an impulse which the device can withstand ten times (5 at each polarity at fixed intervals) without affecting the device. maximum impulse discharge current is the peak current of an impulse the device can withstand once.

Surge protectors are often used in applications requiring a standing DC line voltage. This is typical in applications with mast top electronics. The maximum voltage capacity of a surge protector prior to it surpassing the static voltage threshold and discharging it to ground is defined as its D.C.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Surge Protectors (Continued)

sparkover voltage. This capacity is quoted as follows:

Characteristic		Symbol	Definition	Impulse	Typical Value
	d.c. sparkover voltage	U _{zstat}	Static voltage threshold	n/a	230V

In these applications it is important to select a device that will assure the tube can return to its inactive state after the passage of a surge. This feature of the Surge protector is known as the *holdover voltage*. If the device continues to conduct, the protected line will be short circuited and the tube will heat up (glow mode). If left in this state, the tube can overheat and destruct. GDT's have a finite life span which is inversely proportional to the energy dissipated. At extremes it is possible to reach a level where the tube is unable to discharge all the energy and is destroyed. It is therefore necessary to schedule routine maintenance checks and periodically replace the tube within the surge protector.

Surge protectors offer excellent lightning protection for broadband systems and are usable up to 3 GHz. Standard interfaces include 7-16, N, and SMA. Configurations include straight and bulkhead mounted adapters which allows for ease of assimilation into existing systems.


Specifications

Requirement	Detail
Electrical	
Frequency Range	DC to 3GHz
Impedance	50Ω
VSWR Performance	≤ 1.33:1
Insertion Loss (Typical)	0.45dB
Impulse Discharge Current (8/20µs, multiple strike)	20kA
Maximum Impulse Discharge Current (8/20µs, single strike)	50kA
Dynamic Sparkover Voltage, NEMP (1kV/µs)	2,000V
Dynamic Sparkover Voltage, LEMP (1kV/µs)	800V
Dynamic Sparkover Voltage, Static (<100V/µs)	90V*
Materials	
Body Parts	Brass
Gaskets	Silicone Rubber
Female Contacts	Beryllium Copper
Male Contacts	Brass
Insulators	P.T.F.E.
Environmental	
Operating Temperature Range	-45° C to +85° C
Relative Humidity	up to 100%

* Determined by gas tube used, can be higher than value shown.

N Series Jack to SMA Bulkhead Jack Adapter





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

14


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




Surge Protectors (Continued)

N Series Jack to N Series **Bulkhead Jack Adapter**









25.4

Sq.


Recommended Mounting Hole


_ **13.6** [.054]

Frequency Range	DC to 3.0 GHz
Contact Plating	Gold
Body Plating	White Bronze
Max Panel	10.00mm
Compliant With	CECC22210
Coupling Torque	0.7-1.1 Nm
Proof Torque	1.7 Nm
Endurance	500 Matings

7-16 Plug to 7-16 **Jack Adapter**







Frequency Range	DC to 3.0 GHz
Contact Plating	Silver
Body Plating	White Bronze
Compliant With	CECC22190
Coupling Torque	25 - 30 Nm
Proof Torque	35Nm
Endurance	500 Matings

Gas Discharge Tube Replacement



Part Number
1402314-1

d.c. Sparkover Voltage:	230V ± 46V
Impulse Sparkover Voltage:	700V typ.
(1kV/mS)	(900V max)
Glow Discharge Voltage: Arc Discharge Voltage: a.c. Discharge Current: (1 sec, 50Hz)	72V 10V 20A
Impulse Discharge Current:	20kA (50kA
(8/20mS waveform)	one strike)
Insulation Resistance (@100V):	10GW
Capacitance:	2pF

for

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

_

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

λ /4 Stub Tuners

Product Facts

₹ Tyco

- Ideal for use with GSM, PCS and DCS
- Maintenance Free Operation

Electronics

- Low VSWR Within Specified Bandwidth
- Configurations include direct attachments to Cable variants
- Optional White Bronze Finish



Advantages

- Low VSWR in passband
- Minimal maintenance
- Pass-through voltage eliminated
- No sparkover or residual voltage concerns
- Ease of retro-fitting antenna sights


Limitations

- Frequency specific
- Harmonic passband
- Does not allow DC bias on transmission line

These devices are three port coaxial connectors. The third port extending from the main through path is terminated in a short circuit at a pre-determined distance calculated to be exactly one quarter wavelength at the desired center frequency (see graph).

Unlike surge protectors, this design eliminates concerns about residual pulse, sparkover voltage and residual voltage ensuring greater protection for sensitive electronic equipment. As opposed to surge protectors, stub tuners will absorb lightning strikes without need for replacing components. These devices yield very low VSWR and feature high attenuation within a relatively narrow pass-band (+/- 70 MHz) but are application specific. Stub tuners also pass energy in bands that are harmonically related to the fundamental center frequency. The graphs below show a typical test impulse and the response of a stub tuner.

$\lambda/4$ Shorting Stub Basics



Stub tuners are classified into two broad categoriessimple and broadband. The simple stub tuner exhibits a V-shaped response on the VSWR vs. frequency plot. The trough of the V is designed to occur at the required Fo and the bandwidth is restricted to approximately 8%. The broadband tuner employs extra RF techniques, similar to multiple cavity filtering, which increase the effective bandwidth by approximately 20%.


Tyco Electronics offers a wide variety of stub tuners for the most popular frequency bands to facilitate purchase without need for custom design and manufacturing. Designs exist for GSM, PCS 1900, DCS 1800


ing SMA, 7-16, and Type N. Configurations include cable assemblies, cabled connectors, and adapters for ease of assimilation into existing systems. Stub tuners are maintenance free since they incorporate no active components though it is recommended that a check of the stub tuner affixment be made following heavy discharges at an installation.

frequencies with standard

industry interfaces includ-

Typical Test Impulse





Typical $\lambda/4$ Test Response

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

16

and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are in millimeters


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

λ/4 Stub Tuners (Continued)

Requirement	Detail (Type-N, 7-16)
Electrical	
Impedance	50Ω
VSWR Performance in Band	≤1.2:1
Insertion Loss (Typical)	0.2dB
DC Resistance (stub outer to inner)	1mΩ
Dynamic Voltage @ 250A/ms	≤15V
Residual Voltage @ 2500A, 8/20µs	≤15V
Outer Conductor Contact Resistance	10mΩ
DC Resistance (through-path center contact)	100mΩ
Materials	
Body parts	Brass
Gasket	Silicone Rubber
Female contacts	Beryllium Copper
Male Contacts	Brass
Insulators	P.T.F.E.
Environmental	
Operating temperature range	-45°C to +85°C
Relative humidity (non-condensing)	up to 100%


DCS 1800 Type N Clamp Bulkhead Jack





Part No.


6329818-1



Bandwidth	± 70 MHz
Center Frequency	1795 MHz
Contact Plating	Silver
Body Plating	Silver
Max Panel	10.00mm
Compliant With	CECC22210
Coupling Torque	0.7-1.1Nm
Proof Torque	1.7Nm
Endurance	500 Matings

7-16 Jack to 7-16 **Bulkhead Jack Adapter**







Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Cable

T-Flex402

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

λ/4 Stub Tuners (Continued)

DCS 1800 (Continued) **Type N Crimp Bulkhead Jack**





Type N Jack to Type N **Bulkhead Jack Adapter**



62.9 Ref. [2.48] 25.4 23.5 [1.00] Sq. ←[0.92] Ref. Œ 54.7 [2.15] Ref. 42.0 冈 [1.65] Ref. Recommended Mounting Hole







Endurance	500 Matings
Bandwidth	± 70 MHz
Center Frequency	1795 MHz
Contact Plating	Silver
Body Plating	Silver
Max Panel	10.00mm
Compliant With	CECC22210
Coupling Torque	0.7-1.1Nm
Proof Torque	1.7Nm

± 70 MHz

Silver

Silver

10.00mm

CECC22210

500 Matings

0.7-1.1Nm

1.7Nm

Center Frequency 1795 MHz

Bandwidth

Contact Plating

Compliant With

Coupling Torque

Proof Torque

Endurance

Body Plating

Max Panel

13.6


[0.54]


16.0_{Dia}

[0.63]

GSM 7-16 Bulkhead Jack to 7-16 Bulkhead Jack








Bandwidth ± 70 MHz Center Frequency 925 MHz Contact Plating Silver Body Plating White Bronze Max Panel 8.00mm Compliant With CECC22190 Coupling Torque 25 - 30Nm Proof Torque 35Nm Endurance 500 Matings

PCS 1900 Type N Clamp **Bulkhead Jack**





Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

18

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

ETyco Electronics

RF Coax Connectors

λ/4 Stub Tuners (Continued)



Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

N Series Connectors

Product Facts

- Designated connectors are MIL-C-39012. Class II. Category B gualified
- Captive center contacts
- Completely crimpable application - one hand tool crimps all cables with single or double braided shields of a given size
- Impedance matching crimps
- Broad band performance low VSWR
- Superior cable retention
- TEFLON dielectric
- Silver or nickel finish
- Fully intermateable with MIL-C-39012 connectors
- Listed under the Component **Program of Underwriters** Laboratories Inc., (UL) File No. E81956
- Recognized under the **Component Program of** Underwriters Laboratories Inc., File No. E81956
- Certified by Canadian Standards **(**\$₽́∘ Association **File No. LR 7189**

Between Series Adapters

For N Series Between Series Adapters, see pages 251-260.

The Tyco Electronics N Connector, featuring a 15.88 [5/8] - 24 threaded coupling for optimum stability, is highly suited for critical applications and environments. This medium sized connector can withstand shock and vibration to assure a low noise level and has a constant impedance of 50 ohms. It also features a captive center contact and provides excellent performance at frequencies up to 11 GHz, with voltages to 1000 volts rms.

This Tyco Electronics connector offers the added benefits of low overall applied cost with a laborsaving two-crimp assembly. The contact is simply crimped to the cable's center conductor, then both braid and cable support are simultaneously crimped to complete the termination.

N Series Connectors are available in standard plug, jack, panel jack, bulkhead jack and right-angle plug configurations. Those connectors with a military designation (M39012) are furnished in accordance with all requirements of specification MIL-C-39012, Class II, Category B.

Materials

Plating

Silver per QQ-S-365 Nickel per QQ-N-290 Center Contact -Gold per MIL-B-45204

Body-

Brass — QQ-B-626 Beryllium Copper — QQ-C-530 Dielectric — TEFLON TEFLON --- MIL-P-19468 **Copper, Annealed**—QQ-C-576 Phosphor Bronze — QQ-B-750 Silicone Rubber - ZZ-R-765

Electrical Characteristics

Nominal Impedance — 50 ohms Working Voltage — 1000 volts, rms at sea level

Frequency Range -0 to 11 GHz Voltage Standing Wave Ratio (VSWR)

Straight Plug or Jack — 1.3:1 max. Right-Angle Plug -1.35 max. at 0 to 9.0 GHz

1.50 max. at 9.0 to 11.0 GHz Contact Resistance -Outer Contact - 0.2 milliohms

Center Contact — 1.0 milliohms Right-Angle-2.5 milliohms Insulation Resistance - 5000

megohms min. Dielectric Withstanding Voltage -

2500 Volts, rms at sea level RF Leakage — MIL Type, -90 dB min.

at 2 to 3 GHz RF Insertion Loss - MIL Type, 0.15 dB max, at 10 GHz

Right-Angle Plug, 0.3 dB max. at 10 GHz

min. at 21 336 m [70,000 ft.]

Resistance — 50 ohms ±1% Power Rating - 1.0 watt max.

Mechanical Characteristics

Mating/Unmating — Threaded coupling

Cable Attachment --- Crimp type -center contact and braid Coupling Nut Retention — 445 N

[100 lbs.] min. Cable Retention - 400 N [90 lbs.]

min. RG 214/U Cable

Durability - 500 cycles per MIL-C-39012

Captive Contact - 27 N [6 lbs.] min. axial retention, either direction

Environmental Characteristics

Temperature Range— MIL Type, -65°C to +165°C

Commercial, -55°C to +85°C Vibration - MIL-STD-202, Method 204, Test Cond. B

Shock --- MIL-STD-202. Method 213. Test Cond. I

Moisture Resistance --- MIL-STD-202 Method 106

Salt Spray - MIL-STD-202, Method 101, Test Cond B

Temperature Cycling — MIL-STD-202, Method 107, Test Cond. B (except high temperature is +85°C)

Note: All data pertains to use with MIL-C-39012 specified cables only.

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

20

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Corona Level - MIL Type, 500 volts Terminator-

A





Notes: 1 Hand Tool 69710-1, with Die Insert 220062-1, is available to terminate these connectors. The 626 Pneumatic tool system can also be used. ² Die Set Crimp Tool - PRO-CRIMPER II Hand Tool, P/N 354940-1 or 626 Series Pneumatic Tool with 679304-1.

3 Weatherproof.

BELDEN is a trademark of Belden Wire and Cable Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



RG/U	Termination	Body	M39012/	Dim.	Dim. Integral Die L Hand Tool	Hex Acro	oss Flats	Madaa	Devit Ma
Cable	Туре	Plating	Military No. and/ or Comments	L		Center	Braid	Braid Notes Part No.	Part No.
58A, 58C	Hex Crimp	Nickel	Hex Collar	57.79 2.275	58436-1	1.73 .068	5.41 .213	1	5415255-1
142, 142A, 142B	Hex Crimp	Nickel	Hex Collar	57.79 2.275	58436-1	1.73 .068	5.41 .213	1	5415255-2
8, 8A, 213	O Crimp	Nickel	Knurl Collar	57.79 2.275	220015-1	—	_	—	5225669-2
0, 0A, 213	O Crimp	Silver	05B0002 Knurl Collar	57.79 2.275	220015-1	—	_	—	225014-2
8, 213	Hex Crimp	Nickel	Hex Collar	57.79 2.275	58485-1	2.54 .100	10.90 .429	1	5415255-3
393	O Crimp	Silver	Knurl Collar	62.31 2.453	220015-1	—	_	1,3	225389-6
9, 9A, 9B	O Crimp	Nickel	Knurl Collar	57.79 2.275	220015-1	—	_	—	5225669-1
214	O Crimp	Silver	05B0003 Knurl Collar	57.79 2.275	220015-1	_	—	_	225014-3
9, 214	Hex Crimp	Nickel	Hex Collar	57.79 2.275	58485-1	2.54 .100	10.90 .429	1	5415255-4

Notes: 1 Die Assembly compatible with Crimp Tool — PRO-CRIMPER III Hand Tool, P/N 354940-1, 626 Series Pneumatic Tool 1213855-1, SDE Battery Tool Kit 1725837-1, or SDE Electric Terminator 1490076-2.

³ Weatherproof.

₹ Tyco Electronics

Jacks



RG/U			M39012/ Military No. and/ D		Integral Die	Hex Acro	Hex Across Flats		Part No.
Cable	Туре	Plating	or Comments	L	Hand Tool	Center	Braid	Notes	Part No.
58A, 58C	O Crimp	Nickel	_	44.83 1.765	220045-2	—	_	2, 3	1-5225664-2
142, 142A, 142B	Hex Crimp	Nickel	—	41.28 1.625	58436-1	1.73 .068	5.41 .213	2	5415242-2
8, 8A, 213	O Crimp	Silver	02B0008	49.20 1.937	220015-1	—	_	3	225093-2
8, 213	O Crimp	Nickel	—	49.20 1.937	220015-1	—	—	2, 3	5225664-2
9, 9A, 9B, 214	O Crimp	Silver	02B0009	49.20 1.937	220015-1	_	_	_	225093-1
9, 214	O Crimp	Nickel	—	49.20 1.937	220015-1	_	_	2, 3	5225664-1
393	Hex Crimp	Nickel	_	41.28 1.625	58485-1	2.54 .100	10.90 .429	2	5415242-6
402 Semi Rigid (.141)	Solder	Nickel	—	26.70 1.051	—	—	—	—	6057116-1

Notes: 1 Hand Tool 69710-1, with Die Insert 220062-1, is available to terminate these connectors. The 626 Pneumatic tool system can also be used. ² Die Assembly compatible with Crimp Tool — PRO-CRIMPER III Hand Tool, P/N 354940-1, 626 Series Pneumatic Tool 1213855-1, SDE Battery Tool Kit

1725837-1, or SDE Electric Terminator 1490076-2.

³ Weatherproof.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


22

Catalog 1307191	Dimensi
Revised 3-07	and inch specified
www.tycoelectronics.com	are stand

ions are in millimeters hes unless otherwise d. Values in brackets idard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




Cable	Туре	Plating	L	Hand Tool	Center	Braid	Notes	Part No.
58, 58A, 58B, 58C, LMR195	O Crimp	Silver	49.61 1.953	220045-2	_	_	1	5225363-1
58A, 58C	Hex Crimp	Nickel	45.72 1.800	58436-1	1.73 .068	5.41 .213	2	5415248-1
142, 142A, 142B	Hex Crimp	Nickel	45.72 1.800	58436-1	1.73 .068	5.41 .213	2	5415248-7
124, 140, 210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9269, 89269	O Crimp	Nickel	49.61 1.953	220045-3	_	_	_	1-5225667-6
8, 213	O Crimp	Silver	53.98 2.125	220015-1	_	_	2, 3	225094-2
393	O Crimp	Nickel	53.98 2.125	220015-1	—	—	2, 3	1-225668-1
9, 214	O Crimp	Silver	53.98 2.125	220015-1	_	_	2, 3	225094-1

Notes: 1 Hand Tool 69710-1, with Die Insert 220062-1, is available to terminate these connectors. The 626 Pneumatic tool system can also be used. ² Die Assembly compatible with Crimp Tool — PRO-CRIMPER III Hand Tool, P/N 354940-1, 626 Series Pneumatic Tool 1213855-1, SDE Battery Tool Kit 1725837-1, or SDE Electric Terminator 1490076-2.

3 Weatherproof.

Rear Mount

22.86 Dia. [.900] Max



RG/U Cable	Termination Type	Body Plating	M39012/ Military No. and/or Comments	Dim. L	Integral Die Hand Tool	Part No.
	Crimp	Nickel	Rear Mount	29.37 1.156	*	228658-1
402 Semi-Rigid/.141	Solder	Pass. Gold	Rear Mount	—	*	6057159-1
	Solder	Nickel	Rear Mount	25.4 1.00	—	6057176-1
405 Semi-Rigid/.085	Solder	Nickel	Rear Mount	33.9 1.335	—	6057165-1

*Tooling—Hand Tool No. 59980-1, Requires (2) Crimping Dies No. 312253-1 and (1) Locator No. 220220-2.

BELDEN is a trademark of Belden Wire and Cable Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack, Panel Mount







Recommended Panel Cutout

RG/U T	Termination	Body	Dim.			Hex Across Flats		Part No.
Cable	Туре	Plating	L	Hand Tool	Center	Braid	Notes	Part NO.
58A, 58C	Hex Crimp	Nickel	41.28 1.625	58436-1	1.73 .068	5.41 .213	_	5415252-1
142, 142A, 142B	Hex Crimp	Nickel	41.28 1.625	58436-1	1.73 .068	5.41 .213	_	5415252-2
8, 213	Hex Crimp	Nickel	41.28 1.625	58485-1	2.54 .100	10.90 .429	_	5415252-3
9, 214	Hex Crimp	Nickel	41.28 1.625	58485-1 2.54 10.90 —		_	5415252-4	
RG 225	O Crimp	Silver	49.20 1.937	220015-1	—	—	3	5225089-4

Note: 3 Weatherproof.



Panel Plug, Solder




Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

24


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803






Body Plating	Contact	Dielectric	Part No.
White bronze	Gold	PTFE	1460055-1

Panel Mount Jack, Screw-In





Body Plating	Contact	Dielectric	Part No.
White bronze	Gold	PTFE	1460118-1 ¹
White bronze	Gold	PTFE	1460118-2 ²
White bronze	Gold	PTFE	1460118-3 ³

Notes: 1. Without TUF-LOC Adhesive

2. With TUF-LOC Adhesive around M3 thread 3. With TUF-LOC Spot on M3 thread

(Jack-Jack) Plating

Feedthru Jack Adapter

Body — Nickel Dielectric — General purpose polypropylene Contact — Gold plated



Part Number	
227945-2	

Inter-Series Adapters

 50.69	

Jack-Plug

Туре	Body Plating	Contact	Dielectric	Part No.
Jack-Plug	Stainless steel/ passivate	Gold	TEFLON	1057374-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Quick Lock N (QLN) Series Connectors

Product Facts

₹ Тусо

 Similar performance and applications to standard N Series

Electronics

- Time saving and user friendly snap on/off mating
- Excellent performance to 6 GHz
- No torquing of connector required
- Free rotation of mated connection
- Higher packaging density can be achieved
- Fully compatible with Huber&Suhner and Radiall QN Series QLF® connectors*

Description

Snap-on version of the popular N Series connector

- Snap-on interface facilitates assembly
- Same dependable performance as standard N connector

Applications

- Cellular & PCS Base Stations
- Broadcast equipment
- Telephony applications, WLAN
- Instrumentation and remote measuring equipment
- Mil Aero, SatCom, Radar



Material and Finish

Shell — Brass, plated white bronze Male Pin Center Contact — Brass, plated gold Female Socket Center Contact — Beryllium copper, plated gold Outer Contact — Phosphor bronze, plated white bronze Insulators — PTFE or PFA Electrical Characteristics

Characteristic Impedance — 50 ohms Frequency Range — DC to 6 GHz Voltage Standing Wave Ratio (VSWR) — 1.12 max. DC to 3 GHz Insertion Loss — 0.15 dB max. DC to 3 GHz Rated Voltage — 1000 VAC rms, 50 Hz (at sea level) Insulation Resistance — 5000 megohms min. Contact Resistance — Center Contact — 1.5 milliohms max. Outer Contact — 1.5 milliohms max.

Mechanical Characteristics

Engagement Force — 30 N typical Disengagement Force — 30 N typical Interface Retention Force — 450 N min.

Contact Captivation — 28 N min. Durability — 100 cycles min.

Environmental Characteristics

Operating Temperature — -40°C to +125°C (cable dependent) Thermal Shock — IEC 60169 para. 16.4 Corrosion — MIL-STD-202, Method 101, Condition B Vibration — IEC-1169-1 para. 9.3.3 (10-500 Hz, 5g) IP Rating for Interface — IP68 (connector dependent)

Related Product Data

Internet — http://tycoelectronics.com/products/rfcoax

Product Specification/Design Objectives — 108-2281

* QN and QLF are registered trademarks of Huber&Suhner, Inc. and Radiall S.A.. Huber&Suhner, Inc. and Radiall S.A. are not affiliated with the QLN product.


Catalog 1307191

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

RF Coax Connectors

Quick Lock N (QLN) Series Connectors (Continued)




Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


Quick Lock N (QLN) Series Connectors (Continued)

Panel Mount Receptacles



Adapters — Between Series

QLN Plug to N Series Jack



Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

28

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets .com are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

TNC Connectors

The Tyco Electronics TNC RF connector family,

with 7/16-28 threaded cou-

levels and optimum stability,

plings, provides low noise

present in hostile environ-

Available in both 50 and

connectors feature numer-

ous styles including cable

plugs and jacks, adapters and printed circuit board

connectors. These connec-

tors accept a wide range of

intermateable with industry

designed to MIL-C-39012

Single crimp connectors provide reduced applica-

tion time and lower applied

costs. This is accomplished

one-crimp operation tooling

which simultaneously termi-

nates the inner conductor,

Tyco Electronics can also

with a commercial type

supply low-cost alternatives

product line. These connec-

ing comparable mechanical

and electrical performance.

tors are designed around the mil-specifications, offer-

outer braid and cable support with one controlled

stroke.

by using Tyco Electronics

coaxial cables and are

standard connectors

specifications.

75 ohm versions, these

and can withstand the shock and vibration often

ments.

Product Facts

Hex Crimp and O Crimp Connectors

- 50 and 75 ohm commercial versions available
- Provides excellent performance at frequencies up to 7 GHz
- Low cost commercial type available
- Commercial type is smaller and lighter weight
- Tarnish resistant nickel finish
- Choice of dielectric materials
- Standard and weatherproof versions available
- Plugs available for high temperature cable

Single Crimp Connectors

- Fast application-one crimping operation terminates inner conductor, outer braid and cable support
- Low application cost

Connectors for Semi-Rigid Cable

- Crimp and solder versions available
- Standard cable stripping dimensions
- Universal cable termination common to all configurations

Listed under the Component **Program of Underwriters** Laboratories Inc., (U_L) File No. E81956

PC Board connectors are recognized under the **Component Program of** Underwriters Laboratories Inc.. File No. E81956

Certified by Canadian (S₽® Standards Association File No. LR 7189

Between Series Adapters

For TNC Between Series Adapters. see pages 251-260.

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Related Product Data

Military Category — All crimp connectors are Category B Type (Tyco Electronics Crimp Tooling), unless otherwise noted.

Packaging — All Mil-Type connectors are packaged individually and all Commercial connectors are bulk packaged unless otherwise noted.

29

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

TNC Connectors (Continued)

Specifications

Tyco Electronics

Characteristics	Single Crimp (MIL Type)	Category B O Crimp (MIL Type)	Commercial O Crimp & Hex Crimp 50 & 75 Ohm	Commercial PCB	Commercial Solder Jacks	Semi-Rigid	Solder Clamp
Electrical							
Impedance, Nom. (Ohms)	50	50	50	50	50	50	50
Working Voltage (Volts RMS)	500	500	500	500	500	335	500
Contact Resistance (Milliohms)	Inner: 1.5 Outer: 3	Inner: 1.5 Outer: 0.2	Inner: 2.0 Outer: 0.3	Inner: 6.0 Outer: 3.0	Inner: 2.75 Outer: 1.0	Inner: 1.5 Outer: 0.2	Inner: 1.5 Outer: 0.2
Initial Insulation Resistance (Megohms)	5000	5000	5000	5000	5000	5000	5000
Dielectric Withstanding Voltage (VAC)	1500	1500	1500	1500	1500	1500	1500
Corona Level at 70,000 ft. (Picocoulombs)	5 max. @ 375 VRMS	5 max. @ 375 VRMS	5 max. @ 375 VRMS	_	_	5 max. @ 375 VRMS	5 max. @ 375 VRMS
RF Leakage, Max. (dB)	—	60 @ 2-3 GHz	55 @ 2-3 GHz	—	—	60 @ 2-3 GHz	55 @ 2-3 GHz
RF Insertion Loss, Max. (dB)	_	0.18 @ 9 GHz	0.2 @ 3 GHz	_	_	0.06 @ 3-6 GHz	0.2 @ 3 GHz
Frequency Range (GHz)	0-4	0-11	0-7	0-4	0-4	0-15	0-11
VSWR in Frequency Range Max.	1.35	1.3	1.40	_	_	1.35	1.30 @ 4 GHz
lechanical							
Force to Engage/ Couple, Ibs. [N]	10/2 [44.5/8.9]	2/2 [8.9/8.9]	6/6 [26.7/26.7]	_	_	2 [.023]	2 [.023]
Coupling Nut Retention, Min. Ibs. [N]	100 [444.8]	100 [444.8]	60 [266.9]	_	_	100 [444.8]	100 [444.8]
Cable Retention, lbs. [N]	60 [266.9] RG 58C/U	60 [266.9] RG 58C/U	60 [266.9] RG 58C/U	60 [266.9] (PCB Ret)	_	60 [266.9]	40 [178.0]
Durability (Cycles)	500	500	500	500	500	500	500
Jam Nut Mounting Torque, Max. Ibs. [N∙m]	25 [2.8]	25 [2.8]	25 [2.8]	25 [2.8]	25 [2.8]	25 [2.8]	25 [2.8]
nvironmental							
Temperature Range, Operating (C°)	-65 to +85	-65 to +165 ¹ -55 to +85 ²	-55 to +85	-55 to +85	-65 to +165	-65 to +105	-65 to +165
Vibration	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 201A Cond. A	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 202 Cond. B	MIL-STD-202 Method 202 Cond. B
Physical Shock	MIL-STD-202 Method 213 Cond. G, (50 G's)	MIL-STD-202 Method 213 Cond. I, (100 G's)	MIL-STD-202 Method 213 Cond. I, (100 G's)	MIL-STD-202 Method 213 Cond. I, (100 G's)	MIL-STD-202 Method 213 Cond. I, (100 G's)	MIL-STD-202 Method 213 Cond. I	MIL-STD-202 Method 213 Cond. I
Thermal Shock	MIL-STD-202 Method 107	MIL-STD-202 Method 107 Cond. B	MIL-STD-20 Method 107 Cond. A	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-202 Method 107
Moisture Resistance	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106 Type II	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106
Salt Spray	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B
Product Specification	_	108-12001	108-12046	_	_	108-12032	_

¹Assembled to cable with polytetrafluorethylene dielectric. ²Assembled to cable with polyethylene dielectric.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

TNC Connectors (Continued)

Specifications (Continued)

Characteristics	Single Crimp (MIL Type)	Category B O Crimp (MIL Type)	Commercial O Crimp & Hex Crimp 50 & 75 Ohm	Commercial PCB	Commercial Solder Jacks	Semi-Rigid	Solder Clamp
onnector Material							
Collar	Brass QQ-B-626	Brass QQ-B-626	Brass QQ-B-626	_	_	Brass QQ-B-626	Brass QQ-B-626
Outer Contact (Plug)	Phos. Bronze QQ-B-750 Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-750 Beryl. Copper QQ-C-530	Brass MIL-C-21768	_	_	Brass QQ-B-626	Brass QQ-B-626
Outer Contact (Jack)	Brass QQ-B-626	Brass QQ-B-626	Zinc QQ-Z-363	Zinc QQ-Z-363	Zinc QQ-Z-363	Brass QQ-B-626	Brass QQ-B-626
Dielectric	TEFLON MIL-P-19468	TEFLON MIL-P-19468	Polyethylene Polypropylene Gen. Purpose	Polypropylene Gen. Purpose ¹	TEFLON MIL-P-19468 Polyester PBT MIL-P-24519	TEFLON MIL-P-19468	TEFLON MIL-P-19468
Center Contact (Plug)	Brass QQ-B-626	Brass QQ-B-626	Brass QQ-B-626	_	_	Brass QQ-B-626	Brass QQ-B-626
Center Contact (Jack)	Beryl. Copper ASTM-B-643, QQ-C-530	Beryl. Copper ASTM-B-643, QQ-C-530	Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-570	Phos. Bronze QQ-B-570	Beryl Copper QQ-C-530	Beryl Copper QQ-C-530
Gasket	Silicon Rubber QQ-R-765	Silicon Rubber QQ-R-765	Silicon Rubber QQ-R-765	_	_	Silicone Rubber QQ-R-765	Silicone Rubbe QQ-R-765
Ferrule	Copper QQ-C-576	Copper QQ-C-576	Copper QQ-C-576	—	_	_	—
onnector Primary Finish	es ²						
Collar	Silver QQ-S-365	Silver QQ-S-365	Bright Nickel QQ-N-290	—	_	Nickel QQ-N-290	Nickel QQ-N-290
Outer Contact (Plug & Jack)	Silver QQ-S-365	Bright Nickel QQ-N-290	Bright or Matte Nickel QQ-N-290	Bright Nickel QQ-N-290	Bright Nickel QQ-N-290	Nickel QQ-N-290	Nickel QQ-N-290
Center Contact (Plug & Jack)	Gold MIL-G-45204	Silver QQ-S-365	Tin Lead, ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Tin Lead, ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Tin Lead, ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Gold MIL-G-45204	Gold MIL-G-45204
Ferrule	Silver QQ-S-365	Gold MIL-G-45204	Tin Lead ASTM-B-5	_	_	_	_

¹Several pc board connectors have an outer polyester PBT insulator per MIL-P-24519.

2lf several finishes are listed, refer to individual catalog page(s) or customer drawings for exact specifications.

TEFLON is a trademark of E.I. Dupont de Nemours and Company.


Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

TNC Connectors, 50 Ohm



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Comments	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
174, 188, 188A, 316	Hex Crimp	Gold	Nickel	Polypropylene	Commercial	—	31.24 1.230	_	58436-3	5222506-5
179, 179A, 179B 161, 187, 187A BELDEN 9221	Hex Crimp	Gold	Nickel	Polypropylene	Commercial		31.24 1.230	_	58436-3	5222506-6
58, 58A, 58B, 58C	Hex Crimp	Gold	Nickel	Polypropylene	Commercial	—	31.25 1.230	_	58436-11	5222506-1
30, 30A, 30D, 30U	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	34.93 1.375	220045-2	_	5225555-2
142, 142A 142B, 400	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	34.93 1.375	220045-2	_	5225555-6
8, 8A, 213	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	50.8 2.000	220015-1	_	5225555-7
9, 9A, 9B, 214	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	50.8 2.000	220015-1	_	5225555-8

1Order Tyco Electronics PRO-CRIMPER Coaxial Hex Crimp Hand Tool assembly 58433-2, which includes dies 58436-1.

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

32

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

TNC Connectors, 50 Ohm (Continued)

Plugs for Semi Rigid-Cable



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Comments	Dim. A	Dim. B	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
405 Semi-Rigid/ 2.18 [.086]	Solder	Gold	Passivate	Solid PTFE	MIL Type	_	2.3 .089	3.0 .120	_	3	1057635-1
402 Semi-Rigid/ 3.66 [.141]	Crimp	Gold	Nickel	TEFLON	Commercial	Weather proof		_	1	2	228179-3
RG 402/U .141 3.66 [.141]	Solder	Gold	Gold	Solid PTFE	MIL Type	_	3.7 .144	4.6 .180	_	3	1057631-1

¹Hand Tool 59980-1, Requires (2) Crimping Dies 312253-1 and (1) Locator 312644-1. ²Pneumatic Tool 58318-1, Requires (2) Crimping Dies 313720-1 and (1) Locator 312645-1. ³Refer to Recommended Assembly Tools in Tool Section.

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Tyco Electronics





RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Comments	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
174, 174A, 188 188A, 316	O Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	38.23 1.505		318450-2	5414173-3
58, 58A, 58B 58C	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	47.63 1.875	220045-2	_	5225559-2
55, 55A, 55B 223	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	38.23 1.505	_	220189-1	5414173-6
142, 142A, 142B 400	0 Crimp	Gold	Silver	TEFLON	MIL Type	Weatherproof	47.63 1.875	220045-2	—	5225554-6
8, 8A, 213	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	63.5 2.500	220015-1	_	5225559-8
393, 225	0 Crimp	Gold	Silver	TEFLON	MIL Type	Weatherproof	63.5 2.500	220015-1	_	1-5225554-1
9, 9A, 9B, 214	0 Crimp	Gold	Silver	TEFLON	MIL Type		59.52 2.343	220015-1	_	5225349-9

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

34

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

TNC Connectors, 50 Ohm (Continued)






RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Comments	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
174, 174A, 188 188A, 316	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	30.48 1.200	_	318450-2	5414171-3
58, 58A, 58B 58C	0 Crimp	Gold	Silver	TEFLON	MIL Type	Weatherproof	35.72 1.406	220045-2*	—	225551-2
141, 141A, 303	0 Crimp	Gold	Silver	TEFLON	MIL Type	Weatherproof	35.72 1.406	220045-2*	_	225551-5
55, 55A, 55B 223	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	29.85 1.175	_	220189-1	414171-6
142, 142A, 142B 400	0 Crimp	Gold	Silver	TEFLON	MIL Type	Weatherproof	35.72 1.406	220045-2*	_	225551-6

*Battery, Pneumatic

Jacks, Solder/Clamp



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Part No.
RG 58C/U, RG 141 A/U	Solder/Clamp	Gold	Silver	TEFLON	MIL Type	1312569-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

TNC Connectors, 50 Ohm (Continued)

Bulkhead Jacks, Crimp



Maximum Panel Thickness Single Crimp 3.18 [.125]; Dual Crimp 6.35 [.250]

Recommended Panel Cutout

H= 11/16 [.6875] max. across flats, 20.32 [.800] max. across points.

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Comments	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
174, 174A, 316 188, 188A	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	—	34.93 1.375	_	318450-2	5414168-3
179, 179A, 179B 161, 187, 187A BELDEN 9221	Single Crimp	Gold	Nickel	TEFLON	MIL Type	_	38.1 1.500	_	91910-1	5331238
RD 188, 316 Double Braid	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	34.93 1.375	—	58539-1	5414168-4
58, 58A, 58B, 58C 141, 141A, 303	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	34.93 1.375	_	220189-1	5414168-1
223 55, 55A, 55B	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	34.93 1.375	_	220189-1	5414168-6
142, 142A	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	_	34.93 1.375	_	220189-1	5414168-5
142B, 400	0 Crimp	Gold	Nickel	TEFLON	MIL Type	Weatherproof	38.1 1.500	220045-2	_	5225557-6

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

36

Catalog 1307191 Revised 3-07 and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are in millimeters


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Tyco Electronics


TNC Connectors, 50 Ohm (Continued)

Bulkhead Jacks for Semi-Rigid Cable, Rear Mount



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Part No.
402 Semi-Rigid/ 3.66 [.141]*	Crimp	Gold	Nickel	TEFLON	MIL Type	25.4 1.000	228502-1

*Tooling—Hand Tool 59980-1, Requires (2) Crimping Dies 312253-1 and (1) Locator 220220-2.



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. A	Dim. B	Part No.
RG 402/U 3.66 [.141]	Solder	Gold	Pass. Stainless Steel	Solid PTFE	MIL Type	3.7 .144	4.6 .180	1057676-1
RG 405/U 2.16 [.085]	Solder	Gold	Pass. Stainless Steel	Solid PTFE	MIL Type	2.3 .089	3.0 .120	1057679-1


TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208




Panel Jacks, Crimp



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool With Integral Die	Part No.
58, 58A, 58B, 58C	Crimp	Gold	Silver	TEFLON	MIL Type	34.93 1.375	220045-2	225348-2

Panel Jacks for Semi-Rigid Cable



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. A	Dim. B	Part No.
RG 402/U 3.66 [.141]	Solder	Gold	Gold	TEFLON	MIL Type	3.7 .144 Min.	4.6 .180	1057697-1
RG 405/U 2.16 [.085]	Solder	Gold	Gold	TEFLON	MIL Type	2.3 .089 Min.	3.0 .120	1057699-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Catalog 1307191 Revised 3-07

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


38


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Right-Angle PC Board/ Panel Mount Jacks








laximum	Panel	Thickness	6.1	[.240]

Recommended Panel Cutout

Ν

Body	Ω	Center Contact	Dime	nsions	Part Numbers
Material	32	Plating	Α	В	Part Numbers
VALOX, White	50	Gold	8.56 .337	21.21 .835	5227818-1
Metal	50	Gold	8.26 .325	20.83 .820	5227839-1



Recommended PC Board Layout

Vertical PC Board/ Panel Mount Jacks

*2-56 Self-Tapping Screws: For 1.57 [3/32] or greater panel thickness Part No. 221108-2 For less than 1.57 [3/32] panel thickness Part No. 221108-4

Lockwasher and Jam Nut







Part No. 1-329632-2

Part No. 1-329631-2

VALOX Body



Body	Center Contact	Dimension	Part Number
Material	Plating	B	
VALOX, White	Gold	21.21 .835	5227820-1



Recommended PC Board Layout

VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

TNC Connectors, 50 Ohm (Continued)


Right-Angle PC Board/ Mount Jacks

Electronics

Plating

₹тусо

Body — Nickel Center Contact — Gold Dielectric — TEFLON




Recommended PC Board Cutout


Bulkhead Solder Jacks

Insulation Bushing

Material — Nylon Part No. 227223-1








Recommended Panel Cutout (Jack)

Panel Thickness Refer to chart below.



Recommended Panel Cutout (Bushing) Body
PlatingCenter
Contact
PlatingDielectricDim.
LPanel
ThicknessPart NumberNickelGoldVALOX33.33
1.3121.17-6.35
.046-.2505227764-2


TEFLON is a trademark of E.I. Dupont de Nemours and Company. VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

40

Catalog 1307191 Dimen Revised 3-07 and in specifi www.tycoelectronics.com are sta

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

₹тусо **Électronics**

TNC Connectors, 75 Ohm

Plugs, Crimp

These connectors have been designed for optimum performance and have a true 75 ohm impedance the complete length of the connector. The crimp die tooling listed below is different from the equivalent 50 ohm connectors.



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
179, 179A, 179B, 187, 187A, BELDEN 9221	O Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	27.79 1.094	318451-2	5221506-3
AT&T 735A	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	29.46 1.160	58174-1	5221506-5
302 BELDEN 88241 89269 Hi-Temp 62A Times PL62, BERK-TEK BTDC-59, BTDC-62	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	31.75 1.250	58425-1	5413591-1
BELDEN 8281 9141, 9231	O Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	32.9 1.295	58538-1	5221506-2



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. H	Tooling	Part No.
210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9169, 89269	O Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	11/16 across flats, 20.32 .800 max. across points	Use Hand Tool 354940-1 with Die Set 58536-1	221509-1

AT&T is a trademark of AT&T Corporation.

BELDEN is a trademark of Belden Wire and Cable Company.

BERK-TEK is a trademark of Nexans, Inc.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

42


Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Right-Angle PC Board/ Panel Mount Jacks

Tyco Electronics



Maximum Panel Thickness 6.1 [.240] Recommended

Panel Cutout

Metal Body 1/2-28 Thread 1/2-28 Thread 15.88 [.625] Mtg. Hgt. (1.375]

Body		Center	Dime	nsions	Part Numbers	
Material	Ω	Contact Plating	A	В	Without Mounting Posts	With Mounting Posts
Metal	75	Gold	8.26 .325	20.83 .820		5413506-1

Bulkhead Jack-Jack Adapter



Center Contact Plating	Body Plating	Dielectric	Part No.
Gold	Nickel	Polymethylpentene	414396-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

BNC Connectors (50 ohm/75 ohm)

Product Facts

₹ Тусо

 Bayonet lock coupling for quick connect/disconnect

Electronics

- Various connectors available in 50 and 75 ohm versions
- Fully intermateable with comparable BNC UG/U connectors
- Full range of Hex Crimp and O Crimp Products for common coaxial cables.
- Low VSWR
- Single crimp connectors offer one crimping operation for fast application
- Twist-on connectors require no special tooling for application to the cable
- Field serviceable (Category A) connectors qualified to MIL-C-39012
- Field replaceable (Category C) plugs with captivated center contact
- Field replaceable plugs can be terminated with industry standard tooling
- Tarnish resistant Nickel finish available
- Choice of different dielectrics
- Listed under the Component Program of Underwriters Laboratories Inc., File No. E81956
- PC Board soldered connectors are recognized under the Component Program of Underwriters Laboratories Inc., File No. E81956
- Certified by Canadian Standards Association File No. LR 7189

Between Series Adapters

For BNC Between Series Adapters, see pages 251-260.



nectors feature numerous

and jacks, adapters and

printed circuit board con-

variety of crimp type termi-

nations, connectors are fur-

nished in field replaceable

and twist-on styles. These

connectors accept a wide

industry standard connec-

tors designed to MIL-C-

39012 specifications.

are intermateable with

range of coaxial cables and

nectors. In addition to a

styles including cable plugs

The Tyco Electronics BNC RF connector family with bayonet locking coupling provides highly reliable, quick connect/disconnect coaxial connections. Exclusive single and O crimp terminations allow positive insulation grip and require no soldering, providing terminations at a very low overall applied cost.

Available in both 50 and 75 ohm versions, these con-

Related Product Data

Product Specifications —

i iouuoi opeenicationa
108-1275 — BNC Ohm Terminators
108-12020 — BNC O Crimp Connectors
108-12044 — BNC Commercial Hex Crimp
108-12047 — BNC Commercial and Hex Crimp Connectors
108-12074 — BNC Solder Jacks
108-12075 — BNC Connectors (Category A)
108-12078 — BNC Commercial PCB Panel-Mount Jacks
Panel-Mount Jacks

108-12002 — BNC Commercial T Adapter
108-12095 — BNC Commercial 75 Ohm Connectors
108-12096 — BNC Commercial Feed- Thru and Bulkhead Adapters
108-12079 — BNC Commercial 50 Ohm Solder Jacks
108-12103 — BNC Commercial PCB Press Fit Jacks
Application Specifications —
114-12001 — BNC Commercial PCB Jack Press Fit

Tyco Electronics can also supply low cost alternatives with an extensive commercial type product line. A lower cost consumer series product offers the capability to supply center contacts in strip form and allow for automated center contact crimp technology. All connectors are designed around the mil-specifications, but utilize low-cost materials, offering comparable mechanical and electrical performance.

Performance Specifications — Page 45

Material Specifications — Page 46 Tooling — Pages 266-268

Military Category — All MIL type O crimp connectors are Category B Type (Tyco Electronics Crimp Tooling), unless otherwise noted.

Packaging — All MIL Type connectors are packaged individually, all 0 crimp connectors are bulk packaged and all Hex crimp connectors are individually packaged unless otherwise noted.

44

Catalog 1307191 Revised 3-07

www.tycoelectronics.com specification are st

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Characteristics	Single Crimp (MIL Type)	Category B O Crimp (MIL Type)	Straight Solder Clamp	Right-Angle Solder Clamp	Commercial O Crimp & Hex Crimp 50 Ohms	Commercial O Crimp & Hex Crimp 75 Ohms	Commercial PC Board 50 & 75 Ohms	Commercial Solder 50 Ohm Jacks
lectrical								
Impedance, Nom. (Ohms)	50	50	50	50	50	75	50 & 75	50 & 75
Working Voltage (Volts RMS)	500	500	500	500	500	500	500	500
Contact Resistance (Milliohms)	Inner: 1.5 Outer: 0.3	Inner: 1.5 Outer: 0.2	Inner: 1.5 Outer: .20	Inner: 1.5 Outer: .20	Inner: 2.0 Outer: 1.0	Inner: 2.0 Outer: 2.0	Inner: 6/1.5 Outer: 3/0.2	Inner: 2.75 Outer: 1.0
Initial Insulation Resistance (Megohms)	5000	5000	5000	5000	5000	5000	5000	5000
Dielectric Withstanding Voltage (VAC)	1500	1500	1500	1500	1500	1500	1500	1500
Corona Level at 70,000 ft. (Volts, RMS)	375	375	375	375	375	375	_	375
RF Leakage, Max. (dB)	—	-55 at 2-3 GHz	-55 at 2-3 GHz	-55 at 2-3 GHz	-55 at 2-3 GHz	-55 at 1-2 GHz	—	—
RF Insertion Loss, Max. (dB)	—	0.2 at 3 GHz	0.2 at 3 GHz	0.3 at 3 GHz	0.2 at 3 GHz	0.15 at 2 GHz	—	—
Frequency Range (GHz)	0-2.5	0-4	0-4	0-4	0-4	0-2	0-4 and 0-2	0-4
VSWR in Frequency Range Max.	1.35	1.30	1.30	1.35	1.30	1.30	—	_
echanical								
Force to Engage (Ibs. [N])/couple, (in-Ibs. [N-M]) max.	13.3/11.12 [3/2.5]	13.3/11.12 [3/2.5]	13.3/.028 [3/2.5]	13.3/.028 [3/2.5]	26.7/26.69 [6/6.0]	26.7/26.69 [6/6.0]	—	_
Coupling Nut Retention, Min. N [lbs.]	444.8 [100]	444.8 [100]	444.8 [100]	444.8 [100]	266.9 [60]	266.9 [60]	_	_
Cable Retention, N [lbs.]	266.9 [60] (RG58C/U)	266.9 [60] (RG58C/U)	177.9 [40] (RG58C/U)	177.9 [40] (RG58C/U)	266.9 [60] (RG58C/U)	266.9 [60] (RG58C/U)	266.9 [60] (PCB Ret)	_
Durability (Cycles)	500	500	500	500	500	500	500	500
Jam Nut Mounting Torque, Max. [N∙m] (in. Ibs.)	25 [2.8]	25 [2.8]	25 [2.8]	_	25 [2.8]	25 [2.8]	25 ³ /12 ⁴ [2.8/1.4]	25 [2.8]
vironmental								
Temperature Range, Operating (C°)	-65 to +85	-65 to +165 ¹ -55 to +85 ²	-65 to +165	-65 to +165	-55 to +85	-55 to +85	-55 to +85	-65 to +165
Vibration	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 204 Cond. B	MIL-STD-1344 Method 2005 Cond. III	MIL-STD-202 Method 204 Cond. B	MIL-STD-202 Method 201A	MIL-STD-202 Method 204 Cond. B
Physical Shock	MIL-STD-202 Method 213 Cond. G, 50 G's	MIL-STD-202 Method 213 Cond. G, 50 G's	MIL-STD-202 Method 213 Cond. G	MIL-STD-202 Method 213 Cond. G	MIL-STD-1344 Method 2004 Cond. G, 100 G's	MIL-STD-202 Method 213 Cond. I, 100 G's	MIL-STD-202 Method 213 Cond. I or A, 50 G's	MIL-STD-202 Method 213 Cond. I, 100 G's
Thermal Shock	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-1344 Method 1003 Cond. A	MIL-STD-202 Method 107	MIL-STD-202 Method 107	MIL-STD-202 Method 107
Moisture Resistance	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-1344 Method 1002 Type II	MIL-STD-202 Method 106	MIL-STD-202 Method 106	MIL-STD-202 Method 106
Salt Spray	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-1344 Method 1001 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B	MIL-STD-202 Method 101 Cond. B
Product Specification	108-12002	108-12020	_	_	108-12044 108-12047	108-12095	108-12078	108-12079

BNC Connectors (50 ohm/75 ohm) Performance Specifications

¹Assembled to cable with polytetrafluorethylene dielectric.

²Assembled to cable with polyethylene dielectric.

³For Metal Threads

⁴For Polyester Threads

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Connector Component	Single Crimp (MIL Type)	Category B & C O Crimp (MIL Type)	Straight Solder Clamp	Right-Angle Solder Clamp	Commercial O Crimp Hex Crimp & Terminators	Commercial PCB Solder	Commercial PCB Press Fit	Commercial Solder Ohm Jacks	Adapters
nector Material									
Collar	Brass QQ-B-626	Brass QQ-B-626	Brass	Brass	Brass QQ-B-626 Zinc QQ-Z-363	_	—	_	Brass QQ-B-626
Outer Contact (Plug)	Brass QQ-B-626 Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-750	Brass	Brass	Brass MIL-C-21768	_	_	_	Brass QQ-B-626 Beryl. Copper QQ-C-530
Shell (Jack)	Brass QQ-B-626	Brass QQ-B-626	Brass	_	Zinc QQ-Z-363	Zinc QQ-Z-363	Zinc Zinc QQ-Z-363	QQ-Z-363 Brass QQ-B-626	Brass QQ-B-626
Dielectric	TEFLON MIL-P-19468 Polypropylene Gen. Purpose	TEFLON MIL-P-19468	TEFLON	TEFLON	Polyethylene Polypropylene Polymethylpentene Gen. Purpose	Polymethylpentene Gen. Purpose ¹	TEFLON MIL-P-19468	TEFLON MIL-P-19468 Polyester PBT MIL-P-24519	TEFLON MIL-P-19468 Polypropylene Gen. Purpose
Center Contact (Plug)	Brass QQ-B-626	Brass QQ-B-626	Brass	Brass	Brass QQ-B-626	—	_	—	Brass QQ-B-626 Beryl. Coppe QQ-C-530
Center Contact (Jack)	Beryl. Copper ASTM-B-643 QQ-C-530	Beryl. Copper ASTM-B-643 QQ-C-530	Beryl. Copper	Beryl. Copper	Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-750	Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-570 Beryl. Copper QQ-C-530	Phos. Bronze QQ-B-570 Beryl. Coppe QQ-C-530
Gasket	Silicon Rubber QQ-R-765	Silicon Rubber QQ-R-765	Silicon Rubber	Silicon Rubber	Silicon Rubber QQ-R-765	_	_	_	Silicon Rubbe QQ-R-765
Ferrule	Copper QQ-C-576	Copper QQ-C-576	—	—	Copper QQ-C-576	—		—	_
inector Primary Fi	nishes²								
Collar	Silver QQ-S-365 Bright Nickel QQ-N-290	Silver QQ-S-365 Bright Nickel QQ-N-290	Silver/ Bright Nickel	Silver/ Bright Nickel	Bright Nickel QQ-N-290	_	_	_	Silver QQ-S-365 Bright Nicke QQ-N-290
Outer Contacts (Plug & Jack)	QQ-S-365 Gold	Silver QQ-S-365 Bright Nickel QQ-N-290	Silver/ Bright Nickel	Silver/ Bright Nickel	Bright or Matte Nickel QQ-N-290	Bright Nickel QQ-N-290	Bright Nickel QQ-N-290	Bright Nickel QQ-N-290	Silver QQ-S-365 Bright Nicke QQ-N-290
Center Contacts (Plug & Jack)	MIL-G-45204 Silver	Gold MIL-G-45204	Gold	Gold	Tin Lead ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Tin Lead ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Gold MIL-B-45204	Tin Lead ASTM-B-545 Silver, QQ-S-365 Gold, MIL-G-45204	Silver QQ-S-365 Gold MIL-G-4520
Ferrule ³	QQ-S-365	Silver QQ-S-365 Tin Lead ASTM-B-545	_	_	Tin Lead ASTM-B-545	_	_	_	_

BNC Connectors (50 ohm/75 ohm) Performance Specifications (Continued)

¹Several pc board connectors have an outer polyester PBT insulator per MIL-P-24519. ²If more than one finish is listed, refer to individual catalog page(s) or customer drawings for exact specification.

³Ferrules with tin-lead finish are used with nickel plated outer contacts.

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

46

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

BNC Connectors, 50 Ohm



RG/U Cable	Termination Type	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
178, 178A, 178B, 196, 196A	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	69245-4	—	69471	5330876
	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	—	58436-3	_	2-5221128-1
174, 188, 188A,	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220009-5	318450-2	220217-3	1-5227079-6
316	0 Crimp	Nickel	TEFLON	MIL Type	30.18 1.188	—	1424050-1	220026-1	5225395-7
	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	69245-2	_	69422	2-5330061-1
	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	—	58436-3	_	2-5221128-3
179, 179A, 179B, 161, 187, 187A,	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	—	1424050-1	220217-3	2-5227079-2
BELDEN 9221	0 Crimp	Nickel	TEFLON	MIL Type	30.18 1.188	—	_	220026-1	5225395-8
	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	—	91910-1	69408	2-5329446-1
RD 316, 188, Double Braid	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	69477-4	58539-1	—	8-5227079-2
BELDEN	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	—	58436-12	_	2-5221128-7
8219	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-1	58435-1 ¹	220217-1	6-5227079-73
BELDEN 9907, 89907 COMM/ SCOPE 2104	O Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-1	318452-2	220217-1	6-5227079-84
BELDEN	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	69477-4	58539-1	58376-1	1-5227079-9
8218	0 Crimp	Nickel	TEFLON	MIL Type	30.18 1.188		91904-1	69669-2	1-5225395-0

¹Order Tyco Electronics PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1. ²Order Tyco Electronics PRO-CRIMPER Coaxial Hex Crimp Hand Tool assembly 58433-2, which includes dies 58436-1. ³For use with BELDEN 9907 cable, COMM/SCOPE 3104 cable, and BELDEN 8219 cable only.

4For use with BELDEN 89907 cable, and COMM/SCOPE 2104 cable only.

BELDEN is a trademark of Belden Wire and Cable Company. COMM/SCOPE is a trademark of Commscope, Inc. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



RG/U Cable	Termination Type	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	_	58436-12	_	5221128-1 ³
58, 58A, 58B, 58C	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-1	58435-11	220217-1	5227079-5
58Ŕ, 58Ċ	0 Crimp	Nickel	TEFLON	MIL Type	33.74 1.328	69478-1	220189-3	69727	5225395-1
	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	_	91904-4	69223-1	2-5329444-1
BELDEN 88240,	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	_	58436-12	_	1-5221128-0
BERK-TEK BTDC-58.	0 Crimp	Nickel	Polyethylene	Commercial	33.33 1.312	220187-1	58435-1 ¹	220217-1	4-5227079-3
COMM/ SCOPE 2135	0 Crimp	Nickel	TEFLON	MIL Type	33.33 1.312	69478-1	220189-3	69727	4-5225395-2
	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.280	220187-1	58435-11	220217-1	5227079-6
223, 55, 55A, 55B	0 Crimp	Nickel	TEFLON	MIL Type	43.64 1.718	69478-1	220189-3	69727	5225395-3
550	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	_	91904-3	69424	2-5329444-2
	O Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-1	58435-11	220217-1	6-5227079-1
142, 142A, 142B, 400	0 Crimp	Nickel	TEFLON	MIL Type	30.18 1.188	69478-1	220189-3	69727	5225395-6
	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	69331-1	_	69429-1	2-5330358-2

Consult Tyco Electronics for recommended crimp tooling. 10rder Tyco Electronics PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1. 20rder Tyco Electronics PRO-CRIMPER Coaxial Hex Crimp Hand Tool assembly 58433-2, which includes dies 58436-1. 3Bulk packaged.

BELDEN is a trademark of Belden Wire and Cable Company. BERK-TEK is a trademark of Nexans, Inc. COMM/SCOPE is a trademark of Commscope, Inc. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

48

Catalog 1307191 Revised 3-07 www.tycoelectronics.com	Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.	Dimensions are shown for reference purposes only. Specifications subject to change.	USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803
www.tycoelectronics.com	are stanuaru equivalents.	to change.	0. America. 32-33-1100-0003



RG/U Cable	Termination Type	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	—	58436-1 ²	—	1-5221128-1
124, 140, 210,	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-2	58435-11	220217-2	5227079-7
62, 62A, 62B, 59, 59A, 59B, BELDEN 9291.	0 Crimp	Nickel	Polyethylene	Commercial	27.69 1.090	220187-2	58435-1 ¹	220217-2	1-5227079-1
9209, 9269	0 Crimp	Nickel	TEFLON	MIL Type	30.18 1.188	_	58537-1	_	5225395-2
	Single Crimp	Silver	TEFLON	MIL Type	33.33 1.312	69141-1	_	_	2-5329445-1
302, BELDEN 88241, 89269, Hi-Temp 62A,	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	_	58436-1 ²	_	1-5221128-1
Times PL62, BERK-TEK, BTDC-59, BTDC-62	0 Crimp	Nickel	TEFLON	MIL Type	34.14 1.344	69477-1	58537-1	69669-1	4-5225395-1
Hi-Temp 59, Times PL59, PLF59 (20 AWG C.C.)	O Crimp	Nickel	Polyethylene	Commercial	33.33 1.312	_	58537-1	_	5-5227079-3
BELDEN 9104, 9240, 9112, 9167,	Hex Crimp	Nickel	Polyethylene	Commercial	33.53 1.320	_	58436-12	—	1-5221128-7
9259, 9266, Times FM-59	0 Crimp	Nickel	TEFLON	MIL Type	30.94 1.218	—	58537-1	69669-1	2-5225395-0
BELDEN 8281, 9141, 9231, Western Electric 724, 728, 3049	Single Crimp	Silver	Polypropylene	MIL Type	41.50 1.634	69652	_	220000	5330878
8, 8A, 213	0 Crimp	Silver	TEFLON	MIL Type	27.31 1.075	220015-1	_	_	5225886-1
11, 11A	O Crimp	Silver	TEFLON	MIL Type	47.63 1.875	220015-1	_	_	5225886-4
BELDEN 9914, Times FM-8	0 Crimp	Silver	TEFLON	MIL Type	47.63 1.875	220015-1	_	_	5225886-7
Alpha 9847, BELDEN 8213, 9292	0 Crimp	Silver	TEFLON	MIL Type	47.63 1.875	220015-1	_	_	225886-5 ♦
9, 9A, 9B, 214	0 Crimp	Silver	TEFLON	MIL Type	52.38 2.062	220015-1	_	_	5225886-1

Order Tyco Electronics PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1.

2Order Tyco Electronics PRO-CRIMPER Coaxial Hex Crimp Hand Tool assembly 58433-2, which includes dies 58436-1.

Tyco Electronics PRO-CRIMPER II Hand Tool Frame without dies Part No. 354940-1

BELDEN is a trademark of Belden Wire and Cable Company. BERK-TEK is a trademark of Nexans, Inc. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Plugs, Twist-On

Related Product Data


Twist-On plugs must be used with cable that has a solid conductor. These plugs are not recommended for applications where the cable frequently moves or flexes.

Mating Twist-On Jack — Page 52



Right-Angle Plugs, Crimp

Single Crimp



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
174, 188,	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	—	58436-3	—	5413959-3
188Á, 316	Single Crimp	Gold	Silver	TEFLON	MIL Type	44.45 1.750	_	91910-1	69422	5331178
179, 179A, 179B, 161, 187, 187A, BELDEN 9221	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	_	58436-3	_	5413959-4
180, 180A, 180B, 195, 195A	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	_	58436-3	_	5413959-5
BELDEN 9907, 89907, 8219, COMM/SCOPE 2104, 3104	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	_	58436-1	_	5413959-6
	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	_	58436-1	_	5413959-1
58, 58A, 58B, 58C	O Crimp	Gold	Nickel	TEFLON	MIL Type	37.29 1.468	69478-1	220189-3	69727-1	5225974-1
	Single Crimp	Gold	Silver	TEFLON	MIL Type	44.45 1.750	_	91904-1	69223-1	5331175
55, 55A,	O Crimp	Gold	Nickel	TEFLON	MIL Type	37.29 1.468	69478-1	220189-3	69727-1	5225974-2
55B, 223	Single Crimp	Gold	Silver	TEFLON	MIL Type	44.45 1.750	_	91904-3	69429-1	5331182
142, 142A, 142B, 400	Single Crimp	Gold	Silver	TEFLON	MIL Type	44.45 1.750	69331-1	_	69429-1	5331182
124, 140, 210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9269	O Crimp	Gold	Nickel	TEFLON	MIL Type	37.29 1.468	_	58537-1	69669-1	5225974-5

BELDEN is a trademark of Belden Wire and Cable Company.

COMM/SCOPE is a trademark of Commscope, Inc.

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


50

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	33.02 1.300	_	58436-3	_	5413779-3
174, 188,	0 Crimp	Gold	Nickel	Polypro- pylene	Commercial	30.48 1.200	_	1424050-1	220217-3	5228979-7
188Å, 316	0 Crimp	Gold	Nickel	TEFLON	MIL Type	30.48 1.200	_	1424050-1	220026-1	5225396-7
	Single Crimp	Gold	Silver	TEFLON	MIL Type	33.33 1.312	_	_	69422	2-5330062-1
179, 179A, 179B, 161, 187, 187A, BELDEN 9221	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	33.02 1.300	_	58436-3	_	2-5413779-4
58, 58A,	0 Crimp	Gold	Nickel	Polypro- pylene	Commercial	30.48 1.200	220187-1	58435-1 ¹	220217-1	5228979-5
58Å, 58Ć	0 Crimp	Gold	Nickel	TEFLON	MIL Type	30.48 1.200	_	91901-1	69727	5225396-1
223, 55, 55A, 55B	Single Crimp	Gold	Silver	TEFLON	MIL Type	33.33 1.312	69140-2	91904-3	69424	2-5329452-2
124, 140, 210, 62, 62A, 62B, 50, 50A, 50B	0 Crimp	Gold	Nickel	Polypro- pylene	Commercial	30.48 1.200	220187-2	58435-1 ¹	220217-2	5228979-6
59, 59A, 59B, BELDEN 9291, 9209, 9269	0 Crimp	Gold	Nickel	TEFLON	MIL Type	30.48 1.200	_	58537-1	69669-1	5225396-2

¹Order Tyco Electronics PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1.

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jacks, Twist-On

₹_{Tyco}

Related Product Data

Panel Jacks, Crimp

Twist-on jacks must be used with cable that has a solid conductor. These jacks are not recommended for applications where the cable frequently moves or flexes.


Electronics

Mating Twist-On Plug — Page 50



RG/U Cable	Center Contact	Body Plating	Dielectric	Style	Part No.
59, 59A, 59B	Gold	Nickel	Acetal	Commercial	222428-1





Recommended Panel Cutout

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
174, 188, 188A, 316	O Crimp	Gold	Nickel	TEFLON	MIL Type	—	1424050-1	220026-1	5225397-7
58, 58A, 58B, 58C	O Crimp	Gold	Nickel	TEFLON	MIL Type	69478-1	91901-1	69727	5225397-1
124, 140, 210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9269, 89269	O Crimp	Gold	Nickel	TEFLON	MIL Type	69477-1	58537-1	69669-1	5225397-2

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.


52

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Dimensions are in millimeters Revised 3-07 and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors



H = 11/16" across flats, 20.32 [.800] Max. across points

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	CERTI-CRIMP Hand Tool with Integral Die	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	36.83 1.450	_	58436-3	_	5413771-3
174, 188,	0 Crimp	Gold	Nickel	Polypro- pylene	Commercial	34.93 1.375	_	_	220217-3	5228980-7
188Å, 316	0 Crimp	Gold	Nickel	TEFLON	MIL Type	35.71 1.406	_		220026-1	5225398-7
	Single Crimp	Gold	Silver	TEFLON	MIL Type	32.13 1.265	_		69422	2-5330063-1
179, 179A, 179B, 161,	0 Crimp	Gold	Nickel	TEFLON	MIL Type	35.71 1.406	_	1424050-1	220026-1	5225398-8
187, 187A, BELDEN 9221	Single Crimp	Gold	Silver	TEFLON	MIL Type	32.13 1.265	_	91910-1	69408	2-5329458-1
Times RD316	0 Crimp	Gold	Nickel	TEFLON	MIL Type	35.71 1.406	_	91904-1	69669-2	1-5225398-5

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

53

www.tycoelectronics.com





Interchangeable Dies for PRO-CRIMPER Interchangeable Dies for Hand Tool 69710-1 CERTI-CRIMP Center Contact RG/U Cable Termination Body Dim. Hand Tool Hand Tool 354940-1 Dielectric Style Part No. Туре Plating L with Integral Die or PRO-CRIMPER Plating & 626 Pneu. Head 318161-1 Adapter 679304-1 58, 58A, 58B, 58C BELDEN 88240, Polymethyl-36.83 5413771-1 Hex Crimp Gold Nickel Commercial 58436-1 BERK-TEK BTDC-58, pentene 1.450 COMM/SCOPE 2135 Polypro-pylene **34.93** 1.375 0 Crimp Gold Nickel Commercial 220187-1 58435-11 220217-1 5228980-5 58, 58A, 41.28 0 Crimp Nickel TEFLON MIL Type 91901-1 69727 5225398-1 Gold 58B, 58Ć 1.625 **32.13** 1.265 Single Crimp Gold Silver TEFLON MIL Type 91904-4 69223-1 2-5329456-1 223, 55, 55A, 55B 35.71 O Crimp MIL Type 91901-1 69727 5225398-3 Gold Nickel TFFI ON ____ 1 406 142. 142A 35.71 0 Crimp Gold Nickel TEFLON MIL Type 91901-1 69727 5225398-6 142B, 400 1.406 124, 140, 210 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291 Polypro-pylene 34.93 0 Crimp Gold Nickel Commercial 220187-2 58435-11 220217-2 5228980-6 1.375 9209, 9269

¹Order Tyco Electronics PRO-CRIMPER Coaxial "O" Crimp Hand Tool assembly 58433-1, which includes dies 58435-1.

Panel Insulating Bushings for Bulkhead Jacks


Material - Nylon


₹тусо

Electronics

Note: Can not be used with single crimp bulkhead jacks.

BELDEN is a trademark of Belden Wire and Cable Company. BERK-TEK is a trademark of Nexans, Inc. COMM/SCOPE is a trademark of Commscope, Inc. TEFLON is a trademark of E.I. Dupont de Nemours and Company.





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Dime Revised 3-07 and ir speci www.tycoelectronics.com are st

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Plugs, for JIS Cables, Crimp

Plating Body — Nickel Center Contact — Gold

₹ Tyco Electronics



JIS Cable	Termination Type	Dielectric	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
3D-2V	Hex Crimp	Polyethylene	33.53 1.320	58436-1	3-5221128-1



Contact		Dimer	nsions	Panel	Insulating	Part	10.
Material	Dielectric	L	W	Thickness	Bushing	Without Solder Terminal*	With Solder Terminal**
Silver	VALOX	26.93 1.060	13.09 .515	1.17-3.18 .046125	227223-1 or 221951-1	5227754-3	5227755-3
	VALOX	33.33 1.312	13.09 .515	1.17-6.35 .046250	227223-1 or 221951-1	_	5227169-7
Gold	VALOA	26.93 1.060	13.09 .515	1.17-3.18 .046125	227223-1 or 221951-1	5227754-2	5227755-2
Gold	TEFLON	33.33 1.312	13.09 .515	1.17-6.35 .046250	227223-1 or 221951-1	5227169-4	5227169-8
	TEFLON	26.93 1.060	13.09 .515	1.17-3.18 .046125	227223-1 or 221951-1	5227715-3	5227716-3
Tin	VALOX	33.33 1.312	13.09 .515	1.17-6.35 .046250	227223-1 or 221951-1	_	5227169-5
	VALOX	26.93 1.060	13.09 .515	1.17-3.18 .046125	227223-1 or 221951-1	5227754-1	5227755-1

*Includes lockwasher and jam nut.

**Includes solder terminal and jam nut.


TEFLON is a trademark of E.I. Dupont de Nemours and Company. VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



56

Catalog 1307191 Revised 3-07

www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




Electronics


₹ Tyco

Body --- Nickel Dielectric — Polymethylpentene







Mounting Post Style



Compliant Post





Maximum Panel Thickness 6.1 [.240]

Recommended Panel Cutout

Lockwasher and Jam Nut





Part No. 1-329632-2

Part No. 1-329631-2

Part No. Center Dimensions Body Material Contact Plating With Compliant Posts Without With L L A В C Mounting Posts Mounting Posts 8.59 21.21 15.88 3.48 5226990-1 5227161-1 Tin 137 .338 835 625 8.59 3.48 VALOX. 15.88 21.21 Gold1 5226990-3 5227161-3 White .137 .338 .835 .625 6.91 21.21 13.18 3.48 5227161-7 Gold1 .272 835 .519 137 **21.21** .835 8.59 15.88 3.48 5227161-2 Tin _ 338 .625 137 8.59 21.21 15.88 3.48 Gold1 5226990-6 5227161-6 VALOX, .338 .835 .625 .137 Black 6.91 21.21 13.18 3.48 Gold1 5227161-9 ____ .272 835 .519 .137 **6.17** .243 **21.21** .835 **11.68** .460 Gold1 5415046-1 ____ 8.26 20.83 15.88 3.48 Tin 5227661-1 325 .820 .625 137 15.88 3.48 8.26 20.83 Gold1 5227676-1 5227677-1 325 .820 .625 .137 Metal 6.91 20.83 **12.70** .500 **3.48** .137 Gold1 1274668-1 5413879-1 .272 .820 6.91 20.83 12.70 3.48 5413879-2 Gold2 .500 .137 .272 .820 High Temp. Housing 6.91 21.21 13.18 2.79 Gold1 5415218-5 272 835 519 110

Plating:

Gold1 — 0.00076 [.000030] thick Gold2 — 0.00127 [.000050] thick

Without Mounting Posts

Note: If an Insulating Bushing is required see part number 330620 and Panel Cutout on page 54.

10.16 ±0.08 2.64 [.104] Dia. 400 ±.003 Clearance Hole for 2-56 Self-Tapping Screw' (2 Holes) 5.08 ±0.05 [.200 ±.002] 5.08 ±0.05 Mating [.200 ±.002] Face

0.89 ±0.08

[.035 ±.003]

s


(Top View)

G

2.54 ±0.05

[.100 ±.002]

With Mounting Posts



Recommended PC Board Layouts

VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RF Coax Connectors

₹тусо

Electronics

BNC Connectors, 50 Ohm (Continued)



(Top View)

Recommended PC Board Layouts

* Screw for board thickness of 2.38 [.093] or greater Part No. 221108-2. Screw for thickness of less than 2.38 [.093] Part No. 221108-4.

VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

58

Revised 3-07 www.tycoelectronics.com

Catalog 1307191

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


₹ Tyco Electronics

BNC Connectors, 50 Ohm (Continued)





Maximum Panel Thickness 6.1 [.240] Recommended Panel Cutout



Body Material	Center Contact Plating	Part No.
VALOX,	Tin	5226978-1
White	Gold	5226978-3
	Geid	0220070


Lockwasher and Jam Nut





Part No. 1-329632-2

Part No. 1-329631-2



Recommended PC Board Layout


VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

www.tycoelectronics.com spe

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Vertical Metalized Jacks PC Board Mount



Body Plating	Center Contact Plating	Dielectric	Style	Leg Length L	Part No.
	Silver	VALOX	Α	6.35 .250	5227699-1
	Gold	VALOX	Α	6.35 .250	5227699-2
Nickel	Tin	VALOX	Α	6.35 .250	5227699-3
NICKEI	Gold	VALOX	Α	3.81 .150	5414460-1 ¹
	Silver	VALOX	C	4.45 .175	5222420-1
	Gold	VALOX	E	6.35 .250	5415189-1
	Gold	TEFLON	В	3.30 .130	5413969-2
Tin-Lead	Silver	VALOX	C	3.18 .125	5414305-1
	Gold	VALOX	D	3.43 .135	5221123-2

Style B







1With .76 [.030] standoffs on top of legs.

Style C










Style E (Panel Mount)



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

TEFLON is a trademark of E.I. Dupont de Nemours and Company. VALOX is a trademark of General Electric Company.

60


Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

Tyco Electronics






Press Fit Vertical Metalized Jack, PC Board Mount




Part No. 5222006-1



Recommended PC Board Layout PC Board Thickness Not Less Than 0.99 [.093]

Insulating Bushing

Material — Polypropylene Part No. 222163-1 Only to be used on Part Nos. 5222006-1 & 5222462-1




Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 61

www.tycoelectronics.com

Right-Angle Metalized Jacks, PC Board Mount



	Body Plating	Dielectric	Center Contact Length	Part No.
6 8]	Nickel	Polymethyl- pentene	4.34 .171	5413631-1
	Tin	TEFLON	4.34 .171	5413631-2
ι.	Nickel	Polymethyl- pentene	3.33 .131	5413631-3


Body

Center

Part


Recommended PC Board Layout


	8.64
	[.340]
L'	
21.85	\rightarrow
[.860] 25.4	10
[1.0	00]



Body	Dielectric	Contact	Part No.
Nickel	TPX	Gold	5414373-1

Right-Angle Metalized Jacks, PC Board/Panel Mount 27.64 ± 0.51 [1.088 ±.020]





Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

6.6 ± 0.08

Body Plating	Dielectric	Part No.
Tin	TEFLON	5415025-2
Tin	TPX	5415025-1

Lockwasher and Jam Nut see page 59.

TEFLON is a trademark of E.I. Dupont de Nemours and Company. TPX is a trademark of Mitsui Chemicals America, Inc.


62

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Style	Body Material	Center Contact Material	Dielectric		Dimensions		Comparable UG/U	Packaging No.	Part No	
Style	and Plating	and Plating	Dielectric	D	E	F	Connector	Per Pkg.	ran Nu.	
	Brass, Nickel	BE CU, Gold (30) ²	TEFLON	32.54 1.281	26.19 1.031	14.27 .562	274A	Bulk (100)	221543-2	
		PH BR, Gold (15) ²	Acetal	33.02 1.300	27.31 1.075	14.50 .571	_	Bulk (100)	5413592-2	
А	Zinc,	BE CU, Gold (30) ²	Acetal	33.02 1.300	27.31 1.075	14.50 .571	_	Bulk (100)	5413592-6	
	Nickel	PH BR, Gold (15) ²	Acetal	33.02 1.300	27.31 1.075	14.50 .571	_	Individual (1) ³	5413592-9	
	BE CU, Silver (200) ²			Acetal	33.02 1.300	27.31 1.075	14.50 .571	_	Individual (1)	1-5413592-1
В	Zinc, Nickel	BE CU, Gold (30) ²	Acetal	32.54 1.281	31.12 1.225	17.15 .675	_	Bulk (100)	5413366-21	
C	Brass, Nickel	BE CU, Silver (200) ²	TEFLON	32.54 1.281	23.37 .920	—	_	Bulk (100)	221988-1	
U	Zinc, Nickel	PH BR, Gold (50) ²	Acetal	32.54 1.281	23.62 .930	_	_	Bulk (100)	5413592-2 5413592-6 5413592-9 1-5413592-1 5413366-21	

¹Gray insulation cover

²(Microinches min thickness)

³(Special graphics)

Tee Adapter Covers

Material — Polypropylene, general purpose

Part No.
221586-1
221586-3




TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Gold

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Max

64

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Nickel

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

5414666-1


Polymethylpentene

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


26.97

[1.062]



Jack Covers

Body Plating	Part No.
Silver	330022
Nickel	1-330022-2





Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

* The Short Cover is required when mating the Terminator with a Tee Adapter.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

BNC Connectors, 75 Ohm

Plugs, Crimp

Tyco Electronics

These connectors have been designed for optimum performance and have a true 75 ohm impedance the complete length of the connector. The crimp die tooling listed below is different from the equivalent 50 ohm connectors.

Hex and O Crimp 14.53 [.572] Dia. Max.

Plugs

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
179, 179A, 179B, 187,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2	_	5413589-8
187A, 161, BELDEN 9221	0 Crimp	Gold	Nickel	Polyethelene	Commercial	35.56 1.140	318451-2	_	5221185-8
AT 9 T 705 A	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2	_	1-5413589-0
AT&T 735A	0 Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58174-1	58248-3	1-5221185-8
	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-2	_	5413589-3
BELDEN 8218	0 Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58174-1	58248-3	5221185-3
140, 210, 62, 62A, 62B, 59, 59A, 59B,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-1	_	5413589-2
BELDEN 9291, 9209, 9269	0 Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58536-1	58248-2	5221185-2
302, BELDEN 89269, 88241, Hi-Temp 62A, Times PL-62, Berk Tek BTDC-59, BTDC-62	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-1	_	5413589-1
BELDEN 8212, 9104, 9112, 9167, 9240, 9259,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-1	_	5413589-9
9266, Times FM-59, (RG 59 Type with 20 AWG C.C.)	0 Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58536-1	58248-2	5221185-9
BELDEN 9145.	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-1	_	5413589-7
AT&T 734A	0 Crimp	Gold	Nickel	Polyethelene	Commercial	27.69 1.090	58536-1	_	1-5221185-0
BELDEN 9248, 9114	0 Crimp	Gold	Nickel	Polyethelene	Commercial	25.65 1.010	58536-1	_	5221185-1
6, 6A	O Crimp	Gold	Nickel	Polyethelene	Commercial	37.85 1.490	58538-1	58248-1	5221185-7
BELDEN 8281, 9141, 9231,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	29.46 1.160	58425-3	—	5413589-5
Western Electric 724, 728, 3049	O Crimp	Gold	Nickel	Polyethelene	Commercial	28.45 1.120	58538-1	58248-1	5221185-5
COMM/SCOPE S59 Hec	0 Crimp	Gold	Nickel	Polyethelene	Commercial	28.96 1.140	58536-1	_	2-5221185-9
COMM/SCOPE F59 Hec-z	0 Crimp	Gold	Nickel	Polyethelene	Commercial	28.96 1.140	58536-1	_	3-5221185-1

AT&T is a trademark of AT&T Corporation. BELDEN is a trademark of Belden Wire and Cable Company. COMM/SCOPE is a trademark of Commscope, Inc.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

66

Catalog 1307191 Dir Revised 3-07 and www.tycoelectronics.com are

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Plugs for JIS Cables, Crimp

₹ Tyco Electronics

Plating

Body—Nickel Center Contact—Gold



JIS Cable	Termination Type	Dielectric	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
3C-2V	Hex Crimp	Polymethylpentene	29.46 1.160	58425-1	1-5413589-1
2.5C-2V	Hex Crimp	Polymethylpentene	29.46 1.160	58425-2	1-5413589-6

Bulkhead Jacks for JIS Cables, Crimp

Plating

Body --- Nickel Center Contact - Gold Dielectric — Polymethylpentene



JIS Cable	Termination Type	Dielectric	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Part No.
1.5C-2V	Hex Crimp	75Ω	36.83 1.450	58425-2	5413590-4*

*Packaged in 100 pieces per bag.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Right-Angle Plugs, Crimp

Tyco Electronics



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
179, 179A, 179B, 187, 187A, 161 BELDEN 9221	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	58425-2	_	5413588-8
AT&T 735A	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	58425-2	_	1-5413588-0
AT&T KS 19224 L2, RD179 Double Braid	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	58425-2	_	5413588-4
140, 210, 62, 62A, 62B, 59,	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	58425-1	_	5413588-2
59A, 59B, BELDEN 9291, 9209, 9269	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.88 1.570	58536-1	58248-2	5221402-2
BELDEN 8212, 9104, 9112, 9240, 9167, 9259, 9266, Times FM-59, (RG 59 Type with 20 AWG C.C.)	Hex Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.45 1.553	58425-1	_	5413588-9
BELDEN 9145, AT&T 734A	0 Crimp	Gold	Nickel	Polymethyl- pentene	Commercial	39.88 1.570	58536-1	_	5221402-4

AT&T is a trademark of AT&T Corporation. BELDEN is a trademark of Belden Wire and Cable Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

RF Coax Connectors

BNC Connectors, 75 Ohm (Continued)

Jacks, Crimp



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
179, 179A, 179B, 161,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	33.02 1.300	58425-2	_	5413760-8
187, 187A, BELDEN 9221	0 Crimp	Gold	Nickel	Polyethelene	Commercial	30.48 1.200	318451-2	_	5221199-5
BELDEN 8218	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	33.02 1.300	58425-2	_	5413760-3
140, 210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9269	O Crimp	Gold	Nickel	Polyethelene	Commercial	30.48 1.200	58536-1	58248-2	5221199-2
302, BELDEN 88241 89269, Hi-Temp 62A, Times PL-62, Berk Tek BTDC-59, BTDC-62	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	33.02 1.300	58425-1	_	5413760-1
BELDEN 8212, 9104, 9112, 9240, 9167, 9259, 9266, Times FM-59, (RG 59 Type with 20 AWG C.C.)	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	33.02 1.300	58425-1	_	5413760-9
BELDEN 9248, 9114	0 Crimp	Gold	Nickel	Polyethelene	Commercial	30.48 1.200	58536-1	_	5221199-1

BELDEN is a trademark of Belden Wire and Cable Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Dim. L	Interchangeable Dies for PRO-CRIMPER Hand Tool 354940-1 or PRO-CRIMPER Adapter 679304-1	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
179, 179A, 179B, 161,	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	36.83 1.450	58425-2	—	5413590-8
187, 187A, BELDEN 9221	0 Crimp	Gold	Nickel	Polyethelene	Commercial	34.93 1.375	318451-2	_	5221221-5
AT&T KS 19224 L2, RD179 Double Braid	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	36.83 1.450	58425-2	_	5413590-4
BELDEN 8218	Hex Crimp	Gold	Nickel	Polyethelene	Commercial	36.83 1.450	58425-2	—	5413590-3
140, 210, 62, 62A, 62B, 59, 59A, 59B, BELDEN 9291, 9209, 9269	O Crimp	Gold	Nickel	Polyethelene	Commercial	34.93 1.375	58536-1	58248-2	5221221-2
BELDEN 8212, 9104, 9112, 9240 9167, 9259, 9266 Times FM-59 (RG 59 Type with 20 AWG C.C.)	, O Crimp	Gold	Nickel	Polyethelene	Commercial	34.93 1.375	58536-1	58248-2	5221221-7
BELDEN 9114, 9248	O Crimp	Gold	Nickel	Polyethelene	Commercial	34.93 1.375	58536-1	_	5221221-1

AT&T is a trademark of AT&T Corporation. BELDEN is a trademark of Belden Wire and Cable Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


70

Catalog 1307191 Di Revised 3-07 ar www.tycoelectronics.com ar

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

ETyco Electronics

RF Coax Connectors



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Right-Angle Jacks PC Board/Panel Mount


Electronics


₹тусо

Outer Shell — Nickel Dielectric — Polymethylpentene Lockwasher and Jam Nut see page 73.











Maximum Panel Thickness 6.1 [.240] Recommended Panel Cutout

Recommended PC Board Layouts

Without Mounting Posts



With Mounting Posts



* Screw for panel thickness of 2.38 [3/32] or greater Part No. 221108-2. Screw for panel thickness of less than 2.38 [3/32] Part No. 221108-4.

VALOX is a trademark of General Electric Company.

Body	Center	Dimensions				Part No.		
Material	Contact Plating	Α	B	C	L	Without Mounting Posts	With Mounting Posts	
VALOX, Black w/ Compliant Posts (Economy)*	Gold3	6.17 .243	21.21 .835	11.68 .460	2.79 .110	—	5415105-2	
VALOX, Black (Economy)*	Gold3	6.17 .243	21.21 .835	11.68 .460	4.01 .158	_	5415105-1	
VALOX, White	Gold1	6.91 .272	21.21 .835	13.88 .519	3.48 .137	_	5413194-1	
VALOX, White (Economy)*	Gold1	6.91 .272	21.21 .835	13.88 .519	3.48 .137	—	5415634-2	
VALOX, Black	Gold1	6.91 .272	21.21 .835	13.88 .519	3.48 .137	—	5413194-2	
VALOX, Black	Gold1	6.91 .272	21.21 .835	13.88 .519	3.48 .137	—	5415634-1	
(Economy)*	Gold1	8.59 .338	21.21 .835	15.88 .625	3.48 .137	—	5415633-1	
VALOX, White	Gold2	8.59 .338	21.21 .835	15.88 .625	3.48 .137	—	5414459-1	
Metal	Gold1	8.25 .325	20.83 .820	15.88 .625	2.16 .085	—	5222092-1	
Metal	Gold1	8.25 .325	20.83 .820	15.88 .625	_	5222093-1	_	
Metal (Economy)*	Gold1	8.25 .325	20.83 .820	15.88 .625	3.48 .137	—	5414409-1	
Metal with Compliant	Gold1	6.91 .272	20.83 .820	12.70 .500	3.48 .137	—	5415417-1	
Posts (Economy)*	Tin	8.56 .337	21.21 .835	15.88 .625	3.48 .137	—	5415419-1	
Metal	Gold1	8.25 .325	20.83 .820	15.88 .625	3.48 .137	—	5222092-3	
Metal	Gold1	6.91 .272	20.83 .820	12.70 .500	3.48 .137	_	5414907-1	
Metal	Gold1	6.91 .272	20.83 .820	12.70 .500	_	6274072-1	_	
Metal (Economy)*	Gold1	6.91 .272	20.83 .820	12.70 .500	3.48 .137		6274084-1	

*Economy connector uses 50 Ω part with smaller dielectric and stamped and formed contact, Phosphor Bronze contact material (Compare to regular connector which is 75 Ω , screw machined Beryllium Copper).

Plating:

Gold1-0.00076 [.000030] thick

Gold2-0.00127 [.000050] thick

Note: If an Insulating Bushing is required see part number 330620 and Panel Cutout on page 54.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

Revised 3-07 and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are in millimeters

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

BNC Connectors, 75 Ohm (Continued)





Electronics

Plating

₹тусо

Outer Shell --- Nickel Dielectric — Polymethylpentene





Maximum Panel Thickness 6.1 [.240]

Recommended Panel Cutout

Lockwasher and Jam Nut






Part No. 1-329632-2

Part No. 1-329631-2


* Screw for panel thickness of 2.38 [3/32] or greater Part No. 221108-2. Screw for panel thickness of less than **2.38** [3/32] Part No. 221108-4



*Economy connector uses 50 Ω part with smaller dielectric and stamped and formed contact, Phosphor Bronze contact material (Compare to regular connector which is 75 Ω , screw machined Beryllium Copper).

Plating: Gold1 — 0.00076 [.000030] thick

Note: If an Insulating Bushing is required see part number 330620 and Panel Cutout on page 54.



Recommended PC Board Layout

VALOX is a trademark of General Electric Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 73

15.88


[.625]

34.93

[1.375]


Mtg. Hgt.

₹тусо




www.tycoelectronics.com

and inches unless otherwise specified. Values in brackets are standard equivalents. reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



BNC Connectors, 75 Ohm (Continued)



Revised 3-07


and inches unless otherwise specified. Values in brackets are standard equivalents.

reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

BNC Connectors, 75 Ohm (Continued)



Body Plating	Dielectric	Part No.
Tin	TEFLON	6274425-2


Right-Angle Adapter

(Jack-Plug)

Bulkhead Jack-Jack Adapter

₹ Тусо


Electronics




Bulkhead Jack-Jack Adapter

Plating

Body — Nickel Center Contact — Gold Dielectric — Polymethylpentene





TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

76

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Plating

Body — Nickel

Center Contact — Gold Dielectric — Polymethylpentene

36.04 Max.

Part No. 415567-1


[1.419]

RF Coax Connectors

BNC Connectors, 75 Ohm (Continued)

Bulkhead Jack-Push On Plug Adapter

Tyco Electronics



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Mini BNC Connectors, 75 Ohm

Product Facts

₹ Tyco

 Bayonet locking coupling mechanism

Electronics

- 40% more interconnects in the same area
- Compatible with TROMPETER tooling
- Ideal for telecommunications and broadband applications



Tyco Electronics introduces the Mini BNC series of RF connectors to meet the arowing demand for next generation telecommunications and broadband applications where higher connector densities are needed. Preserving the characteristics that have made the standard BNC so popular, the Mini BNC offers the same high performance currently found in standard Tyco Electronics BNC series, but offers 40% more interconnects in the same area.

The Mini BNC offering is an excellent fit for 75 Ohm systems, offering 500 mating cycles, electrical performance through 2 GHz, and is completely intermateable with competitive miniature BNC offerings. Tyco Electronics' Mini BNC product offers the same advantage of the bayonet locking mechanism as our standard BNC, allowing quicker connect and disconnects than standard threaded interfaces. It uses standard BNC installation tooling meaning there is no need for retraining of field telco installers, and it utilizes the same PCB footprint on the jack side, providing a drop in replacement for DS3 telco applications.

Mini BNC connector configurations currently available include PCB, panel mount, and flexible cable. Other options can be reviewed as well, including additional cable sizes, adapters, PCB surface mounting, and tape and reel packaging. Call your local sales office or authorized distributor for additional information or samples of the Mini BNC connector series.

Tyco Electronics is a leading supplier of RF and Microwave connectors and cable assemblies, and provides advanced technology products from well known and industry leading brands, including AMP and M/A-COM.



Shells, Bodies, Mtg Nuts — Brass, nickel plated

Washers — Stainless Steel, nickel plated

Ferrule — Copper or Brass, tin plated Center Contacts — Phos Bronze and Brass, gold plated Dielectrics — PTFE

Electrical Characteristics

Frequency — DC – 2 GHz Nominal Impedance — 75 ohms Voltage Rating — 300 Volts (VRMS maximum) @ Sea Level VSWR —

1.10 max to 500 MHz (Return Loss -26.4 dB)

1.16 max to 1 GHz (Return Loss -22.6 dB)

Insulation Resistance — 1,000 megohms minimum

Dielectric Withstanding Voltage — 1,000 Volts (VRMS maximum) @ Sea Level

Contact Resistance — 12 milliohms maximum

Mechanical Characteristics

Connector Durability — 500 mating cycles

Force to Engage — 7 pounds maximum

Force to Disengage — 1 pound minimum

Center Contact Retention — 2 pounds minimum

Cable Retention — 20 pounds minimum Vibration — EIA-364-28,

Test Condition VII, Condition D **Shock** — EIA-364-27, Method H

Environmental Characteristics Temperature Rating —

-40 to +85°C **Moisture Resistance** — EIA-364-31, Method II, Condition C **Thermal Shock** — EIA-364-32

Note: Performance specifications are typical, but may not apply to all connector types.

Related Product Data

Product Specification — 108-2159 Sample Kit — 1773042

TROMPETER is a trademark of Trompeter Electronics, Inc.

78

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

╙╙

BNC

32.89 [1.29] Ref.


> USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

ШШЦ

Mini BNC


27.52 [1.08] Ref.

Mini BNC Connectors, 75 Ohm (Continued)



	Dimensions										
Α	В	С	D	E	F	G	н	J	К	L	М
8.89–9.14 .350–.360	7.37–7.62 .290–.300	7.11–7.21 .280–.284	6.63–6.73 .261–.265	6.20–6.30 .244–.248	5.03–5.13 .198–.202	4.39–4.50 .173–.177	1.32–1.42 .052–.056	3.86–4.27 .152–.168	7.70 .303 Min.	0.18–0.30 .007–.012	4.01 .158 Min.





Dimensions								
Α	В	С	D	E	F	G	Н	J
7.70–7.80 .303–.307	—	0.71–0.76 .028–.030	11.43–11.68 .450–.460	4.27–4.93 .168–.194	0.94–1.35 .037–.053	1.57–1.68 .062–.066	9.60–9.70 .378–.382	2.50–2.59 .098–.102
				Dimensions				
к	L	Μ	N	Р	Q	R	S	т
1.57–1.68 .062–.066	0.64–0.74 .025–.029	1.47–1.57 .058–.062	0.20–0.30 .008–.012	4.62–4.93 .182–.194	2.84–3.38 .112–.133	29°–31°	14°-16°	6.20–6.30 .244–.248

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

₹ Tyco Electronics


RF Coax Connectors

Mini BNC Connectors, 75 Ohm (Continued)

Flexible Cable — Crimp Attachment

Straight Cable Plug






Cable	Part Number
735A	1274563-1
734A	1274563-2
RG 179	1274563-3

Right-Angle Cable Plug







Cable	Part Number
735A	1274566-1
734A	1274566-2
RG 179	1274566-3

Bulkhead Cable Jack







Recommended Panel Cutout Tolerance: ± 0.08 [.003]

Cable	Part Number
735A	1274568-1
734A	1274568-2
RG 179	1274568-3

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

80


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Mini BNC Connectors, 75 Ohm (Continued)



Description	Part Number
With Hardware	1274663-2
Without Hardware	1274684-1



Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

24.21 [.953]

> USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

0.51 [.020] Typ.

7.65

[.301]

3.94 [.155] Typ.

81

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

Decoupled Connectors

Product Facts

₹ Тусо

 Built-in chip capacitors filter high-frequency noise to panel ground

Electronics

- PC board mounting with vertical and standard or low-profile right-angle configurations
- Cable mount bulkhead BNC version available
- Drop-in replacement for Tyco Electronics standard BNC printed circuit board connectors
- One-piece design and robotic capacity to reduce assembly time



Tyco Electronics capacitively decoupled connectors provide the fast, better way to reduce noise and reduce ground loops on coaxial interconnections. The highfrequency noise generated by fast rise times can cause both false triggering of circuits as well as emissions that can be radiated or conducted outside the equipment. Such emissions can interfere with nearby equipment. Ground loops are also a problem for networked systems. Ground loops are caused when two interconnected units are at different voltage potentials.

The typical way to handle such EMI and ground loop problems is to decouple the cable shield from the ground panel by soldering a ceramic disk capacitor between the cable shield and the panel. The capacitor shunts high-frequency noise to ground. While effective, this approach is time consuming and expensive.

The Capacitively Decoupled connector has built-in chip capacitors. These capacitors establish the electrical contact between the outer shield and a clip. This clip provides a short electrical path between the capacitors and panel. As a result, high-frequency noise is effectively shunted to ground, while the DC path is blocked.

The connectors offer compatibility in design and manufacture. The same footprint and dimensional envelope make them a drop-in replacement for Tyco Electronics standard BNC or TNC printed circuit board connectors. In addition, they can be robotically picked and placed for highspeed automated assembly to pc boards.

Product Specification

108-1263 — BNC Decoupled PCB Press-Fit Connection 108-1269 — BNC Decoupled PCB Connectors 108-1490 — BNC Decoupled Cable Mount

82


Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


www.tycoelectronics.com

₹ Тусо


Electronics

Decoupled Connectors (Continued)









Maximum Panel Thickness 6.1 [.240] Recommended Panel Cutout

VALOX is a trademark of General Electric Company.


Catalog 1307191 Revised 3-07


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Decoupled Connectors (Continued)

Clip Styles





For use with or without a jam nut



Short Electrical Path For reduced series inductance in ground path

84

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Decoupled Connectors (Continued)

PC Board/Panel Mount Jacks Decoupled to Panel (Continued)

Mounting Post Styles





Compliant

BNC

Description	Capacitance/ Voltage	Clip	Mounting Post	L Mounting Post Length	В*	A *	Style ¹	Part No.
Vertical 50Ω	9400pF 1500VDC	Standard	Standard	3.48 .137	_	_	А	5413476-2
Standard	9400pF 1500VDC	Standard	Standard	4.01 .158	15.88 .625	8.59 .338	В	5413524-2
Right-Angle 50 Ω	9400pF 1500VDC	Standard	Compliant	2.79 .110	15.88 .625	8.59 .338	В	5413524-
Standard Right-Angle V/O Mounting Post $50\Omega^2$	9400pF 1500VDC	Standard	_	_	15.88 .625	8.59 .338	В	5414215-
	9400pF 1500VDC	Standard	Standard	4.01 .158	13.18 .519	6.91 .272	В	5413515-
	20000pF 500VDC	Standard	Standard	4.01 .158	13.18 .519	6.91 .272	В	5413515-
Low Profile Right-Angle 50Ω	7900pF 1600VDC	Standard	Compliant	2.79 .110	13.18 .519	6.91 .272	В	5413515-
0012	9400pF 1500VDC	Standard	Compliant	4.70 .185	13.18 .519	6.91 .272	В	5413515
	9400pF 1500VDC	Standard	Compliant	2.79 .110	13.18 .519	6.91 .272	В	5413515
Low Profile Right- Angle W/Special Clip & High Temperature Housing 50Ω	9400pF 500VDC	Extended	Compliant	2.79 .110	13.18 .519	6.91 .272	В	5414284
Low Profile Right-Angle W/High Temperature Housing 50Ω	9400pF 500VDC	Flush	Compliant	4.70 .185	13.18 .519	6.91 .272	В	5414352·
Low Profile Right-Angle 75 Ω	9400pF 1500VDC	Standard	Standard	4.01 .158	13.18 .519	_	В	5414094
Ultra Low Profile Right-Angle 75 Ω	9400pF 1500VDC	Standard	Standard	4.01 .158	6.17 .243	11.68 .460	_	5415103
	9400pF 1500VDC	Standard	Compliant	2.79 .110	6.17 .243	11.68 .460	_	5415103

¹See pages 83 and 84 for Connector Styles. ²See customer drawing for PC Board Layout. *See page 83 for dimension reference.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Decoupled Connectors (Continued)

Right-Angle BNC Jack PC Board/Panel Mount Decoupled to Panel ESD Protected

₹тусо



See page 83 Style B for panel cutout and recommended PC board configuration.


Note: See Tyco Electronics Customer drawing for voltage breakdown rating.

Description	Capacitance/ Voltage	Contact Plating	Clip	Mounting Post	L Mounting Post Length	B*	A *	Part No.
50Ω Product								
Low Profile Right-Angle W/ ESD Protection	7900pF 1500VDC	Gold1	Standard	Compliant	2.79 .110	13.18 .519	6.91 .272	5414651-3
75Ω Product								
Standard Right-Angle W/ ESD Protection	9400pF 1500VDC	Gold1	Standard	Standard	4.01 .158	15.88 .625	8.59 .338	5415085-1
Low Profile Right-Angle ESD Protected	9400pF 1500VDC	Gold1	Flush	Compliant	2.79 .110	13.18 .519	6.91 .272	5415216-1


*See page 83 for dimension reference.


Right-Angle BNC Jack PC Board/Panel Mount Decoupled to Board ESD Protected

Capacitance	Voltage	
9400pF	1500VDC	



Part No. 5415205-1





Recommended Panel Cutout

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


86

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

₹_{Tyco}

Electronics



Description	RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Dielectric	Style	Interchangeable Dies for Hand Tool 69710-1 & 626 Pneu. Head 318161-1	Part No.
50Ω	RG 58, 58A, 58B, 58C	Hex Crimp	Gold	Nickel	Polymethylpentene	Commercial	58436-1	5414758-1
50Ω	RG 174, 174A, 316, 188, 188A	Hex Crimp	Gold	Nickel	Polymethylpentene	Commercial	58436-3	5414758-2
50Ω	RG 174, 174A, 316, 188, 188A	Hex Crimp	Gold	Nickel	Polymethylpentene	Commercial	58436-3	5414758-3
75 Ω ESD	RG 179, 187	Hex Crimp	Gold	Nickel	Polymethylpentene	Commercial	58425-2	5415779-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Self-Terminating PC Board Connectors

Product Facts

₹тусо

 Built-in chip resistor terminates the signal line to the proper characteristic impedance when in the unmated state

Electronics

- Can be ordered with standard resistance values (50, 75 and 100 Ohms)
- Fits into printed circuit board footprint of standard BNC PCB connectors
- One-piece design is compatible with robotic insertion and wave soldering

Tyco Electronics Self-Terminating printed circuit board BNC connectors provide the capability to automatically terminate an input-output port to the system characteristic impedance. This feature eliminates the need for external terminators when an I/O port is not being used. The Self-Terminating BNC jack contains a chip resistor which bridges the signal and ground paths when the connector is not mated to a BNC plug. When mated, the resistor is switched out of the circuit for direct signal transmission to the board.

The footprint of this connector is compatible with standard BNC connectors, allowing it to be easily installed into existing circuit board designs and suitable for robotic insertion for high speed automated assembly onto the PC board.


The Self-Terminating BNC is available in standard resistance values for use in networking and video systems. Contact Tyco Electronics for new designs that include switching and capacitively decoupled versions.

Material

Body — Polyester, PBT, black **Dielectric** — Polyester, PBT, natural


Plating

Shell — Tin Center Contact — Gold on mating end and Tin on solder tails









Product	Termination Resistance	Part Number
Self-Terminating BNC PCB	75Ω	5414367-2

88

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Twin BNC Connectors

Product Facts

- Crimp connectors require only one-stroke crimping of both conductors, plus braid and cable support
- Lower installed cost with one-stroke crimp
- Reduced noise levels because of Tyco Electronics solderless crimping techniques
- Captive inner contact stability
- No danger of heat damage to coaxial cable
- Ease of inspection
- Listed under the Component **Program of Underwriters** Laboratories Inc., (UL) File No. E81956
- PC Board soldered connectors are recognized under the Component Program of Underwriters **"** Laboratories Inc., File No. E81956
- Certified by Canadian Standards **(**\$<u>P</u>® Association File No. LR 7189

The Twin BNC Connector is a quick connect/disconnect, weatherproof connector designed in accordance with MIL-C-39012 to meet the stringent requirements of MIL-STD-1553 Multiplex Data Bus.

These twin coaxial cable connectors are a unique development by Tyco Electronics which has resulted in the production of high level RF components. Termination of these connectors to twin conductor cable is made with Tyco Electronics exclusive one crimp method which simultaneously terminates inner conductors, outer braid and cable support with one stroke of the matching Tyco Electronics tool.

These rugged connectors accommodate today's most commonly used twin conductor cable sizes.

Materials

Brass - QQ-B-626 Bervllium Copper — QQ-C-530 **TEFLON** — MIL-P-19468 Polypropylene — General purpose **Copper, Annealed**—QQ-C-576 Phosphor Bronze — QQ-B-750 Silicone Rubber — ZZ-R-765

Plating

Silver — QQ-S-365 Packaging — All connectors are pack-Nickel - QQ-N-290 aged individually unless otherwise Tin — ASTM-B-545



Electrical Characteristics

Nominal Impedance --- Non-constant Working Voltage - 500 volts rms sea level Insulation Resistance —

5000 megohms min. Dielectric Withstanding Voltage-1500 volts rms sea level

Mechanical Characteristics Mating/Unmating -

Bayonet lock-quick connect/ disconnect Cable Attachment --- Crimp type --Simultaneous center and braid Coupling Nut Retention - 100 lbs. [444 N] min.

Cable Retention - 25 lbs. [111 N] min., RG 108A/U cable Durability - 200 cycles per MIL-C-39012

Environmental Characteristics

Temperature Range — -55°C to +85°C

Vibration --- MIL-STD-202, Method 204, Condition B Shock --- MIL-STD-202, Method 213, Condition I, 100 G's Salt Spray - MIL-STD-202, Method 101, Condition B

Temperature Cycling --- MIL-STD-202, Method 102, Condition C

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Catalog 1307191 Revised 3-07

noted.

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Twin BNC Connectors (Continued)

Plugs




RG/U Cable	Center Contact Plating	Body Plating	Dielectric	Integral Die Hand Tool	Part No.
108, 108A	Silver	Silver	TEFLON	69667	5332225
BELDEN 9272, 89272	Silver	Nickel	Polypropylene	69667	5332225-5
TROMPETER TWC-124-2	Silver	Silver	TEFLON	69667	5332225-3
ROLM 49D2401 RAYCHEM 7824D013	Silver	Nickel	Polypropylene	69667	5332225-6

Bulkhead Jack



H = 17.45 [.687] Max. across flats, 20.32 [.800] Max. across points



Maximum Panel Thickness 3.18 [.125]

Recommended Panel Cutout

RG/U Cable	Center Contact Plating	Body Plating	Dielectric	CERTI-CRIMP Hand Tool with Integral Die	Integral Die Hand Tool	Die Insert for Tools: Hand Tool-69710-1, 626 Pneu. Head 318161-1	Part No.
108, 108A BELDEN 9272, 89272	Silver	Silver	TEFLON	—	69667	69708	5332342

BELDEN is a trademark of Belden Wire and Cable Company. ROLM is a trademark of the Rolm Corp. TEFLON is a trademark of E.I. Dupont de Nemours and Company. TROMPETER is a trademark of Trompeter Electronics, Inc.

90

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

₹тусо

Electronics



www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors


₹ Tyco Electronics

Twin BNC Connectors (Continued)





PCB Configuration



Part No. 5415832-1

Recommended Panel Cutout

Part No. 5332215

92

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

F Series and **G** Series Connectors

Product Facts

₹ Тусо

- Designs meet SCTE requirements where applicable
- Plugs, jacks and adapters available

Electronics

- Board mount and cable mount available
- Surface mount connectors available
- Sealed product available
- High current carrying capabilities



Tyco Electronics F Series connectors offer performance, which is driven by evolving OEM requirements and expectations. Improved VSWR beyond 1 GHz, high current carrying capability, and pressure sealed products are now part of the standard product offering. Designs compliant with ANSI/SCTE, Bellcore, UL/CSA, and various other industry and agency standards are also available.

Both cable applied and PCB terminated products are offered in a variety of styles. The cable connectors are designed for fast, accurate termination with tools common to the industry. Application cost reductions can be achieved using Tyco Electronics PCB terminated products; pressfit designs eliminate the need for soldering. Center of gravity control and PCB retention designs prevent tipping and eliminate fixturing during soldering. Integral mechanical keys and "D flats" prevent rotation in panels.

These products provide the highly reliable, cost-effective solutions demanded by today's evolving marketplace.

Product Specification

108-1518 — Connector Coaxial, F Series, RF, Single Crimp Plug 108-1643 — Connector Coaxial, F Series, RF, PCB Mounted 108-1755 — Connector Economy, F Series, RF Coaxial, PCB 108-1757 — Connector, 15 amp, G Series Jack, PCB 108-1758 — Connector, F Series Jack, PCB, Surface Mount 108-1629 — Feedthrough, Sealed F Port Jack

Instruction Sheets

408-9221 — Coaxial Series F Plug Connectors 408-4402 — Series F & G Coaxial Cable Bulkhead Jack Connector 408-4291 — PRO-CRIMPER II Hand Tool Assembly 58622-1 and 58622-2

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



F Series Connectors

Crimp Style, Hex C Crimp Style Screw-On Style Α в RG/U Cable Termination Body Plating "B' PRO-CRIMPER Style Part No. Туре Threads Hand Tool Assembly 58425-3, 58436-2, or 58621-2 6 Crimp Nickel А 221539-2 6 Screw-On Nickel В M7x1 221540-2 59 BELDEN 9104, 9100* 58425-3, 58436-2, С Crimp Nickel ____ 414766-1 or 58621-2 58425-3, 58436-2, 59 Crimp Nickel С 414766-8 _ or 58621-2

*NID to inside cable.


† 8.23 [.324] Hex Crimp.



21.59 [.850] Max.

RG/U Cable	Termination Type	Center Contact Plating	Body Plating	Termination Tooling	Part No.
179 Headend Crimp Tin Nickel		Braid: M 22520/5-01 w/ DANIELS Die Set Hx4-1637 (.128 Hex)	5415226-1		
Patch Panel	Crimp	Tin	Nickel	Contact: M 22520/2-01 w/ DANIELS Positioner K727, Pos. 2	5415220-1

Right-Angle Plugs, Crimp



BELDEN is a trademark of Belden Wire and Cable Company. DANIELS is a trademark of Daniels Manufacturing Corporation.

94

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


₹тусо Electronics

RF Coax Connectors





*Connectors will accept a center conductor, diameter of 0.51-1.19 [.020-.047]



PC Board Layout

Recommended Panel Cutout

Body P	Plating	Center Contact		Part		
Barrel	Base	Plating	A	В	C	No.
Nickel	Tin	Tin	29.97 1.180	17.53 .690	12.19 .480	5887078-

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

F Series Connectors (Continued)





Body F	Body Plating Center Contact			Dimensions		Part
Barrel	Base	Plating	Α	В	C	No.
Nickel	Tin	Tin	33.81 1.331	15.75 .620	19.86 .782	5415276-2*

*Connector will accept center conductor diameter range of 0.56-1.19 [.022-.047].


Right-Angle PC Board Mount Jack, High Temperature

*High temperature versions use PTFE dielectric (see table)





Recommended Panel Cutout



PC Board Layout

Dielectric			Solder Post		Dimensions	Part	
Bottom	Middle	Front	Plating	A	В	C	No.
Acetal	Acetal	Polypropylene	Nickel	35.61 1.402	16.89 .665	26.11 1.028	5415024-1
Acetal	Acetal	Polypropylene	Tin	35.61 1.402	16.89 .665	26.11 1.028	5415024-3
PTFE	PTFE	PTFE	Tin	25.40 1.00	17.91 .705	14.99 .590	5415214-1*

*Pin in paste reflow / high temperature processing.

\sim	\sim
u	h
	U.

Catalog 1307191 Di Revised 3-07 ar sp www.tycoelectronics.com ar

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

₹тусо


Electronics

F Series Connectors (Continued)



Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208





Catalog 1307191 Revised 3-07 www.tycoelectronics.com

98


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

G Series Connectors (Continued)

Adapters

F Jack to G Jack Bulkhead Adapter





Part No. 415327-1


Recommended Panel Cutout

F Jack to G Plug Bulkhead Adapter

Connector will accept center conductor diameter range of **0.51–1.19** [.020–.047]. Panel nut 887003-3 available for float mounting.



Part No. 415523-1



Recommended Panel Cutout

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors

Product Facts

Ŧ Тусо

Performance to 12.4 GHz and beyond

Electronics

- Available in various base metal options, including stainless steel, brass and zinc diecast
- Uses industry standard crimp tools and processes
- Available with corrosion resistant, non-magnetic White Bronze plating
- Meets all performance requirements for MIL-C-39012.



Tyco Electronics offers a complete line of SMA connectors designed for performance to 18 GHz to satisfy the growing demand for SMA connectors in the wireless communications industry. The SMA product line offers stainless steel bodies, as well as nonferrous metals. Various plating options are available, including Gold and White Bronze. The SMA interface is fully compatible with Mil-C-39012.

While still offering various options on military (QPL) approved connectors, Tyco Electronics has developed a complete offering tailored to the commercial Communications industry. This includes 3 piece flexible cable products for popular RG 316, 142 and RD 316 cable utilizing industry standard HEX crimps.

The SMA series meets the performance, quality and application requirements of the commercial marketplace. This includes White Bronze plating, a unique finish developed by Tyco Electronics to address the performance needs of the telecommunications market. This plating is highly resistant to wear, and contains no ferrous metals, thus displaying excellent intermodulation characteristics.

To satisfy the broad range of commercial applications, SMA connectors are available in a broad range of standard configurations including; straight and right-angle cable applied plugs, bulkhead cable jacks, two and four hole flange mount panel jacks, straight and right-angle pcb mount jacks and various between and in series adapters. Numerous packaging and testing options are also available to meet specific system criteria as well.

Additionally, standard military approved (QPL) interfaces are offered as well. Including connectors for semi-rigid cable and micro strip applications.

The 3 Piece SMA offering is designed especially for applications in cellular infrastructure where InterModulation Products (IMP) must be minimized. By limiting non-linearities within the connectors, IMP is reduced and increased channel capacity can be offered.

Between Series Adapters For SMA Between Series Adapters, see pages 251-260.

100

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued)

Specifications

	MIL-C-39012 Applicable Paragraph	
General		
Material	3.3	Steel corrosion resistant per ASTM-A-582 and ASTM-A-484, Type 303. Beryllium copper per ASTM-B-196. PTFE Fluorocarbon per ASTM-D-1710.
Finish	3.3.1	Center contacts shall be gold plated to a min. thickness of .00127 [.00005] in accordance with MIL-G-45204, ASTM-B-488. All other metal parts shall be finished as to provide a connector which meets the corrosion requirements.
Design	3.4	The design shall be such that the outline shown in this catalog and the interface dimensions of MIL-STD-348A are met.
Electrical		
Insulation Resistance	3.11	The insulation resistance shall not be less than 10,000 megohms.
Corona Level	3.22	Refer to applicable military slash sheet, product drawing or spec.
Dielectric Withstanding Voltage	3.17	Refer to applicable military slash sheet, product drawing or spec.
RF High Potential	3.23	Refer to applicable military slash sheet, product drawing or spec.
Contact Resistance	3.16	Refer to applicable military slash sheet, product drawing or spec.
VSWR	3.14	Refer to applicable military slash sheet, product drawing or spec. Frequency range dependent on cable used.
RF Leakage	3.26	Refer to applicable military slash sheet, product drawing or spec.
Insertion Loss	3.27	Refer to applicable military slash sheet, product drawing or spec. Frequency range dependent on cable used.
Mechanical		
Force to Engage	3.5.1	The torque required to engage and disengage shall not exceed 2 inlbs. The longitudinal force is not applicable.
Coupling Nut Retention	3.25	60 lbs. min. Applicable for plug connectors only.
Coupling Proof Torque	3.6	15 inlbs. min. Applicable for plug connectors only.
Cable Retention	3.24	Refer to applicable military slash sheet or consult factory.
Mating Characteristics	3.7	Applicable to jack connectors only. Reference MIL-STD-348A for dimensions; oversize test pin .953 [.0375] min. dia., .76 - 1.14 [.030045] deep, insertion force 3 lbs. max. with .940 [.0370] min. dia. pin, withdrawal force 1 oz. min. with .902 [.0355] max. dia. pin.
Connector Durability	3.15	The connector to be tested and its mating connector shall be subjected to 500 insertion and withdrawal cycles at 12 cycles per minute max. The connector shall show no evidence of mechanical failure and shall meet the mating characteristic requirements.
Recommended Mating Torque	_	7 to 10 inlbs.
Environmental		
Vibration	3.18	Specification MIL-STD-202, method 204, test condition D
Shock	3.19	Specification MIL-STD-202, method 213, test condition I
Thermal Shock	3.20	Refer to applicable military slash sheet or consult factory.
Corrosion (Salt Spray)	3.13	Specification MIL-STD-202, method 101, test condition B.
Moisture Resistance	3.21	Specification MIL-STD-202, method 106. No measurements at high humidity. Insulation resistance shall be at least 200 megohms within 5 minutes of removal from humidity.

Tyco Electronics

SMA Connectors (Continued)

Electrical

Connector Type	Cable	Frequency Max. (GHz)	VSWR x (fGHz) -	Contact R (milliohr Center Contact	lesistance ms max.) Outer Contact	Insulation Resistance (megohms min.)	Dielectric Withstanding Voltage (Volts RMS)	Corona Extinction Voltage at 70,000 Ft. (V RMS min.)	RF Transmission Loss	RF High Potential at 5 MHz (V RMS)	RF Leakage (dB min.)
Straight Cable Plug without Contact	RG 402 (3.58 [.141])	Note 1	1.02 + .005	N/A	2.0	10,000	N/A	250	N/A	670	-(90-fGHz
without oontact	RG 405 (2.16 [.085])	18.0	1.05 + .005	2.0	2.0	10,000	1000	250	.03 √f(GHz)	670	-(90-fGHz
	RG 402 (3.58 [.141])	18.0	1.05 + .005	2.0	2.0	10,000	1500	375	.03 √f(GHz)	1000	-(90-fGHz
Straight Cable Plugs	3.58 [.141] Microporous		1.05 + .005	2.0	2.0	10,000	1500	375	.03 √f(GHz)	1000	-(90-fGHz
& Jacks Solder	RG 401 (6.35 [.250])	18.0	1.07 + .007	2.0	2.0	10,000	1500	375	.03 √f(GHz)	1000	-(90-fGH
Attachment	RG 174, 188, 316	Note 1	1.15 + .01	2.0	2.0	10,000	750	190	.06 √f(GHz)	500	-(60-fGH
	RG 55, 58, 141, 142, 223, 303, 400	Note 1	1.10 + .005	2.0	2.0	10,000	1000	250	.06 √f(GHz)	670	-(60-fGHz
Straight Cable Plugs	RG 405 (2.16 [.085])	12.4	1.10 + .015	2.0	2.0	10,000	1000	250	.03 √f(GHz)	670	-(90-fGH;
& Jacks Solder Clamp Attachment	RG 402 (3.58 [.141])	12.4	1.07 + .01	2.0	2.0	10,000	1500	375	.03 √f(GHz)	1000	-(90-fGH
Straight Cable Plugs	RG 55, 58, 141, 142 223, 400	Note 1	1.10 + .005	2.0	2.0	10,000	1000	250	.06 √f(GHz)	670	-(60-fGH
& Jacks Clamp Attachment	RG 174, 188, 316	Note 1	1.15 + .01	2.0	2.0	10,000	750	190	.06 √f(GHz)	500	-(60-fGH
AllaGIIIIEIII	RG 180, 195	Note 1	_	2.0	2.0	10,000	750	190		500	-(60-fGH
	RG 55, 142, 223, 400	Note 1	1.10 + .005	2.0	2.0	10,000	1000	250	.06 √f(GHz)	670	-(60-fGH
Straight Cable Plugs	RG 58, 141, 303	Note 1	1.10 + .005	2.0	2.0	10,000	1000	250	.06 √f(GHz)	670	-(60-fGH
& Jacks Crimp	RG 174, 188, 316	Note 1	1.15 + .01	2.0	2.0	10,000	750	190	.06 √f(GHz)	500	-(60-fGH
Attachment	RG 180, 195	Note 1	—	2.0	2.0	10,000	750	190		500	-(60-fGH
	RG 178, 196	Note 1	1.2 + .02	2.0	2.0	10,000	500	125	.06 √f(GHz)	335	-(60-fGH
	RG 401 (6.35 [.250])	18.0	1.07 + .01	2.0	2.0	10,000	1500	375	.05 √f(GHz)	1000	-70 dB m
Straight Cable Plugs	6.35 [.250] Microporous	18.0	1.07 + .01	2.0	2.0	10,000	1500	375	.05 √f(GHz)	1000	-70 dB m
& Jacks Compression Clamp Attachment	6.35 [.250] 3 Spline	18.0	1.07 + .01	2.0	2.0	10,000	1500	375	.05 √f(GHz)		-70 dB m
•	6.35 [.250] 5 Spline	18.0	1.07 + .01	2.0	2.0	10,000	1500	375	.05 √f(GHz)	1000	-70 dB m
	RG 405 (2.16 [.085])	12.4	1.18 + .015	2.0	2.0	10,000	1000	250	.04 √f(GHz)	670	-(90-fGH
	RG 405 (2.16 [.085])	18.0	1.18 + .015	2.0	2.0	10,000	1000	250	.04 √f(GHz)	670	-(90-fGH
Right-Angle Cable	RG 402 (3.58 [.141])	12.4	1.15 + .015	2.0	2.0	10,000	1500	325	.04 √f(GHz)	1000	-(90-fGH
Plugs Solder Attachment	RG 402 (3.58 [.141])	18.0	1.10 + .010	2.0	2.0	10,000	1500	250	.05 √f(GHz)	1000	-(90-fGH
	RG 55, 58, 141, 142, 223, 303, 400	Note 1	1.15 + .01	2.0	2.0	10,000	1000	250	.07 √f(GHz)	670	-(60-fGH
	RG 174, 188, 316	Note 1	1.15 + .02	2.0	2.0	10,000	750	190	.07 √f(GHz)	500	-(60-fGH
	RG 55, 142, 223, 400	Note 1	1.15 + .02	2.0	2.0	10,000	1000	250	.07 √f(GHz)	670	-(60-fGH
Right-Angle Cable	RG 58, 141, 303	Note 1	1.15 + .02	2.0	2.0	10,000	1000	250	.07 √f(GHz)	670	-(60-fGH
Plugs Crimp Attachment	RG 174, 188, 316	Note 1	1.18 + .02	2.0	2.0	10,000	750	190	.07 √f(GHz)	500	-(60-fGH
,	RG 180, 195	Note 1	1.05 . 005	2.0	2.0	10,000	750	190	07 54(011-)	500	-(60-fGH
Right-Angle Cable	RG 178, 196 RG 55, 58, 141, 142, 223, 303	Note 1 Note 1	1.25 + .025 1.10 + .005	2.0	2.0 2.0	10,000	500 1000	125 250	.07 √f(GHz) .08 √f(GHz)	335 670	-(60-fGH
Plugs Člamp	RG 174, 188, 316	Note 1	1.15 + .01	2.0	2.0	10,000	750	190	.08 √f(GHz)	500	-(60-fGH
Attachment	RG 180, 195	Note 1	1.13 + .01	2.0	2.0	10,000	750	190	.00 \ 1(0112)	500	-(60-fGH
	Non-Captured	18.0	1.03 + .004	2.0	2.0	10,000	1000	250	.03 √f(GHz)		-(100-fGF
Flange Mount Plugs	Epoxy Captured	18.0	1.05 + .005	2.0	2.0	10,000	1000	250	.03 √ f(GHz)	670	-(60-fGH
& Jacks Panel or Bulkhead Mount	Mechanical Capture	18.0	1.04 + .004	2.0	2.0	10,000	1000	250	.03 √f(GHz)		-(100-fGF
_ annous mount	Field Replaceable Hermetic Launchers	18.0	1.04 + .006		2.0	10,000	1000	250	.04 $\sqrt{f(GHz)}$	670	-(100-fGF
Bulkhead	Epoxy Captured	18.0	1.07 + .010		2.0	10,000	1000	250	.04 √f(GHz)	670	-(60-fGH
Feedthrough Jacks	Mechanical Capture	18.0	1.07 + .010		2.0	10,000	1000	250	.04 √f(GHz)		-(100-fGF
Right-Angle Flange Mount Jacks	N/A	18.0	1.07 + .015		2.0	10,000	1000	250	.08 √f(GHz)	670	-(90-fGH
Printed Circuit Board	N/A N/A	12.4 18.0	1.15 + .015 N/A	2.0	2.0	10,000	1000	250 250	.08 √ f(GHz) N/A	670 670	-(90-fGH N/A
ount Straight Terminal Right-Angle Printed Circuit	N/A	12.4	N/A	2.0	2.0	10,000	1000	250	N/A	670	N/A
End Launch Stripline Circuit	N/A	18.0	1.05 + .005	2.0	2.0	10,000	1000	250	.03 √f(GHz)	670	-(60-fGH
Surface Launch Stripline Circuit	N/A	18.0	1.05 + .005	2.0	2.0	10,000	1000	250	.03 √f(GHz)	670	-(60-fGH
Right-Angle Surface	N/A	12.4	1.15 + .015	2.0	2.0	10,000	1000	250	.08 √f(GHz)	670	-(60-fGH
aunch Stripline Circuit				2.0	2.0	10,000	1000	250	.08 √f(GHz)	670	-(60-fGH

Maximum operating frequency of cable per MIL-C-17.
 Specifications do not apply to hermetic or compression crimp connectors.
 For Brass SMA: Frequency Range DC-6GHz, Impedance 50 Ohms, Insulation Resistance.

102


Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued)

Interface Mating Dimensions





Plua

lug			Jack		
Dimension	Minimum	Maximum	Dimension	Minimum	Maximum
А	6.35 .250	_	A	5.28 .208	5.49 .216
В	—	4.59 .1808	В	4.60 .181	—
С	_	3.43 .135	С	1.91 .075	1.98 .078
D	0.00 .000	0.25 .010	D	0.00 .000	0.25 .010
E	—	2.54 .100	E	0.38 .015	1.43 .045
F	0.00 .000	0.25 .010	F	2.92 .115	—
G	0.90 .0355	0.94 .037	G	0.00 .000	0.25 .010
Н	0.00 .000	0.38 .015	Н	4.32 .170	—
			J	.124 .049	1.30 .051
			К	5.54 .218	—

Notes:

1. ID to meet VSWR and contact resistance when mated with 0.51 +.025/-.013 [.036 +.0010/-.0005] Dia. Pin. 2. When fully engaged, the two reference planes must coincide with metal to metal contact.

3. Metric equivalents (to the nearest 0.01mm) are given for general information only.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SMA Connectors (Continued) **Flexible Cable**

Straight Cable Plug, Solder






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Dimension A	Instruction Sheet	Part No.
55, 58, 141, 142, 223, 303, 400	Stainless, Gold ¹	No	Solder	19.7 .775	408-4821	1051638-1
174, 188, 316	Stainless, Gold1	No	Solder	17.5 .690	408-4756	1051644-1

¹Coupling nut is passivated stainless steel.

Straight Cable Jack, Solder






Cable Type	Body Material	Contact	Contact	Dimension	Instruction	Part
RG/U	& Finish	Captivation	Attachment	A	Sheet	No.
55, 58, 141, 142, 223, 303, 400	Stainless, Gold	No	Solder	18.5 .730	408-4820	1051852-1

Bulkhead Cable Jack, Solder







Cable Type RG/U Body Material & Finish Contact Captivation Contact Attachment Dimension Instruction Part Sheet No. А RG 55, 58, 141, 142, 300 **24.0** .945 Stainless, Gold No Solder 408-4817 1051861-1 **21.0** .825 174, 188, 316 Stainless, Gold Solder 408-4817 1051942-1 No

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

104

Catalog 1307191 Revised 3-07

and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are in millimeters

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


₹ Tyco Electronics

RF Coax Connectors

SMA Connectors (Continued) Flexible Cable (Continued)

Right-Angle Cable Plug, Solder






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Dimension A	Instruction Sheet	Part No.
55, 58, 141, 142, 223, 303, 400	Stainless, Gold1	Yes	Solder	16.0 .630	408-4816	1052063-1
174, 188, 316	Stainless, Gold1	Yes	Solder	11.2 .440	408-4815	1052067-1

¹Coupling nut is passivated stainless steel.

Straight Cable Plug, Clamp






Cable Type	Body Material	Contact	Contact	Dimension	Instruction	Part
RG/U	& Finish	Captivation	Attachment	A	Sheet	No.
174, 188, 316	Stainless, Pass.	Yes	Solder	2.9 .116	408-4906	1050721-1

Straight Cable Jack, Clamp





Cable Type	Body Material	Contact	Contact	Dimension	Instruction	Part
RG/U	& Finish	Captivation	Attachment	A	Sheet	No.
174, 188, 316	Stainless, Pass.	Yes	Solder	2.9 .116	408-4906	1050903-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


₹ Tyco Electronics

RF Coax Connectors

SMA Connectors (Continued) Flexible Cable (Continued)

Bulkhead Feedthrough Cable Jack, Clamp






Cable Type	Body Material	Contact	Contact	Instruction	Part
RG/U	& Finish	Captivation	Attachment	Sheet	No.
174, 188, 316	Stainless, Pass.	Yes	Solder	408-4704	1050996-1

Right-Angle Cable Plug, Clamp






Cable Type			Contact	Instruction	Part
RG/U			Attachment	Sheet	No.
174, 188, 316	Stainless, Pass.	Mechanical	Solder	408-4965	1051140-1

Straight Cable Plug, Crimp





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
174, 179, 187, 188, 316	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1056443-1
RD316	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-11	408-4661	1056436-1
55, 142, 223, 400	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1056438-1
174, 179, 187, 188, 316	Brass, White Bronze	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1082034-1

¹Use die 1055270-1 to crimp RD316 ferrule. ²Use die 1055880-1 to crimp center contact.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


Catalog 1307191 D Revised 3-07 ar www.tycoelectronics.com ar

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SMA Connectors (Continued) Flexible Cable (Continued)

Straight Cable Jack, Crimp






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Style	Part No.
174, 316	Brass, Nickel	Mechanical	Solder	1	408-4032	А	5447648-3
58, 141, 303	Stainless, Pass.	Mechanical	Solder	1055236-1	408-4704	В	1051867-1
174, 188, 316	Stainless, Pass.	Mechanical	Solder	1055236-1	408-4708	В	1051855-1
178, 196	Stainless, Pass.	Mechanical	Solder	1055236-1	408-4806	В	1051869-1

¹Refer to Tyco Electronics Customer Print for tooling requirement. DANIELS Mil Tooling used for contact and ferrule crimp.

Bulkhead Feedthrough Cable Jack, Crimp





	Cable Type RG/U	Body Material & Finish	Contact Captivation			Instruction Sheet	Part No.
	174, 179, 187, 188, 316	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1056452-1
	RD316	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1 ³	408-4661	1056445-1
	58, 141, 303	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1056450-1
	55, 142, 223, 400	Stainless, Pass.	Mechanical	Solder/Crimp ²	1055236-1	408-4661	1056447-1
_	174, 188, 316	Brass, Nickel	Mechanical	Crimp	1	408-4032	5448103-2

¹Refer to Tyco Electronics Customer Print for tooling requirement. DANIELS Mil Tooling used for contact and ferrule crimp.

²Use die 1055880-1 to crimp center contact.

³Use die 1055270-1 to crimp RD316 ferrule.

DANIELS is a trademark of Daniels Manufacturing Corporation.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


₹ Tyco Electronics

RF Coax Connectors

SMA Connectors (Continued) Flexible Cable (Continued)

Right-Angle Cable Plug, Crimp






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
174, 179, 187, 188, 316	Stainless, Pass.	Mechanical	Solder	1055236-1	408-4659	1056462-1
58, 141, 303	Stainless, Pass.	Mechanical	Solder	1055236-1	408-4659	1056456-1

Right-Angle Cable Plug, Crimp





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
55, 142, 223, 400	Stainless, Pass.	Ероху	Solder	1055236-1	408-4681	1052072-1
174, 188, 316	Stainless, Pass.	Epoxy	Solder	1055236-1	408-4683	1052076-1
178, 196	Stainless, Pass.	Ероху	Solder	1055236-1	408-4801	1052098-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

108


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued) Flexible Cable (Continued)

Straight Push-On






Cable Type	Body Material	Contact	Contact	Part
RG/U	& Finish	Captivation	Attachment	No.
316	Beryllium Copper, Gold	Mechanical	Crimp	1408541-1

Right-Angle Push-On





Cable Type	e Type Body Material		Contact	Part
RG/U	G/U & Finish		Attachment	No.
316	Beryllium Copper, Gold	Mechanical	Solder/Crimp	1274694-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 109

SMA Connectors (Continued) Direct Solder Attachment, Semi-Rigid Cable

Straight Cable Plug






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Pass.	No Center Contact	No Center Contact	1055420-1	408-4761	1050757-1

Straight Cable Plug






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Gold1	No	Solder	1055420-1	408-4764	1050525-1
405 (2.16 [.085])	Stainless, Gold1	No	Solder	1055420-1	408-4765	1050770-1
402 (3.58 [.141])	Stainless, Gold1	No Center Contact	No Center Contact	N/A	—	1050542-1
405 (2.16 [.085])	Stainless, Gold1	No	Solder	1055420-1	—	1050548-1

¹Coupling nut is passivated stainless steel.

Straight Cable Jack





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Gold	No	Solder	1055420-1	408-4767	1050854-1
405 (2.16 [.085])	Stainless, Gold	No	Solder	1055420-1	408-4833	1050859-1

110

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued) Direct Solder Attachment, Semi-Rigid Cable (Continued)

Bulkhead Cable Jack







Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Brass, Gold	No	Solder	1055420-1	408-4768	1082029-1

2 Hole Flange Mount **Cable Jack**








Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Gold	No	Solder	1055420-1	408-4767	1051052-1
405 (2.16 [.085])	Stainless, Gold	No	Solder	1055420-1	408-4883	1051046-1

4 Hole Flange Mount Cable Jack





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Gold	No	Solder	1055420-1	408-4767	1051081-1
405 (2.16 [.085])	Stainless, Gold	No	Solder	1055420-1	408-4883	1051085-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 111

SMA Connectors (Continued) Semi-Rigid Cable

Right-Angle Cable Plug, Direct Solder Attachment






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Solder Assembly Kit Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Gold1	Epoxy	Solder	1055420-1	408-4831	1051151-1
405 (2.16 [.085])	Stainless, Gold ¹	Epoxy	Solder	1055420-1	408-4831	1051157-1
405 (2.16 [.085])	Brass, Gold	Mechanical	Solder	1055420-1	408-4831	1088312-1

¹Coupling nut is passivated stainless steel.

Straight Cable Plug, Crimp






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
405 (2.16 [.085])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4695	1050598-1
402 (3.58 [.141])	Stainless, Pass.	No Center Contact	Solderless	1055835-1	408-4690	1050740-1

Straight Cable Plug — Low Profile, Crimp





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4696	1050602-1
405 (2.16 [.085])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4697	1050611-1

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


112

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued) Semi-Rigid Cable (Continued)

2 Hole Flange, Crimp






Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4954	1051005-1
405 (2.16 [.085])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4689	1051007-1

Right-Angle Cable Plug, Crimp





Cable Type RG/U	Body Material & Finish	Contact Captivation	Contact Attachment	Crimp Tooling Part No.	Instruction Sheet	Part No.
402 (3.58 [.141])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4691	1051145-1
405 (2.16 [.085])	Stainless, Pass.	Mechanical	Solderless	1055835-1	408-4692	1051147-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 113

RF Coax Connectors

SMA Connectors (Continued) Panel Mount, Solder Pot Terminal

.250-36UNS-2A

Ref. Plane

4 Hole Flange Mount Plug Receptacle



4 Hole Flange Mount Jack Receptacle



2 Hole Flange Mount Jack Receptacle



2 Hole Flange Mount Jack Receptacle



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

114

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Body Material & Finish

Stainless, Passivated

Dimensions are shown for reference purposes only. Specifications subject to change.

Contact Captivation

Ероху

.250-36 UNS-2A

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Ø 4.1 [.162]

RF Leakage db min.

-(60-fGHz)

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Part

No.

1052534-1

[.625]


Ø 2.6 [.102] 2 Plcs.

Temperature Range

-65 to 125° C


14.6 [.575] **0.8** [.030] 9.5 [.375] **5.7** [.223] 7.6 Ref. Plane [.299] Ref. 1.7 [.065] Ø 0.8 -10 [.031] 12.2 * * [.481] 1 1 Ø 15.9

> Ø 1.3 [.050]




Ероху	-(60-fGHZ)	-65 to 125° C
9.5 [.375] [.065]	0.8 Dia. [.223] Typ [.031] Min. 1.3 [.050] Dia.	15.9 12.2 [.625] [.481] 2.6 Dia. [.102] 2 Plcs.


			[.102] 2 Plcs.	
Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	Part No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1052544-1



RF Leakage Temperature Range Part db min. No. 1052324-1



1 Θ Ø 1.3 [.050] 7.6 [.299]




Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1052422-1


RF Coax Connectors

SMA Connectors (Continued) Panel Mount

Bulkhead Feedthrough Jack Receptacle, Solder Pot Terminal









Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Epoxy	N/A	-65 to 125° C	1053092-1

Press-In Jacks, Straight Terminal




Part Number 1460468



Oraclest DE Losless

Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	Part No.
Brass, White Bronze	Mechanical	N/A	–65 to 125° C	1460468-1
Brass, Gold	Mechanical	N/A	–65 to 125° C	1460469-1

Press-In Cable, Jack Panel



Note: Part Numbers are RoHS	Cable Type RG/U	Body Material & Finish	Contact Captivation	Temperature Range	Part No.
compliant except: Indicates	316 D	Brass, Gold	Mechanical	–65 to 125° C	619115-1
non-BoHS compliant					

Catalog 1307191 Revised 3-07


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued) Panel Mount, Straight Terminal

4 Hole Flange Mount Jack Receptacle






Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	Part No.
Stainless, Passivated	None	-(100-fGHz)	-65 to 165° C	1052518-1
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1052523-1
Stainless, Gold	Ероху	-(60-fGHz)	-65 to 125° C	1052522-1

2 Hole Flange Mount Plug Receptacle






Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1052349-1

2 Hole Flange Mount Jack Receptacle





Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1052552-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 D Revised 3-07 a www.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


_

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued) Panel Mount, Straight Terminal (Continued)

Bulkhead Feedthrough Jack Receptacle






Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	1053222-1

2 Hole Flange Mount Right-Angle Jack Receptacle






Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Mechanical	-(90-fGHz)	-65 to 165° C	1052986-1

4 Hole Flange Mount Right-Angle Jack Receptacle





Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	Part No.
Stainless, Passivated	Mechanical	-(90-fGHz)	-65 to 165° C	1052978-1
Stainless, Passivated	Mechanical	-(90-fGHz)	-65 to 165° C	1052982-1

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

SMA Connectors (Continued) **Panel Mount**

4 Hole Flange Mount Jack **Receptacle**, Straight Terminal







Body Material & Finish	Contact Captivation	Slot Width +.076/025 [+.003/001]	RF Leakage db min.	Temperature Range	Part No.
Stainless, Passivated	Epoxy	0.5 [.018]	-(60-fGHz)	-65 to 125° C	1052563-1

4 Hole Flange Mount Plug Receptacle, Tab Terminal







8.6 [.340] Typ.


Ø 2.6 4 Plcs.

[.102]

Body Material	Contact	Tab	RF Leakage	Temperature	Part
& Finish	Captivation	Width	db min.	Range	No.
Stainless, Passivated	Epoxy	1.3 [.050]	-(60-fGHz)	-65 to 125° C	1052360-1

4 Hole Flange Mount Jack Receptacle, Tab Terminal





& Finish	Contact	lab Width	db min.	Temperature Range	No.
Stainless, Passivated	Epoxy	.51 [.020]	-(60-fGHz)	-65 to 125° C	1052898-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

118

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

. -


> Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMA Connectors (Continued)

2 Hole Flange Mount Jack Receptacle, Panel Mount, Tab Terminal






Body Material	Contact	Horizontal	RF Leakage	Temperature	Part
& Finish	Captivation	Tab	db min.	Range	No.
Stainless, Passivated	Epoxy		-(60-fGHz)	-65 to 125° C	1052577-1

4 Hole Flange Mount Jack Receptacle, for Microstrip Transmission Line Circuits






Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Ероху	-(60-fGHz)	-65 to 125° C	

2 Hole Flange Mount Jack Receptacle, for Microstrip Transmission Line Circuits





Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Stainless, Passivated	Ероху	-(60-fGHz)	-65 to 125° C	1052902-1

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 119

SMA Connectors (Continued) Field Replaceable Hermetic Launchers (Continued)

4 Hole Flange Mount Jack **Receptacle with EMI/RFI** Gasket

Electronics

₹_{Тусо}



4 Hole Flange Mount Jack Receptacle without EMI/RFI Gasket



2 Hole Flange Mount Jack Receptacle with EMI/RFI Gasket



2 Hole Flange Mount Jack **Receptacle without EMI/RFI** Gasket, Field Replaceable **Hermetic Launchers**





Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

EMI Gasket Accepts Pin Dia. A .250-36UNS-2A Ð \oplus 12.7 [.500] Ref **8.6** [.340] 2 Plcs. ļ \oplus \oplus Ref. Plane **0.1** [.005] Ref. Ø 2.6 [.102] 4 Plcs. 1.7 7.6 [.065] Ref. [.299] 9.5 [.375]


Material & Finish	Captivation	Pin Diameter A	Part No.
Stainless, Passivated	Mechanical	.38 [.015]	1052684-1
	Meenamear	.00 [.010]	100200



Material & Finish	Captivation	Pin Diameter A	Part No.
Stainless, Passivated	Mechanical	.91 [.036]	1052643-1



Material & Finish	Captivation	Pin Diameter A	Part No.
Stainless, Passivated	Mechanical	.30 [.012]	1052628-1
Stainless, Passivated	Mechanical	.38 [.015]	1052689-1
Stainless, Passivated	Mechanical	.46 [.018]	1052634-1




Material & Finish	Captivation	Pin Diameter A	Part No.
Stainless, Passivated	Mechanical	.51 [.020]	1052652-1
Stainless, Passivated	Mechanical	.91 [.036]	1052646-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

RF Coax Connectors

SMA Connectors (Continued)




Style 2




Material & Finish	Style No.	Part No.
Stainless, Gold	1	1053354-1
Brass, Gold	2	221789-1
Brass, Gold	2	221789-3
Brass, Nickel Plate	3	6274096-1

PC Board Mount Right-Angle Jack







Material & Finish	Style No.	Part No.
Stainless, Gold	1	1053378-1
Stainless, Gold	2	221790-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com are

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

SMA Connectors (Continued)

In-Series Adapter, Jack to Jack

₹ Tyco Electronics



In-Series Adapter, Plug to Plug




In-Series Adapter, Jack to Plug, Right-Angle




In-Series Adapter, Jack to Jack, Right-Angle






Frequency	Material & Finish	Captivation	Part No.
DC-18.0GHz	Stainless, Gold	Epoxy*	1053488-1




Frequency	Material & Finish	Captivation	Part No.
DC-18.0GHz	Stainless, Passivated	Epoxy*	1053635-1

*All adapters listed above employ epoxy captivation. Mechanically captivated versions are also available. Please consult Tyco Electronics.



Frequency	Material & Finish	Captivation	Part No.
DC-12.4GHz	Stainless, Passivated	Mechanical	1055065-1



Frequency	Material & Finish	Captivation	Part No.
DC-12.4GHz	Stainless, Passivated	Mechanical	1055018-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

122

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

SMA Connectors (Continued)






In-Series Adapter, Jack to Plug, Connector Saver




In-Series Adapter, Jack to Jack, Bulkhead Feedthrough




Test Adapter, Plug to Jack, Quick Release






Frequency	Material & Finish	Captivation	Part No.
DC-18.0GHz	Stainless, Passivated	Epoxy	1054426-1



*Mechanically captivated version available. Please consult Tyco Electronics.



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

QMA Connectors

Snap-On SMA Series of RF Connectors

Electronics

Product Facts

₹ Tyco

- Positive snap-on interface facilitates assembly
- Intermateable with competitor product
- Excellent RF performance to 6 GHz
- Ideal for Communications and Industrial Applications



Tyco Electronics' next generation high performance RF products QMA (Snap-On SMA) connectors series offers the same high quality and performance currently found in the standard Tyco Electronics SMA series but does not require the coupling nut torque. By integrating a snap-on feature to the design, denser packaging can be achieved, and the overall applied cost is dramatically reduced. The QMA connector series is excellent for communications as well as industrial applications. The QMA offering is designed for 100 mating cycles, operates through 6 GHz, and is completely intermateable with competitive QMA offerings. This new QMA product is not intermateable with standard SMA interfaces.

QMA connectors are available in a broad range of standard configurations, including PCB and panel mount, flexible and semirigid cable, and adapters. Other options can be reviewed as well, including additional cable sizes, PCB surface mounting, and tape and reel packaging.

The QMA connector series is a cost effective solution for the challenging demands of today's commercial marketplace, with applications including cellular base station, handsets, and test and measurement. Call your local sales office or authorized distributor for additional information or samples of the QMA connector series.

Tyco Electronics is a leading supplier of RF and Microwave connectors and cable assemblies, and provides advanced technology products from well known and industry leading brands, including AMP and M/A-COM. Material and Finish

 $\begin{array}{l} \textbf{Shells and Bodies} \\ \textbf{--} \\ \textbf{Brass, nickel} \\ \textbf{plated} \end{array}$

Collars — Phosphor bronze, white bronze plated

Outer Contacts — Beryllium copper, nickel plated Center Contacts — Beryllium copper,

gold plated Dielectrics — PTFE

Electrical Characteristics

Frequency — dc – 6 GHz Nominal Impedance — 50 ohms Voltage Rating — 335 Volts (VRMS max.) @ Sea Level

VSWR — 1.15 : 1 max. @ 6 GHz Insulation Resistance —

5,000 megohms min.

Insertion Loss — .25 dB Max @ 6 GHz Dielectric Withstanding Voltage —

1000 Volts (VRMS max.) @ Sea Level Contact Resistance —

Center Contact — 5 milliohms max. Outer Contact — 4 milliohms max.

Mechanical Characteristics

Connector Durability — 100 mating cycles

Force to Engage — 27 Newtons Force to Disengage — 20 Newtons

Retention Force (mated pair) — 60 Newtons min.

Cable Retention — Dependent upon cable type

Environmental Characteristics Temperature Rating —

-40 to +125°C Vibration — EIA-364-28,

Test Condition VII, Condition D Shock — EIA-364-27, Method H Moisture Resistance — EIA-364-31,


Method III

Thermal Shock — EIA-364-32

Note: Performance specifications are typical, but may not apply to all connector types.

Related Product Data

Product Specifiation — 108-2087 Sample Kit — 1654882



Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




RF Coax Connectors

QMA Connectors (Continued)

Semi-Rigid Cable — Direct Solder Attachment

Straight Cable Plug







Cable	Part Number
RG 402	1408346-1


Right-Angle Cable Plug












Bulkhead Cable Jack







Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Part Number

1408349-1

125


RF Coax Connectors

QMA Connectors (Continued)

Flexible Cable — Crimp Attachment

Straight Cable Plug






Cable	Dim. A	Part Number
RG 174, 188, 316	22.90 0.90	1408333-1
RD 316	22.90 0.90	1408333-3
RG 400	25.20 0.99	1408333-5
RG 58	25.20 0.99	1408333-7

Right-Angle Cable Plug




Cable	Dim. A	Dim. B	Part Number
RG 174, 188, 316	17.20 0.68	13.10 0.52	1408336-1
RD 316	17.20 0.68	13.10 0.52	1408336-3
RG 400	19.50 0.77	15.40 0.61	1408336-5
RG 58	19.50 0.77	15.40 0.61	1408336-7



Straight Cable Jack


200

·	Cable	Dim. A	Part Number
	RG 174, 188, 316	25.90 1.02	1408338-1
	RD 316	25.90 1.02	1408338-3
	RG 400	28.20 1.11	1408338-5
	RG 58	28.20 1.11	1408338-7



Bulkhead Cable Jack





Cable	Dim. A	Part Number
RG 174, 188, 316	9.90 0.39	1408339-1
RD 316	9.90 0.39	1408339-3
RG 400	12.20 0.48	1408339-5
RG 58	12.20 0.48	1408339-7

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

126

Catalog 1307191 Revised 3-07

and inches unless otherwise specified. Values in brackets are standard equivalents. www.tycoelectronics.com

Dimensions are in millimeters


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors


QMA Connectors (Continued)


Printed Circuit Board



Right-Angle Jack Receptacle

Part Number 1408337-1






Recommended Mounting Hole

Straight Terminal Press-In Jack






Body Material	Contact	RF Leakage	Temperature	Part
& Finish	Captivation	db min.	Range	No.
Brass, Gold	Mechanical	N/A	–65 to 125° C	619215-1

Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 **RF Coax Connectors**



to change.

www.tycoelectronics.com

Series 1.0/2.3 (50 Ohm/75 Ohm)



Miniature coaxial connectors series 1.0/2.3 (CECC 22230 and IEC 61169-29) coaxial connectors are devised to meet the requirements of compact electronic instrumentation. All plugs and jacks with $Z_{\Omega} = 50 \ \Omega$ are designed for a number of different 50 Ω and 75 Ω cables. Owing to the large demand, the Series 1.0/2.3 has also been optimized as a 75 Ω design into the GHz range. The different types of coupling mechanisms, such as screw on, slide-in and latching coupling permit space-saving installation.

In addition, an extensive range of measurement

accessories, adapters as well as terminations is available. The qualitydetermining factors have been established on the basis of corresponding measurements and test procedures in accordance with national and international standards for RF connectors (IEC 61169-1, MIL-C-39012 etc.).

High-quality materials ensure high reliability even in industrial atmospheres. The contact principle is the pin-socket principle and the contacts are gold plated to ensure perfect contact mating. The inner conductor parts are held in PTFE (Polytetrafluoroethylene). The reduced dimensions of all component parts of these connectors permit a compact hole spacing (installation pitch) of 6.8 [0.27] depending upon the corresponding cable diameters.

The cable is connected by crimping the cable braid to the plug or jack body, the inner conductor is soldered or crimped.

In most applications, the plug and jack belong to the same coupling type group. In special instances, such as for measurement purposes, different coupling types can be used together.

Between Series Adapters For Series 1.0/2.3 Adapters please see

pages 251-260.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

Coupling Types

Series 1.0/2.3 (50 Ohm/75 Ohm) (Continued)

Technical Data

₹ Tyco

Electrical and mechanical characteristics in accordance with CECC 22230

 $\begin{array}{l} \text{Characteristic impedance} \\ 50 \ \Omega/75 \ \Omega \end{array}$

Frequency range — up to 10 GHz/ 2 GHz

Reflection factor, referred to 50 Ω cable¹ — up to 1 GHz, r ≤ 0.05

up to 4 GHz, $r \le 0.07$ up to 10 GHz, $r \le 0.15$ **Reflection factor, referred to**

75 Ω cable¹ up to 2 GHz, r \leq 0.10

Insulation resistance initial value $\geq 1 \text{ G}\Omega$ after stressing $\geq 200 \text{ M}\Omega$

Screening effectiveness² — $\ge 90 \text{ dB}$

Inner conductor contact resistance

- after stressing $\leq 10 \text{ m}\Omega$ **Outer conductor continuity** - after stressing $\leq 7.5 \text{ m}\Omega$

Voltage proof³ flexible cables (RG 316) — at sea level, 750 V, 50 Hz — at 20 km altitude, 150 V, 50 Hz

Working voltage³ -


flexible cables (RG 316) — at sea level, 350 V, 50 Hz

— at 20 km altitude, 65 V, 50 Hz Service life — 500 cycles

Climatic category - 40/85/21

Notes:


- ¹ Guide values, depending on cable type and connector style.
- ² Values apply to a straight screw and latching coupling with suitable cable.
- ³ Some cables suitable for use with these connectors have lower characteristic values than specified here.
- ⁴ For applicable cable types see page 151.



Type A

Screw coupling; version with union nut


This type permits the plug and jack to be screwed together manually by means of a union nut secured to the plug. This is necessary for readily accessible locations, front panel test points and cable connections.



Type C

Slide-in coupling; version with centering ferrule

In this type of coupling, the plug features a guide ferrule with a conical entry surface. This ensures that the floatable bulkhead plugs with cable connection make a reliable electrical connection to the rigid installed jack. Examples of this are single and multi-contact connections of slide-in applications. "W" denotes the allowed spacing of the mounting panel for satisfactory contact when the connection is made.



Type F

Latching coupling (Quick Lock)

In this version, the cable plugs bear a funnel ferrule with built-in spring which snaps into a groove on the jack, simultaneously locking the connection. The connection can be easily separated by lightly pulling the outer sleeve of the plug. This type of coupling can be used with a higher packing density, as the screw coupling.

130


Catalog 1307191 Revised 3-07

www.tycoelectronics.com are


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Series 1.0/2.3, 50 Ohm


Plugs, Solder/Crimp




Cable	Coupling Type	Ø Max.	Part No.
RG 316	А	2.67 0.105	1393670-1




Cable	Coupling Type	Ø Max.	Part No.
WP93385L2	F	2.67 0.105	619223-1



Cable	Coupling Type	Ø Max.	Part No.
LMR 240	F	2.67 0.105	619224-1



Cable	Coupling Type	Ø Max.	Part No.
LMR 240FR	F	6.3 0.248	1460010-1




Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 **RF Coax Connectors**

₹ Tyco Electronics

Series 1.0/2.3, 50 Ohm (Continued)




Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

132

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




www.tycoelectronics.com


Revised 3-07


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 133


Series 1.0/2.3, 50 Ohm (Continued)

Right-Angle PC Board Mount Bulkhead Jack










Recommended Mounting Holes

Series 1.0/2.3, 75 Ohm

Plugs, Solder/Crimp



Cable	Coupling Type	Ø Max.	Part No.
RG 179	А	2.67 0.105	5-1393670-5

∼−−−− <u>26</u> [1.02]	Ø 7.9 [0.03]
	-

Cable	Coupling Type	Ø Max.	Part No.
RG 179	F	2.67 0.105	6-1393670-2
ST 212	F	3.2 0.13	6-1393670-5
02Y(St)CY 0.45/2.0	F	3.6 0.14	6-1393670-4


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


134

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Series 1.0/2.3, 75 Ohm (Continued)




Cable	Coupling Type	Ø Max.	Part No.
BELDEN 1855A	A, C, F	2.67 0.105	619226-1




Cable	Coupling Type	Ø Max.	Part No.
BT 3002	A, C, F	2.67 0.105	1460815-1


Right-Angle Plug, Solder/Crimp




Cable	Coupling Type	Ø Max.	Part No.
RG 179	F	2.67 0.105	2-1393670-6
02Y(St)CY 0.45/2.0	F	3.6 0.14	7-1393670-0



Cable	Coupling Type	Ø Max.	Part No.
RG 316	F	2.8 0.110	619228-1



Cable	Coupling Type	Ø Max.	Part No.
RA 7000	A, C, F	2.67 0.105	1460817-1



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


BELDEN is a trademark of Belden Wire and Cable Company.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Series 1.0/2.3, 75 Ohm (Continued)



Bulkhead Jack



6 [.354]

6.00

[.236]

Ø 9.00

are standard equivalents.

Dimensions are shown for and inches unless otherwise reference purposes only. Specifications subject specified. Values in brackets to change.

6.45 [.254]

[.919]

13.35

[.526]

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

ф

ф

Ø 1.00

M5.5 x 0.5

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

[.039] 5 Plcs.

ф

ሐ

Recommended

Mounting Holes

[.200]

5.08 [.200]

> South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Coupling Type

A, C, F

Part No.

619106-1

Catalog 1307191

Revised 3-07

136


www.tycoelectronics.com

RF Coax Connectors

₹ Тусо

Electronics

Series 1.0/2.3, 75 Ohm (Continued)



Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 137


Series 1.6/5.6 mS (75 0hm)



General

The Series 1.6/5.6 mS connectors have been modified to incorporate improved technical advantages. Transmission values have been greatly improved while maintaining the proven positive characteristics of the previous generations. All types of this new "third generation" Series 1.6/5.6 mS connectors are connection-compatible with their predecessor.

Today's PCM technology demands place the Series 1.6/5.6 mS connectors as a most suitable component for transmission of high bit rates. Connectors are available in straight and angled versions as well as with different mechanisms for screw (type A), snap-on (type B), slide-in (type C), and latching (type F) coupling. All connectors of different coupling mechanisms are compatible with each other.



The connectors are designed according to the pin-socket principle. The contacts are partially goldplated, ensuring long service life and stable contact resistance for a high number of intermateability cycles.

The inner conductor parts are secured so that they cannot be displaced. The insulating parts are made of PEEK (polyetheretherketone) or PC (polycarbonate). The cable inner conductors are soldered on, while the outer conductors are screwed or crimped on. Also, cable clamp which is independent of the braid clamping secures the connection point against tensile stressing for both methods of connection.

In addition, assemblyfriendly connectors with full crimp and IDC (Insulation Displacement Contact) connection are included within the scope of delivery. The connectors are characterized by high mechanical strength and low space requirement.

Connection possibilities exist for a number of different cables, including highly-flexible cable types (with foam insulation) with low attenuation or small diameter. Terminations and adapters (see also measurement accessories) round out the spectrum.

Between Series Adapters

₹ Тусо

Electronics

For Series 1.6/5.6 Adapters please see pages 253-262.

138

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Technical data

Coupling Types

Electrical and mechanical characteristics in accordance with CECC 22240 Characteristic impedance — 75 Ω Frequency range — up to 8 GHz

Reflection factor¹, referred to —

flexible cables, straight types up to 1 GHz, $r \le 0.02$ up to 4 GHz, $r \le 0.06$ up to 8 GHz, $r \le 0.10$ flexible cables, angled types up to 1 GHz, $r \le 0.04$ up to 2 GHz, $r \le 0.06$ up to 4 GHz, $r \le 0.10$ **Insulation resistance** —

initial value, $\geq 10 \text{ G}\Omega$ after stressing, $\geq 1 \text{ G}\Omega$

Screening effectiveness — (straight screw connector at 1 GHz) \geq 100 dB

Inner conductor contact

 $\begin{array}{l} \mbox{resistance} & - \mbox{after stressing} \leq 8 \ m\Omega \\ \mbox{Outer conductor continuity} & - \mbox{after stressing} \leq 4 \ m\Omega \\ \end{array}$

Voltage proof² flexible cables (RG 59) at sea level, 1.5 kV, 50 Hz at 20 km altitude, 300 V, 50 Hz

Working voltage² -


flexible cables (RG 59) at sea level, 500 V, 50 Hz at 20 km altitude, 125 V, 50 Hz


Service life — 500 cycles


Climactic category — 40/85/21


Notes:

- Guideline values, depending on cable type and connector style.
 Some cable types suitable for use
- Some cable types suitable for use with these connectors have lower characteristic values than specified here.
 For applicable cable types see
- ³ For applicable cable types see page 151.









Type F

Latching coupling (Quick Lock)

In this version, the cable plugs bear a funnel ferrule with built-in spring which snaps into a groove on the jack, simultaneously locking the connection. The connec-

Туре А

Screw coupling; version with union nut

This type permits the plug and jack to be screwed together manually by means of a union nut secured to the plug manually, thus preventing the coupling from being pulled apart. This is necessary for readily accessible locations, front panel test points and cable connections.

Туре В

Snap-on coupling (push-pull)

Connectors of this type offer fast make/break. They can be used for test and maintenance applications and also if there is lack of space and connectors with screw coupling cannot be used.

Type C

Slide-in coupling; version with centering ferrule

In this type of coupling, the plug features a guide ferrule with a conical entry surface. This ensures that the floatable bulkhead plugs with cable connection make a reliable electrical connection to the rigid installed jack. Examples of this are single and multi-contact connections of slide-in applications. "W" denotes the allowed spacing of the mounting panel for satisfactory contact when the connection is made.


tion can be easily separated by lightly pulling the outer sleeve of the plug. This type of coupling provides the same amount of axial tensile strength as the screw coupling, but can be used with a higher packing density.

Catalog 1307191 Revised 3-07


www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Plugs, Solder/Clamp




Cable	Coupling Type	Ø Max.	Part No.
2YCCY 0.7/4.4	А	7.8 0.31	1393682-1



Cable	Coupling Type	Ø Max.	Part No.
2YCCY 1.0/6.5 2YC(mS)CY 1.0/6.5	А	9.8 0.31	1393682-2




Cable	Coupling Type	Dim. a	Ø Max.	Part No.
2YCY 0.4/2.5	А	30.7 1.21	4.1 0.16	1-1393682-1
2YCCY 0.4/2.5	А	30.7 1.21	4.8 0.19	1-1393682-2
2YC(mS)CY 0.4/2.5	А	30.7 1.21	5.0 0.20	
2YCY 0.7/4.4	А	32.9 1.30	6.1 0.24	1-1393682-3
RG 59	А	32.9 1.30	6.25 0.25	
2YC(mS)CY 0.5/3.0	А	32.9 1.30	6.2 0.24	



Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	F	3.6 0.14	1393681-8

Plugs, Solder/Crimp



Cable	Coupling Type	Dim. a	Ø Max.	Part No.
RG 179	А	32.5 1.28	2.6 0.105	1393680-2
2YCCY 0.4/2.5	А	32.5 1.28	4.8 0.19	1393680-3
2YC(mS)CY 0.4/2.5	А	35.5 1.40	5.0 0.20	
2YC(mS)CY 0.5/3.0	А	35.5 1.40	6.2 0.24	1393680-4
2YCY 0.7/4.4	А	35.5 1.40	6.1 0.24	1393680-5
02Y(St)CY 0.45/2.0	А	32.5 1.28	3.6 0.14	1393680-9

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


1	4	0

(Continued)

Series 1.6/5.6 mS (75 0hm)








Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	F	3.6 0.14	1393672-3

Preassembled Isolation Parts


Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	F	3.6 0.14	1393672-9




Preassembled Version

Cable	Coupling Type	Ø Max.	Part No.
02YS(St)CHH 0.25/1.2	F	2.9 0.11	1460132-1


Right-Angle Plugs, Solder/Crimp



Cable	Coupling Type	Dim. a	Ø Max.	Part No.
2YCCY 0.4/2.5	А	13.0 0.51	4.8 0.19	2-1393682-0
2YC(mS)CY 0.4/2.5	А	13.0 0.51	5.0 0.20	
2YCY 0.7/4.4	А	15.8 0.62	6.1 0.24	
RG 59	А	15.8 0.62	6.25 0.25	2-1393682-2
2YC(mS)CY 0.5/3.0	А	15.8 0.62	6.2 0.24	



Cable	Coupling Type	Ø Max.	Part No.
RG 179	А	2.67 0.105	2-1393682-3



-	Cable	Coupling Type	Ø Max.	Part No.
	02Y(St)CY 0.45/2.0	F	3.6 0.14	1-1393681-0


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803






Cable	Coupling Type	Dim. a	Ø Max.	Part No.
02Y12YC(mS)C6Y 0.45/2.0	А	15.0 0.59	4.0 0.16	1-1393680-6
02Y(St)CY 0.45/2.0	А	15.0 0.59	3.6 0.14	1-1393680-8

Right-Angle Plugs, IDC Connection



Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	А	3.6 0.14	1393757-9
2YCY 0.4/2.5	А	4.1 0.16	1393757-8

Right-Angle Plug, Solder/Crimp



Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	F	3.6 0.14	1393672-5

Bulkhead Jacks, Solder/Clamp


	Cable	Coupling Type	Dim. a	Ø Max.	Part No.
2.0 Max.→ [0.08] Mounting Panel Max. [0.35]×[0.02]	2YCY 0.4/2.5	A, B, F	28.1 1.11	4.1 0.16	3-1393682-2
	2YCCY 0.4/2.5	A, B, F	28.1 1.11	4.8 0.19	3-1393682-3
	2YC(mS)CY 0.4/2.5	A, B, F	28.1 1.11	5.0 0.20	5-1595002-5
Ø8.2	2YCY 0.7/4.4	A, B, F	30.4 1.20	6.1 0.24	
[0.32]	RG 59	A, B, F	30.4 1.20	6.25 0.25	3-1393682-5
	2YC(mS)CY 0.5/3.0	A, B, F	30.4 1.20	6.2 0.24	

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

1	42
---	----



Cable	Coupling Type	Ø Max.	Part No.
2YCCY 1.0/6.5	A, B, F	9.8 0.38	1202602.4
2YC(mS)CY 1.0/6.5	A, B, F	9.8 0.38	1393682-4

Cable	Coupling Type	Ø Max.	Part No.
RG 179	B, C, F	2.67 0.105	4-1393682-2

19.4

[0.76]

12.0

[0.47]

Mounting

Panel

M9.0x0.5

[0.35]x[0.02]

Ø 10.8

[0.43]

082

[0.32]


¥

Part

No.

1-1393681-3


Bulkhead Jacks, Solder



Dim. a	Ø Max.	Part No.
22.3 * 0.88	A, B, C, F	1-1393681-1
23.5 0.93	A, B, C, F	1-1393681-9

*Without soldering tags on outer conductor, dimension a up to inner conductor end.





Cable	Coupling Type	Ø Max.	Part No.
RG 179	A, B, F	2.67 0.105	2-1393680-2
02Y12YC(mS)C6Y 0.45/2.0	A, B, F	4.0 0.16	2-1393680-4
06YCC(St)6Y 0.4/1.6	A, B, F	3.3 0.13	2-1393680-5
02Y(St)CY 0.45/2.0	A, B, F	3.6 0.14	1393672-6

With preassembled insulation parts

6.5

[0.26]

3.0

[0.12]

Max.

8.0 [0.31]

¥

Ø 0.6 [0.02]

Coupling

Туре

A, B, C, F

Cable	Coupling Type	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	A, B, F	3.6 0.14	1-1393672-4

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

[0.43]

Crimp Connection

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

[0.43]


Ø 8.2 [0.32]

> USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

143


Right-Angle Bulkhead Jack, Solder/Clamp



	Cable	Coupling Type	Ø Max.	Part No.
	2YCCY 1.0/6.5	A, B, F	9.8 0.39	1000000 0
-	2YC(mS)CY 1.0/6.5	A, B, F	9.8 0.39	1393682-8

Cable	Coupling Type	Dim. a	Ø Max.	Part No.
02Y(St)CY 0.45/2.0	A, B, F	13.0 0.51	3.6 0.14	4-1393682-9
2YCCY 0.4/2.5	A, B, F	13.0 0.51	4.8 0.19	4-1393682-6
2YC(mS)CY 0.4/2.5	A, B, F	13.0 0.51	5.0 0.20	
2YCY 0.7/4.4	A, B, F	15.8 0.62	6.1 0.24	4-1393682-8
RG 59	A, B, F	15.8 0.62	6.25 0.25	
2YC(mS)CY 0.5/3.0	A, B, F	15.8 0.62	6.2 0.24	

Right-Angle Bulkhead Jack, Solder/Crimp



Cable	Coupling Type	Dim. a	Ø Max.	Part No.
RG 179	A, B, F	15.0 0.59	2.67 0.105	3-1393680-0
2YCCY 0.4/2.5	A, B, F	15.0 0.59	4.8 0.19	3-1393680-2
2YC(mS)CY 0.4/2.5	A, B, F	15.0 0.59	5.0 0.20	
02Y12YC(mS)C6Y 0.45/2.0	A, B, F	15.0 0.59	4.0 0.16	3-1393680-5
06YCC(St)6Y 0.4/1.6	A, B, F	15.0 0.59	3.3 0.13	4-1393682-3
02Y(St)CY 0.45/2.0	A, B, F	15.0 0.59	3.6 0.14	3-1393680-7

27.2 [1.07] Max. Ŧ Ø 10.8 [.43] Ø 8.2 [.32] M9 x 0.5 [.35 x .02] 1.35 Min. [.053] 3.80 ----[.150]

Cable	Coupling Type	Dim. a	Ø Max.	Part No.
02YS(St)CHH 0.25/1.2	2 A, B, F	15.0 0.59	2.9 0.11	1460128-1*
02YS(St)CHH 0.25/1.2	2 A, B, F	15.0 0.59	2.9 0.11	1460169-1**

* Tray Packaging. ** Individual Packaging.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

144


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

₹ Tyco Electronics





Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208




RF Coax Connectors

Series 1.6/5.6 mS (75 Ohm) (Continued)

Right-Angle PC Board Mount Bulkhead Jack






Recommended Mounting Holes


Coupling Type	Dim. a	Dim. b	Dim. c	Dim. d	Dim. e	Part No.
A, B, F	4.0 0.16	16.0 0.63	6.0 0.24	10.75 0.42	1.3 0.05	2-1393681-1
A, B, F	3.3 0.13	16.0 0.63	6.0 0.24	10.75 0.42	1.3 0.05	2-1393681-2
A, B, F	3.7 0.15	22.9 0.90	6.45 0.25	11.25 0.44	1.8 0.07	2-1393681-3*

*With positioning and snap-on system onto PC board

U-link Plug/Plug



Coupling Type	Dim. a ± 0.1 [0.004]	Dim. b Max.	Part No.
А	15.0 0.59	26.5 1.04	6-1460823-1



Coupling Type	Dim. a ± 0.1 [0.004]	Dim. b Max.	Part No.
В	15.0 0.59	26.5 1.04	6-1460823-2

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



Series 1.6/5.6 mS (75 Ohm) (Continued)

Accessories


These components are provided when bulkhead jack part numbers are ordered, but can also be ordered separately.



Threaded ring for installation of bulkhead jacks

_

Part No.	
1-1393562-0	




Soldering aid (sleeve) for jack (1-1393681-9) with solder termination

Part No.	
2-1393562-2	
triania a sur din stallation	

Cable stripping and installation example: see Part number 2-1393562-2 under "Series 1.0/2.3", page 137.

Measurement Accessories

Between Series Adapters (75 Ohm)



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000


Hong Kong: 852-2735-1628 Japan: 81-44-844-8013

UK: 44-8706-080-208

Measurement Accessories (Continued)

Between Series Adapters

(75 Ohm) (Continued)




1) Detent for jack

Coupling	Part		
Type	No.		
A, B ² , F ²	6-1460821-3		

² Only jack side

A, B, F




Jack 1.0/2.3 to) Jack 1.6/5.6
Coupling	Part
Type	No.

6-1460821-4

Î	ET L PAT	1
Ø 14.5 [0.57]		Ø 10.8 [0.43]
[0.57]		[0.43]
		<u> </u>
-	46.4 [1.83]	>
	[1.83]	

BNC Plug to Plug 1.6/5.6
Part No.
7-1393665-4



BNC	Plug	to	Jack	1.6	/5.6
-----	------	----	------	-----	------

Part No.
7-1393665-6

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

148


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Measurement Accessories (Continued)

Between Series Adapters


(75 Ohm) (Continued)








Termination (75 Ohm)



1) Detent for jack



Standard Termination

Plug 1.0/2.3

Coupling	Power	Part
Type	W	No.
А	0.6	7-1393665-2

J	ack 1.0/2.3		
	Coupling Type	Power W	Part No.
	A, F	0.6	7-1393665-3

29.6 [1.17] ►	
	Ø 10.8 [0.43]

Plug	1.6/5.6
------	---------

Coupling Type	Power W	Part No.
А	1.0	6-1393665-1


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Measurement Accessories (Continued)

In-Series Adapter (75 Ohm)




Adapter 1.6/5.	6, Plug/Plug
Coupling Type	Part No.
А	1393681-6



Adapter	1	.6/5.6,	Plug/Jack
---------	---	---------	-----------

Coupling	Part	
Type	No.	
A, B*, F*	1-1393681-7	

*Jack side only



Adapter	1.6	/5.6.	Jack	/Jack
---------	-----	-------	------	-------

Coupling	Part	
Type	No.	
A, B, F	1-1393665-1	

Note: U-link connectors see "1.6/5.6" section, page 146.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

150

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets ics.com are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Coaxial Cables

List of the coaxial cables that are listed in the various connector series of this section.

Characteristic Max. Cable		Dielectric Diemeter (mm)/	Cable-Type Designation			
Impedance (Ω)	Outer Diameter (mm)	Dielectric Diameter (mm)/ Material ¹⁾	VDE Designation ²⁾	US Designation Manufacturer des.	IEC Designation 96-IEC	
50	1.9	0.91max/PTFE	5YC5Ye 0.3/0.86	RG 178	50-1-1	
50	2.1	0.87/PTFE	_	RG 196	50-1-2	
50	2.25	1.71max/PTFE	5YK 0.51/1.68	RG 405	_	
50	2.6	1.60max/PTFE	5YC5Ye 0.5/1.5	RG 316	50-2-1	
50	2.8	1.60max/PE	2YCY 0.5/1.5	RG 174	—	
50	3.0	1.52/PTFE	5YCC5Y 0.5/1.5	RD 316	_	
50	3.6	3.01max/PTFE	5YK 0.9/3.0	RG 402	—	
50	6.4	5.38max/PTFE	5YK 1.63/5.33	RG 401	_	
75	2.67	1.68max/PTFE	5YC6Y 0.3/1.6	RG 179	75-2-1	
75	3.0	1.60max/PTFE	_	RD 179	_	
75	3.3	1.68max/Cell-FEP	06YCC(St)6Y 0.4/1.6	_	_	
75	3.2	2.1max	_	ST 212	_	
75	3.6	2.0max/Cell-PE	02Y(St)CY 0.45/2.0	—	—	
75	4.0	2.0maxE/Cell-PE	02Y12YC(mS)C6Y 0.45/2.0	_	_	
75	4.0	2.54max/PE	2YCY 0.4/2.5	_	_	
75	4.8	2.54max/PE	2YCCY 0.4/2.5	—	_	
75	5.0	2.54max/PE	2YC(mS)CY 0.4/2.5	_	_	
75	6.1	4.25max/PE	2YCY 0.7/4.4	_	_	
75	6.2	2.83max/PE	2YC(mS)CY 0.5/3.0	_	_	
75	6.25	3.8max/PE	2YCY 0.58/3.7	RG 59	_	
75	7.8	4.43max/PE	2YCCY 0.7/4.4	_	_	
75	9.8	6.4/PE	2YCCY 1.0/6.5	_	_	
75	9.8	6.4/PE	2YC(mS)CY 1.0/6.5	_	_	

1) Material label

PTFE Polytetrafluorethylene

ΡE Polyethylene

FEP Perfluorethylene propylene

PFA Perfluoralkoxy copolymer Mounting label of the VDE type numbers (from inside to outside) 2) Example:

Explanation

Dielectric and Jacket 2Y = PE 5Y = PTFE 02Y = Cell PE 06Y = Cell FEP 6Y = FEP	Screen: C = Cu braiding K = Cu tape Intermediate layer: mS = magnetic so St = static screen		٦	condu vs =	silver p u = Bare stee	plated	er-clad	gn = gr = rt =	t color: = green = grey red = white	
		6Y	С	(mS)	С	Y	0.7/4.0	-75	(r2/100)	vs gr
Dielectric										
1st screen										
Intermediate layer										
2nd screen ———										
Outer jacket										
Diameter inner conductor/	dielectric-									
Characteristic impedance										
Max. reflection (r) in % / fr	equency in MHz									
Specifications on inner co	nductor and/or jacket col	lor —								

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SMP Microminiature Push-On Coaxial Connectors


Product Facts

₹тусо

 Intermateable with Corning Gilbert GPO Series Connector

Electronics


- DESC approved
- Enhanced performance features
- Simplified Assembly




SMP microminiature push-on coaxial connectors provide solutions for today's modular designs with denser packaging requirements. The extremely small size of the SMP offers a versatile solution for high density packaging allowing connector center-to-center spacing of 4.32 [0.17]. The push-on interface facilitates easier assembly and test with a positive snap-in feature to indicate a fully mated connection. The rugged SMP interface can withstand harsh environments of mechanical shock and vibration, typically found in military or aerospace related applications. This SMP connector interface is the standard used by Defense Electronics Supply Center (DESC) to generate the SMP push-on connector series.

SMP connectors can be your design solution for mechanical packaging and frequency response. The SMP interface provides 0.020" of radial misalignment for critical blindmate applications. Mating forces are strictly controlled to ensure reliable connections per mated pair or when simultaneously mating multiple connectors. Cable jacks include an anti-rocking ring to ensure reliable mechanical performance regardless of the operating environment. SMP connectors offer enhanced broadband VSWR performance of 1.15:1 max thru 26GHz and 1.40:1 max thru 40GHz.

Standard design SMP configurations include cable connectors, straight and right-angle, for 0.047 and 0.085 semi-rigid cable, full detent, limited detent and smooth bore mating shrouds that can be bulkhead or flange mounted and glass feedthroughs for coax to circuit launchers. In-series adapters for module to module intermating and between series adapters for integrating or testing systems or components parameters.



SMP Shroud and Jack to Jack Adapter Assembly



GPO is a trademark of Corning Gilbert, Inc.

Catalog 1307191 Revised 3-07

152

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

see pages 253-262.

Between Series Adapters

For SMP Between Series Adapters,




Specifications

General	
Materials and Finishes	
Housings and Center Contacts	Beryllium Copper per ASTM-B-196; gold plate over nickel plate
Dielectric	PTFE Fluorocarbon per ASTM-D-1457
Shrouds	Stainless steel per ASTM-A582 Type 303; passivate per ASTM-A380
Hermetic Seal	Glass bead
Electrical	
Frequency Range	dc - 40.0 GHz
VSWR	1.10:1 Maximum dc - 23.0 GHz
	1.15:1 Maximum 23.0 - 26.0 GHz
	1.40:1 Maximum 26.0 - 40.0 GHz
Voltage Rating	335 Vrms maximum at sea level
Insertion Loss	0.10 f√(GHz) maximum
Insulation Resistance	5000 megohms minimum
Dielectric Withstanding Voltage	500 volts (VRMS minimum)
RF High Potential	325 volts (VRMS minimum) @ 5 MHz
Impedance	50 ohms nominal
RF Leakage	-80dB to 3 GHz, -65dB from 3 to 26.5 dB minimum
Contact Resistance	Initial center contact 6.0 milliohms maximum
	Outer contact 2.0 milliohms maximum
Mechanical	
Durability	100 mating cycles minimum
Radial Misalignment	±0.020 minimum
Axial Misalignment	.000/.010
Force to Engage	full detent 15.0 lbs. maximum
	half detent 10.0 lbs. maximum
	smooth bore 2.0 lbs. maximum
Force to Disengage	full detent 5.0 lbs. minimum
	half detent 2.0 lbs. minimum
	smooth bore 0.5 lbs. minimum
Center Contact Retention	1.5 lbs. minimum axial force
Environmental	
Operating Temperature	-65°C to +165°C
Vibration	per mil-std-202, method 204, test condition D
Shock	per mil-std-202, method 213, test condition I
Thermal Shock	per mil-std-202, method 107, test condition B
Moisture Resistance	per MIL-STD-202 method 106, except step 7b shall be omitted. Resistance shall be 200 megohms within 5 minutes after removal from humidity.

Interface Dimensions

Jack Shroud 3.40 Full Detent -[.132]-Min EMI Ring **8.60** ± .076 [.142 ± .003] Dia. 3.70 Dia. 3.43 Dia. [.145] Max. [.135] Max. ¥ ¥ ¥ Anti-Rock Ring 2.8 Bullet <[.112]> Min.



Note: The U.S. Government (DESC) has determined that the above specified interface dimensions are interchangeable and intermateble with Corning Gilbert GPO Series RF Connectors.¹

GPO is a trademark of Corning Gilbert, Inc.

¹ Per DESC drawing numbers 94007 and 94008, series SMP.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


2.80 ± .050

[.110 ± .002]

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


Straight Cable Jack, Solder Attachment

Tyco Electronics




Cable	Part No.
.047 Semi-Rigid	1056526-1
.085 Semi-Rigid (RG 405)	1056527-1


Right-Angle Cable Jack, Solder Attachment



Cable	Dim. A	Dim. B	Part No.
.047 Semi-Rigid	4.8 .190	5.8 .230	1056553-1
.085 Semi-Rigid (RG 405)	5.3 .209	6.7 .265	1056554-1

Jack to Jack Adapter (Bullet)





154

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Shroud — Threaded

₹ Tyco Electronics



Part No.
1056745-1
1056743-1
1056744-1

Shroud — 2 Hole Flange Surface Mount



Description	Dim. A	Dim. B	Dim. C	Dim. D	Part No.
	12.2 .480	8.3 .328	4.7 .187	2.5 .098	1056721-1
Full Detent	15.8 .625	12.2 .481	5.7 .223	2.6 .102	1056722-1
	10.2 .400	7.2 .282	4.2 .165	1.9 .073	1056724-1
	12.2 .480	8.3 .328	4.7 .187	2.5 .098	1056729-1
Limited Detent	10.2 .400	7.2 .282	4.2 .165	1.9 .073	1056731-1

Shroud — Press Fit



Description	Dim. A	Dim. B	Part No.
Limited Detent	3.9 .154	2.0 .080	1056736-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


www.tycoelectronics.com

Shroud — Solder-In Hermetic


Glass Bead Assembly





Description	Part No.
Full Detent	1056750-1
Limited Detent	1056751-1
Smooth Bore	1056752-1



Part No.	
1056728-1	







Catalog 1307191 Revised 3-07 www.tycoelectronics.com

156

Detent

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

OSP Miniature Modular Blind Mate Connectors

Product Facts

₹тусо

 Interface designed for multiple interconnects

Electronics

- For high performance microwave system requirements
- Module to module, module to motherboard, fixed and float mount
- Bulkhead or panel mount
- For flexible and semi-rigid cable



OSP miniature connectors for semi-rigid cable meet high performance requirements for microwave multiple interconnects. Standard units are available in bulkhead or panel mount designs for either direct solder or solderless compression crimp attachment. Complete tooling for both versions is located in the Tooling Section of this catalog. Jack connectors are available in either float or rigid mount. Rigid mount units will function to specifications up to \pm .10 [.004] radial misalignment with the mating plug connector. Applications requiring greater than \pm .10 [.004] radial misalignment can use either the float design or floating connector plates with guide pins.

The solderless compression crimp attachment meets

high performance requirements for microwave system applications. The cable attachment is permanent and highly reliable.

Ease of assembly permits users unskilled in soldering techniques to rapidly produce cable assemblies with consistently excellent mechanical and electrical performance.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

The specifications given refer specifically to mated pair of Part Numbers 1059410-1 and 1059402-1 (RG 402) and 1059412-1 and 1059404-1 (RG 405). Specifications on other connectors are available on request.

Electronics

₹ Tyco

The general electrical, mechanical and environmental specifications in the following table are recommended for procurement documents or drawings.

OSP Miniature Modular Blind Mate Connectors (Continued)

Engineering Data Impedance -50 ohms Frequency dc to 22.0 GHz Temperature Rating --65° to 125° C Electrical VSWR dc - 18.0 GHz 1.02 + .005f (GHz) 1.02 + .008f (GHz) 18.0 - 22.0 GHz RF Transmission Loss -.03 x √f (GHz) Insulation Resistance — Contact Resistance -Center Contact 2.0 milliohms max. Outer Contact 2.0 milliohms max. Outer Contact to Cable 0.5 milliohms max. Dielectric Withstanding Voltage — 1500 volts RMS Corona Extinction Voltage at 70,000 Ft.---375 volts min. RF High Potential at 5 MHz ----1,000 volts RMS RF Leakage Interface Only -----(90-fGHz) dB min. (fully mated) Power Handling -**Environmental** Corrosion -Vibration — Shock -Temperature Cycling — Moisture Resistance — Material Housing Center Contact ----Dielectric — Gasket (O'Ring) -MIL-P-25732 Mechanical Force to Engage ----3 pounds max. Force to Disengage -1.5 pounds max. Center Contact Retention ----6 pounds min. Durablilty ----5,000 Cycles Radial Misalignment ----**Rigid Mount** ±.10 [±. 004] Float Mount ±.51 [±.020] **Mating Characteristics** Jack Connector -Center Contact Socket Test Pin Finish — Insertion Depth ----Test Pin — Insertion Force Test Pin Finish — Insertion Depth ----Insertion Force ----Withdrawal Force Test Pin -Test Pin Finish — Insertion Depth ----Withdrawal Finish

RG 402 (.141) Semi-Rigid

5,000 megohms min.

1.05 + .009f (GHz) .03 x √f (GHz) 5,000 megohms min. 2.0 milliohms max. 2.0 milliohms max. 0.5 milliohms max. 1000 volts RMS 335 volts min. 670 volts RMS -(90-fGHz) dB min. (fully mated) 300W at 3 GHz (sea level) and room temperature

RG 405 (.085) Semi-Rigid

1.05 + .005f (GHz)

Method 101, Condition B, MIL-STD-202 Method 204, Condition D, 20G's, MIL-STD-202 Method 213, Condition I, 100G's, MIL-STD-202 Method 107. Condition B. MIL-STD-202 Method 106, MIL-STD-202

Corrosion resistant steel Type 303 (stainless) per ASTM A484 and A582 Beryllium copper per ASTM-B-196 TFE fluorocarbon per ASTM-D-1457

Oversize test Pin -Number of Insertions -

.945 + .003 [.0372 + .0001] dia. 16 micro inch .76/1.14 [.030/.045] 3 .940 + .003 [.0370 + .0001] dia. 16 micro inch 1.27/1.91 [.050/.075] 3 pounds max. .90 + .003 [.0355 - .0001] dia. 16 micro inch 1.27/1.91 [.050/.075] 1 ounce min.

Gold plate per MIL-G-45204, Type II, Class 1 over copper plate per MIL-C-14550 Gold plate per MIL-G-45204, Typ II, Class 0 over nickel plate per QQ-N-290, Class 2 or passivate per ASTM-A380

All dimensions shown are nominal. Contact the factory for specific tolerances.

158

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Center Contact ----

Housing —

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


OSP Miniature Modular Blind Mate Connectors (Continued) Interface Mating Dimensions


The connector interface, specifically designed for multiple interconnects, maintains reliable performance over the typical mechanical tolerance required in cost effective packaging.

₹ Tyco Electronics

The interface test data shows excellent performance is maintained with mating gaps up to 0.38 [.015].

Meets MIL-STD-348 Figure 321. Intermateable to BMA Connectors.






Jack

Letter	Dimensions		
А	1.78 .070 Nom.		
В	5.72 .225 Min.		
С	7.62 .300 Ref.		
D	5.00 .197 Nom.*		
E	5.08 .200 Max.		
F	3.23 .127 Max.*		

Letter	Dimen	sions
А	1.78 .070	Nom.
В	5.33 .210	Nom.
С	7.62 .300	Ref.
D	5.05 .199	Min.
E	0.91 .036	Nom.
F	3.25 .128	Min.

Plug

*With spring bottomed



Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

OSP Miniature Modular Blind Mate Connectors (Continued) For Semi-Rigid Cable, Direct Solder Attachment

Bulkhead Feedthrough Cable Plug Rear Mount






Cable	Disting	Dimensions	Dimensions	
Cable	ole Plating		В	Part No.
RG 402/U 3.58 .141	Gold	3.7 .144	4.6 .180	1059402-1
RG 405/U 2.16 .085	Gold	2.3 .089	3.0 .120	1059404-1

Bulkhead Feedthrough Cable Jack Rigid Rear Mount






Cable	Dimensions		Part No.	
Cable	Plating	Α	В	Part No.
RG 402/U 3.58 .141	Gold	3.7 .144	4.6 .180	1059410-1
RG 405/U 2.16 .085	Gold	2.3 .089	3.0 .120	1059412-1

Flange Mount Cable Jack Floating Rear Mount





Finish: Inner housing that is soldered to cable is gold plated. Outer housing is passivated stainless steel.

When using semi-rigid cable, it is recommended that a service loop be used to facilitate the float features of the connector.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

160

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


OSP Miniature Modular Blind Mate Connectors (Continued) For Semi-Rigid Cable, Direct Solder Attachment (Continued)

Low Profile — Bulkhead Feedthrough Cable Jack — **Floating Rear Mount**

Electronics



₹тусо




Cable	Plating	Dimer	isions	Part No.
Cable	Flating	Α	В	Fait NO.
RG 402/U 3.58 .141	Gold	3.7 .144	4.6 .180	1059505-1
RG 405/U 2.16 .085	Gold	2.3 .089	3.0 .120	1059506-1

When using semi-rigid cable, it is recommended that a service loop be used to facilitate the float features of the connector.

Low Profile — Panel Feedthrough Cable Jack — **Floating Rear Mount**






Cable Plating		Dimer	nsions	Part No.
Cable	Plating	Α	В	Part No.
RG 402/U 3.58 .141	Gold	3.7 .144	4.6 .180	1059465-1
RG 405/U 2.16 .085	Gold	2.3 .089	3.0 .120	1059467-1

Recommended removal tool part number 1059774-1 is described in the Tooling Section of this catalog.

When using semi-rigid cable, it is recommended that a service loop be used to facilitate the float features of the connector.

Panel A ±.003

2.3 .090



2.3 .090 .438 .222 2.3 12.7 4.1 .090 .500 160 **3.2** .125 9.5 .375 **6.4** .250 3.2 11.1 4.7 .125 .438 .187 **3.2** .125 12.7 **3.2** .125 .500

Panel B ±.003

9.5 .375

11.1

Recommended Mounting Detail

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Stand-Off Panel C +.050/-.000


7.2 .285

5.6

OSP Miniature Modular Blind Mate Connectors (Continued) For Semi-Rigid Cable, Solderless Compression Crimp Attachment

Bulkhead Feedthrough Cable Plug **Fixed Rear Mount**





Outline drawing shows after crimp dimensions.

Steel

.085

Bulkhead Feedthrough Cable Jack Fixed Rear Mount





↑ 11.1 [.437 ↓		A 6.4 Dia. [.250] Dia.	12.7 [.500] Max. [.3	9.1 + 0.03 000 559 + .0001 000 Recommen Mounting H	
			Dii	n. B	
Cable	Plating	Dim. A	Before Crimping	After Crimping	Part No.
RG 402/U 3.58 .141	Passivated Stainless Steel	3.6 .143	21.1 .830	18.2 .715	1059408-1

Outline drawing shows after crimp dimensions.

Flange Mount Cable Jack Floating Rear Mount







Recommended Mounting Hole

			Din	n. B	
Cable	Plating	Dim. A	Before Crimping	After Crimping	Part No.
RG 402/U 3.58 .141	Passivated Stainless Steel	3.6 .143	22.6 .891	19.8 .780	1059451-
RG 405/U 2.16 .085	Passivated Stainless Steel	2.2 .088	22.6 .891	19.8 .780	1059452-1

Outline drawing shows after crimp dimensions.

When using semi-rigid cable, it is recommended that a service loop be used to facilitate the float features of the connector.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

OSP Miniature Modular Blind Mate Connectors (Continued) For Flexible Cable, Crimp Attachment

Bulkhead Feedthrough Cable Plug Rear Mount



Bulkhead Feedthrough Cable Jack Rigid Rear Mount



Flange Mount Cable Jack Floating Rear Mount



Low Profile — Panel Feedthrough Cable Jack — Rear Mount





Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07

www.tycoelectronics.com are


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.







, -,		
RG 174/U, 179, 187, 188, 316	Passivated Stainless Steel	1059541-1
RG 178, Double Braid	Passivated Stainless Steel	1058572-1
7.6		



Cable	Plating	Part No.
RG 174/U, 179, 187, 188, 316	Passivated Stainless Steel	1059551-1

Refer to Recommended Mounting Hole Detail for Semi-Rigid Cable Low Profile Feedthrough Cable Jack.


Recommended removal tool part number 1059774-1 as described in the Tooling Section of this catalog.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

OSP Miniature Modular Blind Mate Connectors (Continued) Panel Mount

Straight Terminal 2-Hole Flange Mount Plug Receptacle








Plating	Part No.
Passivated Stainless Steel	1059566-1

2-Hole Flange Mount Jack Receptacle







Plating	Part No.
Passivated Stainless Steel	1059596-1

4-Hole Flange Mount Plug Receptacle








Plating	Part No.
Passivated Stainless Steel	1059563-1

4-Hole Flange Mount Jack Receptacle





Plating	Part No.
Passivated Stainless Steel	1059594-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

164

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



5.5 [.020] Dia.

OSP Miniature Modular Blind Mate Connectors (Continued) **Panel Mount** (Continued)

5.5 ± 0.03 [.218 ± .001] Dia.

5.3 ± 0.05

[.210 ± .002]

Straight Terminal Threaded Installation — Panel Feedthrough Plug Receptacle



Threaded Installation — Panel Feedthrough Jack Receptacle




0.5 Dia. 1.6 Dia. 5.5 ± 0.03 Dia. [.020] ... [.064] [.218 ± .001] Dia. 10.4 5.3 Dia. 5.3 ± 0.05 [.210 ± .002] [.210 ± .002]

1.6] [.064] Dia.

10.4 5.3

[.410] [.210]

Dia.



1.7 ± 0.03 [.066 ± .001] Dia.

6.4

[.250]

1.7 ± 0.03 [.066 ± .001] Dia.

Recommended Mounting Hole Panel

Recommended Mounting Hole

Plating	Part No.
Passivated Stainless Steel	1059657-1


Plating


Passivated Stainless Steel Part No.

1059617-1

Press Fit Installation — Panel Feedthrough Plug Receptacle








Recommended Mounting Hole

Plating	Part No.
Passivated Stainless Steel	1059651-1

Press Fit Installation — Panel Feedthrough Jack Receptacle





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07


www.tycoelectronics.com are s

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Tyco Electronics

RF Coax Connectors

OSP Miniature Modular Blind Mate Connectors (Continued) Printed Circuit Board Mount



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

166

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


OSP Miniature Modular Blind Mate Connectors (Continued) Hermetically Sealed

Metal-To-Metal Rigid Gasket Seal — Panel Feedthrough Plug Receptacle

Electronics

₹тусо






-	SWR GHz)	RF Leakage (dB)	Plating	Part No.
1.04	+ .009f	–(90-fGHz)	Passivated stainless steel	6059632-1

Installation Thermal Limit: 250°C.

Recommended Mounting Hole Detail A follows, pg 168.

Rigid Gasket Seal — Panel Feedthrough Jack Receptacle





VSWR (GHz)	RF Leakage (dB)	Plating	Part No.
1.04 + .009f	–(90-fGHz)	Passivated stainless steel	6059665-1

Installation Thermal Limit: 250°C.

Recommended Mounting Hole Detail A follows, pg 168.

Field Replaceable Solder and Braze-In Panel Feedthrough Plug Receptacle



VSWR (GHz)	RF Leakage (dB)	Plating	Part No.
1.06 + .01f	–(90-fGHz)	Passivated stainless steel	1059637-1

Recommended Mounting Detail B or E follows, pg 168.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

OSP Miniature Modular Blind Mate Connectors (Continued) Hermetically Sealed (Continued)

Field Replaceable Solder and Braze-In (Continued)

Panel Feedthrough Jack Receptacle





VSWR (GHz)	RF Leakage (dB)	Plating	Part No.
1.06 + .01f	–(90-fGHz)	Passivated stainless steel	1059671-1

Recommended Mounting Detail B or E follows at bottom of this page.

2-Hole Flange Mount Plug Receptacle With EMI/RFI Gasket — 0.5 [.018] Dia. Contact




6.4 [.250] Dia. 9.5 [.375]	2.8+0.0 -0.0 [.112+.00 8.0±0.13 [.315±.005		a. 15.9 [.625] 12.2 [.481] 6.6 [.260]
	eakage IB)	Plating	Part No.


1.06 + .01f -(90-fGHz) Passivated stainless steel 1059572-1

Recommended Mounting Detail D follows at bottom of this page.

Recommended Mounting Hole Detail







5.5 ± 0.03 [.218 ± .001] Dia. 6.4 ± 0.08 [.250 ± .003] Ref. Panel

 $\textbf{3.2} \pm \textbf{0.13}$

[.125 ± .005]

Panel

2 9 ± 0.03


[.115 ± .001]

Dia.

Detail B* (6.35 [.250] Panel Thickness)

Detail D*





*Consult appropriate Instruction Sheet for complete mounting details.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 E Revised 3-07 a www.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

12.2

[.481]

Ref.

ł

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

OSSP Subminiature Modular Blind Mate Connectors

Product Facts

₹ Тусо

 Subminiature version of OSP Blind Mate Connectors

Electronics

- For space savings
- Family of connectors and adapters



OSSP connectors are a subminiature version of the OSP blind mate series. Connectors in this series incorporate the design elements of the OSP interface including the float and mismate features. OSSP blind mates are about 40% smaller than OSP connectors and are designed to be

Engineering Data

Impedance — Frequency — Temperature Rating —

Electrical

VSWR — RF Transmission Loss — Insulation Resistance — Contact Resistance — Center Contact Outer Contact to Cable Dielectric Withstanding Voltage — Corona Extinction Voltage at 70,000 Ft.— RF High Potential at 5 MHz — RF Leakage Interface Only — Power Handling —

Environmental

Corrosion — Vibration — Shock — Temperature Cycling — Moisture Resistance —

Material

Housing —

Center Contact — Dielectric — Gasket (O'Ring) —

50 ohms dc to 28.0 GHz -65° to 125° C

RG 405 (.085) Semi-Rigid

1.05 + .01f (GHz) .040 x \sqrt{f} (GHz) 5,000 megohms min.

6.0 milliohms max.
3.0 milliohms max.
0.5 milliohms max.
675 volts RMS
250 volts min.
675 volts RMS
-(90-fGHz) dB min. (fully mated)
300W at 3 GHz (sea level) and room temperature

Method 101, Condition B, MIL-STD-202 Method 204, Condition D, 20G's, MIL-STD-202 Method 213, Condition I, 100G's, MIL-STD-202 Method 107, Condition B, MIL-STD-202 Method 106, MIL-STD-202

Corrosion resistant steel Type 303 (stainless) per ASTM A484 and A582 Beryllium copper per ASTM-B-196 TFE fluorocarbon per ASTM-D-1457 MIL-P-25732 used in applications where space is at a premium.

A complete family of OSSP connectors and adapters is available including cable connectors, fixed and float mount panel connectors and hermetic connectors. Rigid mount units will function to specifications up to

Mechanical

Force to Engage — Force to Disengage — Center Contact Retention — Durability — Radial Misalignment — Rigid Mount Float Mount 3 pounds max. 1.5 pounds max. 4 pounds min. 1,000 Cycles

±.064 [±.0025] radial mis-

alignment with the mating

greater than ±.064 [±.0025]

radial misalignment can use

either the float design or

floating connector plates

Applications requiring

plug connector.

with guide pins.

±.06 [±.0025] ±.51 [±.020]

Mating Characteristics

Jack Connector —		
Center Contact Socket	Oversize test Pin — Test Pin Finish —	.533 + .003 [.0210 + .0001] dia. 16 micro inch max.
	Insertion Depth — Number of Insertions —	.76/1.14 [.030/.045]
Insertion Force	Test Pin — Test Pin Finish — Insertion Force —	.528 + .003 [.0208 + .0001] dia. 16 micro inch 3 pounds max.
Withdrawal Force	Test Pin — Test Pin Finish — Insertion Depth — Withdrawal —	.495 + .003 [.01950001] dia. 16 micro inch max. 1.27/1.91 [.050/.075] 1/2 ounce min.

Finish

Center Contact — Housing — Gold plate per MIL-G-45204, Type II, Class 0 over nickel plate per QQ-N-290, Class 2 or passivate per ASTM-A380 Gold plate per MIL-G-45204, Type II, Class 0 over nickel plate per QQ-N-290, Class 2 or passivate per ASTM-A380

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


₹ Tyco Electronics


OSSP Subminiature Modular Blind Mate Connectors (Continued)

Interface Mating Dimensions

The connector interface, specifically designed for multiple interconnects, maintains reliable performance over the typical mechanical tolerance required in cost effective packaging.

The interface test data shows excellent performance is maintained with mating gaps up to .015 inch.






Jack

Plug

Description	Dimensions					
Description	Α	В	С	D	E	F
Jack	1.22	3.91	5.33 Ref.	5.00	3.35	3.23
	0.48 Nom.	.154 Min.	.210	.197 Nom.*	.132 Max.	.127 Max.*
Plug	1.22	3.56	5.33	5.00	0.51	3.25
	0.48 Nom.	.140 Nom.	.210 Ref.	.199 Min.	.020 Nom.	.128 Min.

*With spring bottomed.



Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

OSSP Subminiature Modular Blind Mate Connectors (Continued) For Semi-Rigid Cable, Direct Solder Attachment


Bulkhead Feedthrough Cable Plug — Rear Mount





Flange Mount Cable Jack — Floating Rear Mount






Finish: Inner housing that is soldered to cable is gold plated. Outer housing is passivated stainless steel.

When using semi-rigid cable, it is recommended that a service loop be used to facilitate the float features of the connector.

Feedthrough Snap-In





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

OSSP Subminiature Modular Blind Mate Connectors (Continued) For Flexible Cable, Crimp Attachment

Bulkhead Feedthrough Cable Plug — Rear Mount






Braided Only	Passivated Stainless Steel	1059884-1
RG 174/U, 188/U, 316U	Passivated Stainless Steel	1059886-1

Flange Mount Cable Jack — Floating Rear Mount






Cable	Plating	Part No.
RG 188/U, 316 Double Braided Only	Passivated Stainless Steel	1059888-1
RG 174/U, 188/U, 316U	Passivated Stainless Steel	1059887-1

Feedthrough Snap-In Cable Jack





Part No.
1059889-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


172

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Tyco Electronics

RF Coax Connectors

OSSP Subminiature Modular Blind Mate Connectors (Continued) For Panel Mount



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Tyco Electronics


RF Coax Connectors

OSSP Subminiature Modular Blind Mate Connectors (Continued) For Printed Circuit Board Mount



Right-Angle Plug Receptacle





Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

OSSP Subminiature Modular Blind Mate Connectors (Continued) Hermetically Sealed

Metal to Metal Formable Gasket — Panel Feedthrough Plug Receptacle

Electronics

₹тусо




Solder and Braze-In Panel Feedthrough Plug Receptacle



Field Replaceable Solder and Braze-In


2-Hole Flange Mount Plug Receptacle With EMI/RFI Gasket






VSWR (GHz)	RF Leakage (dB)	Plating	Part No.
1.06 + .01f	–(85-fGHz)	Gold	1059905-1

Recommended Mounting Hole Detail A at bottom of this page.




VSWR (GHz)	RF Leakage (dB)	Plating	Part No.	
1.06 + .01f	–(85-fGHz)	Gold	1059902-1	

Recommended Mounting Hole Detail B at bottom of this page.




Recommended Mounting Hole Detail C at bottom of this page.


Recommended Mounting Hole Detail for Hermetically Sealed



Detail B*



Detail C*



Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

*Consult appropriate Instruction Sheet for complete mounting procedure.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Detail A*

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SMB Connectors

Product Facts

- SMB offers snap-fit coupling for quick connect/disconnect
- Choice of Commercial or High Rel Connectors
- 50 and 75 Ω MIL-Type connectors available
- Straight plugs and jacks are completely crimp terminated
- Fast easy cable assembly
- Low VSWR
- Standard military, commercial or Tyco Electronics tooling
- Listed under the Component Program of Underwriters Laboratories Inc., File No. E81956
- PC Board soldered connectors are recognized under the Component Program of Underwriters Laboratories Inc., File No. E81956
- Certified by Canadian Standards Association File No. LR 7189

Packaging — All connectors are packaged individually unless otherwise noted under the "Military No. and/or Comments" column in the connector

Between Series Adapters For SMB Between Series Adapters, please see pages 251-260.

specifications chart.

SMB Connectors are available in commercial and high rel versions. They are ideally suited for circuit miniaturization and are offered in a wide range of configurations including plugs, right-angle plugs, jacks, bulkhead jacks and adapters, as well as printed circuit board and solder jacks.

Termination costs are kept to a minimum using plugs and jacks with a crimp center contact and hex crimp outer braid. Both hand held tooling and pneumatic bench-mounted tooling is available. Easily assembled right-angle plugs have a hex crimp on the outer braid ferrule and bifurcated solder center contacts.

Tyco Electronics' 75 Ohm BT 43 SMB Connectors feature unique spring mating with snap-fit couplings for quick connect/disconnect. These connectors are designed to be intermateable with 75 Ohm SMB MIL-C-39012 connectors. They also feature reliable dual crimp cable terminations.



176

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

SMB Connector Specifications

After

Electrical Characteristics

Electronics

Tyco

Impedance — 50 ohms and 75 ohms, nominal

Frequency Range — 0 to 4.0 GHz		
Voltage Rating (VRMS) —	Sea Level	70,000 Feet
50 ohm connectors for RG 178/U series cable	300	75
50 ohm connectors for RG 316/U series cable	400	100
75 ohm connectors for RG 179/U series cable	300	75
75 ohm connectors for RG 195/U series cable	500	125

Insulations Resistance — 1000 megohms min.

Contact Resistance — (milliohms max.)

	Initial	Environment
Center contact	6.0	8.0
Outer contact	1.0	1.5
Braid to body	1.0	N/A

Contact Current Rating — 1.5 amps DC max.

to 4.0 GHz or 80% of upper cutoff frequency of the cable, whichever is lower.

Cable	Mating Engagement			
Cable	Straight	Right-Angle		
RG 178/U Series	1.30 + .04F	1.45 + .06F		
RG 316/U Series	1.25 + .04F	1.35 + .04F		

F=GHz, does not apply to 75 ohm connectors.

RF High Potential Withstanding Voltage

Frequency — 5 MHZ

Leakage Current — N/A	
50 ohm connectors for RG 178/U series cable	675 VRMS
50 ohm connectors for RG 316/U series cable	950 VRMS
75 ohm connectors for RG 179/U series cable	950 VRMS
75 ohm connectors for RG 195/U series cable	1225 VRMS
RF Leakage — –55 dB min. at 2-3 GHz	
Insertion Loss — .30dB max. at 3 GHz	

Mechanical Characteristics

Engagement Forces — 14 lbs. [62.3 N] maximum engagement initially. After 500 matings, 14 lbs. [62.3 N] maximum engagement and 2 lbs. [8.8 N] minimum disengagement for all of SMBs.

Cable Attachment -

Straight Connectors — Crimp, both center contact and braid

Right-Angle Connectors — Crimp on braid and bifurcated solder center contact Durability — 500 cvcles per MIL-C-39012

Contact Captivation — When captivated, the contacts will withstand 4.0 lbs. minimum axial force.

Cable Retention — When properly assembled to the compatible braided coaxial cable, the retention is equal to the breaking strength of the cable. **Marking** — Per MIL-STD-130 Environmental Characteristics

Temperature Rating — -65°C to +165°C

 $\label{eq:corrosion} \mbox{ (salt spray)} \longrightarrow \mbox{MIL-STD-202, Method 101, test condition B, 5\% salt solution}$

Vibration High Frequency — MIL-STD-202, Method 204, test condition B (15 G's)

Shock - MIL-STD-202, Method 213, test condition B, 75 G's at 6 milliseconds, $1/_2$ sine

Thermal Shock — MIL-STD-202, Method 107, test condition B, except high temperature shall be +85°C. High temperature shall be +200°C for connectors using 200°C cables.

Moisture Resistance — MIL-STD-202, Method 106, when interface gasket is used. No measurements of high humidity. Insulation resistance shall be 200 megohms minimum within five minutes after removal from humidity.

Durability Test — Conducted per MIL-C-39012 Reg. Para. 3.15, Method Para. 4.6.12

Materials

Body, Body Components and Male Contacts — Brass, half hard, per QQ-B-626, Alloy 360, Zinc per QQ-Z-363

Female Contacts — Beryllium copper per QQ-C-530, heat treated per MIL-H-7199 Insulators — TFE fluorocarbon per ASTM D 1710, Type 1, Grade 1 Lockwashers — Phosphor bronze per QQ-B-750

Crimp Ferrule — Annealed copper alloy per WW-T-799

Gaskets — Silicone rubber per ZZ-R-765, Class 11B, Grade 65-75

Plating

Center Contacts — 0.00127 [.000050] min. Gold per MIL-G-452048 Type 1, Grade C, Class 1, over 0.00254 [.000100] min. nickel per QQ-N-290 Other Metal Parts — Gold, Nickel or Solder plated to meet the Finish and Corrosion requirements of MIL-C-39012

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMB Connectors, 50 Ohm

Straight Plugs

₹ Tyco Electronics



RG/U Cable	Center Contact Plating	Outer Contact Plating	Other Metal Parts Plating	Dielectric	Style	Part No.
178, 178A, 178B, 196, 196A	Gold	Gold	Nickel	TEFLON	MIL Type	413985-6
	Gold	Gold	Gold	TEFLON	MIL Type	413985-1
174.040	Gold	Gold	Nickel	TEFLON	MIL Type	413985-3
174, 316, 188, 188A	Gold	Nickel	Nickel	TEFLON	MIL Type	413985-1
	Gold	Gold	Nickel	TEFLON	Die Cast	414946-
	Gold	Nickel	Nickel	TEFLON	Die Cast	5414946-
179. 179A. 179B.	Gold	Gold	Nickel	TEFLON	MIL Type	1-413985-
161, 187, 187A,	Gold	Gold	Nickel	TEFLON	Die Cast	5414946-
BELDEN 9221	Gold	Gold Gold TEFLON Gold Nickel TEFLON Nickel Nickel TEFLON Gold Gold TEFLON Gold Gold TEFLON Gold Gold TEFLON Gold Nickel TEFLON Gold Nickel TEFLON Gold Nickel TEFLON	Die Cast	5414946-		
	Gold	Gold	Gold	TEFLON	MIL Type	413985-
RG 316.	Gold	Gold	Nickel	TEFLON	MIL Type	413985-
188 Double Braid	Gold	Gold	Nickel	TEFLON	Die Cast	5414946-
	Gold	Nickel	Nickel	TEFLON	MIL Type	413985-

Right-Angle Plugs







Die Cast

RG/U Cable	Center Contact Plating	Outer Contact Plating	Other Metal Parts Plating	Dielectric	Style	Part No.
170 1701 1700	Gold	Gold	Gold	TEFLON	MIL Type	414002-7
178, 178A, 178B, 196, 196A	Gold	Gold	Nickel	TEFLON	MIL Type	414002-8
100, 100/1	Gold	Gold	Nickel	TEFLON	Die Cast	5414363-8
	Gold	Gold	Gold	TEFLON	MIL Type	414002-1
174, 316, 188, 188A	Gold	Gold	Nickel	TEFLON	MIL Type	414002-3
179, 179A, 179B 161, 187, 187A	Gold	Nickel	Nickel	TEFLON	MIL Type	414002-5
BELDEN 9221	Gold	Gold	Nickel	TEFLON	Die Cast	5414363-3
DEDEN VEET	Gold	Nickel	Nickel	TEFLON	Die Cast	5414363-5
50.010	Gold	Gold	Gold	TEFLON	MIL Type	414002-2
RG 316, 188 Double Braid	Gold	Gold	Nickel	TEFLON	MIL Type	414002-4
	Gold	Gold	Nickel	TEFLON	Die Cast	5414363-4

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

178

Catalog 1307191 Dimens Revised 3-07 and incl specifie www.tycoelectronics.com are star

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


SMB Connectors, 50 Ohm (Continued)

Straight Jacks



Center Contact Plating	Body Plating	Dielectric	Style	Jack Part No.
Gold	Nickel	TEFLON	MIL Type	5414170-2
Gold	Nickel	TEFLON	MIL Type	5414170-1
Gold	Nickel	TEFLON	Die Cast	414948-1
Gold	Nickel	TEFLON	Commercial	414948-3
	Contact Plating Gold Gold Gold	Contact Plating Body Plating Gold Nickel Gold Nickel Gold Nickel	Contact PlatingBody PlatingDielectricGoldNickelTEFLONGoldNickelTEFLONGoldNickelTEFLON	Contact PlatingDoug PlatingDielectricStyleGoldNickelTEFLONMIL TypeGoldNickelTEFLONMIL TypeGoldNickelTEFLONDie Cast

Bulkhead Jacks



Maximum Panel Thickness 2.36 [.093] Recommended Panel Cutout for Bulkhead Jack and Adapter

Bulkhead Jack Adapter

(Jack-Jack)



RG/U Cable	Center Contact Plating	Body Plating	Dielectric	Style	Bulkhead Jack. Part No.
174, 316,	Gold	Nickel	TEFLON	Commercial	5415006-1
188,188A	Gold	Nickel	TEFLON	Commercial	5228217-1
RD 316, 188 Double Braid	Gold	Nickel	TEFLON	Commercial	5415006-2



Туре	Center Contact Plating	Body Plating	Dielectric	Style	Part No.
lack To Jack	Gold	Nickel	TEFLON	MIL Type	228553-1
Jack-To-Jack	Gold	Gold	TEFLON	MIL Type	228553-2

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RF Coax Connectors

SMB Connectors, 50 Ohm (Continued)

PC Board Vertical Jacks







Recommended PC Board Layout


Jacks


Туре	Center Contact Plating	Body Plating	Dim. A	Dim. B	Dielectric	Style	Part No.
_	Gold	Gold	7.62 .300	3.94 .155	TEFLON	MIL Type	413990-1
_	Gold	Nickel	7.62 .300	3.94 .155	TEFLON	MIL Type	413990-2
_	Gold	Nickel	10.16 .400	2.54 .100	TEFLON	MIL Type	414612-2
_	Gold	Tin	3.94 .155	8.25 .325 Max.	TEFLON	Brass, Stamped	5221111-1

PC Board Vertical Plugs









Recommended PC Board Layout

Plugs

Туре	Center Contact Plating	Body Plating	Dim. A	Dim. B	Dielectric	Recommended PC Board Layout	Style	Part No.
Low Profile (Plug) Mated Pair	Gold	Nickel	3.94 .155	7.62 300	TEFLON	В	MIL Type	415774-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


180

Catalog 1307191 D Revised 3-07 a swww.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMB Connectors, 50 Ohm (Continued)

PC Board, Right-Angle Jacks




Туре	Center Contact Plating	Interface Body Plating	PCB Leg Plating	Dielectric	Dim. A	Dim. B	Style	Recommended PC Board Layout	Part No.
	Gold	Gold	Gold	TEFLON	7.11 .280	3.94 .155	MIL Type	А	413996-2
Low Profile	Gold	Nickel	Nickel	TEFLON	7.11 .280	3.94 .155	MIL Type	А	413996-4
Low Frome	Gold	Gold	Gold	TEFLON	7.11 .280	2.79 .110	Die Cast	А	415340-1
	Gold	Gold	Gold	TEFLON	8.76 .345	2.79 .110	Die Cast	А	415672-1
	Gold	Gold	Gold	TEFLON	8.51 .335	3.94 .155	MIL Type	А	414026-2
	Gold	Nickel	Nickel	TEFLON	8.76 .345	3.94 .155	MIL Type	А	414026-3
With Standoff Pads	Gold	Nickel	Tin-Lead	TEFLON	8.76 .345	3.94 .155	Die Cast	А	5414337-1
	Gold	Nickel	Nickel	TEFLON	8.76 .345	2.79 .110	Die Cast	В	5415379-1*
	Gold	Nickel	Nickel	TEFLON	8.51 .335	3.94 .155	Die Cast	А	415381-1 ♦
Bulkhead	Gold	Gold	Gold	TEFLON	7.67 .302	2.79 .110	Die Cast	А	414963-1
Commercial	Gold	Nickel	Tin	Polypropylene	9.78 .385	3.94 .155	Brass, Stamped	С	5228435-1
Bulkhead	Gold	Gold	Gold	TEFLON	7.67 .302	2.79 .110	Die Cast	А	1274330-1

* 5 leg design

PC Board, Right-Angle Plug





Sund

Plugs								
Center Contact Plating	Interface Body Plating	PCB Leg Plating	Dielectric	Dim. A	Dim. B	Style	Recommended PC Board Layout	Part No.
Gold	Nickel	Nickel	TEFLON	8.76 .345	2.79 .110	Die Cast	В	415380-1*
Gold	Nickel	Tin	TEFLON	8.76 .345	3.94 .155	Die Cast	A	5414338-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

* 5 leg design

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

6.35 Hex

[.250]

Туре

Front Mount

Rear Mount

*includes Jam Nut and Lockwasher

SMB Connectors, 50 Ohm (Continued)

Center Contact Plating

Gold

Gold

.**...0** Max. [.630]

> Body Plating

Nickel

Nickel

Bulkhead PC Board Jack, Solder Receptacle Kits



Kit Includes Lockwasher and Jam Nut

Lockwasher and Jam Nut






Part No. 415001-2

Part No. 414969-2

SMB Receptacle Jack



Туре	Center Contact Plating	Body Plating	Dielectric	Style	Part No.
Front Mount	Gold	Nickel	TEFLON	MIL Type	414895-1

TEFLON is a trademark of E.I. Dupont de Nemours and Company.

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

182

Catalog 1307191 Dimensi Revised 3-07 and incl specifie www.tycoelectronics.com are stan

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

5/4.88 [.197/.192] Dia.

+

Maximum Panel Thickness 2.36 [.093] Recommended Panel Cutout

Style

MIL Type

MIL Type

2.08/2.01 [.082/.079]

Kit Part No.

228216-1*

228215-1*

3.71 [.146]

Dielectric

TEFLON

TEFLON

SMB Connectors, Mini 75 Ohm

Product Facts

₹тусо

Industry standard for miniature 75 ohm SMB

Electronics

- SMB offers snap-fit coupling for quick connect/disconnect
- Suitable for high density applications
- Fast easy cable assembly
- Low VSWR
- Connectors offer consistent mating and unmating forces
- Straight plugs and jacks are completely crimp terminated
- Low cost

Mini 75 ohm SMB connectors are ideally suited for circuit miniaturization in communication, broadband and switching equipment as well as a variety of other applications.

They offer the same low consistent mating/unmating force as Tyco Electronics standard SMB products and therefore, outer contact resistance values are maintained from connector to connector.

Standard military, commercial or Tyco Electronics tooling can be used to terminate these products. Cost effective assembly of the straight plugs is completed with a crimp center contact and hex crimp on the outer braid. Right-angle plugs have a hex crimp on the outer braid ferrule and bifurcated solder center contacts.



Electrical Characteristics

Impedance — 75 ohms Frequency Range — 0 to 4.0 GHz Insulation Resistance — 1000 megohms Contact Current Rating — 1.5 amps DC max.

Mechanical Characteristics

Engagement Forces — Initial—14.0 lbs. [62.3 N] maximum engagement. After 500 matings, 14.0 lbs. [62.3 N] maximum engagement. Durability—500 cycles

Environmental Characteristics


Temperature Rating — -65°C to +165°C

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


SMB Connectors, Mini 75 Ohm (Continued)

Straight Plug




RG Cable	Center Contact Plating	Outer Contact Plating	Body Plating	Part No.
179, 187	Gold	Gold	Nickel	5415487-1
179, 187	Gold	Nickel	Nickel	5415487-2
RD 179	Gold	Nickel	Nickel	5415487-3

Right-Angle Plug



RG Cable	Center Contact Plating	Outer Contact Plating	Body Plating	Part No.
179, 187	Gold	Nickel	Nickel	5415484-1
179, 187	Gold	Gold	Nickel	5415484-2
RD 179	Gold	Gold	Nickel	5415484-3

Bulkhead Jack



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

184

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMB Connectors, Mini 75 Ohm (Continued)



www.tycoelectronics.com

specified. Values in brackets are standard equivalents.

reference purposes only. Specifications subject to change.

Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SMB Connectors, 75 Ohm BT 43 (SMZ)


Product Facts

₹тусо

 Widely used in data transmission and telecommunication applications

Electronics

- BT 43 connector developed from the SMB range and feature snap-on and latching variant
- Most BT 43 connectors are available as fully crimped connectors.
- BT 43 and 75 Ω connectors available in solder and crimp versions



The Tyco Electronics range of 75 ohm SMB (SMZ) connectors are designed to meet the increasing demands of the Telecommunications market, and are designed in accordance with BS9210 F0022. Specifications

Max working voltage (dc) — 500 V Max proof voltage (dc) — 1.5 kV Contact resistance (inner) — 5 milliohm Contact resistance (outer) — 1 milliohm Bodies and other parts — Brass

Female center contacts — Copper Alloy Male center contacts — Copper Alloy Outer contacts — BeCu Plating —


Contacts and critical surfaces — Gold Other parts — Nickel Insulators — P.T.F.E.

186

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Straight Plugs, Snap-On

Tyco Electronics



Coble Ture	Terminatio	on Method	Rody Disting	Part No	
Cable Type	Inner	Outer	Body Plating	Part No.	
RG 179B/U	Crimp	Crimp	Selective Gold	1311097-1	
BT2002	Crimp	Crimp	Selective Gold	1311098-1	

Straight Plugs, Latching, Crimp/Crimp



Cable Type	Body Plating	Part No
RG 179B/U	Selective Gold	1311099-1
BT2003	Selective Gold	1311100-1
BT2002	Selective Gold	1311101-1
BT2001	Selective Gold	1311696-1
BT3002, TZC75024	Selective Gold	1311102-1
RG 59B/U, RG 140/U, URM90	Selective Gold	1313507-1


Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




Tyco Electronics




Cable Type	Body Plating	Part No
RG 179B/U	Selective Gold	1311103-1
BT3002, TZC75024	Selective Gold	1311104-1

Right-Angle Socket, Latching, Solder/Crimp



Cable Type	Body Plating	Part No
RG 179B/U	Selective Gold	1311106-1
BT2003	Selective Gold	1311698-1
BT3002, TZC75024	Selective Gold	1311111-1
RG 59B/U, RG 140/U	Selective Gold	1313508-1

Straight Free Plug, Crimp/Crimp



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

188

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Straight Bulkhead Plug


Tyco Electronics



Mounting Detail


7.5 [0.30]

Cable Type	Termination Method		Pody Plating	Part No.
Cable Type	Inner	Outer	Body Plating	Fart NO.
RG 179B/U	Crimp	Crimp	Selective Gold	1311120-1
BT500B, BT2003, BT2003A	Crimp	Crimp	Selective Gold	1311701-1
BT3002, TZC75024	Crimp	Crimp	Selective Gold	1311122-1



Cable Type	Termination Method		Body Plating	Part No.
Cable Type	Inner	Outer	Body Flating	Fait NO.
3M: 043, 031C, CS4456, Gore: GCX	Crimp	Crimp	Selective Gold	1313511-1


Right-Angle Bulkhead Plug, Solder/Crimp



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Cable Type	Body Plating	Part No
RG 179B/U	Selective Gold	1327083-1
BT2003	Selective Gold	1311117-1
BT2002	Selective Gold	1311700-1
B2001	Selective Gold	1313883-1
BT3002, TZC75024	Selective Gold	1311118-1
RG 59B/U, RG 140/U, URM90	Selective Gold	1313887-1


DDF Plug, Crimp/Crimp


DDF Plug, Crimp/Crimp



Cable Type	Body Plating	Part No
RD179, 124431 (Filotex), 1366 (Orebro), K02253D-1, K02253-2 (Shuner)	Selective Gold	1314422-1

PC Board Plug 43/1D








Body Plating	Part No.
Selective Gold	1311125-1


PC Board Plug 43/1E



Mounting Detail

Part No.
1314103-1

Right-Angle PC Board Plug



Part No. 1314102-1


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Straight Adapter Plug-Plug








Mounting Detail

Part No. 1313364-1


Body Plating	Part No.
Selective Gold	1313364-1
Selective Gold	1311127-1

Part No. 1311127-1

Tester 430A



Body Plating	Part No.
Selective Plating	6-1311703-1



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

SMB Connector Crimp Tooling

50 Ω/**75** Ω

		Comme	rcial Conn	ector Toolir	Ig			IV	ALL Type Cor	nector Too	ling		
	Center Contac	t Crimp Tool	ling	Brai	d Crimp T	ooling	Center C	contact Crimp	Tooling		Braid Crin	np Tooling	
RG/U Cable	Dies for Tyco Electronic PRO-CRIMPER Hand Tool		2-01 I	Tyco Ele	s for ctronics RIMPER Tool	MIL-C- 22520/5-01 Tool DANIELS* Hex	DANIELS* Hand Tool	DANIELS* Positioner Number	Selector Position	Dies Tyco Elec PRO-CR Hand	tronics	DANIELS Hand Tool	Hex Die Across Flats
	Number	Positioner	roontion	Number	Position	Crimp Die				Number	Position		
178, 178A, 178B, 196, 196A	58489-1	Female-K699 Male-K727	9 4	58489-1	A&B	Y624	AFM8	Female-K699 Male-K727	4	58483-1	А	HX4-1637	2.67 .105
Double Braid 178, 196		_	_	_	_	_	AFM8	Female-K699 Male-K727	4	58483-1	В	HX4-1637	3.25 .128
174, 316 188, 188A	58489-1	Female-K699 Male-K727	9 4	58489-1	А	Y444	AFM8	Female-K699 Male-K727	4	58483-1	В	HX4-1637	3.25 .128
Double Braid 174, 316, 188	58489-1	Female-K699) 4	58489-1	С	Y196 Location A	AFM8	Female-K699	4	58483-1	С	HX4-1637	3.84 .151
Double Braid 174, 316, 188	58489-1	Male-K727	4	58489-1	С	Y196 Location A	AFM8	Solder		58483-1	В	HX4-1637	3.25 .128
179, 179A 179B, 161, 187, 187A, BELDEN 922	58489-1	Female-K699) 4	58489-1	A	Y444	AFM8	Female-K699	4	58483-1	В	HX4-1637	3.25 .128
179, 179A 179B, 161, 187, 187A, BELDEN 922	58489-1	Male-K727	4	58489-1	A	Y444	_	Solder	_	58483-1	В	HX4-1637	3.25 .128
180, 180A 180B	—	_	_		_	_	_	Solder	_	58483-1	С	HX4-1637	3.84 .151
Mini SMB 75	5 ohm												
179, 187	—	Female-K699) —	58483-1	В	HX4-1637	_	—	—	—	—	—	—
179, 187	_	Solder Center Contact	_	58483-1	В	HX4-1637	_	_	_	_	_	_	_

Note: All 75 ohm SMB connectors have a solder center contact.

* DANIELS Manufacturing Corporation Telephone: 407-855-6161 6103 Anno Avenue Orlando, Florida 32809 FAX: 407-855-6884

Note: Equivalent military tool part numbers-M22520/5-01 – DANIELS Hand Tool HX4 M22520/5-33 – DANIELS Die Set Y136

M22520/5-37 - DANIELS Die Set Y138 M22520/5-41 – DANIELS Die Set Y140 M22520/5-03 – DANIELS Die Set Y196 M22520/2-01 – DANIELS Hand Tool AFM8

BELDEN is a trademark of Belden Wire and Cable Company. DANIELS is a trademark of Daniels Manufacturing Corporation.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

192

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMC Connectors


Product Facts

₹ Тусо

- Three-piece designs
- Fast, clean cable assembly

Electronics

- Connector bodies preassembled
- Solderless termination no danger of heat damage
- Center conductor and braid terminated with same tool
- Low noise level
- Miniature screw-on coupling
- TEFLON dielectric



The SMC Connector is miniature and light-weight, especially designed for use in critical applications where limited space and vibration are of major concern.

This connector is designed in accordance with the requirements of Specification MIL-C-39012, Class II, Category B to assure the highest standards of electrical and mechanical performance. It has a constant impedance of 50 ohms, a voltage rating of 350 volts and provides excellent operation at frequencies up to 10 GHz. It also has a threaded coupling and can be used with a wide range of miniature coaxial cable sizes including RG 174, 197, 187, 188 and 316.

Materials

Brass — QQ-B-626 Beryllium Copper — QQ-C-530 Copper — QQ-C-576 TEFLON Insulation — MIL-P-19468

Plating

Gold — MIL-G-45204

Electrical Characteristics

Nominal Impedance — 50 ohms Working Voltage — 335 volts rms Frequency Range — 0 to 10 GHz Insulation Resistance — 1000 megohms min.

Contact Resistance -

Outer Contact — 1 milliohms Center Contact — Straight Connectors — 6 milliohms Right-Angle Connectors — 12 milliohms

Dielectric Withstanding Voltage — 1000 volts rms

RF Leakage — -60 dB min., between 2 and 3 GHz

RF Insertion Loss —

Straight Connectors — 0.25 dB max. at 4 GHz Right-Angle Connectors — 0.50 dB max. at 4 GHz

Corona Level — 250 volts min. at 70,000 ft [21 336 m]

Mechanical Characteristics

Mating/Unmating — 10-32 threaded coupling

Cable Attachment — Crimp type, both center contact and braid

Coupling Nut Retention — 35 lb [156 N] min. Cable Retention — 20 lb [89 N] min., GR-174 cable

Durability — 500 cycles per MIL-C-39012

Environmental Characteristics Temperature Range —

-65°C to +85°C

Vibration — MIL-STD-1344, Method 2005, Condition IV

Salt Spray — MIL-STD-1344, Method 1001, Condition B

Temperature Cycling — MIL-STD-1344, Method 1003, Condition A (except low temperature is -65°C)

TEFLON is a trademark of E.I. Dupont de Nemours and Company.


Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMC Connectors (Continued)


Straight Plugs




Cable Attachment	RG/U Cable	Part No.
Crimp	178, 178A, 178B 196, 196A	1060220-1
Crimp	174, 316 188, 188A	1060221-1
Clamp	174, 316 188, 188A	1060163-1



Cable Jacks



Cable Attachment	RG/U Cable	Part No.
Clamp	174, 316 188, 188A	1311638-1



Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

194

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMC Connectors (Continued)




₹ Tyco Electronics



Part No. 1460470-1







Cable Attachment	RG/U Cable	Part No.
Clamp	174, 316 188, 188A	1060183-1


PC Board Jack Receptacles

Straight





Part No. 1060259-1



Rcommended PC Board Layout

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

MCX Connectors


Product Facts

₹тусо

 Snap-on interface facilitates assembly

Electronics

- Conforms to CECC interface specifications for MCX
- 30% smaller than SMB connectors
- Surface mount tape and reel for high volume
- 50 and 75 ohm versions available



Between Series Adapters

For MCX Between Series Adapters, see pages 251-260.

Tyco Electronics MCX microminiature snap-on connectors offer an excellent blend of size, durability and performance for emerging applications in GPS, automotive and wireless communications. MCX connectors are 30% smaller than traditional snap-on SMB connectors, offering greater packaging density and weight reduction. MCX connectors are mechanically robust with beryllium copper spring fingers rated at a minimum of 500 mating cycles. The snap-on interface facilitates assembly, eliminating the need for a threaded connection, and

ensuring full engagement. The forces to engage and disengage have been optimized to ensure ease of mating as well as to prevent damage to PCB solder connections. MCX connectors are designed for broad band performance, DC-6 GHz, and can be utilized for future system upgrades without concerns for performance degradation. Tyco Electronics MCX connectors are fully mateable with standard MCX connectors and conform to the CECC interface specifications.

MCX connectors are available in a broad range of

standard configurations for commercial applications. Tape and reel packaging for MCX surface mount straight and right-angle PCB receptacles is available to facilitate high volume pick and place manufacturing. MCX surface mount connectors are designed to withstand infrared reflow, convection and vapor phase soldering and provide a .254 [.010] standoff for optimal board cleaning. MCX plug and jack PCB receptacles also offer a direct board to board solution providing a nominal 7.11 [0.28] separation.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

MCX Connectors (Continued)

Specifications

General	CECC 22220 PARA				
Materials	_	Brass alloys UNS C36000 (ASTM-B16) or C38500 per QQ-B626, Beryllium copper per ASTM B-196, PTFE fluorocarbon per ASTM-D-1710			
Finish	_	Center Contacts: Gold plated (ASTM-B488) over nickel plate (QQ-N-290)			
		Outer Contacts: Gold plated (ASTM-B488) over nickel plate (OO-N-290)			
		Housings: Nickel plated (QQ-N-290), tin (ASTM-B488) or Gold plated (ASTM-B488)			
	_	All other metal parts shall be furnished so as to provide a connector which meets corrosion requirements of CECC 22220 PARA 4.6.10			
Design	_	The design shall be such that the outline and interface dimensions shown in this catalog and the requirements of CECC 22220 PARA are met			
Electrical	CECC 22220 PARA	(General requirements performance may vary by cable)			
Frequency	_	dc - 6 GHz			
Nominal Impedance	_	50 ohms			
Voltage Rating	_	335 Volts (VRMS Maximum) @ Sea Level			
VSWR	4.4.1	1.25:1 Maximum @ 4 GHz			
	_	1.35:1 Maximum @ 6 GHz			
Insulation Resistance	4.4.4	10,000 Megohms Minimum			
Insertion Loss	_	.1dB Maximum/1000 MHz			
Dielectric Withstanding Voltage	4.4.5	1000 Volts (VRMS Minimum) @ Sea Level			
Contact Resistance					
Center Contact	4.4.2	5.0 Milliohms Maximum			
Outer Contact	4.4.3	1.0 Milliohms Maximum			
Corona 70,000 ft.	_	250 Volts (VRMS Minimum) @ MHz			
RF High Potential @ Sea Level	—	670 Volts (VRMS Minimum) @ MHz			
Contact Current	—	1.5 ADC Max			
Mechanical	CECC 22220 PARA				
Force to Engage	4.5.4	15.5 N [3.4 lbs.] Maximum			
Force to Disengage	_	8 – 20 N [1.8 – 4.5 lbs.]			
Contact Captivation	4.5.2	Designed to maintain MCX interface when mating 10 N [2.2 lbs.] axial			
Connector Durability	4.7.1	500 insertion and withdrawal cycles			
Environmental	CECC 22220 PARA				
Temperature Rating	_	–65°C + 165°C			
Vibration	4.6.3	See CECC 22220			
Moisture Resistance	4.6.4	See CECC 22220			
Corrosion	4.6.10	See CECC 22220			
Thermal Shock	4.6.7	See CECC 22220			
Corrosion	4.6.10	See CECC 22220			

Meets or exceeds requirements of CECC 22220. Tyco Electronics has design control and all data contained herein is subject to change without notice. Contact Tyco Electronics for specifications on other connector types.



Plug

5		
Letter	Minimum	Maximum
А	0.48 [.0189]	0.53 [.0208]
В	2.00 [.0788]	_
С	—	3.8 [.148]
D	0.00 [.000]	0.30 [.0118]
E	2.80 [.111]	3.20 [.125]
F	4.15 [.164]	_
G	2.80 [.111]	_

Jack

Letter	Minimum	Maximum
Н	—	1.98 [.077]
I	3.42 [.135]	3.48 [.137]
J	3.60 [.142]	3.75 [.147]
K	2.30 [.091]	2.80 [.110]
L	2.60 [.103]	2.80 [.110]
М	4.00 [.158]	4.12 [.162]
N	0.75 [.0296]	0.85 [.0334]

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

MCX Connectors (Continued)

Straight Cable Plug, Crimp

₹ Tyco Electronics






Cable	Plating	Part No.
RG 178/U, 196/U	Nickel	1060869-1
RG 174/U, 188/U, 316/U	Nickel	1060872-1
	Gold	1060871-1
RD-316	Nickel	1060875-1
	Gold	1060875-2

Note: For full crimp attachment consult Tyco Electronics at the numbers listed below.

Right-Angle Cable Plug, Crimp








Cable	Plating	Part No.
RG 178/U, 196/U	Nickel	1329293-1
RG 188/U, 316/U RG 179/U, RG 187/U	Nickel	1330723-1
RD-316	Nickel	1363301-1
	Gold	1363301-2

Straight Cable Terminal, PC Board, Without Center Contact





Cable	Dim. A	Dim. B	Plating	Part No.
	11.76	3.94	Nickel	1060811-1
RG 174/U,	.463	.155	Gold	1060811-2
188/U, 316/U	10.74 .423	2.92 .115	Gold	1060813-2

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

- 1	\sim	n
- 1	ч	×
	J	U

₹ Tyco Electronics


RF Coax Connectors

MCX Connectors (Continued)

_

Bulkhead Cable Jack






ricconnicitaca
Mounting Hole

Cable	Plating	Part No.
RG 188/U, RG 316/U	Nickel	1060883-1

Straight Cable Plug, Direct Solder Attachment For Semi-Rigid Cable






Cable	Plating	Part No.
RG 405/U [.085]	Gold	1060772-1
.047	Gold	1060772-2

Straight Cable Jack, Direct Solder Attachment For Semi-Rigid Cable





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

MCX Connectors (Continued)

Right-Angle Plug Receptacle, Direct Solder Attachment For Semi-Rigid Cable

₹ Tyco Electronics






Cable	Plating	Part No.
RG 405/U	Gold	1060787-1


Vertical Plug Receptacle, PC Board



Vertical Jack Receptacle, PC Board







Dim. A	Dim. B	Plating	Part No.
8.28	2.92	Nickel	1060985-1
.326	.115	Gold	1060984-1
9.30	3.94 .155	Nickel	1060989-1
.366		Gold	1330126-1
7.09	1.73	Nickel	1060996-1
.279	.068	Gold	1060995-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


200

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

MCX Connectors (Continued)

Vertical End Launch, PC Board


Electronics



Plating	Part No.
Tin	1061007-1
-	

Right-Angle Jack Receptacle, PC Board







Dim. B	Plating	Part No.
3.94	Nickel	1061023-1
[.155]	Gold	1061022-1
1.73 [.068]	Nickel	1061027-1
	Gold	1061026-1
2.92] [.115]	Nickel	1061030-1
	Gold	1061029-1
	[.155] 1.73 [.068] 2.92	I.155 Gold 1.73 Nickel [.068] Gold 2.92 Nickel

Jack Receptacle, Bulkhead Feedthrough







Recommended Mounting Hole

Plating	Part No.
Nickel	1060960-1
Gold	1060959-1


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

MCX Connectors (Continued)

Vertical Jack Receptacle, Surface Mount






Plating	Part No.	
Tin –	6061002-1	
	6061092-1 ¹	

¹Tape and Reel packaging. 900 connectors per reel (carrier width 16mm, carrier pitch 12mm).


Right-Angle Jack Receptacle, Surface Mount





Part No.
6061035-1
6061094-11

¹Tape and reel packaging. 750 connectors per reel (carrier width 24mm carrier pitch 12mm).



Recommended Mounting Pattern for Microstrip Line

Notes:

- 1. Printed circuit board material: glass epoxy FR-4 or similar; relative permittivity: 4.8, 1 oz. copper clad both sides.
- 2. These dimensions valid for 1.58 [.062] board thickness.
- 3. Decimal inch equivalents are shown in parentheses for general information only.


Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Di Revised 3-07 ar sp www.tycoelectronics.com ar

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics





Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Compression Coax Board-to-Board Connectors

Board-to-Board RF Connector Series

₹тусо

Single connector product

Electronics

- Surface mount technology
- Excellent price-toperformance ratio

Product Facts

- Single connector design no mating connectors needed
- Available in four sizes for varied board spacing: 14mm, 10mm, 6.65mm and 4mm
- Large radial and axial misalignment: For positioning both boards and for gap between boards
- Surface Mount Device for standard pick & place compatibility
- Gold plated phosphor bronze and brass contacts, stainless steel springs
- Mating directly on target board
- Easy connection without risk of breaking soldering or connector when mating or unmating
- Low applied material and assembly costs

Applications

- Modular parallel board-toboard blindmate applications
- Base Station / Sub Station systems
- PDA / PCS / Cellular Handset applications
- Wireless Communications systems (GSM, PCS, WCDMA, UMTS)



Specifications Characteristic Impedance —

50 Ohms Frequency Range — Up to 6 GHz Return Loss — -20dB min.; up to 2.2 GHz (all misalignments)


Shielding Effectiveness — -60 dB min.; up to 2.2 GHz Working Voltage — 125 VAC, 50 Hz (at sea level) Dielectric Withstanding Voltage — 500 VAC, 50 Hz (at sea level) Insulation Resistance — 100 Megohms Operating Temperature —

-40 to +125°C Mating Force — 10 N

Durability — 25 cycles Angle Between Boards — $\pm 2^{\circ}$ max. Axial Misalignment — ± 1.0 mm from nominal boards stacking height; ± 0.4 mm, ± 0.3 mm for shortest models (Part Numbers 619135 and 1658260)

Radial Misalignment — ± 0.8mm from center line in any direction Vibration — 20 g between 58-500 Hz (Const. amplitude of 1.5 mm between 10-58 Hz)





Part Number	Height "H"
619127-1	14 ± 1.0mm
619134-1	10 ± 1.0mm
619135-1	6.65 ± 0.4mm
1658260-1	4 ± 0.3mm

Related Product Data

Internet — http://tycoelectronics.com/products/rfcoax Product Specification/Design Objectives — 108-71060 Test Report — 501-90021 Sample Kit — 1-1773441-3

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

STAX Coax Connectors

Product Facts

₹ Тусо

Low cost, low height and high performance

Electronics

- Low insertion loss 0 to -0.5 dB from 0 to 6 GHz
- VSWR < 1.07 from 0 to 6 GHz
- Wide working range of deflection
- Long term reliability and durability
- Surface mount/pick and place
- Low board separation \leq 2.5 mm
- Technology can support board separations ≤ 1.5 mm
- Easily modified free height
- No tooling required for height modifications
- Modified prototype samples within 2 weeks



Tyco Electronics' STAX coax RF connector is the first surface mount RF board-to-board connector on the market that uses elastomeric connector technology to provide an economical means to achieve low board separation while maintaining excellent RF signal integrity between PCBs.

The connector uses laminated sections of conductive and nonconductive silicone that are tuned to provide a 50 ohm impedance line between mated substrates. The single piece construction of the STAX coax RF connector eliminates some of the signal anomalies normally associated with mated pairs of metal contact coax connectors. The dimensional relationship of the inner and outer conductor is consistently maintained throughout the connector.

With its metal holder, the STAX coax RF connector can be surface mount

soldered to the PCB. An additional metal SMT holder aligns the connector to the mating PCB. If adequate PCB alignment is already maintained by other means, the STAX RF connector may not need the additional mating receptacle and can become a blindmating connector. This has an additional advantage in space constrained mobile applications where very fine-pitch board-to-board connectors are also used.

Electrical Characteristics

 $\label{eq:contact} \begin{array}{l} \mbox{Contact Resistance} \longrightarrow < 50 \ m\Omega \\ \mbox{Insulation Resistance} \longrightarrow 10^{12} \ \Omega \\ \mbox{min.} \end{array}$

Dielectric Withstanding Voltage (without breakdown or arcing) — 1000 Volt

Physical Characteristics

Board Separation — 2.5 mm ± 0.2 (std. part) PCB Board Area — 4.0 mm dia. Typical Clamping Force — See chart

Environmental Characteristics Operating Temperature —

-40°C to +125°C Moisture — 0 to 100% RH

Related Product Data

Internet — www.elastomerictech.com www.tycoelectronics.com

Elastomeric Technologies Applications Engineering —

Phone: 1-800-989-STAX ext. 4453 Fax: 1-215-784-4522 E-mail: ETIapplicationseng@tycoelectronics.com

Technical Documents -

Qualification Test Report — T R 368 RF Performance Report — 00266

Catalog 1307191 Revised 3-07

www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Tyco Electronics


RF Coax Connectors


STAX Coax Connectors (Continued)

Description	Part Number
STAX SMT Coax Connector Assembly: Consists of STAX Coax elastomer in round SMT holder	619229-1
Mating SMT Target Holder: Controls alignment between PCBs	619238-2
STAX Coax RF Elastomer only: Used with customer furnished holder	1442004-1



Part Number 619238-2 SMT Mating Target Holder





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

206

Catalog 1307191 D Revised 3-07 a swww.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMT/QuickGrip Connectors


Product Facts

- Solderless Cable Termination
- 3.0 [.118] Mated Height
- Excellent Cable Retention
- Usable With Flexible and Semi-Rigid Micro-Coaxial Cables
- Tape and Reel Packaging

Tyco Electronics revolutionary SMT/QuickGrip product line is designed to meet the growing demand for a reliable, low cost system for direct termination of coax to a printed circuit board (PCB). SMT/QuickGrip technology eliminates the requirement to connectorize the coaxial cable, reducing assembly times and, therefore, cost. The SMT/QuickGrip surface mount device occupies less PCB area than conventional through hole coaxial connectors. An innovative microstrip mounting pattern and cable receptacle design ensures excellent grounding and PCB retention. The SMT/QuickGrip cable termination system stands a mere 3.0 [.118] off the board when mated, allowing for closer pitch/ spacing when designing a


system. The SMT/QuickGrip design provides optimal cable retention for applications where shock, vibration, and/or cable flexure may be encountered. This unique RF design accepts both flexible and semi-rigid micro-coaxial cables while delivering exceptional RF performance up to 3GHz.


These features make this system extremely versatile for design engineers and offer a reliable, cost effective alternative to direct soldering of cable to the PCB. The cable is inserted into the device by means of a simple self-aligning hand tool, eliminating the requirement for skilled personnel. This system removes the possibility of damaged PCBs and cables which are common quality issues associated with direct solder, while providing superior RF performance. The SMT/QuickGrip accommodates multiple cable insertions allowing easy replacement of cables for repairs. This receptacle is designed for high volume assembly using surface mount technology and is available in tape and reel packaging for pick and place board assembly. Prestripped cables and inter-



series cable pigtails are available as turnkey solutions for your application needs (i.e.: for use in multi-board applications, for connecting antennas to the PCB, or point to point transmission on the same PCB).

The SMT/QuickGrip cable termination system is ideal for wireless surface mount applications in handsets, pagers and personal digital assistants (PDA). The SMT/QuickGrip mechanical and electrical performance, coupled with its ease of use, ensure it to be a high quality, reliable solution for current and future interconnect needs. Tyco Electronics is an ISO9001 certified manufacturer and maintains an SPC controlled manufacturing environment. Please call your local Sales or Distribution office for additional information and qualification samples today.







Omni-Flex 200 cable is a Tyco Electronics specified cable.

PWB

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


SMT/QuickGrip Connectors (Continued)

Specifications


General	
Materials	
Housing:	Polyphenylene Sulfide (PPS)
Contacts:	Copper Alloy
Finishes	
Contacts:	Gold Plate over Nickel
Electrical	
Frequency Range:	DC - 3GHz
Impedance:	Usable with 50 & 75 Ohm systems
Insertion Loss:	.08 √ <i>f</i> GHz
DWV:	750 VRMs
VSWR:	1.3:1 @ 3GHz (Omni-Flex 200 and .047 [.002] Semi-Rigid) 1.4:1 @ 3GHz (.034 [.001] Semi-Rigid)
Mechanical	
Connector Durability:	5 mating cycles min. (receptacle only)
Tape and Reel Packaging:	16 [.629] per EIA-481
Force to Disengage by Cam-Out (grams):	Omni-Flex 200 Cable - 543 typical
	.034 [.001] Semi-Rigid - 852 typical
	.047 [.002] Semi-Rigid - 1066 typical
Environmental	
Temperature Rating:	-40°C(-40°F) to 125°C(257°F) when mated with Omni-Flex 200 Cable
Resistance to Solder Heat:	Infrared, convection, and vapor phase solderable (receptacle only). Maximum reflow time/temperature not to exceed 260°C for 3 minutes.
Cable Information	
	Omni-Flex 200 Cable
Materials:	FEP Flexible Cable (200°C)
Jacket:	Fluorinated Ethylene Propylene
Shield:	Silver plated copper wire, 44 AWG, 90% min. coverage
Dielectric:	PTFE (Polytetrafluoroethylene)
Center Conductor:	Silver Plated Copper Clad Steel, 30 AWG
Minimum Bend Radius:	6.35 [.250]
Insertion Loss (PVC and FEP cable only):	1.3dB/m, 0.4 dB/ft. @ 500 MHz 2.0dB/m, 0.5 dB/ft. @ 1 GHz 3.0dB/m, 0.9 dB/ft. @ 2 GHz
Center Conductor Resistance:	.26 Ohms per foot average

Strip Dimensions

Tyco Electronics Omni-Flex 200 Cable Part Number 1407578-1



Semi-Rigid Cable (.034 and .047)



Omni-Flex 200 cable is a Tyco Electronics specified cable.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

PC Board Mount Receptacle

RF Coax Connectors

SMT/QuickGrip Connectors (Continued)



Recommended Mounting Pattern for Microstrip Line

Description	Part No.
Bulk Packaged 100/bag	1085456-1
700 Piece Reel	1086008-1
2000 Piece Reel	1086009-1

1. Printed wiring board material: glass epoxy FR-4 or similar, relative permittivity: 4.8, 1 oz. copper clad both sides. 2. These dimensions valid for 1.6 [.062] board thickness.



	Å	
	ä	

Part No.
1088313-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMT/QuickGrip Connectors (Continued)

Inter-Series Cable Assemblies



SMA Straight Plug





Cable	Assembly Length (A)	Part No.
Omni-Flex 200	100 [4]	1329174-1
	200 [8]	1329174-2
	305 [12]	1310432-1

Note:

 Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

SMA Bulkhead Jack





Recommended Mounting Hole

Cable	Assembly Length (A)	Part No.
Omni-Flex 200	100 [4]	1329175-1
	200 [8]	1329175-2
	305 [12]	1329175-3

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Note:

 Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

Omni-Flex 200 cable is a Tyco Electronics specified cable.

210

Catalog 1307191 Dimensio Revised 3-07 and inche specified. www.tycoelectronics.com are stand


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SMT/QuickGrip Connectors (Continued)

Inter-Series Cable


Assemblies (Continued)

SMB Bulkhead Jack



Recommended Mounting Hole

SMB Right-Angle Plug



Cable Assembly Length (A) Part No. 100 [4] 1408050-4 0mni-Flex 200 200 [8] 1408050-5 305 [12] 1408050-6

Note:


 Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

Cable	Assembly Length (A)	Part No.
Omni-Flex 200	100 [4]	1255378-4
	200 [8]	1255378-5
	305 [12]	1255378-6

Note:


1. Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

MCX Bulkhead Jack



Recommended Mounting Hole

MCX Right-Angle Plug



Cable	Assembly Length (A)	Part No.
	100 [4]	1408051-4
Omni-Flex 200	200 [8]	1408051-5
	305 [12]	1408051-6

Note:

1. Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

Cable	Assembly Length (A)	Part No.
	100 [4]	1330401-4
Omni-Flex 200	200 [8]	1330401-5
	305 [12]	1330401-6

Note:

1. Cable length tolerances: Length 'A' mm [In], Tolerance mm [In], 50 to 100 [3.94], ± 3 [± .12], 101 to 500 [3.98 to 19.69], ± 5 [± .20], Over 500 [19.69], ± 10 [± .39]

Omni-Flex 200 cable is a Tyco Electronics specified cable.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 211 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013

UK: 44-8706-080-208


Tyco Electronics

SSMT Surface Mount Interconnect System

Microminiature Surface Mount RF Connectors

Product Facts

- 3.0 [.118] mated height
- Excellent interface retention
- Flexible micro-coax cable
- 360 degree mated rotation
- Tape and Reel packaging available



The Tyco Electronics SSMT surface mount Interconnect System is designed to provide superior electrical and mechanical performance for wireless communication applications. The SSMT system occupies less printed circuit board (PCB) real estate than conventional through hole coaxial connectors. An innovative microstrip mounting pattern and plug receptacle design ensure reliable grounding and PCB retention characteristics. The SSMT Interconnect System allows closer pitch/spacing, standing 3.0 [.118] (fully mated height) off the board. The mated SSMT interface allows 360 degrees of rotation providing maximum PCB design flexibility. It has been designed to provide optimal retention for

applications where shock, vibration or cable flexure may be encountered. Force to disengage by cable load (cam-out) exceeds 300 grams.

The SSMT system is designed to provide the performance of much larger industry standard connectors. The SSMT Interconnect System consistently achieves broad band electrical performance through 6 GHz with a maximum VSWR of 1.20:1 at 2 GHz. This broad band performance establishes a reliable interface that can be utilized for future system upgrades without concern for performance degradation.

The SSMT utilizes a common plug receptacle, part number 1251802-1, which is designed for high volume assembly using surface mount technology and is available in tape and reel packaging for automatic pick and place board assembly. The mating cable jack is available terminated to a highly flexible microcoax cable as either a pigtail, jumper or standard interseries connector assembly to meet your needs.


The SSMT Interconnect System can be manually mated, facilitating high volume assembly and eliminating the need for special engagement tooling. The SSMT interface design aligns the center contacts prior to full mating to ensure a robust mechanical engagement. Interface durability is rated at 100 mating cycles.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SSMT Surface Mount Interconnect System (Continued)

Specifications

General		
Materials		
SMT Plug	Housing: Contacts:	Polyphenylene Sulfide (PPS) Copper Alloy
SSMT Cable Jack	Outer Contact: Inner Contact: Dielectric:	Beryllium Copper Beryllium Copper Polypropylene, GF
Finish	Plug and cable ja	ack - Contacts: Gold plate over nickel plate
Electrical		
Frequency	dc - 6 GHz	
Nominal Impedance	50 Ohms	
Voltage Rating	250 Volts (VRMS	Maximum) @ Sea Level
VSWR (Mated Pair)	1.20:1 Maximum @ 2 GHz 1.40:1 Maximum @ 6 GHz	
Insulation Resistance	5000 Megohms Minimum	
Dielectric Withstanding Voltage	500 Volts (VRMS Minimum) @ Sea Level	
Contact Resistance (Connectors Only)		
Center Contact	15 milliohms Maximum	
Outer Contact	10 milliohms Maximum	
Insertion Loss (Connectors Only)	.15dB Max. @ 6	GHz
Mechanical		
Connector Durability	100 mating cycles	
Tape/Reel Packaging (Plug)	12mm per EIA-481	
Force to Engage	5.5 lbs. Max. (3.5 lbs. typ.)	
Force to Disengage	(2.0 lbs. typ.) 4.0 lbs. Max. (2.0 lbs. typ.)	
Force to Disengage by Cable Load (camout)	300 Grams Min. (800 Grams typ. initial mate)	
Environmental		
Temperature Rating (Mated Pair)	-40°C (-40°F) to	→ +125°C (257°F)
Resistance to Solder Heat	Infrared, convection and vapor phase solderable (plug only). Maximum reflow time/temperature not to exceed 260°C for 3 minutes.	
Cable Specifications		
Materials		
Jacket:	FEP (polytetrafluoroethylene)	
Shield:	Silver plated copper wire, 44 AWG, 90% min. coverage	
Dielectric:	PTFE (polytetrafluoroethylene)	
Center Conductor:	Silver plated copper clad steel, 30 AWG	
Minimum Bend Radius	6.35mm (.250 inch)	
Insertion Loss (Cable Only)	0.5 dB/ft., 2.0 dB/m @ 1 GHz 0.9 dB/ft., 3.0 dB/m @ 2 GHz	
Center Conductor Resistance	.25 Ohms per foot average. 819 milliohm/meter Nom.; 250 milliohm/Ft. Nom.	




Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208





[.128] **Recommended Mounting Pattern for Microstrip Line**


1. Printed wiring board material: glass epoxy. FR-4 or similar, rela-tive permittivity: 4.8, 1 oz. copper

2. These dimensions valid for 1.6 [.062] board thickness.

Right-Angle Jack to Jack Cable Assembly

₹тусо

Electronics



Solder Mask

Notes:

1. Consult Tyco Electronics for non-standard cable lengths.

Length A Tolerances.		
Length A	Tolerance	
50 To 100 [3.94]	± 3 [± .12]	
101 To 500 [3.98 to 19.69]	± 5 [± .20]	
Over 500 [19.69]	± 10 [± .39]	

2. Connector centerlines align ± 30° as shown for lengths of 165 [6.5] or less. Cable assemblies over 165 [6.5] have randomly aligned connectors.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

214

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Right-Angle Jack to Jack Cable Assembly (180° Offset)

Electronics


₹тусо



Notes: 1. Consult Tyco Electronics for non-standard cable lengths. Cable length tolerance: Length A Tolerances. Length A $ext{Tolerance}$ 50 To 100 [3.94] \pm 3 [\pm .12] 101 To 500 [3.98 to 19.69] \pm 5 [\pm .20] Over 500 [19.69] \pm 10 [\pm .39] 2. To avoid damaging the cable, minimize time at temperature while soldering and/or applying heat to unterminated end of cable.

Right-Angle Jack Cable Pigtail

Assembly Length (A)	Part No.
100 [4.0]	1064535-1
200 [8.0]	1064538-1
305 [12.0]	1064540-1
510 [20.0]	1064542-1



Notes: 1. Consult Tyco Electronics for non-standard cable lengths. Cable length tolerance: Length A Tolerances. Length A Tolerance 50 To 100 [3.94] $\pm 3 [\pm .12]$ 101 To 500 [3.98 to 19.69] $\pm 5 [\pm .20]$ Over 500 [19.69] $\pm 10 [\pm .39]$ 2. To avoid damaging the cable, minimize time at temperature

To avoid damaging the cable, minimize time at temperature while soldering and/or applying heat to unterminated end of cable.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

UK: 44-8706-080-208

SSMT Surface Mount Interconnect System (Continued)

Inter-Series Cable Assemblies

SMA Straight Plug

SMA Bulkhead Jack


₹ Tyco Electronics



Notes: 1. Consult Tyco Electronics for non-standard cable lengths: Length A Tolerances. Length A Tolerance

Longin A	Torcranoc
50 To 100 (3.94)	± 3 (± .12)
101 To 500 (3.98 to 19.69)	± 5 (± .20)
Over 500 (19.69)	± 10 (± .39)

2. Connectors are randomly aligned unless otherwise noted.




Assembly Length (A)	Part No.
100 [4.0]	1064543-1
200 [8.0]	1064552-1
305 [12.0]	1064560-1

Note:

1064552-1 recommended for customer system verification.

E. 3.4 Ref. Length A [.132] Reference Plane to Centerline 21.3 Ref. 1.3 5.4 Dia. [.250] Min. ∠.1 [.081] Ref. [.839] [.052] Dia. Ref. Cable 6.0 **2.5** [.100] Dia. Ref. [.235] **7.9** [.312] Hex Min SSMT Right Angle Jack 3.2 Max. Panel Recommended Mounting Hole [.125] Thickness

Assembly Length (A)	Part No.
100 [4.0]	1064544-1
200 [8.0]	1064553-1
305 [12.0]	1064561-1



Assembly Length (A)	Part No.
100 [4.0]	1064546-1
200 [8.0]	1064555-1
305 [12.0]	1064563-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.


Catalog 1307191 I Revised 3-07 a www.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

SSMT Surface Mount Interconnect System (Continued)

Inter-Series Cable

Assemblies (Continued)



Note: The SSMT disengagement tool can be utilized as an optional engagement tool versus manual hand installation.

SSMT to SMA Between Series Adapters

SSMT Plug to SMA Jack Adapter

5.5 [.218] Across Flats SMA SSMT Plug Jack 10.5 [.413] Ref.



SSMT Plug to SMA Plug Adapter 13.7


Part No. 1055695-1

[.538]

Ref.



SSMT Jack to SMA Plug



Part No. 1055697-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

SMA

Jack

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

SMA

Plug

Dimensions are shown for reference purposes only. Specifications subject to change.

SSMT

Plug

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

217

SSMT

Jack

MMCX Microminiature Snap-On Connector Series


Product Facts

₹ Tyco

 Snap-on interface facilitates assembly

Electronics

- 35% smaller than MCX Series
- Designed for space saving applications up to 6 GHz
- Conforms to CECC Specifications
- Surface mount tape and reel for high volume




Tyco Electronics' microminiature snap-on connectors offer an excellent blend of size, durability and performance for emerging applications in GPS, PCS, automotive and wireless communications. An extension of the popular MCX series, MMCX connectors are 35% smaller, offering even greater packaging density and weight reduction. MMCX connectors are rated to 500 mating cycles. The snap-on interface facilitates assembly, eliminating the need for a threaded connection, and ensuring full engagement. The forces to engage and disengage have been optimized to ensure ease of mating as

well as to prevent damage to PCB solder connections. MMCX connectors are designed for broadband performance, DC-6 GHz, and can be utilized for future system upgrades without concerns for performance degradation. The non-slotted outer contact provides for minimal RF leakage. MMCX surface mount connectors are designed to withstand infrared reflow, convection and vapor phase soldering.

Tyco Electronics MMCX connectors are fully mateable with competitive MMCX product and conforms to the CECC interface specifications. They are available in a broad range of standard configurations, including PCB and panel mount, flexible and semi-rigid cable. Tape and reel packaging is available on surface mount product to facilitate high volume manufacturing. Other options can be reviewed as well, including additional cable sizes, and adapters.

The MMCX connector series is a cost effective solution for the challenging demands of today's commercial marketplace. It offers one of the smallest conventional crimp terminations without special tooling. Call your local sales office or authorized distributor for additional information or samples of the MMCX connector series.



Material and Finish

Shells — Brass Bodies — Brass, plated gold Center Contacts — (Male) — Brass, plated gold (Female) — Beryllium Copper, plated gold

Dielectrics — PTFE

Electrical Characteristics in accordance with CECC 22000

Frequency — dc – 6 GHz Nominal Impedance — 50 ohms Voltage Rating — 170 Volts (VRMS Max.) @ Sea Level VSWR — 1.25 : 1 Max. @ 6 GHz

Insulation Resistance — 1,000 Megohms Min.

Dielectric Withstanding Voltage – 500 Volts (VRMS Max.) @ Sea Level

RF Leakage — -60 dB Min. @ 2.5 GHz

Contact Resistance —

Center Contact — 5 milliohms max. Outer Contact — 1 milliohm max.

Mechanical Characteristics in accordance with CECC 22000

Connector Durability — 500 mating cycles

Force to Engage — 18 Newtons Max. Force to Disengage — 6 Newtons Max.

Center Contact Retention — 10 Newtons Min.

Cable Retention — Axial — 45 Newtons Min. Rotational — 0.05 N-m Min.

Environmental Characteristics in accordance with CECC 22000, Equivalent Test Conditions

Temperature Rating —

-55 to +155°C Vibration — MIL-STD-202, Method 204, Condition B

Shock — MIL-STD-202, Method 213, Condition A

Moisture Resistance —

MIL-STD-202, Method 106 Thermal Shock — MIL-STD-202,

Method 107, Condition B Note: Performance specifications are typical, but may not apply to all

are typical, but may not apply to all connector types.

Related Product Data

Product Specification — 108-2084 Sample Kit — 1654779

218


Catalog 1307191 Revised 3-07

www.tycoelectronics.com are s


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

MMCX Microminiature Snap-On Connector Series (Continued)


MMCX Interface Dimensions



Semi-Rigid Cable - Direct Solder Attachment **Straight Cable Plug**




Cable	Part No.
RG 405	1408313-1



Right-Angle Cable Plug


Cable	Part No.
RG 405	1408314-1


Flexible Cable – Crimp Attachment **Straight Cable Plugs**




[0.63]


Cable Part No. RG 178, 196 1408148-1







Right-Angle Cable Plug



Cable	Part No.
RG 178, 196	1408149-1
RG 174, 188, 316	1408149-2
RD 316	1408149-3

Captured Center Contact

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


MMCX Microminiature Snap-On Connector Series (Continued)

Printed Circuit Board Straight Jack Receptacle


Electronics


₹тусо







Right-Angle Jack Receptacle















Part No.
1408496-1





Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

MMCX Microminiature Snap-On Connector Series (Continued)

Edge Mount Straight Jack Receptacle



Straight Plug Receptacle



Solder Pad Configuration Only

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

₹тусо Electronics

UMCC — Ultraminiature Coax Connector and Cable Assembly Series

Product Facts

- Ultra low profile (2.0 mm or 2.5 mm maximum mated height)
- Easy snap on/off mating
- Small footprint on PCB (3 mm x 3 mm)
- Excellent performance to 6 GHz
- Surface mount and reflow solderable
- Available on 0.80 mm and 1.37 mm dia. single shield, and 1.32 mm dia. double shield cable
- Style A receptacles mate with HIROSE U.FL/U.FL(v) Series connectors
- Style B receptacles mate with MURATA GSC Series connectors



Description

- Extremely low profile
- Surface mount technology
- 360° mated rotation
- Excellent price-toperformance ratio

Applications

- Wireless LAN, Mini PCI
- Mobile Antenna/GPS/ Radio Systems
- PDA/PCS/Cellular Handset applications
- Wireless Communications systems (LAN, GSM, PCS, WCDMA, UMTS)
- Remote measuring equipment

Electrical Characteristics

Characteristic Impedance — 50 Ohms

Frequency Range — DC to 6 GHz VSWR (mated pair) —

1.30 max. DC to 3 GHz 1.40 max. 3 to 6 GHz (cable dependent) Insertion Loss (connectors only) -

0.24 dB max. DC to 6 GHz Rated Voltage —

60 VAC (rms) — standard receptacle (Styles A, B)

Dielectric Withstanding Voltage -200 VAC, 50 Hz for 1 min. @ sea level

Insulation Resistance -500 Megohms min.

Contact Resistance (connectors only) 20 milliohms max. (Center)

10 milliohms max. (Outer, Plug) 10 milliohms max. (Outer, Receptacle)

Mechanical and Environmental **Characteristics**

Durability — 30 cycles — standard receptacle (Styles A, B)

Disengagement Force —

2N min. perpendicular 4N min. orthogonal

Center Contact Retention Force — 0.15N min

Tape/Reel Packaging (receptacle) — 12 mm carrier per EIA-481

Operating Temperature — -40°C to +90°C

Material and Finish

Shell — Phosphor bronze, plated gold or silver

Male Center Contact — Brass or phosphor bronze, plated gold Female Center Contact — Brass or phosphor bronze, plated gold

Insulator (Plug) — PBT (15% G.F.), black, UL94V-0

Insulator (Receptacle) — LCP, beige or black, UL94V-0

Related Product Data

Product Specification — 108-2231 **Sample Kit** — 1-1773441-6

HIROSE is a trademark of Hirose Electric. MURATA is a trademark of Murata Electronics, Inc.

222

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Cable

UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)

Information	Material and Finish Center Conductor — 0.8 mm Dia. — Silver plated copper 1.32 mm Dia. — Silver plated copper	Shield Coverage — 0.8 mm Dia. — > 90% 1.32 mm Dia. — > 90% layer) 1.37 mm Dia. — > 90%
	1.37 mm Dia. — Silver plated copper Center Conductor Size — 0.8 mm Dia. — Stranded 7/0.05 mm 1.32 mm Dia. — Stranded 7/0.08 mm 1.37 mm Dia. — Stranded 7/0.10 mm	Jacket — 0.8 mm Dia. — FEP or 1.32 mm Dia. — FEP 1.37 mm Dia. — FEP
	Dielectric — 0.8 mm Dia. — FEP or PFA 1.32 mm Dia. — FEP 1.37 mm Dia. — FEP	Jacket Size — 0.8 mm Dia. — 0.80 m 1.32 mm Dia. — 1.32 r 1.37 mm Dia. — 1.37 r
	Dielectric Size — 0.8 mm Dia. — 0.4 mm OD 1.32 mm Dia. — 0.66 mm OD 1.37 mm Dia. — 0.83 mm OD	Mechanical Chara Minimum Bend Radi 0.8 mm Dia. — 5 mm s
	Shield — 0.8 mm Dia. — Silver plated copper braid 1.32 mm Dia. — Double SPL braid 1.37 mm Dia. — Silver plated copper	30 mm continuous fle 1.32 mm Dia. — 5 mm 30 mm continuous fle 1.37 mm Dia. — 5 mm 30 mm continuous fle

braid

- > 90% - > 90% (each braid

-> 90% FEP or PFA — FEP — FEP

0.80 mm 0D

– 1.32 mm OD - 1.37 mm OD

Characteristics

nd Radius -5 mm single bend, nuous flexing - 5 mm single bend,

nuous flexing – 5 mm single bend, 30 mm continuous flexing

Electrical Characteristics

Impedance (Ohms) -0.8 mm Dia. — 50 ± 2 1.32 mm Dia. — 50 ± 2 1.37 mm Dia. - 50 ± 2

Velocity of Propagation —


0.8 mm Dia. — 70% 1.32 mm Dia. — 70% 1.37 mm Dia. — 70%

CC Resistance (Ohms/KM) ----


0.8 mm Dia. — 1450 1.32 mm Dia. — 560 1.37 mm Dia. — 354

Voltage Rating — 0.8 mm Dia. — 60 VAC 1.32 mm Dia. — 60 VAC 1.37 mm Dia. — 60 VAC

Attenuation — See chart



UMCC Cable Attenuation



Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

₹ Tyco Electronics


UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)

PCB Receptacles — Style A



		H Max. Printed Circuit Board	Receptacle	
Style	Mates with UMCC Connector Type	Mated Height (H)	Description	Part Number
А	11 / 111	2.00–2.50 .079–.098	UMCC PCB Receptacle, 2500 Pc Reel	1566230-1
А	11 / 111	2.00–2.50 .079–.098	UMCC PCB Receptacle, 500 Pc Bag	1566230-2


UMCC PCB Receptacle



Recommended PC Board Layout


PCB Receptacles — Style B





Style	Mates with UMCC Connector Type	Mated Height (H)	Description	Part Number
В	I	2.00 .079	UMCC PCB Receptacle, 2500 Pc Reel	1775146-1
В	I	2.00 .079	UMCC PCB Receptacle, 500 Pc Bag	1775146-2

UMCC PCB Receptacle



Recommended PC Board Layout

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

224

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


RF Coax Connectors

UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)


Standard Double Ended Cable Assemblies

Tyco Electronics





UMCC Connector Type	Mated Height (H)	Cable Dia.	Length L	Mates with PCB Rcpt.	Part Number
	2.00 .079	0.80 .031	100.00 3.937	Style B	1750109-1
I	2.00 .079	0.80 .031	200.00 7.874	Style B	1750109-2
	2.00 .079	0.80 .031	100.00 3.937	Style A	1750108-1
II	2.00 .079	0.80 .031	200.00 7.874	Style A	1750108-2
	2.50 .098	0.80 .031	100.00 3.937	Style A	1750107-1
	2.50 .098	0.80 .031	200.00 7.874	Style A	1750107-2
	2.50 .098	1.32 .052	100.00 3.937	Style A	1750107-3
III	2.50 .098	1.32 .052	200.00 7.874	Style A	1750107-4
	2.50 .098	1.37 .054	100.00 3.937	Style A	1750107-5
	2.50 .098	1.37 .054	200.00 7.874	Style A	1750107-6



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)


Interseries Cable Assemblies



UMCC Connector Type	Mated Height (H)	Cable Dia.	Length	Description	Part Number
	2.50 .098	1.37 .054	200.00 7.874	UMCC Plug to FME Plug	1750110-2
	2.50 .098	1.37 .054	200.00 7.874	UMCC Plug to SMA Plug	1750110-4
Ш	2.50 .098	1.37 .054	200.00 7.874	UMCC Plug to SMA Bulkhead Jack	1750110-6
	2.50 .098	1.37 .054	200.00 7.874	UMCC Plug to MCX Right-Angle Plug	1750110-8
	2.50 .098	1.37 .054	200.00 7.874	UMCC Plug to MMCX Right-Angle Plug	1-1750110-0
	2.00 .079	0.80 .031	200.00 7.874	UMCC Plug to MCX Right-Angle Plug	1750110-7
II	2.00 .079	0.80 .031	200.00 7.874	UMCC Plug to MMCX Right-Angle Plug	1750110-9

UMCC to FME Plug





Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

226

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)

Adapters


UMCC Connector Type	Description	Part Number
I	UMCC Jack Receptacle to SMA Plug	1775228-1
	UMCC Plug to SMA Jack	1775229-1
/	UMCC Jack Receptacle to SMA Plug	1775227-1
	UMCC Plug to SMA Jack	1775230-1

5.6


[.220]




Part Number 1775228-1



Part Number 1775227-1




Part Number 1775229-1



Part Number 1775230-1

Extraction Tool Part Number 1775231-1



Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com are st

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

UK: 44-8706-080-208

UMCC — Ultraminiature Coax Connector and Cable Assembly Series (Continued)

2. To unmate the connectors,

insert the end portion of

the extraction tool under

the SMT receptacle con-

vertically in the direction

of the mating axis.


nector flanges and pull off

0.30

[.012]


Application Notes Mating/Unmating — **Cable Plugs**





Mating/Unmating

1. To mate the connectors, insert the cable plug into the SMT receptacle, making sure the cable plug is as vertical as possible and the mating axis of both connectors are aligned. Do not insert on an extreme angle.



Permissible Load

Do not apply excessive load to the cable after the connectors are mated. Please refer to the permissible loads indicated in the figure to the right.


1.40


[.055]

[.512]

Tape and Reel Packaging Specifications

Standard Receptacles





Dimensions Reel (2500 Pieces/Reel)


Soldering Profile — **SMT Receptacle**

Recommended Temperature Profile (Reference)

- 1. The preferred technique for mounting the SMT Receptacle package is to reflow solder the device onto a PCB (Printed Circuit Board).
- 2. The maximum temperature for the lead of PCB surface does not exceed 240°C.
- 3. The right reflow soldering profile is for reference and will modify under individual different conditions.

Hand Soldering (Reference only)

- 1. Soldering iron: The maximum temperature is 240°C.
- 2. Soldering period: within 5 seconds.



228

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

COAXICON Series Mobile Phone Switching Coax Connectors

Product Facts

- Able to switch RF signal from internal to external antenna
- SMD component for standard pick & place
- Up to 2.4 GHz
- Up to 30,000 life cycles
- High radial and axial tolerance capture
- Low insertion loss
- Right-angle cable plug with floating for alignment tolerance capture
- Application in handsets

Product Specification 108-71000

Technical Features Impedance — 50 Ohms Operating Temperature — -40°C to +85°C

Radial Tolerance Capture — ±1.0 [.039] (except for 3.5 [.138] height) Axial Tolerance Capture — 0.6 [.024] Plating — Outer shell and center contact are gold plated

Short Stamped Contact — Selective gold plating

Long Stamp Contact (switch) — Full gold plating with ink barrier Insertion Loss — 0.30 dB max. at 2 GHz

Isolation — 26 dB min. at 2 GHz **VSWR** — 1.15:1 at 1 GHz. below 1.20:1 at 2 GHz

Mated Insertion Loss (after life cycle testing) — Below 0.30 dB at 1 GHz, below 0.45 dB at 2 GHz

Unmated Insertion Loss (after life cycle testing) — Below 0.20 dB at 1 GHz, below 0.35 dB at 2 GHz Packaging on reels for SMD. For more details, refer to the product specification.



The Tyco Electronics SMD mobile phone connector system offers a low-cost and effective solution to passive switching between an internal and external phone antenna. When implemented in a cradle kit, the connector helps to make possible hands-free operation of the mobile

phone within a vehicle, enhancing safety and permitting compliance with a growing body of legislation. Connection to the external antenna also enhances signal gain and clarity.

The connector design accommodates gross misalignment between the

phone and cradle, which is extremely important when blindmating is necessary. The Tyco Electronics switching coax connector system meets all performance objectives, including up to 30,000 connect/disconnect and switching cycles over the connector's life.





Figure 1 — System Configuration





and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are in millimeters


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

COAXICON Series Mobile Phone Switching Coax Connectors (Continued)

Right-Angle Cable Plugs







Note: Hex Crimp Dim. 3.25 [.128]

RG/U			Dimensions	i		Single Packed	Bulk Packed
Cable	Α	D	F	L1	L2	Part No.	Part No.
	5x5 Square	3.4 .134	6.9 .272	15.6 .614	10.9 .429	619028-2	5-619028-2
	5x5 Square	3.4 .134	9.6 .378	15.6 .614	10.9 .429	619028-4	5-619028-4
RG 174	6.0 .236	3.4 .134	6.9 .272	15.8 .622	10.9 .429	619041-2	5-619041-2
nu 1/4	6.0 .236	3.4 .134	9.6 .378	15.8 .622	10.9 .429	619041-4	5-619041-4
	6.0 .236	3.4 .134	6.9 .272	20.3 .799	11.0 .433	619078-1	5-619078-3
	6.0 .236	3.4 .134	9.6 .378	20.3 .799	11.0 .433	619078-2	5-619078-4

SMD Switching Jacks







	Dimensions		Diameter Part No	
н	L	e	D	Part NO.
6.0	8.0	3.2	5.4	619061-1
.236	.315	.126	.213	
4.5	8.0	3.2	5.4	619062-1
.177	.315	.126	.213	
3.5	8.0	3.2	5.4	619072-1
.137	.315	.126	.213	

Other models upon request. For all dimensions, stencil and PCB recommended layout, see customer drawing.

*Dim. ℓ is the width of the connector on the PCB.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


RF Coax Connectors

COAXICON Series Mobile Phone Switching Coax Connectors (Continued)

Switching SMD Jack Low Profile

Part Number 619061-1, Part Number 619062-1, and Part Number 619072-1





Recommended PCB Layout

Plating	Dim. A	Part No.
Gold	6.00 ± 0.10 .236 ± .004	619061-1
Gold	4.50 ± 0.10 .177 ± .004	619062-1
Gold	3.50 ± 0.10 .138 ± .004	619072-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

UK: 44-8706-080-208


COAXICON Series Mobile Phone Switching Coax Connectors (Continued)


Switching SMD Jack ESD Protected Part Number 619133-3

₹ Tyco Electronics

Plating — Gold








Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

232

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803




COAXICON Series Mobile Phone Switching Coax Connectors (Continued)

*Mirrored Version of Part Number 619201-1 Also Available Under Part Number 619231-1

Switching SMD Jack Mid Part Number 619075-1

Plating — Gold



Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com a

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


RF Coax Connectors


COAXICON Series Mobile Phone Switching Coax Connectors (Continued)

Micro Switching Coax Connector Part Number 619196-1

Plating — Gold









Right-Angle Cable Plug For Micro Switching Coax Connector Cable RG 316/ RG 174

Part Number 619211-2

Plating — Gold










Nano Switching Coax Part Number 619213-1

Plating — Gold





0.45




Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

COAXICON Series Mobile Phone Switching Coax Connectors (Continued)




Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 **RF Coax Connectors**

COAXICON Series Mobile Phone Switching Coax Connectors (Continued)




Adapter SMA Jack — MSC Test Plug With Conical Flange Part Number 619210-1

Plating — Gold


₹ Тусо

Electronics



Adapter SMA Jack — NSC Test Plug With Two-Hole Flange Part Number 619214-1

Plating — Gold



Note: Part Numbers are RoHS compliant except: Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

236

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Quick Snap Stripline (QSL) Coaxial Connector

Coaxial Cable Displacement Interface

- Low profile
- Highly reliable ruggedized interface
- Surface mount technology
- Excellent price-toperformance ratio
- Platform expandable to include multi-port versions and other customization

Product Facts

- Surface mount compatible
- RoHS compliant (lead-free SMT process [260° C] compatible)
- PCI / PCI Express compatible
- Designed for RG 174 & RG 316 Cable, and easily adaptable to other cable types
- Overall Height < 10 mm
- Can be packaged to meet IP67 Sealing
- 10mm x 10.6mm max. footprint (w/o panel extension)
- Cost effective solution to standard screw machine RF connectors

Applications

- PCI, Mini PCI, PCI Express
- Mobile Antenna/GPS/Radio Systems/RFID
- PDA / PCS / Cellular Handset applications
- Wireless Communications systems
- Satellite Communications, Broadcast, Multimedia
- Automotive Telematics

Related Product Data

Product Specification — 108-2224


PCI, PCI EXPRESS are trademarks of PCI SIG.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208 237

-_____ [.394] --____ Max.



Surface Mount Jack Receptacle

Part Number	
1274794-1	



Cable Plug

Part Number	
1274795-1	

Specifications Characteristic Impedance — 50 Ohms Frequency Range — Dc to 6 GHz

VSWR — 1.3 Max to 3 GHz, 1.5 Max to 6 GHz Rated Voltage — 60 VAC rms Dielectric Withstanding Voltage — 800 VAC, 50 Hz (at sea level) Insulation Resistance — 100 Megohms min Operating Temperature — -40 to +125°C Engagement Force — < 30 N Disengagement Force — < 20 N

Cable Retention — 110 N Durability — 250 cycles





DIN Inserts

Product Facts

- Meets requirements of DIN 41626 and CECC 22330
- Suitable for DIN 41612 Type M Connectors (Eurocard), Siedecon, and Z-PACK 2mm HM Connectors
- Meets DIN Performance Level II
- Crimp termination for inner and outer conductors (cable mount only) eliminates the need for solder
- Right-angle and vertical style board mount pin and socket contacts
- Board mount product available with both solder and compliant tails
- Straight cable mount pin and socket contacts for RG 316, and RG 179 cable
- Contact impedance of 50 and 75 ohms for cable mount and 50 ohms for board mount

Coaxial inserts according to CECC 22 330 and highcurrent inserts (CECC specification under preparation) can be used in conjunction with a DIN 41612 style M contact base (CECC 75 101-801), SIEDECON, and Z-PACK 2mm HM connectors.

Coaxial inserts have a contact system based on the pin-socket principle with the same dimensions as the Series 1.0/2.3 coaxial connectors and are plug-compatible. The product family is represented by various 50Ω and 75Ω styles that can be used far into the GHz range. The high mounting density (pitch between adjacent contacts starting at 7.5 mm) and installation into the contact base, by means of a "snap-in" lock, make the inserts particularly well suited for applications.

Due to the centering,

- coaxial plugs are installed in contact bases with audio-frequency (AF) female contacts
- coaxial jacks are installed in contact bases with AF male contacts.

The high-quality materials used with coaxial inserts ensure a high grade of service even in an industrial atmosphere.

Technical Data

Electrical and mechanical characteristics of coaxial inserts in accordance with DIN 41626 Part 2 and CECC 22 330 Characteristic Impedance - 50/75 Ω

Frequency Range — up to 2 GHz Reflection Factor Up To 2 GHz 1 — ≤ 0.10

Insulation Resistance — Initial value — $\ge 1 \text{ G}\Omega$ After stressing — $\ge 200 \text{ M}\Omega$

 $\begin{array}{l} \mbox{Screening Effectiveness} \longrightarrow \geq 70 \mbox{ dB} \\ \mbox{Inner Conductor Contact Resistance} \\ \mbox{After Stressing} \longrightarrow \leq 10 \mbox{ m}\Omega \\ \mbox{Outer Conductor Continuity After} \\ \mbox{Stressing} \longrightarrow \leq 7.5 \mbox{ m}\Omega \end{array}$

Voltage Proof ² — Flexible Cables (RG 316) At sea level — 750 V, 50 Hz At 20 km altitude — 150 V, 50 Hz

Working Voltage ² — Flexible Cables (RG 316)

At sea level — 350 V, 50 Hz At 20 km altitude — 65 V, 50 Hz

Service Life — 500 cycles Climatic Category — 55/125/56

Notes

- 1 Guideline dimensions, depending on cable type and connector style.
- Some cable types suitable for use with these connectors have lower characteristic values than specified here.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803





RF Coax Connectors

DIN Inserts (Continued)




Vertical PC Board Mount, Compliant





Recommended PC Board Layout


Right-Angle PC Board Mount, Compliant




Туре	Housing Type	Application Tooling	Part No.
Vertical PCB Socket, Compliant	Z-PACK 2mm HM Male	904800-1	5148385-1
Rt. Angle PCB Pin, Compliant	Z-PACK 2mm HM Female	904805-1 904804-1 Support Anvil	5148386-1


Coaxial Inserts to SMA Adapters

Coaxial Insert Plug to SMA Jack





Coaxial Insert Socket to SMA Jack



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 239

DIN Inserts (Continued)

Coaxial Inserts (50 Ω /75 Ω)

Bulkhead Cable Jack for


male connectors



Ø Max.	Max. Cable Type Width Across Flats of Hex Profile		Part No.
2.6 .102	RG 316 (50 Ω)	3.2 .126	1392020-1
2.67 .105	RG 179 (75 Ω)	3.2 .126	3-1393668-4

Bulkhead Cable Jack for


female connectors



Ø Max.	Cable Type	Width Across Flats of Hex Profile	Part No.
2.6 .102	RG 316 (50 Ω)	3.2 .126	1392019-1
2.67 .105	RG 179 (75 Ω)	3.2 .126	3-1393668-0


Right-Angle Bulkhead Jack for

male connectors



Dim A	Ø Max.	Cable Type	Width Across Flats of Hex Profile	Part No.	
19	2.6 .102	RG 316 (50 Ω)	3.2	4 4000000 0	
.748	2.67 .105	RG 179 (75 Ω)	.126	1-1393668-2	
22.4 .882	2.67 .105	RG 179 (75 Ω)	3.2 .126	2-1393668-8	
24.0 .945	2.67 .105	RG 179 (75 Ω)	3.2 .126	3-1393668-6	

Right-Angle Bulkhead Plug for female connectors



Dim A	Ø Max.	Cable Type	Width Across Flats of Hex Profile	Part No.
18.7 .736	2.6 .102	RG 316 (50 Ω)	3.2 .126	1393668-4
22.3 .878	2.6 .102	RG 316 (50 Ω)	3.2 .126	1393668-8
18.7 .736	3.0 .118	RD 316 (50 Ω)	3.6 .142	1393668-7
18.7 .736	2.67 .105	RG 179 (75 Ω)	3.2 .126	2-1393668-4

240

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.


Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

female connectors


DIN Inserts (Continued)

Coaxial Inserts (50 Ω /75 Ω) (Continued)




Right-Angle Bulkhead Jack, PC Board for DIN 41612 M

male connectors




Part No.
1-1393662-4

Right-Angle Bulkhead Plug, PC Board for SIEDECON female connectors



Part No.	
1-1393662-2	



Recommended Mounting holes for Part No. 1-1393662-2 and 1-1393662-4

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

241

www.tycoelectronics.com

Size 8 Contacts

Performance Characteristics

Frequency Range — 0 to 500 MHz Operating Voltage, Max. — 275 vac rms @ sea level

Termination Resistance, Max. — Center Contact — 6.0 milliohms Outer Contact — 3.0 milliohms

Insulation Resistance, Min. — 5,000 megohms @ 500 vdc

Dielectric Withstanding Voltage — Sea Level — 800 Volts rms 30,000 ft [9,144 m] — 525 volts rms 70,000 ft [21,336m] — 275 volts rms

VSWR to 500MHz, Max.

Straight Contacts

Pin/Socket	VSWR
Straight/Straight	1.30
Right-Angle/Straight	1.35
Right-Angle/Right-Angle	1.40

RF Crosstalk — 90dB @ 5-500 MHz Mating Force, Max. — 4.0 lb [17.8 N] Unmating Force, Min. — 2.0 oz [0.556 N] Contact Retention — 20 lb [89 N] Contact Durability — 500 cycles

 Cable RG/U
 Force Ib

 316, 188, 174, 179, 179A, 179B
 20
 89

 188-type Double-Braid
 35
 155.8

 Double-Braid
 50
 222.5

Operating Temperature — 55°C to +125°C

Thermal Shock — 55°C to +125°C per MIL-STD-1344, Method 1003, Cond. A Physical Shock — 50 G's per MIL-STD-1344, Method 2004, Cond. A Vibration — MIL-STD-1344, Method 2005, Cond. II Moisture Resistance — 240 hours per MIL-STD-1344, Method 1002, Cond. II

Salt Fog — 48 hours per MIL-STD-1344, Method 1001, Cond. B


Extraction Tool Numbers Subminiature D Housings 58095-1 (AMPLIMITE) AMP-HDI Housings — 58095-2

Material

Brass — per QQ-B-626 and MIL-C-50 Phosphor Bronze — per QQ-B-750 Beryllium Copper — per QQ-C-530 TEFLON—per MIL-P-19468 Nylon—per MIL-M-20693

Finish

Bright Tin Plating — per ASTM-B-571 Copper Plating — per MIL-C-14550 Gold Plating — per MIL-G-45204 Nickel Plating — per QQ-N-290



RG/Cable	Shell	Dimen	Dimensions		50 (Dhm	Non-Impedance Matche	
nu/Gable	Туре	Α	В	Insert*	Pin	Socket	Pin	Socket
178, 178A 178B,196, 196A	Brass	24.13 .950	5.94 .234	59993-1	—	—	5228618-5	5228596-5
174, 316, 188, 188A	Brass	24.28 .956	5.94 .234	59993-1	5221980-1	—	5228618-1	5228596-1
179, 179A, 179B, 187, 187A, 161, BELDEN 9221	Brass	24.28 .956	5.94 .234	59993-1	_	_	5228618-2	5228596-2
174, 316, 188, Double Braid	Brass	24.28 .956	5.94 .234	59993-1	_	_	5228618-3	5228596-3
142, 142A, 142B, 400, BELDEN 9246	Brass	27.43 1.08	6.48 .255	58212-1	—	5221981-2	5228618-4	5228596-4

*For hand tool 69710-1 or pneumatic tool 69365-8.

Note: Non-Impedance Matched and 50 Ohm are not intermateable.

BELDEN is a trademark of Belden Wire and Cable Company. TEFLON is a trademark of E.I. Dupont de Nemours and Company.

242

Catalog 1307191 Dime Revised 3-07 and spec

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208


www.tycoelectronics.com


Size 8 Contacts (Continued)

PC Board Mount Contacts

Tyco Electronics

Right-Angle Socket Contact





Recommended PC Board Layout

Туре	Contact Part No. Non-Impedance Matched
Right-Angle Socket Contact	5221162-1

Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

COAXICON Contacts

Product Facts

- Tyco Electronics provides a variety of contacts for coaxial connectors
- Contacts are available in a range of sizes that may be used with the various types of coaxial cable on the market
- COAXICON contacts are of the crimp, snap-in type and are available in the following designs: Miniature Contacts, Subminiature Contacts and Size 8 Contacts

Miniature Contacts are designed for high density multiple circuit connector applications. A wide range of cable sizes is accommodated by using three sizes of outer shell termination ends and three sizes of contacts.

Subminiature Contacts

are used in high density applications and are ideal for mixing coaxial and other styles of pin and socket contacts in the same connector housing.

Size 8 Contacts are compatible with industry standard size 8 connectors such as Subminiature D and AMP-HDI connector housings. Straight and right-angle styles, as well as pc board versions for AMP-HDI connectors are available.



Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Miniature Contacts

Performance Characteristics

Insulation Resistance - 5000 megohms min

Dielectric Withstanding Voltage-1,000 volts rms for 1 minute

Contact Resistance — 2.0 milliohms @ 1 ampere

Low-Level Conductivity - 10 millivolts DC min.

VSWR - 1.3 to 1.0 @ 1,000 MHz max. Cable Retention -

RG/U Cable	Retention Ibs [N]
58C	50 [222]
188A	30 [133]
180B	28 [125]
195A	16 [71]

Durability - 500 cycles @ 10 cycles per minute max.

Vibration - 2 hrs. per MIL-STD-202, Method 201

Shock - 50 G's per MIL-Std-202, Method 213, Cond. G

Temperature Cycling — 5 cycles per MIL-STD-202, Method 102, Cond C.

Temperature Range — -55°C to +125°C


Test Method for Electronic and **Electrical Component Parts** -MIL-STD-202

Material

Outer Shell — Brass per MIL-C-50 Center Conductor — Brass per QQ-B-626, or Beryllium copper per QQ-C-533

Note:

A ferrule and retention spring (201142-2) are required for each pin and socket. Extraction Tool No. 305183-8



Inner Dielectric — Polypropylene, nylon, or polymethylpentene, general purpose Retention Spring — Stainless steel per QQ-S-766

Ferrule — Copper per QQ-C-576


Finish

Outer Shell, Center Conductor —

0.00076 [.000030] gold over 0.00076 [.000030] nickel

Retention Spring --- Nickel per QQ-N-290

Ferrule — Bright tin per MIL-T-10727



Die Insert for Tools:

	Ferrule	Integral Die	PRO-CRIMPER	Die Insert for Tools: Hand Tool 69710-1	Part Nu	imbers
RG/U Cable	No.	Hand Tool	PRU-GRIMPER	Pneu. 69365-2, 69365-3 ²	Pin	Socket
316, 188, 188A 174	328666	_	_	69227-2	201143-5	201144-5
179, 179A, 179B 161, 187, 187A Belden 9221	328666	_	_	69227-2	201143-1	201144-1
188 Double Braid 316 Double Braid	221848-3	58290-1	_	69227-2	201143-5	201144-5
122	328664	45639-2	91912-3	69222-2	201145-1	
180, 180A, 180B 195, 195A, 21-597	328664	45639-2	91912-3	69222-2	201145-2	201146-2
Belden 8218	328664	45639-2	91912-3	69222-2	201145-2	201146-2
58, 58A, 58B, 58C	328663	45740-2	_	69220-2	201145-4	201146-4
141 55, 55A, 55B, 223	330478	69248-4	_	69315-4	201145-4	201146-4
124, 140, 210 62, 62A, 62B 59, 59A, 59B	329006	_	_	69675-1	201097-1*	201098-1*
Twisted Pair						
24-22 AWG [0.2-0.4 mm ²] (Stranded) ¹	328666	91912-4	_	69672	201143-5	201144-5
Shielded Wire 22, NAS-702, Class B	328663	45740-2	—	69220-2	201145-4	201146-4
Brand Rex T5788A 26 AWG [0.12-0.155 mm ²] ³	328664	45639-2	91912-3	69222-2	201145-2	201146-2

*These contacts are for use in the 4-position G Series connector modules only.

¹Maximum insulation diameter-2.92 [.115] (two wires combined).

²Includes bench mount and foot control; requires Manual Take-Up Attachment No. 69689.

³Dielectric O.D.-2.69 [.106] max.; Cable O.D.-4.06 [.160].

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

UK: 44-8706-080-208

RF Coax Connectors

Miniature PC Board Sockets

Material

₹тусо

Shell and Center Contact — Brass per MIL-C-50 and QQ-B-626 Dielectric — Polypropylene, or Polymethylpentene, general purpose

Electronics


Finish


Center Contact — 0.00076 [.000030] gold over copper Shell — Gold plated per MIL-G-45204

Performance Characteristics


Dielectric Withstanding Voltage— 1,000 volts, rms

Impedance — Non-constant Operating Temperature Range — -55°C to +85°C





Recommended Mounting Hole Layout



Turne	PC Board	Retention		Dime	nsions	Part No.	
Туре	Thickness	lb.	[N]	Α	В	Part No.	
Spring Latch	1.57 .062	1.25	5.56	9.07 .357	3.18 .125	50084-1	
Spring Latch	3.18 .125	1.25	5.56	7.49 .295	4.75 .187	50095-1	
Locking Latch	3.18 .125	7	31.1	7.49 .295	4.75 .187	50105-1	
Locking Latch	1.57 .062	7	31.1	9.07 .357	3.18 .125	50107-1	

Note: For mateable Miniature Contacts, see page 245.

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

Catalog 1307191 Dir Revised 3-07 an sp www.tycoelectronics.com are

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax Connectors

Subminiature PC Board Sockets

Material

₹_{Тусо}

Shell and Center Contact — Brass per MIL-C-50 and QQ-B-626 Dielectric — Polypropylene, or polymethylpentene, general purpose

Electronics


Finish

Center Contact — 0.00076[.000030] gold per MIL-G-45204 over copper per MIL-C-14550 Shell — Gold


Performance Characteristics


Dielectric Withstanding Voltage 600 volts, rms

Operating Temperature Range — -55°C to +85°C



Recommended Mounting Hole Layout





Туре	PC Board Thickness	Dim. L	Part No.
Spring Latch	1.57 .062	2.54 .100	226023-1
Locking Latch	1.57 .062	2.54	226060-1

Mating Subminiature COAXICON Pins

These short Subminiature COAXICON Pins are recommended for use with any of the sockets listed above.

Note: Alignment springs are not required for this application and are not included with the pin assemblies.



RG/U Cable	Ferrule No.	Integral Die Hand Tool	Die Insert for Tools: Hand Tool 69710-1 Pneu. 69365-2, 69365-3	Part No.
174 316, 188, 188A	1-332056-0	91911-3	69690	51563-8
179, 179A, 179B 187, 187A	1-332056-0	91911-4	69690-1	51563-8
161	1-332056-0	69656-5	_	51563-8

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Subminiature Contacts

Material

₹тусо

Outer Shell — Brass per MIL-C-50 Center Conductor — Beryllium copper per QQ-C-533 (Pin); Brass per QQ-B-626 (Socket)

Electronics

Inner Dielectric — Polypropylene, nylon, or polymethylpentene, general purpose


Retention Spring — Stainless steel per QQ-S-766

Ferrule — Copper per QQ-C-576

Finish

Outer Shell and Socket Center Conductor — 0.00076 [.000030] gold over 0.00127 [.000050] nickel

Pin Center Conductor — 0.00076 [.000030] gold over 0.00254 [.000100] copper Ferrule — Bright tin per MIL-T-10727



A = Multimate Pin 25.65 [1.010] Short Pin 22.66 [.892]

Selection Chart for Coaxial Cable

	Integral		Die Insert for Tools: Hand Tool 69710-1		Contact Part Numbers			
RG/U Cable	Die Hand Tool	PRO-CRIMPER	Pneu. Tool 69365-2, 69365-3*	Multimate Pin	Short Pin	Socket	ket Ferrule i5-2 1-332057-0 i5-2 225088-1 i5-1 1-332056-0 i5-1 1-332056-0 i5-1 225088-3 i5-1 225088-1	
178, 178A, 178B 196, 196A	69656-2		69690-2	226537-2	_	51565-2	1-332057-0	
196 (Double Braid)	69656-9		_	226537-2	_	51565-2	225088-1	
174, 316 188, 188A	—	91911-3	69690	226537-1	—	51565-1	1-332056-0	
179, 179A, 179B 187, 187A Belden 9221	_	911911-4	69690-1	226537-1	_	51565-1	1-332056-0	
RD-316	69656-7		_	226537-1	_	51565-1	225088-3	
187 (Double Braid)	69656-8		_	226537-1		51565-1	225088-	
161	69656-5		_	226537-1	_	51565-1	1-332056-0	

Selection Chart for Twisted Pairs and Shielded Wire

Wire Size		Integral Die		Die Insert for Tools: Hand Tool	Contact Part Numbers				
AWG	[mm ²]	Integral Die Hand Tool	PRO-CRIMPER	69710-1 Pneu. Tool 69365-2, 69365-3*	Multimate Pin	Short Pin	Socket	Ferrule	
30 (Twisted Pair, Solid)	0.05	69656-2	_	69690-2	226537-3	51563-3	51565-3	1-332057-0	
28 (Twisted Pair, Solid)	0.08-0.09		91911-3	69690	226537-3	51563-3	51565-3	1-332057-0	
28 (Twisted Pair, Stranded; 7 str., .005 [0.13] Dia.)	0.08-0.09	_	91911-4	69690-1 or 69690-2	226537-3	51563-3	51565-3	1-332057-0	
26 (Twisted Pair, Solid or Stranded; 7 str., .0063 [0.16] Dia.)	0.12-0.15	_	91911-3	69690	226537-3	51563-3	51565-3	1-332057-0	
26 (Shielded, 0.75 [1.91] Max. 0.D.)	0.12-0.15	69656-3	_	69690-3	226537-1	_	51565-1	1-332057-0	

*Includes bench mount and foot control.

Extraction Tool 305183

Note: A ferrule is required for each pin and socket.

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SIEMAX Connectors

Applications

₹тусо

- Multiplex Systems
- Base Stations
- High Density Systems


Electronics

Product Facts

- Multi Coax Surface Mount
- Maximum packaging density
- Component placement on both sides of PCB
- Fully automated assembly (pick-and-place)
- Modular design

Technical Data

- Interface: Series 1.0/2.3
- Impedance: 75 Ω
- International specifications: IEC 169-29 and CECC 22 230
- Frequency range up to 2 GHz
- Compact grid pitch 10 [0.39]
- Guaranteed coplanarity of max. 0.1 [0.004]
- Integrated positioning pins for manual placement
- Optional mechanical securing




SIEMAX connectors combine the benefits of surface mount technology and modular design. This multi coax connector is packaged in tape-and-reel for automatic placement, has optimum solder joints and 100% reflow suitability. This connector is ideal for systems requiring superior packaging density because it can be placed on both sides of the printed circuit board.

The modular design provides flexibility in terms of the number of poles offered (two- or three-poles). It can be stacked, enabling any required configuration to be produced. The SIEMAX connector also allows the use of any other connector series, e.g. SMB, is resistant to high temperatures, and is robust, with reliably sustained coplanarity.

For General Information on Series 1.0/2.3 Connectors, see Page 129.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

SIEMAX Connectors, Series 1.0/2.3 (75 Ohm)



www.tycoelectronics.com

Revised 3-07

and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Between Series Adapters

Between Series Coaxial Transmission Line Adapters provide convenient transitions between popular series coaxial connectors. The adapter design provides a minimum length consistent with good electrical performance. The small size, low VSWR, and broad frequency coverage permits a wide range of applications in both measurement and systems use.

Design and Construction

The standard units are constructed of stainless steel with passivated finish, nickel plated brass, and gold plated brass. The material and plating is to be consistent with the basic connector series. All dielectrics are TFE fluorocarbon. The center contacts are made of beryllium copper, gold plated.

Types

The straight in-line adapters are available in many combinations of plug and jack (male and female) configurations. Also, popular panel mount versions are cataloged. For special modifications and hermetic seal version, consult Tyco Electronics.

Application

The major application is the requirement for a low VSWR, compact transition in both test system and operating systems. Many panel mount and bulkhead mount versions are available so the designer can use small size connectors for internal design, but adapt to a larger rugged version for external connection.

Selection charts follow to help you find the correct adapter for your application.

Plug-Plug

	N Series	OSP	OSP Bulkhead	BNC	7-16	SMB	SMA	SMP	SSMT	Series 1.0/2.3	QMA
MCX							Page 253				
N Series					Page 253						
BNC						Page 253					
Series 1.6/5.6				Page 253						Page 253	
SMA/SMA 18 GHz	Page 253	Page 253	Page 253			Page 253		Page 253	Page 253		Page 253

Jack-Jack

	MCX	N Series N Series Flange Mount N Series Bulkhead	OSP OSP Bulkhead OSP Floating Rear Mount	BNC BNC Bulkhead	TNC TNC Flange Mount TNC Bulkhead	7-16	SMB 75 OHM SMB	SMP	SSMT	Series 1.0/2.3	Series 1.6/5.6
N Series						Page 254					
BNC							Page 254				Page 256
TNC		Page 254		Page 254							
SMA SMA Bulkhead SMA 18 GHz	Page 254	Page 254 and 255	Page 255 and 256	Page 254	Page 254 and 255		Page 255	Page 255	Page 255		
Series 1.0/2.3											Page 256

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

Between Series Adapters (Continued)


Jack-Plug

	7 mm	7 mm best VSWR	MCX	N Series N Series Flange Mount	OSP OSP Bulkhead	BNC	TNC	SMB	SMA SMA Flange Mount SMA 18 GHz	SMP	SSMT	DIN-Series 1.0/2.3	DIN-Series 1.6/5.6	UMCC
7 mm				Page 256	Page 256		Page 256		Page 256					
7 mm best VSWR				Page 256			Page 256							
MCX									Page 256					
N Series N Series Flange Mount	Page 256	Page 257				Page 257	Page 257		Page 257					
OSP OSP Bulkhead	Page 257								Page 257					
BNC				Page 257				Page 257	Page 257				Page 259	
TNC TNC Flange Mount	Page 258	Page 258		Page 258					Page 258					
SMB 75 OHM SMB				Page 259					Page 258					
SMA SMA Flange Mount SMA 18 GHz	Page 259		Page 258	Page 258 and 259	Page 260	Page 258	Page 259	Page 259		Page 259	Page 259			Page 259
SMP									Page 260					
SSMT									Page 260					
DIN-Series 1.0/2.3													Page 260	
DIN-Series 1.6/5.6						Page 259						Page 260		
QMA									Page 260					
UMCC									Page 260					

252

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Plug-Plug



Note: Part Numbers are RoHS compliant except:
Indicates non-RoHS compliant.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Jack



Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.


Catalog 1307191 Revised 3-07 www.tycoelectronics.com

254

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Jack (Continued)


₹тусо



www.tycoelectronics.com a


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Jack (Continued)




Part No. 1061742-1

SMA Flange Mount Plug to 7 mm Jack




Part No. 1061751-1


TNC Plug to 7 mm Best VSWR Jack



Part No. 1061744-1




SMA Plug to 7 mm Jack




Part No. 1053646-1

MCX Jack - SMA Plug




Part No. 1061073-1

TNC Plug to 7 mm Jack




Part No. 1061739-1

N Series Plug to 7 mm Best VSWR Jack



Part No. 1061738-1

N Series Jack – 7 mm Plug



Part No. 1061757-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

256

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Plug (Continued)

Electronics


₹тусо



Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.


Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Plug (Continued)




Part No. 1061753-1

TNC Flange Mount Jack - SMA Plug



Part No. 1057857-1

SMA 18 GHz Jack - N Series Plug




Part No. 1057377-1

SMA Jack - SMB Plug



Part No. 1060498-1

TNC Jack – 7 mm Best VSWR Plug



Part No. 1061758-1

SMA Plug - SMB Jack

20.7 [.815] Ref. 7.9 Hex. [.312] Hex.

Part No. 1060500-1

SMA Jack – BNC Plug



Part No. 1058081-1


SMA Jack – SMP Plug



Part No. 1056707-1

Note: Part Numbers are RoHS compliant except: ♦ Indicates non-RoHS compliant.

TNC Jack - N Series Plug



Part No. 1057387-1

SMA Jack - MCX Plug



Part No. 1061072-1

TNC Plug - SMA Jack



Part No. 1057853-1

SMA Jack - SSMT Plug




Part No. 1055696-1

258

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Plug (Continued)




www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Jack-Plug (Continued)

Series Plug 1.0/2.3 - Series 1.6/5.6 Jack




Part No. 2-1393670-3 ♦ Coupling Type A, B², F²

1) Detent for jack


2 Only jackside

QMA Jack - SMA Plug




Part No. 1408343-1

UMCC Jack - SMA Plug



Part No. 1775228-1

UMCC Jack - SMA Plug



Part No. 1775227-1

Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

260

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


RF Coax Connectors

Coaxial Terminations

SMA Plug Terminator Part Number 1460802

Plating — Gold Frequency — 6 GHz






SMC Plug Terminator Part Number 1460803

Plating — Gold Frequency — 6 GHz








Push Pull Plug Terminator Part Number 619219

Plating — Gold Frequency — 6 GHz



QMA Plug Terminator

Part Number 619271-1 Single Packaging


Plating — Standard Gold Part Number 5-619271-1

1000 Pieces per Pack
Plating — Standard Gold

Part Number 619271-2 Single Packaging Plating — Higher Gold

Part Number 5-619271-2 1000 Pieces per Pack Plating — Higher Gold





Note: Part Numbers are RoHS compliant except:
 Indicates non-RoHS compliant.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com are

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Application Tooling

Installation Kit Part No. 1055469-1 For TNC Connectors

₹ Tyco Electronics



Fixture Sub-Assembly

For installation of TNC Series connectors to 3.66 [.141] and 2.16 [.085] diameter semirigid cable. Most BNC Series connectors can also be assembled using this kit. See appropriate assembly procedure for specific tooling. This kit contains:


Description	Model No.	NSN	Part No.
Center Contact Holder	T-4580		1055474-1
Fixture Sub-Assembly	T-4567		1055439-1
Inserts – 2.16 [.085] (2)	T-4700-2	5120-00-132-6808	1055441-1
Inserts - 3.66 [.141] (2)	T-4700-1	5120-00-132-6807	1055440-1
Locator Tool	T-4596		1055476-1
Locator Tool	T-4574		1055477-1
Solder Gage .813 [.032]	T-4562-6		1055475-1

All Tools May Be Purchased Separately.

262

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Universal Compression Crimp Tool

Kit Part Number 1055835-1

Tyco Electronics Universal **Compression Crimp Tool** offers the ability to rapidly produce cable assemblies using solderless compression crimp connectors with semi-rigid cables. This universal assembly tool kit will attach SMA, OSP, N and TNC series connectors to 3.58 [.141], 2.16 [.085] and 6.35 [.250] cable quickly and consistently with excellent mechanical and electrical results.

The tool kit permits single hand assembly. Anvils and cable supports can be quickly changed. Crimp lengths can be adjusted from .025 [.001] to 25.4 [1.000] in increments of .025 [.001]. Sharp radius bends in cables are easily accommodated. The kit contains:



Description	Part No.
Crimp Frame	1055831-1
Calibration Gauge	1055832-1
3.58 [.141] Cable Support	1055833-1
2.16 [.085] Cable Support	1055834-1
SMA Plug Anvil	1055836-1
SMA Jack Anvil	1055837-1
Type N Plug Anvil	1055838-1
Type N Jack Anvil	1055839-1
TNC Plug Anvil	1055840-1
TNC Jack Anvil	1055841-1
OSP Plug Anvil	1055842-1
OSP Jack Anvil	1055843-1

All tools may be purchased separately.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹тусо Electronics

Application Tooling (Continued)


Crimping Tools

Crimping tools are used for assembling coaxial connectors on coaxial cables. They can be applied particularly economically for small batch sizes.

The crimping dies are a fixed part of the crimping tools. Each tool is equipped with 2 or 3 different profiles. A total of 6 widths across flats are possible with 2 tools, whose hand lengths are adapted to the dimensions of the hexagon profiles. The tools can be distinguished at a glance by different colored handles.




Item	Width Across Flats of the Profile		ross Flats of the Profile Dim.		Color of	Part No.
	1	2	3	L	handles	Part NO.
Crimping Tool	2.8 0.11	3.2 0.13	3.6 0.14	214.0 8.43	Green	1393524-4
Crimping Tool	2.8 0.11	5.4 0.21	4.5 0.18	260.0 10.24	Yellow	1393524-5



IDC Tool


For assembling IDC coaxial connectors Series 1.6/5.6 mS on coaxial cables.



Part No.
1-1393524-1

Removal Tool

For replacing the special contacts on connectors DIN 41612 M and SIEDECON.



264

Catalog 1307191 Revised 3-07

and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are in millimeters

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Setting Gauge

₹тусо

Protective Caps/Setting Gauges


Electronics

The setting gauges are used to position coaxial jacks and pre-mating high-current plugs on male connectors DIN 41612 M if the pins are flow-soldered into PC boards.

The gauges are held by clamping in connector body and protect the blade contacts.

The gauges provide protection

- during transport (if the male connectors have already been removed from the packaging),
- during assembly,
- against soiling,
- during soldering.



Item Part No. 1393494-9 Setting gauge for types Μ M/2 1-1393494-0 M/3 1-1393494-1

Note: These gauges can also be used to protect types C, C/2, C/3 and D.


Wrench

Ø 6.1

[0.24]

Ø 7.3

1.2 [0.05]



50.0

[1.97]



1.5 [0.06]

Used to tighten the threaded ring on bulkhead jacks Series 1.0/2.3


Item	Part No.
Wrench	1393488-3

Used to tighten the threaded ring on bulkhead jack 1393670-8.

Item	Part No.
Wrench	1393488-4

Used to tighten the threaded rings 1-1393562-0 on bulkhead jacks Series 1.6/5.6.

Part No.
393524-1



Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Hand Tools

₹ Tyco

Electronics

Tyco Electronics PRO-CRIMPER II Hand Tools are economy versions of our Tyco Electronics CERTI-CRIMP Hand Tools, featuring ratcheted crimp control to provide full die closure and help eliminate partial crimps. With an all new design, the PRO-CRIMPER II hand tools require dramatically less hand force to produce the same connection as comparable tools. Dies are interchangeable. It's the most versatile and reliable crimping tool in the mid-price class. Recommended for networking installations, and commercial, industrial and institutional maintenance work. See Catalog 82276 for further information.

Typical PRO-CRIMPER III Hand Tool



No. 58433-1 for 50 Ohm BNC Dual "O" Crimp Commercial Connectors

Tyco Electronics CERTI-CRIMP Hand Tools are our top-ofthe-line crimping tools featuring the original ratcheted crimp control. All tools are designed to exacting specifications, and manufactured using the highest quality materials to provide long service life. Recommended for low production runs, repairs and prototype work, and applications requiring consistent, highly-reliable terminations. See Catalog 65780 for further information.

Typical CERTI-CRIMP Hand Tools with Integral (Non-Interchangeable) Dies



No. 69477-1 for 50 Ohm BNC Dual Crimp MIL Type Connectors

No. 220015-1 for 50 Ohm N Connectors

CERTI-CRIMP Hand Tool with Interchangeable Dies



No. 69710

Pneumatic Tools

The 626 Pneumatic Tool System, as the name implies, will apply a broad range of products in the 6-26 AWG [13-0.12 mm²] wire range. A basic 626 Pneumatic Tool System requires a power unit, a tool holder, a crimp head assembly and a die set when applicable. This premium system is well suited for low- to medium- volume production and harness assembly operations. Since the crimp head can be rotated to any angle, the operator can also work on more difficult terminations in confined equipment cabinets or enclosures.

Interchangeable tool holder assemblies and crimping heads are available to crimp a variety of products. Crimping heads for the earlier Model 2614 pneumatic power unit can be used with the 626 Pneumatic Tool System. If you are already using Tyco Electronics hand tools, many crimp heads and die sets can be removed, attached to an adapter with quick

pins and used with the 626 Pneumatic Tool System. An adapter is even available to accept lower cost die sets of the PRO-CRIMPER II hand tool. For more information, order catalog 124208



Fully adjustable stand allows operator free use of both hands — recommended for maximum productivity.

Battery Powered Crimp Tool

Take automatic crimping away from the bench to the product, with this convenient, portable, battery-operated tool. It's at home in the factory or in the field.

- Completely portableperforms about 100 crimps per charge
- Terminates wires to 10 AWG [6 mm²]
- Weighs only 1.57 kg [3.46 lb] including battery; 360 mm [14.2 in] long
- Pressure-sensitive cycle control
- Kit includes tool, 2 batteries, and charger

No. 856402-1

No. 189721-1



Part Number 1725837-1 Part Number 1213890-1 (Open Barrel)

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Bench-Mounted Machines

AMP-O-LECTRIC bench-mounted, semi-automatic terminating machines may be used to apply RF products such as Commercial BNC and TNC Connectors, Miniature and Standard UHF Connectors, and Braid-Pic Contacts and Terminals. The Model G unit features interchangeable applicators, and is used to apply strip-form contacts. The "Coax" unit is used to apply loose-piece contacts and ferrules with dies that are mounted onto the machine. See Catalog 65828 and Customer Manual 409-2627 for further information.



AMP-O-LECTRIC Model G, No. 354500 Series with Tyco Electronics Crimp Quality Monitor

Stripping Tools

The hand-operated Tyco Electronics Coaxial Cable Stripper features interchangeable, color-coded blade cassettes and V-blocks to accommodate 2- or 3-step stripping for cable diameters ranging from 2.54 [.10] through 7.62 [.30]. You strip cable by simply clamping and rotating the tool around the cable. See Instruction Sheet IS 2766 for further information.



For Use With Connector Type	Tool No.
BNC Single Crimp	603995-1
BNC Commercial and UHF Miniature	603995-2
UHF Standard	603995-3
BNC MIL Type Dual Crimp	603995-5
BNC Commercial Dual Crimp	603995-6

Semi-Rigid Cable Tooling

The tools listed here are designed specifically to strip and terminate semi-rigid cable. These tools operate basically the same as the flexible cable tools, in that they produce uniform terminations time after time, without heat damage from soldering.

Hand Tool for BNC and TNC Semi-Rigid Cable Connectors

> No. 59980-1 Frame only does not include dies and locator

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Hand Tool Kit for SMA and Blindmate Connectors No. 59981-1

₹ Tyco Electronics



Pneumatic Tool for Terminating BNC, TNC, SMA and Blindmate Connectors (for RG 402/U and RG 405/U Cable)

No. 58318-1*



This pneumatic tool is a bench-mounted, semi-automatic power tool designed for easy operation. The operator needs only to depress the trigger to complete a termination. It is used with the cable preparation machine to produce finished terminations.

*Includes Locators 220241-1 and 308075-2. Dies are not included.

	Part Numbers		
Item Description	Tyco Electronics	Military (M22520/)	
Hand Tool	59980-1	36-01	
Plug Locator (without Center Contact)	220220-2	36-06	
Plug Locator (with Center Contact)	220221-2	36-04	
Jack Locator	220222-2	36-05	
Die Set for RG 402/U Cable (3.58 [.141] O.D.)	312253-1	36-03	
Die Set for RG 405/U Cable (2.18 [.086] O.D.)	312253-2	36-02	
Cutoff Fixture	311395-1	36-09	
Cable Dressing Fixture	311396-1	36-07	
Trimmer Tool	312317-1	36-08	
Cable Bend Fixture Assembly Includes following 6 items:	220224-1	36-10	
Bend Segment, RG 402/U (3.18 [.125] Radius)	311386-1	36-11	
Bend Segment, RG 402/U (6.35 [.250] Radius)	311386-2	36-12	
Bend Segment, RG 405/U	311386-3	36-13	
Tool Holder	311392-1	—	
Limiting Pin	307581-1	_	
Conforming Block	312067-1	_	
Hex Wrench	21027-6		
Carrying Case	13126-1		
Insert, Case	13127-1	_	

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Electronics

Cable Assembly Capabilities




When your RF application demands a high performance cable assembly, make Tyco Electronics your advantage. We specialize in solving tough problems with assemblies designed and manufactured to the most demanding requirements. Why Tyco Electronics? Quite simply, because we can give you a comprehensive engineered solution to your application needs. By providing a precise match between cable, connector and application, we supply cable assemblies that meet your exact needs.

Every cable assembly application is unique.

A Tyco Electronics custom solution can be designed to meet your special requirements — whether these are related to return and insertion loss, propagation delay and phase matching, shielding and EMI, or special mechanical issues like density, latching, appearance, flexibility, or even weight. We approach your cable assembly individually, using the vast resources and knowledge gained from years of experience generating custom solutions. By making Tyco Electronics your partner in cable assembly design, you reduce risk and gain the assurance that you will receive assembly on time,

to specification and within your budget.

Tyco Electronics offers a wide range of RF/Coax Cable assemblies including 50 and 75 Ohm solutions. from micro-miniature UMCC and SSMT to high power assemblies using N-Series and DIN 7/16 connectors. Furthermore, we use a variety of cable types to meet unique requirements from standard military qualified RG cable to low loss foamed PE and PTFE tape wrapped cable as well as semi-rigid. Our engineering experts will find the right combination of materials to provide a solution that is cost effective.



Catalog 1307191 Revised 3-07

www.tycoelectronics.com are st

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Cable Assembly Capabilities (Continued)



Utilizing network analyzers, TDR, and intermodulation test equipment to mention a few, our testing capability allows extensive electrical and environmental characterization of your assembly. We offer full test capabilities right in our manufacturing facilities. Tests such as those listed below can be an integral part of the manufacturing process:

- VSWR,
- Return Loss,
- Insertion Loss.
- Phase matching,
- Propagation Delay,
- Impedance,
- Passive Intermodulation.

Our cable manufacturing centers are designed to meet your production requirements and delivery needs. Our global locations, combined with Tyco Electronics logistic strengths assures you will get the product where and when you need it.


32/03

Norwood, MA

Product Development Screw Machining Plating Connector and Cable

Ooskampt, Belgium

Product Management Product Development Screw Machining Plating Switzerland Development Eng. Screw Machining Assembly



270

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Harrisburg, PA


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



RF Coax Connectors

Coaxial Cable Assembly Specification Guide

Please use this handy reference guide when specifying or building your new cable assembly.



CONNECTOR A	CONNECTOR B	
INTERFACE	INTERFACE	
STYLEexample: Straight Plug, Right-Angle Plug, Bulkhead Jack, etc.	STYLEexample: Straight Plug, Right-Angle Plug, Bulkhead Jack, etc.	
HEAT SHRINK	HEAT SHRINK	
MARKING	MARKING	
CABLE		
LENGTH (inch/mm)		
RG TYPE	MARKING	
OR		
CABLE MFG		
MFG. PART NO		
OR	ELECTRICAL SPECIFICATIONS	
FREQUENCY RANGE (MHz/GHz)	VSWR	
	OR RETURN LOSS	
INSERTION LOSSdB	INSERTION LOSS	
SHIELDING EFFECTIVENESS dB	DELAY	
TEMP. RANGE (°C/°F)	INSERTION PHASE	
MAX. AVG. POWER HANDLING* Watt * 25°C at sea level and max. specified frequency		
OTHER SPECIFICATIONS		

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix A - Theory and Application

Theory and Application

Electronics

Tvco

As a leading manufacturer of RF products, Tyco Electronics produces a large variety of coaxial connectors. The proper selection and application of these connectors requires a knowledge of factors not involved in other types of connectors and terminals. The following paragraphs have been prepared to improve understanding of the theory behind RF connectors:

Basic RF Theory1

RF energy travels by electromagnetic waves, and it is primarily the frequency of these waves that we are interested in. Briefly, if an oscillating voltage source is connected to a cable, a continuous electromagnetic wave will propagate along the cable. A sensor placed at some point on the cable would indicate a varying voltage (E field) as well as a current and magnetic field (H field) as the wave travels past it. This is called an electromagnetic wave because both electric and magnetic fields are varying. The wave shape is initially determined by the variation of the source with time.

Figure 7 shows the radiant energy spectrum. Visible light, radio, television, x-rays and Gamma rays are all phenomenon of electromagnetic waves at different frequencies. This introduction will treat only those that are generated by an electrical source and propagated along a physical cable or other transmission media. That is, frequencies above zero and up to about 50 gigahertz.

¹The majority of the technical terms, relative to RF and coaxial cable and connectors, used here-in and throughout this catalog are defined in the Glossary (Appendix G) starting on page 301.

Frequency or Wavelengths	Designation	Applications
0 - 29.9 KHz	VLF (Very Low Frequency)	Commercial AC electricity, deep depth sounders, ultrasonic grinders, sonic oscillators
30 - 299.9 KHz	LF (Low sonar Frequency)	Shallow-to-medium depth sounders
300 - 2999.9 KHz	MF (Medium Frequency)	Commercial AM radio broadcasting, marine radio telephone, direction finders
3 - 29.9 MHz	HF (High Frequency)	Citizen band radio, amateur radio, international broadcasting
30 - 299.9 MHz	VHF (Very High Frequency)	VHF television (Channels 2 thru 13), commercial FM radio broadcasting, amateur radio, fire and police radio
300 - 2999.9 MHz	UHF (Ultra-high Frequency)	UHF television (Channels 14 thru 83), microwave ovens, aeronautical radionavigation
3 - 29.9 GHz	SHF (Super High Frequency)	Microwave communications, marine radar, aircraft tracking and airborne radars
30 - 299.9 GHz	EHF (Extremely High Frequency)	Space communications, radio astronomy

Notes:

1. KHz = Kilohertz (1 thousand cycles per second)

2. MHz = Megahertz (1 million cycles per second)

3. GHz = Gigahertz (1 billion cycles per second)

Figure 7


Radiant Energy Spectrum

In the following paragraphs we will discuss waves in greater detail, including the relationship of frequency and wave length, how pulses are formed and used, how each differs from the other and the problems involved in their transmission.

Sine Waves

An RF wave is a sine wave, meaning that it smoothly swings from zero to a positive peak value, then back down past zero to a negative peak value, then back to zero to complete a 360 electrical degree cycle. The positive and negative peaks are always equal in amplitude. The two qualities which characterize this type of wave are amplitude and frequency (f). Figure 8 shows these two characteristics. Amplitude refers to the peak value attained by the wave and corresponds to voltage. Frequency refers to the number of oscillations per second. For example, the sign wave in Figure 8(B) has completed 12 cycles in one second. Therefore, we would say that this wave has a frequency of 12 cycles per second or 12 Hertz. The time for one complete cycle is defined as the period (T). The relationship between the period and frequency is given by the equation:

f = 1 / T in Hertz





Typical Sine Wave Characteristics

The wave travels away from the generator at speeds approaching the speed of light. When an electromagnetic wave travels in a medium other than air or vacuum, the **speed** for the wave is reduced by a factor of the square root of the dielectric constant (ϵ . The velocity (v) of the propagation of a signal is given by:

Where c is the speed of light, 3×10^8 m/sec or 1.18×10^{10} in/sec, and ε is the dielectric constant of the medium. (See Table 1 for dielectric constants of various materials) The **wavelength** of a signal is given by the formula

$$\lambda = v/f = \frac{c}{\sqrt{\epsilon} \times f (GHz)} \frac{1.18 \times 10^{10}}{\sqrt{\epsilon} \times f (GHz)}$$

See Figure 9


272

Catalog 1307191 Revised 3-07

www.tycoelectronics.com specifie are star

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803






Constant	Temperature Range
2.03	-70 +250°C
2.3	-60 +80°C
4.6-4.0	-40 +120°C
2.12	-65 +85°C
2.25	-40 +105°C
3.7	-65 +85°C
	2.03 2.3 4.6-4.0 2.12 2.25

Pulses

The sine wave is most often used for communication purposes where intelligence is imposed on the wave by a variation in amplitude (amplitude modulation, AM) or by a variation in frequency (frequency modulation, FM).

Pulses, on the other hand, are primarily used in computers and digital instrumentation. Since pulses are generally used for triggering purposes, the pulse rise/fall time, amplitude and width are the most important. Figure 10 shows a pulse and identifies these characteristics.



Notice that rise time is the time required for the pulse to rise from 10% to 90% of its amplitude - not from zero to maximum. Rise and fall time is perhaps the single most important characteristic of a pulse in today's high-speed digital equipment. Figure 11 shows that the faster the rise and fall time, the more pulses will fit in a given time frame.




Figure 11
Pulse Rise and Fall Time

The bit rate for a system is the maximum rate of pulses per second that a system can process without causing data errors. The maximum performance can also be specified in terms of baud rate. The baud rate is defined as the number of characters (bytes) that are transmitted per second. Generally a character represents 10 bits (7 bits for the information, one parity bit, and two for start and stop, totalling 10).

Now that we know why fast pulses are required, the next problem is how to obtain faster rise times. A pulse is made up of a great number of different frequencies, and the more high frequencies a pulse contains, the faster will be its rise time and the flatter will be its peak. To better understand this, refer to Figure 12. At A, you will see a fundamental frequency (1), its third harmonic (3), and the resultant waveform (S3), which is a combination of 1 and 3. Although this does not yet resemble a square wave, you will note that the rise time is decreased, and a dip appears at the peak. At B of Figure 12, we have added the fifth harmonic. Rise time is further decreased, and the peak is beginning to flatten out. At C the seventh harmonic has been included, and the resultant wave S7 begins to resemble a square wave. As more high frequency harmonics are added to the waveform, it will more closely resemble a square wave, and the squarer it becomes, the faster will be the rise time.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Fast rise times and short pulse widths require high frequency components.

Two frequent causes of digital signal degradation can be (1) high capacitance of the transmission line and (2) impedence mismatches of connector transmission line or I/0 devices. Selection of an impedance-matched connector on a digital line, especially if short cable assemblies are used, can be as important as connector selection for an RF modulated line. **Reflected pulses out of phase with the original pulse can cause false signals or high error rates in a digital system.**

Since pulses with fast rise times are necessary in highspeed computers, any circuit element which could reduce or attenuate high frequency response is undesirable.




Figure 12 Development of a Square Wave

Signal Integrity and Propagation

To explain how to maintain signal integrity, it is necessary to review how the signal is configured in a cable and how it propagates. Ignoring digital signals for this discussion we will identify the issues that deal with the integrity of a sine wave. Consider a coaxial cable consisting of an inner conductor surrounded by a dielectric material and then an outer conductor (See Figure 13). The outer conductor may be a braid, a foil, or a solid metal.




Diagram of a Cable

An electromagnetic wave traveling in a coaxial cable produces an electric and a magnetic field between the inner conductor and the outer conductor (Figure 14). The electric (E field) is radial and varies in time. An alternating current flows along the inner conductor and the outer conductor. An oscillating magnetic field (H field) circles the inner conductor.




Figure 14

Electric field (E) and magnetic field (H) belonging to the principal mode in a coaxial line.

The alternating current on a conductor is not spread throughout the conductor but is strongest at the surface and decays exponentially at points further into the conductor. This is called the skin effect. At a frequency of 1MHz, three skin depths is 0.0078" (95% of the current is within three skin depths of the surface) and at 10GHz three skin depths is 0.00078". As a result, the current is on the outer surface of the inner conductor and the inner surface of the outer conductor over the entire range of interest for most RF systems. The dimensions and material beyond several skin depths have no effect on the wave; gold plated plastic will propagate as well as gold plated copper at sufficiently high frequencies.

274

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

Attenuation

A wave loses energy (attenuates) in several ways: (1) The resistance of the inner and outer conductors is small but can be significant over long lengths and will produce some heat. (2) The dielectric may be lossy; its resistance is high but not infinite, and some energy is lost. (3) Electromagnetic energy radiates at high frequencies; significant energy losses are caused by radiation of electromagnetic energy (the cable acts like an antenna). (4) Energy is reflected due to impedance mismatches. The combination of these four types of losses are referred to as the **insertion loss** of a transmission line system. Connectors have similar losses.

Characteristic Impedance

A parameter which defines the behavior of a cable, connector, or any propagating system is **Characteristic Impedance**, Zo. The characteristic impedance of a lossless cable is related to the inductance per unit length, L, and the capacitance per unit length, C, as follows:


 $Zo = \sqrt{L/C}$ in ohms

The equivalent circuit of a transmission line is shown in Figure 15. R represents the conductor resistance for a unit length

For a coaxial cable the characteristic impedance is given by:

$$Zo = \frac{138}{\sqrt{\epsilon}} x \text{ Log}_{10} \frac{D}{d} \text{ in ohms}$$

where D is the inner diameter of the outer conductor and d is the outer diameter of the inner conductor, respectively. Similar equations apply for other geometries such as two parallel wires.



Typical Transmission Line Schematic

The maximum power is transferred between two systems if they have the same impedance. This is called impedance matching. However, impedance variations that are short compared to a wavelength can have a negligible effect on signal loss.

Standard impedances are 50 ohm, 75 ohm and 93-125 ohm. Most systems use 50 ohm because it is a compromise between maximum power transmission and minimum line loss. The telephone industry and the broadcast industry use 75 ohm for minimum line attenuation. The need for low capacitance instrumentation cable has produced the 93-125 ohm systems. The higher impedances are generally achieved by changing the conductor diameters and by modifying the dielectric material to add air.

Reflections

When the characteristic impedance changes in a transmission line system, part of an incident wave is reflected. The reflection coefficient can be calculated as:

Reflection Coefficient =
$$\rho = \frac{V_i}{V_R} = \frac{Z_R - Z_O}{Z_R + Z_O}$$

Where Vi and ZO are the incident voltage and impedance of the first media. V_R and Z_R represent the reflected voltage and impedance of the media that caused the reflection. The decibel loss due to reflection is given by:

Return Loss = 10 Log₁₀ (
$$\frac{1}{1-\rho^2}$$
) dB

VSWR


The traditional way to determine the reflection coefficient is to measure the standing wave caused by the superposition of the incident wave and the reflected wave. Traditionally the voltage is measured at a series of points using a slotted line. The ratio of the maximum divided by the minimum is the Voltage Standing Wave Ratio (VSWR). The VSWR is infinite for total reflections because the minimum voltage is zero. If no reflection occurs the VSWR is 1.0. VSWR and reflection coefficient are related as follows:

$$VSWR = (1 + \rho)/(1 - \rho)$$

Most present instrumentation measures the reflection coefficient and calculates the VSWR.

Figure 16 represents the direct relationship between VSWR and its equivalent in return loss (expressed in dB).

Figure 16 VSWR vs. Return Loss



Multiple Reflections

If there is a series of impedance changes, each one will have a reflection coefficient. The total reflection coefficient is the vector addition of each of the individual coefficients accounting for the distance between reflections and the reflection of any reflected waves. Even though the calculations are difficult, a total VSWR can still be measured.

Multiple reflections can produce a resonance phenomenon that is unique to wave theory. Properly understood some serious difficulties can be avoided. An example will make the point clear. Consider an electromagnetic wave with a

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 1.02

1.08

- 1.5 - 1.6


- 1.7

1.8

/OLTAGE STANDIN

RETURN LOSS (dB)

wavelength of 4 inches traveling on a cable that changes from 50 ohms to 25 ohms. The reflection coefficient is -.33, which means that one third of the incident voltage is reflected toward the source. Assume that one inch (one guarter wavelength) down the cable the impedance changes back to 50 ohm. Again, one third of the wave is reflected, but without any phase shift. It travels back to the first interface where one third of this reflected wave is reflected back toward the second interface. Two thirds of the wave is transmitted through the interface and travels back to the source. Since the first (reflected) wave is shifted 180 degrees at the reflection, and the second (transmitted-reflected-transmitted) wave is shifted 180 degrees because it traveled the one inch separation twice, the two waves are in phase. The net result is that the VSWR is much larger because the length of the 25 ohm section was just the right length to cause a resonance. If the length of the 25 ohm section had been one half wavelength, the two waves would have interfered and the VSWR would be at a minimum.



Multiple Wave Reflections (Caused by Impedance Mismatch)

In summary, avoid cable lengths, printed circuit board paths, or connectors that are multiple of one quarter ($\lambda/4$, $3\lambda/4$, etc.) of the intended signal transmission wavelength. Coaxial cables, when manufactured, also have periodic variations in diameter that result in periodic changes in impedance (Zo), that can cause significant levels of reflected signal (high return loss) at specific frequencies.

Reflections of Digital Signals

The previous discussions dealing with attenuation, reflections and standing waves can apply to digital signals with some extra thought.

A single pulse can be thought of as a combination of high frequency sine waves. The maximum frequency component in a square wave pulse can be calculated by this equation:

> f = 0.35/rise time where f = GHz when "t" is in nanoseconds

Attenuation of the frequencies necessary to support the short risetime will produce a slower rise and possibly prohibit the pulse from ever reaching the detector. This 'slurring' of the pulse is similar to the behavior of an RC circuit and the attenuation is sometimes called capacitive attenuation.

A series of pulses can demonstrate resonance. If a portion of a pulse is reflected at each interface, it is possible for them to come together and add up to form a new phantom pulse.

The critical frequency here is the bit rate. Think of a sine wave with a frequency the same as the bit rate; if it will resonate in the cable, the pulses will also. Extra pulses caused by resonance might easily result in an error signal from the receiving system requesting a retransmittal. The final result would be a communication system that is much slower than intended.

Cut-off Frequency

The cut-off frequency of a coaxial transmission line is the frequency at which modes of energy transmission, other than the "TEM" mode, can be generated.

fco =
$$\frac{7.5}{\sqrt{\epsilon} (D+d)}$$
 (in GHz)

(D and d are measured in inches)

Types of Transmission Lines

Twin Lead transmission cable is generally used where impedance matching alone is important, since it provides only minimal shielding. Impedance values of 300 ohms and 600 ohms are common. Lower impedance values require closer spacing of the conductors and are not normally available in this type of cable. A typical application for twin lead cable is in antenna lead wire for television sets.

Twisted Pair is a variation of the twin lead type. It consists of two lengths of ordinary hookup wire twisted together. A twisted pair provides relatively constant impedance plus better magnetic shielding than twin lead cables. It is flexible, inexpensive, easy to terminate and is used extensively by the computer industry. However, it should not be used when maximum shielding is required.

276

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

www.tycoelectronics.com

Shielded Twisted Pair Cable is used to eliminate inductive and capacitive coupling. Twisting cancels out inductive coupling, while the shield eliminates capacitive coupling. Most applications for this cable are between equipment, racks and buildings.

Flexible (Braided) Coaxial Cable is by far the most common type of closed transmission line because of its flexibility. It is a coaxial cable, meaning that both the signal and the ground conductors are on the same center axis. The outer conductor is made from fine braided wire, hence the name "braided coaxial cable". This type of cable is used in practically all applications requiring complete shielding of the center conductor. The effectiveness of the shielding depends upon the weave of the braid and the number of braid layers. Tyco Electronics manufacturers connectors for cable sizes ranging from less than 1/8 in. diameter, for low power applications of around 50 watts, to over 1/2 in. diameter for power of 850 watts at 100 MHz and voltages up to 5000. In addition to power handling capabilities, cables are available for high frequency applications, high and low temperature applications, severe environmental applications and many other specialized uses.

Triaxial Cable is used when higher "shielding" efficiency characteristics are required in applications similar to those using shielded twisted pair cable.





Figure 18

Twin Conductor and Triaxial Cable



Often you will hear the term "shielded cable". This is very similar to coaxial cable except the spacing between center conductor and shield is not carefully controlled during manufacture, resulting in non-constant impedance.

Semirigid Coaxial Cable uses a solid tubular outer conductor rather than the braided type, so that all the RF energy is contained within the cable. One of the drawbacks of braided cable is that the shielding is not 100% effective, especially at higher frequencies. This is because the braided construction can permit small amounts of short wavelength (high frequency) energy to radiate. Normally this does not present a problem; however, if a higher degree of shielding is required, semirigid coaxial cable is recommended. For applications using frequencies higher than 30 GHz a miniature semirigid cable is recommended. Various connectors are available from Tyco Electronics to terminate these cables.

Ribbon Coaxial Cable is a relatively recent Tyco Electronics innovation which combines the advantages of both ribbon cable and coaxial cable. Tyco Electronics currently provides both the cable and the insulation displacing coaxial connector to terminate the cable. Each individual coaxial cable consists of the signal conductor, dielectric, a foil shield and a drain wire which is in continuous contact with the foil. The entire assembly is then covered with an outer insulating jacket. The unique manufacturing feature of this cable is the precise placement of the drain wires to permit gang stripping of the outer jacket and foil. The major advantage of this cable is the speed and ease with which it can be mass terminated with the Tyco Electronics insulation displacement technique. They can also be separated into individual coaxial lines and terminated with standard coaxial connectors as required.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

Appendix B - White Bronze

High Quality Surface Plating & Excellent Intermodulation Performance for RF Connectors

Product Facts

- Low intermodulation
- High corrosion resistance
- Low porosity
- Low RF losses
- Wear and scratch resistance



Tyco Electronics' industrial electroplating facilities is one of the most advanced in the world.

The Tyco Electronics White Bronze surface finish represents a dramatic improvement upon the wear characteristics and life expectancy of silver plating, at the same time offering a far better electrical performance than nickel. White Bronze plated connectors exhibit intermodulation characteristics significantly better than stainless steel or nickel plated products. Silver has always been the preferred finish from an electrical standpoint but its corrosion and wear characteristics especially in harsh conditions are often unacceptable. While nickel is an extremely rugged finish it

has properties undesirable in many RF applications; including, high RF and insertion losses, poor intermodulation performance, high permeability and poor screening effectiveness.

The Tyco Electronics White Bronze is composed of copper, tin and zinc which are applied simultaneously to produce a finished color similar to stainless steel. With one of the most advanced industrial electroplating facilities in the world Tyco Electronics can achieve the levels of control over the complex galvanic process necessary in the application of this alloy. The Tyco Electronics White Bronze is similar in composition and performance to other copper/tin/zinc alloys developed in the industry such as Sucoplate[®] and BBR.

Comprehensive conditioning tests have been performed to provide a thorough evaluation of The Tyco Electronics White Bronze plated connector bodies. The tests were performed to the specifications of the European and International RF connector standards — CECC 22000/IEC 68-2-14/ IEC 169-1. The results are summarized on page 280.

Deposit Characteristics

Composition — Copper (55-60%), Tin (20-25%), Zinc (15-20%)

Density — 7.9-8.1 g/cm³

Hardness — 300-380 HV

Passivation — Immersion Chrome

Sucoplate® is a plating trademark for Huber & Suhner. BBR is a plating trademark for Radiall.

Need more information?

Call Technical Support Center at 1-800-522-6752 for product and tooling information.

The Technical Support Center is staffed with specialists well versed in all Tyco Electronics products. The Center can provide you with:

- Engineering Support
- Catalogs
- Technical Documents
- Product SamplesTyco Electronics
- Authorized Distributor Locations Tyco Electronics Internet
- Home Page: www.tycoelectronics.com

278

Catalog 1307191 Revised 3-07

www.tycoelectronics.com specified are stand

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

₹ Тусо

Electronics

Appendix B - White Bronze (Continued)

Low Intermodulation Products

Dissimilar metals, finishes and discontinuities within a coaxial line structure give rise to Intermodulation Products (IMP). This is of particular concern in applications requiring low levels of intermodulation, such as cellular base stations and antennas. White Bronze plated connectors offer better IMP performance and lifetime characteristics than nickel. Due to the similarity of electrolytic potentials and the non magnetic properties of the finish, levels of intermodulation are commensurate with silver and far in excess of stainless steel/nickel connectors. At the same time the excellent wear characteristics and durability of the finish ensure that the intermodulation life of the connector is greater than silver. The life is also improved as a direct result of the excellent corrosion resistance properties of White Bronze; thereby minimizing metal/metal oxide junctions.

Highly Corrosion Resistant

Even under continuous exposure to harsh environments White Bronze retains its aesthetic appearance. Unlike silver it does not discolor when exposed to sulphur, potassium sulphides etc., neither is there any build up in oxide layers as is the case with nickel. Furthermore, White Bronze parts have successfully passed all international salt spray tests (MIL, BS, CECC, IEC).

In conditions of continuously high temperatures (>100°C) and/or excessive humidity (>100%) there is no build up of foreign layers which may affect contact resistance.

Low Porosity and No Reaction with Contact Surfaces

Less than 2µm of White Bronze is needed to create a completely nonporous, corrosion resistant surface. Tyco Electronics applies White Bronze to a thickness of between 2µm and 3µm. This compares favorably with the typical plating thickness of nickel (>10µm) and consequently, variations in plating depth are significantly less.

White Bronze does not alloy with brass and since its coefficient of expansion is virtually identical to that of brass, rapid temperature shocks (-50°C/200°C) do not cause blistering or cracking of the plating.

The electrolytic potential of White Bronze is approximately that of brass. Consequently, any White Bronze plated connectors in contact with stainless steel, silver, nickel or nickel containing finishes carry no risk of corrosion as a result of any chemical potential difference.

Low RF Losses

The relative permeability (μr) of the Tyco Electronics White Bronze is 1 giving rise to low RF losses even at high frequencies. As a direct result of the good conductivity of the finish, skin depth is minimized further reducing insertion loss and ensuring a better impedance match across the frequency range of the connectors.

Non Magnetic Finish

The Tyco Electronics White Bronze contains no ferrous materials and so has no magnetic properties. This is particularly desirable in many RF applications.

Wear and Scratch Resistant

The hardness of the Tyco Electronics White Bronze at 300-380HV is more than double that of silver and marginally harder than platings containing nickel. This gives a scratch resistance which is rarely surpassed and makes it ideal for high mating applications.

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix B - White Bronze (Continued)



White Bronze is available on all products, including 7-16, N, TNC, OSP and SMA.

Low Coefficient of Friction

The coefficient of friction is approximately 70% that of silver to give lower insertion forces and smoother coupling. These properties combine to produce a harder wearing, longer lasting finish which prolongs connector life and reduces the ongoing cost of ownership.

Tyco Electronics' White Bronze

Environmental Test

Four groups of conditioning tests were performed to provide a comprehensive evaluation of the Tyco Electronics White Bronze plated connector bodies. The tests were performed to the specifications of the European and International RF connector standards - CECC 22000/ IEC 68-2-14/IEC 169-1. Full details and relevant data are available from Tyco Electronics and results are summarized below.

Test 1 - Industrial Atmosphere & Temperature

Endurance

1.1 Industrial Atmosphere Exposure to Sulphur Dioxide Atmosphere (as specified in IEC 68-2-42 Test Kc) for 21 days of mated connectors, previously subjected to 500 matings, to determine the influence of sulphur dioxide on the corrosion resistance properties of White Bronze Plating. Contact resistance measured after matings and sulphur dioxide exposure was less than 5% (0.23mohm) of the permissible specification.

1.2 High Temperature Endurance Exposure to temperatures of 85°C ±5°C for 250 hours, to determine the impact of prolonged high temperatures on plating adhesion. Prior to testing the connectors were subject to 500 matings. Results showed no visual deterioration in plating finish (blistering, cracking etc.) and the results of outer conductivity performance were comparable to Test 1 (above).

Test 2 - Rapid Temperature Change & Damp Heat

Steady State

2.1 Rapid Temperature Change Exposure to -55°C and +85°C for 15 minutes, transition time 2-3 minutes, 50 cycles. To determine possible plating deterioration caused by prolonged and rapid temperature change. No visual deterioration, outer conductivity performance were comparable with Test 1 (above).

2.2 Damp Heat Steady State Exposure to 93% relative humidity (at 40°C) for 10 days. To determine plating adhesion. No visual deterioration, outer conductivity performance were comparable with Test 1 (above).

Test 3 - Soldering Heat

3.1 Resistance to Soldering Heat Exposure to concentrated soldering heat (250°C) for 10 seconds to evaluate any possible deterioration in plating finish. No deterioration detected.

Test 4 - Salt Mist & Mechanical Endurance

4.1 Salt Mist

Exposure to salt mist spray (as defined in BS 2011 Pt. 2.1 Ka) for 48 hours to evaluate the uniformity of protective coatings, any visual deterioration, or impact on electrical performance. No visual deterioration, outer conductivity performance were comparable with Test 1 (above).

4.2 Mechanical Endurance Electrical and visual evaluation of the connectors after 500 matings to determine any electrical or visual deterioration. No visual deterioration, outer conductivity performance were comparable with Test 1 (above).

Availability and Ordering

Tyco Electronics offers White Bronze on all products including 7-16, N, TNC, SMA and OSP. For more information on White Bronze contact your local Tyco Electronics Sales Office.

280


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Tyco Electronics

Appendix C - Intermodulation in RF Coaxial Connectors

Product Facts

- High quality plating to 6µm for IM-sensitive products
- Restrict materials to copper and its alloys
- Avoid the use of stainless steel, nickel, ferrites, etc. in the signal path
- Quality machining
- Ensure, by design, a properly defined contact interface at connector, panel and contact interfaces
- Avoidance of crimps




The increased demand from the mobile communication industry to provide greater channel capacity coupled with the increased sensitivity of receivers has exposed a condition within RF Coaxial Connectors referred to as Intermodulation Distortion (IMD). This condition occurs when non-linearities within the connectors act as imperfect diodes to generate other frequencies known as Intermodulation Products (IMP). Some of these frequencies appear within the receive band and effectively block the channel. The purpose of this application note is to outline the basic causes of Intermodulation and the techniques Tyco Electronics has undertaken to minimize this condition.

IM Basics

Modern developments in base stations for GSM, DCS 1800 and PCS 1900 have necessitated the use of "7-16", "4.1/9.5" and "N" connectors due to the increased power requirements. The requirements for performance are typically in the order of -

160 dBc to -163dBc (when working in dBc) or -120dBm (when working in dBm), both with 2 x (+43dBm) tones. The requirement is so stringent because the connectors are used in post-filtering sections of the transmit path (between the diplexer and the antenna) and also because the system is a full duplex system where the multiple-carrier transmit path is also the receive path. In a truly linear system, the output is directly proportional to the input, following the form of y=mx+c (see fig. 2). Coaxial connectors have traditionally been viewed as following this pattern. In reality, there have always been non-linearities present in coaxial connectors. These were not readily apparent as the resultant IM products were significantly below the noise floor of the system due to relatively weak carrier signals. This situation becomes apparent when the incident power is raised above 30 dBm.

The small non-linearities have a characteristic similar to a square-law (see Fig 3). The distortion to the waveform is evident, the



Catalog 1307191 Revised 3-07

Locations

you with:

Catalogs

www.tycoelectronics.com

Need more information?

Call Technical Support at

the numbers listed below.

Technical Support is staffed with specialists well versed in all Tyco Electronics

products. They can provide

Technical Support

Product Samples

Tyco Electronics

Technical Documents

Authorized Distributor

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix C - Intermodulation in RF Coaxial Connectors (Continued)

IM Basics (Continued)

Electronics

Tyco

positive 1/2 cycle being significantly greater in amplitude than the negative 1/2-cycle. When converted to the frequency domain, this waveform consists of the desired fundamental plus a decaying series of related harmonics that, in themselves, interact with other carriers present on the transmission line.

The effect of this interaction produces additional frequencies, some of which occur where they are least wanted (see fig. 4). The 2F1-F2 (3rd order IMP), 3F1-2F2 (5th order IMP) and 4F1-3F2 (7th order IMP) products can all manifest in the receive band and, if sufficiently large, effectively block a channel by making the base station receiver think that a carrier is present when one is not.

Potential causes of IM in Coaxial Connectors

There are numerous factors which can affect intermodulation performance in RF coaxial connectors. Identified below are the most likely sources of concern:

- Contaminated plating solution
- Insufficient plating thickness
- Corrosion
- Dissimilar metals in intimate contact

Remedies for IM in RF Coaxial Connectors

To combat the above identified IM sources, Tyco Electronics undertakes precautions during the design and manufacture of the product, as summarized below:

High quality plating to 6µm for IM-sensitive products

The plating must also be free from contaminants and properly passivated with a chromate passivate. Silver has been the preferred plating material as it possesses the lowest practical resistivity thereby minimizing interface contact resistances. Tyco Electronics also offers a unique White Bronze plating finish which provides excellent durability, tarnish resistance and non-magnetic properties ideal for low intermodulation. During testing with a system noise floor of -145 dBm, the difference in performance between the Tyco Electronics silver-plating and the Tyco Electronics White Bronze finish is not discernible (refer to White Bronze Application Note 1307057).

Restrict materials to copper and its alloys.


This ensures maximum plating adhesion and minimum electrochemical potential difference between the base materials and their over-platings.

 Avoid the use of stainless steel, nickel, ferrites, etc. in the signal path


Magnetic and para-magnetic materials will only compound non-linearites and give poorer interface contact resistances. During experimentation, Tyco Electronics discovered a degradation in performance of 20dB when nickel plate was used. The presence of magnetic or para-magnetic materials will also cause the forward IMP figure to differ from the reverse IMP.

Quality machining

Surface finish is paramount. The signal propagates within a "skin" if this skin is too rough, the signal will repeatedly transition through metal and surface oxide layers, thereby creating the



- Magnetic materials in the signal path
- Low contact pressure
- Less than 360-degree contact
- Poor surface finish
- Debris and dust within the connector
- Convoluted signal path



same effect as a poor panel contact (see fig. 5). For IM-sensitive designs Tyco Electronics ensures $0.4 \mu m$ is the maximum.

Contact design

This primarily affects the connector interface. Repeated matings can generate small amounts of plating from the individual parts. These oxidize and interfere with the mechanical (and therefore electrical) mating of connectors. The oxidized debris gives further rise to metal and surface oxide junctions and consequently, higher IM products.

• Ensure, by design, a properly defined contact interface at connector, panel and contact interfaces

Insufficient contact force will give rise to metal to oxide junctions. The classic rectifiers were metal oxide by composition.

Axial maximum material condition at the connector interface is critical in order to ensure minimum mismatch and maximum

282

Catalog 1307191 Dime Revised 3-07 and ir speci www.tycoelectronics.com are st

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix C - Intermodulation in RF Coaxial Connectors (Continued)

Remedies for IM in RF Coaxial Connectors (Continued)

potential of a butt-contact. Panel interfaces generally concern the physical contact of the connector body to the panel. In this case, it has been determined that a protruding feature as close as possible to the body bore will give the best IM performance. The applied mounting force is concentrated in the surface area of the protrusion which, on engagement with the panel, punctures the existing oxide layer to give a metal-to-metal, gas-tight junction.

Improving IM Connector Design

Tyco Electronics continues to pursue design techniques which improve intermodulation performance to address emerging telecommunication market needs. A state of the art intermodulation test facility and participation on the international (IEC SC46D WG5) committee to develop standard test practices

Most commonly asked questions regarding Intermodulation

Why is intermodulation such a concern for cellular infrastructure equipment?

The primary concerns for cellular service providers today are channel efficiency and clarity of transmission. Growth in demand for mobile communications has created a need to operate equipment at greater capacities and reliability to service the competitive market. Intermodulation degrades or limits the ability of the service provider to operate at optimal levels of performance and may ultimately cause subscribers to experience poor call quality. Intermodulation has become an important factor in system selection to ensure the best possible network service.

2. Where is intermodulation most likely to occur in cellular infrastructure equipment?

Intermodulation is typically of greatest concern between the filtering elements of the system and the antenna. The introduction of higher power levels for the transmit side of the equipment creates greater potential for intermodulation to occur. This is why the majority of focus for intermodulation concerns 7-16, Type N, SMA and 4.1/9.5 connector interfaces.

$\mathbf{S}_{\mathbf{I}}$ is intermodulation a recent development?

Intermodulation has always been inherently present in RF coaxial connectors but may be relatively imperceptible in some devices for a variety of reasons. The amount of power applied to an RF connector determines the relative IM threshold which can be observed. Intermodulation is therefore more likely to cause concern in a higher power system, for example, utilizing a 7-16 connector interface rather than an equivalent low power OSX solution. The trend toward higher power digital cellular systems creates the need for greater intermodulation sensitivity.

4. What is the best method of cable attachment for IM sensitive cable assembly applications?

Soldering and clamping are preferred methods due to the 360-degree point of contact created at the cable to connector interface. Such intimate contact improves the overall contact resistance leading to improved IM characteristics. In addition, it is also better to solder the center conductor of the connector to the cable versus crimping due to the improved contact resistance path and elimination of voids.

Avoidance of crimps

Crimps, by nature, can only give multiple point-contact rather than 360-degree contact and also cause a variability in the position of electrical contact during dynamic testing. IM products will therefore be greater. It has been found that soldered center contacts and clamp/solder outer contacts give the best static and dynamic IM performance.

ensures our commitment to the understanding of intermodulation characteristics. This applied technology base is instrumental in developing innovative low intermodulation products for 7-16, Type N, SMA and OSP interfaces.

5. Are there ways to test for intermodulation in an RF coaxial connector?

Yes, very sophisticated methods are needed to test for intermodulation in RF connectors. The test system must utilize extremely sensitive filtering or clean amplification so that the equipment itself has a very low intermodulation noise floor. There is not yet a standardized approach to testing, although an international committee has been formed in the connector industry to address the situation. Tyco Electronics has a state of the art test facility where our designs are optimized for low intermod performance and where further analysis on the effects of this phenomena can be studied.

No. Because coaxial connectors are broadband devices there is no frequency dependency. Some apparent variability can be detected during testing but this is not due to the connector. The impedance matches of the output diplexer/triplexer and terminations are the causes of the variations and should not be incorrectly attributed to the connector/assembly. Tyco Electronics Interconnect Business Unit has demonstrated that by varying the impedance match of the test station termination, a DUT can show 15dB better IMP₃ than exists in reality.

IMP₃ in mixers follows a 3dB/dB relationship. What is it for connectors?

The relationship is identical. Taking the 3rd order (2F1-F2): varying the power of F2 gives an IMP₃ relationship of 1dB/dB whereas varying the power of F1 gives a relationship of 2dB/dB as the IMP is derived from the 2nd harmonic of F1. This gives a total of 3dB/dB when symmetrically varying both carrier powers.

8. I am buying a complete cable assembly from Tyco Electronics. How do I interpret the IMP result now?

With caution! It is the Tyco Electronics policy when testing devices to move away from the normal static test to a dynamic test where the cable termination interfaces are mechanically exercised during live IM conditions. It is also a good indicator to customers of the build quality of the assemblies. A dynamic evaluation has shown 15dB degradation in IMP performance for poor assemblies and even as much as 50dB for bad ones. It is therefore strongly advisable that IM performance figures are stated in the context of a dynamic measurement.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix D - Typical Coaxial Cable Specifications

Abbreviations

Dielectric

PE	Solid polyethylene
PTEE	Solid polyetrafluoroethylene
PIB	Polyisobulylene, Type B, per MIL-C-17
Rubber	Per MIL-C-17D
Sil	Silicone rubber
PS	Polystyrene

Conductors and Braid Materials

BC SC CCS TC	Silver covered copper covered aluminum Bare copper Silver covered copper Copper covered steel Tinned copper
SCCS	Silver covered copper covered steel.
3663	Silver covered copper covered steer

SCCad Br.....Silver covered cadmium bronze GS.....Galvanized steel TCCSTin copper covered steel SSCSilver covered strip HR.....High resistance wire SA.....Silver covered alloy **Jacket Material** PVC-I "Black polyvinylchloride, contaminating, Type I, per MIL-C-17D

PVC-IIGray polyvinylchloride, noncontaminating, Type II, per MIL-C-17D
PVC-IIABlack polyvinylchloride, noncontaminating, Type IIA, per MIL-C-17D
PE-IIIClear polyethylene
PE-IIIAHigh molecular weight, black polyethylene, Type IIIA, per MIL-C-17D
FG Braid VFiberglass, impregnated, Type V, per MIL-C-17D
FEP-IXFluorinated ethylene propylene, Type IX, per MIL-C-17D
PURPolyurathane, black specific compounds
SIL/DAC-VIDacron braid over silicone rubber, Type VI, per MIL-C-17D
RubberPer MIL-C-17D

Max

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
4	0.81 BC .0320	PE	.295 .116	2/BC	PVC-1	5.74 .226	.025	50	30.8	-40 +80	1900	Use RG 58C
5	1.29 BC .0508	PE	4.7 .185	2/BC	PVC-1	8.43 .332	.088	52.5	28.5	-40 +80	3000	Use up to 100 MHz
5A	1.29 SC .0508	PE	4.6 .181	2/SC	PVC-II	8.33 .328	.088	50	30.8	-40 +80	3000	Use RG 212
5B	1.29 SC .0508	PE	4.6 .181	2/SC	PVC-IIA	8.33 .328	.087	50	30.8	-40 +80	3000	Use RG 212
6	0.72 CCS .0285	PE	4.7 .185	2/Inner SC Outer BC	PVC-II	8.43 .332	.081	76	20.0	-40 +80	2700	Use RG 6A
6A	0.72 CCS .0285	PE	4.7 .185	2/Inner SC Outer BC	PVC-IIA	8.43 .332	.082	75	20.6	-40 +80	2700	Good Attenuation Stability
7	0.91 BC .0359	Air-Space PE	6.35 .250	1/BC	PVC-I	9.4 .370	.080	95	12.5	-40 +80	1000	Use RG 63B
8	2.17 .0855 7/ 0.72 BC .0285	PE	7.24 .285	1/BC	PVC-I	10.29 .405	.106	52	29.5	-40 +80	4000	Use RG 213
8A	2.17 .0855 7/ 0.72 BC .0285	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.106	52	29.5	-40 +80	5000	Use RG 213
9	2.17 .0855 7/ 0.72 SC .0285	PE	7.11 .280	2/Inner SC Outer BC	PVC-II	10.67 .420	.140	51	30.0	-40 +80	4000	Use RG 214
9A	2.17 .0855 7/ 0.72 SC .0285	PE	7.11 .280	2/SC	PVC-II	10.67 .420	.140	51	30.0	-40 +80	4000	Use RG 214
9B	2.17 .0855 7/ 0.72 SC .0285	PE	7.11 .280	2/SC	PVC-IIA	10.67 .420	.150	50	30.8	-40 +80	5000	Uase RG 214
10	2.17 .0855 7/ 0.72 BC .0285	PE	7.24 .285	1/BC	PVC-II w/Armor	11.76 .463	.146	52	29.5	-40 +80	4000	Use RG 215
10A	2.17 .0855 7/ 0.72 BC .0285	PE	7.24 .285	1/BC	PBC-IIA w/Armor	11.76 .463	.146	52	29.5	-40 +80	5000	Use RG 215
11	1.21 .0477 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-I	10.29 .405	.096	75	20.6	-40 +80	4000	Use up to 100 MHz
11A	1.21 .0477 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.096	75	20.6	-40 +80	5000	Use up to 1000 Mhz
12	1.21 .0477 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-II w/Armor	11.76 .463	.141	75	20.6	-40 +80	4000	Use RG 12A

284

Catalog 1307191 Revised 3-07

and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are in millimeters

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
12A	1.21 .0477 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-IIA w/Armor	11.76 .463	.141	75	20.6	-40 +80	5000	Use up to 1000 MHz
13	1.21 .0477 7/ 0.4 TC .0159	PE	7.11 .280	2/BC	PVC-I	10.67 .420	.126	74	20.8	-40 +80	4000	Use RG 216
13A	1.21 .0477 7/ 0.4 TC .0159	PE	7.11 .280	2/BC	PVC-IIA	10.67 .420	.126	52	20.8	-40 +80	4000	Use RG 216
14	2.59 BC .1020	PE	9.4 .370	2/BC	PVC-II	13.84 .545	.216	52	29.5	-40 +80	5500	Use RG 217
14A	2.59 BC .1020	PE	9.4 .370	2/BC	PVC-IIA	13.84 .545	.216	76	29.5	-40 +80	7000	Use RG 217
15	1.45 CCS .0571	PE	9.4 .370	2/BC	PVC-I	13.84 .545	.197	52	20.0	-40 +80	5000	Use up to 1000 MHz
16	2.59 BC .1250 Tube	PE	11.68 .460	1/BC	PVC-I	16 .630	.254	52	29.5	-40 +80	6000	Use up to 1000 MHz
17	4.78 BC .1880	PE	17.27 .680	1/BC	PVC-II	22.1 .870	.460	52	29.5	-40 + 80	11,000	Use up to 1000 MHz
17A	4.78 BC .1880	PE	17.27 .680	1/BC	PVC-IIA	22.1 .870	.460	52	29.5	-40 +80	11,000	Use RG 218
17B	Cancelled, Reassig	gned New Nomer	,	i 177								
18	4.78 BC .1880	PE	17.27 .680	1/BC	PVC-II w/Armor	23.50 .925	.585	52	29.5	-40 + 80	11,000	Use RG 219
18A	4.78 BC .1880	PE	17.27 .680	1/BC	PVC-IIA w/Armor	23.57 .928	.585	52	29.5	-40 + 80	11,000	Use RG 219
19	6.35 BC .2500	PE	23.11 .910	1/BC	PVC-II	28.45 1.120	.740	52	29.5	-40 +80	14,000	Use RG 220
19A	6.35 BC .2500	PE	23.11 .910	1/BC	PVC-IIA	28.45 1.120	.740	52	29.5	-40 +80	14,000	Use RG 220
20	6.35 BC .2500	PE	23.11 .910	1/BC	PVC-II w/Armor	29.92 1.178	.925	52	29.5	-40 +80	14,000	Use RG 221
20A	6.35 BC .2500	PE	23.11 .910	1/BC	PVC-IIA w/Armor	29.92 1.178	.925	53	29.5	-40 +80	14,000	Use RG 221
21	1.29 0508 High Res. Wire	PE	4.7 .185	2/SC	PVC-II	8.43 .332	.087	53	29.0	-40 +80	2700	Use RG 222
21A	1.29 .0508 High Res. Wire	PE	4.7 .185	2/SC	PVC-IIA	8.43 .332	.087	95	29.0	-40 +80	2700	Use RG 222
22	2 Cond. 1.16 .0456 7/ 0.39 BC .0152	PE	7.24 .285	1/TC	PVC-I	10.29 .405	.105	95	16.0	-40 +80	1000	Balanced Line w/Twisted Cond.
22A	2 Cond. 1.16 .0456 7/ 0.39 BC .0152	PE	7.24 .285	2/TC	PVC-II	10.67 .420	.151	95	16.0	-40 +80	1000	Balanced Line w/Twisted Cond.
22B	2 Cond. 1.16 .0456 7/ .0.39 BC .0152	PE	7.24 .285	2/TC	PVC-IIA	10.67 .420	.151	125	16.0	-40 +80	1000	Balanced Line w/Twisted Cond.
23	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE,2 Cores	9.65 .380	2/Inidividual Inner Common Outer BC	PVC-I	16.51 x .4 .650 24 .945	.490	125	12.0	-40 +80	3000	Use RG 23A
23A	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE,2 Cores	9.65 .380	2/Individual Inner Common Outer BC	PVC-IIA	16.51 x .4 .650 24 .945	.490 .490	125	12.0	-40 +80	3000	Dual Coaxial Balanced Line
24	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE,2 Cores	9.65 .380	2/Individual Inner Common Outer BC	PVC-I w/Armor	25.48 1.003 19.81 .780	.670	.670	12.0	$\frac{2}{100}$	3000	Use RG 24A

Appendix D - Typical Coaxial Cable Specifications (Continued)

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RG/U

Type Cable

24A

25A

26A

27A

28B

29

Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)
2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE,2 Cores	9.65 .380	2/Individual Inner Common Outer BC	PVC-IIA w/Armor	25.48 1.003 19.81 .780	.670	125	12.0	-40 +80	3000
1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	2/TC	Rubber-IV	12.83 .505	.205	48	50.0	-40 +80	10,000
1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	1/TC	Rubber-IV w/Armor	12.27 .483	.189	48	50.0	-40 +80	10,000
2.35 .0925 19/ 0.47 TC .0185	Rubber-D	11.56 .455	1/TC	Rubber-IV w/Armor	16.59 .653	.304	48	50.0	-40 +80	15,000
2.35 .0925 19/ 0.47 TC .0185	Rubber-D	11.56 .455	2/TC, GS	Rubber-IV w/Armor	19.05 .750	.370	48	50.0	-40 +80	15,000
0.81 BC .0320 1.21 .0477	PE	2.95 .116	1/TC	PE-111	4.67 .184	0.21	53.5	28.5	-55 +80	1900
7/ 0.4 BC .0159	PIB	4.7 .185	1/BC	PVC-I	6.35 .250	.044	50	27.0	-40 +80	1500
2.17 .0855 7/ 0.72 BC .0285	PIB	7.24 .285	1/BC	PVC-I	10.29 .405	.106	51	31.0	-40 +80	2000
2.17 .0855 7/ 0.72 BC .0285	PIB	7.24 .285	1/BC	PVC-I w/Armor	11.81 .465	.141	51	29.0	-40 +80	2000
2.59 BC .1019	PE	9.4 3.70	None	Lead	11.94 .470	.390	51	30.0	-55 +80	6000
2.17										

Appendix D - Typical Coaxial Cable Specifications (Continued)

Comments

Use RG 23A

Use RG 58

30	7/ 0.4 BC .0159	PIB	4.7 .185	1/BC	PVC-I	6.35 .250	.044	50	27.0	-40 +80	1500	Use RG 58
31	2.17 .0855 7/ 0.72 BC .0285	PIB	7.24 .285	1/BC	PVC-I	10.29 .405	.106	51	31.0	-40 +80	2000	Use RG 213
32	2.17 .0855 7/ 0.72 BC .0285	PIB	7.24 .285	1/BC	PVC-I w/Armor	11.81 .465	.141	51	29.0	-40 +80	2000	Use RG 215
33	2.59 BC .1019	PE	9.4 3.70	None	Lead	11.94 .470	.390	51	30.0	-55 +80	6000	_
34	2.17 .0855 7/ 0.72 BC .0285	PE	11.56 .455	1/BC	PVC-I	15.88 .625	.224	71	21.5	-40 +80	5200	Use RG 31B
34A	1.9 .0747 7/ 0.63 BC .0249	PE	11.68 .460	1/BC	PVC-IIA	16 .630	.224	75	20.6	-40 +80	6500	Use RG 34B
34B	1.9 .0747 7/ 0.63 BC .0249	PE	11.68 .460	1/BC	PVC-IIA	16 .630	.224	75	20.6	-40 +80	6500	Use up to 1000 MHz
35	2.91 BC .1144 1.6 0.63	PE	11.68 .460	1/BC	PVC-II w/Armor	23.57 .928	.525	71	21.5	-40 +80	10,000	Use RG 35B
35A	2.65 BC .1045	PE	11.68 .460	1/BC	PVC-IIA w/Armor	23.57 .928	.525	75	20.6	-40 +80	10,000	Use RG 35B
35B	2.65 BC .1045	PE	11.68 .460	1/BC	PVC-IIA	23.57 .928	.525	75	20.6	-40 +80	10,000	Unarmored: see RG 164
36	4.11 BC .1620	PE	23.11 .910	1/BC	PVC-I	29.97 1.180	.805	69	22.0	-40 +80	13,000	Use up to 1000 MHz
37	0.81 TC .0320	Rubber-C	3.56 .140	1/TC	PE-III	5.33 .210	.040	52.5	38.0	-55 +80	750	_
38	1.15 TC .0453	Rubber-C	4.98 .196	2/TC	PE-III	7.92 .312	.110	52.5	38.0	-55 +80	1000	_
39	0.64 CCS .0253	Rubber-C	4.98 .196	2/TC	PE-III	7.92 .312	.100	72.5	28.6	-55 +80	1000	_
40	0.64 CCS .0253	Rubber-C	4.98 .196	2/TC	Rubber IV	10.67 .420	.150	72.5	28.0	-40 +80	1000	
41	1.24 .0490 16/ 0.25 TC .0100	Rubber-IV	6.35 .250	1/TC	Rubber-IV	10.8 .425	.150	67.5	27.6	-40 +80	3000	_
42	0.72 .0285 Res. Wire	PE	4.98 .196	2/SC	PVC-II	8.69 .342	.050	78	20.0	-40 +80	2700	Use RG 222

286

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
43	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	Rubber-B	11.99 .427	1/BC	PVC-I	15.67 .617	_	95	17.6	-40 +80	1500	Use RG 57
54	1.21 .0477 7/ 0.4 BC .0159	PE	4.7 .185	1/BC	PVC-I	6.99 .275	.045	58	27.0	-40 +80	2500	Use RG 54A
54A	1.16 .0456 7/ 0.39 BC .0152	PE	4.52 .178	1/TC	PE-III	6.22 2.45	.041	58	26.5	-55 +80	3000	Use up to 1000 MHz
55	0.81 BC .0320	PE	2.95 .116	2/TC	PE-III	5.08 .200	.032	53.5	28.5	-55 +80	1900	Use RG 55B
55A	.0.89 SC .0350	PE	2.95 .116	2/SC	PVC-IIA	5.08 .200	.034	50	30.8	-40 +80	1900	Use RG 223
55B	0.81 SC .0320	PE	2.95 .116	2/TC	PE-IIIA	5.08 .200	.033	53.5	28.5	-55 +80	1900	Use up to 1000 MHz
56	1.49 .0585 19/ 0.3 BC .0117	Rubber-D	7.82 .308	2/BC	PVC-I	13.59 .535	.243	48	50.0	-40 +80	8000	
57	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE	11.99 .472	1/TC	PVC-I	15.88 .625	.225	95	17.0	-40 +80	3000	Balanced Line Parallel
57A	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE	11.99 .472	1/TC	PVC-IIA	15.88 .625	.225	95	17.0	-40 +80	3000	Balanced Line Parallel
58	0.81 BC .0320	PE	2.95 .116	1/TC	PVC-I	4.95 .195	.029	53.5	28.5	-40 +80	1900	Use RG 58B
58A	0.9 .0355	PE	2.95 .116	1/TC	PVC-I	4.95 .195	.029	52	28.5	-40 +80	1900	Use RG 58C
58B	0.81 BC .0320	PE	2.95 .116	1/TC	PVC-IIA	4.95 .195	.029	53.5	28.5	-40 +80	1900	Use up to 1000 MHz
58C	0.9 .0355 19/ 0.8 TC .0071	PE	2.95 .116	1/TC	PVC-IIA	4.95 .195	.029	50	30.8	-40 +80	1900	Extra Flexible Version RG 58B
59	0.64 CCS .0253	PE	3.71 .146	1/BC	PVC-I	6.15 .242	.032	73	21.0	-40 +80	2300	Use RG 59B
59A	0.64 CCS .0253	PE	3.71 .146	1/BC	PVC-IIA	6.15 .242	.032	73	21.0	-40 +80	2300	Use RG 59B
59B	0.58 CCS .0230	PE	3.71 .146	1/BC	PVC-IIA	6.15 .242	.032	75	20.6	-40 +80	2300	Use up to 1000 MHz
60	1.29 Str. C .0508	Rubber-C	6.35 .250	1/BC	Rubber-IV	10.8 .425	.150	50	39.0	-40 +80	1100	_
62	0.64 CCS .0253	Air-space PE	3.71 .146	1/BC	PVC-I	6.15 .242	.038	93	13.5	-40 +80	750	Use RG 62A Low
62A	0.64 CCS .0253	Air-space PE	3.71 .146	1/BC	PVC-IIA	6.15 .242	.038	93	13.5	-40 +80	750	Capacitance
62B	0.61 .0240 7/0.2 CCS .0080	Air-space PE	3.71 .146	1/BC	PVC-IIA	6.15 .242	.038	93	13.5	-40 +80	750	Extra Flexible RG 62A
63	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-I	10.29 .405	.083	125	10.0	-40 +80	1000	Use RG 63B
63A	0.64 BC .0253	Air-space PE	7.24 .285	1/BC	PVC-I	10.29 .405	.083	125	10.0	-40 +80	1000	Use RG 63B
63B	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.083	125	10.0	-40 +80	1000	Low Capacitance
64	1.49 .0585 19/ 0.3 TC .0117	Rubber-D	7.82 .308 7.24 .285	2/TC	Rubber-IV	12.57 .495 10.29 .405	.225	48	60.0	-40 +80	10,000	Capacitance
64A	1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	2/TC	Rubber-IV	11.68 .460	.205	48	50.0	-40 +80	10,000	_
65	0.2 [.0080] Formex-F 3.25 [.1280] Dia. Helix	PE	7.24 .285	1/BC	PVC-I	10.29 .405	.096	950	44.0	-40 +80	1000	High Impedance Video Delay Line

Appendix D - Typical Coaxial Cable Specifications (Continued)

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (lb/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
65A	.02 [.0080] Formex-F 3.25 [.1280] Dia. Helix	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.096	950	44.0	-40 +80	1000	High Impedance Video Delay Line
71	0.64 CCS .0253	Air-space PE	3.71 .146	2/TC	PVC-I	6.22 .245	.046	93	13.5	-40 +80	750	Use RG 71B
71A	0.64 CCS .0253	Air-space PE	3.71 .146	2/TC	PE-III	6.22 .245	.046	93	13.5	-55 +80	750	Use RG 71B
71B	0.64 CCS .0253	Air-space PE	3.71 .146	2/TC	PE-IIIA	6.22 .245	.046	93	13.5	-55 +80	750	Low Capacitance
72	0.64 CCS .0253	Air-space PE	11.68 .460	1/BC	PVC-I	16 .630	.169	150	7.8	-40 +80	750	Low Capacitance
73	1.65 BC .0650	PE	2.95 .116	2/BC	Copper Braid	4.45 .175	.031	25	61.8	-55 +80	1000	Low Impedance
74	2.59 BC .1020	PE	9.4 .370	2/BC	PVC-II w/Armor	15.32 .603	.310	52	29.5	-40 +80	5500	Use RG 224
74A	2.59 BC .1020	PE	9.4 .370	2/BC	PVC-IIA w/Armor	15.32 .603	.310	52	29.5	-40 +80	5500	Use RG 224
77A	1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	2/TC	PVC-IIA	11.43 .450	.195	48	50.0	-40 +80	8000 Peak	_
78A	1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	1/TC	PVC-IIA	10.67 .420	.149	48	50.0	-40 +80	8000 Peak	_
79	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-I w/Armor	11.76 .463	.136	_	10.0	-40 +80	1000	Low Capacitance
79A	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-I w/Armor	11.76 .463	.130	.125	10.0	-40 +80	1000	Low Capacitance
79B	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-IIA w/Armor	11.76 .463	.136	.125	10.0	-40 +80	1000	Low Capacitance
81	1.59 BC .0625	Magnesium Oxide G	8.15 .321	None	Copper Tube	8.26 .325	.172	50	37.0	250	3000	_
82	3.18 BC .1250	Magnesium Oxide G	16.51 .650	None	Copper Tube	19.05 .750	.698	50	36.0	250	5000	_
83	2.59 BC .1020	PE	6.1 .240	1/BC	PVC-I	10.29 .405	.120	35	44.0	-40 +80	2000	Low Impedance
84A	2.65 BC .1045	PE	17.27 .680	1/BC	PVC-IIA w/Lead Sheath	25.4 1.000	1.325	75	20.6	-40 +80	10,000	RG 35B with Special Armor
85A	2.65 BC .1045	PE	17.27 .680	1/BC	PVC-IIA w/Lead Armor	39.75 1.565	2.910	75	20.6	-40 +80	10,000	RG 84A with Special Armor
86	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE	7.62 .300 x 16. .650	51 None	None	7.62 .300 x 16. .650	51 .100	200	7.8	-55 +80	10,000	Twin Lead
87A	2.44 .0960 7/ 0.81 SC .0320	PTFE	7.11 .280	2/SC	FG Braid-V	10.8 .425	.180	50	29.4	-55 +250	5000	Use RG 225
88	1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	4/TC	PVC-I	13.08 .515	.211	48	50.0	-40 +80	10,000	_
88A	1.49 .0585 19/ 0.3 TC .0117	Ruber-E	7.32 .288	4/TC	PVC-IIA	13.08 .515	.211	48	50.0	-40 +80	10,000	_
88B	1.49 .0585 19/ 0.3 TC .0117	Rubber-E	7.32 .288	4/TC	Rubber-IV	14.35 .565	.238	48	50.0	-40 +80	10,000	
89	0.64 CCS .0253	Air-space PE	7.24 .285	1/BC	PVC-I	16.05 .632	.195	125	10.0	-40 +80	1000	Low Capacitance
90	1.53 .0603 7/ 0.51 SC .0201	PE	4.95 .195	3/SC, GS, SC	PVC-IIA	10.8 .425	_	50	30.8	-40 +80	3000	Excellent Shielding
93	5.08 .2000 19/ 1.02 BC .0400	Taped PTFE	14.55 .573	1/BC	FG Braid-V	18.03 .710	.475	50	29.4	-55 +250	10,000	Use RG 211A

Appendix D - Typical Coaxial Cable Specifications (Continued)

288

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

											Mox	
RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (lb/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
94	2.86 .1125 19/ 0.57 SC .0225	Taped PTFE	7.42 .292	2/BC	FG Braid-V	11.3 .445	.270	50	29.4	-55 +250	7000	Use RG 226
94A	3.23 .1270 19/ 0.65 SC .0254	Taped PTFE	9.4 .370	2/BC	FG Braid-V	12.7 .500	.445	50	29.4	-55 +250	7000	Use RG 226
100	1.87 .0735 19/ 0.37 BC .0147	PE	3.71 .146	1/BC	PVC-I	6.15 .242	.046	35	44.0	-40 +80	2000	Use up to 1000 MHz
101	1.63 BC .0641	Rubber	_	1/TC	—	14.94 .588	_	75	_	—	—	—
102	2 Cond. 2.05 BC .0808	Rubber	_	1/TC	_	27.64 1.088	_	140	_		_	_
108	2 Cond. 0.96 .0378 7/ 0.32 TC .0126	PE	2.01 .079 Each	1/TC	PVC-II	5.97 .235	.032	78	19.6	-40 +80	1000	Use RG 108A
108A	2 Cond. 0.96 .0378 7/ 0.32 TC .0126	PE	2.01 .079 Each	1/TC	PVC-IIA	5.97 .235	.032	78	19.6	-40 +80	1000	Balanced Line
111	2 Cond. 1.16 .0456 7/ 0.39 BC .0152	PE	7.24 .285	2/TC	PVC-II w/Armor	12.14 .478	.146	95	16.0	-40 +80	1000	Use RG 111A
111A	2 Cond. 1.16 .0456 7/ 0.39 BC .0152	PE	7.24 .285	2/TC	PVC-IIA w/Armor	12.14 .478	.146	95	16.0	-40 +80	1000	Use RG 22B w/Armor
114	0.18 CCS .0070	Air-space PE	7.24 .285	1/BC	PVC-I	10.29 .405	.087	185	6.5	-40 +80	1000	Use RG 114A
114A	0.18 CCS .0070	Air-space PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.087	185	6.5	-40 +80	1000	Low Capacitance
115	2.13 .0840 7/ 0.71 SC .0280	Taped PTFE	6.35 .250	2/BC	FG Braid-V	9.53 .375	.148	50	29.4	-55 +250	5000	Use RG 115A
115A	2.13 .0840 7/ 0.71 SC .0280	Taped PTFE	6.48 .255	2/BC	FG Braid-V	10.54 .415	.180	50	29.4	-55 +250	5000	Extra Flexible RG 225
116	2.44 .0960 7/ 0.81 SC .0320	PTFE	7.11 .280	2/SC	FG Braid-V w/Armor	12.7 .475	.198	50	29.4	-55 +250	5000	Use RG 227
117	4.78 BC .1880	PTFE	15.75 .620	1/BC	FG Braid-V	18.54 .730	.641	50	29.4	-55 +250	7000	Use RG 211A
117A	4.78 BC .1880	PTFE	15.75 .620	1/BC	FG Braid-V	18.54 .730	.641	50	29.4	-55 +250	7000	Use RG 211A
118	4.78 BC .1880	PTFE	15.75 .620	1/BC	FG Braid-V w/Armor	19.81 .780	.682	50	29.4	-55 +250	7000	Use RG 228A
118A	4.78 BC .1880	PTFE	15.75 .620	1/BC	FG Braid-V w/Armor	19.81 .780	.682	50	29.4	-55 +250	7000	Use RG 228A
119	2.59 BC .1020	PTFE	8.43 .332	2/BC	FG Braid-V	11.81 .465	.225	50	29.4	-55 +250	6000	Use up to 1000 MHz
120	2.59 BC .1020	PTFE	8.43 .332	2/BC	FG Braid-V	13.28 .523	.282	50	29.4	-55 +250	6000	RG 119 w/Armor
122	0.76 .0300 7/ 0.13 TC .0050	PE	2.44 .096	1/TC	PVC-IIA	4.06 .160	.016	50	29.4	-40 +80	1900	Use up to 1000 MHz

Appendix D - Typical Coaxial Cable Specifications (Continued)

Catalog 1307191 Revised 3-07

124

125

126

www.tycoelectronics.com

.0050 0.64 TCCS .0253

0.4 CCS

.0159

1.55 .0609 7/**0.52** HR .0203

> Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

3.43 .135

11.68

.460

4.7

.185

1/TC

1/BC

1/HR

Taped PTFE

Air-space PE

PTFE

Dimensions are shown for reference purposes only. Specifications subject to change.

6.1 .240

15.24

.600

7.11 .280

.210

.180

.070

73

150

50

FG Braid-V

PVC-IIA

FG Braid-V

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

20.3

7.8

29.4

-55 + 250

-40 + 80

-55 + 250

2300

2000

3000

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Use RG 140

Low

Capacitance

High Loss Cable

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
130	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE	11.99 .472	1/TC	PVC-I	15.88 .625	.220	95	17.0	-40 +80	3000	RG 57 w/ Twisted Cond.
131	2 Cond. 2.17 .0855 7/ 0.72 BC .0285	PE	11.99 .472	1/TC	PVC-I w/Armor	17.35 .683	.290	95	17.0	-40 +80	3000	Armored RG 130
133	0.72 BC .0285	PE	7.24 .285	1/BC	PVC-I	10.29 .405	.094	95	16.2	-40 +80	4000	Use RG 133A
133A	0.64 BC .0253	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.094	95	16.2	-40 +80	4000	95 Ohm Version RG 8
140	0.64 SCCS .0250	PTFE	3.71 1.46	1/SC	FG Braid-V	5.92 .233	.056	75	19.5	-55 +250	2300	See RG 302 for FEP Jacket
141	0.91 SCCS .0359	PTFE	2.95 .116	1/SC	FG Braid-V	4.83 .190	.036	50	29.4	-55 +250	1900	Use RG 141A
141A	0.99 SCCS .0390	PTFE	2.95 .116	1/SC	FG Braid-V	4.83 .190	.036	50	29.4	-55 +250	1900	See RG 303 for FEP Jacket
142	0.91 SCCS .0359	PTFE	2.95 .116	2/SC	FG Braid-V	4.95 .195	.047	50	29.4	-55 +250	1900	Use RG 142A
142A	0.99 SCCS .0390	PTFE	2.95 .116	2/SC	FG	4.95 .195	.047	50	29.4	-50 +250	1900	See RG 142B for FEP Jacket
142B	0.99 SCCS .0390	PTFE	2.95 .116	2/SC	FEP	4.95 .195	.047	50	29.4	-55 +250	1900	Standard Center Cond. Available
143	1.45 SCCS .0570	PTFE	4.7 .185	2/SC	FG Braid-V	8.26 .325	.114	50	29.4	-55 +250	3000	Use RG 143A
143A	1.5 SCCS .0590	PTFE	4.7 .185	1/SC	FG Braid-V	8.26 .325	.109	50	29.4	-55 +250	3000	See RG 304 for FEP Jacket
144	1.36 .0537 7/ 0.45 SCCS .0179	Air-space PE	7.24 .285	Copper Tube	FG Braid-V	10.41 .410	.137	75	19.5	-55 +250	5000	High Temp. RG 11A
145	2 Cond. 1.83 BC .0720	Air-space PTFE	_	1/BC	Lead/Tar	_	_	75	14.6	_	_	_
146	0.18 CCS .0070	PE	7.24 .285	1/BC	FG Braid-V	9.53 .375	.108	190	6.0	-55 +200	1000	Low Capacitance
147	6.35 BC .2500	PE	23.11 .910	1/BC	PVC-I w/Armor	49.2 1.937	_	52	29.5	-40 +80	14,000	RG 19U w/Armor
148	2.17 .0855 7/ 0.72 BC .0285	PTFE	7.24 .285	1/SC	PVC-I w/Armor	20.32 .800	_	52	29.5	-40 +80	4000	
149	1.22 .048 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.105	75	20.6	-40 +80	5000	Use RG 391
150	1.22 .048 7/ 0.4 TC .0159	PE	7.24 .285	1/BC	PVC-IIA w/Armor	11.76 .463	.112	75	20.6	-40 +80	5000	Use RG 392
156	2.17 .0855 7/ 0.72 TC .0285	PE and Cond. PE	7.24 .285	3/TC, GS, TC	PVC-IIA	13.72 .540	.211	50	32.0	-40 +80	10,000	Triaxial Pulse Cable
157	2.55 .1005 19/ 0.51 TC .0201	PE and Cond. PE	11.56 .455	3/TC, GS, TC	PVC-IIA	18.42 .725	.317	50	38.0	-40 +80	15,000	Triaxial Pulse Cable
158	5.05 .1988 37/ 0.72 TC .0284	PE and Cond. PE	11.56 .455	3/TC, GS, TC	PVC-IIA	18.42 .725	.380	25	78.0	-40 +80	15,000	Triaxial Pulse Cable
159	0.81 SC .0320	Taped PTFE	2.95 .116	1/SC	FG Braid-V	4.95 .195	.035	50	29.4	-55 +250	1900	Use RG 141
160	4 Cond. 1.8 .071 19/ 0.36 2TC, 2BC .0142	PE	8.18 .322	1/BC	PVC-I	26.8 1.055	_	125	12.0	-40 +80	3000	4 Cond. Balanced Line
161	0.3 .012 7/ 0.1 S Cad. BR .004	PTFE	1.45 .057	1/SC	Nylon	2.08 .082	.015	70	20.0	-60 +120	1000	Miniature
164	2.65 BC .1045	PE	17.27 .680	1/BC	PVC-IIA	22.1 .870	.490	75	20.6	-40 +80	10,000	RG 35B without Armor

290

www.tycoelectronics.com

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (lb/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
165	2.44 .0960 7/ 0.81 SC .0320	PTFE	7.24 .285	1/SC	FG Braid-V	10.41 .410	.121	50	29.4	-55 +250	5000	RG 225 w/One Braid
166	2.44 .0960 7/ 0.81 SC .0320	PTFE	7.24 .285	1/SC	FG Braid-V w/Armor	11.68 .460	.144	50	29.4	-55 +250	5000	RG 165 w/ Armor
174	0.48 .0189 7/0.16 CCS .0063	PE	1.52 .060	1/TC	PVC	2.54 .100	.008	50	30.8	-40 +80	1500	Miniature Data Transmission
174A	0.48 .0189 7/0.16 CCS .0063	PE	1.52 .060	1/TC	PVC-IIA	2.54 .100	.008	50	30.8	-40 +80	1500	Miniature Data Transmission
176	3.43 .135 Helix over Magnetic Core	PE	7.24 .285	1/Magnet Wire	PVC-I	10.29 .405	.120	2240	49.0	-40 +80	5000	—
177	4.95 BC .195	PE	17.27 .680	2/SC	PVC-IIA	22.73 .895	.470	50	30.8	-40 +80	11,000	High Frequency RG 218
178	0.3 .0120 7/0.1 SCCS .0040	PTFE	0.91 .036	1/SC	KEL-F	1.83 .072	.0054	50	29.4	-40 +150	1000	Use RG 178B
178A	0.3 .0120 7/0.1 SCCS .0040	PTFE	0.86 .034	1/SC	KEL-F	1.83 .072	.005	50	29.4	-40 +150	1000	Use RG 178B
178B	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	0.86 .034	1/SC	FEP-IX	1.83 .072	.0054	50	29.4	-55 +200	1000	High Strength Cond. Available
179	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	1.45 .057	1/SC	KEL-F	2.54 .100	.010	70	20.4	-55 +150	1200	Use RG 179B
179A	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	1.6 .063	1/SC	KEL-F	2.54 .100	.010	75	19.5	-40 +150	1200	Use RG 179B
179B	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	1.6 .063	1/SC	FEP-IX	2.54 .100	.010	75	19.5	-55 +200	1200	High Strength Cond. Available
180	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	2.62 .103	1/SC	KEL-F	3.56 .140	.019	93	15.4	-40 +150	1500	Use RG 180B
180A	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	2.59 .102	1/SC	KEL-F	3.56 .140	.019	95	15.4	-40 +150	1500	Use RG 180B
180B	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	2.59 .102	1/SC	KEP-IX	3.56 .140	.019	95	15.4	-55 +200	1500	High Strength Cond. Available
181	2 Cond. 1.21 .0477 7/ 0.4 BC .0159	PE	5.33 .210	2/Individual Inner Common Outer BC	PVS-IIA	16.25 .640	.198	125	12.0	-40 +80	3500	Balanced Line
182	2 of 19/ 0.36 BC .0142 2 of 19/ 0.17 TC .0066	4 Cores PE	2/ 8.43 .332 2/ 3.71 .146	Each Core 1/BC Overall Shield 1/BC	PVC-IIA each PVC-I overall	26.8 1.055	_	125 each	12.0 each	-40 +80	2300 3000	Special 4 Coaxial
183	6.38 BC .2510	PS Helix	16.05 .632	AI. Tube	None	19.05 .750	.380	50	23.0	-40 +80	1800	See Times AM-5034S
185	0.08 [.0031] Mag. Wire Helix on PE Core	Air-Space PE	4.78 .188	1/Magnet Wire	PVC-IIA	7.16 .282	_	2000	_	-40 +80	_	Delay Line Cable

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
187	0.3 .0120 7/ 0.1 SCCS .0040	PTFE	1.52 .060	1/SC	PTFE	2.67 .105	.010	75	19.5	-55 +250	1200	Use RG 179B
187A	0.3 .0120 7/0.1 SCCS .0040	PTFE	1.52 .060	1/SC	PTFE	2.67 .105	.010	75	19.5	-55 +250	1200	Use RG 179B
188	0.51 .0201 7/ 0.17 SCCS .0067	PTFE	1.52 .060	1/SC	PTFE	2.67 .105	.011	50	29.4	-55 +250	1200	Use RG 316
188A	0.51 .0201 7/ 0.17 SCCS .0067	PTFE	1.52 .060	1/SC	PTFE	2.67 .105	.011	50	29.4	-55 +250	1200	Use RG 316
189	6.38 BC .2510	PS Helix	16.05 .632	2/SC	PE-IIIA	22.23 .875	.570	50	23.0	-55 +80	3500	Use RG 389
190	1.49 .0585 7/ 0.3 TC .0117	Rubber H, J	9.65 .380	3/TC, GS, TC	Neoprene VIII	17.78 .700	.353	50	50.0	-55 +80	15,000	_
191	12.32 TC Braid .485	Rubber H, J, H	27.05 1.065	3/TC, GS, GS	Neoprene VIII	37.08 1.460	1.469	25	85.0	-55 +80	15,000	_
192	26.8 GS Tube 1.055 TC Braid	Butyl Rubber	_	3/TC, GS, GS	Rubber	55.88 2.200	_	12.5	175.0	-55 +80	15,000 Peak	_
193	26.8 GS Tube 1.055 TC Braid	Silicone Rubber	_	3/TC, GS, GS	Rubber	53.34 2.100	_	12.5	159.0	-55 +80	30,000 Peak	_
194	26.8 GS Tube 1.055 TC Braid	Silicone Rubber	_	3/TC, GS, GS	Rubber w/ Al. Armor	49.4 1.945	_	12.5	159.0	-55 +80	30,000 Peak	_
195	0.3 .0120 7/0.1 SCCS .004	PTFE	2.59 .102	1/SC	PTFE	3.68 .145	.020	95	15.4	-55 +250	1500	Use RG 180B
195A	0.3 .0120 7/0.1 SCCS .004	PTFE	2.59 .102	1/SC	PTFE	3.68 .145	.020	95	15.4	-55 +250	1500	Use RG 180B
196	0.3 .0120 7/0.1 SCCS .004	PTFE	0.86 .034	1/SC	PTFE	1.83 .072	.006	50	29.4	-55 +250	1000	Use RG 178B
196A	0.3 .0120 7/0.1 SCCS .004	PTFE	0.86 .034	1/SC	PTFE	1.83 .072	.006	50	29.4	-55 +250	1000	Use RG 178B
197	7.62 BC .300	PS Helix	19.25 .758	22.23 [.875] OD Al. Tube	None	22.23 .875	.500	50	22.0	-55 +80	2400 Peak	_
198	2.9 BC .1140	PS Helix	10.69 .421	12.7 [.500] OD Al. Tube	PE	15.24 .600	.155	70	16.0	-55 +80	1300 Peak	
199	5.31 BC .209	PS Helix	19.25 .758	22.23 [.875] OD Al. Tube	PE	25.78 1.015	.435	70	16.0	-55 +80	2400 Peak	_
200	0D- 10.29 .405 ID- 7.65 BC Tube .301	PS Helix	37.39 1.472	41.28 [1.625] OD AI. Tube	PE	44.83 1.765	.900	70	16.0	-55 +80	4600 Peak	
209	4.8 .189 19/ 0.96 SC .0378	Air-Space PTFE	12.7 .500	2/SC	SR and Polyester-IV	18.42 .725	.432	50	25.0	-55 +150	3200	Low Loss RG 211A
210	0.64 SCCS .0253	Air-Space PTFE	3.71 .146	1/SC	FG Braid-V	6.15 .242	.040	93	13.5	-55 +250	750	High Temp. Low Capacitance
211	4.83 BC .1900	PTFE	15.75 .620	1/BC	FG Braid-V	18.54 .730	.641	50	29.4	-55 +250	7000	High Temp. High Power
211A	4.83 BC .1900	PTFE	15.75 .620	1/BC	FG Braid-V	18.54 .730	.641	50	29.4	-55 +250	7000	High Temp. High Power
212	1.44 SC .0556	PE	4.7 .185	2/SC	PVC-IIA	8.43 .332	.083	50	29.4	-40 +80	3000	Use up to 10,000 MHz
213	2.26 .0888 7/ 0.75 BC .0296	PE	7.24 .285	1/BC	PVC-IIA	10.29 .405	.099	50	30.8	-40 +80	5000	Use up to 1000 MHz

292

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (lb/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
214	2.26 .0888 7/ 0.75 SC .0296	PE	7.24 .285	2/SC	PVC-IIA	10.0 .425	.126	50	30.8	-40 +80	5000	Use up to 10,000 MHz
215	2.26 .0888 7/ 0.75 .0296	PE	7.24 .285	1/BC	PVC-IIA w/Armor	11.76 .463	.121	50	30.8	-40 +80	5000	Armored RG 213
216	1.21 .0477 7/ 0.75 BC .0159	PE	7.24 .285	2/BC	PVC-IIA	10.8 .425	.114	75	20.6	-40 +80	5000	Use up to 1000 MHz
217	2.7 BC .106	PE	9.4 .370	2/BC	PVC-IIA	13.84 .545	.201	50	30.8	-40 +80	7000	Use up to 1000 MHz
218	4.95 BC .195	PE	17.27 .680	1/BC	PVC-IIA	22.1 .870	.460	50	30.8	-40 +80	11,000	Use up to 1000 MHz
219	4.95 BC .195	PE	17.27 .680	1/BC	PVC-IIA w/Armor	23.57 .928	.585	50	30.8	-40 +80	11,000	Armored RG 218
220	6.6 BC .260	PE	23.11 .910	1/BC	PVC-IIA	28.45 1.120	.740	50	30.8	-40 +80	14,000	Use up to 1000 MHz
221	6.6 BC .260	PE	23.11 .910	1/BC	PVC-IIA w/Armor	29.92 1.178	.925	50	30.8	-40 +80	14,000	Armored RG 220
222	1.41 .0556 High Res. Wire	PE	4.7 .185	2/SC	PVC-IIA	8.43 .332	.087	50	30.8	-40 +80	3000	High Attenuation
223	0.89 SC .035	PE	2.95 .116	2/SC	PVC-IIA	5.36 .211	.034	50	30.8	-40 +80	1900	Use up to 10,000 MHz
224	2.609 BC .106	PE	9.4 .370	2/BC	PVC-IIA w/Armor	15.32 .603	.310	50	30.8	-40 +80	7000	Armored RG 217
225	2.38 .0936 7/ 0.79 SC .0312	PTFE	7.24 .285	2/SC	FG Braid-V	10.92 .430	.180	50	29.4	-55 +250	5000	See RG 393 for FEP Jacket
226	3.23 .1270 19/ 0.65 SC .0254	Taped PTFE	9.4 .370	2/SC	FG Braid-V	12.7 .500	.445	50	29.4	-55 +250	7000	_
227	2.38 .0936 7/ 0.79 SC .0312	PTFE	7.24 .285	2/SC	FG Braid-V w/Armor	12.40 .488	.198	50	29.4	-55 +250	5000	Armored RG 225
228	4.83 BC .1900	PTFE	15.75 .620	1/BC	FG Braid-V w/Armor	20.02 .788	.682	50	29.4	-55 +250	7000	Armored RG 211
228A	4.83 BC .1900	PTFE	15.75 .620	1/BC	FG Braid-V w/Armor	20.02 .788	.682	50	29.4	-55 +250	7000	Armored RG 211A
229	2.44 .0960 7/ 0.81 SC .032	PTFE	7.24 .285	1/SC	FG Braid-V w/Armor	11.68 .460	.144	50	29.4	-55 +250	5000	Use RG 166
230	5.05 .1988 37/ 0.72 TC .0284	Rubber-D	11.56 .455	3/TC, GS, GS	Rubber-IV	18.8 .740	_	25	100.0	-40 +80	15,000	
231	0D- 4.11 .162 ID- 2.84 BC .112	Foam PE	11.43 .450	12.7 .500 OD Al. Tube	None	12.7 .500	.118	50	25.0	-55 +80	5000 Peak	RG 331 for Jacketed Cable
232	7.62 BC .300	PE Helix	19.25 .758	22.23 .875 OD Al. Tube	PE-IIIA	28.07 1.015	.570	50	22.0	-50 +80	2400 Peak	_
233	0D- 15.01 BC .591 ID- 12.22 .481	PS Helix	37.39 1.472	41.28 1.625 OD Al. Tube	PE-IIIA	44.83 1.765	1.050	50	22.0	-55 +80	4700 Peak	
234	OD- 29.39 BC 1.570 ID- 25.78 1.015	PS Helix	70.49 2.775	79.38 3.125 OD Al. Tube	PE-IIIA	83.69 3.295	3.110	50	22.0	-55 +80	8700 Peak	
235	2.16 .0852 7/ 0.72 .0284	Taped PTFE	5.72 .255	2/SC	SIL/DAC VI	11.43 .450	.160	50	29.5	-55 +250	5000	RG 115A 235 w/VI Jacket

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
236	4.11 BC .1620	PS Helix	10.69 .421	12.7 [.500] OD Al. Tube	None	12.7 .500	.165	50	24.0	-55 +80	1300 Peak	_
237	4.11 BC .1620	PS Helix	10.69 .421	12.7 [.500] OD Al. Tube	PE-IIIA	15.24 .600	.195	50	24.0	-55 +80	1300 Peak	—
238	—	_	—	—	—	—	—	—	—	—	—	Use RG 197/U
239	_	_	_		_		_	_	_	_	_	Use RG 232/U
240	0D- 15.01 BC .591 ID- 12.22 BC .481	PS Helix	36.07 1.420	41.28 1.625 OD Al. Tube	None	41.28 1.625	.930	50	22.0	-55 +80	4700	_
241	—	—	—	—	—	—	—	—	—	—	—	Use RG 233
242	0D- 29.39 1.157 ID- 25.78 1.0150	PS Helix	72.39 2.850	79.38 3.125 OD Al. Tube	None	79.3 3.125	2.700	50	22.0	-55 +80	8700 Peak	_
243	_	_	_				—					Use RG 234
244	2.59 BC .102	PS Helix	10.69 .421	12.7 [.500] OD Al. Tube	None	12.7 .500	.118	75	15.5	-55 +80	1200 Peak	—
245	2.59 BC .102	PS Helix	10.69 .421	12.7 [.500] OD Al. Tube	PE-IIIA	15.24 .600	.148	75	15.5	-55 +80	1200 Peak	_
246	4.78 BC .1880	PS Helix	19.25 .758	22.23 [.875] OD Al. Tube	None	22.23 .875	.348	75	15.2	-55 + 80	2200 Peak	—
247	4.78 BC .1880	PS Helix	19.25 .758	22.23 [.875] OD Al. Tube	PE-IIIA	25.78 1.015	.418	75	15.2	-55 +80	2200 Peak	—
248	OD- 9.5 BC .3740 ID- 6.96 27.40	PS Helix	37.39 1.472	41.28 1.625 OD AI. Tube	None	41.28 1.625	.948	75	15.0	-55 +80	4300 Peak	_
249	OD- 9.5 BC .3740 ID- 6.96 27.40	PS Helix	37.39 1.472	41.28 1.625	PE-IIIA	44.83 1.765	1.068	75	15.0	-55 +80	4300 Peak	_
250	18.59 BC .732 16.05 .632	PS Helix	72.39 2.850	79.38 3.125 OD AI. Tube	None	79.38 3.125	2.395	75	15.0	-55 +80	8500 Peak	_
251	18.59 BC .732 16.05 .632	PS Helix	72.39 2.850	79.38 3.125 OD AI. Tube	PE-IIIA	32.95 2.805	.175	75	15.0	-55 +80	8500 Peak	_
252	4.24 BC .1670	PE Tubes	11.58 .456	13.46 [.530] OD Al. Tube	None	13.46 .530	.225	50	24.0	-55 +80	1000	_
253	4.24 BC .1670	PE Tubes	11.58 .456	13.46 [.530] OD Al. Tube	PE	16.64 .655	.655	50	24.0	-55 +80	1000	—
254	7.9 BC .3110	PE Tubes	21.16 .833	24.21 [.953] OD Al. Tube	PE	27.94 1.100	.555	50	24.0	-55 +80	1860	_
255	7.9 BC .3110	PE Tubes	21.16 .833	24.21 [.953] OD Al. Tube	None	24.21 .953	.550	50	24.0	-55 +80	1860	_
256	OD- 7.9 SC .3110 ID- 6.48 .2550	PTFE Tubes	21.16 .833	24.21 .953 OD Al. Tube	None	24.21 .953	1.200	50	24.0	-55 +80	1860	_
257	OD- 15.39 .6060 ID- 1.23 BC .4860	PS Tubes	41.2 1.622	45.36 1.786 OD Al. Tube	None	45.36 1.786	1.380	50	24.0	-55 +80	3640	_
258	0D- 15.39 .6060 ID- 1.23 BC Tube .4860	PS Tubes	41.2 1.622	45.36 1.786 OD Al. Tube	PE	48.92 1.926	.100	50	24.0	-55 +80	3640	_
259	2.92 BC Tube .1150	PTFE Tubes	8.08 .318	9.91 [.390] OD Al. Tube	None	9.91 .390	.140	50	24.0	-55 +80	697	_
260	2.92 BC Tube .1150	PE Tubes	8.08 .318	9.91 [.390] OD Al. Tube	PE-IIIA	11.43 .450	.170	50	24.0	-55 +80	697	_
263	4.37 BC .1720	Air-Space PTFE	10.69 .421	Al. Tube	None	12.7 .500	.336	50	21.5	-40 +250	1300 Peak	_
264	4 Cond. 19/ 0.36 .0142 2 TC, 2 BC	PE	4.47 .176 e/core	2 TC, 2 BC BC Overall	PVC-IIA	19.05 .750	.327	36.8	41.0	-40 +80	2000	Use RG 264C

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

RF Coax	Connectors	
---------	------------	--

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
264A	4 Cond. 19/ 0.36 .0142 2 TC, 2 BC	PE	4.47 .176 e/core	2 TC, 2 BC BC Overall	PUR	19.05 .750	.327	36.8	41.0	-40 +80	2000	Use RG 264C
264C	4 Cond. 1.73 .068 2 BC, 2 TC	PE	4.72 .186 e/core	2 TC, 2 BC BC Overall	PUR	19.43 .765	—	40	38.4	-40 +80	2000	Watertight 4 Coax.
265	17.2 BC Tube .6770	PE Helix	40.08 1.578	Copper Clad Mild Steel Tube	PE-IIIA	52.58 2.070	.120	50	22.3	-40 +80	145 KW Peak	_
266	0.29 Cond. Over .0113 3.66 Mag. Core .144	PE	7.24 .285	75 Spiral Wound Cond. 68 BC & 7 are Insulated	PVC-I	10.16 .400		1530	53.0	-40 +80	5000 DC	Delay Line Cable 50 ns/ft
267	9.02 BC Tube .3550	PS Helix	—	Copper Clad Mild Steel Cor. Tubing	PE-IIIA	30.23 1.190	.234	50	22.2	-40 +80	44 KW Peak	—
268	4.09 BC .1610	PE Helix	8.89 .350	Corrugated BC Tube	None	12.65 .498	.430	50	23.0	-55 +80	10 KW Peak	_
269	ID- 7.29 .2870 OD- 9.09 BC .3580 Tube	PE Helix	20.19 .795	Corrugated BC Tube	None	23.53 1.005	.430	50	22.2	-55 +80	44 KW Peak	_
269A	OD- 7.29 .2870 ID- 9.09 BC .3580 Tube	PE Helix	20.19 .795	Corrugated BC Tube	None	23.53 1.005	.875	50	22.2	-55 +80	44 KW Peak	_
270	ID- 14.94 .5880 OD- 17.48 BC .6880 Tube	PE Helix	40.08 1.578	Corrugated BC Tube	None	46.48 1.830	.875	50	22.3	-55 +80	145 KW Peak	_
270A	ID- 14.94 .5880 OD- 17.48 BC .6880 Tube	PE Helix	40.08 1.578	Corrugated BC Tube	None	46.48 1.830	.125	50	22.3	-55 +80	145 KW Peak	—
279	0.64 .0250 19/ 0.13 SCCS .0050	Air-space PTFE	2.79 .110	1/SC	FG Braid-V	3.68 .145	.200	75	19.5	-55 +250	Extra Flex. High Temp. Cable	Extra Flex. High Temp. Cabl
280	2.91 BC .1144	Taped PTFE	8.31 .327	2/SC	FEP-IX	11.89 .468	.400	50	25.4	-55 +200	3000	Low Loss High Frequency
281	4.8 .1890 19/ 0.96 SC .0378	Taped PTFE	12.7 .500	2/SC	Sil./DAC-VI	19.05 .750	.031	50	25.4	-55 +150	4000	Low Loss High Power
282	0.64 SC .0253	Irradiated PE	2.51 .099	2/SC	FEP	5.08 .200	.145	54.5	28.2	-40 +150	4500	_
283	1.49 .0585 19/ 0.3 SC .0117	Rubber-D	7.31 .288	2/SC	Sil.	12.07 .475	.410	46	50.0	-55 +150	8000	_
284A	5.59 BC .220	PE Helix	20.19 .795	Corrugated BC Tube	None	25.53 1.005	.430	75	15.0	-55 +80	29 KW	_
285A	2.9 BC .1140	PTFE Helix	20.19 .795	Corrugated BC Tube	None	25.53 1.005	.720	100	13.0	-55 +200	22 KW Peak	_
286	OD- 10.92 .4300 ID- 9.14 BC .3600 Tube	PE Helix	39.88 1.570	Corrugated BC Tube	None	46.48 1.830	.750	75	15.1	-55 +80	100 KW Peak	—
287	5 BC .1970	PE Helix	39.88 1.570	Corrugated BC Tube	None	46.48 1.830	3.000	100	13.5	-55 +80	73 KW Peak	_
288	0D- 8.46 .3330 ID- 5.64 BC .2221 Tube	PE Helix	75.18 2.960	95.25 CCS 3.750	None	95.25 3.750	3.000	50	21.6	-40 +80	440 KW Peak	_
289	0D- 20.83 .8200 ID- 18.8 CCS .7400 Tube	PE Helix	75.18 2.960	95.25 CCS 3.750	None	95.25 3.750	1.040	75	14.7	-40 +80	290 KW Peak	
292	10.92 BC Tube .4300	PE Helix	39.88 1.570	46.48 [1.8300] Corr. BC Tube	PE and Flooding Comp.	50.8 2.000	.160	75	15.1	-55 +80	100 KW Peak	
293	2.69 BC .106	PE	9.53 .375	1/SC	PE-IIIA	13.84 .545	.160	50	30.8	-55 +80	7000	Use RG 293A

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
293A	2.69 BC .106	PE	9.4 .370	1/SC	PE-IIIA	13.84 .545	.205	50	30.8	-55 +80	7000	Watertight RG 217
294	2 Cond. 2.05 .0808 1 BC, 1 TC	PE	11.99 .472	1/TC	PE-IIIA	16 .630	.205	95	16.3	-55 +80	3000	Use RG 294A
294A	2 Cond. 2.05 .0808 1 BC, 1 TC	PE	11.99 .472	1/SC	PE-IIIA	16 .630	.420	95	16.3	-55 +80	3000	Watertight RG 130
295	4.95 BC .1950	PE	17.27 .680	1/SC	PE-IIIA	22.73 .895	_	50	30.8	-55 +80	11,000	Watertight RG 218
296	5.97 .2352 37/ 0.85 SC .0336	Silicone Rubber	23.01 .906	1/SC	Neoprene	30.23 1.190	_	50	36.4	-55 +80	13,800	_
297	0D- 9.02 .3550 ID- 7.29 BC .2870 Tube	PFTE Helix	20.19 .795	Corrugated BC Tube	None	25.53 1.005	.090	50	21.4	-55 +200	44 KW Peak	_
298	15.32 .6030 7/ 0.51 CCS .0201	PE	2.92 .115	None	Foam PE	16.51 .650	.056	_	_	-55 +80	_	Buoyant Per MIL-C-22667
301	1.55 .0609 7/ 0.52 HR .0203	PTFE	4.7 .185	1/HR	FEP-IX	6.23 .245	.031	50	29.4	-55 +200	3000	FEP Jacketed RG 126
302	0.64 SCCS .0250	PTFE	3.71 .146	1/SC	FEP-IX	5.11 .201	.030	75	19.5	-55 +200	2300	FEP Jacketed RG 140
303	0.99 SCCS .0390	PTFE	2.95 .116	1/SC	FEP-IX	4.32 .170	.088	50	29.4	-55 +200	1900	FEP Jacketed RG 141A
304	1.5 SCCS .0590	PTFE	4.7 .185	2/SC	FEP-IX	7.11 .280	_	50	29.4	-55 +200	300	FEP Jacketed RG 143A
305	0D- 10.92 .4300 ID- 9.14 .3600 Tube	FEP	39.88 1.570	46.48 BC Tube 1.830	PE-IIIA	50.55 1.990	.545	75	14.4	-55 +80	2720	_
306A	4.39 BC .1730	Foam PE	20.35 .801	22.23 Al. Tube .8750	PE-IIIA	25.78 1.015	.070	75	16.5	-55 +80	5700	Per MIL-C-23806
307	0.74 .0290 19/0.15 SC .0058	Foam PE	3.71 .146	2/SC PUR Interlayer	PE-IIIA	6.86 .270	.070	75	16.7	-55 +80	1000	Triax Use to 100 MHz
307A	0.74 .0290 19/ 0.15 SC .0058	Foam PE	3.71 .146	2/SC PUR Interlayer	PE-IIIA	6.86 .270	.060	75	16.7	-55 +80	1000	Triax Use to 100 MHz
316	0.51 .0201 7/ 0.17 SCCS .0067	PTFE	1.52 .060	1/SC	FEDP-IX	2.59 .102	.012	50	29.4	-55 +200	1200	FEP Jacketed RG 188A
317	2 Cond. 2.21 .0870 7/ 0.74 BC .0290	FEP	11.33 .446	1/TC	Neoprene	18.03 .710	_	95	15.4	-55 +80	10,000	Water Blocked
318	OD- 9.09 BC .3580 Tube ID- 7.29 .2870	PE Helix	20.19 .795	25.53 1.005 Corr. BC Tube	PE-IIIA	28.58 1.125	.530	50	22.0	-55 +80	44 KW Peak	_
319	OD- 17.48 BC .6880 Tube ID- 14.94 .5580	PE Helix	39.88 1.570	46.48 1.830 Corr. BC Tube	PE-IIIA	50.8 2.000	1.040	50	22.0	-55 +80	145 KW Peak	
321	OD- 28.96 1.1400 Corr. BC Tube	PE Helix	_	79.39 2.850 Corr. BC Tube	None	72.39 2.850	1.210	50	21.7	-55 +80	320 KW Peak	—
322	0D- 28.96 1.1400 Corr. BC Tube	PE Helix	_	79.39 2.850 Corr. BC Tube	PE & Flood Comp.	77.22 3.040	1.780	50	21.7	-55 +80	320 KW Peak	_

296

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Appendix D - Typical Coaxial Cable Specifications	(Continued)

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
323	7.92 BC Tube .312	Foam PE	_	24.89 .980 Corr. BC Tube	PE & Flood Comp.	26.92 1.060	.420	50	25.6	-55 +80	1480	_
324	7.92 BC Tube .312	Foam PE	_	24.89 .980 Corr. BC Tube	None	24.89 .980	.320	50	25.6	-55 +80	1480	_
325	2.54 .1000 19/ 0.51 SC AI. .0200	PE Spline	6.6 .260	2/SC Strip Braids	PUR	8.89 .350	.10	50	26.3	-55 +80	750	Low Loss
326	5.08 .2000 19/ 1.02 SC AI. .0400	PE Spline	13.97 .550	2/SC Strip Braids	PUR	17.7 .697	.24	50	26.3	-55 +80	1700	Low Loss
327	8.13 .3200 19/ 1.63 SC AI. .0640	PE Spline	21.34 .840	2/SC Strip Braids	PUR	25.65 1.010	.55	50	26.3	-55 +80	2500	Low Loss
328	12.32 TC Braid .4850	Rubber H.J.H.	27.05 1.065	3/TC, GS, TC	Neoprene	37.08 1.460	1.469	25	85.0	-55 +80	20,000	—
329	1.49 .0585 19/ 0.3 TC .0117	Rubber H.J.H.	9.65 .380	3/TC, GS, TC	Neoprene	17.78 .700	.353	50	50.0	-55 +80	15,000	_
330	SC	Foam PE	_	1/SC	_	6.15 .242	_	50	25.0	_	_	_
331	4.11 BC .1620	Foam PE	11.43 .450	12.7 Al. Tube .500	PE-IIIA	15.24 .600	.187	50	25.0	-55 +80	2500	Jacketed 231 Solid Conducto
332	7.11 BC .2800	Foam PE	20.35 .801	22.23 Al. Tube .8750	None	22.23 .875	.466	50	25.0	-55 +80	4500	Per MIL-C-2380
333	7.11 BC .2800	Foam PE	20.35 .801	22.23 Al. Tube .8750	PE-IIIA	25.78 1.015	.548	50	25.0	-55 +80	4500	Jacketed RG 33
334	2.49 BC .0980	Foam PE	11.43 .450	12.7 Al. Tube .500	None	12.7 .500	.109	75	17.0	-55 +80	2500	Per MIL-C-2380
335	2.49 BC .0980	Foam PE	11.43 .450	12.7 Al. Tube .500	PE-IIIA	15.88 .625	.143	75	17.0	-55 +80	2500	Jacketed RG 33
336	4.39 BC .1730	Foam PE	20.35 .801	22.23 Al. Tube .8750	None	22.23 .875	.315	75	17.0	-55 +80	4000	Per MIL-C-2380
360	6.17 BC .2430	Foam PE	17.17 .676	19.05 Al. Tube .7500	PE-IIIA	20.95 .825	.397	50	25.0	-55 +80	4000	Per MIL-C-2380
366	4.06 .1600	Foam PE	_	13.72 .540 Corr. BC Tube	PE-IIIA	15.75 .620		50	62.6	-55 +80	4000	
367	Corrugated BC Tube	PE Helix	—	12.7 .5000 Corr. BC Tube	PE-IIIA	132.08 5.2000	4.590	50	21.7	-55 +80	830 KW Peak	—
369	2.97 BC .1170	PE Tubes	8.08 .318	9.91 Al. Tube .390	PE-IIIA	11.94 .470	.140	50	24.0	-55 +80	700	—
370	2.97 BC .1170	PE Tubes	8.08 .318	9.91 Al. Tube .390	None	9.91 .390	.100	50	24.0	-40 +80	700	
374	0.72 BC .0285	PE	4.06 .160	None	Foam PE	16.51 .650	.097	_	_	-55 +80		Buoyant Antennna
376	7.92 BC Tube .3120	Foam PE	—	Corr. Al. Tube	PE-IIIA	26.92 1.060	.390	50	26.0	-55 +80	6000	_
377	4.19 SC Tube .1650	PTFE Tubes		13.46 Al. Tube .5300	None	13.36 .530	.170	50	24.0	-55 +250	1000	
378	18.11 BC Tube .7130	PE Helix	—	46.48 1.830 Corr. Al. Tube	PE-IIIA	50.8 2.000	.620	50	22.1	-55 +80	145 KW Peak	_
383	2 Cond. 1.02 .0403 2000 lb. Break	PE	_	None	Foam PE	16.51 .650	—	100	—	-55 +80	_	Exper. Buoyant Twisted Pair
384	1.29 BC .0508	PE		1/Flat BC Braid Waterproofed	Foam PE	16.51 .650	—	50	30.8	-55 +80	_	Buoyant Antenni 600 psig.
385	3.89 SC .1530	Semi-Solid PTFE	10.8 .425	12.7 Corr. Al. .500	Optional	16.76 .660	.178	50	25.0	-55 +250	1500	Low Loss No Press. Req.

Catalog 1307191 Revised 3-07 Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

297

www.tycoelectronics.com

RG/U Type Cable	Inner Conductor	Dielectric Material	DOD	Number/Type of Shielding Braids	Jacket Material	0.D.	Weight (Ib/ft)	Nom. Imped. (Ohms)	Nom. Cap pf/ft	Max. Operating Temp. (C°)	Max. Operating Voltage (Volts RMS)	Comments
386	1.29 CCS .0508	PE	_	None Non-hosing	Foam PE	16.51 .650	_	_	_	-55 +80	_	Buoyant Antennna 400 lb. Break
388	CS	PE	_	11.28 .444 Max. SC	PE-IIIA	13.84 .545	_	50	30.8	-55 +80	_	Watertight See RG 14A
389	6.35 BC AI. .2500	PE Spline	16.13 .635	2/SC	PE-IIIA	22.23 .875	.336	50	22.8	-55 +80	2000	Low Loss Replaces RG 189
391	1.22 .048 7/ 0.4 TC .0159	Cond. PE and PE	7.24 .285	1/TC	PVC-IIA	10.29 .405	.092	72	_	-55 +80	5000	Low Noise Cable
392	1.22 .048 7/ 0.4 TC .0159	Cond. PE and PE	7.24 .285	1/TC	PVC-IIA w/Armor	12.07 .475	.114	72	_	-55 +80	5000	Armored RG 391
393	2.38 .0936 7/ 0.79 SC .0312	PTFE	7.24 .285	2/SC	FEP-IX	9.91 .390	.165	50	29.4	-55 +200	5000	Moistureproof RG 225
397	2.44 .096 7/ 0.81 SC .032	Air-space PTFE	6.86 .270	2/SC	FEP-IX	8.89 .350	.125	50	28.0	-55 +200	2000	Low Loss RG 393
400	0.98 .0385 19/0.2 SPC .0077	PTFE	2.95 .116	2/SC	FEP-IX	4.95 .195	.050	50	29.3	-55 +200	1900	
401	1.64 SPC .0645	PTFE	5.46 .215	6.35 OD .250 Copper Tube	None	6.35 .250	.081	50	29.3	-40 +125	3000	Semirigid
402	0.91 SCCS .0360	PTFE	3.02 .119	3.58 OD .141 Copper Tube	None	3.58 .141	.032	50	29.3	-40 +125	2500	Semirigid
403	0.3 SCCS .012 7/0.1 .004	PTFE	0.86 .034	2/SC FEP Interlayer	FEP-IX	2.95 .116	.0075	50	29.3	-55 +200	2500	Triaxial RG 178B
404	0.3 SCCS .012 7/0.1 .004	PTFE and Cond. PTFE	0.86 .034	1/SC	FEP-IX	1.83 .072	.0054	50	31.5 Max.	-55 +200	2000	Low Loss RG 178B
405	0.51 SCCS .0201	PTFE	1.68 .066	2.18 OD .086 Copper Tube	None	2.19 .0865	.015	50	29.4	-40 +125	1500	Semirigid

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 Tyco Electronics RF Coax Connectors

Appendix E - Maximum Power Handling Capabilities for Cables

(Average Input Power in Watts)

RG/U				F	requency in M	Hz			
Type Cable	10	50	100	200	400	1,000	3,000	5,000	10,000
5, 5A, 5B	2,000	800	550	350	230	125	60	40	22
8, 8A, 10A, 213, 215	3,700	1,300	850	540	350	190	95	65	37
9, 9A, 9B, 214	3,700	1,300	850	540	350	190	95	65	37
11, 11A, 12, 12A, 13, 13A, 216	2,500	1,000	650	400	260	150	70	50	26
217	6,000	2,000	1,200	800	480	260	120	85	50
22, 22B	1,700	650	430	280	190	110	50	38	20
55, 55A, 55B, 223	800	310	205	137	90	53	28	20	10
58, 58B	730	280	180	125	85	50	25	17	—
58A, 58C	650	225	170	110	75	44	22	15	
59, 59A, 59B	1,300	480	310	200	135	77	40	27	15
62, 62A, 71, 71A, 71B	1,300	480	310	200	135	77	40	27	15
62B	1,150	420	280	180	120	69	35	25	14
115, 115A, 165, 225, 393	25,000	9,500	6,300	4,300	2,800	1,700	880	620	350
108, 108A	340	145	100	70	50	30	15	—	—
122	540	205	140	90	60	35	18	12	_
140, 141, 141A, 142, 142B, 302, 303, 400, 402	9,000	3,500	2,400	1,600	1,100	650	350	245	140
143, 143A	11,500	4,600	3,200	2,100	1,450	850	460	330	190
144	25,000	9,500	6,300	4,300	2,800	1,700	880	620	350
161, 179, 179A, 179B, 187, 187A	1,600	780	570	420	310	200	110	76	41
174, 174A	170	72	50	36	25	16		_	_
178, 178A, 178B, 196, 196A	710	340	240	170	123	78	41	28	14
180, 180A, 180B, 195, 195A	2,500	1,100	800	570	400	250	135	93	50
188, 188A, 316	1,250	600	450	330	240	160	80	57	30
210	8,500	3,300	2,300	1,600	1,100	620	310	220	140

Note: Values above 3 GHz vary considerably depending on construction.

Conditions

Ambient: 40°C Altitude: Sea level Center Conductor Temperature: 80°C for polyethylene 200°C for PTFE

Catalog 1307191 Revised 3-07 www.tycoelectronics.com **RF Coax Connectors**

Appendix F - Nominal Loss Characteristics for Cables

(Decibels per Hundred Feet)

RG/U				F	requency in M	Hz			
Type Cable	10	50	100	200	400	1,000	3,000	5,000	10,000
5, 5A, 5B	.80	1.40	2.90	4.30	6.40	11.00	22.00	30.00	52.00
8, 8A, 10A, 213, 215	.66	1.50	2.20	3.20	4.60	9.00	19.00	28.00	47.00
9, 9A, 9B, 214	.66	1.50	2.20	3.20	4.60	9.00	19.00	28.00	47.00
11, 11A, 12, 12A, 13, 13A, 216	.66	1.50	2.20	3.20	4.60	9.00	19.00	28.00	
217	.41	1.00	1.40	2.10	3.10	5.80	13.00	19.00	31.00
22, 22B	1.20	2.80	4.20	6.30	9.50	—	—	—	—
55, 55A, 55B, 223	1.35	3.00	4.30	6.00	8.80	16.50	36.00	51.00	85.00
58, 58B	1.20	3.10	4.60	7.00	10.00	17.50	38.00	—	—
58A, 58C	1.40	3.30	4.90	7.30	11.00	20.00	41.00	—	
59, 59A, 59B	1.10	2.30	3.30	4.70	6.70	11.50	25.50	41.00	
62, 62A, 71, 71A, 71B	.90	1.90	2.80	3.70	5.20	8.50	18.40	29.50	—
62B	.90	2.10	3.00	4.30	6.10	10.50	23.50	36.00	
115, 115A, 165, 225, 393	.60	1.40	2.10	3.10	4.50	7.50	14.00	21.00	35.00
108, 108A	2.30	5.20	7.50	11.00	16.00	26.20	54.00	—	—
122	1.60	4.40	6.90	11.00	16.60	29.20	57.20	89.00	—
140, 141, 141A, 142, 142B, 302, 303, 400, 402	1.20	2.70	3.90	5.50	8.00	13.00	26.00	36.00	62.00
143, 143A	.85	1.80	2.50	3.80	5.70	9.70	18.10	26.10	40.70
144	.38	1.00	1.60	2.30	3.80	7.00	15.10	—	
161, 179, 179A, 179B, 187, 187A	5.00	7.90	9.80	12.70	15.80	25.00	43.00	62.50	135.00
174, 174A	3.80	6.50	8.90	12.00	17.50	31.00	64.30	97.00	185.00
178, 178A, 178B, 196, 196A	5.30	10.00	13.30	20.00	27.50	45.00	78.00	115.00	172.00
180, 180A, 180B, 195, 195A	3.10	4.20	5.10	7.30	10.40	16.50	36.00	49.50	89.00
188, 188A, 316	3.80	7.90	11.50	15.00	20.00	30.00	58.00	79.00	133.00
210	.23	.58	.85	1.30	1.90	3.10	6.50	9.00	15.00

Note: Values above 3 GHz vary considerably depending on construction.

Conditions

Ambient: 20°C

Tyco Electronics

Appendix G - Glossary of Terms

A

₹ Tyco

Electronics

ambient The atmospheric conditions surrounding a given item. Normally in terms of factors which influence or modify, such as temperature, humidity, etc. **amplitude** The magnitude of variation in a changing quantity from its zero value. The word requires modification - as with adjectives such as peak, maximum, rms, etc. - to designate the specific amplitude in question.

arc voltage voltage that continues to pass through a surge protector during activation of GDT(approx. 20 volts)

attenuation A reduction in power. It occurs naturally during wave travel through lines, waveguides, space or a medium such as water. It may be produced intentionally by placing an attenuator in a circuit. The amount of attenuation is generally expressed in decibels per unit of length.

В

back mounted A connector attached to the inside of a panel or box with its mounting flanges inside the equipment.

bayonet coupling A quick coupling device for plug and receptacle connectors. Pins projecting from the outside of the cylindrical receptacle engage with corresponding cam slots in the bayonet plug.

bellmouth Flared at the mouth. The rear of a properly crimped wire barrel will have a slight flare (bellmouth) to relieve the strain on the wire strands as they leave the area of high compression and take their natural "lay". A bellmouth condition may also be present in front of the wire barrel.

black box A term used to refer to any assembly or subassembly, usually electronic, that can readily be installed or removed from a larger system.

BNC Connector A radio frequency connector covered by Military Specification. It has an impedance of 50 or 75 ohms, and is designed to operate in the 0 to 4 GHz frequency range. It features quick connect/disconnect by pin and cam bayonet coupling.

body Main or largest portion of a connector to which other portions are attached.

braid A weave of metal fibers used as a shield covering for an insulated conductor or group of insulated conductors. When flattened it may be used as a grounding strap.

broad-band E Interference generated over a wide range of frequencies (e.g., automotive ignition noise).

bulkhead A term used to define a mounting style of connectors. Bulkhead connectors are designed to be inserted into a panel cutout from the rear (component side) of the panel.

C

cable Either a standard conductor, with or without insulation and other coverings, or a combination of conductors insulated from each other.

cable assembly A completed cable and its associated hardware.

capacitance The property of an electrical conductor (dielectric in a capacitor) that permits the storage of energy as a result of electrical displacement. The basic unit of capacitance is the farad, however, measurement is more commonly in microfarads or picofarads.

cavity A metallic enclosure in some types of tubes and circuits within which resonant fields may be excited at the microwave frequency to which the cavity is tuned. Usually referred to as resonant cavity. See also: contact cavity.

characteristic impedance The ratio of voltage to current at any point along a transmission line on which there are no standing waves.

circular mil area (CMA) A unit of area equal to the area of a circle whose diameter is 1 mil (0.001 inch). Used chiefly in specifying cross-sectional areas of conductors. (See Tyco Electronics Brochure No. 4402-8, Computing Circular Mil Area for Tyco Electronics Terminals and Splices).

closed entry contact A female contact designed to prevent the entry of a pin or probing device having a cross-sectional dimension (diameter) greater than the mating pin.

coaxial cable A transmission line consisting of two conductors concentric with and insulated from each other. In its flexible form it consists of either a solid or stranded center conductor surrounded by a dielectric. A braid is then woven over the dielectric to form an outer conductor. A weatherproof plastic covering, usually vinyl, is placed on top of the braid.

connector A coupling device employed to connect conductors to one circuit with those of another circuit. Used to provide rapid connect/disconnect mating with pc boards, posts or another connector.

connector assembly Includes housing and contact plus additional components such as hardware used to hold the assembly together and/or make the assembly a functional connector.

contact An electrically conductive component designed for use in a multicircuit connector.

contact cavity A defined hole in the connector insert or housing into which the contact must fit. See also: cavity.

contact durability The number of insertion and withdrawal cycles that a connector must be capable of withstanding while remaining within the performance levels of the applicable specification.

contact engaging and separating force Force required to either engage or separate contacts. Values are generally established for maximum and minimum forces.

contact inspection hole A hole, perpendicular to the cylindrical rear portion of screw machined contacts, used to check the depth to which wire has been inserted into the barrel.

contact resistance Measurement of electrical resistance of mated contacts when assembled in a connector under typical service use. Electrical resistance is determined by measuring from the rear of the electrical area of one contact to the rear of the contact area of the mating contact (excluding both crimps) while carrying a specified test current.

contact shoulder The flanged or enlarged portion of a contact that prevents it from being over-inserted into the appropriate contact cavity. The shoulder may also contribute to proper orientation and stability with the connector housing.

contact, two-piece A contact made of two separate parts joined by swedging, brazing or other means of fastening to form a single contact. While this provides the mechanical advantages of two metals, it also has the inherent electrical disadvantage of difference in conductivity.

corona A discharge of electricity appearing as a bluish-purple glow on the surface of, and adjacent to, a conductor when the voltage gradient exceeds a certain critical value. It is caused by the ionization of surrounding air by high voltage.

crimp The final configuration of a terminal barrel after the necessary compression forces have been applied to cause a functional union between the terminal barrel and the wire.

crimp height A top to bottom measurement of the crimped barrel, using a crimp height comparator in the prescribed manner. (Refer to Tyco Electronics Instruction Sheet 7424).

crimping dies A term used to identify the shaping tools that, when moved toward each other, produce a certain desirable shape to the barrel of the terminal or contact that has been placed between them. Crimping dies are often referred to as die sets or as die inserts.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

crimping head Tooling containing jaws and linkage for use in pneumatic or hydraulic powered units to crimp loose-piece contacts/terminals that may be too large for hand tool applications.

crimping tool A term commonly used to identify a hand held mechanical device that is used to crimp a contact, terminal or splice.

crosstalk A magnetic or electrostatic coupling which causes the unwanted transfer of energy from one circuit (disturbing circuit) to another circuit (disturbed circuit)

current rating The maximum continuous electrical flow of current recommended for a given situation. It is expressed in amperes.

cycle One complete sequence of values of an alternating quantity, including a rise to maximum in one direction and return to zero; a rise to maximum in the opposite direction and return to zero. The number of cycles occurring in one second is called the frequency.

D

daisy chain A cable assembly with common wires jumpering three or more connections/connectors. The term is also used as a verb, implying to connect in jumper manner.

dB Abbreviation — see decibel.

D.C. sparkover voltage defined as the maximum voltage across a device before it discharges the energy to ground when subjected to a slowly rising voltage ramp. A rate of rise of 100V/s is usually chosen for testing purposes.

decibel A unit expressing the ratio of two voltages, currents or powers. It is equal to 20 times the common logarithm of the ratio of two voltages across or two currents through equal loads, or 10 times the common logarithm of the two powers. One decibel is approximately the smallest change in audible power that can be recognized by the human ear.

die closure Term used to designate a crimping area (crimping chamber) when the dies are fully closed or bottomed. Die closure is checked with go/no go plug gage to insure that the crimp produced by the tooling satisfies the crimp height specification.

dielectric A material that serves as an insulator. The amount of resistance to voltage in a given insulation.

dielectric withstanding voltage The maximum potential gradient that a dielectric material can withstand without failure.

discontinuity Rated interconnection: a broken connection (open circuit) or the loss of a specified connection characteristic. Transient phenomena: Short term (temporary) interruption or unacceptable variation in current or voltage.

dissipation Unusable or lost energy, such as the production of unused heat in a circuit.

distortion An unwanted change or addition to a signal or waveform when it is amplified. This definition excludes noise which is an extraneous signal superimposed on the desired signal.

dummy load A dissipative device used at the end of a transmission line or waveguide to convert transmitted energy into heat, so essentially no energy is radiated outward or reflected back to its source.

dust cap A device attached to a connector to provide protection against dust and foreign debris.

Е

electromagnetic compatibility (EMC) The ability of an electronic device to operate in its intended environment without its performance being affected by EMI and without generating EMI that will affect other equipment.

electromagnetic interference (EMI) Unwanted electrical or electromagnetic energy that causes undesirable responses, degrading performance or complete malfunctions in electronic equipment. See also: noise.

electromotive force (emf) See voltage.

environmentally sealed A unit is provided with gaskets, seals, grommets, potting or other means to keep out moisture, dust, air or dirt which might reduce or impair its performance.

F

feedthrough A connector or terminal block, usually having double-ended terminals, which permits distribution and bussing of electrical circuits. Also used to describe a bushing in a wall or bulkhead, separating compartments at different pressure levels, with terminations on both sides.

ferrule A short tube used to make solderless connections to shielded or coaxial cable. Also molded into the plastic inserts of multiple contact connectors to provide strong, wear-resistant shoulders on which contact retaining springs can bear.

flange A projection extending from or around the periphery of a connector and having holes that provide for mounting the connector to a panel or to a mating connector.

frequency modulation (fm) A scheme for modulating a carrier frequency in which the amplitude remains constant but the carrier frequency is displaced in frequency proportionally to the amplitude of the modulating signal. An fm broadcast is practically immune to atmospheric and manmade interference.

fretting corrosion A form of excellerated oxidation that appears at the interface of contacting materials undergoing slight cyclic relative motion. All non-nobel metals (tin) are susceptible to some degree of fretting corrosion and will suffer contact resistance increases.

front mounted A connector is said to be front mounted when it is attached to the outside of the mating side of a panel. A front mounted connector can only be installed or removed from the outside of the equipment.

G

gas discharge tube (GDT) hermetically sealed device containing an inert gas.

GHz See gigahertz.

giga A prefix meaning one billion (10⁹).

gigahertz (GHz) One billion cycles per second (10⁹ cps).

glow mode condition in which the GDT continues to conduct after an impulse passed. Characterized by a visible glow in the device caused by over-heating.

ground A connection, intentional or accidental, between an electrical circuit and the earth or some conducting body (e.g. chassis) serving in place of earth.

Η

heat-shrinkable A type of plastic material that has been cross-linked. A term describing tubes, sleeves, caps, boots, films or other forms of plastic which shrink to encapsulate, protect or insulate connections, splices, terminations and other configurations.

hermetic Airtight, impervious to external influence, as in a hermetic package. Often used to describe metal-to-metal solder or weld-sealed packages.

302

Catalog 1307191 Revised 3-07

www.tycoelectronics.com are stan

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

hermetic seal Hermetically sealed connectors are usually multiple contact connectors where the contacts are bonded to the connector by glass or other materials and permits maximum leakage rate of gas through the connector of 1.0 micron ft./hr. at one atmosphere pressure for special applications.

hertz (Hz) International standard term for cycles per second. Named after the German physicist Heinrich R. Hertz (e.g., 60 cycles per second is equal to 60 hertz or 60 Hz).


impedance (Z) The total opposition offered by a component or circuit to the flow of alternating or varying current. Impedance is expressed in ohms and is similar to the actual resistance in a direct current circuit. In computations, impedance is handled as a complex ratio of voltage to current.

I

impedance match A condition in which the impedance of a component or circuit is equal to the internal impedance of the source, or the surge impedance of a transmission line. This gives maximum transfer of energy from the source to the load, as well as minimum reflection and distortion.


impulse discharge current

is defined as the peak current of an impulse which the device can withstand ten times (5 of each polarity at fixed time intervals) without substantially affecting device performance. The test normally used to determine this capacity uses the 8/20ms waveform as depicted below where T1=8ms and T2=20ms.





defined as the maximum level of voltage across a device before it discharges the energy to ground when subjected to a voltage impulse. The three common waveform profiles used to determine this capacity are:



inductance One cause of reactance. An electromagnetic phenomenon in which the expanding and collapsing of a magnetic field surrounding a conductor or device tends to impede changes in current. The effects of inductance become greater as frequencies increase. The basic unit for inductance is the henry.

input impedance The impedance that exists between the input terminals of an amplifier or transmission line when the source is disconnected. The circuit, signal level and frequency must be specified.

insertion loss The loss in load power due to the insertion of a component, connector or device at some point in a transmission system. Generally expressed in decibels as the ratio of the power received at the load before insertion of the apparatus, to the power received at the load after insertion.

insulation crimp The area of a terminal splice or contact that has been formed around the insulation of a wire.

insulation grip The ability of certain crimped terminals to hold firmly in place both the conductor and a small portion of insulation. This prevents the conductor from being exposed due to insulation receding away from the terminal.

insulation resistance The electrical resistance between two conductors separated by an insulating material.

interface The two surfaces of a multiple-contact connector that face each other when the connector is assembled.

interference An electrical or electromagnetic disturbance that causes undesirable response in electronic equipment.

J

jack A connecting device into which a plug can be inserted to make circuit connections. The jack may also have contacts which open or close to perform switching functions when the plug is inserted or removed. See also: receptacle.

L

line impedance Impedance as measured across the terminals of a transmission line; frequently the characteristic impedance of the line.

М

matched impedance The coupling of two circuits in such a way that the impedance of one circuit equals the impedance of the other.

mate Two join two connectors in a normal engaging mode.

maximum discharge current defined as the peak current of an impulse which the device can withstand once without substantially affecting device performance.

mega (M) A prefix meaning one million (10⁶).

microwave That portion of the electromagnetic spectrum lying between the far infrared and conventional radio frequency range. The microwave frequency range extends from 1 GHz to 300 GHz. Microwaves are usually used in point-to-point communications because they are easily concentrated into a beam.

Military Specification Military requirements. The demand imposed upon a system to meet a military operational need.

mismatch The condition in which the impedance of a source does not match or equal the impedance of the connected load. This reduces power transfer by causing reflection.

Ν

 narrow-band EMI generated from a device operating at a specific and limited range of frequencies. See also: electromagnetic interference (EMI).
 N Connector A large radio frequency connector covered by Military Specification. It has an impedance of 50 ohms and is designed to operate in the 0 to 11 CMF trequency consected acumulant and is physic.

the 0 to 11 GHz frequency range. It has a threaded coupling and is physically larger than a TNC connector. **noise** An extraneous signal in an electrical circuit, capable of interfering

with the desired signal. Classes of noise include burst of popcorn noise, intermediate frequency noise at low audio frequencies, white (thermal) noise, etc. Signals from power supply or ground line coupled into an amplifier output may be considered noise.

0

"O" crimp An insulation support crimp for open barrel terminals and contacts. In its crimped form it resembles an "O" and conforms to the shape of the round wire insulation. "O" crimp is also used to describe the circumferential crimps used on COAXICON ferrules.

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

ohm The unit of measurement for electrical resistance. A circuit is said to have a resistance of one ohm when an applied emf of one volt causes a current of one ampere to flow.

Ρ

panel mount A method of fixing a connector to a board, panel or frame. The mounted connector is usually the receptacle or female connector. The plug or male connector is usually the removable portion.

pcb Abbreviation: see printed circuit board.

permeability (chemical) The passage or diffusion (or rate of passage) of a gas, vapor, liquid or solid through a barrier without physically or chemically affecting it.

permeability (magnetic) The measure of how much better a material is than air as a path for magnetic lines of force. Air is assumed to have a permeability of 1.

plug In coaxial RF connectors the plug is usually the movable portion, and is usually attached to a cable or removable assembly. Plugs mate with receptacles, jacks, outlets, etc.

printed circuit board An insulating board serving as a base for a printed circuit. When the printing process is completed, the board may include printed components, as well as printed wiring.

propagation delay Time required for an electronic digital device, or transmission network to transfer information from its input to its output.

propagation delay time The time between the application of a digital input waveform and the corresponding change in input waveform. It is measured between reference points on the waveforms. The time is generally different for positive-going and negative-going waveforms.

prototype A model suitable for use in the complete evaluation of form, design and performance.

pulse A change in the level, over a relatively short period of time, of a signal whose value is normally constant.

pulse width The length of time that the pulse voltage is at the transient level. Electronic pulse widths are usually in the millisecond (10^{-3}) , microsecond (10^{-6}) or nanosecond (10^{-9}) range.

R

receptacle In coaxial RF connectors, the receptacle is usually the fixed or stationary portion that is mounted to the panel. In shell-type, multiple-contact connectors the receptacle usually contains the pin contacts and is mounted on the "cold" side of a circuit such as in a drawer or black box. Receptacles mate with plugs. See also: jack.

residual impulse defined as the voltage that will pass through the device prior to activation of the GDT.

residual voltage defined as the small amount of voltage left on the line after an impulse passes.

resonance A frequency at which captive reactance and inductive reactance are equal and therefore cancel one another's effects.

RF Abbreviation for radio frequency.

RG/U Symbol used to designate coaxial cables that are made to Government Specification (e.g., RG 58U; in this designation the "R" means radio frequency, the "G" means Government, the "58" is the number assigned to the government approval, and the "U" means it is a universal specification). **rise time** The time required for a component or logic circuit to change from the quiescent to the transient state when an input is applied. (i.e. elapsed time between application of input and attainment of full output level). **rms** Abbreviation for root mean square.

root mean square The effective value of an alternating current, corresponding to the direct current value that will produce the same heating effect.

S

screw machine contact A contact which is machined from solid bar stock.

semi-rigid A cable containing a flexible inner core and a relatively inflexible sheathing.

sheath The outer covering of a jacket over the insulated conductors to provide mechanical protection for the conductors. Also known as the external conduction surface of a shielded transmission line.

shield/shielding (cable) A conducting envelope, composed of metal strands, which enclose a wire, group of wires or cable so constructed that substantially every point on the surface of the underlying insulation is at ground potential or at some predetermined potential with respect to ground.

shield/shielding (circuit) The metal sleeving surrounding one or more of the conductors in a wire circuit to prevent interference, interaction or current leakage. Shielding protects a circuit against crosstalk.

shock (mechanical) (1) An abrupt impact applied to a stationary object. (2) An abrupt or nonperiodic change in position, characterized by suddenness, and by the development of substantial internal forces.

SHV Abbreviation for standard high voltage.

sine wave A wave which can be expressed as the sine of a linear function of time, space or both. A waveform, often viewed on an oscilloscope, of a pure alternating current or voltage.

skin effect The tendency of alternating currents to flow near the surface of the conductor, thus being restricted to a small part of the total cross-sectional area. This effect increases the resistance and becomes more marked as the frequency rises.

sleeve The insulated or metallic covering over the barrel of a terminal.

solder contact A contact or terminal having a cup, hollow cylinder, eyelet or hook to accept a wire for a conventional soldered termination.

standard high voltage (SHV) A quick connect/disconnect connector series employing a bayonet lock coupling and designated to operate safely up to 5000 volts AC. It is the industry standard connector specified by the National Bureau of Standards (NBS) for high voltage use by the Atomic Energy Commission (AEC).

standing-wave Distribution of current and voltage on a transmission line, resulting from two sets of waves traveling in opposite directions.

standing wave ratio The ratio between maximum and minimum current or voltage along a line. It is a measure of the mismatch between the load and the line. It is equal to 1 when the line impedance is perfectly matched to the load. (In which case the maximum and minimum are the same, as current and voltage do not vary along the line). The perfect match would be a 1 to 1 ratio.

super high frequency (shf) The Federal Communications Commission designation for the band from 3,000 to 30,000 MHz in the radio spectrum.

Т

tensile The amount of axial load (longitudinal stress) required to break or pull the wire from the crimped barrel of the terminal, splice or contact.

www.tycoelectronics.com are sta

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

tensile strength The greatest longitudinal stress that a substance or union can bear without tearing or pulling apart. In crimped terminations, it is the greatest longitudinal stress that a terminal can bear without the wire separating from the terminal.

thermal shock The effect of heat or cold applied at such a rate that nonuniform thermal expansion or contraction occurs within a given material or combination materials. The effect can cause inserts and other insulation materials to pull away from metal parts.

time-delay A circuit that delays the transmission of an impulse for a definite and desired period of time.

TNC Connector A radio frequency connector covered by Military Specification. It has an impedance of 50 ohms and is designed to operate in a 0 to 11 GHz frequency range. Reliability is assured by a threaded coupling that can be safely wired to prevent accidental disconnect.

U

UG Symbol used to describe coaxial connectors that were made to a Government specification. This specification is now obsolete.

ultra-high frequency (uhf) A Federal Communications Commission designation for the band from 300 to 3000 MHz on the radio spectrum. In television – channels 14 to 83 or 470 to 890 MHz.

V

very high frequency (vhf) A Federal Communications Commission designation for the band from 30 to 300 MHz on the radio spectrum.
 voice-frequency (vf) Any frequency within that part of the radio frequency range essential to speech transmission of a commercial quality (i.e., 300 to 3400 Hz). Also referred to as telephone frequency.

volt (V) The unit of measurement for electromotive force (emf). It is equivalent to the force required to produce 1 ampere through a resistance of 1 ohm.

voltage (E) The term most often used to designate electrical pressure that exists between two points and is capable of producing a flow of current when a closed circuit is connected between the two points. Voltage is measured in volts, millivolts, microvolts and kilovolts. The terms electromotive force (emf), potential, potential difference and voltage drop are often referred to as voltage.

voltage drop The voltage developed across a component or conductor by the flow of current through the resistance or impedance of that component or conductor.

voltage hold over refers to the maximum line voltage at which recovery of the GDT to its inactive state will take place within

a specified period of time (normally 150ms) after an induced lightning pulse (normally 10/1000ms) has been applied.

VSWR Abbreviation for voltage standing wave ratio. Also see: standing wave ratio.

W

wavelength The distance between two points which are in phase on adjacent waves. It is the distance traveled by the wave in the same span of one cycle. Electromagnetic waves (both light and radio) have a speed in space of about 300,000,000 meters (186,000 miles) per second. Thus wavelength in meters is equal to 300,000,000 divided by frequency.

Z

Z Letter symbol used to represent impedance in ohms.

Catalog 1307191 Revised 3-07


Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

www.tycoelectronics.com

E Tyco Electronics

RF Coax Connectors

RF Coaxial Solutions for Communications Equipment




306

Catalog 1307191 D Revised 3-07 ar www.tycoelectronics.com ar

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Wireless Base Station

Radio base station cabinets demand packaging that combines high power r.f. signals, high speed digital data, and analog signals. Cabinet input/output connections are provided by N Series and 7/16 connectors. Plug-in r.f. modules require Blindmate, DIN inserts, and panel mount connectors. Transceiver modules utilize MCX, and SSMT board and cable connectors for board to board and panel to board applications. Finally, both semi-rigid and flexible RG cable assemblies route signals throughout the entire cabinet.




Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Carrier Rack Equipment

For today's fast paced Carrier Equipment market, Tyco Electronics offers a broad line of RF interconnect products that meet demanding customer requirements for CATV, telecom and data transmission applications. Connectors, cable assemblies, and applicator tooling are available for applications ranging from central office to customer premise environments, 50 or 75 ohms, from rack based equipment to set top boxes. Styles range from standard miniature RF connectors such as F series, BNC and TNC to subminiature RF connectors such as SMA, SMB, SMC and Blindmate connectors, to Micro miniature MMCX, SSMT and SMT/QuickGrip products. SIEMAX connectors provide multi-positional surface mount technology RF connection for pcb and panel applications, and offer superior packaging density. Between Series adapters are available, along with connectors meeting international DIN and IEC standard interfaces. High performance GHz range BNC connectors meet the needs for faster signaling.



G Series Connectors, Page 98

F Series Connectors, Page 93

308

Revised 3-07 www.tycoelectronics.com

Catalog 1307191

and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are in millimeters

Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803


Chassis, NIC Card and Set Top Box

Coaxial interconnects have evolved in the enterprise market place over the years. The BNC interfaces that once dominated the Ethernet premise installations to coax products that provide high speed access to the carrier infrastructure.

In today's environment, Network Interface Cards (NIC) still feature Capacitively Decoupled BNC connectors with builtin chip capacitors to reduce noise and ground loop currents.

For the infrastructure, the standard coaxial interfaces to the infrastructure include both 50 and 75 ohm BNC connectors. The BNC family features numerous styles including cable plugs and jacks, adapters and printed circuit board connectors. To address manufacturability, we offer the board mount in SMT, wave solder, and press fit. More recently, the SMB interface is the one of choice for improved density and is available in both commercial and MIL-type. Again, our portfolio has a wide variety of configurations to address your system requirements.

Lastly, as broadband CATV becomes more prevalent for internet access in cable modems, our family of F connectors offer a high performance solution.



Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Non-RoHS to RoHS Compliant Part Number Cross Reference

Part No.	RoHS Compliant Part No.	Non-RoHS R Part No.	OHS Compliant Part No.	Non-RoHS R Part No.	oHS Compliant Part No.	Non-RoHS R Part No.	oHS Complian Part No.
13126-1	Exempt	222092-1	5222092-1	225669-2	5225669-2	227764-2	5227764-2
13127-1	Exempt	222092-3	5222092-3	225699-1	5225699-1	227818-1	5227818-
59980-1	Exempt	222093-1	5222093-1	225886-1	5225886-1	227820-1	5227820-
69477-1	Exempt	222117-1	5222117-1	225886-4	5225886-4	227839-1	5227839-
69710-1	Exempt	222132-1	5222132-1	225886-5	5225886-5	228217-1	5228217-
148385-1	5148385-1	222165-2	5222165-2	225886-7	5225886-7	228226-1	5228226-
148386-1	5148386-1	222420-1	5222420-1	225974-1	5225974-1	228226-3	5228226-
189721-1	Exempt	222462-1	5222462-1	225974-2	5225974-2	228435-1	5228435-
220015-1	Exempt	222506-1	5222506-1	225974-5	5225974-5	228596-1	5228596-
220220-2	Exempt	222506-5	5222506-5	226978-1	5226978-1	228596-2	5228596-
220221-2	Exempt	222506-6	5222506-6	226978-3	5226978-3	228596-3	5228596-
220222-2	Exempt	225089-4	5225089-4	226990-1	5226990-1	228596-4	5228596-
220222-2	· · · ·	225092-8	5225089-4	226990-3			
-	Exempt				5226990-3	228596-5	5228596-
221111-1	5221111-1	225349-9	5225349-9	226990-6	5226990-6	228618-1	5228618-
221123-2	5221123-2	225361-2	5225361-2	226993-1	5226993-1	228618-2	5228618-
221128-1	5221128-1	225361-4	5225361-4	226993-2	5226993-2	228618-3	5228618-
1-221128-0	1-5221128-0	1-225361-2	1-5225661-2	226993-3	5226993-3	228618-4	5228618-
1-221128-1	1-5221128-1	225363-1	5225363-1	226993-6	5226993-6	228618-5	5228618-
1-221128-7	1-5221128-7	225392-2	5225392-2	227079-5	5227079-5	228686-1	5228686-
2-221128-1	2-5221128-1	225395-1	5225395-1	227079-6	5227079-6	228979-5	5228979-
2-221128-3	2-5221128-3	225395-2	5225395-2	227079-7	5227079-7	228979-6	5228979
2-221128-7	2-5221128-7	225395-3	5225395-3	1-227079-1	1-5227079-1	228979-7	5228979
3-221128-1	3-5221128-1	225395-6	5225395-6	1-227079-6	1-5227079-6	228980-5	5228980
221162-1	5221162-1	225395-7	5225395-7	1-227079-9	1-5227079-9	228980-6	5228980
221185-1	5221185-1	225395-8	5225395-8	2-227079-2	2-5227079-2	228980-7	5228980
221185-2							
	5221185-2	1-225395-0	1-5225395-0	4-227079-3	4-5227079-3	307581-1	Exem
221185-3	5221185-3	2-225395-0	2-5225395-0	5-227079-3	5-5227079-3	311386-1	Exem
221185-5	5221185-5	4-225395-1	4-5225395-1	6-227079-1	6-5227079-1	311386-2	Exem
221185-7	5221185-7	4-225395-2	4-5225395-2	6-227079-7	6-5227079-7	311386-3	Exem
221185-8	5221185-8	225396-1	5225396-1	6-227079-8	6-5227079-8	311392-1	Exem
221185-9	5221185-9	225396-2	5225396-2	8-227079-2	8-5227079-2	311395-1	Exem
1-221185-0	1-5221185-0	225396-7	5225396-7	1-227086-0	1-5227086-0	311396-1	Exem
1-221185-8	1-5221185-8	225397-1	5225397-1	227161-1	5227161-1	312067-1	Exem
2-221185-9	2-5221185-9	225397-2	5225397-2	227161-2	5227161-2	312253-1	Exem
3-221185-1	3-5221185-1	225397-7	5225397-7	227161-3	5227161-3	312253-2	Exem
221198-1	5221198-1	225398-1	5225398-1	227161-6	5227161-6	312317-1	Exem
221199-1	5221199-1	225398-3	5225398-3	227161-7	5227161-7	2-329444-1	2-5329444
221199-2	5221199-2	225398-6	5225398-6	227161-9	5227161-9	2-329444-2	2-5329444
221199-5	5221199-5	225398-7	5225398-7	227169-5	5227169-5	2-329445-1	2-5329445
				-			
221221-1	5221221-1	225398-8	5225398-8	227169-7	5227169-7	2-329446-1	2-5329446
221221-2	5221221-2	1-225398-5	1-5225398-5	227169-8	5227169-8	2-329452-2	2-5329452
221221-5	5221221-5	225554-6	5225554-6	227222-1	5227222-1	2-329456-1	2-5329456
221221-7	5221221-7	1-225554-1	1-5225554-1	227222-2	5227222-2	2-329458-1	2-5329458
221244-1	5221244-1	225555-2	5225555-2	227222-3	5227222-3	329517	532951
221325-1	5221325-1	225555-6	5225555-6	227222-6	5227222-6	2-330061-1	2-5330061
221336-3	5221336-3	225555-7	5225555-7	227426-1	5227426-1	2-330062-1	2-5330062
221336-4	5221336-4	225555-8	5225555-8	227661-1	5227661-1	2-330063-1	2-5330063
221402-2	5221402-2	225557-6	5225557-6	227671-1	5227671-1	2-330358-2	2-5330358
221402-4	5221402-4	225559-2	5225559-2	227673-1	5227673-1	330876	533087
221506-2	5221506-2	225559-8	5225559-8	227676-1	5227676-1	330878	533087
221506-3	5221506-3	225661-1	5225661-1	227677-1	5227677-1	331175	533117
221506-5	5221506-5	225661-2	5225661-2	227699-1	5227699-1	331178	533117
221629-1	5221629-1	1-225661-3	1-5225661-3	227699-2	5227699-2	331182	533118
221629-2	5221629-2	1-225661-6	1-5225661-6	227699-3	5227699-3	331238	533123
221629-4	5221629-4	225662-2	5225662-2	227716-3	5227716-3	332215	533221
221629-5	5221629-5	1-225662-8	1-5225662-8	227726-1	5227726-1	332225-3	5332225
	5221629-6	225664-1	5225664-1	227726-2	5227726-2	332225-5	5332225
221629-6	011.010.0						
221629-6	1-5221629-6	225664-2	5225664-2	227726-3	5227726-3	332225-6	5332225
221629-6 1-221629-6		225664-2 1-225664-2	5225664-2 1-5225664-2	227726-3 227755-1	5227726-3 5227755-1	332225-6 332225	
	1-5221629-6						5332225 533222 533234

310

Catalog 1307191 Revised 3-07

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets www.tycoelectronics.com are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Non-RoHS to RoHS Compliant Part Number Cross Reference (Continued)

Non-RoHS Part No.	RoHS Compliant Part No.						
413194-2	5413194-2	413969-2	5413969-2	415189-1	5415189-1	1055441-1	Exempt
413311-1	5414311-1	413986-1	5413986-1	415205-1	5415205-1	1055442-1	Exempt
413364-2	5413364-2	414088-1	5414088-1	415214-1	5415214-1	1055443-1	Exempt
413366-2	5413366-2	414094-2	5414094-2	415216-1	5415216-1	1055444-1	Exempt
413476-2	5413476-2	414105-1	5414105-1	415218-5	5415218-5	1055445-1	Exempt
413506-1	5413506-1	414160-5	5414160-5	415226-1	5415226-1	1055446-1	Exempt
413515-2	5413515-2	414168-1	5414168-1	415232-4	5415232-4	1055447-1	Exempt
413515-3	5413515-3	414168-3	5414168-3	415232-7	5415232-7	1055448-1	Exempt
413515-7	5413515-7	414168-4	5414168-4	415242-2	5415242-2	1055449-1	Exempt
413515-8	5413515-8	414168-5	5414168-5	415242-6	5415242-6	1055450-1	Exempt
413515-9	5413515-9	414168-6	5414168-6	415248-1	5415248-1	1055451-1	Exempt
413524-2	5413524-2	414170-1	5414170-1	415248-7	5415248-7	1055454-1	Exempt
413524-5	5413524-5	414170-2	5414170-2	415252-1	5415252-1	1055474-1	Exempt
413557-1	5413557-1	414171-3	5414171-3	415252-2	5415252-2	1055475-1	Exempt
413557-2	5413557-2	414173-3	5414173-3	415252-2	5415252-3	1055476-1	
		-					Exempt
413558-1	5413558-1	414194-1	5414194-1	415252-4	5415252-4	1055477-1	Exempt
413558-2	5413558-2	414215-1	5414215-1	415255-1	5415255-1	1055500-1	Exempt
413558-3	5413558-3	414217-1	5414217-1	415255-2	5415255-2	1055831-1	Exempt
413558-5	5413558-5	414265-3	5414265-3	415255-3	5415255-3	1055832-1	Exempt
413588-2	5413588-2	414284-2	5414284-2	415255-4	5415255-4	1055833-1	Exempt
413588-4	5413588-4	414305-1	5414305-1	415276-2	5415276-2	1055834-1	Exempt
413588-8	5413588-8	414337-1	5414337-1	415302-1	5415302-1	1055836-1	Exempt
413588-9	5413588-9	414338-1	5414338-1	415302-2	5415302-2	1055837-1	Exempt
1-413588-0	1-5413588-0	414352-1	5414352-1	415322-2	5415322-2	1055838-1	Exempt
413589-1	5413589-1	414363-3	5414363-3	415332-1	5415332-1	1055839-1	Exempt
413589-2	5413589-2	414363-4	5414363-4	415379-1	5415379-1	1055840-1	Exempt
413589-3	5413589-3	414363-5	5414363-5	415381-1	5415381-1	1055841-1	Exempt
413589-5	5413589-5	414363-8	5414363-8	415406-2	5415406-2	1055842-1	Exempt
413589-7	5413589-7	414367-2	5414367-2	415417-1	5415417-1	1055843-1	Exempt
413589-8	5413589-8	414373-1	5414373-1	415419-1	5415419-1	1057088-1	6057088-1
413589-9	5413589-9	414394-1	5414394-1	415485-1	5415485-1	1057094-1	6057094-1
1-413589-0	1-5413589-0	414409-1	5414409-1	415485-2	5415485-2	1057116-1	6057116-1
1-413589-1	1-5413589-1	414414-1	5414414-1	415485-3	5415485-3	1057159-1	6057159-1
1-413589-6	1-5413589-6	414459-1	5414459-1	415487-1	5415487-1	1057165-1	6057165-1
413590-3	5413590-3	414460-1	5414460-1	415487-2	5415487-2	1057176-1	6057176-1
413590-4	5413590-4	414493-4	5414493-4	415487-3	5415487-3	1059632-1	6059632-1
413590-8	5413590-8	414553-1	5414553-1	415520-1	5415520-1	1059665-1	6059665-1
413591-1	5413591-1	414651-3	5414651-3	415569-2	5415569-2	1061002-1	6061002-1
413592-2	5413592-2	414666-1					
		-	5414666-1	415632-1	5415632-1	1061035-1	6061035-1
413592-6	5413592-6	414758-1	5414758-1	415632-2	5415632-2	1061092-1	6061092-1
413592-9	5413592-9	414758-2	5414758-2	415633-1	5415633-1	1061094-1	6061094-1
1-413592-1	1-5413592-1	414758-3	5414758-3	415634-1	5415634-2	1213890-1	Exempt
413631-1	5413631-1	414907-1	5414907-1	415634-2	5415634-2	1274020-1	6274020-1
413631-2	5413631-2	414946-2	5414946-2	415683-1	5415683-1	1274032-1	6274032-1
413631-3	5413631-3	414946-3	5414946-3	415712-1	5415712-1	1274045-1	6274045-1
413760-1	5413760-1	414946-5	5414946-5	415779-1	5415779-1	1274072-1	6274072-1
413760-3	5413760-3	414946-6	5414946-6	415832-1	5415832-1	1274084-1	6274084-1
413760-8	5413760-8	415006-1	5415006-1	447648-3	5447648-3	1274086-1	6274086-1
413760-9	5413760-9	415006-2	5415006-2	448103-2	5448103-2	1274096-1	6274096-1
413771-1	5413771-1	415020-1	5415020-1	603995-1	Exempt	1274124-2	6274124-2
413771-3	5413771-3	415024-1	5415024-1	603995-2	Exempt	1274127-1	6274127-1
413779-3	5413779-3	415024-3	5415024-3	603995-3	Exempt	1274220-1	6274220-1
2-413779-4	2-5413779-4	415025-1	5415025-1	603995-5	Exempt	1274291-1	6274291-1
413879-1	5413879-1	415025-2	5415025-2	603995-6	Exempt	1274291-2	6274291-2
413879-2	5413879-2	415046-1	5415046-1	856402-1	Exempt	1274314-1	6274314-1
413933-1	5413933-1	415085-1	5415085-1	887000-1	5887000-1	1274314-1	6274315-1
413959-1	5413959-1	415103-1	5415103-1	887046-1	5887046-1	1274313-1	6274313-1
413959-1							
	5413959-3	415103-2	5415103-2	887078-1	5887078-1	1274360-1	6274360-1
413959-4	5413959-4	415105-1	5415105-1	887089-1	5887089-1	1274425-2	6274425-2
413959-5	5413959-5	415105-2	5415105-2	1055439-1	Exempt	1274431-1	6274431-1
413959-6	5413959-6	415187-1	5415187-1	1055440-1	Exempt	1274532-1	6274532-1

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Non-RoHS Part No.	RoHS Compliant Part No.						
1311164-1	Exempt	1361137-1	6361137-1	1-1393524-1	Exempt	1393696-2	6-1393696-2
1312079-1	6312079-1	1361138-1	1361138-1	2-1393524-4	Exempt	1393696-7	6-1393696-7
1312113-1	6312113-1	1361139-1	6361139-1	2-1393524-6	6 Exempt	1402314-1	1402314-1
1312121-1	6312121-1	1362765-1	6362765-1	2-1393524-7	Z Exempt	1408026-1	6408026-1
1312123-1	6312123-1	1363524-1	6363524-1	1393665-1	6-1393665-1	1408027-1	6408027-1
1312124-1	6312124-1	1363525-1	6363525-1	1-1393665-4	· —	1408028-1	6408028-1
1312137-1	1312137-1	1363526-1	6363526-1	1-1393665-5	j	1408030-1	6408030-1
1312138-1	6312138-1	1363527-1	6363527-1	1-1393665-6	<u> </u>	1408032-1	6408032-1
1312139-1	6312139-1	1393488-3	Exempt	1-1393665-7		1408033-1	6408033-1
1328873-1	6328873-1	1393488-4	Exempt	2-1393670-1	_	1408036-1	6408036-1
1329818-1	6329818-1	1393524-1	Exempt	2-1393670-2	2 —	1408037-1	6408037-1
1329819-1	1329819-1	1393524-4	Exempt	2-1393670-3	3 —	1408038-1	6408038-1
1331959-1	6331959-1	1393524-5	Exempt	2-1393670-4	· _	1725637-1	Exempt

Non-RoHS to RoHS Compliant Part Number Cross Reference (Continued)

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

M/A-COM to Tyco Electronics Part Number Cross Reference

M/A-COM T Part No.	yco Electronics Part No.	M/A-COM Part No.	Tyco Electronics Part No.	M/A-COM Part No.	Tyco Electronics Part No.	M/A-COM Part No.	Tyco Electronic Part No.
127669-92	1311164-1	2052 5674 0	2 1052902-1	2598 5208 5	4 1055843-1	3104 7985 00) 1057679- ⁻
127893-98	1402314-1	2054 1201 0	2 1052978-1	2598 5342 5	4 1221286-1	3106 7941 00) 1057697- ⁻
2001 5003 02	1050525-1	2054 1231 0	2 1052982-1	2598 5438 5	4 1088313-1	3106 7985 00) 1057699- ⁻
2001 5031 02	1050542-1	2054 1241 0	2 1052986-1	2831 7316 0	2 1056436-1	3152 0000 10) 1057775- ⁻
2001 5032 02	1050548-1	2056 5006 0	2 1053092-1	2831 7341 0	2 1056438-1	3152 1201 10) 1057780- ⁻
2001 5385 02	1050598-1	2058 5029 0	2 1053222-1	2831 7388 0	2 1056443-1	3180 2242 00) 1057841-
2001 5395 02	1050602-1	2062 0000 0	0 1053354-1	2834 7316 0	2 1056445-1	3180 2302 00) 1057843-
2001 5443 02	1050611-1	2064 0000 0	0 1053378-1	2834 7341 0	2 1056447-1	3180 2320 00) 1057845- ⁻
2001 7188 02	1050721-1	2080 0000 0	0 1053488-1	2834 7358 0	2 1056450-1	3182 2240 00) 1057853-
2001 7641 02	1050740-1	2081 0000 0	2 1053635-1	2834 7388 0	2 1056452-1	3182 2243 00) 1057857-
2001 7941 02	1050757-1	2081 2301 0	0 1053646-1	2837 7316 0	2 1056456-1	3184 2240 00) 1057908-
2001 7985 02	1050770-1	2082 2249 0		2837 7388 0	2 1056462-1	3280 2224 00	
2002 5015 00	1050854-1	2082 2700 0		2902 7947 6		3280 2240 00	
2002 5016 00	1050859-1	2082 5133 0		2902 7985 6		3281 2223 00	
2002 7188 02	1050903-1	2084 0000 0		2908 7947 6		3282 2223 00	
2002 7188 02	1050996-1	2086 0000 0		2908 7985 6		3282 2240 00	
2004 7 188 02	1051005-1	2080 0000 0		2965 5006 6		3282 2240 00	
2004 7685 02	1051007-1	2088 0000 0		2980 0000 6		3284 2240 00	
2006 5010 00	1051046-1	2098 5206 5		2980 2240 0		3680 2240 00	
2006 5013 00	1051052-1	2098 5207 5		2981 2241 0		3680 2242 00	
2006 7941 00	1051081-1	2098 5208 5		2982 2240 0		3682 2241 00	
2006 7985 00	1051085-1	2098 5209 0		2982 2241 0		3682 2242 00	
2007 7188 02	1051140-1	2098 5210 0		2998 5001 0		3684 2240 00) 1058675-
2007 7641 02	1051145-1	2098 5211 0	2 1055444-1	2998 5002 0	2 1056722-1	4503 7685 02	2 1059399-
2007 7685 02	1051147-1	2098 5212 0	2 1055445-1	2998 5003 0	2 1056724-1	4503 7941 00) 1059402-
2007 7941 02	1051151-1	2098 5213 0	2 1055446-1	2998 5022 9	4 1056728-1	4503 7985 00) 1059404-
2007 7985 02	1051157-1	2098 5214 0	2 1055447-1	2998 5028 0	2 1056729-1	4504 7641 02	2 1059408-
2031 5002 00	1051638-1	2098 5215 0	2 1055448-1	2998 5030 0	2 1056731-1	4504 7941 00) 1059410-
2031 5003 02	1051644-1	2098 5216 5	4 1055449-1	2998 5035 0	2 1056736-1	4504 7985 00) 1059412-
2032 5002 00	1051852-1	2098 5217 5	4 1055450-1	2998 5043 0	2 1056743-1	4506 7641 02	2 1059451-
2032 5003 02	1051855-1	2098 5218 0	2 1055451-1	2998 5044 0	2 1056744-1	4506 7685 02	2 1059452-
2032 5007 00	1051861-1	2098 5221 1	0 1055454-1	2998 5045 0	2 1056745-1	4506 7941 02	2 1059453-
2032 5021 02	1051867-1	2098 5279 1	0 1055474-1	2998 5054 9	4 1056750-1	4506 7985 02	2 1059456-
2032 5026 02	1051869-1	2098 5281 0		2998 5055 9		4510 7941 00	
2034 5008 00	1051942-1	2098 5282 0		2998 5056 9		4510 7985 00	
2037 5005 02	1052063-1	2098 5283 0		3001 7941 0		4522 7941 02	
2037 5006 02	1052067-1	2098 5516 0		3001 7985 0		4522 7985 02	
2037 5007 02	1052072-1	2204 7941 0		3002 7941 0		4533 7388 02	
2037 5008 02	1052076-1	2207 7985 0		3004 7941 0		4534 7341 02	
2037 5000 02	1052098-1	2231 7388 3		3004 7985 0		4536 5014 02	
		23173883		3004 7985 0			
2051 0000 02	1052324-1			3051 0000 1		4536 7341 02	
2051 1352 02	1052349-1	2367 0000 5					
2051 1618 02	1052360-1	2367 5001 5		3051 1200 1		4540 7388 02	
2052 0000 02	1052422-1	2367 5002 5		3051 1201 1		4551 1201 02	
2052 1200 02	1052518-1	2380 2240 0		3052 0000 1		4551 1352 02	
2052 1201 00	1052522-1	2381 2241 0		3052 1201 1		4551 3357 02	
2052 1201 02	1052523-1	2382 2240 0		3080 2240 0		4552 1201 02	
2052 1215 02	1052528-1	2382 2241 0	0 1055697-1	3080 2242 0	0 1057343-1	4552 1352 02	2 1059596-
2052 1300 02	1052534-1	2399 5011 5	4 1086008-1	3081 2241 0	0 1057367-1	4557 5009 02	2 1059617·
2052 1350 02	1052544-1	2399 5012 5	4 1086009-1	3082 0000 0	0 1057374-1	4557 5119 02	6059632-
2052 1352 02	1052552-1	2598 5196 5	4 1055831-1	3082 2240 0	0 1057377-1	4557 5329 02	2 1059637-
2052 1612 02	1052563-1	2598 5197 5	4 1055832-1	3082 2241 0	0 1057381-1	4557 5368 02	2 1059651-
2052 1658 02	1052577-1	2598 5198 5	4 1055833-1	3082 2243 0	0 1057385-1	4558 1154 02	2 1059654-
2052 3354 02	1052628-1	2598 5199 5	4 1055834-1	3082 2310 0	0 1057387-1	4558 5009 02	2 1059657-
2052 3356 02	1052634-1	2598 5201 5		3082 2311 0		4558 5119 02	
2052 3358 02	1052643-1	2598 5202 5		3082 2320 0		4558 5329 02	
2052 3359 02	1052646-1	2598 5203 5		3082 2321 0		4562 0000 00	
2052 3363 02	1052652-1	2598 5204 5		3084 2240 0		4563 0000 00	
2052 3500 02	1052684-1	2598 5205 5		3101 7941 0		4563 5004 00	
2052 3500 02	1052689-1	2598 5206 5		3101 7985 0		4565 0000 00	
2052 5502 02				-			
2032 3030 02	1052898-1	2598 5207 5	4 1055842-1	3104 7941 0	0 1057676-1	4580 2240 02	2 1059707·

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

M/A-COM to Tyco Electronics Part Number Cross Reference (Continued)

M/A-COM Part No.	Tyco Electronics Part No.	M/A-COM Part No.	Tyco Electronics Part No.	M/A-COM Part No.	Tyco Electronics Part No.	M/A-COM Ty Part No.	co Electronics Part No.
4581 2241 0	1059711-1	5837 5025 1	0 1330723-1	9960 3100 24	1082845-1	B67B44TA25X	1313508-1
4581 2700 0	0 1059713-1	5837 5030 1	0 1329293-1	9960 4100 01	1064543-1	B67E64T022X	1408041-1
4582 2240 0	2 1059716-1	5837 5031 0	9 1363301-2	9960 4100 02	2 1064544-1	B67H16T493X	1313511-1
4582 2241 0	2 1059718-1	5837 5031 1	0 1363301-1	9960 4100 04	1 1064546-1	B67H49T022X	1311115-1
4582 2700 0	0 1059720-1	5858 0000 0	9 1060959-1	9960 4100 07	7 1064549-1	B67H64T022X	1327083-1
4583 2240 0	1059724-1	5858 0000 1	0 1060960-1	9960 4100 08	3 1064550-1	B67H64T062X	1311117-1
4584 2240 0	1059729-1	5862 5002 0	9 1060984-1	9960 4200 01	1064552-1	B67H64T117X	1311700-1
4584 2242 0	1059731-1	5862 5002 1	0 1060985-1	9960 4200 02	2 1064553-1	B67H64T280X	1313883-1
4584 2244 0	1059733-1	5862 5003 0	9 1330126-1	9960 4200 04	1064555-1	B67H64T437X	1311118-1
4585 2240 0	1059756-1	5862 5003 1	0 1060989-1	9960 4200 07	7 1064558-1	B67H64TA25X	1313887-1
4585 2241 0	1059758-1	5862 5004 0	9 1060995-1	9960 4200 08	3 1064559-1	B67H66T022X	1311120-1
4703 7985 0	0 1059857-1	5862 5004 1	0 1060996-1	9960 4305 01	1064560-1	B67H66T062X	1311701-1
4706 7985 0	1059868-1	5862 5007 1	3 6061002-1	9960 4305 02	2 1064561-1	B67H66T437X	1311122-1
4710 7985 0	0 1059874-1	5862 5018 1	3 1061007-1	9960 4305 04	1064563-1	B67H74T463X	1314422-1
4733 7316 0	1059884-1	5863 0000 0	9 1085221-1	9960 4305 07	7 1064566-1	B67N08T999X	1311125-1
4733 7388 0	2 1059886-1	5863 0000 1	0 1061015-1	9960 4305 08	3 1064567-1	B67N12T999X	1314103-1
4736 5001 0	1059887-1	5864 5001 0	9 1061022-1	9980 4100 01		B67N25T999X	1314102-1
4736 7316 0		5864 5001 1		9980 4100 02		B67P34G999X	1313364-1
4740 7388 0		5864 5002 0		9980 4100 04		B67R53G999X	1311127-1
4751 3355 0		5864 5002 1		9980 4100 05		B67Z50T999X	6-1311703-1
4757 1154 0		5864 5003 0		9980 4100 07		C65E06G022X	1311638-1
4757 3204 0		5864 5003 1		9980 4100 08		D75A02B001X	6331959-1
4757 5006 0		5864 5008 1		9980 4200 01		D75A02B004X	6362765-1
4757 5014 0		5880 2240 0		9980 4200 02		D75B01B470X	6328873-1
4763 0000 0		5881 2241 0		9980 4200 04		D75B02B010X	6408028-1
5001 5015 0		5882 2240 0		9980 4200 05		D75B03B001X	6408030-1
5007 5008 0		5882 2241 0		9980 4200 07		D75B03B004X	6312113-1
5031 5007 0		5899 5004 5		9980 4200 08		D75B04B004X	6408027-1
5031 5014 0		5899 5009 5		9980 4305 01		D75B04B010X	6408026-1
5062 5003 0		7081 2301 0		9980 4305 02		D75B05B004X	6408038-1
5064 5003 0		7081 2311 0		9980 4305 04		D75G03B001R	6408032-1
5134 5016 1		7081 5008 0		9980 4305 05		D75G03B004R	6408033-1
5180 2240 0		7081 5009 0		9980 4305 07		D75G07B060R	6363524-1
5181 2241 0		7082 2242 0		9980 4305 08		D75G08B001R	6363525-1
5182 2240 0		7082 2243 0		A55P22E999		D75G08B004R	6363526-1
5182 2241 0		7082 2300 0		A55P23E999		D75G09B010R	6363527-1
5801 7947 0		7082 2310 0		A55X01B999		D75G10B004R	6408036-1
5801 7985 0		7082 5004 0		A57R03G999		D75R02B999X	6408037-1
5802 7947 0		7082 5005 0		B67A54T022		D75X06B999X	6312121-1
5802 7985 0		9631 7179 1		B67A54T117		D75X12E470X	6312123-1
5807 7985 0		9637 7179 1		B67A64T022		D75X14B999X	6312124-1
5818 5002 0		9662 5000 1		B67A64T062		D75X15B999X	6361137-1
5818 5002 1		9664 0000 1		B67A64T280		N15X09E470X	1312137-1
5818 5002 1		9960 1100 2		B67A64T437		N15X10B999X	6312138-1
5831 5002 1		9960 1200 2		B67A64TA25		N15X10B939X	6329818-1
5831 5002 1		9960 1200 2		B67B42T022		N15X12E470X	6312139-1
5831 5003 0		9960 1305 2		B67B42T022		N15X14E010X	1361138-1
							6361139-1
5831 7316 0		9960 2200 2		B67B44T022		N15X17E999X	
5831 7316 1		9960 2305 2		B67B44T062		N15X18E010X	1329819-1
5834 7388 1	0 1060883-1	9960 2510 2	4 1064542-1	B67B44T437	X 1311111-1	T35E60E010X	1312569-1

314

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Part Number Index

Note: This index lists all cataloged parts by base no. only. Complete part nos. (with prefixes and/or suffixes) are shown on the page(s) indicated.

on the page(s) mult	aleu.	410000
		413996
Part No.	Page	414002
50084	246	414026
50095	246	414171
50105	246	414396
50107	246	414612
51563	247, 248	414766
51565	248	414895
51692	21	414946
51751	194	414948
201097	245	414963
201098	245	414969
201143	245	415001
201144	245	415232
201145	245	415327
201146	245	
221108	58, 72, 73	415340
221500	41	415377
221509	42	415380
221539	94	415381
221540	94	415490
221543	63	415500
221551	64	415504
221586	63	415523
221300	121	415567
221789	121	415672
		415774
221951	55, 56	415796
221988	63	619028
222163	61, 74	619041
222428	52	619052
225014	22	619053
225088	248	619061
225093	22	619062
225094	23	619068
225348	38	619072
225389	22	619075
225551	35	619076
225668	23	619078
225886	49	619085
226023	247	619106
226060	247	619107
226537	248	619115
227223	55, 56	619127
227945	25	619133
228179	33	
228215	182	619134
228216	182	619135
228502	37	619137
228553	179	619196
228658	23	619201
282938	97	619210
329631	57, 58, 59	619211
020001	73, 91	619213
329632	57, 58, 59,	619214
	73, 91	619215
330022	65	619219
330024	64	619220
330620	54	619223
332056	248	619224
332057	248	619226
413453	65	619228

Part No.	Page
413985	178
413990	180
413996	181
414002	
	178
414026	181
414171	35
414396	43
414612	180
414766	94
414895	182
414946	178
414948	179
414963	181
414969	182
415001	182
415232	21
415327	99
415340	181
415377	185
415380	181
415381	181
415490	185
415500	185
	-
415504	185
415523	99
415567	76
415672	181
415774	180
415796	64
619028	230, 235
619041	230
619052	235
619053	236
619061	230, 231
619062	230, 231
619068	235
619072	230, 231
619075	233
619076	235
619078	230, 235
619085	131
619106	136
619107	133
619115	115
619127	204
619133	232
619134	204
619135	204
619137	235
619196	234
619201	233
619210	236
619211	234
619213	234
619214	236
619215	127
619219	261
619220	136
619223	131
619223	131
619226	135
619228	135

Part No.	Page	Part No.	Page
619229	206	1052689	120
619231	233	1052898	118
619238	206	1052902	119
619271	261	1052978	117
887098	94	1052982	117
1050525	110	1052986	117
1050542	110	1053092	115
1050548	110	1053222	117
1050598	112	1053354	121
1050602	112	1053378	121
1050611	112	1053488	122
1050721	105	1053635	122
1050740	112	1053646	256
1050757	110	1053780	123
1050770	110	1053788	259
1050854	110	1054426	123
1050859	110	1054869	123
1050903	105	1055018	122
1050996	106	1055047	123
1051005	113	1055065	122
1051007	113	1055689	214
1051046	111	1055694	217, 255
1051052	111	1055695	217, 253
1051081	111	1055696	217, 258
1051085	111	1055697	217, 259
<u>1051140</u> 1051145	106	1056436	106
1051145	113	1056438 1056443	106
1051147	113	1056445	100
1051157	112	1056445	107
1051638	104	1056450	107
1051644	104	1056452	107
1051852	104	1056456	107
1051855	107	1056462	108
1051861	104	1056526	154
1051867	107	1056527	154
1051869	107	1056553	154
1051942	104	1056554	154
1052063	105	1056700	152, 154
1052067	105	1056702	255
1052072	108	1056706	253
1052076	108	1056707	258
1052098	108	1056708	259
1052324	114	1056721	152, 155
1052349	116	1056722	155
1052360	118	1056724	155
1052422	114	1056728	156
1052518	116	1056729	155
1052522	116	1056731	155
1052523	116	1056736	155
1052528	119	1056743	155
1052534	114	1056744	155
1052544	114	1056745	155
1052552	116	1056750	156
1052563	118	1056751	156
1052577	119	1056752	156
1052628	120	1057275	24
1052634	120	1057277	24
1052643	120	1057279	24
1052646	120	1057284	24
1052652	120	1057290	24
1052684	120	1057341	254

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Part Number Index (Continued)

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
1057343	254	1059617	165	1061007	201	1274330	181
1057367	253	1059637	167	1061015	200	1274449	133
1057374	25	1059651	165	1061022	201	1274513	145
1057377	258	1059654	165	1061023	201	1274520	133
1057381	257	1059657	165	1061026	201	1274544	134
1057385	257	1059671	168	1061027	201	1274563	80
1057387	258	1059681	166	1061029	201	1274566	80
1057388	257	1059684	166	1061030	201	1274568	80
1057390	257	1059691	166	1061070	254	1274571	81
1057392	257	1059707	255	1061071	253	1274572	81
1057463	254	1059711	253	1061072	258	1274584	81
1057631	33	1059713	256	1061073	256	1274594	133
1057635	33	1059716	259	1061692	156	1274662	28
1057676	37	1059718	257	1061738	256	1274663	81
1057679	37	1059720	257	1061739	256	1274668	57
1057697	38	1059724	255	1061742	256	1274684	81
1057699	38	1059729	255	1061744	256	1274688	27
1057775	41	1059731	255	1061750	259	1274689	27
1057780	41	1059733	255	1061751	256	1274694	109
1057841	254	1059756	259	1061752	257	1274714	137
1057843	254	1059758	257	1061753	258	1274734	27
1057845	254	1059857	171	1061757	256	1274735	27
1057853	258	1059868	171	1061758 1064524	258	1274794	237
1057857	258 255	1059874	171	1064524	214	1274795 1274804	237 27
1057908	255	1059884	172		214		27
1058056 1058058	254	1059886 1059887	172	1064533 1064535	214	1274805 1274806	27
1058066	253	1059888	172	1064538	215	1274807	28
1058077	253	1059889	172	1064540	215	1274808	28
1058081	258	1059894	172	1064542	215	1274935	76
1058083	257	1059901	173	1064543	215	1310432	210
1058085	254	1059902	175	1064544	210	1311097	187
1058572	163	1059903	173	1064546	210	1311098	187
1058651	255	1059905	175	1064549	217	1311099	187
1058653	255	1059919	173	1064550	217	1311100	187
1058664	257	1060163	194	1064552	216	1311101	187
1058666	259	1060183	195	1064553	216	1311102	187
1058675	255	1060220	194	1064555	216	1311103	188
1059399	162	1060221	194	1064558	217	1311104	188
1059402	158, 160	1060256	195	1064559	217	1311106	188
1059404	158, 160	1060259	195	1064560	216	1311111	188
1059408	162	1060487	255	1064561	216	1311115	189
1059410	158, 160	1060494	253	1064563	216	1311117	190
1059412	158, 160	1060498	258	1064566	217	1311118	190
1059451	162	1060500	258	1064567	217	1311120	189
1059452	162	1060772	199	1082029	111	1311122	189
1059453	160	1060774	199	1082034	106	1311125	190
1059456	160	1060787	200	1082845	215	1311127	191
1059465	161	1060811	198	1083946	214	1311206	254
1059467	161	1060813	198	1085221	200	1311209	254
1059505	161	1060869	198	1085456	209	1311638	194
1059506	161	1060871	198	1086008	209	1311696	187
1059523	163	1060872	198	1086009	209	1311698	188
1059525	163	1060875	198	1088312	112	1311700	190
1059540	163	1060883	199	1088313	209	1311701	189
1059541	163	1060959	201	1221286	217	1311703	191
1059551	163	1060960	201	1251802	214	1312137	18
1059563	164	1060984	200	1253111	166	1312569	35
1059566	164	1060985	200	1255378	211	1313364	191
1059572	168	1060989	200	1274007	77	1313453	253
1059594	164	1060995	200	1274191	239	1313507	187
1059596	164	1060996	200	1274192	239	1313508	188

Catalog 1307191 Revised 3-07 www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

Part Number Index (Continued)

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
1313511	189	1408347	125	5222420	60	5329458	53
1313883	190	1408348	125	5222462	74	5329517	64
1313887	190	1408349	125	5222506	32	5330061	47
1314102	190	1408393	128, 253	5225089	24	5330062	51
1314103	190	1408496	220	5225092	21	5330063	53
1314422	190	1408541	109	5225349	34	5330358	48
1327083	190	1442004	206	5225361	21	5330876	47
1329174	210	1460010	131	5225363	23	5330878	49
1329175	210	1460052	10	5225392	21	5331175	50
1329293	198	1460055	25	5225395	47, 48, 49	5331178	50
1329819	18	1460060	134	5225396	51	5331182	50
1330126	200	1460118	25	5225397	52	5331238	36
1330401	211	1460128	144	5225398	53, 54	5332215	92
1330723	198	1460132	141	5225554	34	5332225	90
1361138	18	1460139	134	5225555	32	5332342	90
1361169	203	1460159	9	5225557	36	5413194	72
1362990	203	1460169	144	5225559	34	5413364	65
1362991	203	1460468	115	5225661	21	5413366	63
1363106	203	1460469	115	5225662	21	5413476	85
1363301	198	1460470	195	5225664	22	5413506	43
1392019	240	1460802	261	5225667	23	5413515	85
1392020	240	1460803	261	5225669	22	5413524	85
1393562	137, 147	1460815	135	5225699	21	5413557	65
1393662	241	1460817	135	5225886	49	5413558	75
1393665	148, 149, 150,	1460821	147, 148	5225974	50	5413588	68
1000000	253, 256, 259	1460823	146	5226978	59	5413589	66, 67
1393668	240	1484546	174	5226990	57	5413590	67, 70
1393670	131, 132, 133, 134,	1566230	224	5226993	58	5413591	42
	135, 136, 147, 253, 256, 259, 260	1658260	204	5227079	47, 48, 49	5413592	63
1393672	141, 142, 143	1750107	204	5227086	21	5413631	62
1393680	, ,	1750108	225	5227161	57	5413760	69
1393681	140, 142, 143, 144 140, 141, 143,	1750109	225	5227169	55	5413771	53, 54
1393001	145, 146, 150	1750110	226	5227222	58	5413779	51
1393682	140, 141, 142,	1775146	224	5227426	56	5413879	57
	143, 144	1775227	227, 260	5227661	57	5413933	40
1393696	250	1775228	227, 260	5227671	58	5413959	50
1393757	142, 145, 220	1775229	227, 259	5227673	58	5413969	60
1402314	15	1775230	227, 259	5227676	57	5413986	74
1407578	208	5148385	239	5227677	57	5414088	74
1408041	188	5148386	239	5227699	60	5414094	85
1408050	211	5221111	180	5227715	55	5414105	64
1408051	211	5221123	60	5227716	55	5414160	21
1408120	221	5221128	47, 48, 49, 55	5227726	56	5414168	36
1408148	219	5221120	243	5227754	55	5414170	179
1408149	219	5221185	66	5227755	55	5414171	35
1408150	220	5221105	91	5227764	40	5414173	34
1408151	220	5221198	69	5227818	39	5414194	56
1408152	221	5221221	70	5227820	39	5414215	85
1408312	219	5221244	70	5227839	39	5414217	71
1408313	219	5221325	41	5228217	179	5414265	50
1408314	219	5221325	75	5228226	64	5414285	85
1408332	127	5221336		5228435	181		60
1408333	126		68			5414305	63
1408336	126	5221506	42	5228596	242	5414311	
1408337	127	5221629	65	5228618	242	5414337	181
1408338	126	5221980	242	5228686	91	5414338	181
1408339	126	5221981	242	5228979	51	5414352	85
1408340	128	5222006	61	5228980	53, 54	5414363	178
1408341	128	5222092	72	5329444	48	5414367	88
1408342	128	5222093	72	5329445	49	5414373	62
1408343	128, 260	5222117	76	5329446	47	5414394	74
1408346	125	5222132	73	5329452	51	5414409	72
	-	5222165	64	5329456	54	5414414	64

Catalog 1307191 Revised 3-07

www.tycoelectronics.com

Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Part Number Index (Continued)

Part No.	Page						
5414459	72	5415255	22	6057116	22	6312079	14
5414460	60	5415276	96	6057159	23	6312113	9
5414493	87	5415302	95	6057165	23	6312121	15
5414553	87	5415322	97	6057176	23	6312123	19
5414651	86	5415332	98	6059632	167	6312124	19
5414666	64	5415379	181	6059665	167	6312138	15
5414758	87	5415406	98	6061002	202	6312139	19
5414907	72	5415417	72	6061035	202	6328873	10
5414946	178	5415419	72	6061092	202	6329818	17
5415006	179	5415484	184	6061094	202	6331959	9
5415020	76	5415487	184	6274020	97	6361137	17
5415024	96	5415520	73	6274032	98	6361139	19
5415025	62	5415569	95	6274045	98	6362765	9
5415046	57	5415632	73	6274072	72	6363524	11
5415085	86	5415633	72	6274084	72	6363525	11
5415103	85	5415634	72	6274086	71	6363526	11
5415105	72	5415683	98	6274096	121	6363527	11
5415187	71	5415712	95	6274124	75	6408026	10
5415189	60	5415779	87	6274127	75	6408027	10
5415205	86	5415832	92	6274291	74	6408028	9
5415214	96	5447648	107	6274314	61	6408030	9
5415216	86	5448103	107	6274315	61	6408032	10
5415218	57	5887000	98	6274359	74	6408033	10
5415226	94	5887046	97	6274360	74	6408036	11
5415232	21	5887078	95	6274425	76	6408037	11
5415242	22	5887089	97	6274431	133	6408038	10
5415248	23	6057088	21	6274532	21	6408399	18
5415252	24	6057094	21	6311225	10		

Tooling Part Number Index

Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
13126	268	311395	268	1055454	263	1393488	265
13127	268	311396	268	1055469	262	1393494	265
21027	268	312067	268	1055474	262	1393524	264 , 265
58318	268	312253	268	1055475	262	1725837	266
58433	266	312317	268	1055476	262	1775231	227
58483	192	354500	267	1055477	262	M22520/36-01	268
58489	192	603995	267	1055500	263	M22520/36-02	268
59980	267, 268	856402	266	1055831	263	M22520/36-03	268
59981	268	1055420	263	1055832	263	M22520/36-04	268
69477	266	1055439	262, 263	1055833	263	M22520/36-05	268
69710	266	1055440	262, 263	1055834	263	M22520/36-06	268
189721	266	1055441	262, 263	1055835	263	M22520/36-07	268
220015	266	1055442	263	1055836	263	M22520/36-08	268
220220	268	1055443	263	1055837	263	M22520/36-09	268
220221	268	1055444	263	1055838	263	M22520/36-10	268
220222	268	1055445	263	1055839	263	M22520/36-11	268
220224	268	1055446	263	1055840	263	M22520/36-12	268
220241	268	1055447	263	1055841	263	M22520/36-13	268
307581	268	1055448	263	1055842	263	MIL-C-22520/2-01	192
308075	268	1055449	263	1055843	263	MIL-C-22520/5-01	192
311386	268	1055450	263	1213890	266		
311392	268	1055451	263	1311164	191		

318

Catalog 1307191 Revised 3-07 www.tycoelectronics.com Dimensions are in millimeters and inches unless otherwise specified. Values in brackets are standard equivalents. Dimensions are shown for reference purposes only. Specifications subject to change. USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803



Americas

Argentina – Buenos Aires Phone: +54-11-4733-2200 +54-11-4733-2211 Fax:

Brasil - São Paulo +55-11-3611-1311 Phone: +55-11-3611-0397 Fax.

Asia/Pacific

Australia - Sydney +61-2-9554-2600 +61-2-9502-2556 Phone: Fax: **Product Information Center:** (Technical Support) +61-2-9840-8200 Phone: Fax: +61-2-9634-6188

India - Bangalore +91-80-285-40800 Phone: Fax: +91-80-285-40820

Indonesia – Jakarta +65-6482-0311 Phone: Fax: +65-6482-1012 Canada – Toronto +905-475-6222 Phone: Fax: +905-474-5520 **Product Information Center:** (Technical Support) +905-470-4425 . Phone: Fax: +905-474-5525

Colombia - Bogota Phone: +57-1-231-9398 +57-1-660-0206 Fax:

+81-44-844-8111

+81-44-812-3207

+81-44-844-8013

+81-44-812-3200

+82-2-3415-4500

+82-2-3486-3810

+60-3-78053055

+60-3-78053066

Product Information Center:

Malaysia - Kuala Lumpur

Japan – Toyko

(Technical Support)

Korea - Seoul

Phone:

Phone:

Phone:

Phone:

Fax:

Fax:

Fax:

Fax:

Fax:

Mexico – Mexico City Phone: +52-55-1106-0800 +01-800-733-8926 Fax: +52-55-1106-0901

United States - Harrisburg, PA Phone: +717-564-0100 +717-986-7575 Fax: Product Information Center (Technical Support) +800-522-6752 Phone: +717-986-7575 Fax:

New Zealand - Auckland +64-9-634-4580 Phone: +64-9-634-4586 Fax:

Philippines - Makati City +632-848-0171 Phone: Fax: +632-867-8661

People's Republic of China Hong Kong +852-2735-1628 Phone: +852-2735-0243 Fax: Shanghai Phone: +86-21-2407-1588 +86-21-2407-1599

Taiwan - Taipei +886-2-8768-2788 Phone: Fax: +886-2-8768-2268

Fax:

For Latin/South American

Phone: +54-11-4733-2015

+54-11-4733-2083

Countries not shown

Fax:

Singapore - Singapore +65-6482-0311 Phone: +65-6482-1012 Fax:

Thailand - Bangkok +66-2-955-0500 Phone: Fax: +66-2-955-0505

Vietnam and Indochina -Ho Chi Minh City Phone: +84-8 930-5546 +84-8 930-3443 Fax:

Europe/Middle East/Africa

Austria - Vienna Phone: +43-1 90 5 60-0 Fax: +43-1 90 5 60-1333

Belgium - Kessel-Lo Phone: +32-16-35-23-00 +32-16-35-23-52 Fax:

Bulgaria - Sofia Phone: +359-2-971-2152 +359-2-971-2153 Fax:

Czech Republic - Kurim +420-5-41-162-111 Phone: +420-5-41-162-223 Fax:

Denmark - Glostrup +45-43-480-452 +45-43-441-414 Phone: Fax:

Egypt - Cairo +20-2-29 04 281 Phone: Fax: +20-2-41 92 334

Estonia – Tartu +372-5138-274 Phone: +372-7400-779 Fax:

Finland – Helsinki +358-95-12-34-20 Phone: +358-95-12-34-250 Fax:

France - Cergy-Pontoise Phone: +33-1-3420-8888 +33-1-3420-8600 Fax: Product Information Center: (Technical Support) Phone: +33-1-3420-8943 +33-1-3420-8623 Fax:

1307191-3M-LUG-FP-3-07

Printed in the U.S.A.

Germany - Bensheim Phone: +49-6251-133-0 Fax: +49-6251-133-1600 Product Information Center: (Technical Support) Phone: +49-6251-133-1999

+49-6251-133-1988

Germany - Langen +49-6103-709-0 Phone: +49-6103-709-1223 Fax:

Germany – Speyer Phone: +49-6232-30-0 Fax: +49-6232-30-2243

Germany - HTS Division - Neunkirchen Phone: +49-2247-305-0 Fax: +49-2247-305-122

Greece – Athens Phone: +30-210-9370-396/397 Fax: +30-210-9370-655

Hungary - Budapest +36-1-289-1000 Phone: Fax: +36-1-289-1010

Ireland - Dublin +353-1-820-3000 Phone: +353-1-820-9790 Fax:

Israel – Yokneam Phone: +972-4-959-0508 +972-4-959-0506 Fax:

Italy - Collegno (Torino) Phone: +39-011-4012-111 +39-011-4031116 Fax:

Lithuania - Vilnius Phone: +370-5-2131-402 Fax: +370-5-2131-403

Netherlands - 's-Hertogenbosch +31-73-624-62-46 Phone: Fax. +31-73-621-23-65 Product Information Center: (Technical Support) Phone: +31-73-6246-999

+31-73-6246-998 Fax: Norway - Nesbru +47-66-77-8886 Phone:

Fax: +47-66-77-8855 Poland - Warsaw +48-22-45-76-700 Phone: +48-22-45-76-720 Fax:

Romania - Bucharest +40-21-311-3479/3596 Phone: +40-21-312-0574 Fax:

Russia - Moscow +7-495-926-5506/07/08/09 Phone: Fax: +7-495-926-5505

Russia – St. Petersburg Phone: +7-812-718-8192 +7-812-718-8193 Fax:

Slovenia – Ljubljana Phone: +386-1561-3270 Fax: +386-1561-3240

South Africa - Port Elizabeth Phone: +2741-503-4500 +2741-581-0440 Fax:

Spain – Barcelona Phone: +34-93-291-0330 Fax: +34-93-201-7879 Product Information Center: (Technical Support): Phone: +34-93-291-0330 Fax: +34-93-200-3779

Sweden – Upplands Väsbv Phone: +46-8-50-72-50-00 +46-8-50-72-50-01 Fax:

Switzerland – Steinach Phone: +41-71-447-0447 Fax: +41-71-447-0444

Turkev – Istanbul +90-212-281-8181/2/3 Phone: +90-212-281-8184 Fax:

Ukraine - Kiev Phone: +380-044-206-2265 Fax: +380-044-206-2264

United Kingdom - Swindon Phone: +44-8706-080-208 +44-1793-572-109 Fax: Product Information Center: (Technical Support) Freephone GB: 0800-267-666 Phone: +44-208-420-8341 or 8343

+44-208-420-8081 For Middle East/African Countries

Not Shown +33-1-3420-8866 Phone: +33-1-3420-8300 Fax:

Global Contacts

Tyco Electronics Corporation Harrisburg, Pennsylvania

1307191 Revised 3-07 3M-LUG-FP

tycoelectronics.com

