

HDP-20 Crimp Snap-In Contact Connectors



Product Selection Guide

		Connector			Contacts	
Туре	Insert Material	Shell Type Material and Finish	Mounting	Туре	Termination	Plating
Plug (pg. 92)	94V-0 Rated Thermoplastic Black	Zinc Plated Steel Without Grounding Indents Tin Plated Steel Without Grounding Indents Tin Plated Steel With Grounding Indents	.120 [3.05] Dia. Holes Clinch Nut, 4-40 Threads	Pins (pgs. 100, 101)	Crimp Posted	Duplex (.000030 [0.00076] Gold and Tin) Duplex (Gold Flash and Tin) Select (.000030 [0.00076] Gold and Gold Flash)
Receptacle (pg. 93)	94V-0 Rated Thermoplastic Black	Zinc Plated Steel Tin Plated Steel	.120 [3.05] Dia. Holes Clinch Nuts, 4-40 Threaded	Sockets (pgs. 100, 101)	Crimp Posted	Duplex (.000030 [0.00076] Gold and Tin) Duplex (Gold Flash and Tin) Select (.000030 [0.00076] Gold and Gold Flash)



Product Facts

- Shell sizes offer wide choice of contact positions—9, 15, 25, 37 and 50
- Lower cost, commercial version of the military approved series
- Tin or zinc plated shells, with or without grounding indents
- Crimp snap-in contacts allows loading of only the number of contacts being used
- Available with shielding hardware and shielding enclosure kits
- Numerous cable clamps and mating hardware options
- Low cost, high performance, precisionformed crimp contacts

- Machine applied terminations assure highest production rates at lowest applied cost
- Intermateable with any size 20 Subminiature D connector dimensionally complying with MIL-C-24308
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476
- Listed under Underwriters
 Laboratories Inc., Standard
 1863, Communication
 Circuit Accessories,
 File No. E81956
- Certified by Canadian Standards
 Association, File No. LR 1088108 (LR 7189-207)

Section Contents

Plug and Receptacle Connectors	92, 93
Basic Shielding Hardware Kits	94, 95
Shielding Hardware Enclosure Kits	96, 97
Preassembled Shielded Connector Kits	98
Ferrules for Shielding Hardware Kits	99
Contacts	100, 101
Application Tooling	102

Unshielded Cable Clamps

One-Piece Cable Clamp 180°/120° Quik-Snap (pg. 134)

Box and Lid Straight/90° Exit (pg. 137)

Box and Lid with Male Screw Retainers (pg. 137)

Clam Shell Straight/45° Exit (pg. 138)

Clam Shell Straight/45° Exit with Male Screw Retainers (pg. 138)

Shielded Cable Clamps and Shielding Hardware and Enclosure Kits

Straight Exit RFI/EMI Shields for Jacketed Cable (pgs. 139, 142)

90° Exit Die Cast RFI/EMI Shields for Jacketed Cable (pg. 142)

Basic Shielding Hardware Kits (pgs. 94, 95)

Shielding Hardware Enclosure Kits (pgs. 96, 97)

Mounting and Mating Hardware

Keying Plug (pg. 155)

Male Screw Retainers (pgs. 146, 147)

Female Screwlocks (pg. 148)

Locking Posts and Slide Latches (pgs. 149, 151)

Spring Latch, Two-Piece (pg. 152)

Latching Blocks (pgs. 153, 154)

Standoff Bushings (pg. 155)

Contact Retention Features

Radius lead-in minimizes force needed to insert contact into housing

Generous lead-in to minimize "stubbing"

Socket

Radius lead-in minimizes force needed to insert contact into housing

Housing Cutaway



Catalog 82068 Revised 1-08





Plug

Material and Finish:

Shell—Steel, zinc or tin plated **Insert**—94V-0 rated thermoplastic, black

Mounting Holes:

Standard—.120 [3.05] Dia. **Clinch Nut**—4-40 threads with self-locking feature

Related Product Data:

Contact Arrangements—page 40 **Performance Characteristics**—page 41

Contacts—pages 100, 101 **Application Tooling**—page 102

Mateable Connectors:

HDE—pages 110-123 **HDP**—pages 90-102


HD-20 Board Mount pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42 **Cable Clamps**—pages 132, 133, 135-137, 140, 141, 144, 145

Mating Hardware—pages 146-150, 153, 155


Technical Documents:

Product Specification—108-40005 **Application Specifications**— 114-10000, 114-40030



Clinch Nut (Plug and Receptacle)


Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**








Receptacle



							PI	ug Part Numbe	ers	December	e Part Nos.
Shell	No. of	A B C Material Method P		ıs	Insert Mounting	Zinc	Tin Pla	ted Shell	Zinc	Tin	
Size	Contact Positions			Plated Shell	Without Grounding Indents	With Grounding Indents	Plated Shell	Plated Shell			
	9	1.213			94V-0	Standard	205204-9	205204-8	205204-4	205203-8	205203-3
'	30.8	30.81 24.99	12.55	944-0	Clinch Nut	_	1658642-2	1658642-1	_	1658643-1	
2	15	1.541	1.312	.494	94V-0	Standard	205206-9	205206-8	205206-3	205205-7	205205-2
2	15	39.14	39.14 33.33		94 V-U	Clinch Nut	_	_	5745908-2	_	1658644-1
	0.5	2.088	1.852	.494	041/40	Standard	5205208-1	207464-7	207464-2	5205207-1	207463-1
3	25	53.04	47.04	12.55	94V-0	Clinch Nut	_	_	5745036-2	207516-6	207516-5
	07	2.729	2.500	.494	041/10	Standard	205210-8	205210-7	205210-3	205209-7	205209-2
4	4 37		63.50	12.55	94V-0	Clinch Nut	_	_	745135-4	_	5207661-3
	50	2.635	2.406	.605	041/10	Standard	1658641-3	1658641-1	1658641-2	1658640-2	1658640-1
5	50	66.93	61.11	15.37	94V-0	Clinch Nut	_	_	5745883-2	_	5745884-1

Note: Plugs accept size 20 DF pin contacts and receptacles accept size 20 DF socket contacts.



Clinch Nut (Plug and Receptacle)

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**



HDP-20 Basic Shielding Hardware Kits

Plug



Each kit contains:

- Connector
- Inner shield
- Outer shield

Contacts and ferrules must be purchased separately.

Material and Finish:

Connector Shells—Steel, tin plated Connector Insert—94V-0 rated thermoplastic, black

Shield-Steel, tin plated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristicspage 41

Contacts—pages 100, 101

Application Tooling—page 102

Mateable Connectors:

HDE-pages 110-123 **HDP**—pages 90-102

HD-20 Board Mount-

pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42

Mating Hardware—pages 146-150,

153, 155

Ferrules—page 99

Technical Documents:

Product Specifications-

108-40005

108-40030

Application Specifications—


114-10000

114-40030

Instruction Sheet—408-9010

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.







HDP-20 Basic Shielding Hardware Kits (Continued)

Receptacle







Clinch Nut (Plug and Receptacle)

Shell			nsions	Recommended Max. Inner Cable Cable		Mounting	Plug Kit Numbers	Receptacle Kit Numbers	
Size	Positions	D	Е	Outer Dia. Range	Bundle Dia.†	Method	Flug Kit Nullibers	nooptaolo kit nambolo	
-	9	.700	1.535	.165455	.350	Standard	1658645-1	1658646-1	
ı	9	17.78	38.99	4.19-11.56	19-11.56 8.89	Clinch Nut	5748526-1	5748536-1	
2	15	1.024	1.535	.165455	.350	Standard	1658647-1	5747539-1	
2	15	26.01	38.99	9 4.19-11.56	8.89	Clinch Nut	5750636-1	5787908-1	
3	25	1.576	1.535	.165455	.350	Standard	1658648-1	1658649-1	
3	25	40.03	38.99	4.16-11.56	8.89	Clinch Nut	_	1658662-1	
	07	2.215	1.892	.338562	.450	Standard	1658650-1	1658651-1	
4	37	56.26	48.06	8.59-14.28	11.43	Clinch Nut	5786929-1	_	
5	50	2.120 53.85	1.876 47.65	.338480 8.59-12.19	.450 11.43	Standard	1658652-1	1658653-1	

Notes: 1. Plugs accept size 20 DF pin contacts and receptacles accept size 20 DF socket contacts.

2. Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces.

Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces †Maximum cable diameter after jacket and braid removed.



HDP-20 Shielding Hardware Enclosure Kits





Each Kit Contains:

- Connector
- Inner shield
- Outer shield
- Enclosure
- Two jackscrews

Contacts and ferrules must be purchased separately.

Material and Finish:

Connector Shells—Steel, tin plated. Connector Insert-94V-0 rated thermoplastic, black **Shield**—Steel, tin plated Enclosure—PVC, black

Related Product Data:

Jackscrews—Zinc alloy

Contact Arrangements—page 40 Performance Characteristics page 41

Contacts-pages 100, 101

Application Tooling—page 102

Mateable Connectors:

HDE—pages 110-123 **HDP**—pages 90-102

HD-20 Board Mount-

pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42 Mating Hardware—pages 146-150,

153, 155

Ferrules—page 99

Technical Documents:

Product Specifications-

108-40005 108-40030


Application Specifications-


114-10000 114-40030


Instruction Sheet—408-9172

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.








www.tycoelectronics.com





HDP-20 Shielding Hardware Enclosure Kits (Continued)



Receptacle







Shell Size	No. of Contact		mensio		Outer Cable Mat		Insert Material		mbers	Shielding Enclosure Expansion Tool	
	Positions	D	E	Г	Diameter Range	Bundle Dia.†	waterial	Plug	Receptacle	Cable O.D. (Max.)	Part Number
1	9	1.660 42.16	1.355 34.42	.630 16.00	.190330 4.83-8.38	.330 8.38	94V-0	1658655-1	1658654-1	.330	58241-4
2	15	1.660 42.16	1.685 42.80	.630 16.00	.190330 4.83-8.38	.330 8.38	94V-0	1658657-1	1658656-1	8.38	30241-4
3	25	1.660 42.16	2.210 56.13	.630 16.00	.217435 5.51-11.05	.350 8.89	94V-0	1658659-1	1658658-1	.450 11.43	58241-1
4	37	2.010 51.05	2.865 72.77	.730 18.54	.338562 8.59-14.28	.450 11.43	94V-0	5747958-1	1658660-1	.572	E8041 0
5	50	2.010 51.05	2.775 70.49	.730 18.54	.338562 8.59-14.28	.450 11.43	94V-0	1658661-1	5747959-1	14.52	58241-2

Notes: 1. Plugs accept size 20 DF pin contacts and receptacles accept size 20 DF socket contacts.

2. Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces.

†Maximum cable diameter after jacket and braid removed.



Shielded Connector, Preassembled Kit

Designed to meet the requirements of Local Area Networking, this Subminiature D Shielded Connector Kit is available with slide latches attached to the receptacle. The receptacle is shielded and covered with a durable plastic enclosure. This shielding decreases emissions and provides an effective EMI/RFI barrier.

Preassembled connector kits are available in Subminiature D, shell size 2, 15-position configuration and accept crimp, snap-in HD-20 contacts. Contacts are available separately and allow for selective positioning.

Other sizes and styles can be made available, consult Tyco Electronics.

Material and Finish:

Inserts—94V-0 rated nylon, black **Enclosures**—Elastomer, styrene polyolefin, or PVC, black

Shields and Shells—Carbon steel per ASTM A109, plated with .000200 [0.00508] min. tin over .000050 [0.00127] min. copper

Related Product Data:


Contact Arrangements—page 40
Performance Characteristics—
page 41
Contacts—pages 100, 101

Application Tooling—page 102

Ferrules—page 99

Technical Documents:

Product Specifications— 108-40005, 108-40030, 108-40032 Application Specifications— 114-10000 & 114-40030



Receptacle Part No. 749246-1

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.

Note: All part numbers are RoHS compliant.

www.tycoelectronics.com



HDP-20 Ferrules for Shielding Hardware Kits

Ferrules for Shielding Hardware Kits



Stepped



Straight

Material and Finish:

Steel (annealed), tin plated

Related Product Data:

Shielding Hardware and Enclosure Kits—pages 94-98


Technical Documents:


Instruction Sheets-

408-9507 408-9508

408-9243 408-9242

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111**.





Shell		L	Cable	Part Nu	mbers
Sizes	Style	Dim.	Diameter	Ferrule	Die Sets*
1-3	Stepped	.440 11.18	.165190 4.19-4.83	3-747579-0	543424-3
1-3	Stepped	.440 11.18	.190217 4.83-5.51	3-747579-0	543424-2
1-3	Stepped	.440 11.18	.217246 5.51-6.25	3-747579-0	543424-8
1-3	Stepped	.440 11.18	.246284 6.25-7.21	3-747579-2	543424-1
1-3	Stepped	.440 11.18	.284324 7.21-8.23	3-747579-2	543424-7
1-3	Stepped	.440 11.18	.324375 8.23-9.53	3-747579-4	543424-6
1-3	Straight	.440 11.18	.375437 9.53-11.10	2-747579-7	543424-5
1-3	Straight	.440 11.18	.400460 10.16-11.56	3-747579-6	543424-4
4-5	Stepped	.625 15.88	.230265 5.84-6.73	2-747580-4	543425-2
4-5	Stepped	.625 15.88	.338385 8.59-9.78	2-747580-3	543425-1
4-5	Stepped	.625 15.88	.375-432 9.53-10.97	2-747580-1	58238-1
4-5	Stepped	.625 15.88	.422490 10.72-12.45	3-747580-1	58237-2
4-5	Straight	.625 15.88	.480562 12.19-14.28	2-747580-2	58237-1

*Die sets used with Hand Crimping Tool Part No. 543344-1 or Pneumatic Bench Tool Part No. 312522-3 equipped with Die Set Holder Part No. 58449-1.

Application Tooling for Shielding Hardware Kits



Hand Crimping Tool No. 543344-1 (Requires Die Sets, see table above.)



Pneumatic Bench Tool No. 312522-3 (Requires Die Set Holder No. 58449-1.)



Note: All part numbers are RoHS compliant.

99



HDP-20 Connector Contacts, Precision Formed

Contact Size 20 DF Pin Diameter .040 [1.02]

Material and Finish:

Pin—Brass

Socket-Phosphor bronze

Plated

A—Select—Gold flash over nickel on entire contact, with additional .000030 [0.00076] gold on mating end

B—Duplex—.000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

C—Gold flash over nickel on entire contact

D—Duplex—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Performance Characteristics—page 41

Connectors used with: HDP—pages 92-97

Application Tooling—page 102


Technical Documents:

Product Specification—108-40005

Application Specifications-

114-10000 114-40030

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**





Wire Size		Contact		Contact Pa	art Numbers		Hand Tools	for Loose Form	Contacts
Range	Ins. Dia. Max.	Finish (Plating	P	in	Soc	ket	PRO-CRIMPER II	CERTI-CRIMP II	
AWG [mm²]	IVIAX.	Code)	Strip Form	Loose Form	Strip Form	Loose Form	Hand Tool	Hand Tool (Color Code)	for Strip Form Contacts
		Α	66507-3	66507-9	66505-3	66505-9		91503-1 (Blue Dot)	466423-4** 466901-1***
	.040 1.02	В	1658540-4	1658540-5	1658538-2		58448-2		
		С	66507-4	1-66507-0	66505-4	1-66505-0	56446-2		
28-24 0.08-0.2		D	1658540-1	1658540-2	1658538-3	1658538-1			
0.00-0.2		Α	66682-2	66682-4	66683-2	66683-4			466963-1***
	.060 1.52	В	5066682-9	_	1-5066683-0		_	91549-1 (Black Dot)	
	1.02	D	5066682-6	_	5066683-7			(Black Bot)	
		Α	745254-2	745254-6	745253-2	745253-6		91525-1	
26-22	.040	В	1658544-2	1658544-1	1658543-2	1658543-1			
0.15-0.4	1.27	С	745254-3	745254-7	745253-3	745253-7	_	(Yellow Dot)	466968-1***
		D	1658544-3	_	1658543-3				
		Α	66506-3	66506-9	66504-3	66504-9			
24-20	.060	В	1658539-1	1658539-3	1658537-3	1658537-4	50440.0	91503-1	466422-4**
0.2-0.6	1.52	С	66506-4	1-66506-0	66504-4	1-66504-0	58448-2	(Red Dot)	466900-1***
		D	1658539-2	1658539-4	1658537-1	1658537-2			

*For Part Nos. of Special Applicators and Applicators for other model machines, call the Tyco Electronics Tooling Assistance Center at 1-800-722-1111.

**For use with AMP-O-LECTRIC Model "G" Terminating Machine.

***For use with AMP-O-MATIC Model II Stripper-Crimper Machine.





Socket

Insertion/Extraction Tool No. 91285-1

Instruction Sheet—408-9404

Wire Size Range		Contact	Contact Pa	rt Numbers	Hand Tools for Loose Form Contacts		
AWG [mm²]	Ins. Dia. Max.	Finish (Plating Code)	Pin Strip Form	Socket Strip Form	CERTI-CRIMP II Hand Tool	Applicators* for Strip Form	
[IIIIII-]		0000)	C C		(Color Code)	Contacts	
28-24 0.08-0.2	.068 1.73	А	205310-2	205311-3	91548-1 (Blue Dot)	466903-1***	
24-20	.068	Α	205202-2	205201-3	91548-1	100000 1***	
0.2-0.6	1.73	C	205202-6	205201-6	(Red Dot)	466902-1***	
		Α	745229-2	745230-2			
22-18 0.4-0.8	.068	В	1658541-1	1658542-2	91513-1	100000 1111	
	1.73	С	745229-5	745230-5	(Green Dot)	466996-1***	
			_	1658542-1			

Note: Wire insulation diameter is limited by the connector housing cavity and clearance for the insertion/extraction tool.

*For Part Nos. of Special Applicators and Applicators for other model machines, call the Tyco Electronics Tooling Assistance Center at 1-800-722-1111.

***For use with AMP-O-MATIC Model II Stripper-Crimper Machine.



HDP-20 Connector Contacts, Precision Formed (Continued)

Contact Size 20 DF Pin Diameter .040 [1.02] Material and Finish:

Pin—Brass

Socket-Phosphor bronze

Plated:

A—Duplex plated .000030 [0.00076] gold on mating end, with entire contact .000050 [0.00127] min. nickel underplated

B—Duplex plated gold flash on mating end, with entire contact .000050 [0.00127] min. nickel underplated

Related Product Data:

Performance Characteristics—page 41

Connectors used with: HDP—pages 92, 93

Technical Documents:

Product Specification—108-40005 Application Specifications— 114-10000 114-40030

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**

Contact Size 20 DF Pin Diameter .040 [1.02] Material and Finish:

Pin—Brass

Socket—Phosphor bronze

Plated—Gold flash over nickel on entire contact, with additional .000030 [0.00076] gold on mating end

Related Product Data:

Performance Characteristics—page 41

Connectors used with: HDP—pages 92-97

Technical Documents:

Product Specification—108-40005 Application Specification—


114-40030

Insertion/Extraction Tool No. 91285-1

This tool includes interchangeable tips to Insert/Extract:


Size 22, 28-22 AWG [0.08-0.4 mm²] Size 20, Posted Contacts


(Instruction Sheet—408-9404)



Contact		Loose Form Contact Numbers									
Finish (Plating		5 [3.18] Length*	.188 [4.78] Post Length*		.427 [10.85] Post Length*		.651 [16.54] Post Length*				
Code)	Pin	Socket	Pin	Socket	Pin	Socket	Pin	Socket			
A	_	5-745288-5	5-745287-4	7-745288-0	4-745287-7	5-745288-8	5-745287-0	6-745288-1			
В	_	_	_	_	_	7-745288-2	_	7-745288-2			


^{*}Length of post extending from rear of HDP-20 metal-shell connector.





18 AWG Max. Wire (.046 [1.17] Max. Conductor Diameter)

	Form t Number	Loose Form Contact Number			
Pin	Socket	Pin	Socket		
66570-2	66569-2	66570-3	66569-3		



Note: All part numbers are RoHS compliant.

101



HDP-20 Application Tooling

HDP-20 contacts may be applied by a variety of hand tools and machines. For low production runs, repairs and prototype work, we offer either our premium CERTI-CRIMP Hand Tool or our commercial PRO-CRIMPER II Hand Tool. For medium-volume production, you have the choice of our AMP-O-LECTRIC Model "G" Terminating Machine, our new Model "M" Terminating Machine, or our AMP-O-MATIC Model II Stripper-Crimper Machine. The Stripper-Crimper is typically used for terminating the wires of jacketed cable. All three machines can be bench mounted.

For production requirements ranging from non-stop high volumes to countless series of short runs, our popular AMPOMATOR CLS IV+ fully-automated lead-making machine is an ideal choice.

For further information about these or other Tyco Electronics hand tools and machines, call the Tyco Electronics Tooling Assistance Center at 1-800-722-1111.



AMPOMATOR CLS IV+ Lead-Making Machine

This versatile machine now incorporates two AMP-O-LECTRIC Model "G" Terminating Units. Basically, it produces single-wire leads in lengths from 1.62 [41.2] to 1000 [25 400]. It measures, cuts, strips and terminates wire sizes from 26 to 10 AWG [0.12 to 6 mm²] stranded and 26 to 16 AWG [0.12 to 1.4 mm²] solid. Production rates range up to 4800 leads per hour for 3 [76.2] lengths.

The machine is microprocessor controlled, and programmed and operated with

an easy-to-follow, menu-driven touchscreen. It can retain data for up to 200 lead assemblies. Off-line programming is also possible with optional software OffLine-Plus for Windows 95, **Part No. 189263-2**.

Air requirement is 90 psi [6.21] bar minimum at 15 scfm [0.0071 m³/s]. Power requirement is single-phase 220 VAC, 50 or 60 Hz, 25 A.

For further information request Catalog 124324.

www.tycoelectronics.com



HDP-22 Crimp Snap-In Contact Connectors



Product Selection Guide

	Con	nector		Contacts			
Туре	Insert Material	Shell Type Material and Finish	Mounting	 Туре	Termination	Plating	
Plug (pg. 105)	94V-0 Rated Thermoplastic, Black	Tin Plated Steel with Grounding Indents	. 120 [3.05] Dia. Holes	Pin (pg. 109)	Crimp	Duplex (.000030 [0.00076] Gold and Tin) Duplex (Gold Flash and Tin)	



Receptacle (pg. 105)

94V-0 Rated Thermoplastic, Black

Tin Plated Steel

.120 [3.05] Dia. Holes



Socket (pg. 109)

Crimp

Duplex (0.000030 [0.00076] Gold and Tin)

> Duplex (Gold Flash and Tin)



Product Facts:

- Approximately 65% higher density than HD-20 connectors
- Lower cost, commercial version of the military approved Series 90 family
- Available with shielding overmold hardware and shielding enclosure kits
- Capable of using numerous standard HD-20 cable clamps and mating hardware

- Low cost, high performance, precisionformed crimp contacts
- Intermateable with any size 22 Subminiature D connector dimensionally complying with MIL-C-24308
- Recognized under the Component Program of Underwriters
 Laboratories Inc., File No. E28476
- Listed under Underwriters Laboratories Inc., Standard 1863, Communication Circuit Accessories, File No. E81956
- Certified by Canadian Standards Association, File No. LR 1088108 (LR 7189-207)

Section Contents

Plug and Receptacle Connectors	105
Basic Shielding Hardware Kits	106
Shielding Hardware Enclosure Kits	107
Ferrules for Shielding Hardware Kits	108
Contacts	
Application Tooling	. 108, 109

Unshielded Cable Clamps

One-Piece All Plastic Cable Clamp 180°/120° (Quik-Snap) (pg. 133)

Box and Lid Straight/90° Exit (pg. 137)

Box and Lid Straight/90° Exit with Male Screw Retainers (pg. 137)

Clam Shell Straight/45° Exit (pg. 138)

Clam Shell Straight/45° Exit with Screw Retainers (pg. 138)

Shielded Cable Clamps and Shielding Hardware and Enclosure Kits

Straight Exit RFI/EMI Shields for Jacketed Cable

(pg. 141)

90° Exit RFI/EMI Die Cast Shields For Jacketed Cable (pg. 142)

Basic Shielding Hardware Kits (pg. 106)

Shielding Hardware Enclosure Kits (pg. 107)

Crimp & Split Ring Ferrules (pgs. 143-145)

Mounting and Mating Hardware

(SP.®

Male Screw Retainers (pgs. 146, 147)


> Female Screwlocks (pg. 148)

Locking Posts and Slide Latches (pgs. 149, 151)


Two-Piece Spring Latch (pg. 152)

Latching Blocks (pgs. 153, 154)

Contact Retention Features



Socket Radius lead-in minimizes force needed to insert contact into housing



104

Catalog 82068 Revised 1-08 USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208






Plug (With Grounding Indents)



Receptacle



Clinch Nut (Plug and Receptacle)

Material and Finish:

Shell—Steel, tin plated **Insert**—94V-0 rated thermoplastic,

Contacts and ferrules must be purchased separately.

Related Product Data:

Contact Arrangements—page 40 **Performance Characteristics**—page 41

Contacts—page 109

Ferrules—page 108

Mating/Panel Mounting—page 42

Cable Clamps—pages 132, 133, 135-137, 140, 141, 144, 145


Mating Hardware—pages 146-150, 153, 155

Technical Documents:


Application Specification—114-10001


Product Specification—108-1268 Instruction Sheets—408-9381

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**



Receptacle





						Part Numbers					
Shell Size	No. of Contact	Dimensions		With Grounding Indents	With Clinch Nuts		With Clinch Nuts				
OIZC	Positions	Α	В	С	Plug	Plug	Receptacle	Receptacle			
1	15	1.213 30.81	.984 24.99	.494 12.55	748364-1	1658691-1	1658681-1	1658690-1			
2	26	1.541 39.14	1.312 33.33	.494 12.55	1658671-1	5749717-1	1658682-1	5788816-1			
3	44	2.088 53.84	1.852 47.04	.494 12.55	1658672-1	_	1658683-1	5786583-1			
4	62	2.729 69.32	2.500 63.50	.494 12.55	1658673-1	6658293-1	1658684-1	_			
5	78	2.635 66.93	2.406 61.11	.605 15.37	1658674-1	_	1658685-1	5788817-1			

Note: Plugs accept size 22 DF pin contacts and receptacles accept size 22 DF socket contacts.



Basic Shielding Hardware Kits



Plug



Receptacle

Each kit contains:

- Connector
- Inner shield
- Outer shield

Contacts and ferrules must be purchased separately

Material and Finish:

Connector Shell—Steel, tin plated **Connector Insert**—94V-0 rated thermoplastic, black

Shields-Steel, tin plated

Related Product Data:

Contact Arrangements—page 40 **Performance Characteristics**—page 41

Contacts—page 109

Ferrules—page 108

Application Tooling—pages 108 &

Mateable Connectors—

pages 105 & 107

Mating Hardware—pages 146-150, 153, 155


Mating/Panel Mounting—page 42


Technical Documents:

Application Specifications—114-10001


Product Specification—108-1268 Instruction Sheet—408-9381, 408-9010


Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**














Shell	No. of Contact	Dimensions		Recommended Cable	Max. Inner Cable	Kit Numbers	
Size	Positions	С	D	Outer Dia. Range	Bundle Dia.†	Plug	Receptacle
1	15	1.535 38.99	.700 17.78	.165455 4.19-11.56	.350 8.89	1658675-1	5748634-1
2	26	1.535 38.99	1.024 26.01	.165455 4.19-11.56	.350 8.89	1658676-1	1658687-1
3	44	1.535 38.99	1.576 40.03	.165455 4.19-11.56	.350 8.89	1658677-1	5748636-1
4	62	1.892 48.06	2.215 56.26	.338562 8.59-14.28	.450 11.43	5748471-1	_
5	78	1.876 47.65	2.120 53.85	.338490 8.59-12.45	.450 11.43	5748472-1	_

Notes: 1. Plugs accept size 22 DF pin contacts and receptacles accept size 22 DF socket contacts.

2. Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces.

†Maximum cable diameter after jacket and braid removed.



Shielding Hardware Enclosure Kits





Receptacle

Each kit contains:

- Connector
- Inner shield
- Outer shield
- Enclosure
- Two jackscrews

Contacts and ferrules must be purchased separately.

Material and Finish:

Connector Shell—Steel, tin plated

Connector Insert—94V-0 rated thermoplastic, black

Shields—Steel, tin plated

Enclosure—PVC, black

Jackscrews—Zinc alloy

Related Product Data:

Contact Arrangements—page 40

Performance Characteristics—

page 41

Contacts—page 109

Ferrules—page 108

Application Tooling—pages 108 &

Mateable Connectors—

pages 105 & 106

Mating Hardware—pages 146-150, 153-155


Mating/Panel Mounting—page 42


Technical Documents:

Application Specifications—114-10001


Product Specification—108-1268 Instruction Sheet—408-9381 408-9172


Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**






Receptacle







Shell	No. of Contact	Di	mensio	ns	Recommended Cable	Max. Inner	Kit Numbers		Shielding Enclosure Expansion Tool	
Size	Positions	С	D	Е	Outer Diameter	Cable Bundle Dia.†	Plug	Receptacle	Cable O.D. (Max.)	Part Number
1	15	1.640 41.66	1.355 34.42	.630		.330 8.38	1658678-1	1658688-1	.330	58241-4
2	26	1.640 41.66	1.685 42.80	.630		.330 8.38	1658679-1	1658689-1	8.38	30241-4
3	44	1.640 41.66	2.205 56.01	.630		.350 8.89	1658680-1	5748641-1	.450 11.43	58241-1
4	62	2.010 51.05	2.860 72.64	.730 18.54		.450 11.43	5748476-1	5748642-1	.572	50044.0
5	78	2.010 51.05	2.770 70.36	.730 18.54		.450 11.43	5748477-1	_	14.52	58241-2

Notes: 1. Plugs accept size 22 DF pin contacts and receptacles accept size 22 DF socket contacts.

Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces.†Maximum cable diameter after jacket and braid removed.



Ferrules for Shielding Hardware Kits





Straight

Material and Finish:

Steel (annealed), tin plated

Related Product Data:

Shielding Hardware and Enclosure Kits—pages 106 & 107

Technical Documents:

Instruction Sheets-

408-9507 408-9508

408-9243 408-9242


Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional informa-tion call the Tooling Assistance Center: 1-800-722-1111.





Hand Crimping Tool No. 543344-1 (Requires Die Sets, see table above.)





Shell	Otrala	L	Cable	Part Nu	t Numbers	
Sizes	Style	Dim.	Diameter	Ferrule	Die Sets*	
1-3	Stepped	.440 11.18	.165190 4.19-4.83	3-747579-0	543424-3	
1-3	Stepped	.440 11.18	.190217 4.83-5.51	3-747579-0	543424-2	
1-3	Stepped	.440 11.18	.217246 5.51-6.25	3-747579-0	543424-8	
1-3	Stepped	.440 11.18	.246284 6.25-7.21	3-747579-2	543424-1	
1-3	Stepped	.440 11.18	.284324 7.21-8.23	3-747579-2	543424-7	
1-3	Stepped	.440 11.18	.324375 8.23-9.53	3-747579-4	543424-6	
1-3	Straight	.440 11.18	.375437 9.53-11.05	7-747579-7	543424-5	
1-3	Straight	.440 11.18	.400460 10.16-11.56	3-747579-6	543424-4	
4-5	Stepped	.625 15.88	.230265 5.84-6.73	2-747580-4	543425-2	
4-5	Stepped	.625 15.88	.338385 8.59-9.78	2-747580-3	543425-1	
4-5	Stepped	.625 15.88	.375-432 9.53-10.97	2-747580-1	58238-1	
4-5	Stepped	.625 15.88	.422490 10.72-12.45	3-747580-1	58237-2	
4	Straight	.625 15.88	.480562 12.19-14.28	2-747580-2	58237-1	

*Die sets used with Hand Crimping Tool Part No. 543344-1 or Pneumatic Bench Tool Part No. 312522-3 equipped with Die Set Holder Part No. 58449-1.

> **Pneumatic Bench Tool** No. 312522-3 (Requires Die Set Holder No. 58449-1.)



Shielding Enclosure Expansion Tools Part No. 58241-1 (.450 [11.43])† 58241-2 (.572 [14.53])† 58241-4 (.330 [8.38])† †Maximum Cable Diameter (Instruction Sheet—408-9507)

Note: All part numbers are RoHS compliant.



108

Catalog 82068 Revised 1-08

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



Material

Pin—Brass

Socket—Phosphor bronze

Finish

A—Duplex plated .000030 [0.00076] gold on mating end, tin on crimp barrel, with entire contact nickel underplated

B—Duplex plated gold flash on mating end, tin on crimp barrel, entire contact nickel underplated

Related Product Data:

Performance Characteristics—


Connectors used with—pages 105-107

Technical Documents:

Application Specification—114-10001

Product Specification—108-1268 Instruction Sheet—408-9381

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111. Precision Formed
Crimp Snap-In Contacts,
Size 22 DF



Wire		Contact		Contact Pa	rt Numbers		Hand Tools		
Size AWG	Insulation Diameter	Finish	Pin		Socket		for Loose Form Contacts		
AWG mm ²	Max.	(Plating Code)	Strip Form	Loose Form	Strip Form	Loose Form	PRO-CRIMPER II Hand Tool	CERTI-CRIMP II Hand Tool	
28-22	.040	Α	1658670-1	1658670-2	1658686-1	1658686-2	90800-1	91520-1	
0.4-0.08	1.02	В	1658670-3	1658670-4	1658686-3	1658686-4	90000-1	91520-1	

Notes: 1. Strip form contacts shipped 20,000 pieces/reel.

Insertion/Extraction Tool No. 91285-1 (Instruction Sheet—408-9404)

This tool contains interchangeable tips to Insert/Extract Size 22, 28-22 AWG [0.08-0.4 mm²] Crimp Contacts Size 20, 28-20 AWG [0.08-0.4 mm²] Crimp Contacts Size 20, Posted Contacts

Application Tooling



Applicators

To accommodate the broad range of wire termination products that Tyco Electronics produces, most Tyco Electronics terminating machines are designed for use with interchangeable applicators. The basic styles are quickly interchangeable to minimize costly down times, and feature dial-in wire and insulation crimp-height settings. Special applicators are now available for use with the AMP Crimp Quality Monitor, for measuring the crimp height of each termination as it is made, plus evaluating the quality of each crimp.

For further information, request Catalog 65404.

For applicator part numbers, call the Tyco Electronics Tooling Assistance Center at 1-800-722-1111.



AMP-O-LECTRIC MODEL "G" Terminating Machine

A totally new design of our most popular machine for bench-top operation. It features a quiet and highly-reliable direct motor drive, electronic controls for ease of setup and operation, and improved guarding and lighting for operator convenience and safety. All versions also include either manual or automatic precision adjustment for crimp height. Power requirement is 120 or 220 VAC, 50 or 60 Hz.

For further information, request Catalog 65828.



AMP-O-MATIC Model II Stripper-Crimper Machine

This machine automatically strips as well as terminates individual wires. Similar to the AMP-O-LECTRIC Model "G" machine, applicators are quickly interchangeable, and it includes precision adjustment for crimp height. All adjustments can be made from the front of the machine without special tools. Power requirement is 120 VAC. Air requirement is 80-100 psi [5.52-6.89 bar], 3.5 scfm [0.00165 m³/s].

For further information request Catalog 65004.



PRO-CRIMPER II Hand Tool Part No. 90800-1

Features interchangeable die sets and ratchet control that provides full die closure to help eliminate partial crimps. The new design is more durable, and requires dramatically less hand force.

For further information, request Catalog 82276.



HDE-20 IDC Connectors for Discrete Wire and Jacketed Cable



Product Coloction Cuido

		Connector		Contacts Pre-Loaded*		
Туре	Insert Material	Shell Type Material and Finish	Mounting	Туре	Termination	Plating
Plug						
All-Plastic (pg. 112) Metal-Shell (pg. 114)	94V-0 Rated Thermoplastic, Black	Tin Plated Steel	.120 [3.05] Dia. Holes	Pins	Insulation Displacement * Interchangeable crimp snap-in contacts available, see page 121	Duplex (.000030 [0.00076] Gold and Tin) Duplex (Gold Flash and Tin)
Receptacle						
All-Plastic						Duplex (.000030 [0.00076]



(pg. 113)

94V-0 Rated Thermoplastic, Black Metal-Shell (pg. 115)

Tin Plated Steel

.120 Dia. Holes



Insulation Displacement

* Interchangeable crimp snap-in contacts available, see page 121

Gold and Tin)

Duplex (Gold Flash and Tin)

www.tycoelectronics.com



HDE-20 IDC Connectors for Discrete Wire and Jacketed Cable (Continued)

Product Facts

- Insulation displacement contacts preloaded in housings
- No wire stripping
- Post plated contacts with no bare edges
- Duplex plated contacts gold on mating end and tin on crimp end
- Patented contact ensures reliable termination of a wide range of wire sizes and insulation diameters
- Removable contacts for replacement and repair

- Selective loading of contacts available
- Crimp snap-in contacts available for making jumpers between circuits
- Recognized under the Component Program of Underwriters Laboratories Inc., File No. E28476
- Listed under
 Underwriters Laboratories
 Inc., Standard 1863,
 Communication
 Circuit Accessories,
 File No. E81956
- Certified by Canadian Standards Association, File No. 1088108 (LR 7189-207)

Section Contents

All-Plastic Plug and Receptacle Connectors	112, 113
Metal-Shell Plug and Receptacle Connectors	114, 115
Basic Shielding Hardware Kits	
Shielding Hardware Enclosure Kits	
Ferrules for Shielding Hardware Kits	120
Interchangeable Contacts, Crimp Snap-In	
Application Tooling	122, 123

Typical Application Rates

Tool	Rate		
Pistol Style	7.4 Sec./Line		
Arbor Tool	5.0 Sec./Line		
CHAMPOMATOR Machine	2.8 Sec./Line		

Note: Rates are based on total time to complete a double ended 25 position Jacketed Cable Assembly

Unshielded Cable Clamps Shielded Cable Clamps and Shielding Hardware and Enclosure Kits

Mounting and Mating Hardware

(Fe

One-Piece, All-Plastic Cable Clamp, 180°/120° Exit (Quik-Snap) (pg. 133)

Unshielded Cable Clamps Straight/90° Exit (pg. 132)

Slide-On Back Cover (pg. 136)



(pg. 142)
Basic Shielding

Hardware Kits (pgs. 116, 117)

Shielding Hardware Enclosure Kits (pgs. 118, 119) Male Screw Retainers (pgs. 146, 147)

Female Screwlocks (pg. 148)

Locking Posts and Slide Latches (pgs. 149, 151)

Spring Latches, (pg. 152)

Latching Blocks, (pgs. 153, 154)

Keying Plug (pg. 155)



HDE-20 All-Plastic IDC Connectors

Plug



Plug

Material and Finish:

Housing—94V-0 rated thermoplastic, black

Contacts—Phosphor bronze

Contact Finish—Duplex plated: A—.000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40
Performance Characteristics—
page 41

Interchangeable Crimp Snap-In Contacts—page 121

Application Tooling—pages 121-123 **Mateable Connectors:**

HDP—pages 90-97

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42 **Cable Clamps**—pages 132, 133, 135, 136, 139, 140, 144, 145


Mating Hardware—pages 146-150, 153, 155


Technical Documents:

Product Specification—108-40011 Application Specifications— 114-40002 114-40003

Instruction Sheet—408-6621

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.





					Connector Pa	rt Numbers
Shell Size	No. of Contact Positions	Dimer	nsions B	Contact Finish (Plating Code)	Contact Identification No. 1 for 30-26 AWG [0.05-0.15mm ²] Wire	Contact Identification No. 2 for 26-22 AWG [0.15-0.4mm²] Wire
					Plug	Plug
-1	9	1.213	.984	A	_	745203-2
1	9	30.81	24.99	В	_	1-745203-1
2	15	1.541	1.312	Α	_	745207-7
2	15	39.14	33.33	В	_	_
	25	2.090	1.852	Α	745211-9	745211-7
3 2	25	53.09	47.04	В	_	745211-8
4	4 07		2.500	Α	_	745215-7
4	37	2.732 69.39	63.50	В	_	_

Notes: 1. All connectors are preloaded with insulation displacement contacts. Pins in plug connectors and sockets in receptacle connectors. Contacts accept a max. wire insulation thickness of .015 [0.38] and a max. wire insulation dia. of .060 [1.52].

- 2. HDE connectors are designed for terminating solid or stranded (7-strand max.) wire.
- 3. Individual conductor strands should be larger than .005 inch [0.127] diameter.
- Extraction Tool Part No. 91232-1 (Instruction Sheet 408-6631) is used to remove pin or socket contacts.
- 5. For terminating more than one wire, or a drain wire, use crimp contacts on page 121.

Note: All part numbers are RoHS compliant.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



HDE-20 All-Plastic IDC Connectors (Continued)

Receptacle



Receptacle

Material and Finish:

Housing—94V-0 rated thermoplastic,

Contacts—Phosphor bronze

Contact Finish—Duplex plated: **A**—.000030 [0.00076] gold on mating end, tin on termination end, with entire

contact nickel underplated **B**—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristicspage 41

Interchangeable Crimp Snap-In Contacts—page 121

Application Tooling—pages 121-123

Mateable Connectors:

HDP—pages 90-97

HD-20 Board Mount—pages 54-71,

78-85, 87-89

Mating/Panel Mounting—page 42 Cable Clamps—pages 132, 133, 135,

136, 139, 140, 144, 145

Mating Hardware—pages 146-150,

153, 155

Technical Documents:

Product Specification—108-40011 Application Specifications-114-40002

114-40003

Instruction Sheet—408-6621

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.

Molded Cavity Indentification & AMP Trademark .109 .112 [2.85] Typ .120 ¬ [3.05] Dia 2 Holes 00000 00000 .509 Max. [12.93] 00000 **.243** [6.17] .824 [20.93] Ref. .080

					Connector Part Numbers
Shell	No. of Contact	Dimer	nsions	Contact Finish	Contact Identification No. 2
Size	Positions	Α	В	(Plating Code)	for 26-22 AWG [0.15-0.4mm²] Wire
					Receptacle
	9	1.213	.984	А	745201-7
ı	9	30.81	24.99	В	745201-9
2	15	1.541 39.14	1.312 33.33	Α	745205-7
	O.F.	2.090	1.852	А	745209-7
3	25	53.09	47.04	B	745209-8

Notes: 1. All connectors are preloaded with insulation displacement contacts. Pins in plug connectors and sockets in receptacle connectors. Contacts accept a max. wire insulation thickness of .015 [0.38] and a max. wire insulation dia. of .060 [1.52].

- 2. HDE connectors are designed for terminating solid or stranded (7-strand max.) wire.
- 3. Individual conductor strands should be larger than .005 inch [0.127] diameter.
- Extraction Tool Part No. 91232-1 (Instruction Sheet 408-6631) is used to remove pin or socket contacts.
- 5. For terminating more than one wire, or a drain wire, use crimp contacts on page 121.



HDE-20 Metal-Shell IDC Connectors

Plug



Material and Finish:

Shell—Steel, tin plated **Insert**—94V-0 rated thermoplastic,

Contacts—Phosphor bronze Contact Finish—Duplex plated: A—.000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristicspage 41

Interchangeable Crimp Snap-In Contacts—page 121

Application Tooling—pages 121-123 **Mateable Connectors:**

HDP-pages 90-97

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42 Cable Clamps—pages 132, 133, 135, 136, 138, 140, 144, 145

Mating Hardware—pages 146-150, 153, 155

Technical Documents:


Product Specification—108-40011


Application Specifications— 114-40002

114-40003

Instruction Sheet—408-6645

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.





					Cc	onnector Part Numbe	rs	
Shell Size	No. of Contact Positions	Dimensions A B		A B (Plating		Contact Identification No. 1 for 30-26 AWG [0.05-0.15mm ²] Wire	Contact Identification No. 2 for 26-22 AWG [0.15-0.4mm²] Wire	Contact Identification No. 3 for 22-20 AWG [0.4-0.6mm ²] Wire
					Plug	Plug	Plug	
	9	1.213	.984	Α	1-745492-7	1-745492-8	1-745492-9	
- '	9	30.81 2	24.99	В	_	2-745492-0	_	
2	15	1.541	1.541 1.312 39.14 33.33	Α	1-745494-7	1-745494-5	_	
	15	39.14		В	_	1-745494-6	_	
3	25	2.088	1.852	Α	1-745496-9	1-745496-7	2-745496-0	
	25	53.04	47.04	В	_	1-745496-8	_	
4	37	2.729	2.500	Α	1-745498-6	1-745498-5	_	
4	3/	69.32	63.50	В	_	1-745498-7	_	

Notes: 1. All connectors are preloaded with insulation displacement contacts. Pins in plug connectors and sockets in receptacle connectors. Contacts accept a max. wire insulation thickness of .015 [0.38] and a max. wire insulation dia. of .060 [1.52].

- 2. Connectors can be made available with clinch nuts, contact Tyco Electronics.
- HDE connectors are designed for terminating solid or stranded (7-strand max.) wire.
 Individual conductor strands should be larger than .005 inch [0.127] diameter.
- 5. Extraction Tool Part No. 91232-1 (Instruction Sheet 408-6631) is used to remove pin or socket contacts.
- 6. For terminating more than one wire, or a drain wire, use crimp contacts on page 121.



HDE-20 Metal-Shell IDC Connectors (Continued)

Receptacle



Material and Finish:

Shell—Steel, tin plated **Insert**—94V-0 rated thermoplastic, black

Contacts—Phosphor bronze
Contact Finish—Duplex plated:
A—.000030 [0.00076] gold on mating
end, tin on termination end, with entire
contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 **Performance Characteristics**—page 41

Interchangeable Crimp Snap-In Contacts—page 121

Application Tooling—pages 121-123

Mateable Connectors:

HDP—pages 90-97

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 42 **Cable Clamps**—pages 132, 133, 135, 136, 139, 140, 144, 145

Mating Hardware—pages 146-150, 153, 155


Technical Documents:


Product Specification—108-40011 **Application Specifications**— 114-40002

114-40002

Instruction Sheet—408-6645

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.





		tions A B (Plating Code) No. 1 No. 1 (Plating Code) for 30-26 AW [0.05-0.15mm²]			Co	onnector Part Numbe	rs
Shell Size	No. of Contact Positions			Identification	Contact Identification No. 2 for 26-22 AWG [0.15-0.4mm²] Wire Receptacle	Contact Identification No. 3 for 22-20 AWG [0.4-0.6mm²] Wire Receptacle	
	9	1.213	.984	Α	1-745491-6	1-745491-7	1-745491-9
'	9	30.81	31 24.99	В	_	1-745491-8	_
2	15	1.541 1.312	Α	1-745493-6	1-745493-4	_	
2	15	39.14	33.33	В	_	1-745493-5	_
3*	25	2.088	1.852	Α	1-745495-7	1-745495-8	1-745495-9
3	25	53.04	47.04	В	_	2-745495-0	_
4	37	2.729	2.500	Α	1-745497-6	1-745497-5	_
4	3/	69.32	63.50	В	_	1-745497-7	_

^{*} RS-232, size 3 connector, for 26-22 [0.15-0.4mm²] AWG wire select loaded circuits 1-8,15,17, 20 and 22, Plug Part No. 747740-1, Receptacle Part No. 747741-1, gold flash contacts.

- Notes: 1. All connectors are preloaded with insulation displacement contacts. Pins in plug connectors and sockets in receptacle connectors. Contacts accept a max. wire insulation thickness of .015 [0.38] and a max. wire insulation dia. of .060 [1.52].
 - 2. Connectors can be made available with clinch nuts, contact Tyco Electronics.
 - 3. HDE connectors are designed for terminating solid or stranded (7-strand max.) wire.
 - 4. Individual conductor strands should be larger than .005 inch [0.127] diameter.
 - 5. Extraction Tool Part No. 91232-1 (Instruction Sheet 408-6631) is used to remove pin or socket contacts.
 - 6. For terminating more than one wire, or a drain wire, use crimp contacts on page 121.



HDE-20 Basic Shielding Hardware Kits



Each kit contains:

- Connector
- Inner shield
- Outer shield

Ferrules must be purchased separately.

Material and Finish:

Connector Shell—Steel, tin plated Connector Insert—94V-0 rated thermoplastic, black

Shield—Steel, tin plated

Contacts—Phosphor bronze

Contact Finish—Duplex plated: **A**—.000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristicspage 41


Application Tooling—pages 121-123

Mateable Connectors: HDP—pages 90-97

HD-20 Board Mount—pages 54-71, 78-85. 87-89

Mating Hardware—pages 146-150,

Mating/Panel Mounting—page 42



Technical Documents:

Product Specifications—

108-40011 108-40030

Application Specifications-114-40002

114-40003

114-40006

Instruction Sheet—408-9010

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: 1-800-722-1111.

							Coi	nnector Part Num	bers
Shell Size	No. of Contact Pos.	Dimer	nsions D	Recommended Cable Outer Dia. Range	Max. Inner Cable Bundle Dia.†	Contact Finish (Plating Code)	Contact I.D. No. 1 for 30-26 AWG [0.05-0.15mm ²] Wire	Contact I.D. No. 2 for 26-22 AWG [0.15-0.4mm ²] Wire	Contact I.D. No. 3 for 22-20 AWG [0.4-0.6mm ²] Wire
							Plug	Plug	Plug
1	9	1.520 38.61	.678 17.22	.165455 4.19-11.56	.350 8.89	Α	_	747515-7	_
	45	1.520	1.002	.165455	.350	Α	747531-7	747531-8	_
2	15	38.61	25.45	4.19-11.56	8.89	В	_	747531-9	_
	05	1.520	1.550	.165455	.350	Α	747547-8	747547-9	_
3	25	38.61	39.37	4.19-11.56	8.89	В	_	1-747547-0	
4	0.7	1.867	2.205	.338562	.450	А	_	_	_
4	37	17 19	56.01	9 50 14 29	11 /2			4 747500 0	

11.43

Note: Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces. †Maximum cable diameter after jacket and braid removed.

Note: All part numbers are RoHS compliant.

8.59-14.28

56.01

47.42

1-747563-0

Ferrule (Must be Purchased Separately)



HDE-20 Basic Shielding Hardware Kits (Continued)



Each kit contains:

- Connector
- Inner shield
- Outer shield

Ferrules must be purchased separately.

Material and Finish:

Connector Shell—Steel, tin plated **Connector Insert**—94V-0 rated thermoplastic, black

Shield-Steel, tin plated

Contacts—Phosphor bronze

Contact Finish—Duplex plated: **A**—.000030 [0.00076] gold on mating end, tin on termination end, with entire

contact nickel underplated **B**—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristics—

page 4


Application Tooling—pages 121-123 **Mateable Connectors:**

HDP—pages 90-97

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating Hardware—pages 146-150, 153, 155

Mating/Panel Mounting—page 42



Technical Documents:

.490 [12.45] Max.

Product Specifications—

108-40011

108-40030

Application Specifications—

114-40002 114-40003

114-4000

114-40006

Instruction Sheet—408-9010

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.

							Cor	nnector Part Numl	bers
Shell Size	No. of Contact Pos.	Dimer	nsions D	Recommended Cable Outer Dia. Range	Max. Inner Cable Bundle Dia.†	Contact Finish (Plating Code)	Contact I.D. No. 1 for 30-26 AWG [0.05-0.15mm ²] Wire	Contact I.D. No. 2 for 26-22 AWG [0.15-0.4mm ²] Wire	Contact I.D. No. 3 for 22-20 AWG [0.4-0.6mm ²] Wire
							Receptacle	Receptacle	Receptacle
-	9	1.520	.678	.165455	.350	Α	_	747516-7	747516-8
,	9	38.61	17.22	4.19-11.56	8.89	В	_	747516-9	_
0	45	1.520	1.002	.165455	.350	Α	_	747532-7	_
2	15	38.61	25.45	4.19-11.56	8.89	В	_	747532-8	_
0	0.5	1.520	1.550	.165455	.350	А	_	747548-8	_
3	25	38.61	39.37	4.19-11.56	8.89	В	_	747548-9	_
4	37	1.867 47.42	2.205 56.01	.338562 8.59-14.28	.450 11.43	В	747564-8	747564-9	_

Note: Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces. †Maximum cable diameter after jacket and braid removed.

Note: All part numbers are RoHS compliant.

View of Rear Shell (With Shields Removed)



HDE-20 Shielding Hardware Enclosure Kits



Each kit contains:

- Connector
- Inner shield
- Outer shield
- Enclosure
- Two jackscrews

Ferrules must be purchased separately.

Material and Finish:

Connector Shell—Steel, tin plated

 $\textbf{Connector Insert} \color{red} -94 \text{V-0 rated}$

thermoplastic, black

Shield-Steel, tin plated

 $\textbf{Enclosure} \textcolor{red}{\longleftarrow} \text{PVC, black}$

Jackscrews—Zinc alloy

Contacts—Phosphor bronze

Contact Finish—Duplex plated: **A**—.000030 [0.00076] gold on mating end, tin on termination end, with entire

contact nickel underplated **B**—Gold flash on mating end, tin on termination end, with entire contact

Related Product Data:

nickel underplated

Contact Arrangements—page 40

Performance Characteristics-

page 41

Application Tooling—pages 121-123

Mateable Connectors:

HDP—pages 90-97


HD-20 Board Mount—pages 54-71,


78-85, 87-89

Mating Hardware—pages 146-150,

153, 155

Mating/Panel Mounting—page 42





Technical Documents:

Product Specifications-

108-40011

Plug

108-40030

Application Specifications—

114-40002

114-40003

114-40006

114-40008

Instruction Sheet—408-9172

Note: Instruction Sheets for Tyco Electronics Tooling are packaged

with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.

								Kit Part Numbers	3	Shieldi	ng	
Shell	No. of	Di	mensio	ns	Recommended Cable	Max. Inner	Contact Finish	Contact I.D. No. 1	Contact I.D. No. 2	Contact I.D. No. 3	Enclos Expans	ion
Size	Contact Pos.	С	D	Е	Outer Dia.	Cable Bundle Dia.†	(Plating Code)	for 30-26 AWG [0.05-0.15mm ²]	for 26-22 AWG [0.15-0.4mm ²]	for 22-20 AWG [0.4-0.6mm ²]	Tool Cable	Part
					Range	ыа.т	,	Plug	Plug	Plug	O.D. (Max.)	No.
		1.640	1.355	.630	.190330	.330	Α	_	1-747944-5	_		
ı	9	41.66	34.42	16.00	4.83-8.38	8.38	В	_	1-747944-6	_	.330	58241-4
0	45	1.640	1.685	.630	.190330	.330	Α	_	1-747946-5	_	8.38	30241-4
2	15	41.66	42.80	16.00	4.83-8.38	8.38	В	_	1-747946-6	_		
0	05	1.640	2.210	.630	.217435	.350	Α	1-747948-5	1-747948-6	_	.450	E0044 4
3	25	41.66	56.13	16.00	5.51-11.05	8.89	В	_	1-747948-8	1-747948-9	11.43	58241-1
4	07	2.010	2.865	.730	.338562		Α	1-747950-4	1-747950-5	_	.572	E0041.0
4	37	51.05	72.77	18.54	8.59-14.28		В	_	1-747950-6		14.52	58241-2

†Maximum cable diameter after jacket and braid removed.

Note: All part numbers are RoHS compliant.

Dimensions are in inches and

Receptacle



HDE-20 Shielding Hardware Enclosure Kits (Continued)



Each kit contains:

- Connector
- Inner shield
- Outer shield
- Enclosure
- Two jackscrews

Ferrules must be purchased separately.

Material and Finish:

Connector Shell—Steel, tin plated Connector Insert—94V-0 rated thermoplastic, black

Shield—Steel, tin plated

Enclosure—PVC, black

Jackscrews-Zinc alloy

Contacts—Phosphor bronze

Contact Finish—Duplex plated:

A—.000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Related Product Data:

Contact Arrangements—page 40 Performance Characteristicspage 41


Application Tooling—pages 121-123 **Mateable Connectors:**


HDP—pages 90-97

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating Hardware—pages 146-150,

Mating/Panel Mounting—page 42





Technical Documents:

Product Specifications-

108-40011

108-40030

Application Specifications-

114-40002

114-40003

114-40006

114-40008

Instruction Sheet—408-9172

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.

								Kit Part	Numbers	Shield	ing
Shell	No. of Contact	Di	imensio	ns	Recommended Cable Outer	Max. Inner Cable	Contact Finish	Contact I.D. No. 1	Contact I.D. No. 2	Enclos Expans	sion
Size	Pos.	С	D	E	Dia. Range	Bundle Dia.†	(Plating Code)	for 30-26 AWG [0.05-0.15mm ²]	for 26-22 AWG [0.15-0.4mm ²]	Too Cable	Part
					riange	halige Dia.		Receptacle	Receptacle	O.D. (Max.)	No.
	0	1.640	1.355	.630	.190330	.330	А	1-747943-5	1-747943-6		
ı	9	41.66	34.42	16.00	4.83-8.38	8.38	В	_	1-747943-7	.330	58241-4
	45	1.640	1.685	.630	.190330	.330	Α	1-747945-5	_	8.38	30241-4
2	15	41.66	42.80	16.00	4.83-8.38	8.38	В	_	_		
	05	1.640	2.210	.630	.217435	.350	Α	1-747947-5	1-747947-6	.450	50044.4
3	25	41.66	56.13	16.00	5.51-11.05	.51-11.05 8.89		_	1-747947-7	11.43	58241-1
	07	2.010	2.865	.730	.338562	.338562 .450 8.59-14.28 11.43		_	_	.572	50044.0
4	37	51.05	72.77	18.54	8.59-14.28			_	_	14.52	58241-2

†Maximum cable diameter after jacket and braid removed.

Note: All part numbers are RoHS compliant.

119



HDE-20 Crimp Snap-In Contact Connectors

Ferrules for Shielding Hardware Kits



Stepped



Straight

Material and Finish:

Steel (annealed), tin plated

Related Product Data:

Shielding Hardware and Enclosure Kits—pages 116-119


Technical Documents:


Instruction Sheets-

408-9242 408-9243

408-9507 408-9508

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center: **1-800-722-1111.**





Shell	Shell Ctule		Cable	Part Nu	ımbers
Sizes	Style	L Dim.	Diameter	Ferrule	Die Sets*
1-3	Stepped	.440 11.18	.165190 4.19-4.83	3-747579-0	543424-3
1-3	Stepped	.440 11.18	.190217 4.83-5.51	3-747579-0	543424-2
1-3	Stepped	.440 11.18	.217246 5.51-6.25	3-747579-0	543424-8
1-3	Stepped	.440 11.18	.246284 6.25-7.21	3-747579-2	543424-1
1-3	Stepped	.440 11.18	.284324 7.21-8.23	3-747579-2	543424-7
1-3	Stepped	.440 11.18	.324375 8.23-9.53	3-747579-4	543424-6
1-3	Straight	.440 11.18	.375435 9.53-11.05	2-747579-7	543424-5
1-3	Straight	.440 11.18	.400455 10.16-11.56	3-747579-6	543424-4
4	Stepped	.625 15.88	.230265 5.84-6.73	2-747580-4	543425-2
4	Stepped	.625 15.88	.338385 8.59-9.78	2-747580-3	543425-1
4	Stepped	.625 15.88	.375-432 9.53-10.97	2-747580-1	58238-1
4	Stepped	.625 15.88	.422490 10.72-12.45	3-747580-1	58237-2
4	Straight	.625 15.88	.480562 12.19-14.28	2-747580-2	58237-1

^{*}Die sets used with Hand Crimping Tool Part No. 543344-1 or Pneumatic Bench Tool Part No. 312522-3 equipped with Die Set Holder Part No. 58449-1.

Application Tooling for Shielding Hardware Kits



Hand Crimping Tool No. 543344-1 (Requires Die Sets, see table above.)



Shielding Enclosure Expansion Tools Part No. 58241-1 (.450 [11.43])† 58241-2 (.572 [14.53])† 58241-4 (.330 [8.38])† †Maximum Cable Diameter (Instruction Sheet—408-9507)

Note: All part numbers are RoHS compliant.



No. 58449-1.)

Pneumatic Bench Tool No. 312522-3 (Requires Die Set Holder



HDE-20 Contacts, Precision Formed


Material and Finish:


Phosphor bronze, duplex plated as follows:

A—Duplex plated .000030 [0.00076] gold on mating end, tin on termination end, with entire contact nickel underplated

B—Gold flash on mating end, tin on termination end, with entire contact nickel underplated

Interchangeable Contacts, Crimp Snap-In





Wire Size		Insul Diam		Contact Finish	Contact Part Numbers	
Range AWG mm²	Code* Single Two (Plating Wire Wire Code)		Single Two		Pin Strip Form	Socket Strip Form
26-22		.054	.039	Α	_	1-745269-1
0.15-0.4	4	1.37	0.99	В	1-745266-0	1-745269-0
22-18	22-18	.075	.054	Α	1-745267-0	1-745270-1
0.4-0.8	3	1.91	1.37	В	_	1-745270-0

^{*} A Code indicating accepted wire size range is stamped inside insulation crimp barrel of each contact.

Notes: 1. Extraction Tool No. 91232-1 is used to remove pin and socket contacts.

2. Strip form contacts shipped 10,000 pieces/reel.

Related Product Data:

Performance Characteristics—page 41

Connectors used with: HDE—pages 112-119

Technical Documents:

Product Specifications-

108-40011 108-40030

Application Specifications-

114-40002 114-40003

114-40006

114-40008

Instruction Sheet—408-6738

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Center:

1-800-722-1111.



HDE-20 Application Tooling

Hand Tools with Modular Heads

Technical Documents:

Instruction Sheets— 408-6790 408-9414 408-6789

Note: Instruction Sheets for Tyco Electronics Tooling are packaged with the tooling. For additional information call the Tooling Assistance Hotline: **1-800-722-1111**.

A modular interchangeable head provides versatility to these tools. Along with the head used to terminate Subminiature D connectors, heads are available to terminate other Tyco Electronics product lines.

The head used to terminate the Subminiature D, HDE connectors can be used with a manual pistol grip tool, an air pistol grip tool and a bench mount power assembly. These tools terminate one unstripped wire per cycle and index the connector to the next terminating position. The head rotates to permit optimum access to the wiring area.

Manual Pistol Grip Tool



Handle and Head Tool Assembly No. 608868-1 Handle No. 58074-1 Head Assembly No. 58063-2

This tool is manually actuated, using modular heads.

Air Pistol Grip Tool



Handle No. 58075-1 Head Assembly No. 58063-2 Air actuated, utilizing modular heads.

Bench Mounted Tools with Modular Heads

Bench Mount Pneumatic Power Assembly



Bench Assembly No. 58338-1 Head Assembly No. 58063-2

This tool is air actuated with either a foot or knee switch.

Bench Mount Electric Power Assembly



Head Assembly No. 58063-2

This tool electrically powered and actuated by a foot switch.



HDE-20 Application Tooling (Continued)

Product Facts

- Low applied costs
- Automatic termination of jacketed cable
- Automatic continuity check and shorts test
- Single- or double-ended assemblies
- Microprocessor controlled with touch input screen
- Stored program capability
- Selective termination of connector positions
- Rapid tooling changeover for different connector types
- Handles a variety of Tyco Electronics insulationdisplacement connectors
- Terminates both multicolor and single-color wires
- Remote programming capability
- Straight or right-angle wire dress
- **Control Module** 852423-1 120 VAC

Technical Documents:

408-7777 Manual Arbor Tool

Note: Instruction Sheets for

Tyco Electronics Tooling are packaged

with the tooling. For additional informa-

tion call the Tooling Assistance Center:

Instruction Sheets

1-800-722-1111.



Control Module No. 852423-1

CHAMPOMATOR 2.5 Machine No. 354786-4

Manual **Arbor Tool**

Arbor Tool No. 91085-2 Applicators: Wire O.D. .041-.060 [1.04-1.52]—No. 543157-1 (tool mount), 543426-1 (termination tool) Wire O.D. .040 [1.02] and smaller-No. 543157-1 (tool mount), 543426-2 (termination tool)

Note: All part numbers are RoHS compliant.

CHAMPOMATOR 3A Terminating Machine

This machine is the high-productivity way to terminate multiconductor. jacketed cable with a variety of Tyco Electronics connectors having insulation displacement contacts. It automatically sorts the wires, and terminates them in a programmed sequence. The sequence may use all or some of the connector contacts, such as for various RS-232 wiring patterns.

All cable assemblies are tested for continuity and shorts.

The machine is microprocessor controlled, and programmed by a touch input screen. The easy programming simplifies the process and reduces training requirements. The machine's internal storage capability can retain up to 50 cable assemblies, which can be easily retrieved by number or name. Production monitoring and diagnostics can also be accessed through the touch

Contact Tyco Electronics for the tooling required for your specific applications.

CHAMPOMATOR 2.5 Terminating Machine

This is a compact, semiautomatic bench machine. It is microprocessor controlled, and programmed using a membrane switch keyboard. The potential machine rate is one pair of wires per second. Contact Tyco Electronics for the tooling required for your specific applications.

The CHAMPOMATOR Model 2.5 Bench Terminating Machine-Part No. 354786-4 is used in conjunction with Control Module—Part No. 852423-1.

Contact Tyco Electronics for application specific requirements.

Manual Arbor Tool

The arbor tool with applicator is used to terminate jacketed cable. Wires are neatly routed and trimmed to length with the cable jacket close to the connector. 400 to 800 terminated wires per hour are typical.

123



Subminiature D Connectors HDF-20 for Flat Ribbon Cable

Product Facts

- Available in all 5 standard shell sizes
- Visual inspection of termination possible
- Fluted cover provides positive alignment of cable prior to termination
- Wide range of application tooling
- Patented insulation displacement contact latches into the connector cover
- Contact design provides a "gas-tight" termination
- Contacts accept 28 AWG [0.08mm2] solid and stranded, and 26 AWG [0.15mm2] solid and stranded round conductor flat ribbon cable on .050 [1.27] centers
- Qualified to Battelle Level III environment
- UL Component Recognized in File No. E28476
- CSA Certified in File No.164196 (LR 7189)
- UL Listed in File No. E81956, evaluated to requirements found in UL 1863 standard, Communication Circuit Accessories

Plug — Low Profile Metal Shell



Receptacle — Low Profile Metal Shell



		Plug Pa	rt Nos.	Receptacle Part Nos.		
No. of Pos. & (Shell Size)	Cable Stabilizer Part No.	W ith Standard Mounting Holes	W ith 4-40 Threaded Inserts	W iith Standard Mounting Holes	W ith 4—40 Threaded Inserts	
9 (1)	747275-4	1658613-4	1658608-4	1658612-4	1658610-4	
15 (2)	747275-3	1658613-3	1658608-3	1658612-3	1658610-3	
25 (3)	747275-2	1658613-2	1658608-2	1658612-2	1658610-2	
37 (4)	747275-1	1658613-1	1658608-1	1658612-1	1658610-1	
50 (5)	746785-1	_	1658607-1	_	1658606-1	

Note: All assemblies are supplied with housing and cover pre-assembled. Optional cable stabilizer must be ordered separately.

Material

Front Shell—Steel, tin or tin plated Housing, Cover & Cable Stabilizer— Thermoplastic, 94V-0, black

Threaded Inserts—Brass, unplated Contacts—Phosphor bronze, duplex plated .000030 [0.00076] min. gold on mating end, .000100-.000200 [0.00254-0.00508] bright tin on termination end with entire contact underplated .000050 [0.00127] min. nickel

Related Product Data

Contact Arrangement—page 40
Performance Characteristics—
page 41

Mateable Receptacles:

HDF-20 Metal-Shell—page 124 HDE—pages 110-121 (Sizes 1–4 only)

HDP—pages 90-109

HD-20 Board Mount—pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 126

Ribbon Cable—page 125

Accessories:

Commoning Strip—page 146

Mating Hardware—pages 146-150,

153 & 154

Application Tooling—page 127

Technical Documents

Product Specification—108-40012



HDF-20 Low Profile All-Plastic Connectors (for Round Conductor Flat Ribbon Cable)

Material and Finish

Housing, Cover & Cable Stabilizer—Black thermoplastic, 94V-0 rated

Threaded Inserts—Brass, unplated Pin Contacts—Phosphor bronze, duplex plated .000030 [0.00076] gold on mating end, .000100-.000200 [0.00254-0.00508] bright tin on termination end, with entire contact

underplated .000050 [0.00127] nickel

Related Product Data

Contact Arrangement—page 40
Performance Characteristics—page 41

Mateable Receptacles: HDF-20 AlI-Plastic—page 124 HD-20 Board Mount—pages 54-71, 78-85, 87-89

HDE All-Plastic—pages 147, 148

Mating/Panel Mounting—page 126

Ribbon Cable—page 125

Accessories: Mating Hardware—pages 146-150, 153, 155

Application Tooling—page 127

Technical Documents

Product Specifications— 108-40012 HDF-20 Low Profile Connectors

Plug Assemblies



Housing and Covers are Preassembled; Cable Stabilizer is Separate.

Receptacle Assemblies



Housing and Covers are Preassembled; Cable Stabilizer is Separate.

No. of	Optional	Plug Assem	bly Part No.	Receptacle Assembly Part No.		
Contact Pos. & (Shell Size)	Cable Stabilizer Part No.	With Standard Mounting Holes	With Threaded Inserts	With Standard Mounting Holes	With Threaded Inserts	
9 (1)	747275-4	1658615-4	1658611-4	1658614-4	1658609-4	
15 (2)	747275-3	1658615-3	1658611-3	1658614-3	1658609-3	
25 (3)	747275-2	1658615-2	1658611-2	1658614-2	1658609-2	
37 (4)	747275-1	1658615-1	_	1658614-1	1658609-1	

Note: All assemblies are supplied with housing and cover pre-assembled. Optional cable stabilizer must be ordered separately.

Ribbon Cable Parameters

	28 AWG [0.08	mm²] Part No.	26 AWG [0.15mm ²] Part No.
No. of Conductors	Length	Per Reel	Length Per Reel
Conductors	100 Ft. [30.5m]	500 Ft. [152.4m]	500 Ft. [152.4m]
9	1-57040-2	1-971111-2	57034-2
15	1-57040-5	1-971111-5	57034-5
25	57040-2	971111-2	57034-9
37	1-57040-8	1-971111-8	1-57034-3
50	57040-6	971111-6	1-57034-5

Note: All part numbers are RoHS compliant.


www.tycoelectronics.com



HDF-20 Plugs/Receptacles Mating and Panel Mounting Specifications

Plug/Receptacle Mating

Panel Cutouts



The .265/.256 [6.73/6.50] dimensions are required to assure full mating of connector halves. These dimensions must be taken into consideration when determining the method of mounting, panel thickness, etc.

Panel Mounting


Plugs and receptacles can be mounted to a panel from either the front or rear, using a variety of accessory hardware. Typical examples are shown below.




Typical Front-Panel Mounted HDF-20 Plug



Typical Rear-Panel Mounted HDF-20 Plug





Cutout for Rear Mount and Short Latching Blocks

Shell	Mounting Method	Dimensions								
Size (Pos.)	Front/Rear Panel	Α	В	С	D	E	F	H*	J*	K
1	Front	.984 24.99	.492 12.50	.874 22.20	.437 11.10	.513 13.03	.257 6.53	_	_	.083 2.11
(9)	Rear	.984 24.99	.492 12.50	.806 20.47	.403 10.24	.449 11.41	.225 5.72	.550 13.97	.750 19.05	.132 3.35
2 (15)	Front	1.312 33.33	.656 16.66	1.202 30.53	.601 15.27	.513 13.03	.257 6.53	_	_	.083 2.11
	Rear	1.312 33.33	.656 16.66	1.134 28.80	.567 14.40	.449 11.41	.225 5.72	.730 18.54	.750 19.05	.132 3.35
3	Front	1.852 47.04	.926 23.52	1.743 44.27	.872 22.15	.513 13.03	.257 6.53	_	_	.083 2.11
(25)	Rear	1.852 47.04	.926 23.52	1.674 42.52	.842 21.39	.449 11.41	.225 5.72	1.275 32.39	.750 19.05	.132 3.35
4	Front	2.500 63.50	1.250 31.75	2.391 60.73	1.196 30.38	.513 13.03	.257 6.53	_	_	.083 2.11
(37)	Rear	2.500 63.50	1.250 31.75	2.326 59.08	1.163 29.54	.449 11.41	.225 5.72	1.920 46.05	.750 16.13	.132 3.35
5	Front	2.406 61.11	1.203 30.56	2.297 58.34	1.149 29.19	.623 15.82	.312 7.93	_	_	.083 2.11
(50)	Rear	2.406 61.11	1.203 30.56	2.218 56.34	1.109 28.17	.555 14.10	.278 7.06	1.753 44.52	.750 19.05	.132 3.35

^{*}Panel cutout configuration with H and J dimensions provides clearance for mounting connectors with cable clamps.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



HDF-20 Application Tooling

Application Tooling



Hand Tool Kit No. 768340-1

Consists of a hand tool frame, a universal base assembly, a bench mount kit, and connector-specific tooling for AMP-LATCH Standard and Novo Receptacles, Card-Edge Connectors, and AMPLIMITE HDF-20 Connectors.

Note: For 50-position HDF connectors, you must also order Connector-Specific Kit No. 768350-1.




HD-20 Solder Cup Connectors

Product Facts

- Preloaded duplex-plated solder cup contacts
- Shell finish in choice of standard zinc or tin
- Two-piece 94V-0 rated plastic insert
- Anti-solderwicking contact design
- Intermateable with other subminiature D connectors
- Available in 9, 15, 25 and 37 position (shell sizes 1-4) plugs and receptacles
- Easy application without special application tools
- Shields offer full EMI shielding and ESD insulation
- Crimped shield termination for low impedance
- Shield crimp provides strain relief
- Shields may be post molded or covered with enclosures
- Recognized under the Component Program of Underwriters
 Laboratories, Inc., File No. E28476
- Listed under Underwriters
 Laboratories Inc.,
 connectors for use in
 data, signal, control &
 Power Applications —
 components,
 File No. E127344
- Certified by Canadian Standards Association, File No. LR 97981







HD-20 Solder Cup Connectors (Continued)





Material and Finish:

Shell—Steel, tin or zinc plated **Insert**—94V-0 rated thermoplastic, black

Contacts—Phosphor bronze; duplex plated with gold flash on mating end, tin on solder cup, with entire contact nickel underplated

#4-40 UNC x 3.0 2 Plcs. -607 ± .015 [15.40 ± 0.38] -426 [1.20] -426 [1.20]

Related Product Data:

Mateable Connectors:

HDE-pages 110-119

HDF-pages 124-126

HDP—pages 90-101

HD-20 Solder Cup—pages 128-130 **HD-20 Board Mount**—pages 54-71, 78-85, 87-89

Cable Clamps—pages 132, 133, 135, 136, 140, 141, 144, 145

Mating Hardware—pages 146-150, 151-154

Technical Documents:


Product Specification 108-40031

Instruction Sheet

408-9193



Receptacle



Shell	No. of	Dimen	sions	Plug Part	Numbers	Receptacle	Part Numbers
Size	Contact Positions	A	В	Tin Plated Shell	Zinc Plated Shell	Tin Plated Shell	Zinc Plated Shell
1	9	1.210 30.80	.984 24.99	5-747904-2	5-747904-2	5-747905-2	5-747905-2
2	15	1.544 39.20	1.313 33.32	5-747908-2	5-747908-2	5-747909-2	5-747909-2
3	25	2.089 53.01	1.853 47.04	5-747912-2	5-747912-2	5-747913-2	5-747913-2
4	37	2.734 69.40	2.502 63.50	5-747916-2	5-747916-2	5-747917-2	747917-4



HD-20 Solder Cup Shielding Hardware Enclosure Kits



Each kit contains

- Connector with preloaded, nonremovable contacts
- Shield
- Enclosure
- Two jackscrews

Material and Finish:

Connector Shell—Steel, tin plated **Connector Insert**—94V-0 rated thermoplastic, black

Shields—Steel, tin plated **Enclosure**—PVC, black

Jackscrews—Brass, zinc coated

Contacts—Phosphor bronze; duplex plated with gold flash on mating end, tin on solder cup, with entire contact nickel underplated

Related Product Data:

Mateable Connectors:

HDF—pages 124-126 **HDP**—pages 90-101


HD-20 Solder Cup—pages 128-130 **HD-20 Board Mount**—pages 82-85, 87-89

Technical Documents:

Product Specification 108-40031

Instruction Sheets


408-9193



Shell	No. of Contact	D	Dimensions		Cable	Cable Kit Insulation Part Numbers		Shielding E Expansion				
Size	Positions	С	D	E	Diameter	Plug	Receptacle	Cable O.D. (Max.)	Part Number			
					.217270 5.51-6.86	1571650-4	1571654-4					
1	9	1.64	1.33	.659	.270324	1571650-5	1571654-5	.355	58241-4			
'	9	41.67	33.74	16.74	6.86-8.23	1571650-6	1571654-6	9.02	36241-4			
					.324385 8.23-9.78	1571650-6	1571654-6					
					.217270 5.51-6.86	1571651-4	1571655-4					
2	15	1.64	1.65	.659	.270324	1571651-5	1571655-5	.355	58241-4			
2	15	41.67	41.86	16.74	16.74	16.74	16.74	6.86-8.23	1571651-6	1571655-6	9.02	30241-4
					.324385 8.23-9.78	1571651-6	1571655-6					
					.217270 5.51-6.86	1571652-4	1571656-4					
3	25	1.64	2.20	.659	.270324	1571652-5	1571656-5	.465	58241-1			
3	23	41.67	55.86	16.74	6.86-8.23	1571652-6	1571656-6	11.56	30241-1			
					.324385 8.23-9.78	1571652-6	1571656-6					
4	37	2.35 59.67	2.82 71.63	.659 16.74	.455480 11.58-12.19	1571653-2	1571657-2	.562 14.28	58241-2			

Note: Components of the kits are shipped unassembled and bulk-packaged in quantities of 100 pieces.

HD-20 Solder Cup Shielding Hardware Crimping Tool



Assembled Tooling: Part Number 1571750-1 Individual Tools (for customer fabrication): 1571749-1 & 1571749-2



Accessories

Numerous accessories are available for strain relief and cable clamping, shielding, connector-to-connector mating, connector-to-connector pc board mounting, and keying. These accessories are illustrated and tabled on the following pages.

To help discern the accessories available for a particular connector type, refer to the Product Selection Guide at the beginning of the connector section. Also, the connector the accessory is used with is listed under the Related Product Data heading next to the accessory listing.



Section Contents

Unshielded Cable Clamps	
Universal Cable Clamps for Jacketed Cable	132
One-Piece, All-Plastic Cable Clamp	3, 134
Straight/90° Low Profile Cable Clamps	135
Slide-On Back Covers	136
Box and Lid, Straight/90° Exit	137
Clam Shell, Straight/45°	138
Straight Exit, Dataphone	139
Straight Exit for Jacketed Cable (Two-Piece)	
Straight/90° Exit	140
Shielded Cable Clamps	
Straight Exit RFI/EMI Shields for Jacketed Cable	
(HDE, HDP)	141
Straight/90° Exit RFI/EMI Die Cast Shields for	
Jacketed Cable (HDE, HDP)	142
Crimp and Split-Ring Ferrules14	

Hardware	
Commoning Strip	146
Male Screw Retainers for Metal-Shell Connectors	
(HDE, HDP)	
Male Screw Retainers for All-Plastic Connectors (HDE)	147
Male Screw Retainers for Metal-Shell and All-Plastic	
Connectors (HDF)	147
Female Screwlocks for Metal-Shell and All-Plastic	
Connectors (HDE, HDF, HDP)	
Slide Latches149,	150
Slide Latch Clips	
Locking Post Assemblies	
Spring Latches (Two-Piece)	
Latching Blocks (HDE, HDF, HDP, HD)153,	
Standoff Bushings	
Keying Plug	155
EMI/RFI Gasket	155



Unshielded Cable Clamps

Material and Finish:

Cable Clamp Housing-Thermoplastic, black

Cable Clamp Wedge Set-Thermoplastic, black

4-40 Mounting Screws-Steel, zinc plated


Related Product Data:

Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell—pages 90-102 Other accessory capabilities: Spring Latches (Two Piece)—

page 152

Technical Documents:

Instruction Sheet—408-9238



Female Screwlock

(Order separately, see page 144.)

2. Each kit is comprised of two cable clamp halves, two cable clamp wedge sets and two mounting crews.

Material and Finish:

Cable Clamp Housing-

Thermoplastic, gray

4-40 Mounting Screws-

Steel, zinc plated

4-40 Housing Screws & Hex Nuts


—Steel, zinc plated

Related Product Data:

Connectors used with: HDE All-Plastic—pages 112 & 113 HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell—pages 90-102 Other accessory capabilities: Spring Latches (Two Piece) page 152

Technical Documents:

Instruction Sheet—408-7555



Shell	Dime	nsions	Cable Dia.	Cable Clamp Kit No.
Size	Α	В	(Max.)	Individual
2	1.550 39.37	.826 20.98	.350 8.89	5206471-1
3	2.090	.826	.335 8.51	5206472-1
3	53.09	20.98	.460 11.68	5745134-1
4	2.738 69.55	.826 20.98	.675 17.15	5745081-1
5	2.644 67.16	.938 23.83	.775 19.69	5745082-1

Notes: 1. All parts are packaged unassembled.

2. Straight or 90° cable exit is achieved by inserting AMP-TY Cable Ties through cable tie openings and clamping the cable to one housing half only.



The Tyco Electronics Quik-Snap Backshell Kit is a one-piece, all-plastic cable clamp kit designed for use with either the AMPLIMITE HDP-20, HDP-22, or HDE, all-plastic or metal-shell connectors.

Kits are available for connector sizes 1, 2, 3, and 4 with a cable exit option of 180° or 120°.

Each kit contains:

- 1-Hinged, plastic clamp
- 2-Self-tapping screws
- 1-Strain relief clip
- 1-Cable exit gate plug (Used to close unused exit)

(For metal-shell connector applications an optional kit with 2 retainer clips and screws is available.)

Material and Finish:


Cover—Polypropylene, black
Strain Relief Clip—Stainless steel
Retainer Clip—Stainless steel
Screws—Carbon steel, zinc plated
Cable Gate—Polypropylene, Black


Related Product Data:

Connectors used with: HDP Metal-Shell—pages 90-102 HDE All-Plastic—pages 112 & 113 HDE Metal-Shell—pages 114 & 115

Technical Documents:

Instruction Sheet—408-7837 Instruction Sheet—408-9544 One-Piece, All-Plastic Cable Clamp for Jacketed Cable, 180°/120° Exit (HDP and HDE) (Quik-Snap)









Shell Size	Cable Dia. Range (Ref.)	Dimension A	Kit Number* with Retainer Screws and Clips	Kit Number*** without Retainer Screws and Clips	Packaging	
			5749914-1	_	Bulk Pkg.	
1	.075250 1.91-6.35	.785 19.94	5749914-2	5750100-1	- Unit Kit	
	1.01 0.00	10.01	5749914-4**	_	Unit Kit	
3	.180460 4.57-11.68	1.650 41.91	5749626-2	5750078-1	Unit Kit	
4	.250550	2.285	5749916-2	_	Bulk Pkg.	
4	6.35-13.97	58.04	5749916-2	_	Unit Kit	

^{*}For metal-shell connectors only.

^{**}Type 2 Retainer Clip

^{***}For Metal-Shell or All-Plastic Connectors



Unshielded Cable Connector and Clamp Kits

The AMPLIMITE Quik-Snap Backshell and Connector kit presents a complete package for your unshielded subminiature D connector needs. Kits are available for Shell Sizes 1, 2 and 3, and are packaged 25 and 100 kits per unit.

Each kit contains:

- 1-Hinged Plastic Clamp
- 2-Retention Screws
- 2-Retention Clips
- 1-Cable Gate Plug
- 1-Strain Relief Clip
- 2-Self Tapping Screws
- 1-Connector and Contacts

Material and Finish:

Cover—Polypropylene, black
Retention Screws—Steel, zinc plated
Retention Clips—Stainless steel
Cable Gate Plug—Polypropylene,
Rlack

Strain Relief Clip—Stainless steel Self Tapping Screws—Steel, zinc plated

Contacts—Brass (HDP Pins), Phosphor Bronze (All Others), plated gold flash on the mating end, .000100 [0.00254] min. tin or tin on the terminating end, all over .000030 [0.00076] min. nickel underplating

Housing—Polyester or nylon, glass-filled, UL rated 94V-0, black

Shell—Steel, plated .000200 [0.00508] min. tin over .000050 [0.00127] min. copper

Technical Documents:

HDE Connectors: Instruction Sheets— 408-6621

Application Specifications-

114-40002 114-40003

HDP Connectors:

Application Specifications-

114-10000


114-40030

Cable Clamps:

Instruction Sheet—408-9544

Retainer Clips:

Instruction Sheet—408-7837



Unshielded Cable Clamp Kits with HDP-20 Connectors

Shell Size	Cable Dia. Range (Ref.)	Dimension A	Plug Kit Part No.	Receptacle Kit Part No.	Packaging
1	.075250 1.91-6.35	.785 19.94	749808-8	749812-7	100/pack
2	.170380 4.32-9.65	1.110 28.19	749808-9	_	100/pack
3	.180460 4.58-11.68	1.650 41.91	749808-7	1-749812-1	100/pack

Unshielded Cable Clamp Kits with HDE-20 All-Plastic Connectors


Shell	Cable Dia.	Dimension	Plug Kit	Receptacle Kit	Packaging
Size	Range (Ref.)	A	Part No.	Part No.	
3	.180460 4.58-11.68	1.650 41.91	749809-9	749813-8	100/pack



Unshielded Cable Clamps

Low Profile Cable Clamps feature a two-piece construction which allows the two cover halves to be snapped together, no hardware is required for assembly. They can be used on plugs or receptacles and will not interfere with commonly used mating hardware. Sufficient Cable Support Gates (or a Cable Support Gate Latch) are supplied with each cable clamp kit to achieve adjustable clamping over a wide range of jacketed cable diameters.

Straight Exit Low Profile for Jacketed Cable



Material

Black thermoplastic

Related Product Data:

Connectors used with:
HDE All-Plastic—pages 112 & 113
HDE Metal-Shell—pages 114 & 115
Other accessory capabilities:
Male Screw Retainers—
pages 146 & 147

Female Screwlocks—page 148 Locking Posts and Slide Latches pages 149-151

Latching Blocks—pages 153 & 154


		Dimension	ns			
Shell			В	Cable Dia.	Cable Cl	amp Kit No.
Size	Α	When used On Plug	When used on Receptacle	(Max.)	Individual	Bulk Packed*
1	.732 18.59	1.582 40.18	1.533 38.94	.330 8.38	745547-1	745547-2
2	1.056 26.82	1.582 40.18	1.533 38.94	.425 10.80	745553-1	745553-2
3	1.604 40.74	1.700 43.18	1.651 41.94	.550 13.97	745560-1	745560-2


*Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- 2. Each kit is comprised of two cover halves (F and M) and an assortment of cable support gates.
- 3. Cable support gate must be used as shown for small diameter cable.

90° Exit Low Profile for Jacketed Cable





Shell	Din	nension A	Cable Dia. (Max.)	Cable Clamp Kit No.
Size	When used on Plug	When used on Receptacle	Cable Dia. (Wax.)	Individual
1	1.290 32.77	1.241 31.52	.330 8.38	745550-1

Notes: 1. All parts are packaged unassembled.

Each kit is comprised of a cover half and an assortment of cable support gate latches.



Material

Black thermoplastic


Related Product Data:

Connectors used with:
HDE All-Plastic—pages 112 & 113
HDE Metal-Shell—pages 114 & 115
Other accessory capabilities:
RFI/EMI Metal Shields—
pages 141 & 142
Male Screw Retainers—
pages 146 & 147
Locking Posts and Slide Latches—
pages 149-151
Latching Blocks—pages 153 & 154

Technical Documents:

Instruction Sheet—408-6658

Slide-On Back Covers



Back Cover Half (See Note 2.)

Shell Size	Dim. A	Back Cover Kit No. Individual
1	.610 15.49	745530-1
2	.934 23.72	745530-2
3	1.482 37.64	745530-3
4	2.134 54.20	745530-4

Notes: 1. All parts are packaged unassembled.

Each slide-on back cover kit includes two identical cover halves which snap together over the connector.



Box and Lid Cable Clamps can be used on either plugs or receptacles and will not interfere with commonly used hardware. Their hinged construction allows easy assembly to a harness. A wide range of cable diameters are accommodated through the use of cable support gates, supplied with each cable clamp.

Cable clamps are available in kits with appropriate hardware for convenient plug/receptacle mating. See below for kits with Male Screw Retainers.

Material and Finish:

Cable Clamp Housing-

Thermoplastic, black with textured finish

Gates—Thermoplastic, black

Flat Head Screws—Steel, black, zinc

Related Product Data:

Connectors used with:

HDP Metal-Shell—pages 90-102

Other accessory capabilities: Male Screw Retainers-

pages 146 & 147

Female Screwlocks—page 148 Locking Posts and Slide Latches pages 149-151

Spring Latches (Two Piece)-

Latching Blocks—pages 153 & 154

Technical Documents:

Instruction Sheet—408-7555

Material and Finish:

Cable Clamp Housing-

Thermoplastic, black with textured finish

Gates—Thermoplastic, black

Flat Head Screws—Steel, black, zinc plated

Male Screw—Steel, zinc plated yellow chromate

Retaining Clip—Stainless steel


Related Product Data:

Connectors used with: HDP Metal-Shell—pages 90-102

Technical Documents::

Instruction Sheets-

408-7555 408-7837



Shell Size 1 & 2

Shell Size 3 & 4 & 5


Shell Dimer		nsions	Cable Dia. M	ax. (Ref.)	Cable CI	amp Kit No.	
Size	A B		Straight Cable Exit	90° Cable Exit	Individual	Bulk Packed*	
1	.755 19.18	.630 16.00	.160 4.06	.160 4.06	207467-1	207467-2	
2	1.078 27.38	.630 16.00	.320 8.13	.320 8.13	207470-1	_	
3	1.620 41.15	.770 19.56	.390 9.91	.390 9.91	207345-1	207345-2	
4	2.268 57.61	.770 19.56	.640 16.26	.405 10.29	207473-1	207473-2	
5	2.178 55.32	.880 22.35	.490 12.45	.490 12.45	207476-1	_	

*Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- Cable diameter is adjustable by changing cable support gates. Use the flat side of cable support gates for discrete wire, and the semicircle side for jacketed cable.
- 3. Cable clamp assemblies are available in kits with male screw retainers, see below.

Box and Lid Straight/90° Exit Cable Clamp Kits with Male Screw Retainers



Shell Size 1 & 2

Shell Size 3 & 4 & 5

Shell Size	Cable Clamp Kit No.
1	5207908-1
2	5207908-4
3	5207908-7
4	1-5207908-0
5	1-5207908-3

Notes: 1. All parts are packaged unassembled.

- 2. Each kit is comprised of a cable clamp and male screw retainer hardware(2 each). Male screw retainers are also available in kit form, see page 146.
- 3. For ordering cable clamps separately, see above.

Note: All part numbers are RoHS compliant.

Cable Clamp (See Note 3.)



Straight/45° Exit Cable Clamps can be used on either a plug or receptacle and will not interfere with commonly used hardware, such as Male Screw Retainers, Female Screw-locks or Spring Latches and Latching Blocks. Their hinged construction allows easy assembly to a harness. Also, the straight or 45° angle of the cable exit is achieved by merely positioning the Cable Support Gate for the desired angle prior to installing the assembly onto the plug or receptacle. Adjustable screws are used to tighten cable strain reliefs. Cable Clamp assemblies

Cable Clamp assemblies are available in kits with appropriate hardware for convenient plug/receptacle mating.

Material and Finish: Cable Clamp Housing—

Thermoplastic, black with textured finish **Gates**—Thermoplastic, black

Pan Head Screws, 6-32 Set Screw and 6-32 Square Nut—Steel, zinc plated (sizes 1 and 2 include self-tapping screws only)

Related Product Data:

Connectors used with:

HDP Metal-Shell—pages 90-102

Other accessory capabilities: Male Screw Retainers—

pages 146 & 147

Female Screwlocks—page 148 Locking Posts and Slide Latches pages 149-151

Spring Latches (Two Piece)—page 152

Latching Blocks—pages 153 & 154

Technical Documents:

Instruction Sheet—408-7555

Material and Finish:

Cable Clamp Housing-

Thermoplastic, black with textured finish

Gates—Thermoplastic, black

Pan Head Screws, 6-32 Set Screw and 6-32 Square Nut—Steel, zinc plated (sizes 1 and 2 include self-tapping screws only)

Male Screw—Steel, zinc plated yellow chromate

Retaining Clip—Stainless steel

Related Product Data: Connectors used with:

HDP Metal-Shell—pages 90-102


Technical Documents:

Instruction Sheets—

408-7555 408-7837

Revised 1-08

Note: All part numbers are RoHS compliant.




Shell		Dimen			Cable Dia.	Short Cable Clamp Part No.		Standard Cable Clamp Part No.	
Size	Α	В	С	D	(Max.)	Individual	Bulk Packed*	Individual	Bulk Packed*
1	1.625 41.28	.750 19.05	.640 16.26	.640 16.26	.256 6.30	!		5205729-1	5205729-3
-	1.250 31.75	1.073 27.25	.600 15.24	.640 16.26	.320 8.13	5206393-1	_	_	_
2	1.625 41.28	1.073 27.25	.640 16.26	.640 16.26	.320 8.13	_	_	5205730-1	5205730-3
3	1.250 31.75	1.615 41.02	.600 15.24	.640 16.26	.420 10.67	5206390-1	5206390-3	_	_
3	1.625 41.28	1.615 41.02	.640 16.26	.640 16.26	.420 10.67	_	_	5205718-1	5205718-4
4	1.625 41.28	2.263 57.48	.640 16.26	.640 16.26	.490 12.45	_	_	5205731-1	_

*Each part is individually bulk packed for multiple assembly orders.

Notes: 1. All parts are packed unassembled.

- Quantity of pan head screws supplied with cable clamp assembly varies with shell size.
- 3. Cable clamps are available in kits with male screw retainers, see below.
- 4. All pan head screws have combination cross-recessed and slotted heads.



Shell Size		ble Clamp No.	Standard Cable Clamp Kit No.		
	Individual	Bulk Packed*	Individual	Bulk Packed*	
1	_	_	5206478-1	_	
2	_	_	5206478-2	_	
3	1-5206478-2	2-5206478-6	5206478-3	2-5206478-2	
4	_	_	5206478-4	_	
5	_	_	5206478-5	_	

*Each part is individually bulk packed for multiple assembly orders.

Notes: 1. All parts are packaged unassembled.

- Each kit is comprised of a cable clamp and male screw retainer hardware (2 each). Male screw retainers are also available in kit form, see page 146.
- For ordering cable clamps separately, see above.

Catalog 82068



Material and Finish:

Cable Clamp Housing— Nylon, black

4-40 Fillister Head Screws & Hex Nuts—Steel, clear zinc plated **Jackscrews**—Steel, black zinc plated

Related Product Data:

Connectors used with: HDP Metal-Shell—pages 90-102

Straight Exit Dataphone Metal-Shell HDP-20 Plug or Receptacle (Shown for Ref. only) Female Screwlock (Order separately, see page 144.)

Shell Size	Dimer	nsions B	Max. Cable Dia. (without Gate)	Max. Cable Dia. (with Gate)	Cable Gate Identification*	Thread Size	Cable Clamp Kit No.
			(without date)	.200 5.08	2A		
2	1.575 40.01	1.312 33.32	.400 10.16	.260 6.60	2B	4-40	5745122-2
				.320 8.13	2C		
				.250 6.35	3A		
3	2.115 53.72	1.421 36.09	.500 12.70	.340 8.64	3B	4-40	5745121-2
				.420 10.67	3C		

^{*}Molded-in identification (as shown in chart above) is provided on cable support gates to facilitate proper selection with regard to shell size and maximum acceptable cable diameter.

Notes: 1. All parts are packaged unassembled.

2. Cable diameter is adjustable by changing cable support gates.

Straight Exit for Jacketed Cable (Two-Piece)

This cable clamp allows cable to be fully prepared and terminated to the connector before the clamp is installed.

Material and Finish:

Cable Clamps—ABS black 4-40 Fillister Head Screws and Hex Nuts—Steel, zinc plated

4-40 Mounting Screws—Steel, zinc plated


Jackscrews—Stainless steel, passivated

Related Product Data:

Ferrules—pages 143-145
Connectors used with:
HDE Metal-Shell—pages 114 & 115
HDP Metal-Shell—pages 90-102
Other accessory capabilities:
Spring Latch (Two-Piece)—

Technical Documents:

Instruction Sheet—408-6609



Cable Clamp Kits with Grommets

Shell		Dimer	nsions		Cable	No. of	Kit Numbers
Size	Α	В	С	D	O.D. Range	Grommets Per Set	Kit Numbers
1	1.215 30.86	1.910 48.51	.570 14.48	.630 16.00	.185320 4.70-8.13	4	5748678-1
2	1.545 39.24	1.910 48.51	.620 15.75	.620 15.75	.185320 4.70-8.13	4	5748678-2
3	2.090 53.09	1.920 48.77	.680 17.27	.640 16.26	.255470 6.48-11.94	6	5748678-3
4	2.738 69.55	1.920 48.77	.800 20.32	.620 15.75	.255470 6.48-11.94	6	5748678-4
5	2.644 67.16	1.920 48.77	.900 22.86	.730 18.54	.255470 6.48-11.94	6	5748678-5

Notes: 1. All parts are packaged unassembled.

- Jackscrews must be purchased separately.
- 3. Split-ring and crimp ferrules are shown on pages 143-145.
- 4. Shielded cable clamps will not accept connector housings with clinch nuts.

Note: All part numbers are RoHS compliant.

page 152



Straight/90° Exit Cable Clamps can be used on a plug or receptacle and will not interfere with commonly used mating hardware. Their three-piece construction allows easy assembly to a cable harness. Also, the same cable clamp components are used for both straight and 90° cable exit applications. This is accomplished by simply positioning the Male and Female Panels on the Yoke for the desired angle.


Material

Black thermoplastic


Related Product Data:


Connectors used with:
HDE All-Plastic—pages 112 & 113
HDE Metal-Shell—pages 114 & 115
HDP Metal-Shell—pages 90-102
Other accessory capabilities:
Female Screwlocks—page 148
Locking Posts and Slide Latches—pages 149-151

Latching Blocks—pages 153 & 154



Straight Cable Exit Application





Typical Cable Support Gate (Supplied with Cable Clamp Kit)

Ohall Oias	Cable Clamp	Dimer	nsions	Cable	Cable Clamp Kit No.	
Shell Size	Configuration	Α	В	Dia.	Individual	
	Straight Exit	1.906	1.672	.550	745306-1	
3	90° Exit	2.066	1.396	.550		
4	Straight Exit	2.424 1.820		750	745044.4	
	90° Exit	2.638	1.596	.750	745311-1	

Notes: 1. All parts are packaged unassembled.

Each cable clamp assembly includes a yoke, male panel, female panel and four cable support gates.The cable diameter is adjustable by changing the cable support gates.

Note: All part numbers are RoHS compliant.

www.tycoelectronics.com

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803 South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208



Shielded Cable Clamps

Straight Exit RFI/EMI Shields for Jacketed Cable (Two-Piece)

This RFI/EMI shield allows cable to be fully prepared and terminated to the connector before the shield is installed. During installation, the shield of the jacketed cable is folded back and compressed into the cable opening of the RFI/EMI shield. For greater cable support and/or shielding effectiveness, split-ring and crimp ferrules are available (pages 143-145).

Material and Finish:

Die Cast Shield—Zinc alloy, plated bright nickel over bright copper

Metal-Plated Plastic Shield-Thermoplastic, plated nickel over copper

4-40 Fillister Head Screws and Hex Nuts-Steel, zinc plated 4-40 Mounting Screws—Steel, zinc

plated Jackscrews—Stainless steel, passivated

Related Product Data:

Ferrules—pages 143-145 Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell (Tin plated only)—pages 90-102 Other accessory capabilities: Spring Latch (Two-Piece)page 152

Technical Documents:

Product Specification— 108-40032 Instruction Sheet—408-6609

A	
	1,920
C	[48.77]
HDE or HDP Plug or Receptacle (Shown for Ref. only)	4-40 Male Jackscrew Kit Nos.: 747784-8 (bulk packed)*† *Each part is individually bulk packed for multiple kit orders. +Slotted for screwdriver use

Shell		Dimen	sions		Cable	Die Cast	Metal-Plated		Grommet Sets		
Size	Α	В	С	D	O.D. (Max.)	Shield Kit Numbers	Plastic Shield Kit Numbers	Cable O.D. Range	No. of Grommets Per Set	Part Number	
					.200 5.08	5745171-2	5745854-5	_	_	_	
1	1.215 30.86	1.910 48.51	.550** 13.97	.620** 15.75	.250 6.35	5745171-1	5745854-3	_	_	_	
					.370 9.40	5745171-5	5745854-1	.185320 4.70-8.13	4	747746-1	
					.225 5.72	5745172-3	5747099-7	_	_	_	
	1.545	1.910	.620	.620	.300 7.62	5745172-2	5747099-5	_	_	_	
2	39.24	48.51	15.75	15.75	.375 9.53	5745172-1	5747099-3	.185320 4.70-8.13	4	747746-1	
					.430 10.92	1-5745172-3	5747099-1	_	_	_	
				.280 7.11	5745173-5	5745833-9	_	_	_		
				.350 8.89	5745173-4	5745833-7	_	_	_		
3	2.090 53.09	1.920 48.77			.430 10.92	5745173-3	5745833-5	_	_	_	
					.480 12.19	5745173-2	5745833-4	_	_	_	
					.530 13.46	5745173-1	5745833-1	.255470 6.48-11.94	6	747973-1	
						.350 8.89	5745174-5	5747100-9	_	_	_
							.425 10.80	5745174-4	5747100-7	_	_
4	2.738	1.920	.800	.620	.500 12.70	5745174-3	-	_	_	_	
4	69.55	48.77	20.32	15.75	.530 13.46	2-5745174-7	_	.255470 6.48-11.94	6	747973-1	
					.575 14.61	5745174-2	5747100-3	_	_	_	
					.650 16.51	5745174-1	5747100-1	_	_	_	
					.375 9.53	5745175-6	_	_	_		
					.450 11.43	5745175-5		_	_	_	
_	2.644	1.920	.900	.730	.525 13.34	5745175-4		.255470 6.48-11.94	6	747973-1	
5	67.16	48.77	22.86	18.55	.600 15.24	5745175-3	_	_	_	_	
					.675 17.15	5745175-2	_	_	_	_	
					.750	==15155					

Cable Clamp Kits with Grommets

					Cable	No. of	Kit Nu	ımbers
Shell		Dimen	sions		O.D.	Grommets	Dis Cost Objets	Metal-Plated
Size	Α	В	С	D	Range	Per Set	Die Cast Shield With Grommets	Plastic Shield With Grommets
1	1.215 30.86	1.910 48.51	.550 ** 13.97	.620** 15.75	.185320 4.70-8.13	4	5748676-1	5748677-1
2	1.545 39.24	1.910 48.51	.620 15.75	.620 15.75	.185320 4.70-8.13	4	5748676-2	5748677-2
3	2.090 53.09	1.920 48.77	.680 17.27	.620** 15.75	.255470 6.48-11.94	6	5748676-3	5748677-3
4	2.738 69.55	1.920 48.77	.800 20.32	.620 15.75	.255470 6.48-11.94	6	5748676-4	5748677-4
5	2.644 67.16	1.920 48.77	.900 22.86	.730 18.54	.255470 6.48-11.94	6	5748676-5	5748677-5

5745175-1

Notes: 1. All parts are packaged unassembled.

Jackscrews must be purchased separately.
 Split-ring and crimp ferrules are shown on pages 143-145.

** The following dimensions apply to metal-plated plastic Size 1: C=.570 [14.48], D=.630 [16.0] Size 3: D=.640 [16.26]

5747098-1

4. Shielded cable clamps will not accept connector housings with clinch nuts.

Note: All part numbers are RoHS compliant.

www.tycoelectronics.com



Both the straight exit and the 90° exit die cast RFI/EMI shield allows cable to be fully prepared and terminated to the connector before the shield is installed. During installation, the shield of the jacketed cable is folded back and compressed into the cable opening of the RFI/EMI shield. For greater cable support and/or shielding effectiveness, splitring and crimp ferrules are available (pages 143-145).

Material and Finish:

Shield—Zinc alloy, plated nickel over copper

4-40 Pan Head Screws & Latch Screws (90° Exit Only)—Steel, zinc

One-Piece Slide Latch (90° Exit Only)—Stainless steel

Related Product Data:

Ferrules—pages 143-145 Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell (Tin plated **only)**—pages 90-102

Technical Documents:

Product Specification-108-40032

Instruction Sheet—408-6769

Straight Exit RFI/EMI Die Cast Shield for Jacketed Cable (Two-Piece)	1.805 [45.85]
HDE or HDP Plug or Rec (Shown for Ref. onl	000 000 000 000 000 000 000 000 000 00


Shell Size	No. of Positions	ID Letter	Cable Dia. w/Ferrules	Part Number	Grommet Kit
		E	.260300 6.60-7.72	5745919-3	_
2	15	Н	.190375 4.83-9.53	5745919-2	747746-1*
		К	.190430 4.83-10.92	5745919-1	_

*Cable Dia. Range using Grommet is .185-.320 [4.70-8.13].

- Notes: 1. All parts packaged unassembled.

 2. Each kit comprised of a two-piece shield with 2 pan head screws.
 - 3. Split-ring and crimp ferrules are shown on pages 143-145.

90° Exit RFI/EMI **Die Cast Shields** for Jacketed Cable (Two-Piece)



Shell Size	Dimension A	Cable Dia. w/Ferrules	Shield with Slide Latch Kit Numbers (See Note 2)	Shield without Slide Latch Kit Numbers (See Note 3)	Grommet Kit
		.185225 4.70-6.48	5745652-4	_	_
2	2.310	.260300 6.60-7.62	5745652-3	_	_
	58.67	.190375 4.83-9.53	5745652-2*	_	747746-1
		. 190430 4.83-10.92	5745652-1	_	_
		.240280 6.10-7.11	5745653-5	_	_
		.315355 8.00-9.02	5745653-4	_	_
3	2.850 72.39	.190430 4.83-10.92	5745653-3	5747194-3	_
		.440480 11.18-12.19	5745653-2	_	_
		.380530 9.65-13.46	5745653-1*	_	747973-1

^{*}Cable Dia. with Grommet Kit: Size 2 = .185-.320 [4.70-8.13]; Size 3 = .255-.470 [6.48-11.94].

Notes: 1. All parts are packaged unassembled.

- 2. Each kit is comprised of a two-piece shield with three pan head screws and a slide latch with two 4-40 slide latch screws.
- 3. Each kit is comprised of a two-piece shield with three pan head screws.

4. Split-ring and crimp ferrules are shown on pages 143-145.



Material and Finish:

Outer Ferrule—Copper, plated .000100 [0.00254] min. tin

Inner Ferrule—.023 [0.58] thick brass, plated .000050 [0.00127] tin over copper

Related Product Data:

Shields used with: Straight Exit—pages 141 & 142 **90° Exit**—page 142

Technical Documents:

Product Specification— 108-40032

Instruction Sheets-408-9315 Hand Tool 408-9318 Die Sets

Application Tooling

Note: Crimp ferrules are for use with braided shields only. Crimp ferrules require application tooling with die sets for attachment to cable.

Split-Ring Ferrules for Foil or Braided Cable Shield (See pages 144 & 145 for Split-Ring Ferrule Part Numbers.)

Material:


Aluminum


Related Product Data:

Shields used with: Straight Exit—pages 141 & 142 **90° Exit**—page 142

Technical Document

Product Specification—108-40032








Pneumatic Bench Tool No. 312522-2 (Requires Die Set Holder No. 58449-1.)



AMP Hand Tool No. 543344-1 (See pages 144 & 145 for Hand Tool Die Set Numbers)



ferrules. Split-ring ferrules are suitable for both foil and braided shields. The ferrules do not require tooling for assembly.

Note: All part numbers are RoHS compliant.

143

used with outer and inner



Crimp and Split-Ring Ferrules

		—	- When using th	ese Shield Kit	s —	■ Use these Ferrules ■ ■				
Shell	Cable	Straight Evit	Shield Kit No.		it Die Cast d Kit No.		C	rimp Ferrule No	o. and Tooling I	No.**
Size	Dia. (Max.)	Die Cast	Metal-Plated Plastic	With Slide Latch	Without Slide Latch	Split-Ring* Ferrule No.	Inner	Outer	Die Set For Hand Tool 543344-1	Applicator Die Set
	.200 5.08	5745171-2	5745854-5	_	_	745508-2	_	_	_	_
	.240 6.10	5745171-5	5745854-1	_	_	_	7-745129-8	3-745130-8	543013-2	813809-1
1	.250 6.35	5745171-1	5745854-3	_	_	745508-3	_	_	_	
	.280 7.11	5745171-5	5745854-1	_	_	_	7-745129-9	4-745130-5	1-543013-7	813809-7
	.370 9.40	5745171-5	5745854-1	_	_	745508-6	6-745129-9	4-745130-0	543013-6	813809-5
	.225 5.72	5745172-3	5747099-7	5745652-4	_	745508-3	_	_	_	
	.240 6.10	5745172-1	5747099-3	5745652-2			7-745129-8	3-745130-8	543013-2	813809-1
	.240 6.10	1-5745172-3 5745919-1	- 5747099-1	5745652-1	_	_	7-745129-3	3-745130-8	543013-3	813809-1
	.280 7.11	1-5745172-3 5745919-1	- 5747099-1	5745652-1	_	_	7-745129-8	4-745130-5	1-543013-6	813809-7
2	.300 7.62	5745172-2 5745919-3	- 5747099-5	5745652-3	_	745508-4	_	_	_	_
	.350 8.90	1-5745172-3 5745919-1	- 5747099-1	5745652-1	_	_	7-745129-2	3-745130-9	543013-4	813809-2
	.365 9.27	5745172-1	5747099-3	5745652-2	_	_	6-745129-9	4-745130-0	543013-6	813809-5
	.375 9.53	5745172-1 5745919-2	- 5747099-3	5745652-2	_	745508-6	_	_	_	_
	.430 10.92	1-5745172-3 5745919-1	- 5747099-1	5745652-1	_	745508-1	7-745129-1	4-745130-1	543013-7	813809-3
	.240 6.10	5745173-3	5745833-5	5745653-3	5747194-3	_	7-745129-3	3-745130-8	543013-3	813809-1
	.280 7.11	5745173-5	5745833-9	5745653-5	_	745508-4	_	_	_	_
	.280 7.11	5745173-3	5745833-5	5745653-3	5747194-3	_	7-745129-8	4-745130-5	1-543013-6	813809-7
	.350 8.90	5745173-4	5745833-7	5745653-4	_	745508-5	_	_	_	_
3	.350 8.90	5745173-3	5745833-5	5745653-3	5747194-3	_	7-745129-2	3-745130-9	543013-4	813809-2
	.430 10.92	5745173-3	5745833-5	5745653-3	5747194-3	745508-1	7-745129-1	4-745130-1	543013-7	813809-3
	.430 10.92	5745173-1	5745833-1	5745653-1	_	_	7-745129-5	4-745130-1	543013-8	813809-3
	.480 12.19	5745173-2	_	5745653-2	_	745508-8	_	_	_	
	.530 13.46	5745173-1	5745833-1	5745653-1	_	745508-9	7-745129-4	4-745130-2	1-543013-0	813809-4

Continued on Page 145

^{*}For split-ring ferrules, Min. O.D. is .040 [1.02] smaller than Max. O.D.
**For inner and outer ferrules, Min. O.D. is .050 [1.27] smaller than Max. O.D. At the Max. cable O.D. the Min. insulation thickness is .060 [1.52].



Crimp and Split-Ring Ferrules (Continued)

		—	── When using these Shield Kits ── ➤			←	—— Use	these Ferrule	es ———	→
Shell	Cable	Straight Exit	Shield Kit No.	90° Exit I Shield				Crimp Ferrule	No. and Tooli	ng No.**
Size	Dia. (Max.)	Die Cast	Metal-Plated Plastic	With Slide Latch	Without Slide Latch	Split-Ring* Ferrule No.	Inner	Outer	Die Set for Hand Tool 54334-1	Applicator Die Set
	.240 6.10	5745174-4	5747100-7	_	_	_	7-745129-3	3-745130-8	543013-3	813809-1
	.280 7.11	5745174-4	5747100-7	_	_	_	7-745129-8	4-745130-5	1-543013-6	813809-7
	.350 8.90	5745174-5	5747100-9	_	_	745508-5	_	_	_	_
	.350 8.90	5745174-4	5747100-7	_	_	_	7-745129-2	3-745130-9	543013-4	813809-2
4	.430 10.92	5745174-4	5747100-7	_	_	745508-1	7-745129-1	4-745130-1	543013-7	813809-3
	.500 12.70	5745174-3	_	_	_	745508-8	_	_	_	_
	.525 13.34	5745174-1	5747100-1	_	_	_	7-745129-6	4-745130-2	1-543013-1	813809-4
	.575 14.61	5745174-2	5747100-3	_	_	1-745508-0	_	_	_	_
	.650 16.51	5745174-1	5747100-1	_	_	1-745508-1	_	_	_	_
	.240 6.10	5745175-6	_	_		_	7-745129-0	3-745130-8	543013-2	813809-1
	.365 9.27	5745175-6	_	_		_	6-745129-9	4-745130-0	543013-6	813809-5
	.375 9.53	5745175-6	_	_	_	745508-6	_	_	_	_
	.430 10.92	5745175-4	_	_	_	_	7-745129-5	4-745130-1	543013-8	813809-3
	.450 11.43	5745175-5	_	_	_	745508-7	_	_	_	_
5	.525 13.34	5745175-4	_	_	_	745508-9	_	_	_	_
	.530 13.46	5745175-4	_	_	_	_	7-745129-4	4-745130-2	1-543013-0	813809-4
	.600 15.24	5745175-3	_	_	_	1-745508-0	_	_	_	
	.650 16.51	5745175-1	5747098-1	_	_	_	1-745508-1	4-745130-3	1-543013-4	
	.675 17.15	5745175-2		_	_	1-745508-1	_	_		_
	.750 19.05	5745175-1	5747098-1	_	_	1-745508-2	_	_	_	_

^{*}For split-ring ferrules, Min. O.D. is .040 [1.02] smaller than Max. O.D.

^{**}For inner and outer ferrules, Min. O.D. is .050 [1.27] smaller than Max. O.D. At the Max. cable O.D. the Min. insulation thickness is .060 [1.52]. **Note:** Refer to page 143 for Application Tooling for ferrules.



Hardware


Commoning Strip (for HDF-20 Plugs, Size 20 Pin Contacts)


Material and Finish:

Brass, .004 [0.10] thick, tin plated **Part No. 206918-2** (Continuous Strip)

Related Product Data:

Used with HDF-20 Plugs—page 126





Notes:

- Use punching tool to remove undesired pin commoning locations on commoning strip.
 Use mating receptacle to seat strip over pins in plug. Punching tool is not supplied by Tyco Electronics.
- 2. Sold in strip form, strip contains 10,000 commoning locations.

Male Screw Retainers for Metal-Shell Connectors (HDE and HDP)

Material and Finish:

Male Screw—Steel, zinc plated clear or yellow chromate


Retaining Clip—.012 [0.31] stainless

Related Product Data:

Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell—pages 90-102

Technical Documents:

Instruction Sheet—408-7837



Male Screw	Thread Size	Dimension	Male Screw R	etainer Kit No.
Finish	Tilleau Size	Α	Individual	Bulk Packed*
		.220	5205980-1	5205980-3
	4-40	5.59	5787354-1**	_
Yellow Chromate	4-40	.200 5.08	5745136-1	5745136-2
	M3 (Metric)	.225 5.72	5207871-1	_
Clear	4-40	.220 5.59	5205980-4	5205980-5
Chromate	4-40	.200 5.08	5745136-3	5745136-4

^{*}Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- Each kit is comprised of two male screws and two retaining clips. Male screw retainers are also furnished as part of cable clamp kits (pages 137 and 138).
- Male screw retainers mate with female screwlocks (page 144), with HDF metal-shell connectors featuring 4-40 threaded inserts (page 148) and with HD metal-shell board mount connectors featuring 4-40 threaded inserts or female screwlocks.
- Retaining clip must be assembled onto connector flanges with threaded hole toward wire side of connector.
- 5. All screws have straight slotted heads except where noted.
- Retaining clip must be assembled onto connector flanges with notched side of retainer toward mating side of connector.

^{**} Phillips Head Screw



Material and Finish:

Male Screw—Steel, zinc plated yellow chromate

Retaining Clip—.012 [0.51] stainless steel

Related Product Data:


Connectors used with:

HDE All-Plastic—pages 112 & 113

Technical Documents:

Instruction Sheet-408-7837

Male Screw Retainers for All-Plastic Connectors (HDE)



Kit Numbers:

745647-1 (Individually packaged, see Note 2)

745647-2 (Bulk packed)*

*Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- 2. Each kit is comprised of two 4-40 male screws and two retaining clips.
- Male screw retainers mate with female screwlocks (page 148), with HDF All-Plastic connectors featuring 4-40 threaded inserts (page 125), with HD All-Plastic board mount connectors featuring integral standoffs with 4-40 threaded inserts and female screwlocks.
- 4. Retaining clips must be assembled onto connector flanges with threaded hole toward wire side of connector.

Material and Finish:

Male Screw—Steel, zinc plated clear chromate

Retaining Clip—.012 [0.51] stainless


Related Product Data:

Connectors used with: HDF Metal-Shell and All-Plastic pages 125 & 126

Technical Documents:

Instruction Sheet—408-7837

Male Screw Retainers for Metal-Shell and All-Plastic Connectors (HDF)



Kit Numbers:

746881-1 (Individually packaged, see Note 2)

746881-2 (Bulk packed)*

*Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- 2. Each kit is comprised of two male screws and two retaining clips.
- Male screw retainers mate with female screwlocks (page 148), and with HD board mount connectors featuring female screwlocks.
- 4. Retaining clips must be assembled onto connector flanges with threaded hole toward wire side of connector.



Material and Finish:

All Parts—Cold rolled steel, zinc plated clear or yellow chromate

Related Product Data:

Connectors used with: HDE Metal-Shell or All-Plasticpages 112-115 HDF Metal-Shell or All-Plasticpages 125 & 126

HDP Metal-Shell—pages 90-102 HD Board Mount—pages 54-71, 78-85, 87-89

Technical Documents:

Instruction Sheet—408-7837



Nut Driver, Part No. 811262-1 (Used for assembling female screwlocks to connector flange)

Female Screwlocks for Metal-Shell and All-Plastic Connector (HDE, HDF, HDP)	Flat Washers 250 [6.35]	188† [4.78] Style (A). Female Screwlocks Kit	Style (B). Standard and Long Female Screwlocks Kit .188† [4.78]
(Sh	Metal-Shell or All-Plastic Plug or Receptacle own for Ref. only.	Loci Hex Nut	Flat Washers (See Note 3.) k Washer †Part Number 5748270-2 Dimension .158 [4.01]

Connector	Style	Dimension	Thread	Finish	Kit N	lumber
Used with	Style	С	Size	FIIIISII	Individual	Bulk Packed
HD All-Plastic Right-Angle	(\(\)	.250	4-40	Yellow Chromate	5207952-1	_
Plugs and Receptacles	(A)	6.35	4-40	Clear Chromate	5207952-3	_
HDE Metal-Shell or All-Plastic	(D)	.250	4-40	Yellow Chromate	5745563-1	5745563-1
Plugs and Receptacles	(B)	6.35		Clear Chromate	5745563-3	5745563-4
		.312 7.93	4-40	Yellow Chromate	5205817-1	5205817-2
HDP or HDF Metal-Shell or All-Plastic Plugs and	(D)			Clear Chromate	5205817-3	5205817-4
Receptacles	(B)		7.93 M3 (Metric)	Yellow Chromate	5207872-1	_
·				Clear Chromate	5207872-3	_
HD or HDF All-Plastic Plugs			4-40	Yellow Chromate	5207719-1	5207719-2
and Receptacles with	(B)	.560 14.22	4-40	Clear Chromate	5207719-3	5207719-4
Integral Standoffs	. ,	17.22	2-56*	Clear Chromate	5747223-3	_

 $^{^{\}star}$ 2-56 is the male thread size. The female thread size is 4-40.

- 2. Each female screwlock kit is comprised of two assemblies as illustrated above.
- 3. One or two flat washers may be required for panel thicknesses less than .060 [1.52]. Female screwlocks are not recommended for panel thicknesses greater than .060 [1.52].
- 4. Female screwlocks with 2-56 thread size are to be used with cable clamps with mounting flanges. Female screwlocks with 4-40 and M3 (Metric) thread sizes can be used with all other cable clamps.
- 5. Female screwlocks mate with male screw retainers (pages 146 and 147).
- 6. Short female screwlocks cannot be used with HDF connectors (pages 125 & 126)

Individual Screwlocks

(Washers and Nuts not included)

Connector	Chulo	Dimension	Thread	Finish	Screwlocks	
Used with	Style	C	Size	FINISN	Individual	Bulk Packed [△]
HD All-Plastic Right-Angle	(4)	.250	4-40	Yellow Chromate	5207953-2	_
Plugs and Receptacles	(A)	6.35		Clear Chromate	5207953-3	_
		.312 7.93	4-40	Clear Chromate	_	5205818-3**
					5748558-3	5748558-4
				Yellow Chromate	5748270-2	5205818-2-
HDP or HDF Metal-Shell or All-Plastic Plugs and	(B)		M2.6** (Metric)	Clear Chromate	5749765-3	_
Receptacles			M3*** (Metric)	Clear Chromate	5747404-3	_
	(Special)	.185 4.70	4-40	Clear Chromate	5747877-3	_

[△] Each part is individually bulk packed for multiple kit orders.

[△] Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

^{△△}With captivated star washer. No additional hardware included.

[†]Part No. 5748270-2 Dimension .158 [4.01]

^{**}M2.6 is the female thread size. The male thread size is 4-40.

^{***}M3 is the female thread size. The male thread size is 4-40.



Slide Latches

Material and Finish:

4-40 Screws, Washers and Hex Nuts—Steel, zinc plated yellow chromate


2-56 Screws, Washers and Hex Nuts—Steel, zinc plated clear chromate Slide Latch—Stainless steel

Related Product Data:


Connectors used with: HDE Metal-Shell or All-Plastic pages 112-115 HDF Metal-Shell or All-Plastic pages 125 & 126 HDP Metal-Shell—pages 90-102 HD Board Mount—pages 54-71, 78-85, 87-89


Technical Documents:

Instruction Sheet—408-6551



For Shell Sizes 1 and 4






For Shell Sizes 2, 3 and 5



Slide Latches



Typical Applications of Locking Posts and Slide Latches

Shell	Chulo		Dimensions	3	Slide Latch	Kit Numbers	Side Latch
Size	Style	Α	В	С	Individual	Bulk Packed*	Only
1	1	1.397 35.48	.490 12.45	.415 10.54	5745404-1	_	164890-1
	II	1.725 43.82	.470 11.94	.547 13.89	5745583-1	_	749027-1
		1.725 43.82	.470 11.94	.415 10.54	5745583-5	_	749027-1
2	III	1.725 43.82	.470 11.94	.450 11.43	5745583-7	_	_
2		1.725 43.82	.470 11.94	.415 10.54	_	5748653-1	_
		1.725 43.82	.490 12.45	.290 7.37	5749028-1 ⁷	_	_
		1.725 43.82	.437 11.10	.415 10.54	_	5786138-1 ⁷	_
3	II	2.265 57.53	.470 11.94	.547 13.89	5745584-1	_	749996-1
J	III	2.265 57.53	.470 11.94	.415 10.54	5745584-3	_	749996-1
4	1	2.913 73.99	.490 12.45	.415 10.54	5745407-1	_	164890-4
5	III	2.819 71.60	.575 14.61	.415 10.54	5745578-3	_	749997-1

^{*}Each part is individually bulk packed for multiple kit orders.

Notes: 1. All parts are packaged unassembled.

- Each kit is comprised of a slide latch and two screws, flat washers (if required), lock washers and hex nuts.
 Style I slide latches are also furnished as part of cable clamp kits (page 142).
- Style I slide latches can be used with cable clamps that do not extend beyond the front flange of the connector or on connectors without cable clamps.
- Style II slide latches can be used with any cable clamp that has the mounting ear configuration as shown above.
- 5. Style III slide latches can be used on connectors without cable clamps or with cable clamps that do not have the mounting ear configuration shown with Style II above.
- 6. Slide latches mate with locking posts (page 151).
- 7. No nuts, washers, or lockwashers.



Slide Latch Clip Assembly for **Unfiltered Mating Half**


Material and Finish:

Screw, Washers and Hex Nut—Cold rolled steel, zinc plated clear chromate

Clip—Stainless steel

Technical Documents:


Instruction Sheet—408-7785



Kit Part Numbers:

Thread Size	Screw Length L	Pkg.	Screw Style	Part No.
4-40	.415	Unit [†]	1	5206942-1
4-40	10.54	Bulk	ı	5206942-2
2-56	.547	Unit	2	5748078-1**
2-30	13.89		2	

- † Two assemblies per package.
- * Each part is individually bulk packed for multiple kit orders.
- ** Designed for cable clamps with mounting ears. No flat washers included.



Notes:

- 1. All parts are packaged unassembled.
- Slide Latch Clip Assemblies can be used on any Subminiature D AMPLIMITE HD-20 metal-shell plug or receptacle.
- Slide Latch Clip Assemblies mate with Locking Post Assemblies shown below.

Locking Post Assembly


Material and Finish:

All Parts—Cold rolled steel, zinc plated clear or yellow chromate

Related Product Data:

Connectors used with: HDE Metal-Shell or All-Plasticpages 112-115 HDF Metal-Shell or All-Plasticpages 125 & 126 HDP Metal-Shell—pages 90-102 HD Board Mount—pages 54-71, 78-85, 87-89


Instruction Sheets-408-6551 408-7785




Thread	Locking Post	Dimensions		Locking Post Kit Number (See Note 4)		
Size	Finish	Α	В	Individual	Bulk Packed*	
	Yellow Chromate	. 410 . 110 e 10.41 2.79		5206514-1	5206514-3	
4-40	Clear Chromate	.410 10.41	.110 2.79	5206514-4	_	
	Yellow Chromate	.560 14.22	.110 2.79	5206514-6	5206514-7	
2-56	Yellow Chromate	.615 15.62	.172 4.37	5747242-1	_	

^{*}Each part is individually bulk packed for multiple kit orders.

Note: All part numbers are RoHS compliant.





- 1. All parts are packaged unassem-
- 2. Each kit is comprised of two complete assemblies, as illustrated above.
- 3. For front panel mounting, it is recommended that a shim be used between the connector flange and panel to prevent bowing of the flange.
- 4. Locking posts with 2-56 thread size are to be used with cable clamps with mounting flanges. Locking posts with 4-40 thread size can be used with all other cable clamps
- 5. Locking posts mate with slide latches (page 149).

Catalog 82068 Revised 1-08



Material


.015 [0.38] Stainless steel

Related Product Data:

Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell (Tin plated only)pages 90-102

Technical Documents:

Instruction Sheet—408-9130



745255-3 (bulk packed)*

*Two-piece spring latches are individually bulk packed for multiple part

RFI/EMI shields (pages 141).

2. Two-piece spring latches mate with latching blocks (pages 153 & 154).

Typical Application of Two-Piece Spring Latches with Straight Exit RFI/EMI Shield

Spring Latches (Two-Piece)

Material:


Stainless steel

Related Product Data:

Connectors used with: HDE Metal-Shell—pages 114 & 115 HDP Metal-Shell—pages 90-102

Technical Documents:

Instruction Sheet—408-9131



Spring Latch Part Numbers


Size	Dimension A	Two Per Package	Bulk Packed*
1-4	.540 13.72	745779-2	745779-3
5	.650 16.51	745779-5	_

^{*}Two-piece spring latches are individually bulk packed for multiple part orders.

2. Two-piece spring latches mate with latching blocks (pages 153 & 154).

Note: All part numbers are RoHS compliant.

Typical Application of Two-Piece Spring Latches with Post Molded Strain Relief



152 Catalog 82068

Revised 1-08

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-470-4425 Mexico: 01-800-733-8926 C. America: 52-55-1106-0803

South America: 55-11-2103-6000 Hong Kong: 852-2735-1628 Japan: 81-44-844-8013 UK: 44-8706-080-208

Notes: 1. These dimensions must be maintained to assure satisfactory operation of the spring latches.



Material and Finish:

Latching Blocks—Zinc
Pan Head Screws—Steel, zinc plated


Related Product Data:

Connectors used with:
HDE Metal-Shell or All-Plastic—
pages 112-115
HDF Metal-Shell or All-Plastic—
pages 125 & 126
HDP Metal-Shell—pages 90-102
HD Board Mount—pages 54-71,
78-85, 87-89
Mating/Panel Mounting—page 136

Technical Documents:

Instruction Sheet—408-9128


Latching Blocks with Threaded Hole




Shell (No. of	of Dimensions Panel		Panel	Thread		Rear-Panel Latching Block Part No.		Front-Panel Latching Block Part No.	
Contact Pos.)			Inickness	Size	Individual	Bulk Packed*	Individual	Bulk Packed*	
	.400 .190 10.16 4.83		.060	M3 (Metric)	_	745403-2	_	_	
		1.52 -	4-40	745403-8	_	_	_		
1 thru 4 (9 thru 37)	.400 10.16	.220 5.59	.030 0.76	4-40	747717-2	_	_	_	
				M3			5745007-1	_	
	.400 10.16	.250 6.35		(Metric)	_	_	208101-1	208101-2	
	10.10	0.00		4-40	_	_	208101-8	208101-9	
5 (50)	.530 13.46	.250 6.35	_	4-40	_	_	1-208101-1	_	

^{*}Bulk packed for multiple part orders.

- Notes: 1. All parts are packaged unassembled.
 - Each front panel latching block kit is comprised of two latching blocks. Two pan head screws of the appropriate length and thread size to be supplied by customer.
 - B dimension .250 [6.35] is for connector flange mounting, .220 [5.59] is for use with .030 [0.76] thick panels, and .190 [4.83] is for use with .060 [1.52] thick panels.
 - 4. Latching blocks mate with spring latches (page 152).



Typical Application of Front-Panel Mounted Subminiature D Connector using Front-Panel Latching Blocks



Typical Application of Rear-Panel Mounted Subminiature D Connector using Rear-Panel Latching Blocks

^{**}Individual kits contain two latching blocks per package.



Material

Latching Blocks—Zinc

Related Product Data:


Connectors used with: HDE Metal-Shell or All-Plasticpages 112-115 HDF Metal-Shell or All-Plasticpages 125 & 126 HDP Metal-Shell—pages 90-102 HD Board Mount—pages 54-71, 78-85, 87-89

Mating/Panel Mounting—page 136

Technical Documents:

Instruction Sheet—408-9128

Latching Blocks with Slot Recess and Thru Hole




.196 [4.98] Dia. (Max.) x .110 [2.79] Deep Slot

Shell (No. of	Dimensions		Panel	Rear-Panel Latching Block Part No.		Front-Panel Latching Block Part No.	
Contact Pos.)	Α	В	Thickness	Individual	Bulk Packed*	Individual	
1 thru 4 (9 thru 37)		.160 4.06	.090 2.29	747080-2	_	_	
	.400 10.16	.190 4.83	.060 1.52	745245-2	745245-3	_	
		.250 6.35	_	_	_	745286-2	
5 (50)	.530 13.46	.190 4.83	.060 1.52	_	_	745245-5	


^{*}Bulk packed for multiple part orders.

- Notes: 1. Mounting screws and nuts are to be supplied by Customer.
 - 2. These latching blocks allow mounting screws to be installed thru the front of the block and to be screwed into the bracket of a right-angle connector, a fixed insert in a connector mounting flange, or a nut behind the connector mounting flange (as illustrated above).

 3. Latching blocks mate with spring latches (page 152).







Typical Application of Rear-Panel Mounted Subminiature D Connector using Rear-Panel Latching Blocks

^{**}Individual kits contain two latching blocks per package.



Standoff Bushings

Material:

Aluminum

Related Product Data:

Connectors used with: **HD Straight Posted**pages 76-85, 87-89

4-40 Screws (Customer Supplied) Metal-Shell Plug or Receptacle (Shown for Ref. only) Standoff Bushing 4-40 Screws Pc Board (Customer Supplied)

4-40 Threads (thru) .250 [6.35] **.435** [11.05]

Kit Numbers:

205933-3 (two bushings per package)

205933-4 (bulk packed)*

*Parts are individually bulk packed for multiple part orders.

Keying Plug (for Size 20 Socket Contacts)

Material:

Polyphenylene oxide

Related Product Data:

Connectors used with: All HDE, HDP and HD Receptacles with Socket Contacts


Keying Plug


499712-1 AMP-LATCH (electrical connectors) can be used on **HD22 Socket Contacts**


EMI/RFI Gaskets

Material and Finish:

Brass, .006 [0.15] thick; bright tin plated








Part Number: 206509-1

Notes: 1. Keying plug is installed taper-end first into front of receptacle.

2. Sold individually.





Shell Size		Dimensions		Gasket Part No.
(No. of Contact Pos.)	Α	В	С	
1 (9)	.746 18.95	.984 24.99	1.220 30.99	5747024-3
2	1.074	1.312	1.555	5747025-3
(15)	27.28	33.32	39.50	
3	1.614	1.852	2.100	745776-4
(25)	41.00	47.04	53.34	
4	2.266	2.500	2.730	745777-4
(37)	57.56	63.50	69.34	

Note: All part numbers are RoHS compliant.

www.tycoelectronics.com