





C Series General Application

Type:

C0402 [EIA CC01005] C0603 [EIA CC0201] C1005 [EIA CC0402] C1608 [EIA CC0603] C2012 [EIA CC0805] C3216 [EIA CC1206] C3225 [EIA CC1210] C4532 [EIA CC1812] C5750 [EIA CC2220]

Issue date:

April 2011

TDK MLCC US Catalog


Version B11

REMINDERS

Please read before using this product

SAFETY REMINDERS

- 1. If you intend to use a product listed in this catalog for a purpose that may cause loss of life or other damage, you must contact our company's sales window.
- 2. We may modify products or discontinue production of a product listed in this catalog without prior notification.
- 3. We provide "Delivery Specification" that explain precautions for the specifications and safety of each product listed in this catalog. We strongly recommend that you exchange these delivery specifications with customers that use one of these products.
- 4. If you plan to export a product listed in this catalog, keep in mind that it may be a restricted item according to the "Foreign Exchange and Foreign Trade Control Law". In such cases, it is necessary to acquire export permission in harmony with this law.
- 5. Any reproduction or transferring of the contents of this catalog is prohibited without prior permission from our company.
- 6. We are not responsible for problems that occur related to the intellectual property rights or other rights of our company or a third party when you use a product listed in this catalog. We do not grant license of these rights.
- 7. This catalog only applies to products purchased through our company or one of our company's official agencies. This catalog does not apply to products that are purchased through other third parties.



C Series

General Application Type: C0402, C0603, C1005, C1608, C2012, C3216, C3225, C4532, C5750

Features



- · High capacitance has been achieved through precision technologies that enable the use of multiple thinner ceramic dielectric layers.
- A monolithic structure ensures superior mechanical ٠ strength and reliability.
- High-accuracy automatic mounting is facilitated through • the maintenance of very precise dimensional tolerances.
- · Composed of only ceramics and metals, these capacitors provide extremely dependable performance, exhibiting virtually no degradation even when subjected to temperature extremes.
- · Low stray capacitance ensures high conformity with nominal values, thereby simplifying the circuit design process.
- · Low residual inductance assures superior frequency characteristics.
- Because electrostatic capacity has been obtained up to • the electrolytic capacitor range, these capacitors offer long service life and are optimally suited for power supply designs that require high levels of reliability.
- · Owing to their low ESR and excellent frequency characteristics, these products are optimally suited for high frequency and high-density type power supplies.

Applications




- · Electronics equipment
- Mobile communications equipment

OVE

- · Office automation equipment
- · Automotive electronics
- Test and measurement equipment
- Hybrid ICs, etc.
- Decoupling
- Smoothing ٠
- Charge pump





Dimensions in mm

Part Number

onstruction

	uction L									
·			ç	2012 X7	<u>R 1</u> E	105	кт	XXXX	letere al Ocales	
Series Name									Internal Codes	
Dimensions L 3	« W (mm)						11		Packaging Style	
Case Code	Length	Width							Packaging Code	Style
C0402	0.40 ± 0.02	0.20 ± (0.02						Т	Tape & Reel
C0603	0.60 ± 0.03	0.30 ± (0.03						Capacitance Toler	ance
C1005	1.00 ± 0.05	0.50 ± (0.05						Tolerance Code	Tolerance
C1608	1.60 ± 0.10	0.80 ± 0							W	± 0.05 pF
C2012	2.00 ± 0.20	1.25 ± (B C	± 0.10 pF
C3216	3.20 ± 0.20	1.60 ± 0							С	± 0.25 pF
C3225	3.20 ± 0.40	2.50 ± 0							D	± 0.50 pF
C4532	4.50 ± 0.40	3.20 ± 0							E G	± 0.20 pF
C5750	5.70 ± 0.40	5.00 ± 0	0.40						G	± 2%
Femperature C	haracteristic	;							J	± 5%
Temperature	Capacitance	Tempe	rature						K	± 10%
Characteristics	Change	Range							M	± 20%
COG	0±30 ppm/°C		125°C						Z	+80-20%
SL	+350/-1000 g								Nominal Capacita	nce (pF)
X5R	±15%	-55 to +							The capacitance i	s expressed in three digit
X6S	+22%	-55 to +	105°C						codes and in units	s of pico Farads (pF). The fire
X7R	±15%	-55 to +	-125°C							identify the first and second
X7S	±22%	-55 to +	·125°C						•	of the capacitance. The third
Y5V	+22/-82%	-33 to +	∙85°C						0 0	multiplier. R designates a
Rated Voltage	(DC)								decimal point.	multiplier. It designates a
Voltage Volta	age Voltag	je Voltage	Voltage	Voltage					Capacitance Code	Capacitance
Code (DC		(DC)	Code	(DC)					0R5	0.5pF
0G 4V	1C	16V	1H	50V	-				010	1pF
		25V			_				102	1,000pF (1nF)
0J 6.3V	IE	237								

TDK MLCC US Catalog

Version B11

COG

1C

(16V)

Cap

Code

6R8

7R5

8R2

9R1

100

110

120 130

150

160

180

330

360

390

430 470

910

101

Tolerance

B: ± 0.10pF

E: ± 0.20pF

C: ± 0.25pF

D: ± 0.50pF

G: ± 2%

J: ± 5%



C0402 [EIA CC01005]

Capacitance Range Chart

Temperature Characteristics: C0G (0 ± 30ppm/°C) Rated Voltage: 16V (1C)

Capacitance	Сар	Tolerance	COG	Capacitance
(pF)	Code	TOIErance	1C (16V)	(pF)
0.1	0R1	W: ± 0.05pF		6.8
0.2	0R2	B: ± 0.10pF		7.5
0.3	0R3	C: ± 0.25pF		8.2
0.4	0R4	D: ± 0.50pF		9.1
0.5	0R5			10
0.6	0R6			11
0.7	0R7			12
0.8	0R8			13
0.9	0R9			15
1	010			16
1.1	1R1			18
1.2	1R2			20
1.3	1R3			22
1.5	1R5			24
1.6	1R6			27
1.8	1R8			30
2	020			33
2.2	2R2			36
2.4	2R4			39
2.7	2R7			43
3	030			47
3.3	3R3			51
3.6	3R6			56
3.9	3R9			62
4.3	4R3			68
4.7	4R7			75
5.1	5R1			82
5.6	5R6]		91
6.2	6R2			100

Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%), X5R (± 15%) Rated Voltage: 16V (1C), 10V (1A), 6.3V (0J)

Canacitanaa	Con		X7R		X5R	
Capacitance (pF)	Cap Code	Tolerance	1A (10V)	1C (16V)	1A (10V)	0J (6.3V)
100	101	K: ± 10%				
150	151					
220	221					
330	331					
470	471					
680	681					
1,000	102					
1,500	152					
2,200	222					
3,300	332					
4,700	472]				
6,800	682					
10,000	103					



MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0402 [EIA CC01005]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0402C0G1C0R2W	C0G	16V	0.2	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R2B	COG	16V	0.2	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R3W	COG	16V	0.3	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R3B	COG	16V	0.3	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R4W	COG	16V	0.4	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R4B	COG	16V	0.4	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R5W	COG	16V	0.5	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R5C	COG	16V	0.5	± 0.25pF	0.20 ± 0.02
C0402C0G1C0R5B	COG	16V	0.5	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R6W	COG	16V	0.6	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R6B	COG	16V	0.6	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R7W	C0G	16V	0.7	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R7B	COG	16V	0.7	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R8W	C0G	16V	0.8	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R8B	COG	16V	0.8	± 0.10pF	0.20 ± 0.02
C0402C0G1C0R9W	C0G	16V	0.9	± 0.05pF	0.20 ± 0.02
C0402C0G1C0R9B	COG	16V	0.9	± 0.10pF	0.20 ± 0.02
C0402C0G1C010B	COG	16V	1.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C010C	COG	16V	1.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R1B	COG	16V	1.1	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R1C	COG	16V	1.1	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R2B	COG	16V	1.2	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R2C	COG	16V	1.2	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R3B	COG	16V	1.3	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R3C	COG	16V	1.3	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R5B	COG	16V	1.5	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R5C	COG	16V	1.5	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R6B	COG	16V	1.6	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R6C	COG	16V	1.6	± 0.25pF	0.20 ± 0.02
C0402C0G1C1R8B	COG	16V	1.8	± 0.10pF	0.20 ± 0.02
C0402C0G1C1R8C	COG	16V	1.8	± 0.25pF	0.20 ± 0.02
C0402C0G1C020B	COG	16V	2.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C020C	COG	16V	2.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C2R2B	COG	16V	2.2	± 0.10pF	0.20 ± 0.02
C0402C0G1C2R2C	COG	16V	2.2	± 0.25pF	0.20 ± 0.02
C0402C0G1C2R4B	COG	16V	2.4	± 0.10pF	0.20 ± 0.02
C0402C0G1C2R4C	COG	16V	2.4	± 0.25pF	0.20 ± 0.02
C0402C0G1C2R7B	COG	16V	2.7	± 0.10pF	0.20 ± 0.02
C0402C0G1C2R7C	COG	16V	2.7	± 0.25pF	0.20 ± 0.02
C0402C0G1C030B	COG	16V	3.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C030C	COG	16V	3.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C3R3B	COG	16V	3.3	± 0.10pF	0.20 ± 0.02
C0402C0G1C3R3C	COG	16V	3.3	± 0.25pF	0.20 ± 0.02
C0402C0G1C3R6B	COG	16V	3.6	± 0.10pF	0.20 ± 0.02

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0402 [EIA CC01005]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0402C0G1C3R6C	COG	16V	3.6	± 0.25pF	0.20 ± 0.02
C0402C0G1C3R9B	COG	16V	3.9	± 0.10pF	0.20 ± 0.02
C0402C0G1C3R9C	COG	16V	3.9	± 0.25pF	0.20 ± 0.02
C0402C0G1C040B	COG	16V	4.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C040C	COG	16V	4.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C4R3B	COG	16V	4.3	± 0.10pF	0.20 ± 0.02
C0402C0G1C4R3C	COG	16V	4.3	± 0.25pF	0.20 ± 0.02
C0402C0G1C4R7B	COG	16V	4.7	± 0.10pF	0.20 ± 0.02
C0402C0G1C4R7C	COG	16V	4.7	± 0.25pF	0.20 ± 0.02
C0402C0G1C050B	COG	16V	5.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C050C	COG	16V	5.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C5R1B	COG	16V	5.1	± 0.10pF	0.20 ± 0.02
C0402C0G1C5R1C	COG	16V	5.1	± 0.25pF	0.20 ± 0.02
C0402C0G1C5R1D	COG	16V	5.1	± 0.50pF	0.20 ± 0.02
C0402C0G1C5R6B	COG	16V	5.6	± 0.10pF	0.20 ± 0.02
C0402C0G1C5R6C	COG	16V	5.6	± 0.25pF	0.20 ± 0.02
C0402C0G1C5R6D	COG	16V	5.6	± 0.50pF	0.20 ± 0.02
C0402C0G1C060B	COG	16V	6.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C060C	COG	16V	6.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C060D	COG	16V	6.0	± 0.50pF	0.20 ± 0.02
C0402C0G1C6R2B	COG	16V	6.2	± 0.10pF	0.20 ± 0.02
C0402C0G1C6R2C	COG	16V	6.2	± 0.25pF	0.20 ± 0.02
C0402C0G1C6R2D	COG	16V	6.2	± 0.50pF	0.20 ± 0.02
C0402C0G1C6R8B	COG	16V	6.8	± 0.10pF	0.20 ± 0.02
C0402C0G1C6R8C	COG	16V	6.8	± 0.25pF	0.20 ± 0.02
C0402C0G1C6R8D	COG	16V	6.8	± 0.50pF	0.20 ± 0.02
C0402C0G1C070B	COG	16V	7.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C070C	COG	16V	7.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C070D	COG	16V	7.0	± 0.50pF	0.20 ± 0.02
C0402C0G1C7R5B	COG	16V	7.5	± 0.10pF	0.20 ± 0.02
C0402C0G1C7R5C	COG	16V	7.5	± 0.25pF	0.20 ± 0.02
C0402C0G1C7R5D	COG	16V	7.5	± 0.50pF	0.20 ± 0.02
C0402C0G1C080B	COG	16V	8.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C080C	COG	16V	8.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C080D	COG	16V	8.0	± 0.50pF	0.20 ± 0.02
C0402C0G1C8R2B	COG	16V	8.2	± 0.10pF	0.20 ± 0.02
C0402C0G1C8R2C	COG	16V	8.2	± 0.25pF	0.20 ± 0.02
C0402C0G1C8R2D	COG	16V	8.2	± 0.50pF	0.20 ± 0.02
C0402C0G1C090B	COG	16V	9.0	± 0.10pF	0.20 ± 0.02
C0402C0G1C090C	C0G	16V	9.0	± 0.25pF	0.20 ± 0.02
C0402C0G1C090D	COG	16V	9.0	± 0.50pF	0.20 ± 0.02
C0402C0G1C9R1B	C0G	16V	9.1	± 0.10pF	0.20 ± 0.02
C0402C0G1C9R1C	C0G	16V	9.1	± 0.25pF	0.20 ± 0.02
C0402C0G1C9R1D	COG	16V	9.1	± 0.50pF	0.20 ± 0.02

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0402 [EIA CC01005]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0402C0G1C100E	COG	16V	10	± 0.20pF	0.20 ± 0.02
C0402C0G1C100D	COG	16V	10	± 0.50pF	0.20 ± 0.02
C0402C0G1C110G	COG	16V	11	± 2%	0.20 ± 0.02
C0402C0G1C110J	COG	16V	11	± 5%	0.20 ± 0.02
C0402C0G1C120G	COG	16V	12	± 2%	0.20 ± 0.02
C0402C0G1C120J	COG	16V	12	± 5%	0.20 ± 0.02
C0402C0G1C130G	COG	16V	13	± 2%	0.20 ± 0.02
C0402C0G1C130J	COG	16V	13	± 5%	0.20 ± 0.02
C0402C0G1C150G	COG	16V	15	± 2%	0.20 ± 0.02
C0402C0G1C150J	COG	16V	15	± 5%	0.20 ± 0.02
C0402C0G1C160G	COG	16V	16	± 2%	0.20 ± 0.02
C0402C0G1C160J	COG	16V	16	± 5%	0.20 ± 0.02
C0402C0G1C180G	COG	16V	18	± 2%	0.20 ± 0.02
C0402C0G1C180J	COG	16V	18	± 5%	0.20 ± 0.02
C0402C0G1C200G	COG	16V	20	± 2%	0.20 ± 0.02
C0402C0G1C200J	COG	16V	20	± 5%	0.20 ± 0.02
C0402C0G1C220G	COG	16V	22	± 2%	0.20 ± 0.02
C0402C0G1C220J	COG	16V	22	± 5%	0.20 ± 0.02
C0402C0G1C240G	COG	16V	24	± 2%	0.20 ± 0.02
C0402C0G1C240J	COG	16V	24	± 5%	0.20 ± 0.02
C0402C0G1C270G	COG	16V	27	± 2%	0.20 ± 0.02
C0402C0G1C270J	COG	16V	27	± 5%	0.20 ± 0.02
C0402C0G1C300G	COG	16V	30	± 2%	0.20 ± 0.02
C0402C0G1C300J	COG	16V	30	± 5%	0.20 ± 0.02
C0402C0G1C330G	COG	16V	33	± 2%	0.20 ± 0.02
C0402C0G1C330J	COG	16V	33	± 5%	0.20 ± 0.02
C0402C0G1C360G	COG	16V	36	± 2%	0.20 ± 0.02
C0402C0G1C360J	COG	16V	36	± 5%	0.20 ± 0.02
C0402C0G1C390G	COG	16V	39	± 2%	0.20 ± 0.02
C0402C0G1C390J	COG	16V	39	± 5%	0.20 ± 0.02
C0402C0G1C430G	COG	16V	43	± 2%	0.20 ± 0.02
C0402C0G1C430J	COG	16V	43	± 5%	0.20 ± 0.02
C0402C0G1C470G	COG	16V	47	± 2%	0.20 ± 0.02
C0402C0G1C470J	COG	16V	47	± 5%	0.20 ± 0.02
C0402C0G1C510G	COG	16V	51	± 2%	0.20 ± 0.02
C0402C0G1C510J	COG	16V	51	± 5%	0.20 ± 0.02
C0402C0G1C560G	COG	16V	56	± 2%	0.20 ± 0.02
C0402C0G1C560J	COG	16V	56	± 5%	0.20 ± 0.02
C0402C0G1C620G	COG	16V	62	± 2%	0.20 ± 0.02
C0402C0G1C620J	COG	16V	62	± 5%	0.20 ± 0.02
C0402C0G1C680G	COG	16V	68	± 2%	0.20 ± 0.02
C0402C0G1C680J	COG	16V	68	± 5%	0.20 ± 0.02
C0402C0G1C750G	COG	16V	75	± 2%	0.20 ± 0.02
C0402C0G1C750J	COG	16V	75	± 5%	0.20 ± 0.02



Capacitance Range Table

C0402 [EIA CC01005]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number	Temperature	Rated	Capacitance	Capacitance	Thickness
(Ordering Code)	Characteristics	Voltage	(pF)	Tolerance	(mm)
C0402C0G1C820G	COG	16V	82	± 2%	0.20 ± 0.02
C0402C0G1C820J	COG	16V	82	± 5%	0.20 ± 0.02
C0402C0G1C910G	C0G	16V	91	± 2%	0.20 ± 0.02
C0402C0G1C910J	COG	16V	91	± 5%	0.20 ± 0.02
C0402C0G1C101G	C0G	16V	100	± 2%	0.20 ± 0.02
C0402C0G1C101J	C0G	16V	100	± 5%	0.20 ± 0.02

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0402X7R1A101K	X7R	10V	100	± 10%	0.20 ± 0.02
C0402X7R1A151K	X7R	10V	150	± 10%	0.20 ± 0.02
C0402X7R1A221K	X7R	10V	220	± 10%	0.20 ± 0.02
C0402X7R1A331K	X7R	10V	330	± 10%	0.20 ± 0.02
C0402X7R1A471K	X7R	10V	470	± 10%	0.20 ± 0.02
C0402X7R1A681K	X7R	10V	680	± 10%	0.20 ± 0.02
C0402X5R1C101K	X5R	16V	100	± 10%	0.20 ± 0.02
C0402X5R1C151K	X5R	16V	150	± 10%	0.20 ± 0.02
C0402X5R1C221K	X5R	16V	220	± 10%	0.20 ± 0.02
C0402X5R1C331K	X5R	16V	330	± 10%	0.20 ± 0.02
C0402X5R1C471K	X5R	16V	470	± 10%	0.20 ± 0.02
C0402X5R1C681K	X5R	16V	680	± 10%	0.20 ± 0.02
C0402X5R1A101K	X5R	10V	100	± 10%	0.20 ± 0.02
C0402X5R1A221K	X5R	10V	220	± 10%	0.20 ± 0.02
C0402X5R1A471K	X5R	10V	470	± 10%	0.20 ± 0.02
C0402X5R1A102K	X5R	10V	1,000	± 10%	0.20 ± 0.02
C0402X5R1A152K	X5R	10V	1,500	± 10%	0.20 ± 0.02
C0402X5R1A222K	X5R	10V	2,200	± 10%	0.20 ± 0.02
C0402X5R0J681K	X5R	6.3V	680	± 10%	0.20 ± 0.02
C0402X5R0J102K	X5R	6.3V	1,000	± 10%	0.20 ± 0.02
C0402X5R0J152K	X5R	6.3V	1,500	± 10%	0.20 ± 0.02
C0402X5R0J222K	X5R	6.3V	2,200	± 10%	0.20 ± 0.02
C0402X5R0J332K	X5R	6.3V	3,300	± 10%	0.20 ± 0.02
C0402X5R0J472K	X5R	6.3V	4,700	± 10%	0.20 ± 0.02
C0402X5R0J682K	X5R	6.3V	6,800	± 10%	0.20 ± 0.02
C0402X5R0J103K	X5R	6.3V	10,000	± 10%	0.20 ± 0.02



C0603 [EIA CC0201]

Capacitance Range Chart

Temperature Characteristics: COG (0 ± 30ppm/°C) Rated Voltage: 50V (1H), 25V (1E)

Oanacitanaa	0.00		C)G	Oomooltomoo	0.00		C)G
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)
0.2	0R2	W: ± 0.05pF			6.8	6R8	B: ± 0.10pF		
0.3	0R3	B: ± 0.10pF			7.5	7R5	E: ± 0.20pF		
0.4	0R4	C: ± 0.25pF			8.2	8R2	C: ± 0.25pF		
0.5	0R5	D: ± 0.50pF			9.1	9R1	D: ± 0.50pF		
0.6	0R6				10	100	G: ± 2%		
0.7	0R7				11	110	J: ± 5%		
0.75	R75				12	120			
0.8	0R8				13	130			
0.9	0R9				15	150			
1	010				16	160			
1.1	1R1				18	180			
1.2	1R2				20	200			
1.3	1R3				22	220			
1.5	1R5				24	240			
1.6	1R6				27	270			
1.8	1R8				30	300			
2	020				33	330			
2.2	2R2	-			36	360	1		
2.4	2R4				39	390			
2.7	2R7				43	430	1		
3	030				47	470			
3.3	3R3				51	510			
3.6	3R6	-			56	560	1		
3.9	3R9				62	620			
4.3	4R3				68	680	1		
4.7	4R7				75	750	1		
5.1	5R1				82	820	1		
5.6	5R6				91	910	1		
6.2	6R2				100	101	1		

• Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.

⊘TDK


MULTILAYER CERAMIC CHIP CAPACITORS



C0603 [EIA CC0201]

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%), X5R (± 15%) Rated Voltage: 50V (1H), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J)



• Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.





MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603C0G1H0R5B	COG	50V	0.5	± 0.10pF	0.30 ± 0.03
C0603C0G1H0R5C	COG	50V	0.5	± 0.25pF	0.30 ± 0.03
C0603C0G1H010B	COG	50V	1.0	± 0.10pF	0.30 ± 0.03
C0603C0G1H010C	COG	50V	1.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H1R2C	COG	50V	1.2	± 0.25pF	0.30 ± 0.03
C0603C0G1H1R5B	COG	50V	1.5	± 0.10pF	0.30 ± 0.03
C0603C0G1H1R5C	COG	50V	1.5	± 0.25pF	0.30 ± 0.03
C0603C0G1H1R8C	COG	50V	1.8	± 0.25pF	0.30 ± 0.03
C0603C0G1H020B	COG	50V	2.0	± 0.10pF	0.30 ± 0.03
C0603C0G1H020C	COG	50V	2.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H2R2B	COG	50V	2.2	± 0.10pF	0.30 ± 0.03
C0603C0G1H2R2C	COG	50V	2.2	± 0.25pF	0.30 ± 0.03
C0603C0G1H2R7C	COG	50V	2.7	± 0.25pF	0.30 ± 0.03
C0603C0G1H030B	COG	50V	3.0	± 0.10pF	0.30 ± 0.03
C0603C0G1H030C	COG	50V	3.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H3R3B	COG	50V	3.3	± 0.10pF	0.30 ± 0.03
C0603C0G1H3R3C	COG	50V	3.3	± 0.25pF	0.30 ± 0.03
C0603C0G1H3R9C	COG	50V	3.9	± 0.25pF	0.30 ± 0.03
C0603C0G1H040B	COG	50V	4.0	± 0.10pF	0.30 ± 0.03
C0603C0G1H040C	COG	50V	4.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H4R7B	COG	50V	4.7	± 0.10pF	0.30 ± 0.03
C0603C0G1H4R7C	COG	50V	4.7	± 0.25pF	0.30 ± 0.03
C0603C0G1H050B	COG	50V	5.0	± 0.10pF	0.30 ± 0.03
C0603C0G1H050C	COG	50V	5.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H5R6C	COG	50V	5.6	± 0.25pF	0.30 ± 0.03
C0603C0G1H060C	COG	50V	6.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H060D	COG	50V	6.0	± 0.50pF	0.30 ± 0.03
C0603C0G1H6R8C	COG	50V	6.8	± 0.25pF	0.30 ± 0.03
C0603C0G1H6R8D	COG	50V	6.8	± 0.50pF	0.30 ± 0.03
C0603C0G1H070C	C0G	50V	7.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H070D	COG	50V	7.0	± 0.50pF	0.30 ± 0.03
C0603C0G1H080C	C0G	50V	8.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H080D	COG	50V	8.0	± 0.50pF	0.30 ± 0.03
C0603C0G1H8R2C	COG	50V	8.2	± 0.25pF	0.30 ± 0.03
C0603C0G1H090C	COG	50V	9.0	± 0.25pF	0.30 ± 0.03
C0603C0G1H090D	COG	50V	9.0	± 0.50pF	0.30 ± 0.03
C0603C0G1H100C	C0G	50V	10	± 0.25pF	0.30 ± 0.03
C0603C0G1H100D	C0G	50V	10	± 0.50pF	0.30 ± 0.03
C0603C0G1H110J	C0G	50V	11	± 5%	0.30 ± 0.03
C0603C0G1H120J	COG	50V	12	± 5%	0.30 ± 0.03
C0603C0G1H130J	COG	50V	13	± 5%	0.30 ± 0.03
C0603C0G1H150J	COG	50V	15	± 5%	0.30 ± 0.03
C0603C0G1H160J	COG	50V	16	± 5%	0.30 ± 0.03
C0603C0G1H180J	COG	50V	18	± 5%	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603C0G1H200J	COG	50V	20	± 5%	0.30 ± 0.03
C0603C0G1H220J	COG	50V	22	± 5%	0.30 ± 0.03
C0603C0G1H240J	COG	50V	24	± 5%	0.30 ± 0.03
C0603C0G1H270J	COG	50V	27	± 5%	0.30 ± 0.03
C0603C0G1H300J	COG	50V	30	± 5%	0.30 ± 0.03
C0603C0G1H330J	COG	50V	33	± 5%	0.30 ± 0.03
C0603C0G1H360J	COG	50V	36	± 5%	0.30 ± 0.03
C0603C0G1H390J	COG	50V	39	± 5%	0.30 ± 0.03
C0603C0G1H430J	COG	50V	43	± 5%	0.30 ± 0.03
C0603C0G1H470J	COG	50V	47	± 5%	0.30 ± 0.03
C0603C0G1H510J	COG	50V	51	± 5%	0.30 ± 0.03
C0603C0G1H560J	COG	50V	56	± 5%	0.30 ± 0.03
C0603C0G1H620J	COG	50V	62	± 5%	0.30 ± 0.03
C0603C0G1H680J	COG	50V	68	± 5%	0.30 ± 0.03
C0603C0G1H750J	COG	50V	75	± 5%	0.30 ± 0.03
C0603C0G1H820J	COG	50V	82	± 5%	0.30 ± 0.03
C0603C0G1H910J	COG	50V	91	± 5%	0.30 ± 0.03
C0603C0G1H101J	COG	50V	100	± 5%	0.30 ± 0.03
C0603C0G1E0R2W	COG	25V	0.2	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R2B	COG	25V	0.2	± 0.10pF	0.30 ± 0.03
CO6O3COG1EOR3W	COG	25V	0.3	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R3B	COG	25V	0.3	± 0.10pF	0.30 ± 0.03
C0603C0G1E0R4W	COG	25V	0.4	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R4B	COG	25V	0.4	± 0.10pF	0.30 ± 0.03
C0603C0G1E0R5W	COG	25V	0.5	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R5C	COG	25V	0.5	± 0.25pF	0.30 ± 0.03
C0603C0G1E0R5B	COG	25V	0.5	± 0.10pF	0.30 ± 0.03
C0603C0G1E0R6W	COG	25V	0.6	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R6B	COG	25V	0.6	± 0.10pF	0.30 ± 0.03
C0603C0G1E0R7W	COG	25V	0.7	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R7B	COG	25V	0.7	± 0.10pF	0.30 ± 0.03
C0603C0G1ER75B	COG	25V	0.75	± 0.10pF	0.30 ± 0.03
C0603C0G1ER75C	COG	25V	0.75	± 0.25pF	0.30 ± 0.03
C0603C0G1E0R8W	COG	25V	0.8	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R8B	COG	25V	0.8	± 0.10pF	0.30 ± 0.03
C0603C0G1E0R9W	COG	25V	0.9	± 0.05pF	0.30 ± 0.03
C0603C0G1E0R9B	COG	25V	0.9	± 0.10pF	0.30 ± 0.03
C0603C0G1E010B	COG	25V	1.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E010C	COG	25V	1.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R1B	COG	25V	1.1	± 0.10pF	0.30 ± 0.03
C0603C0G1E1R1C	COG	25V	1.1	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R2B	C0G	25V	1.2	± 0.10pF	0.30 ± 0.03
C0603C0G1E1R2C	C0G	25V	1.2	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R3B	C0G	25V	1.3	± 0.10pF	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603C0G1E1R3C	COG	25V	1.3	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R5B	COG	25V	1.5	± 0.10pF	0.30 ± 0.03
C0603C0G1E1R5C	COG	25V	1.5	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R6B	COG	25V	1.6	± 0.10pF	0.30 ± 0.03
C0603C0G1E1R6C	COG	25V	1.6	± 0.25pF	0.30 ± 0.03
C0603C0G1E1R8B	COG	25V	1.8	± 0.10pF	0.30 ± 0.03
C0603C0G1E1R8C	COG	25V	1.8	± 0.25pF	0.30 ± 0.03
C0603C0G1E020B	COG	25V	2.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E020C	COG	25V	2.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E2R2B	COG	25V	2.2	± 0.10pF	0.30 ± 0.03
C0603C0G1E2R2C	COG	25V	2.2	± 0.25pF	0.30 ± 0.03
C0603C0G1E2R4B	COG	25V	2.4	± 0.10pF	0.30 ± 0.03
C0603C0G1E2R4C	COG	25V	2.4	± 0.25pF	0.30 ± 0.03
C0603C0G1E2R7B	COG	25V	2.7	± 0.10pF	0.30 ± 0.03
C0603C0G1E2R7C	COG	25V	2.7	± 0.25pF	0.30 ± 0.03
C0603C0G1E030B	COG	25V	3.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E030C	COG	25V	3.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E3R3B	COG	25V	3.3	± 0.10pF	0.30 ± 0.03
C0603C0G1E3R3C	COG	25V	3.3	± 0.25pF	0.30 ± 0.03
C0603C0G1E3R6B	COG	25V	3.6	± 0.10pF	0.30 ± 0.03
C0603C0G1E3R6C	COG	25V	3.6	± 0.25pF	0.30 ± 0.03
C0603C0G1E3R9B	COG	25V	3.9	± 0.10pF	0.30 ± 0.03
C0603C0G1E3R9C	COG	25V	3.9	± 0.25pF	0.30 ± 0.03
C0603C0G1E040B	C0G	25V	4.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E040C	COG	25V	4.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E4R3B	COG	25V	4.3	± 0.10pF	0.30 ± 0.03
C0603C0G1E4R3C	COG	25V	4.3	± 0.25pF	0.30 ± 0.03
C0603C0G1E4R7B	C0G	25V	4.7	± 0.10pF	0.30 ± 0.03
C0603C0G1E4R7C	COG	25V	4.7	± 0.25pF	0.30 ± 0.03
C0603C0G1E050B	COG	25V	5.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E050C	COG	25V	5.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E5R1B	COG	25V	5.1	± 0.10pF	0.30 ± 0.03
C0603C0G1E5R1C	COG	25V	5.1	± 0.25pF	0.30 ± 0.03
C0603C0G1E5R1D	COG	25V	5.1	± 0.50pF	0.30 ± 0.03
C0603C0G1E5R6B	COG	25V	5.6	± 0.10pF	0.30 ± 0.03
C0603C0G1E5R6C	COG	25V	5.6	± 0.25pF	0.30 ± 0.03
C0603C0G1E5R6D	COG	25V	5.6	± 0.50pF	0.30 ± 0.03
C0603C0G1E060B	COG	25V	6.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E060C	COG	25V	6.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E060D	COG	25V	6.0	± 0.50pF	0.30 ± 0.03
C0603C0G1E6R2B	COG	25V	6.2	± 0.10pF	0.30 ± 0.03
C0603C0G1E6R2C	COG	25V	6.2	± 0.25pF	0.30 ± 0.03
C0603C0G1E6R2D	COG	25V	6.2	± 0.50pF	0.30 ± 0.03
C0603C0G1E6R8B	COG	25V	6.8	± 0.10pF	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603C0G1E6R8C	COG	25V	6.8	± 0.25pF	0.30 ± 0.03
C0603C0G1E6R8D	COG	25V	6.8	± 0.50pF	0.30 ± 0.03
C0603C0G1E070B	COG	25V	7.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E070C	COG	25V	7.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E070D	COG	25V	7.0	± 0.50pF	0.30 ± 0.03
C0603C0G1E7R5B	COG	25V	7.5	± 0.10pF	0.30 ± 0.03
C0603C0G1E7R5C	COG	25V	7.5	± 0.25pF	0.30 ± 0.03
C0603C0G1E7R5D	COG	25V	7.5	± 0.50pF	0.30 ± 0.03
C0603C0G1E080B	COG	25V	8.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E080C	COG	25V	8.0	± 0.25pF	0.30 ± 0.03
0603C0G1E080D	COG	25V	8.0	± 0.50pF	0.30 ± 0.03
C0603C0G1E8R2B	COG	25V	8.2	± 0.10pF	0.30 ± 0.03
C0603C0G1E8R2C	COG	25V	8.2	± 0.25pF	0.30 ± 0.03
C0603C0G1E8R2D	COG	25V	8.2	± 0.50pF	0.30 ± 0.03
C0603C0G1E090B	COG	25V	9.0	± 0.10pF	0.30 ± 0.03
C0603C0G1E090C	COG	25V	9.0	± 0.25pF	0.30 ± 0.03
C0603C0G1E090D	COG	25V	9.0	± 0.50pF	0.30 ± 0.03
C0603C0G1E9R1B	COG	25V	9.1	± 0.10pF	0.30 ± 0.03
C0603C0G1E9R1C	COG	25V	9.1	± 0.25pF	0.30 ± 0.03
C0603C0G1E9R1D	COG	25V	9.1	± 0.50pF	0.30 ± 0.03
0603C0G1E100E	COG	25V	10	± 0.20pF	0.30 ± 0.03
C0603C0G1E100C	COG	25V	10	± 0.25pF	0.30 ± 0.03
C0603C0G1E100D	COG	25V	10	± 0.50pF	0.30 ± 0.03
C0603C0G1E110G	COG	25V	11	± 2%	0.30 ± 0.03
C0603C0G1E110J	COG	25V	11	± 5%	0.30 ± 0.03
C0603C0G1E120G	COG	25V	12	± 2%	0.30 ± 0.03
C0603C0G1E120J	COG	25V	12	± 5%	0.30 ± 0.03
C0603C0G1E130G	COG	25V	13	± 2%	0.30 ± 0.03
C0603C0G1E130J	COG	25V	13	± 5%	0.30 ± 0.03
C0603C0G1E150G	COG	25V	15	± 2%	0.30 ± 0.03
C0603C0G1E150J	COG	25V	15	± 5%	0.30 ± 0.03
C0603C0G1E160G	COG	25V	16	± 2%	0.30 ± 0.03
C0603C0G1E160J	COG	25V	16	± 5%	0.30 ± 0.03
C0603C0G1E180G	COG	25V	18	± 2%	0.30 ± 0.03
C0603C0G1E180J	COG	25V	18	± 5%	0.30 ± 0.03
C0603C0G1E200G	COG	25V	20	± 2%	0.30 ± 0.03
C0603C0G1E200J	COG	25V	20	± 5%	0.30 ± 0.03
0603C0G1E220G	COG	25V	22	± 2%	0.30 ± 0.03
C0603C0G1E220J	COG	25V	22	± 5%	0.30 ± 0.03
C0603C0G1E240G	C0G	25V	24	± 2%	0.30 ± 0.03
C0603C0G1E240J	C0G	25V	24	± 5%	0.30 ± 0.03
C0603C0G1E270G	C0G	25V	27	± 2%	0.30 ± 0.03
C0603C0G1E270J	C0G	25V	27	± 5%	0.30 ± 0.03
C0603C0G1E300G	COG	25V	30	± 2%	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603C0G1E300J	COG	25V	30	± 5%	0.30 ± 0.03
C0603C0G1E330G	COG	25V	33	± 2%	0.30 ± 0.03
C0603C0G1E330J	COG	25V	33	± 5%	0.30 ± 0.03
C0603C0G1E360G	COG	25V	36	± 2%	0.30 ± 0.03
C0603C0G1E360J	COG	25V	36	± 5%	0.30 ± 0.03
C0603C0G1E390G	COG	25V	39	± 2%	0.30 ± 0.03
C0603C0G1E390J	COG	25V	39	± 5%	0.30 ± 0.03
C0603C0G1E430G	COG	25V	43	± 2%	0.30 ± 0.03
C0603C0G1E430J	COG	25V	43	± 5%	0.30 ± 0.03
C0603C0G1E470G	COG	25V	47	± 2%	0.30 ± 0.03
C0603C0G1E470J	COG	25V	47	± 5%	0.30 ± 0.03
C0603C0G1E510G	COG	25V	51	± 2%	0.30 ± 0.03
C0603C0G1E510J	COG	25V	51	± 5%	0.30 ± 0.03
C0603C0G1E560G	COG	25V	56	± 2%	0.30 ± 0.03
C0603C0G1E560J	COG	25V	56	± 5%	0.30 ± 0.03
C0603C0G1E620G	COG	25V	62	± 2%	0.30 ± 0.03
C0603C0G1E620J	COG	25V	62	± 5%	0.30 ± 0.03
C0603C0G1E680G	COG	25V	68	± 2%	0.30 ± 0.03
C0603C0G1E680J	COG	25V	68	± 5%	0.30 ± 0.03
C0603C0G1E750G	COG	25V	75	± 2%	0.30 ± 0.03
C0603C0G1E750J	COG	25V	75	± 5%	0.30 ± 0.03
C0603C0G1E820G	COG	25V	82	± 2%	0.30 ± 0.03
C0603C0G1E820J	COG	25V	82	± 5%	0.30 ± 0.03
C0603C0G1E910G	COG	25V	91	± 2%	0.30 ± 0.03
C0603C0G1E910J	COG	25V	91	± 5%	0.30 ± 0.03
C0603C0G1E101G	COG	25V	100	± 2%	0.30 ± 0.03
C0603C0G1E101J	COG	25V	100	± 5%	0.30 ± 0.03

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603X7R1H101K	X7R	50V	100	± 10%	0.30 ± 0.03
C0603X7R1H101M	X7R	50V	100	± 20%	0.30 ± 0.03
C0603X7R1H151K	X7R	50V	150	± 10%	0.30 ± 0.03
C0603X7R1H151M	X7R	50V	150	± 20%	0.30 ± 0.03
C0603X7R1H221K	X7R	50V	220	± 10%	0.30 ± 0.03
C0603X7R1H221M	X7R	50V	220	± 20%	0.30 ± 0.03
C0603X7R1H331K	X7R	50V	330	± 10%	0.30 ± 0.03
C0603X7R1H331M	X7R	50V	330	± 20%	0.30 ± 0.03
C0603X7R1H471K	X7R	50V	470	± 10%	0.30 ± 0.03
C0603X7R1H471M	X7R	50V	470	± 20%	0.30 ± 0.03
C0603X7R1E101K	X7R	25V	100	± 10%	0.30 ± 0.03
C0603X7R1E101M	X7R	25V	100	± 20%	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603X7R1E151K	X7R	25V	150	± 10%	0.30 ± 0.03
C0603X7R1E151M	X7R	25V	150	± 20%	0.30 ± 0.03
C0603X7R1E221K	X7R	25V	220	± 10%	0.30 ± 0.03
C0603X7R1E221M	X7R	25V	220	± 20%	0.30 ± 0.03
C0603X7R1E331K	X7R	25V	330	± 10%	0.30 ± 0.03
C0603X7R1E331M	X7R	25V	330	± 20%	0.30 ± 0.03
C0603X7R1E471K	X7R	25V	470	± 10%	0.30 ± 0.03
C0603X7R1E471M	X7R	25V	470	± 20%	0.30 ± 0.03
C0603X7R1E681K	X7R	25V	680	± 10%	0.30 ± 0.03
C0603X7R1E681M	X7R	25V	680	± 20%	0.30 ± 0.03
C0603X7R1E102K	X7R	25V	1,000	± 10%	0.30 ± 0.03
0603X7R1E102M	X7R	25V	1,000	± 20%	0.30 ± 0.03
C0603X7R1E152K	X7R	25V	1,500	± 10%	0.30 ± 0.03
0603X7R1E152M	X7R	25V	1,500	± 20%	0.30 ± 0.03
0603X7R1E222K	X7R	25V	2,200	± 10%	0.30 ± 0.03
0603X7R1E222M	X7R	25V	2,200	± 20%	0.30 ± 0.03
C0603X7R1E332K	X7R	25V	3,300	± 10%	0.30 ± 0.03
0603X7R1E332M	X7R	25V	3,300	± 20%	0.30 ± 0.03
0603X7R1C101K	X7R	16V	100	± 10%	0.30 ± 0.03
0603X7R1C101M	X7R	16V	100	± 20%	0.30 ± 0.03
0603X7R1C151K	X7R	16V	150	± 10%	0.30 ± 0.03
0603X7R1C151M	X7R	16V	150	± 20%	0.30 ± 0.03
0603X7R1C221K	X7R	16V	220	± 10%	0.30 ± 0.03
0603X7R1C221M	X7R	16V	220	± 20%	0.30 ± 0.03
0603X7R1C331K	X7R	16V	330	± 10%	0.30 ± 0.03
0603X7R1C331M	X7R	16V	330	± 20%	0.30 ± 0.03
0603X7R1C471K	X7R	16V	470	± 10%	0.30 ± 0.03
0603X7R1C471M	X7R	16V	470	± 20%	0.30 ± 0.03
0603X7R1C681K	X7R	16V	680	± 10%	0.30 ± 0.03
0603X7R1C681M	X7R	16V	680	± 20%	0.30 ± 0.03
0603X7R1C102K	X7R	16V	1,000	± 10%	0.30 ± 0.03
0603X7R1C102M	X7R	16V	1,000	± 20%	0.30 ± 0.03
0603X7R1C152K	X7R	16V	1,500	± 10%	0.30 ± 0.03
0603X7R1C152M	X7R	16V	1,500	± 20%	0.30 ± 0.03
0603X7R1C222K	X7R	16V	2,200	± 10%	0.30 ± 0.03
0603X7R1C222M	X7R	16V	2,200	± 20%	0.30 ± 0.03
0603X7R1C332K	X7R	16V	3,300	± 10%	0.30 ± 0.03
0603X7R1C332M	X7R	16V	3,300	± 20%	0.30 ± 0.03
0603X7R1C472K	X7R	16V	4,700	± 10%	0.30 ± 0.03
0603X7R1C472M	X7R	16V	4,700	± 20%	0.30 ± 0.03
C0603X7R1A682K	X7R	10V	6,800	± 10%	0.30 ± 0.03
C0603X7R1A682M	X7R	10V	6,800	± 20%	0.30 ± 0.03
0603X7R1A103K	X7R	10V	10,000	± 10%	0.30 ± 0.03
	/////	101	10,000	= 1070	0.00 ± 0.00

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S(-55 to 105°C, ±22%), X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	eristics: X7R (-55 to +12 Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603X7R0J103K	X7R	6.3V	10,000	± 10%	0.30 ± 0.03
C0603X7R0J103M	X7R	6.3V	10,000	± 20%	0.30 ± 0.03
C0603X6S0G104K	X6S	4V	100,000	± 10%	0.30 ± 0.03
C0603X6S0G104M	X6S	4V	100,000	± 20%	0.30 ± 0.03
C0603X5R1H101K	X5R	50V	100	± 10%	0.30 ± 0.03
C0603X5R1H101M	X5R	50V	100	± 20%	0.30 ± 0.03
C0603X5R1H151K	X5R	50V	150	± 10%	0.30 ± 0.03
C0603X5R1H151M	X5R	50V	150	± 20%	0.30 ± 0.03
C0603X5R1H221K	X5R	50V	220	± 10%	0.30 ± 0.03
C0603X5R1H221M	X5R	50V	220	± 20%	0.30 ± 0.03
C0603X5R1H331K	X5R	50V	330	± 10%	0.30 ± 0.03
C0603X5R1H331M	X5R	50V	330	± 20%	0.30 ± 0.03
C0603X5R1H471K	X5R	50V	470	± 10%	0.30 ± 0.03
C0603X5R1H471M	X5R	50V	470	± 20%	0.30 ± 0.03
C0603X5R1E101K	X5R	25V	100	± 10%	0.30 ± 0.03
C0603X5R1E101M	X5R	25V	100	± 20%	0.30 ± 0.03
C0603X5R1E151K	X5R	25V	150	± 10%	0.30 ± 0.03
C0603X5R1E151M	X5R	25V	150	± 20%	0.30 ± 0.03
C0603X5R1E221K	X5R	25V	220	± 10%	0.30 ± 0.03
C0603X5R1E221M	X5R	25V	220	± 20%	0.30 ± 0.03
C0603X5R1E331K	X5R	25V	330	± 10%	0.30 ± 0.03
C0603X5R1E331M	X5R	25V	330	± 20%	0.30 ± 0.03
C0603X5R1E471K	X5R	25V	470	± 10%	0.30 ± 0.03
C0603X5R1E471M	X5R	25V	470	± 20%	0.30 ± 0.03
C0603X5R1E681K	X5R	25V	680	± 10%	0.30 ± 0.03
C0603X5R1E681M	X5R	25V	680	± 20%	0.30 ± 0.03
C0603X5R1E102K	X5R	25V	1,000	± 10%	0.30 ± 0.03
C0603X5R1E102M	X5R	25V	1,000	± 20%	0.30 ± 0.03
C0603X5R1E152K	X5R	25V	1,500	± 10%	0.30 ± 0.03
C0603X5R1E152M	X5R	25V	1,500	± 20%	0.30 ± 0.03
C0603X5R1E222K	X5R	25V	2,200	± 10%	0.30 ± 0.03
C0603X5R1E222M	X5R	25V	2,200	± 20%	0.30 ± 0.03
C0603X5R1E332K	X5R	25V	3,300	± 10%	0.30 ± 0.03
C0603X5R1E332M	X5R	25V	3,300	± 20%	0.30 ± 0.03
C0603X5R1C222K	X5R	16V	2,200	± 10%	0.30 ± 0.03
C0603X5R1C222M	X5R	16V	2,200	± 20%	0.30 ± 0.03
C0603X5R1C332K	X5R	16V	3,300	± 10%	0.30 ± 0.03
C0603X5R1C332M	X5R	16V	3,300	± 20%	0.30 ± 0.03
C0603X5R1C472K	X5R	16V	4,700	± 10%	0.30 ± 0.03
C0603X5R1C472M	X5R	16V	4,700	± 20%	0.30 ± 0.03
C0603X5R1C104K	X5R	16V	100,000	± 10%	0.30 ± 0.03
C0603X5R1C154K	X5R	16V	150,000	± 10%	0.30 ± 0.03
C0603X5R1C224K	X5R	16V	220,000	± 10%	0.30 ± 0.03
C0603X5R1C224M	X5R	16V	220,000	± 20%	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C0603 [EIA CC0201]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C0603X5R1A682K	X5R	10V	6,800	± 10%	0.30 ± 0.03
C0603X5R1A682M	X5R	10V	6,800	± 20%	0.30 ± 0.03
C0603X5R1A103K	X5R	10V	10,000	± 10%	0.30 ± 0.03
C0603X5R1A103M	X5R	10V	10,000	± 20%	0.30 ± 0.03
C0603X5R1A104K	X5R	10V	100,000	± 10%	0.30 ± 0.03
C0603X5R1A154K	X5R	10V	150,000	± 10%	0.30 ± 0.03
C0603X5R1A224K	X5R	10V	220,000	± 10%	0.30 ± 0.03
C0603X5R1A224M	X5R	10V	220,000	± 20%	0.30 ± 0.03
C0603X5R0J103K	X5R	6.3V	10,000	± 10%	0.30 ± 0.03
C0603X5R0J103M	X5R	6.3V	10,000	± 20%	0.30 ± 0.03
C0603X5R0J153K	X5R	6.3V	15,000	± 10%	0.30 ± 0.03
C0603X5R0J153M	X5R	6.3V	15,000	± 20%	0.30 ± 0.03
C0603X5R0J223K	X5R	6.3V	22,000	± 10%	0.30 ± 0.03
C0603X5R0J223M	X5R	6.3V	22,000	± 20%	0.30 ± 0.03
C0603X5R0J333K	X5R	6.3V	33,000	± 10%	0.30 ± 0.03
C0603X5R0J333M	X5R	6.3V	33,000	± 20%	0.30 ± 0.03
C0603X5R0J473K	X5R	6.3V	47,000	± 10%	0.30 ± 0.03
C0603X5R0J473M	X5R	6.3V	47,000	± 20%	0.30 ± 0.03
C0603X5R0J683K	X5R	6.3V	68,000	± 10%	0.30 ± 0.03
C0603X5R0J683M	X5R	6.3V	68,000	± 20%	0.30 ± 0.03
C0603X5R0J104K	X5R	6.3V	100,000	± 10%	0.30 ± 0.03
C0603X5R0J104M	X5R	6.3V	100,000	± 20%	0.30 ± 0.03
C0603X5R0J154K	X5R	6.3V	150,000	± 10%	0.30 ± 0.03
C0603X5R0J154M	X5R	6.3V	150,000	± 20%	0.30 ± 0.03
C0603X5R0J224K	X5R	6.3V	220,000	± 10%	0.30 ± 0.03
C0603X5R0J224M	X5R	6.3V	220,000	± 20%	0.30 ± 0.03
C0603Y5V1C103Z	Y5V	16V	10,000	+80/-20%	0.30 ± 0.03

MULTILAYER CERAMIC CHIP CAPACITORS



C1005 [EIA CC0402]

Capacitance Range Chart

Temperature Characteristics: C0G (0 ± 30ppm/°C) Rated Voltage: 50V (1H), 25V (1E)

Oonocitonoo	0.00		COG	Oomeeltenee	0.00		С	0G
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)
0.1	0R1	B: ± 0.10pF		30	300	J: ± 5%		
0.5	0R5	C: ± 0.25pF		33	330			
0.75	R75	D: ± 0.50pF		36	360			
1	010			39	390			
1.2	1R2			43	430			
1.5	1R5			47	470			
1.8	1R8			51	510			
2.2	2R2			56	560			
2.7	2R7			62	620			
3.3	3R3			68	680			
3.9	3R9			75	750			
4.7	4R7			82	820			
5.6	5R6	C: ± 0.25pF		91	910			
6.8	6R8	D: ± 0.50pF		100	101			
8.2	8R2			120	121			
10	100			150	151			
11	110	J: ± 5%		180	181			
12	120			220	221			
13	130]		270	271]		
15	150]		330	331			
16	160]		390	391]		
18	180			470	471			
20	200			560	561			
22	220	1		680	681	1		
24	240			820	821			
27	270			1,000	102	1		

• Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%) Rated Voltage: 50V (1H), 35V (1V), 25V (1E), 16V(1C), 10V (1A)

Canacitanaa	Con				X7R		
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)
220	221	K: ± 10%					
330	331	M: ± 20%					
470	471						
680	681						
1,000	102						
1,500	152						
2,200	222						
3,300	332						
4,700	472						
6,800	682						
10,000	103						
15,000	153						
22,000	223						
33,000	333						
47,000	473						
68,000	683						
100,000	104						
150,000	154]					
220,000	224						

Standard Thickness 0.50 mm

MULTILAYER CERAMIC CHIP CAPACITORS



C1005 [EIA CC0402]

Capacitance Range Chart

Temperature Characteristics: X5R (± 15%), X6S (± 22%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 35V (1V), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V (0G)

Capacitanaa	Con			X6S							
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)		
10,000	103	K: ± 10%									
22,000	223	M: ± 20%									
47,000	473										
100,000	104										
220,000	224										
470,000	474										
1,000,000	105										
2,200,000	225										

Oomeeltenee	0.00					X5R			
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)
220	221	K: ± 10%							
330	331	M: ± 20%							
470	471								
680	681								
1,000	102								
1,500	152								
2,200	222								
3,300	332								
4,700	472								
6,800	682								
10,000	103								
15,000	153								
22,000	223								
33,000	333								
47,000	473								
68,000	683								
100,000	104								
220,000	224								
330,000	334								
470,000	474								
1,000,000	105	1							
1,500,000	155	1							
2,200,000	225								
3,300,000	335	1							
4,700,000	475								

Conscitores	0.00		Y5V						
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)		
10,000	103	Z: +80/-20%							
100,000	104								
220,000	224								
470,000	474]							
1,000,000	105								

Standard Thickness 0.50 mm Version B11

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005C0G1H0R5B	C0G	50V	0.5	± 0.10pF	0.50 ± 0.05
C1005C0G1H0R5C	COG	50V	0.5	± 0.25pF	0.50 ± 0.05
C1005C0G1HR75C	COG	50V	0.75	± 0.25pF	0.50 ± 0.05
C1005C0G1H010B	COG	50V	1.0	± 0.10pF	0.50 ± 0.05
C1005C0G1H010C	COG	50V	1.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H1R2B	COG	50V	1.2	± 0.10pF	0.50 ± 0.05
C1005C0G1H1R2C	COG	50V	1.2	± 0.25pF	0.50 ± 0.05
C1005C0G1H1R5B	COG	50V	1.5	± 0.10pF	0.50 ± 0.05
C1005C0G1H1R5C	COG	50V	1.5	± 0.25pF	0.50 ± 0.05
C1005C0G1H1R8B	COG	50V	1.8	± 0.10pF	0.50 ± 0.05
C1005C0G1H1R8C	COG	50V	1.8	± 0.25pF	0.50 ± 0.05
C1005C0G1H020B	COG	50V	2.0	± 0.10pF	0.50 ± 0.05
C1005C0G1H020C	C0G	50V	2.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H2R2B	COG	50V	2.2	± 0.10pF	0.50 ± 0.05
C1005C0G1H2R2C	C0G	50V	2.2	± 0.25pF	0.50 ± 0.05
C1005C0G1H2R5C	C0G	50V	2.5	± 0.25pF	0.50 ± 0.05
C1005C0G1H2R7B	C0G	50V	2.7	± 0.10pF	0.50 ± 0.05
C1005C0G1H2R7C	C0G	50V	2.7	± 0.25pF	0.50 ± 0.05
C1005C0G1H030B	C0G	50V	3.0	± 0.10pF	0.50 ± 0.05
C1005C0G1H030C	C0G	50V	3.0	± 0.25pF	0.50 ± 0.05
1005C0G1H3R3B	COG	50V	3.3	± 0.10pF	0.50 ± 0.05
1005C0G1H3R3C	C0G	50V	3.3	± 0.25pF	0.50 ± 0.05
005C0G1H3R5C	COG	50V	3.5	± 0.25pF	0.50 ± 0.05
005C0G1H3R9B	C0G	50V	3.9	± 0.10pF	0.50 ± 0.05
C1005C0G1H3R9C	C0G	50V	3.9	± 0.25pF	0.50 ± 0.05
C1005C0G1H040B	C0G	50V	4.0	± 0.10pF	0.50 ± 0.05
C1005C0G1H040C	COG	50V	4.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H4R7B	C0G	50V	4.7	± 0.10pF	0.50 ± 0.05
C1005C0G1H4R7C	C0G	50V	4.7	± 0.25pF	0.50 ± 0.05
C1005C0G1H050B	C0G	50V	5.0	± 0.10pF	0.50 ± 0.05
C1005C0G1H050C	C0G	50V	5.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H5R6C	C0G	50V	5.6	± 0.25pF	0.50 ± 0.05
C1005C0G1H5R6D	C0G	50V	5.6	± 0.50pF	0.50 ± 0.05
C1005C0G1H060C	C0G	50V	6.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H060D	COG	50V	6.0	± 0.50pF	0.50 ± 0.05
C1005C0G1H6R8C	COG	50V	6.8	± 0.25pF	0.50 ± 0.05
005C0G1H6R8D	C0G	50V	6.8	± 0.50pF	0.50 ± 0.05
C1005C0G1H070C	C0G	50V	7.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H070D	C0G	50V	7.0	± 0.50pF	0.50 ± 0.05
C1005C0G1H080C	C0G	50V	8.0	± 0.25pF	0.50 ± 0.05
C1005C0G1H080D	COG	50V	8.0	± 0.50pF	0.50 ± 0.05
C1005C0G1H8R2C	C0G	50V	8.2	± 0.25pF	0.50 ± 0.05
C1005C0G1H8R2D	C0G	50V	8.2	± 0.50pF	0.50 ± 0.05
C1005C0G1H090C	C0G	50V	9.0	± 0.25pF	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005C0G1H090D	C0G	50V	9.0	± 0.50pF	0.50 ± 0.05
C1005C0G1H100C	COG	50V	10	± 0.25pF	0.50 ± 0.05
C1005C0G1H100D	COG	50V	10	± 0.50pF	0.50 ± 0.05
C1005C0G1H110J	COG	50V	11	± 5%	0.50 ± 0.05
C1005C0G1H120J	COG	50V	12	± 5%	0.50 ± 0.05
C1005C0G1H130J	COG	50V	13	± 5%	0.50 ± 0.05
C1005C0G1H150J	C0G	50V	15	± 5%	0.50 ± 0.05
C1005C0G1H160J	COG	50V	16	± 5%	0.50 ± 0.05
C1005C0G1H180J	C0G	50V	18	± 5%	0.50 ± 0.05
C1005C0G1H200J	C0G	50V	20	± 5%	0.50 ± 0.05
C1005C0G1H220J	C0G	50V	22	± 5%	0.50 ± 0.05
C1005C0G1H240J	C0G	50V	24	± 5%	0.50 ± 0.05
C1005C0G1H270J	C0G	50V	27	± 5%	0.50 ± 0.05
C1005C0G1H300J	COG	50V	30	± 5%	0.50 ± 0.05
C1005C0G1H330J	C0G	50V	33	± 5%	0.50 ± 0.05
C1005C0G1H360J	C0G	50V	36	± 5%	0.50 ± 0.05
C1005C0G1H390J	C0G	50V	39	± 5%	0.50 ± 0.05
C1005C0G1H430J	C0G	50V	43	± 5%	0.50 ± 0.05
C1005C0G1H470J	C0G	50V	47	± 5%	0.50 ± 0.05
C1005C0G1H510J	C0G	50V	51	± 5%	0.50 ± 0.05
C1005C0G1H560J	COG	50V	56	± 5%	0.50 ± 0.05
C1005C0G1H620J	C0G	50V	62	± 5%	0.50 ± 0.05
C1005C0G1H680J	COG	50V	68	± 5%	0.50 ± 0.05
C1005C0G1H750J	C0G	50V	75	± 5%	0.50 ± 0.05
C1005C0G1H820J	COG	50V	82	± 5%	0.50 ± 0.05
C1005C0G1H910J	C0G	50V	91	± 5%	0.50 ± 0.05
C1005C0G1H101J	COG	50V	100	± 5%	0.50 ± 0.05
C1005C0G1H121J	COG	50V	120	± 5%	0.50 ± 0.05
C1005C0G1H151J	COG	50V	150	± 5%	0.50 ± 0.05
C1005C0G1H181J	COG	50V	180	± 5%	0.50 ± 0.05
C1005C0G1H221J	COG	50V	220	± 5%	0.50 ± 0.05
C1005C0G1H271J	COG	50V	270	± 5%	0.50 ± 0.05
C1005C0G1H331J	COG	50V	330	± 5%	0.50 ± 0.05
C1005C0G1H391J	C0G	50V	390	± 5%	0.50 ± 0.05
C1005C0G1H471J	C0G	50V	470	± 5%	0.50 ± 0.05
C1005C0G1H561J	C0G	50V	560	± 5%	0.50 ± 0.05
C1005C0G1H681J	COG	50V	680	± 5%	0.50 ± 0.05
C1005C0G1H821J	C0G	50V	820	± 5%	0.50 ± 0.05
C1005C0G1H102J	C0G	50V	1,000	± 5%	0.50 ± 0.05
C1005C0G1E561J	C0G	25V	560	± 5%	0.50 ± 0.05
C1005C0G1E681J	COG	25V	680	± 5%	0.50 ± 0.05
C1005C0G1E821J	C0G	25V	820	± 5%	0.50 ± 0.05
C1005C0G1E102J	COG	25V	1,000	± 5%	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005X7R1H221K	X7R	50V	220	± 10%	0.50 ± 0.05
C1005X7R1H221M	X7R	50V	220	± 20%	0.50 ± 0.05
C1005X7R1H331K	X7R	50V	330	± 10%	0.50 ± 0.05
C1005X7R1H331M	X7R	50V	330	± 20%	0.50 ± 0.05
C1005X7R1H471K	X7R	50V	470	± 10%	0.50 ± 0.05
C1005X7R1H471M	X7R	50V	470	± 20%	0.50 ± 0.05
C1005X7R1H681K	X7R	50V	680	± 10%	0.50 ± 0.05
C1005X7R1H681M	X7R	50V	680	± 20%	0.50 ± 0.05
C1005X7R1H102K	X7R	50V	1,000	± 10%	0.50 ± 0.05
C1005X7R1H102M	X7R	50V	1,000	± 20%	0.50 ± 0.05
C1005X7R1H152K	X7R	50V	1,500	± 10%	0.50 ± 0.05
C1005X7R1H152M	X7R	50V	1,500	± 20%	0.50 ± 0.05
C1005X7R1H222K	X7R	50V	2,200	± 10%	0.50 ± 0.05
C1005X7R1H222M	X7R	50V	2,200	± 20%	0.50 ± 0.05
C1005X7R1H332K	X7R	50V	3,300	± 10%	0.50 ± 0.05
C1005X7R1H332M	X7R	50V	3,300	± 20%	0.50 ± 0.05
C1005X7R1H472K	X7R	50V	4,700	± 10%	0.50 ± 0.05
C1005X7R1H472M	X7R	50V	4,700	± 20%	0.50 ± 0.05
C1005X7R1H682K	X7R	50V	6,800	± 10%	0.50 ± 0.05
C1005X7R1H682M	X7R	50V	6,800	± 20%	0.50 ± 0.05
C1005X7R1H103K	X7R	50V	10,000	± 10%	0.50 ± 0.05
C1005X7R1H103M	X7R	50V	10,000	± 20%	0.50 ± 0.05
C1005X7R1H153K	X7R	50V	15,000	± 10%	0.50 ± 0.05
C1005X7R1H153M	X7R	50V	15,000	± 20%	0.50 ± 0.05
C1005X7R1H223K	X7R	50V	22,000	± 10%	0.50 ± 0.05
C1005X7R1H223M	X7R	50V	22,000	± 20%	0.50 ± 0.05
C1005X7R1H333K	X7R	50V	33,000	± 10%	0.50 ± 0.05
C1005X7R1H333M	X7R	50V	33,000	± 20%	0.50 ± 0.05
C1005X7R1H473K	X7R	50V	47,000	± 10%	0.50 ± 0.05
C1005X7R1H473M	X7R	50V	47,000	± 20%	0.50 ± 0.05
C1005X7R1H683K	X7R	50V	68,000	± 10%	0.50 ± 0.05
C1005X7R1H683M	X7R	50V	68,000	± 20%	0.50 ± 0.05
C1005X7R1H104K	X7R	50V	100,000	± 10%	0.50 ± 0.05
C1005X7R1H104M	X7R	50V	100,000	± 20%	0.50 ± 0.05
C1005X7R1V103K	X7R	35V	10,000	± 10%	0.50 ± 0.05
C1005X7R1V103M	X7R	35V	10,000	± 20%	0.50 ± 0.05
C1005X7R1V223K	X7R	35V	22,000	± 10%	0.50 ± 0.05
C1005X7R1V223M	X7R	35V	22,000	± 20%	0.50 ± 0.05
C1005X7R1V473K	X7R	35V	47,000	± 10%	0.50 ± 0.05
C1005X7R1V473M	X7R	35V	47,000	± 20%	0.50 ± 0.05
C1005X7R1V104K	X7R	35V	100,000	± 10%	0.50 ± 0.05
C1005X7R1V104M	X7R	35V	100,000	± 20%	0.50 ± 0.05
C1005X7R1E102K	X7R	25V	1,000	± 10%	0.50 ± 0.05
C1005X7R1E102M	X7R	25V	1,000	± 20%	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005X7R1E152K	X7R	25V	1,500	± 10%	0.50 ± 0.05
C1005X7R1E152M	X7R	25V	1,500	± 20%	0.50 ± 0.05
C1005X7R1E222K	X7R	25V	2,200	± 10%	0.50 ± 0.05
C1005X7R1E222M	X7R	25V	2,200	± 20%	0.50 ± 0.05
C1005X7R1E332K	X7R	25V	3,300	± 10%	0.50 ± 0.05
C1005X7R1E332M	X7R	25V	3,300	± 20%	0.50 ± 0.05
C1005X7R1E472K	X7R	25V	4,700	± 10%	0.50 ± 0.05
C1005X7R1E472M	X7R	25V	4,700	± 20%	0.50 ± 0.05
C1005X7R1E682K	X7R	25V	6,800	± 10%	0.50 ± 0.05
C1005X7R1E682M	X7R	25V	6,800	± 20%	0.50 ± 0.05
C1005X7R1E103J	X7R	25V	10,000	± 5%	0.50 ± 0.05
C1005X7R1E103K	X7R	25V	10,000	± 10%	0.50 ± 0.05
C1005X7R1E103M	X7R	25V	10,000	± 20%	0.50 ± 0.05
C1005X7R1E153K	X7R	25V	15,000	± 10%	0.50 ± 0.05
C1005X7R1E153M	X7R	25V	15,000	± 20%	0.50 ± 0.05
C1005X7R1E223K	X7R	25V	22,000	± 10%	0.50 ± 0.05
C1005X7R1E223M	X7R	25V	22,000	± 20%	0.50 ± 0.05
C1005X7R1E333K	X7R	25V	33,000	± 10%	0.50 ± 0.05
C1005X7R1E333M	X7R	25V	33,000	± 20%	0.50 ± 0.05
C1005X7R1E473K	X7R	25V	47,000	± 10%	0.50 ± 0.05
C1005X7R1E473M	X7R	25V	47,000	± 20%	0.50 ± 0.05
C1005X7R1E683K	X7R	25V	68,000	± 10%	0.50 ± 0.05
C1005X7R1E683M	X7R	25V	68,000	± 20%	0.50 ± 0.05
C1005X7R1E104K	X7R	25V	100,000	± 10%	0.50 ± 0.05
C1005X7R1E104M	X7R	25V	100,000	± 20%	0.50 ± 0.05
C1005X7R1C103K	X7R	16V	10,000	± 10%	0.50 ± 0.05
C1005X7R1C103M	X7R	16V	10,000	± 20%	0.50 ± 0.05
C1005X7R1C153K	X7R	16V	15,000	± 10%	0.50 ± 0.05
C1005X7R1C153M	X7R	16V	15,000	± 20%	0.50 ± 0.05
C1005X7R1C223K	X7R	16V	22,000	± 10%	0.50 ± 0.05
C1005X7R1C223M	X7R	16V	22,000	± 20%	0.50 ± 0.05
C1005X7R1C333K	X7R	16V	33,000	± 10%	0.50 ± 0.05
C1005X7R1C333M	X7R	16V	33,000	± 20%	0.50 ± 0.05
C1005X7R1C473K	X7R	16V	47,000	± 10%	0.50 ± 0.05
C1005X7R1C473M	X7R	16V	47,000	± 20%	0.50 ± 0.05
C1005X7R1C683K	X7R	16V	68,000	± 10%	0.50 ± 0.05
C1005X7R1C683M	X7R	16V	68,000	± 20%	0.50 ± 0.05
C1005X7R1C104K	X7R	16V	100,000	± 10%	0.50 ± 0.05
C1005X7R1C104M	X7R	16V	100,000	± 20%	0.50 ± 0.05
C1005X7R1C154K	X7R	16V	150,000	± 10%	0.50 ± 0.05
C1005X7R1C154M	X7R	16V	150,000	± 20%	0.50 ± 0.05
C1005X7R1C224K	X7R	16V	220,000	± 10%	0.50 ± 0.05
C1005X7R1C224M	X7R	16V	220,000	± 20%	0.50 ± 0.05
C1005X7R1A473K	X7R	10V	47,000	± 10%	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S(-55 to 105°C, ±22%), X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005X7R1A473M	X7R	10V	47,000	± 20%	0.50 ± 0.05
C1005X7R1A683K	X7R	10V	68,000	± 10%	0.50 ± 0.05
C1005X7R1A683M	X7R	10V	68,000	± 20%	0.50 ± 0.05
C1005X7R1A104K	X7R	10V	100,000	± 10%	0.50 ± 0.05
C1005X7R1A104M	X7R	10V	100,000	± 20%	0.50 ± 0.05
C1005X7R1A224K	X7R	10V	220,000	± 10%	0.50 ± 0.05
C1005X7R1A224M	X7R	10V	220,000	± 20%	0.50 ± 0.05
C1005X6S1H103K	X6S	50V	10,000	± 10%	0.50 ± 0.05
C1005X6S1H103M	X6S	50V	10,000	± 20%	0.50 ± 0.05
C1005X6S1H223K	X6S	50V	22,000	± 10%	0.50 ± 0.05
C1005X6S1H223M	X6S	50V	22,000	± 20%	0.50 ± 0.05
C1005X6S1H473K	X6S	50V	47,000	± 10%	0.50 ± 0.05
C1005X6S1H473M	X6S	50V	47,000	± 20%	0.50 ± 0.05
C1005X6S1H104K	X6S	50V	100,000	± 10%	0.50 ± 0.05
C1005X6S1H104M	X6S	50V	100,000	± 20%	0.50 ± 0.05
C1005X6S1V104K	X6S	35V	100,000	± 10%	0.50 ± 0.05
C1005X6S1V104M	X6S	35V	100,000	± 20%	0.50 ± 0.05
C1005X6S1E104K	X6S	25V	100,000	± 10%	0.50 ± 0.05
C1005X6S1E104M	X6S	25V	100,000	± 20%	0.50 ± 0.05
C1005X6S1E224K	X6S	25V	220,000	± 10%	0.50 ± 0.05
C1005X6S1E224M	X6S	25V	220,000	± 20%	0.50 ± 0.05
C1005X6S1C224K	X6S	16V	220,000	± 10%	0.50 ± 0.05
C1005X6S1C224M	X6S	16V	220,000	± 20%	0.50 ± 0.05
C1005X6S1A474K	X6S	10V	470,000	± 10%	0.50 ± 0.05
C1005X6S1A474M	X6S	10V	470,000	± 20%	0.50 ± 0.05
C1005X6S1A105K	X6S	10V	1,000,000	± 10%	0.50 ± 0.05
C1005X6S1A105M	X6S	10V	1,000,000	± 20%	0.50 ± 0.05
C1005X6S0J474K	X6S	6.3V	470,000	± 10%	0.50 ± 0.05
C1005X6S0J474M	X6S	6.3V	470,000	± 20%	0.50 ± 0.05
C1005X6S0J105K	X6S	6.3V	1,000,000	± 10%	0.50 ± 0.05
C1005X6S0J105M	X6S	6.3V	1,000,000	± 20%	0.50 ± 0.05
C1005X6S0G105K	X6S	4V	1,000,000	± 10%	0.50 ± 0.05
C1005X6S0G105M	X6S	4V	1,000,000	± 20%	0.50 ± 0.05
C1005X6S0G225M	X6S	4V	2,200,000	± 20%	0.50 ± 0.05
C1005X5R1H221K	X5R	50V	220	± 10%	0.50 ± 0.05
C1005X5R1H331K	X5R	50V	330	± 10%	0.50 ± 0.05
C1005X5R1H471K	X5R	50V	470	± 10%	0.50 ± 0.05
C1005X5R1H681K	X5R	50V	680	± 10%	0.50 ± 0.05
C1005X5R1H102K	X5R	50V	1,000	± 10%	0.50 ± 0.05
C1005X5R1H152K	X5R	50V	1,500	± 10%	0.50 ± 0.05
C1005X5R1H222K	X5R	50V	2,200	± 10%	0.50 ± 0.05
C1005X5R1H332K	X5R	50V	3,300	± 10%	0.50 ± 0.05
C1005X5R1H472K	X5R	50V	4,700	± 10%	0.50 ± 0.05
C1005X5R1H682K	X5R	50V	6,800	± 10%	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005X5R1H473K	X5R	50V	47,000	± 10%	0.50 ± 0.05
C1005X5R1H473M	X5R	50V	47,000	± 20%	0.50 ± 0.05
C1005X5R1H683K	X5R	50V	68,000	± 10%	0.50 ± 0.05
C1005X5R1H683M	X5R	50V	68,000	± 20%	0.50 ± 0.05
C1005X5R1H104K	X5R	50V	100,000	± 10%	0.50 ± 0.05
C1005X5R1H104M	X5R	50V	100,000	± 20%	0.50 ± 0.05
C1005X5R1V104K	X5R	35V	100,000	± 10%	0.50 ± 0.05
C1005X5R1V104M	X5R	35V	100,000	± 20%	0.50 ± 0.05
C1005X5R1E103K	X5R	25V	10,000	± 10%	0.50 ± 0.05
C1005X5R1E153K	X5R	25V	15,000	± 10%	0.50 ± 0.05
C1005X5R1E223K	X5R	25V	22,000	± 10%	0.50 ± 0.05
C1005X5R1E333K	X5R	25V	33,000	± 10%	0.50 ± 0.05
C1005X5R1E473K	X5R	25V	47,000	± 10%	0.50 ± 0.05
C1005X5R1E473M	X5R	25V	47,000	± 20%	0.50 ± 0.05
C1005X5R1E683K	X5R	25V	68,000	± 10%	0.50 ± 0.05
C1005X5R1E683M	X5R	25V	68,000	± 20%	0.50 ± 0.05
C1005X5R1E104K	X5R	25V	100,000	± 10%	0.50 ± 0.05
C1005X5R1E104M	X5R	25V	100,000	± 20%	0.50 ± 0.05
C1005X5R1E224K	X5R	25V	220,000	± 10%	0.50 ± 0.05
C1005X5R1E224M	X5R	25V	220,000	± 20%	0.50 ± 0.05
C1005X5R1C473K	X5R	16V	47,000	± 10%	0.50 ± 0.05
C1005X5R1C473M	X5R	16V	47,000	± 20%	0.50 ± 0.05
C1005X5R1C683K	X5R	16V	68,000	± 10%	0.50 ± 0.05
C1005X5R1C683M	X5R	16V	68,000	± 20%	0.50 ± 0.05
C1005X5R1C104K	X5R	16V	100,000	± 10%	0.50 ± 0.05
C1005X5R1C104M	X5R	16V	100,000	± 20%	0.50 ± 0.05
C1005X5R1C224K	X5R	16V	220,000	± 10%	0.50 ± 0.05
C1005X5R1C224M	X5R	16V	220,000	± 20%	0.50 ± 0.05
C1005X5R1C334K	X5R	16V	330,000	± 10%	0.50 ± 0.05
C1005X5R1C334M	X5R	16V	330,000	± 20%	0.50 ± 0.05
C1005X5R1C474K	X5R	16V	470,000	± 10%	0.50 ± 0.05
C1005X5R1C474M	X5R	16V	470,000	± 20%	0.50 ± 0.05
C1005X5R1C105K	X5R	16V	1,000,000	± 10%	0.50 ± 0.05
C1005X5R1C105M	X5R	16V	1,000,000	± 20%	0.50 ± 0.05
C1005X5R1A473K	X5R	10V	47,000	± 10%	0.50 ± 0.05
C1005X5R1A473M	X5R	10V	47,000	± 20%	0.50 ± 0.05
C1005X5R1A683K	X5R	10V	68,000	± 10%	0.50 ± 0.05
005X5R1A683M	X5R	10V	68,000	± 20%	0.50 ± 0.05
C1005X5R1A104K	X5R	10V	100,000	± 10%	0.50 ± 0.05
C1005X5R1A104M	X5R	10V	100,000	± 20%	0.50 ± 0.05
C1005X5R1A224K	X5R	10V	220,000	± 10%	0.50 ± 0.05
C1005X5R1A224M	X5R	10V	220,000	± 20%	0.50 ± 0.05
C1005X5R1A334K	X5R	10V	330,000	± 10%	0.50 ± 0.05
C1005X5R1A334M	X5R	10V	330,000	± 20%	0.50 ± 0.05

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1005 [EIA CC0402]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	eristics: X5R (-55 to +85 Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1005X5R1A474K	X5R	10V	470,000	± 10%	0.50 ± 0.05
C1005X5R1A474M	X5R	10V	470,000	± 20%	0.50 ± 0.05
C1005X5R1A105K	X5R	10V	1,000,000	± 10%	0.50 ± 0.05
C1005X5R1A105K	X5R	10V	1,000,000	± 10 %	0.50 ± 0.05
C1005X5R1A105M	X5R	10V	1,500,000	± 10%	0.50 ± 0.05
C1005X5R1A155K	X5R	10V	1,500,000	± 10%	0.50 ± 0.05
C1005X5R1A155M	X5R	10V	2,200,000	± 10%	0.50 ± 0.05
C1005X5R1A225K C1005X5R1A225M	X5R X5R	10V		± 10% ± 20%	0.50 ± 0.05 0.50 ± 0.05
	-	-	2,200,000		
C1005X5R0J104K	X5R	6.3V	100,000	± 10%	0.50 ± 0.05
C1005X5R0J104M	X5R	6.3V	100,000	± 20%	0.50 ± 0.05
C1005X5R0J224K	X5R	6.3V	220,000	± 10%	0.50 ± 0.05
C1005X5R0J224M	X5R	6.3V	220,000	± 20%	0.50 ± 0.05
C1005X5R0J334K	X5R	6.3V	330,000	± 10%	0.50 ± 0.05
C1005X5R0J334M	X5R	6.3V	330,000	± 20%	0.50 ± 0.05
C1005X5R0J474K	X5R	6.3V	470,000	± 10%	0.50 ± 0.05
C1005X5R0J474M	X5R	6.3V	470,000	± 20%	0.50 ± 0.05
C1005X5R0J105K	X5R	6.3V	1,000,000	± 10%	0.50 ± 0.05
C1005X5R0J105M	X5R	6.3V	1,000,000	± 20%	0.50 ± 0.05
C1005X5R0J225K	X5R	6.3V	2,200,000	± 10%	0.50 ± 0.05
C1005X5R0J225M	X5R	6.3V	2,200,000	± 20%	0.50 ± 0.05
C1005X5R0J335K	X5R	6.3V	3,300,000	± 10%	0.50 ± 0.15
C1005X5R0J335M	X5R	6.3V	3,300,000	± 20%	0.50 ± 0.15
C1005X5R0J475K	X5R	6.3V	4,700,000	± 10%	0.50 ± 0.15
C1005X5R0J475M	X5R	6.3V	4,700,000	± 20%	0.50 ± 0.15
C1005X5R0G225K	X5R	4V	2,200,000	± 10%	0.50 ± 0.05
C1005X5R0G225M	X5R	4V	2,200,000	± 20%	0.50 ± 0.05
C1005X5R0G335K	X5R	4V	3,300,000	± 10%	0.50 ± 0.15
C1005X5R0G335M	X5R	4V	3,300,000	± 20%	0.50 ± 0.15
C1005X5R0G475K	X5R	4V	4,700,000	± 10%	0.50 ± 0.15
C1005X5R0G475M	X5R	4V	4,700,000	± 20%	0.50 ± 0.15
C1005Y5V1H103Z	Y5V	50V	10,000	+80/-20%	0.50 ± 0.05
C1005Y5V1E104Z	Y5V	25V	100,000	+80/-20%	0.50 ± 0.05
C1005Y5V1E224Z	Y5V	25V	220,000	+80/-20%	0.50 ± 0.05
C1005Y5V1C104Z	Y5V	16V	100,000	+80/-20%	0.50 ± 0.05
C1005Y5V1C224Z	Y5V	16V	220,000	+80/-20%	0.50 ± 0.05
C1005Y5V1A224Z	Y5V	10V	220,000	+80/-20%	0.50 ± 0.05
C1005Y5V1A474Z	Y5V	10V	470,000	+80/-20%	0.50 ± 0.05
C1005Y5V0J105Z	Y5V	6.3V	1,000,000	+80/-20%	0.50 ± 0.05
010001002	101	0.0 V	1,000,000	00/ 20/0	0.00 ± 0.00

MULTILAYER CERAMIC CHIP CAPACITORS



C1608 [EIA CC0603]

Capacitance Range Chart

Temperature Characteristics: C0G (0 ± 30ppm/^oC) Rated Voltage: 50V (1H), 25V (1E)

Capacitance	Сар		C0G	Capac	itance	Con		C	0G
(pF)	Code	Tolerance	1H (50V)		F)	Cap Code	Tolerance	1H (50V)	1E (25V)
0.1	0R1	B: ± 0.10pF			91	910	J: ± 5%		
0.5	0R5	C: ± 0.25pF			100	101			
0.75	R75				110	111			
1	010				120	121			
1.2	1R2				130	131			
1.5	1R5				150	151			
1.8	1R8				160	161			
2.2	2R2				180	181			
2.7	2R7				200	201			
3.3	3R3				220	221			
3.9	3R9				240	241			
4.7	4R7				270	271			
5.6	5R6	C: ± 0.25pF			300	301			
6.8	6R8	D: ± 0.50pF			330	331			
8.2	8R2				360	361			
10	100				390	391			
11	110	J: ± 5%			430	431			
12	120				470	471			
13	130				510	511			
15	150				560	561			
16	160				620	621			
18	180				680	681			
20	200				750	751			
22	220				820	821			
24	240				910	911			
27	270				1,000	102			
30	300				1,200	122			
33	330				1,500	152			
36	360				1,800	182			
39	390				2,200	222			
43	430				2,700	272			
47	470				3,300	332			
51	510				3,900	392			
56	560				4,700	472			
62	620				5,600	562			
68	680				6,800	682			
75	750				8,200	822			
82	820			1	0,000	103			

• Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.

Capacitance Range Chart

Temperature Characteristics: X6S (± 22%) Rated Voltage: 50V (1H), 35V (1V), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V (0G)

Capacitanaa	Con		X6S						
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)
220,000	224	K: ± 10%							
470,000	474	M: ± 20%							
1,000,000	105								
2,200,000	225								
4,700,000	475								
10,000,000	106								

Standard Thickness 0.80 mm 0.50 mm

MULTILAYER CERAMIC CHIP CAPACITORS



C1608 [EIA CC0603]

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%), X5R (± 15%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 35V (1V), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V (0G)

Conceltance	0.00					X5R			
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)
100,000	104	K: ± 10%							
150,000	154	M: ± 20%							
220,000	224								
330,000	334								
470,000	474								
680,000	684								
1,000,000	105								
1,500,000	155								
2,200,000	225								
3,300,000	335								
4,700,000	475								
6,800,000	685]							
10,000,000	106								

Conscitores	Con				X	7R		
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
100	101	K: ± 10%						
220	221	M: ± 20%						
330	331							
470	471							
680	681							
1,000	102							
1,500	152							
2,200	222							
3,300	332							
4,700	472							
6,800	682							
10,000	103							
15,000	153							
22,000	223							
33,000	333							
47,000	473							
68,000	683							
100,000	104							
150,000	154							
220,000	224							
330,000	334							
470,000	474							
680,000	684							
1,000,000	105							
2,200,000	225							

Conseitence	0.00		Y5V					
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	
100,000	104	Z: +80/-20%						
220,000	224							
470,000	474							
1,000,000	105							
2,200,000	225							
4,700,000	475							
10,000,000	106							

Standard Thickness 0.80 mm

TDK MLCC US Catalog

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608C0G1H0R5B	COG	50V	0.5	± 0.10pF	0.80 ± 0.10
C1608C0G1H0R5C	COG	50V	0.5	± 0.25pF	0.80 ± 0.10
C1608C0G1HR75C	COG	50V	0.75	± 0.25pF	0.80 ± 0.10
C1608C0G1H010B	COG	50V	1.0	± 0.10pF	0.80 ± 0.10
C1608C0G1H010C	COG	50V	1.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H1R2B	COG	50V	1.2	± 0.10pF	0.80 ± 0.10
C1608C0G1H1R2C	COG	50V	1.2	± 0.25pF	0.80 ± 0.10
C1608C0G1H1R5B	COG	50V	1.5	± 0.10pF	0.80 ± 0.10
C1608C0G1H1R5C	COG	50V	1.5	± 0.25pF	0.80 ± 0.10
C1608C0G1H1R8B	COG	50V	1.8	± 0.10pF	0.80 ± 0.10
C1608C0G1H1R8C	COG	50V	1.8	± 0.25pF	0.80 ± 0.10
C1608C0G1H020B	COG	50V	2.0	± 0.10pF	0.80 ± 0.10
C1608C0G1H020C	COG	50V	2.0	± 0.25pF	0.80 ± 0.10
1608C0G1H2R2B	COG	50V	2.2	± 0.10pF	0.80 ± 0.10
1608C0G1H2R2C	COG	50V	2.2	± 0.25pF	0.80 ± 0.10
C1608C0G1H2R7B	COG	50V	2.7	± 0.10pF	0.80 ± 0.10
C1608C0G1H2R7C	COG	50V	2.7	± 0.25pF	0.80 ± 0.10
1608C0G1H030B	COG	50V	3.0	± 0.10pF	0.80 ± 0.10
1608C0G1H030C	COG	50V	3.0	± 0.25pF	0.80 ± 0.10
1608C0G1H3R3B	COG	50V	3.3	± 0.10pF	0.80 ± 0.10
1608C0G1H3R3C	COG	50V	3.3	± 0.25pF	0.80 ± 0.10
1608C0G1H3R9B	COG	50V	3.9	± 0.10pF	0.80 ± 0.10
1608C0G1H3R9C	COG	50V	3.9	± 0.25pF	0.80 ± 0.10
C1608C0G1H040B	COG	50V	4.0	± 0.10pF	0.80 ± 0.10
C1608C0G1H040C	COG	50V	4.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H4R7B	COG	50V	4.7	± 0.10pF	0.80 ± 0.10
C1608C0G1H4R7C	COG	50V	4.7	± 0.25pF	0.80 ± 0.10
C1608C0G1H050B	COG	50V	5.0	± 0.10pF	0.80 ± 0.10
C1608C0G1H050C	COG	50V	5.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H5R6C	COG	50V	5.6	± 0.25pF	0.80 ± 0.10
1608C0G1H5R6D	COG	50V	5.6	± 0.50pF	0.80 ± 0.10
C1608C0G1H060C	COG	50V	6.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H060D	COG	50V	6.0	± 0.50pF	0.80 ± 0.10
C1608C0G1H6R8C	COG	50V	6.8	± 0.25pF	0.80 ± 0.10
1608C0G1H6R8D	COG	50V	6.8	± 0.50pF	0.80 ± 0.10
C1608C0G1H070C	COG	50V	7.0	± 0.25pF	0.80 ± 0.10
1608C0G1H070D	COG	50V	7.0	± 0.50pF	0.80 ± 0.10
1608C0G1H080C	COG	50V	8.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H080D	COG	50V	8.0	± 0.50pF	0.80 ± 0.10
C1608C0G1H8R2C	COG	50V	8.2	± 0.25pF	0.80 ± 0.10
C1608C0G1H8R2D	COG	50V	8.2	± 0.50pF	0.80 ± 0.10
C1608C0G1H090C	COG	50V	9.0	± 0.25pF	0.80 ± 0.10
C1608C0G1H090D	COG	50V	9.0	± 0.50pF	0.80 ± 0.10
C1608C0G1H100C	COG	50V	10	± 0.25pF	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 1 (Temperature Compensating)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608C0G1H100D	C0G	50V	10	± 0.50pF	0.80 ± 0.10
C1608C0G1H110J	COG	50V	11	± 5%	0.80 ± 0.10
C1608C0G1H120J	COG	50V	12	± 5%	0.80 ± 0.10
C1608C0G1H130J	COG	50V	13	± 5%	0.80 ± 0.10
C1608C0G1H150J	COG	50V	15	± 5%	0.80 ± 0.10
C1608C0G1H160J	COG	50V	16	± 5%	0.80 ± 0.10
C1608C0G1H180J	COG	50V	18	± 5%	0.80 ± 0.10
C1608C0G1H200J	COG	50V	20	± 5%	0.80 ± 0.10
C1608C0G1H220J	COG	50V	22	± 5%	0.80 ± 0.10
C1608C0G1H240J	COG	50V	24	± 5%	0.80 ± 0.10
C1608C0G1H270J	C0G	50V	27	± 5%	0.80 ± 0.10
C1608C0G1H300J	C0G	50V	30	± 5%	0.80 ± 0.10
C1608C0G1H330J	C0G	50V	33	± 5%	0.80 ± 0.10
C1608C0G1H360J	C0G	50V	36	± 5%	0.80 ± 0.10
C1608C0G1H390J	C0G	50V	39	± 5%	0.80 ± 0.10
C1608C0G1H430J	C0G	50V	43	± 5%	0.80 ± 0.10
1608C0G1H470J	C0G	50V	47	± 5%	0.80 ± 0.10
1608C0G1H510J	C0G	50V	51	± 5%	0.80 ± 0.10
1608C0G1H560J	C0G	50V	56	± 5%	0.80 ± 0.10
1608C0G1H620J	C0G	50V	62	± 5%	0.80 ± 0.10
1608C0G1H680J	COG	50V	68	± 5%	0.80 ± 0.10
1608C0G1H750J	C0G	50V	75	± 5%	0.80 ± 0.10
1608C0G1H820J	C0G	50V	82	± 5%	0.80 ± 0.10
1608C0G1H910J	C0G	50V	91	± 5%	0.80 ± 0.10
1608C0G1H101J	C0G	50V	100	± 5%	0.80 ± 0.10
C1608C0G1H111J	C0G	50V	110	± 5%	0.80 ± 0.10
C1608C0G1H121J	C0G	50V	120	± 5%	0.80 ± 0.10
C1608C0G1H131J	C0G	50V	130	± 5%	0.80 ± 0.10
C1608C0G1H151J	C0G	50V	150	± 5%	0.80 ± 0.10
C1608C0G1H161J	C0G	50V	160	± 5%	0.80 ± 0.10
1608C0G1H181J	C0G	50V	180	± 5%	0.80 ± 0.10
C1608C0G1H201J	C0G	50V	200	± 5%	0.80 ± 0.10
1608C0G1H221J	C0G	50V	220	± 5%	0.80 ± 0.10
1608C0G1H241J	C0G	50V	240	± 5%	0.80 ± 0.10
1608C0G1H271J	C0G	50V	270	± 5%	0.80 ± 0.10
1608C0G1H301J	C0G	50V	300	± 5%	0.80 ± 0.10
1608C0G1H331J	COG	50V	330	± 5%	0.80 ± 0.10
1608C0G1H361J	COG	50V	360	± 5%	0.80 ± 0.10
1608C0G1H391J	COG	50V	390	± 5%	0.80 ± 0.10
C1608C0G1H431J	C0G	50V	430	± 5%	0.80 ± 0.10
C1608C0G1H471J	C0G	50V	470	± 5%	0.80 ± 0.10
C1608C0G1H511J	C0G	50V	510	± 5%	0.80 ± 0.10
C1608C0G1H561J	COG	50V	560	± 5%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608C0G1H681J	COG	50V	680	± 5%	0.80 ± 0.10
C1608C0G1H751J	COG	50V	750	± 5%	0.80 ± 0.10
C1608C0G1H821J	COG	50V	820	± 5%	0.80 ± 0.10
C1608C0G1H911J	COG	50V	910	± 5%	0.80 ± 0.10
C1608C0G1H102J	COG	50V	1,000	± 5%	0.80 ± 0.10
C1608C0G1H122J	COG	50V	1,200	± 5%	0.80 ± 0.10
C1608C0G1H152J	COG	50V	1,500	± 5%	0.80 ± 0.10
C1608C0G1H182J	COG	50V	1,800	± 5%	0.80 ± 0.10
C1608C0G1H222J	COG	50V	2,200	± 5%	0.80 ± 0.10
C1608C0G1H272J	COG	50V	2,700	± 5%	0.80 ± 0.10
C1608C0G1H332J	COG	50V	3,300	± 5%	0.80 ± 0.10
C1608C0G1H392J	COG	50V	3,900	± 5%	0.80 ± 0.10
C1608C0G1H472J	COG	50V	4,700	± 5%	0.80 ± 0.10
C1608C0G1H562J	COG	50V	5,600	± 5%	0.80 ± 0.10
C1608C0G1H682J	COG	50V	6,800	± 5%	0.80 ± 0.10
C1608C0G1H822J	COG	50V	8,200	± 5%	0.80 ± 0.10
C1608C0G1H103J	COG	50V	10,000	± 5%	0.80 ± 0.10
C1608C0G1E392J	COG	25V	3,900	± 5%	0.80 ± 0.10
C1608C0G1E472J	COG	25V	4,700	± 5%	0.80 ± 0.10
C1608C0G1E562J	COG	25V	5,600	± 5%	0.80 ± 0.10
C1608C0G1E682J	COG	25V	6,800	± 5%	0.80 ± 0.10
C1608C0G1E822J	COG	25V	8,200	± 5%	0.80 ± 0.10
C1608C0G1E103J	C0G	25V	10,000	± 5%	0.80 ± 0.10

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X7R1H101K	X7R	50V	100	± 10%	0.80 ± 0.10
C1608X7R1H101M	X7R	50V	100	± 20%	0.80 ± 0.10
C1608X7R1H221K	X7R	50V	220	± 10%	0.80 ± 0.10
C1608X7R1H221M	X7R	50V	220	± 20%	0.80 ± 0.10
C1608X7R1H331K	X7R	50V	330	± 10%	0.80 ± 0.10
C1608X7R1H331M	X7R	50V	330	± 20%	0.80 ± 0.10
C1608X7R1H471K	X7R	50V	470	± 10%	0.80 ± 0.10
C1608X7R1H471M	X7R	50V	470	± 20%	0.80 ± 0.10
C1608X7R1H681K	X7R	50V	680	± 10%	0.80 ± 0.10
C1608X7R1H681M	X7R	50V	680	± 20%	0.80 ± 0.10
C1608X7R1H102J	X7R	50V	1,000	± 5%	0.80 ± 0.10
C1608X7R1H102K	X7R	50V	1,000	± 10%	0.80 ± 0.10
C1608X7R1H102M	X7R	50V	1,000	± 20%	0.80 ± 0.10
C1608X7R1H152K	X7R	50V	1,500	± 10%	0.80 ± 0.10
C1608X7R1H152M	X7R	50V	1,500	± 20%	0.80 ± 0.10
C1608X7R1H222K	X7R	50V	2,200	± 10%	0.80 ± 0.10
C1608X7R1H222M	X7R	50V	2,200	± 20%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X7R1H332K	X7R	50V	3,300	± 10%	0.80 ± 0.10
C1608X7R1H332M	X7R	50V	3,300	± 20%	0.80 ± 0.10
C1608X7R1H472K	X7R	50V	4,700	± 10%	0.80 ± 0.10
C1608X7R1H472M	X7R	50V	4,700	± 20%	0.80 ± 0.10
C1608X7R1H682K	X7R	50V	6,800	± 10%	0.80 ± 0.10
C1608X7R1H682M	X7R	50V	6,800	± 20%	0.80 ± 0.10
C1608X7R1H103J	X7R	50V	10,000	± 5%	0.80 ± 0.10
C1608X7R1H103K	X7R	50V	10,000	± 10%	0.80 ± 0.10
C1608X7R1H103M	X7R	50V	10,000	± 20%	0.80 ± 0.10
C1608X7R1H153K	X7R	50V	15,000	± 10%	0.80 ± 0.10
C1608X7R1H153M	X7R	50V	15,000	± 20%	0.80 ± 0.10
C1608X7R1H223K	X7R	50V	22,000	± 10%	0.80 ± 0.10
C1608X7R1H223M	X7R	50V	22,000	± 20%	0.80 ± 0.10
C1608X7R1H333K	X7R	50V	33,000	± 10%	0.80 ± 0.10
C1608X7R1H333M	X7R	50V	33,000	± 20%	0.80 ± 0.10
C1608X7R1H473K	X7R	50V	47,000	± 10%	0.80 ± 0.10
C1608X7R1H473M	X7R	50V	47,000	± 20%	0.80 ± 0.10
C1608X7R1H683K	X7R	50V	68,000	± 10%	0.80 ± 0.10
C1608X7R1H683M	X7R	50V	68,000	± 20%	0.80 ± 0.10
C1608X7R1H104K	X7R	50V	100,000	± 10%	0.80 ± 0.10
C1608X7R1H104M	X7R	50V	100,000	± 20%	0.80 ± 0.10
C1608X7R1H154K	X7R	50V	150,000	± 10%	0.80 ± 0.10
C1608X7R1H154M	X7R	50V	150,000	± 20%	0.80 ± 0.10
C1608X7R1H224K	X7R	50V	220,000	± 10%	0.80 ± 0.10
C1608X7R1H224M	X7R	50V	220,000	± 20%	0.80 ± 0.10
C1608X7R1H334K	X7R	50V	330,000	± 10%	0.80 ± 0.10
C1608X7R1H334M	X7R	50V	330,000	± 20%	0.80 ± 0.10
C1608X7R1H474K	X7R	50V	470,000	± 10%	0.80 ± 0.10
C1608X7R1H474M	X7R	50V	470,000	± 20%	0.80 ± 0.10
C1608X7R1V334K	X7R	35V	330,000	± 10%	0.80 ± 0.10
C1608X7R1V334M	X7R	35V	330,000	± 20%	0.80 ± 0.10
C1608X7R1V474K	X7R	35V	470,000	± 10%	0.80 ± 0.10
C1608X7R1V474M	X7R	35V	470,000	± 20%	0.80 ± 0.10
C1608X7R1V105K	X7R	35V	1,000,000	± 10%	0.80 ± 0.10
C1608X7R1V105M	X7R	35V	1,000,000	± 20%	0.80 ± 0.10
C1608X7R1E103J	X7R	25V	10,000	± 5%	0.80 ± 0.10
C1608X7R1E103K	X7R	25V	10,000	± 10%	0.80 ± 0.10
C1608X7R1E103M	X7R	25V	10,000	± 20%	0.80 ± 0.10
C1608X7R1E153K	X7R	25V	15,000	± 10%	0.80 ± 0.10
C1608X7R1E153M	X7R	25V	15,000	± 20%	0.80 ± 0.10
C1608X7R1E223K	X7R	25V	22,000	± 10%	0.80 ± 0.10
C1608X7R1E223M	X7R	25V	22,000	± 20%	0.80 ± 0.10
C1608X7R1E333K	X7R	25V	33,000	± 10%	0.80 ± 0.10
C1608X7R1E333M	X7R	25V	33,000	± 20%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X7R1E473K	X7R	25V	47,000	± 10%	0.80 ± 0.10
C1608X7R1E473M	X7R	25V	47,000	± 20%	0.80 ± 0.10
C1608X7R1E683K	X7R	25V	68,000	± 10%	0.80 ± 0.10
C1608X7R1E683M	X7R	25V	68,000	± 20%	0.80 ± 0.10
C1608X7R1E104K	X7R	25V	100,000	± 10%	0.80 ± 0.10
C1608X7R1E104M	X7R	25V	100,000	± 20%	0.80 ± 0.10
C1608X7R1E154K	X7R	25V	150,000	± 10%	0.80 ± 0.10
C1608X7R1E154M	X7R	25V	150,000	± 20%	0.80 ± 0.10
C1608X7R1E224K	X7R	25V	220,000	± 10%	0.80 ± 0.10
C1608X7R1E224M	X7R	25V	220,000	± 20%	0.80 ± 0.10
C1608X7R1E334K	X7R	25V	330,000	± 10%	0.80 ± 0.10
C1608X7R1E334M	X7R	25V	330,000	± 20%	0.80 ± 0.10
C1608X7R1E474K	X7R	25V	470,000	± 10%	0.80 ± 0.10
C1608X7R1E474M	X7R	25V	470,000	± 20%	0.80 ± 0.10
C1608X7R1E684K	X7R	25V	680,000	± 10%	0.80 ± 0.10
C1608X7R1E684M	X7R	25V	680,000	± 20%	0.80 ± 0.10
C1608X7R1E105K	X7R	25V	1,000,000	± 10%	0.80 ± 0.10
C1608X7R1E105M	X7R	25V	1,000,000	± 20%	0.80 ± 0.10
01608X7R1C223K	X7R	16V	22,000	± 10%	0.80 ± 0.10
C1608X7R1C223M	X7R	16V	22,000	± 20%	0.80 ± 0.10
C1608X7R1C333K	X7R	16V	33,000	± 10%	0.80 ± 0.10
1608X7R1C333M	X7R	16V	33,000	± 20%	0.80 ± 0.10
C1608X7R1C473K	X7R	16V	47,000	± 10%	0.80 ± 0.10
1608X7R1C473M	X7R	16V	47,000	± 20%	0.80 ± 0.10
1608X7R1C683K	X7R	16V	68,000	± 10%	0.80 ± 0.10
C1608X7R1C683M	X7R	16V	68,000	± 20%	0.80 ± 0.10
C1608X7R1C104K	X7R	16V	100,000	± 10%	0.80 ± 0.10
C1608X7R1C104M	X7R	16V	100,000	± 20%	0.80 ± 0.10
C1608X7R1C154K	X7R	16V	150,000	± 10%	0.80 ± 0.10
C1608X7R1C154M	X7R	16V	150,000	± 20%	0.80 ± 0.10
C1608X7R1C224K	X7R	16V	220,000	± 10%	0.80 ± 0.10
C1608X7R1C224M	X7R	16V	220,000	± 20%	0.80 ± 0.10
C1608X7R1C334K	X7R	16V	330,000	± 10%	0.80 ± 0.10
C1608X7R1C334M	X7R	16V	330,000	± 20%	0.80 ± 0.10
C1608X7R1C474K	X7R	16V	470,000	± 10%	0.80 ± 0.10
C1608X7R1C474M	X7R	16V	470,000	± 20%	0.80 ± 0.10
C1608X7R1C684K	X7R	16V	680,000	± 10%	0.80 ± 0.10
C1608X7R1C684M	X7R	16V	680,000	± 20%	0.80 ± 0.10
C1608X7R1C105K	X7R	16V	1,000,000	± 10%	0.80 ± 0.10
C1608X7R1C105M	X7R	16V	1,000,000	± 20%	0.80 ± 0.10
C1608X7R1A224K	X7R	10V	220,000	± 10%	0.80 ± 0.10
C1608X7R1A224M	X7R	10V	220,000	± 20%	0.80 ± 0.10
C1608X7R1A334K	X7R	10V	330,000	± 10%	0.80 ± 0.10
C1608X7R1A334M	X7R	10V	330,000	± 20%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S (-55 to +105°C, ±22%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X7R1A474K	X7R	10V	470,000	± 10%	0.80 ± 0.10
C1608X7R1A474M	X7R	10V	470,000	± 20%	0.80 ± 0.10
C1608X7R1A105K	X7R	10V	1,000,000	± 10%	0.80 ± 0.10
C1608X7R1A105M	X7R	10V	1,000,000	± 20%	0.80 ± 0.10
C1608X7R1A225K	X7R	10V	2,200,000	± 10%	0.80 ± 0.10
C1608X7R1A225M	X7R	10V	2,200,000	± 20%	0.80 ± 0.10
C1608X7R0J225K	X7R	6.3V	2,200,000	± 10%	0.80 ± 0.10
C1608X7R0J225M	X7R	6.3V	2,200,000	± 20%	0.80 ± 0.10
C1608X6S1H224K	X6S	50V	220,000	± 10%	0.80 ± 0.10
C1608X6S1H224M	X6S	50V	220,000	± 20%	0.80 ± 0.10
C1608X6S1H474K	X6S	50V	470,000	± 10%	0.80 ± 0.10
C1608X6S1H474M	X6S	50V	470,000	± 20%	0.80 ± 0.10
C1608X6S1H105K	X6S	50V	1,000,000	± 10%	0.80 ± 0.10
C1608X6S1H105M	X6S	50V	1,000,000	± 20%	0.80 ± 0.10
C1608X6S1V224K	X6S	35V	220,000	± 10%	0.80 ± 0.10
C1608X6S1V224M	X6S	35V	220,000	± 20%	0.80 ± 0.10
C1608X6S1V474K	X6S	35V	470,000	± 10%	0.80 ± 0.10
C1608X6S1V474M	X6S	35V	470,000	± 20%	0.80 ± 0.10
C1608X6S1V105K	X6S	35V	1,000,000	± 10%	0.80 ± 0.10
C1608X6S1V105M	X6S	35V	1,000,000	± 20%	0.80 ± 0.10
C1608X6S1E474K	X6S	25V	470,000	± 10%	0.80 ± 0.10
C1608X6S1E474M	X6S	25V	470,000	± 20%	0.80 ± 0.10
C1608X6S1E105K	X6S	25V	1,000,000	± 10%	0.80 ± 0.10
C1608X6S1E105M	X6S	25V	1,000,000	± 20%	0.80 ± 0.10
C1608X6S1C105K	X6S	16V	1,000,000	± 10%	0.80 ± 0.10
C1608X6S1C105M	X6S	16V	1,000,000	± 20%	0.80 ± 0.10
C1608X6S1C225K	X6S	16V	2,200,000	± 10%	0.80 ± 0.10
C1608X6S1C225M	X6S	16V	2,200,000	± 20%	0.80 ± 0.10
C1608X6S1A225K/0.50	X6S	10V	2,200,000	± 10%	0.50 ± 0.05
C1608X6S1A225M/0.50	X6S	10V	2,200,000	± 20%	0.50 ± 0.05
C1608X6S1A475K	X6S	10V	4,700,000	± 10%	0.80 ± 0.10
C1608X6S1A475M	X6S	10V	4,700,000	± 20%	0.80 ± 0.10
C1608X6S0J225K	X6S	6.3V	2,200,000	± 10%	0.80 ± 0.10
C1608X6S0J225M	X6S	6.3V	2,200,000	± 20%	0.80 ± 0.10
C1608X6S0J475K	X6S	6.3V	4,700,000	± 10%	0.80 ± 0.10
C1608X6S0J475M	X6S	6.3V	4,700,000	± 20%	0.80 ± 0.10
C1608X6S0G225K/0.50	X6S	4V	2,200,000	± 10%	0.50 ± 0.05
C1608X6S0G225M/0.50	X6S	4V	2,200,000	± 20%	0.50 ± 0.05
C1608X6S0G475K/0.50	X6S	4V	4,700,000	± 10%	0.50 ± 0.05
C1608X6S0G475M/0.50	X6S	4V	4,700,000	± 20%	0.50 ± 0.05
C1608X6S0G475K/0.80	X6S	4V	4,700,000	± 10%	0.80 ± 0.10
C1608X6S0G475M/0.80	X6S	4V	4,700,000	± 20%	0.80 ± 0.10
C1608X6S0G106K	X6S	4V	10,000,000	± 10%	0.80 ± 0.10
C1608X6S0G106M	X6S	4V	10,000,000	± 20%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X5R1H104K	X5R	50V	100,000	± 10%	0.80 ± 0.10
C1608X5R1H104M	X5R	50V	100,000	± 20%	0.80 ± 0.10
C1608X5R1H154K	X5R	50V	150,000	± 10%	0.80 ± 0.10
C1608X5R1H154M	X5R	50V	150,000	± 20%	0.80 ± 0.10
C1608X5R1H224K	X5R	50V	220,000	± 10%	0.80 ± 0.10
C1608X5R1H224M	X5R	50V	220,000	± 20%	0.80 ± 0.10
C1608X5R1H334K	X5R	50V	330,000	± 10%	0.80 ± 0.10
C1608X5R1H334M	X5R	50V	330,000	± 20%	0.80 ± 0.10
C1608X5R1H474K	X5R	50V	470,000	± 10%	0.80 ± 0.10
C1608X5R1H474M	X5R	50V	470,000	± 20%	0.80 ± 0.10
C1608X5R1H684K	X5R	50V	680,000	± 10%	0.80 ± 0.10
C1608X5R1H684M	X5R	50V	680,000	± 20%	0.80 ± 0.10
C1608X5R1H105K	X5R	50V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R1H105M	X5R	50V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R1V105K	X5R	35V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R1V105M	X5R	35V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R1E154K	X5R	25V	150,000	± 10%	0.80 ± 0.10
C1608X5R1E154M	X5R	25V	150,000	± 20%	0.80 ± 0.10
C1608X5R1E224K	X5R	25V	220,000	± 10%	0.80 ± 0.10
C1608X5R1E224M	X5R	25V	220,000	± 20%	0.80 ± 0.10
C1608X5R1E334K	X5R	25V	330,000	± 10%	0.80 ± 0.10
C1608X5R1E334M	X5R	25V	330,000	± 20%	0.80 ± 0.10
C1608X5R1E474K	X5R	25V	470,000	± 10%	0.80 ± 0.10
C1608X5R1E474M	X5R	25V	470,000	± 20%	0.80 ± 0.10
C1608X5R1E105K	X5R	25V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R1E105M	X5R	25V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R1E155K	X5R	25V	1,500,000	± 10%	0.80 ± 0.10
C1608X5R1E155M	X5R	25V	1,500,000	± 20%	0.80 ± 0.10
C1608X5R1E225K	X5R	25V	2,200,000	± 10%	0.80 ± 0.10
C1608X5R1E225M	X5R	25V	2,200,000	± 20%	0.80 ± 0.10
C1608X5R1C224K	X5R	16V	220,000	± 10%	0.80 ± 0.10
C1608X5R1C224M	X5R	16V	220,000	± 20%	0.80 ± 0.10
C1608X5R1C334K	X5R	16V	330,000	± 10%	0.80 ± 0.10
C1608X5R1C334M	X5R	16V	330,000	± 20%	0.80 ± 0.10
C1608X5R1C474K	X5R	16V	470,000	± 10%	0.80 ± 0.10
C1608X5R1C474M	X5R	16V	470,000	± 20%	0.80 ± 0.10
C1608X5R1C684K	X5R	16V	680,000	± 10%	0.80 ± 0.10
C1608X5R1C684M	X5R	16V	680,000	± 20%	0.80 ± 0.10
C1608X5R1C105K	X5R	16V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R1C105M	X5R	16V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R1C225K/0.50	X5R	16V	2,200,000	± 10%	0.50 ± 0.05
C1608X5R1C225M/0.50	X5R	16V	2,200,000	± 20%	0.50 ± 0.05
C1608X5R1C225K/0.80	X5R	16V	2,200,000	± 10%	0.80 ± 0.10
C1608X5R1C225M/0.80	X5R	16V	2,200,000	± 20%	0.80 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X5R1C335K	X5R	16V	3,300,000	± 10%	0.80 ± 0.10
C1608X5R1C335M	X5R	16V	3,300,000	± 20%	0.80 ± 0.10
C1608X5R1C475K	X5R	16V	4,700,000	± 10%	0.80 ± 0.10
C1608X5R1C475M	X5R	16V	4,700,000	± 20%	0.80 ± 0.10
C1608X5R1A224K	X5R	10V	220,000	± 10%	0.80 ± 0.10
C1608X5R1A224M	X5R	10V	220,000	± 20%	0.80 ± 0.10
C1608X5R1A334K	X5R	10V	330,000	± 10%	0.80 ± 0.10
C1608X5R1A334M	X5R	10V	330,000	± 20%	0.80 ± 0.10
C1608X5R1A474K	X5R	10V	470,000	± 10%	0.80 ± 0.10
C1608X5R1A474M	X5R	10V	470,000	± 20%	0.80 ± 0.10
C1608X5R1A684K	X5R	10V	680,000	± 10%	0.80 ± 0.10
C1608X5R1A684M	X5R	10V	680,000	± 20%	0.80 ± 0.10
C1608X5R1A105K	X5R	10V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R1A105M	X5R	10V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R1A225K/0.50	X5R	10V	2,200,000	± 10%	0.50 ± 0.05
C1608X5R1A225M/0.50	X5R	10V	2,200,000	± 20%	0.50 ± 0.05
C1608X5R1A225K/0.80	X5R	10V	2,200,000	± 10%	0.80 ± 0.10
C1608X5R1A225M/0.80	X5R	10V	2,200,000	± 20%	0.80 ± 0.10
C1608X5R1A335K	X5R	10V	3,300,000	± 10%	0.80 ± 0.10
C1608X5R1A335M	X5R	10V	3,300,000	± 20%	0.80 ± 0.10
C1608X5R1A475K/0.50	X5R	10V	4,700,000	± 10%	0.50 ± 0.05
C1608X5R1A475M/0.50	X5R	10V	4,700,000	± 20%	0.50 ± 0.05
C1608X5R1A475K/0.80	X5R	10V	4,700,000	± 10%	0.80 ± 0.10
C1608X5R1A475M/0.80	X5R	10V	4,700,000	± 20%	0.80 ± 0.10
C1608X5R1A685K	X5R	10V	6,800,000	± 10%	0.80 ± 0.10
C1608X5R1A685M	X5R	10V	6,800,000	± 20%	0.80 ± 0.10
C1608X5R1A106K	X5R	10V	10,000,000	± 10%	0.80 ± 0.10
C1608X5R1A106M	X5R	10V	10,000,000	± 20%	0.80 ± 0.10
C1608X5R0J105K	X5R	6.3V	1,000,000	± 10%	0.80 ± 0.10
C1608X5R0J105M	X5R	6.3V	1,000,000	± 20%	0.80 ± 0.10
C1608X5R0J155K	X5R	6.3V	1,500,000	± 10%	0.80 ± 0.10
C1608X5R0J155M	X5R	6.3V	1,500,000	± 20%	0.80 ± 0.10
C1608X5R0J225K	X5R	6.3V	2,200,000	± 10%	0.80 ± 0.10
C1608X5R0J225M	X5R	6.3V	2,200,000	± 20%	0.80 ± 0.10
C1608X5R0J335K	X5R	6.3V	3,300,000	± 10%	0.80 ± 0.15
C1608X5R0J335M	X5R	6.3V	3,300,000	± 20%	0.80 ± 0.15
C1608X5R0J475K/0.50	X5R	6.3V	4,700,000	± 10%	0.50 ± 0.05
C1608X5R0J475M/0.50	X5R	6.3V	4,700,000	± 20%	0.50 ± 0.05
C1608X5R0J475K/0.80	X5R	6.3V	4,700,000	± 10%	0.80 ± 0.15
C1608X5R0J475M/0.80	X5R	6.3V	4,700,000	± 20%	0.80 ± 0.15
C1608X5R0J685K	X5R	6.3V	6,800,000	± 10%	0.80 ± 0.15
C1608X5R0J685M	X5R	6.3V	6,800,000	± 20%	0.80 ± 0.15
C1608X5R0J106K	X5R	6.3V	10,000,000	± 10%	0.80 ± 0.10
C1608X5R0J106M	X5R	6.3V	10,000,000	± 20%	0.80 ± 0.20

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C1608 [EIA CC0603]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

i sinperaturo onaraot		0, = 1070), 100		/0/	
TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C1608X5R0G106M	X5R	4V	10,000,000	± 20%	0.80 ± 0.20
C1608Y5V1H104Z	Y5V	50V	100,000	+80/-20%	0.80 ± 0.10
C1608Y5V1H224Z	Y5V	50V	220,000	+80/-20%	0.80 ± 0.10
C1608Y5V1H474Z	Y5V	50V	470,000	+80/-20%	0.80 ± 0.10
C1608Y5V1E104Z	Y5V	25V	100,000	+80/-20%	0.80 ± 0.10
C1608Y5V1E224Z	Y5V	25V	220,000	+80/-20%	0.80 ± 0.10
C1608Y5V1E474Z	Y5V	25V	470,000	+80/-20%	0.80 ± 0.10
C1608Y5V1E105Z	Y5V	25V	1,000,000	+80/-20%	0.80 ± 0.10
C1608Y5V1C104Z	Y5V	16V	100,000	+80/-20%	0.80 ± 0.10
C1608Y5V1C105Z	Y5V	16V	1,000,000	+80/-20%	0.80 ± 0.10
C1608Y5V1C225Z	Y5V	16V	2,200,000	+80/-20%	0.80 ± 0.10
C1608Y5V1A105Z	Y5V	10V	1,000,000	+80/-20%	0.80 ± 0.10
C1608Y5V1A225Z	Y5V	10V	2,200,000	+80/-20%	0.80 ± 0.10
C1608Y5V0J475Z	Y5V	6.3V	4,700,000	+80/-20%	0.80 ± 0.10
C1608Y5V0J106Z	Y5V	6.3V	10,000,000	+80/-20%	0.80 ± 0.15

MULTILAYER CERAMIC CHIP CAPACITORS



C2012 [EIA CC0805]

Capacitance Range Chart

Temperature Characteristics: C0G (0 ± 30ppm/^oC) Rated Voltage: 50V (1H), 25V (1E)

Oomooitemaa	0.00		C)G
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)
10	100	J: ± 5%		
100	101			
120	121			
150	151			
180	181			
220	221			
270	271			
330	331			
390	391			
470	471			
560	561			
680	681			
820	821			
1,000	102			
1,200	122			
1,500	152			
1,800	182			
2,200	222			
2,700	272			
3,300	332			
3,900	392			
4,700	472			
5,600	562			
6,800	682			
8,200	822			
10,000	103			
15,000	153			
22,000	223			
33,000	333			


• Standard capacitance is shown. Please refer to Capacitance Range Table for additional capacitance values.

Capacitance Range Chart

Temperature Characteristics: X6S (± 22%) Rated Voltage: 50V (1H), 35V (1V). 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V(0G)

Canacitanaa	Can		X6S						
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)
1,000,000	105	K: ± 10%							
2,200,000	225	M: ± 20%							
4,700,000	475								
10,000,000	106								
22,000,000	226								
47,000,000	476]							

• Standard thickness is shown. Please refer to Capacitance Range Table for additional thicknesses.



②TDK

MULTILAYER CERAMIC CHIP CAPACITORS



C2012 [EIA CC0805]

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%), X5R (± 15%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 35V (1V), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V (0G)

Canacitanaa	Con				X	ōR		
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)
1,000,000	105	K: ± 10%						
1,500,000	155	M: ± 20%						
2,200,000	225							
3,300,000	335							
4,700,000	475							
6,800,000	685							
10,000,000	106							
15,000,000	156							
22,000,000	226							
33,000,000	336							
47,000,000	476							

Consoltance	Con		X7R					
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
1,000	102	K: ± 10%						
2,200	222	M: ± 20%						
4,700	472							
10,000	103							
22,000	223							
47,000	473							
100,000	104							
150,000	154							
220,000	224							
330,000	334							
470,000	474							
680,000	684							
1,000,000	105							
1,500,000	155							
2,200,000	225							
3,300,000	335							
4,700,000	475							
10,000,000	106							

Conceltance	Con		Y5V				
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
100,000	104	Z: +80/-20%					
470,000	474	,					
1,000,000	105						
2,200,000	225						
4,700,000	475						
10,000,000	106]					
22,000,000	226						

Standard Thickness



• Standard thickness is shown. Please refer to Capacitance Range Table for additional thicknesses.

⇔TDK

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012C0G1H100D	COG	50V	10	± 0.50pF	0.60 ± 0.10
C2012C0G1H101J	COG	50V	100	± 5%	0.60 ± 0.10
C2012C0G1H121J	COG	50V	120	± 5%	0.60 ± 0.10
C2012C0G1H151J	COG	50V	150	± 5%	0.60 ± 0.10
C2012C0G1H181J	COG	50V	180	± 5%	0.60 ± 0.10
C2012C0G1H221J	COG	50V	220	± 5%	0.60 ± 0.10
C2012C0G1H271J	COG	50V	270	± 5%	0.60 ± 0.10
C2012C0G1H331J	COG	50V	330	± 5%	0.60 ± 0.10
C2012C0G1H391J	COG	50V	390	± 5%	0.60 ± 0.10
C2012C0G1H471J	COG	50V	470	± 5%	0.60 ± 0.10
C2012C0G1H561J	COG	50V	560	± 5%	0.60 ± 0.10
C2012C0G1H681J	COG	50V	680	± 5%	0.60 ± 0.10
C2012C0G1H821J	C0G	50V	820	± 5%	0.60 ± 0.10
C2012C0G1H102J	COG	50V	1,000	± 5%	0.60 ± 0.10
C2012C0G1H122J	COG	50V	1,200	± 5%	0.60 ± 0.10
C2012C0G1H152J	COG	50V	1,500	± 5%	0.60 ± 0.10
C2012C0G1H182J/0.60	COG	50V	1,800	± 5%	0.60 ± 0.10
C2012C0G1H182J/0.85	COG	50V	1,800	± 5%	0.85 ± 0.10
C2012C0G1H222J/0.60	COG	50V	2,200	± 5%	0.60 ± 0.10
C2012C0G1H222J/0.85	COG	50V	2,200	± 5%	0.85 ± 0.10
C2012C0G1H272J/0.60	COG	50V	2,700	± 5%	0.60 ± 0.10
C2012C0G1H272J/1.25	COG	50V	2,700	± 5%	1.25 ± 0.20
C2012C0G1H332J/0.60	COG	50V	3,300	± 5%	0.60 ± 0.10
C2012C0G1H332J/1.25	COG	50V	3,300	± 5%	1.25 ± 0.20
C2012C0G1H392J/0.60	COG	50V	3,900	± 5%	0.60 ± 0.10
C2012C0G1H392J/0.85	COG	50V	3,900	± 5%	0.85 ± 0.10
C2012C0G1H472J/0.60	COG	50V	4,700	± 5%	0.60 ± 0.10
C2012C0G1H472J/0.85	COG	50V	4,700	± 5%	0.85 ± 0.10
C2012C0G1H562J/0.60	COG	50V	5,600	± 5%	0.60 ± 0.10
C2012C0G1H562J/0.85	COG	50V	5,600	± 5%	0.85 ± 0.10
C2012C0G1H682J/0.60	COG	50V	6,800	± 5%	0.60 ± 0.10
C2012C0G1H682J/1.25	COG	50V	6,800	± 5%	1.25 ± 0.20
C2012C0G1H822J/0.60	COG	50V	8,200	± 5%	0.60 ± 0.10
C2012C0G1H822J/1.25	COG	50V	8,200	± 5%	1.25 ± 0.20
C2012C0G1H103J/0.60	COG	50V	10,000	± 5%	0.60 ± 0.10
C2012C0G1H103J/1.25	COG	50V	10,000	± 5%	1.25 ± 0.20
C2012C0G1H153J	COG	50V	15,000	± 5%	0.85 ± 0.10
C2012C0G1H223J	COG	50V	22,000	± 5%	1.25 ± 0.20
C2012C0G1H333J	COG	50V	33,000	± 5%	1.25 ± 0.20
C2012C0G1E392J	COG	25V	3,900	± 5%	0.60 ± 0.10
C2012C0G1E472J	COG	25V	4,700	± 5%	0.60 ± 0.10
C2012C0G1E562J	COG	25V	5,600	± 5%	0.60 ± 0.10
C2012C0G1E682J	COG	25V	6,800	± 5%	0.60 ± 0.10
C2012C0G1E822J	COG	25V	8,200	± 5%	0.60 ± 0.10



Capacitance Range Table

C2012 [EIA CC0805]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012C0G1E103J	COG	25V	10,000	± 5%	0.60 ± 0.10
C2012C0G1E153J	COG	25V	15,000	± 5%	0.85 ± 0.10
C2012C0G1E223J	COG	25V	22,000	± 5%	1.25 ± 0.20
C2012C0G1E333J	COG	25V	33,000	± 5%	1.25 ± 0.20

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X7R1H102K	X7R	50V	1,000	± 10%	0.60 ± 0.10
C2012X7R1H102M	X7R	50V	1,000	± 20%	0.60 ± 0.10
C2012X7R1H222K	X7R	50V	2,200	± 10%	0.60 ± 0.10
C2012X7R1H222M	X7R	50V	2,200	± 20%	0.60 ± 0.10
C2012X7R1H472K	X7R	50V	4,700	± 10%	0.60 ± 0.10
C2012X7R1H472M	X7R	50V	4,700	± 20%	0.60 ± 0.10
C2012X7R1H103K	X7R	50V	10,000	± 10%	0.60 ± 0.10
C2012X7R1H103M	X7R	50V	10,000	± 20%	0.60 ± 0.10
C2012X7R1H223K/0.60	X7R	50V	22,000	± 10%	0.60 ± 0.10
C2012X7R1H223M/0.60	X7R	50V	22,000	± 20%	0.60 ± 0.10
C2012X7R1H473K/1.25	X7R	50V	47,000	± 10%	1.25 ± 0.20
C2012X7R1H473M/1.25	X7R	50V	47,000	± 20%	1.25 ± 0.20
C2012X7R1H104K/0.85	X7R	50V	100,000	± 10%	0.85 ± 0.10
C2012X7R1H104M/0.85	X7R	50V	100,000	± 20%	0.85 ± 0.10
C2012X7R1H104K/1.25	X7R	50V	100,000	± 10%	1.25 ± 0.20
C2012X7R1H104M/1.25	X7R	50V	100,000	± 20%	1.25 ± 0.20
C2012X7R1H154K	X7R	50V	150,000	± 10%	1.25 ± 0.20
C2012X7R1H154M	X7R	50V	150,000	± 20%	1.25 ± 0.20
C2012X7R1H224K	X7R	50V	220,000	± 10%	1.25 ± 0.20
C2012X7R1H224M	X7R	50V	220,000	± 20%	1.25 ± 0.20
C2012X7R1H334K	X7R	50V	330,000	± 10%	1.25 ± 0.20
C2012X7R1H334M	X7R	50V	330,000	± 20%	1.25 ± 0.20
C2012X7R1H474K	X7R	50V	470,000	± 10%	1.25 ± 0.20
C2012X7R1H474M	X7R	50V	470,000	± 20%	1.25 ± 0.20
C2012X7R1H684K	X7R	50V	680,000	± 10%	1.25 ± 0.20
C2012X7R1H684M	X7R	50V	680,000	± 20%	1.25 ± 0.20
C2012X7R1H105K	X7R	50V	1,000,000	± 10%	1.25 ± 0.20
C2012X7R1H105M	X7R	50V	1,000,000	± 20%	1.25 ± 0.20
C2012X7R1H155K	X7R	50V	1,500,000	± 10%	1.25 ± 0.20
C2012X7R1H155M	X7R	50V	1,500,000	± 20%	1.25 ± 0.20
C2012X7R1H225K	X7R	50V	2,200,000	± 10%	1.25 ± 0.20
C2012X7R1H225M	X7R	50V	2,200,000	± 20%	1.25 ± 0.20
C2012X7R1V105K	X7R	35V	1,000,000	± 10%	1.25 ± 0.20
C2012X7R1V105M	X7R	35V	1,000,000	± 20%	1.25 ± 0.20
C2012X7R1V225K	X7R	35V	2,200,000	± 10%	1.25 ± 0.20
C2012X7R1V225M	X7R	35V	2,200,000	± 20%	1.25 ± 0.20

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X7R1V335K	X7R	35V	3,300,000	± 10%	1.25 ± 0.20
C2012X7R1V335M	X7R	35V	3,300,000	± 20%	1.25 ± 0.20
C2012X7R1V475K	X7R	35V	4,700,000	± 10%	1.25 ± 0.20
C2012X7R1V475M	X7R	35V	4,700,000	± 20%	1.25 ± 0.20
C2012X7R1E104K/0.85	X7R	25V	100,000	± 10%	0.85 ± 0.10
C2012X7R1E104M/0.85	X7R	25V	100,000	± 20%	0.85 ± 0.10
C2012X7R1E104K/1.25	X7R	25V	100,000	± 10%	1.25 ± 0.20
C2012X7R1E104M/1.25	X7R	25V	100,000	± 20%	1.25 ± 0.20
C2012X7R1E224K	X7R	25V	220,000	± 10%	1.25 ± 0.20
C2012X7R1E224M	X7R	25V	220,000	± 20%	1.25 ± 0.20
C2012X7R1E334K	X7R	25V	330,000	± 10%	1.25 ± 0.20
C2012X7R1E334M	X7R	25V	330,000	± 20%	1.25 ± 0.20
C2012X7R1E474K	X7R	25V	470,000	± 10%	1.25 ± 0.20
C2012X7R1E474M	X7R	25V	470,000	± 20%	1.25 ± 0.20
C2012X7R1E684K	X7R	25V	680,000	± 10%	1.25 ± 0.20
C2012X7R1E684M	X7R	25V	680,000	± 20%	1.25 ± 0.20
C2012X7R1E105K	X7R	25V	1,000,000	± 10%	1.25 ± 0.20
C2012X7R1E105M	X7R	25V	1,000,000	± 20%	1.25 ± 0.20
C2012X7R1E155K	X7R	25V	1,500,000	± 10%	1.25 ± 0.20
C2012X7R1E155M	X7R	25V	1,500,000	± 20%	1.25 ± 0.20
C2012X7R1E225K	X7R	25V	2,200,000	± 10%	1.25 ± 0.20
C2012X7R1E225M	X7R	25V	2,200,000	± 20%	1.25 ± 0.20
C2012X7R1E335K	X7R	25V	3,300,000	± 10%	1.25 ± 0.20
C2012X7R1E335M	X7R	25V	3,300,000	± 20%	1.25 ± 0.20
C2012X7R1E475K	X7R	25V	4,700,000	± 10%	1.25 ± 0.20
C2012X7R1E475M	X7R	25V	4,700,000	± 20%	1.25 ± 0.20
C2012X7R1C224K	X7R	16V	220,000	± 10%	1.25 ± 0.20
C2012X7R1C224M	X7R	16V	220,000	± 20%	1.25 ± 0.20
C2012X7R1C334K/1.25	X7R	16V	330,000	± 10%	1.25 ± 0.20
C2012X7R1C334M/1.25	X7R	16V	330,000	± 20%	1.25 ± 0.20
C2012X7R1C474K	X7R	16V	470,000	± 10%	1.25 ± 0.20
C2012X7R1C474M	X7R	16V	470,000	± 20%	1.25 ± 0.20
C2012X7R1C684K	X7R	16V	680,000	± 10%	1.25 ± 0.20
C2012X7R1C684M	X7R	16V	680,000	± 20%	1.25 ± 0.20
C2012X7R1C105K/0.85	X7R	16V	1,000,000	± 10%	0.85 ± 0.10
C2012X7R1C105M/0.85	X7R	16V	1,000,000	± 20%	0.85 ± 0.10
C2012X7R1C105K/1.25	X7R	16V	1,000,000	± 10%	1.25 ± 0.20
C2012X7R1C105M/1.25	X7R	16V	1,000,000	± 20%	1.25 ± 0.20
C2012X7R1C155K	X7R	16V	1,500,000	± 10%	1.25 ± 0.20
C2012X7R1C155M	X7R	16V	1,500,000	± 20%	1.25 ± 0.20
C2012X7R1C225K	X7R	16V	2,200,000	± 10%	1.25 ± 0.20
C2012X7R1C225M	X7R	16V	2,200,000	± 20%	1.25 ± 0.20
C2012X7R1C335K	X7R	16V	3,300,000	± 10%	1.25 ± 0.20
C2012X7R1C335M	X7R	16V	3,300,000	± 20%	1.25 ± 0.20

⇔TDK

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S(-55 to 105°C, ±22%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X7R1C475K	X7R	16V	4,700,000	± 10%	1.25 ± 0.20
C2012X7R1C475M	X7R	16V	4,700,000	± 20%	1.25 ± 0.20
C2012X7R1A105K	X7R	10V	1,000,000	± 10%	1.25 ± 0.20
C2012X7R1A105M	X7R	10V	1,000,000	± 20%	1.25 ± 0.20
C2012X7R1A155K	X7R	10V	1,500,000	± 10%	1.25 ± 0.20
C2012X7R1A155M	X7R	10V	1,500,000	± 20%	1.25 ± 0.20
C2012X7R1A225K	X7R	10V	2,200,000	± 10%	1.25 ± 0.20
C2012X7R1A225M	X7R	10V	2,200,000	± 20%	1.25 ± 0.20
C2012X7R1A335K	X7R	10V	3,300,000	± 10%	1.25 ± 0.20
C2012X7R1A335M	X7R	10V	3,300,000	± 20%	1.25 ± 0.20
C2012X7R1A475K	X7R	10V	4,700,000	± 10%	1.25 ± 0.20
C2012X7R1A475M	X7R	10V	4,700,000	± 20%	1.25 ± 0.20
C2012X7R1A106K	X7R	10V	10,000,000	± 10%	1.25 ± 0.20
C2012X7R1A106M	X7R	10V	10,000,000	± 20%	1.25 ± 0.20
C2012X7R0J106K	X7R	6.3V	10,000,000	± 10%	1.25 ± 0.20
C2012X7R0J106M	X7R	6.3V	10,000,000	± 20%	1.25 ± 0.20
C2012X6S1H105K	X6S	50V	1,000,000	± 10%	1.25 ± 0.20
C2012X6S1H105M	X6S	50V	1,000,000	± 20%	1.25 ± 0.20
C2012X6S1H225K	X6S	50V	2,200,000	± 10%	1.25 ± 0.20
C2012X6S1H225M	X6S	50V	2,200,000	± 20%	1.25 ± 0.20
C2012X6S1H475K	X6S	50V	4,700,000	± 10%	1.25 ± 0.20
C2012X6S1H475M	X6S	50V	4,700,000	± 20%	1.25 ± 0.20
C2012X6S1V475K	X6S	35V	4,700,000	± 10%	1.25 ± 0.20
C2012X6S1V475M	X6S	35V	4,700,000	± 20%	1.25 ± 0.20
C2012X6S1E225K	X6S	25V	2,200,000	± 10%	1.25 ± 0.20
C2012X6S1E225M	X6S	25V	2,200,000	± 20%	1.25 ± 0.20
C2012X6S1E475K	X6S	25V	4,700,000	± 10%	1.25 ± 0.20
C2012X6S1E475M	X6S	25V	4,700,000	± 20%	1.25 ± 0.20
C2012X6S1C225K	X6S	16V	2,200,000	± 10%	0.90 +0.05,-0.10
C2012X6S1C225M	X6S	16V	2,200,000	± 20%	0.90 +0.05,-0.10
C2012X6S1C475K	X6S	16V	4,700,000	± 10%	1.25 ± 0.20
C2012X6S1C475M	X6S	16V	4,700,000	± 20%	1.25 ± 0.20
C2012X6S1C106K	X6S	16V	10,000,000	± 10%	1.25 ± 0.20
C2012X6S1C106M	X6S	16V	10,000,000	± 20%	1.25 ± 0.20
C2012X6S1A106K/0.85	X6S	10V	10,000,000	± 10%	0.85 ± 0.10
C2012X6S1A106M/0.85	X6S	10V	10,000,000	± 20%	0.85 ± 0.10
C2012X6S1A226K	X6S	10V	22,000,000	± 10%	1.25 ± 0.20
C2012X6S1A226M	X6S	10V	22,000,000	± 20%	1.25 ± 0.20
C2012X6S0J106K	X6S	6.3V	10,000,000	± 10%	0.85 ± 0.10
C2012X6S0J106M	X6S	6.3V	10,000,000	± 20%	0.85 ± 0.10
C2012X6S0J226K	X6S	6.3V	22,000,000	± 10%	1.25 ± 0.20
C2012X6S0J226M	X6S	6.3V	22,000,000	± 20%	1.25 ± 0.20
C2012X6S0G226M	X6S	4V	22,000,000	± 20%	0.85 ± 0.10
C2012X6S0G476M	X6S	4V	47,000,000	± 20%	1.25 ± 0.20

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X5R1H105K	X5R	50V	1,000,000	± 10%	1.25 ± 0.20
C2012X5R1H105M	X5R	50V	1,000,000	± 20%	1.25 ± 0.20
C2012X5R1H155K	X5R	50V	1,500,000	± 10%	1.25 ± 0.20
C2012X5R1H155M	X5R	50V	1,500,000	± 20%	1.25 ± 0.20
C2012X5R1H225K	X5R	50V	2,200,000	± 10%	1.25 ± 0.20
C2012X5R1H225M	X5R	50V	2,200,000	± 20%	1.25 ± 0.20
C2012X5R1H335K	X5R	50V	3,300,000	± 10%	1.25 ± 0.20
C2012X5R1H335M	X5R	50V	3,300,000	± 20%	1.25 ± 0.20
C2012X5R1H475K	X5R	50V	4,700,000	± 10%	1.25 ± 0.20
C2012X5R1H475M	X5R	50V	4,700,000	± 20%	1.25 ± 0.20
C2012X5R1E105K/0.85	X5R	25V	1,000,000	± 10%	0.85 ± 0.10
C2012X5R1E105M/0.85	X5R	25V	1,000,000	± 20%	0.85 ± 0.10
C2012X5R1E105K/1.25	X5R	25V	1,000,000	± 10%	1.25 ± 0.20
C2012X5R1E105M/1.25	X5R	25V	1,000,000	± 20%	1.25 ± 0.20
C2012X5R1E155K	X5R	25V	1,500,000	± 10%	1.25 ± 0.20
C2012X5R1E155M	X5R	25V	1,500,000	± 20%	1.25 ± 0.20
C2012X5R1E225K	X5R	25V	2,200,000	± 10%	1.25 ± 0.20
C2012X5R1E225M	X5R	25V	2,200,000	± 20%	1.25 ± 0.20
C2012X5R1E475K	X5R	25V	4,700,000	± 10%	1.25 ± 0.20
C2012X5R1E475M	X5R	25V	4,700,000	± 20%	1.25 ± 0.20
C2012X5R1E685K	X5R	25V	6,800,000	± 10%	1.25 ± 0.20
C2012X5R1E685M	X5R	25V	6,800,000	± 20%	1.25 ± 0.20
C2012X5R1E106K	X5R	25V	10,000,000	± 10%	1.25 ± 0.20
C2012X5R1E106M	X5R	25V	10,000,000	± 20%	1.25 ± 0.20
C2012X5R1C105K/0.85	X5R	16V	1,000,000	± 10%	0.85 ± 0.10
C2012X5R1C105M/0.85	X5R	16V	1,000,000	± 20%	0.85 ± 0.10
C2012X5R1C105K/1.25	X5R	16V	1,000,000	± 10%	1.25 ± 0.20
C2012X5R1C105M/1.25	X5R	16V	1,000,000	± 20%	1.25 ± 0.20
C2012X5R1C225K/0.85	X5R	16V	2,200,000	± 10%	0.85 ± 0.10
C2012X5R1C225M/0.85	X5R	16V	2,200,000	± 20%	0.85 ± 0.10
C2012X5R1C225K/1.25	X5R	16V	2,200,000	± 10%	1.25 ± 0.20
C2012X5R1C225M/1.25	X5R	16V	2,200,000	± 20%	1.25 ± 0.20
C2012X5R1C475K/1.25	X5R	16V	4,700,000	± 10%	1.25 ± 0.20
C2012X5R1C475M/1.25	X5R	16V	4,700,000	± 20%	1.25 ± 0.20
C2012X5R1C685K	X5R	16V	6,800,000	± 10%	1.25 ± 0.20
C2012X5R1C685M	X5R	16V	6,800,000	± 20%	1.25 ± 0.20
C2012X5R1C106K/0.85	X5R	16V	10,000,000	± 10%	0.85 ± 0.10
C2012X5R1C106M/0.85	X5R	16V	10,000,000	± 20%	0.85 ± 0.10
C2012X5R1C106K/1.25	X5R	16V	10,000,000	± 10%	1.25 ± 0.20
C2012X5R1C106M/1.25	X5R	16V	10,000,000	± 20%	1.25 ± 0.20
C2012X5R1C226K	X5R	16V	22,000,000	± 10%	1.25 ± 0.20
C2012X5R1C226M	X5R	16V	22,000,000	± 20%	1.25 ± 0.20
C2012X5R1A105K/0.85	X5R	10V	1,000,000	± 10%	0.85 ± 0.10
C2012X5R1A105M/0.85	X5R	10V	1,000,000	± 20%	0.85 ± 0.10

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X5R1A105K/1.25	X5R	10V	1,000,000	± 10%	1.25 ± 0.20
C2012X5R1A105M/1.25	X5R	10V	1,000,000	± 20%	1.25 ± 0.20
C2012X5R1A225K/0.85	X5R	10V	2,200,000	± 10%	0.85 ± 0.10
C2012X5R1A225M/0.85	X5R	10V	2,200,000	± 20%	0.85 ± 0.10
C2012X5R1A225K/1.25	X5R	10V	2,200,000	± 10%	1.25 ± 0.20
C2012X5R1A225M/1.25	X5R	10V	2,200,000	± 20%	1.25 ± 0.20
C2012X5R1A335K	X5R	10V	3,300,000	± 10%	1.25 ± 0.20
C2012X5R1A335M	X5R	10V	3,300,000	± 20%	1.25 ± 0.20
C2012X5R1A475K/0.85	X5R	10V	4,700,000	± 10%	0.85 ± 0.10
C2012X5R1A475M/0.85	X5R	10V	4,700,000	± 20%	0.85 ± 0.10
C2012X5R1A475K/1.25	X5R	10V	4,700,000	± 10%	1.25 ± 0.20
C2012X5R1A475M/1.25	X5R	10V	4,700,000	± 20%	1.25 ± 0.20
C2012X5R1A106K/0.85	X5R	10V	10,000,000	± 10%	0.85 ± 0.10
C2012X5R1A106M/0.85	X5R	10V	10,000,000	± 20%	0.85 ± 0.10
C2012X5R1A106K/1.25	X5R	10V	10,000,000	± 10%	1.25 ± 0.20
C2012X5R1A106M/1.25	X5R	10V	10,000,000	± 20%	1.25 ± 0.20
C2012X5R1A156M	X5R	10V	15,000,000	± 20%	1.25 ± 0.20
C2012X5R1A226M/0.85	X5R	10V	22,000,000	± 20%	0.85 ± 0.10
C2012X5R1A226K/1.25	X5R	10V	22,000,000	± 10%	1.25 ± 0.20
C2012X5R1A226M/1.25	X5R	10V	22,000,000	± 20%	1.25 ± 0.20
C2012X5R0J225K/0.85	X5R	6.3V	2,200,000	± 10%	0.85 ± 0.10
C2012X5R0J225M/0.85	X5R	6.3V	2,200,000	± 20%	0.85 ± 0.10
C2012X5R0J225K/1.25	X5R	6.3V	2,200,000	± 10%	1.25 ± 0.20
C2012X5R0J225M/1.25	X5R	6.3V	2,200,000	± 20%	1.25 ± 0.20
C2012X5R0J335K/1.25	X5R	6.3V	3,300,000	± 10%	1.25 ± 0.20
C2012X5R0J335M/1.25	X5R	6.3V	3,300,000	± 20%	1.25 ± 0.20
C2012X5R0J475K/0.85	X5R	6.3V	4,700,000	± 10%	0.85 ± 0.10
C2012X5R0J475M/0.85	X5R	6.3V	4,700,000	± 20%	0.85 ± 0.10
C2012X5R0J475K/1.25	X5R	6.3V	4,700,000	± 10%	1.25 ± 0.20
C2012X5R0J475M/1.25	X5R	6.3V	4,700,000	± 20%	1.25 ± 0.20
C2012X5R0J685K/1.25	X5R	6.3V	6,800,000	± 10%	1.25 ± 0.20
C2012X5R0J685M/1.25	X5R	6.3V	6,800,000	± 20%	1.25 ± 0.20
C2012X5R0J106K/0.85	X5R	6.3V	10,000,000	± 10%	0.85 ± 0.10
C2012X5R0J106M/0.85	X5R	6.3V	10,000,000	± 20%	0.85 ± 0.10
C2012X5R0J106K/1.25	X5R	6.3V	10,000,000	± 10%	1.25 ± 0.20
C2012X5R0J106M/1.25	X5R	6.3V	10,000,000	± 20%	1.25 ± 0.20
C2012X5R0J156M/0.85	X5R	6.3V	15,000,000	± 20%	0.85 ± 0.10
C2012X5R0J156M/1.25	X5R	6.3V	15,000,000	± 20%	1.25 ± 0.20
C2012X5R0J226M/0.85	X5R	6.3V	22,000,000	± 20%	0.85 ± 0.10
C2012X5R0J226K/1.25	X5R	6.3V	22,000,000	± 10%	1.25 ± 0.20
C2012X5R0J226M/1.25	X5R	6.3V	22,000,000	± 20%	1.25 ± 0.20
C2012X5R0J336M	X5R	6.3V	33,000,000	± 20%	1.25 ± 0.20

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C2012 [EIA CC0805]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C2012X5R0J476M	X5R	6.3V	47,000,000	± 20%	1.25 ± 0.20
C2012X5R0G476M	X5R	4V	47,000,000	± 20%	1.25 ± 0.20
C2012Y5V1H104Z/0.60	Y5V	50V	100,000	+80/-20%	0.60 ± 0.10
C2012Y5V1H104Z/0.85	Y5V	50V	100,000	+80/-20%	0.85 ± 0.10
C2012Y5V1H474Z/0.85	Y5V	50V	470,000	+80/-20%	0.85 ± 0.10
C2012Y5V1H105Z/0.85	Y5V	50V	1,000,000	+80/-20%	0.85 ± 0.10
C2012Y5V1H105Z/1.25	Y5V	50V	1,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V1H225Z	Y5V	50V	2,200,000	+80/-20%	1.25 ± 0.20
C2012Y5V1E105Z/0.85	Y5V	25V	1,000,000	+80/-20%	0.85 ± 0.10
C2012Y5V1E105Z/1.25	Y5V	25V	1,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V1E225Z	Y5V	25V	2,200,000	+80/-20%	1.25 ± 0.20
C2012Y5V1E475Z	Y5V	25V	4,700,000	+80/-20%	1.25 ± 0.20
C2012Y5V1C105Z/0.85	Y5V	16V	1,000,000	+80/-20%	0.85 ± 0.10
C2012Y5V1C105Z/1.25	Y5V	16V	1,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V1C225Z/0.85	Y5V	16V	2,200,000	+80/-20%	0.85 ± 0.10
C2012Y5V1C225Z/1.25	Y5V	16V	2,200,000	+80/-20%	1.25 ± 0.20
C2012Y5V1C475Z/0.85	Y5V	16V	4,700,000	+80/-20%	0.85 ± 0.10
C2012Y5V1C475Z/1.25	Y5V	16V	4,700,000	+80/-20%	1.25 ± 0.20
C2012Y5V1C106Z	Y5V	16V	10,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V1A475Z/0.85	Y5V	10V	4,700,000	+80/-20%	0.85 ± 0.10
C2012Y5V1A475Z/1.25	Y5V	10V	4,700,000	+80/-20%	1.25 ± 0.20
C2012Y5V1A106Z	Y5V	10V	10,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V0J106Z	Y5V	6.3V	10,000,000	+80/-20%	1.25 ± 0.20
C2012Y5V0J226Z	Y5V	6.3V	22,000,000	+80/-20%	1.25 ± 0.20

MULTILAYER CERAMIC CHIP CAPACITORS



C3216 [EIA CC1206]

Capacitance Range Chart

Temperature Characteristics: COG (0 ± 30ppm/°C) Rated Voltage: 50V (1H), 25V (1E), 10V (1A)

Consoitance	Can		C)G	SL
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1A (10V)
3,900	392	J: ± 5%			
4,700	472				
5,600	562				
6,800	682				
8,200	822				
10,000	103				
15,000	153				
22,000	223				
33,000	333				
47,000	473				
68,000	683				
100,000	104				
220,000	224				

Capacitance Range Chart

Temperature Characteristics: X7R (±15%), X6S (±22%), X5R (±15%), Y5V (+22/-82) Rated Voltage: 50V (1H), 35V (1V). 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V(0G)

Canacitanaa	Con			X5R						X6S	
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	0G (4V)	1A (10V)	0J (6.3V)	0G (4V)
1,000,000	105	K: ± 10%									
2,200,000	225	M: ± 20%									
3,300,000	335										
4,700,000	475										
6,800,000	685										
10,000,000	106										
15,000,000	156										
22,000,000	226										
33,000,000	336										
47,000,000	476										
100,000,000	107										

Osnasitanas	0.00				X7R					Y5V		
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1V (35V)	1E (25V)	1C (16V)	1A (10V)	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
100,000	104	K: ± 10%										
220,000	224	M: ± 20%										
330,000	334	Z: +80/-20%										
470,000	474											
680,000	684											
1,000,000	105											
1,500,000	155											
2,200,000	225											
3,300,000	335											
4,700,000	475											
6,800,000	685											
10,000,000	106											
22,000,000	226											
47,000,000	476											

Standard Thickness

0.60 mm 0.85 mm 1.15 mm 1.30 mm 1.60 mm

• Standard capacitance and thickness is shown. Please refer to Capacitance Range Table for additional capacitance values and thicknesses.

⇔TDK

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C3216 [EIA CC1206]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C), SL (-25 to +85°C, +350/-1000 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3216C0G1H392J	C0G	50V	3,900	± 5%	0.60 ± 0.10
C3216C0G1H472J/0.60	COG	50V	4,700	± 5%	0.60 ± 0.10
C3216C0G1H472J/0.85	COG	50V	4,700	± 5%	0.85 ± 0.10
C3216C0G1H562J/0.60	COG	50V	5,600	± 5%	0.60 ± 0.10
C3216C0G1H562J/0.85	COG	50V	5,600	± 5%	0.85 ± 0.10
C3216C0G1H682J/0.60	COG	50V	6,800	± 5%	0.60 ± 0.10
C3216C0G1H822J/0.60	COG	50V	8,200	± 5%	0.60 ± 0.10
C3216C0G1H822J/0.85	COG	50V	8,200	± 5%	0.85 ± 0.10
C3216C0G1H822J/1.15	C0G	50V	8,200	± 5%	1.15 ± 0.10
C3216C0G1H103J/0.60	C0G	50V	10,000	± 5%	0.60 ± 0.10
C3216C0G1H103J/1.15	C0G	50V	10,000	± 5%	1.15 ± 0.10
C3216C0G1H153J/0.60	COG	50V	15,000	± 5%	0.60 ± 0.10
C3216C0G1H153J/1.15	C0G	50V	15,000	± 5%	1.15 ± 0.10
C3216C0G1H223J/0.60	COG	50V	22,000	± 5%	0.60 ± 0.10
C3216C0G1H223J/1.15	COG	50V	22,000	± 5%	1.15 ± 0.10
C3216C0G1H333J/0.85	COG	50V	33,000	± 5%	0.85 ± 0.10
C3216C0G1H333J/1.60	C0G	50V	33,000	± 5%	1.60 ± 0.30
C3216C0G1H473J	COG	50V	47,000	± 5%	1.15 ± 0.10
C3216C0G1H683J	COG	50V	68,000	± 5%	1.60 ± 0.30
C3216C0G1H104J	COG	50V	100,000	± 5%	1.60 ± 0.30
C3216C0G1E822J	COG	25V	8,200	± 5%	0.60 ± 0.20
C3216C0G1E103J	COG	25V	10,000	± 5%	0.60 ± 0.20
C3216C0G1E153J	C0G	25V	15,000	± 5%	0.60 ± 0.20
C3216C0G1E223J	C0G	25V	22,000	± 5%	0.60 ± 0.10
C3216C0G1E333J	COG	25V	33,000	± 5%	0.85 ± 0.10
C3216C0G1E473J	C0G	25V	47,000	± 5%	1.15 ± 0.10
C3216C0G1E683J	C0G	25V	68,000	± 5%	1.60 ± 0.30
C3216C0G1E104J	C0G	25V	100,000	± 5%	1.60 ± 0.30
C3216SL1A224J	SL	10V	220,000	± 5%	1.60 ± 0.30

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3216X7R1H104K	X7R	50V	100,000	± 10%	0.85 ± 0.10
C3216X7R1H104M	X7R	50V	100,000	± 20%	0.85 ± 0.10
C3216X7R1H224K	X7R	50V	220,000	± 10%	1.15 ± 0.10
C3216X7R1H224M	X7R	50V	220,000	± 20%	1.15 ± 0.10
C3216X7R1H334K	X7R	50V	330,000	± 10%	1.60 ± 0.30
C3216X7R1H334M	X7R	50V	330,000	± 20%	1.60 ± 0.30
C3216X7R1H474K	X7R	50V	470,000	± 10%	1.60 ± 0.30
C3216X7R1H474M	X7R	50V	470,000	± 20%	1.60 ± 0.30
C3216X7R1H684K	X7R	50V	680,000	± 10%	1.60 ± 0.30
C3216X7R1H684M	X7R	50V	680,000	± 20%	1.60 ± 0.30
C3216X7R1H105K	X7R	50V	1,000,000	± 10%	1.60 ± 0.30

```
TDK MLCC US Catalog
```

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C3216 [EIA CC1206]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3216X7R1H105M	X7R	50V	1,000,000	± 20%	1.60 ± 0.30
C3216X7R1H155K	X7R	50V	1,500,000	± 10%	1.60 ± 0.30
C3216X7R1H155M	X7R	50V	1,500,000	± 20%	1.60 ± 0.30
C3216X7R1H225K	X7R	50V	2,200,000	± 10%	1.60 ± 0.30
C3216X7R1H225M	X7R	50V	2,200,000	± 20%	1.60 ± 0.30
C3216X7R1H335K	X7R	50V	3,300,000	± 10%	1.60 ± 0.30
C3216X7R1H335M	X7R	50V	3,300,000	± 20%	1.60 ± 0.30
C3216X7R1V335K	X7R	35V	3,300,000	± 10%	1.60 ± 0.30
C3216X7R1V475K	X7R	35V	4,700,000	± 10%	1.60 ± 0.30
C3216X7R1E224K	X7R	25V	220,000	± 10%	1.15 ± 0.10
C3216X7R1E224M	X7R	25V	220,000	± 20%	1.15 ± 0.10
C3216X7R1E334K	X7R	25V	330,000	± 10%	1.15 ± 0.10
C3216X7R1E334M	X7R	25V	330,000	± 20%	1.15 ± 0.10
C3216X7R1E474K/0.85	X7R	25V	470,000	± 10%	0.85 ± 0.10
C3216X7R1E474M/0.85	X7R	25V	470,000	± 20%	0.85 ± 0.10
C3216X7R1E684K/0.85	X7R	25V	680,000	± 10%	0.85 ± 0.10
C3216X7R1E684M/0.85	X7R	25V	680,000	± 20%	0.85 ± 0.10
C3216X7R1E105K/0.85	X7R	25V	1,000,000	± 10%	0.85 ± 0.10
C3216X7R1E105M/0.85	X7R	25V	1,000,000	± 20%	0.85 ± 0.10
C3216X7R1E105K/1.60	X7R	25V	1,000,000	± 10%	1.60 ± 0.30
C3216X7R1E105M/1.60	X7R	25V	1,000,000	± 20%	1.60 ± 0.30
C3216X7R1E155K	X7R	25V	1,500,000	± 10%	1.60 ± 0.30
C3216X7R1E155M	X7R	25V	1,500,000	± 20%	1.60 ± 0.30
C3216X7R1E225K	X7R	25V	2,200,000	± 10%	1.60 ± 0.30
C3216X7R1E225M	X7R	25V	2,200,000	± 20%	1.60 ± 0.30
C3216X7R1E335K	X7R	25V	3,300,000	± 10%	1.60 ± 0.30
C3216X7R1E335M	X7R	25V	3,300,000	± 20%	1.60 ± 0.30
C3216X7R1E475K	X7R	25V	4,700,000	± 10%	1.60 ± 0.30
C3216X7R1E475M	X7R	25V	4,700,000	± 20%	1.60 ± 0.30
C3216X7R1E685K	X7R	25V	6,800,000	± 10%	1.60 ± 0.30
C3216X7R1E685M	X7R	25V	6,800,000	± 20%	1.60 ± 0.30
C3216X7R1E106K	X7R	25V	10,000,000	± 10%	1.60 ± 0.30
C3216X7R1E106M	X7R	25V	10,000,000	± 20%	1.60 ± 0.30
C3216X7R1C474K	X7R	16V	470,000	± 10%	1.15 ± 0.10
C3216X7R1C474M	X7R	16V	470,000	± 20%	1.15 ± 0.10
C3216X7R1C105K/0.85	X7R	16V	1,000,000	± 10%	0.85 ± 0.10
C3216X7R1C105M/0.85	X7R	16V	1,000,000	± 20%	0.85 ± 0.10
C3216X7R1C105K/1.15	X7R	16V	1,000,000	± 10%	1.15 ± 0.10
C3216X7R1C105K/1.30	X7R	16V	1,000,000	± 10%	1.30 ± 0.15
C3216X7R1C225K/1.60	X7R	16V	2,200,000	± 10%	1.60 ± 0.30
C3216X7R1C225M/1.60	X7R	16V	2,200,000	± 20%	1.60 ± 0.30
C3216X7R1C335K/1.60	X7R	16V	3,300,000	± 10%	1.60 ± 0.30
C3216X7R1C335M/1.60	X7R	16V	3,300,000	± 20%	1.60 ± 0.30
C3216X7R1C475K/1.60	X7R	16V	4,700,000	± 10%	1.60 ± 0.30

TDK MLCC US Catalog

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C3216 [EIA CC1206]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S(-55 to 105°C, ±22%), X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3216X7R1C475M/1.60	X7R	16V	4,700,000	± 20%	1.60 ± 0.30
C3216X7R1C685K	X7R	16V	6,800,000	± 10%	1.60 ± 0.30
C3216X7R1C685M	X7R	16V	6,800,000	± 20%	1.60 ± 0.30
C3216X7R1C106K	X7R	16V	10,000,000	± 10%	1.60 ± 0.30
C3216X7R1C106M	X7R	16V	10,000,000	± 20%	1.60 ± 0.30
C3216X7R1A106K	X7R	10V	10,000,000	± 10%	1.60 ± 0.30
C3216X7R1A106M	X7R	10V	10,000,000	± 20%	1.60 ± 0.30
C3216X6S1A476M	X6S	10V	47,000,000	± 20%	1.60 ± 0.30
C3216X6S0J476M	X6S	6.3V	47,000,000	± 20%	1.60 ± 0.30
C3216X6S0G107M	X6S	4V	100,000,000	± 20%	1.60 ± 0.30
C3216X5R1H105K	X5R	50V	1,000,000	± 10%	1.60 ± 0.30
C3216X5R1H105M	X5R	50V	1,000,000	± 20%	1.60 ± 0.30
C3216X5R1H335K	X5R	50V	3,300,000	± 10%	1.60 ± 0.30
C3216X5R1H335M	X5R	50V	3,300,000	± 20%	1.60 ± 0.30
C3216X5R1H475K	X5R	50V	4,700,000	± 10%	1.60 ± 0.30
C3216X5R1H475M	X5R	50V	4,700,000	± 20%	1.60 ± 0.30
C3216X5R1H685K	X5R	50V	6,800,000	± 10%	1.60 ± 0.30
C3216X5R1H685M	X5R	50V	6,800,000	± 20%	1.60 ± 0.30
C3216X5R1H106K	X5R	50V	10,000,000	± 10%	1.60 ± 0.30
C3216X5R1H106M	X5R	50V	10,000,000	± 20%	1.60 ± 0.30
C3216X5R1E225K	X5R	25V	2,200,000	± 10%	1.60 ± 0.30
C3216X5R1E225M	X5R	25V	2,200,000	± 20%	1.60 ± 0.30
C3216X5R1E335K/1.60	X5R	25V	3,300,000	± 10%	1.60 ± 0.30
C3216X5R1E335M/1.60	X5R	25V	3,300,000	± 20%	1.60 ± 0.30
C3216X5R1E475K	X5R	25V	4,700,000	± 10%	1.60 ± 0.30
C3216X5R1E475M	X5R	25V	4,700,000	± 20%	1.60 ± 0.30
C3216X5R1E106K	X5R	25V	10,000,000	± 10%	1.60 ± 0.30
C3216X5R1E106M	X5R	25V	10,000,000	± 20%	1.60 ± 0.30
C3216X5R1E226M	X5R	25V	22,000,000	± 20%	1.60 ± 0.30
C3216X5R1C225K/1.60	X5R	16V	2,200,000	± 10%	1.60 ± 0.30
C3216X5R1C225M/1.60	X5R	16V	2,200,000	± 20%	1.60 ± 0.30
C3216X5R1C335K/1.60	X5R	16V	3,300,000	± 10%	1.60 ± 0.30
C3216X5R1C335M/1.60	X5R	16V	3,300,000	± 20%	1.60 ± 0.30
C3216X5R1C475K/1.15	X5R	16V	4,700,000	± 10%	1.15 ± 0.10
C3216X5R1C475M/1.15	X5R	16V	4,700,000	± 20%	1.15 ± 0.10
C3216X5R1C475K/1.60	X5R	16V	4,700,000	± 10%	1.60 ± 0.30
C3216X5R1C475M/1.60	X5R	16V	4,700,000	± 20%	1.60 ± 0.30
C3216X5R1C685K	X5R	16V	6,800,000	± 10%	1.60 ± 0.30
C3216X5R1C685M	X5R	16V	6,800,000	± 20%	1.60 ± 0.30
C3216X5R1C106K	X5R	16V	10,000,000	± 10%	1.60 ± 0.30
C3216X5R1C106M	X5R	16V	10,000,000	± 20%	1.60 ± 0.30
C3216X5R1C226M	X5R	16V	22,000,000	± 20%	1.60 ± 0.30
C3216X5R1C336M	X5R	16V	33,000,000	± 20%	1.60 ± 0.30
C3216X5R1C476M	X5R	16V	47,000,000	± 20%	1.60 ± 0.30

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C3216 [EIA CC1206]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

Temperature Characteri TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3216X5R1A225K/0.85	X5R	10V	2,200,000	± 10%	0.85 ± 0.10
C3216X5R1A225M/0.85	X5R	10V	2,200,000	± 20%	0.85 ± 0.10
C3216X5R1A335K/0.85	X5R	10V	3,300,000	± 10%	0.85 ± 0.10
C3216X5R1A335M/0.85	X5R	10V	3,300,000	± 20%	0.85 ± 0.10
C3216X5R1A335K/1.15	X5R	10V	3,300,000	± 10%	1.15 ± 0.10
C3216X5R1A335M/1.15	X5R	10V	3,300,000	± 20%	1.15 ± 0.10
C3216X5R1A475K	X5R	10V	4,700,000	± 10%	1.60 ± 0.30
C3216X5R1A475M	X5R	10V	4,700,000	± 20%	1.60 ± 0.30
C3216X5R1A106K	X5R	10V	10,000,000	± 10%	1.60 ± 0.30
C3216X5R1A106M	X5R	10V	10,000,000	± 20%	1.60 ± 0.30
C3216X5R1A226M	X5R	10V	22,000,000	± 20%	1.60 ± 0.30
C3216X5R1A336M	X5R	10V	33,000,000	± 20%	1.60 ± 0.30
C3216X5R1A476M	X5R	10V	47,000,000	± 20%	1.60 ± 0.30
C3216X5R1A107M	X5R	10V	100,000,000	± 20%	1.60 ± 0.30
C3216X5R0J106K/0.85	X5R	6.3V	10,000,000	± 10%	0.85 ± 0.10
C3216X5R0J106M/0.85	X5R	6.3V	10,000,000	± 20%	0.85 ± 0.10
C3216X5R0J106K/1.60	X5R	6.3V	10,000,000	± 10%	1.60 ± 0.30
C3216X5R0J106M/1.60	X5R	6.3V	10,000,000	± 20%	1.60 ± 0.30
C3216X5R0J156M	X5R	6.3V	15,000,000	± 20%	1.60 ± 0.30
C3216X5R0J226M/0.85	X5R	6.3V	22,000,000	± 20%	0.85 ± 0.10
C3216X5R0J226K/1.60	X5R	6.3V	22,000,000	± 10%	1.60 ± 0.30
C3216X5R0J226M/1.60	X5R	6.3V	22,000,000	± 20%	1.60 ± 0.30
C3216X5R0J336M	X5R	6.3V	33,000,000	± 20%	1.30 ± 0.15
C3216X5R0J476M	X5R	6.3V	47,000,000	± 20%	1.60 ± 0.30
C3216X5R0J107M	X5R	6.3V	100,000,000	± 20%	1.60 ± 0.30
C3216X5R0G107M	X5R	4V	100,000,000	± 20%	1.60 ± 0.30
C3216Y5V1H225Z/0.85	Y5V	50V	2,200,000	+80/-20%	0.85 ± 0.10
C3216Y5V1H225Z/1.15	Y5V	50V	2,200,000	+80/-20%	1.15 ± 0.10
C3216Y5V1H475Z	Y5V	50V	4,700,000	+80/-20%	1.60 ± 0.30
C3216Y5V1E475Z/0.85	Y5V	25V	4,700,000	+80/-20%	0.85 ± 0.10
C3216Y5V1E475Z/1.15	Y5V	25V	4,700,000	+80/-20%	1.15 ± 0.10
C3216Y5V1E106Z	Y5V	25V	10,000,000	+80/-20%	1.60 ± 0.30
C3216Y5V1C475Z/0.85	Y5V	16V	4,700,000	+80/-20%	0.85 ± 0.10
C3216Y5V1C475Z/1.15	Y5V	16V	4,700,000	+80/-20%	1.15 ± 0.10
C3216Y5V1C475Z/1.30	Y5V	16V	4,700,000	+80/-20%	1.30 ± 0.15
C3216Y5V1C106Z	Y5V	16V	10,000,000	+80/-20%	1.60 ± 0.30
C3216Y5V1C226Z	Y5V	16V	22,000,000	+80/-20%	1.60 ± 0.30
C3216Y5V1A106Z/0.85	Y5V	10V	10,000,000	+80/-20%	0.85 ± 0.10
C3216Y5V1A106Z/1.15	Y5V	10V	10,000,000	+80/-20%	1.15 ± 0.10
C3216Y5V1A226Z	Y5V	10V	22,000,000	+80/-20%	1.60 ± 0.30
C3216Y5V0J476Z	Y5V	6.3V	47,000,000	+80/-20%	1.60 ± 0.30

MULTILAYER CERAMIC CHIP CAPACITORS



C3225 [EIA CC1210]

Capacitance Range Chart

Temperature Characteristics: COG (0 ± 30ppm/^oC) Rated Voltage: 50V (1H)

Canacitanaa	Con		C0G
Capacitance (pF)	Cap Code	Tolerance	1H (50V)
22,000	223	J: ± 5%	
33,000	333		
47,000	473		
68,000	683		
100,000	104		

Capacitance Range Chart

Temperature Characteristics: X7R (±15%), X7S (±22%), X5R (±15%), X6S (±22%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J), 4V (0G)

Capacitanaa	Capacitance Cap Tolerance			X5R				X6S		
(pF)	(pF) Code Toleran	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)	1H (50V)	0J (6.3V)	0G (4V)
4,700,000	475	K: ± 10%								
10,000,000	106	M: ± 20%								
15,000,000	156									
22,000,000	226									
33,000,000	336									
47,000,000	476									
68,000,000	686									
100,000,000	107									

Canacitanaa	Con			X	7R		X7S
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	1H (50V)
470,000	474	K: ± 10%					
1,000,000	105	M: ± 20%					
1,500,000	155						
2,200,000	225						
3,300,000	335						
4,700,000	475						
6,800,000	685						
10,000,000	106						
15,000,000	156]					
22,000,000	226						

Conscitores	Con		Y5V						
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)		
4,700,000	475	Z: +80/-20%							
10,000,000	106								
22,000,000	226								
47,000,000	476								
100,000,000	107								

Standard Thickness

1.15 mm 1.25 mm 1.30 mm 1.60 mm 2.00 mm 2.00 mm 2.50 mm 2.50 mm 2.30 mm

• Standard capacitance and thickness is shown. Please refer to Capacitance Range Table for additional capacitance values and thicknesses.



Capacitance Range Table

C3225 [EIA CC1210]

Class 1 (Temperature Compensating)

Temperature Characteristics: C0G (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3225C0G1H223J	COG	50V	22,000	± 5%	1.30 ± 0.15
C3225C0G1H333J	COG	50V	33,000	± 5%	1.60 ± 0.30
C3225C0G1H473J	COG	50V	47,000	± 5%	2.00 ± 0.20
C3225C0G1H683J	COG	50V	68,000	± 5%	2.00 ± 0.20
C3225C0G1H104J	COG	50V	100,000	± 5%	2.50 ± 0.30

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X7S (-55 to +125°C, ±22%), X6S (-55 to +105°C, ±22%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3225X7R1H474K/1.30	X7R	50V	470,000	± 10%	1.30 ± 0.15
C3225X7R1H474M/1.30	X7R	50V	470,000	± 20%	1.30 ± 0.15
C3225X7R1H105K/1.60	X7R	50V	1,000,000	± 10%	1.60 ± 0.30
C3225X7R1H105M/1.60	X7R	50V	1,000,000	± 20%	1.60 ± 0.30
C3225X7R1H105K/2.00	X7R	50V	1,000,000	± 10%	2.00 ± 0.20
C3225X7R1H105M/2.00	X7R	50V	1,000,000	± 20%	2.00 ± 0.20
C3225X7R1H155K	X7R	50V	1,500,000	± 10%	2.00 ± 0.20
C3225X7R1H155M	X7R	50V	1,500,000	± 20%	2.00 ± 0.20
C3225X7R1H225K/2.00	X7R	50V	2,200,000	± 10%	2.00 ± 0.20
C3225X7R1H225M/2.00	X7R	50V	2,200,000	± 20%	2.00 ± 0.20
C3225X7R1H225K/2.50	X7R	50V	2,200,000	± 10%	2.50 ± 0.30
C3225X7R1H225M/2.50	X7R	50V	2,200,000	± 20%	2.50 ± 0.30
C3225X7R1H335K	X7R	50V	3,300,000	± 10%	2.50 ± 0.30
C3225X7R1H335M	X7R	50V	3,300,000	± 20%	2.50 ± 0.30
C3225X7R1H475K	X7R	50V	4,700,000	± 10%	2.50 ± 0.30
C3225X7R1H475M	X7R	50V	4,700,000	± 20%	2.50 ± 0.30
C3225X6S1H475K	X6S	50V	4,700,000	± 10%	2.50 ± 0.30
C3225X6S1H475M	X6S	50V	4,700,000	± 20%	2.50 ± 0.30
C3225X7S1H685K	X7S	50V	6,800,000	± 10%	2.50 ± 0.30
C3225X7S1H685M	X7S	50V	6,800,000	± 20%	2.50 ± 0.30
C3225X7S1H106K	X7S	50V	10,000,000	± 10%	2.50 ± 0.30
C3225X7S1H106M	X7S	50V	10,000,000	± 20%	2.50 ± 0.30
C3225X7R1E225K/1.60	X7R	25V	2,200,000	± 10%	1.60 ± 0.30
C3225X7R1E225M/1.60	X7R	25V	2,200,000	± 20%	1.60 ± 0.30
C3225X7R1E335K	X7R	25V	3,300,000	± 10%	1.60 ± 0.30
C3225X7R1E335M	X7R	25V	3,300,000	± 20%	1.60 ± 0.30
C3225X7R1E475K	X7R	25V	4,700,000	± 10%	2.00 ± 0.20
C3225X7R1E475M	X7R	25V	4,700,000	± 20%	2.00 ± 0.20
C3225X7R1E685K/2.50	X7R	25V	6,800,000	± 10%	2.50 ± 0.30
C3225X7R1E685M/2.50	X7R	25V	6,800,000	± 20%	2.50 ± 0.30
C3225X7R1E106K	X7R	25V	10,000,000	± 10%	2.50 ± 0.30
C3225X7R1E106M	X7R	25V	10,000,000	± 20%	2.50 ± 0.30
C3225X7R1C106K	X7R	16V	10,000,000	± 10%	2.00 ± 0.20
C3225X7R1C106M	X7R	16V	10,000,000	± 20%	2.00 ± 0.20
C3225X7R1C156M	X7R	16V	15,000,000	± 20%	2.50 ± 0.30

TDK MLCC US Catalog

会TDK

MULTILAYER CERAMIC CHIP CAPACITORS



Capacitance Range Table

C3225 [EIA CC1210]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X6S (-55 to +105°C, ±22%), X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3225X7R1C226K	X7R	16V	22,000,000	± 10%	2.50 ± 0.30
C3225X7R1C226M	X7R	16V	22,000,000	± 20%	2.50 ± 0.30
C3225X7R1A226K/2.30	X7R	10V	22,000,000	± 10%	2.30 ± 0.20
C3225X7R1A226M/2.30	X7R	10V	22,000,000	± 20%	2.30 ± 0.20
C3225X5R1H475K	X5R	50V	4,700,000	± 10%	2.50 ± 0.30
C3225X5R1H475M	X5R	50V	4,700,000	± 20%	2.50 ± 0.30
C3225X5R1E106K	X5R	25V	10,000,000	± 10%	2.50 ± 0.30
C3225X5R1E106M	X5R	25V	10,000,000	± 20%	2.50 ± 0.30
C3225X5R1C106K	X5R	16V	10,000,000	± 10%	2.00 ± 0.20
C3225X5R1C106M	X5R	16V	10,000,000	± 20%	2.00 ± 0.20
C3225X5R1C156M	X5R	16V	15,000,000	± 20%	2.50 ± 0.30
C3225X5R1C226K	X5R	16V	22,000,000	± 10%	2.50 ± 0.30
C3225X5R1C226M	X5R	16V	22,000,000	± 20%	2.50 ± 0.30
C3225X5R1A106K	X5R	10V	10,000,000	± 10%	2.00 ± 0.20
C3225X5R1A106M	X5R	10V	10,000,000	± 20%	2.00 ± 0.20
C3225X5R1A156M/2.30	X5R	10V	15,000,000	± 20%	2.30 ± 0.20
C3225X5R1A226M	X5R	10V	22,000,000	± 20%	2.30 ± 0.20
C3225X5R1A336M	X5R	10V	33,000,000	± 20%	2.00 ± 0.20
C3225X5R1A476M	X5R	10V	47,000,000	± 20%	2.50 ± 0.30
C3225X5R0J226M/1.60	X5R	6.3V	22,000,000	± 20%	1.60 ± 0.30
C3225X5R0J226K/2.00	X5R	6.3V	22,000,000	± 10%	2.00 ± 0.20
C3225X5R0J226M/2.00	X5R	6.3V	22,000,000	± 20%	2.00 ± 0.20
C3225X5R0J226K/2.50	X5R	6.3V	22,000,000	± 10%	2.50 ± 0.30
C3225X5R0J226M/2.50	X5R	6.3V	22,000,000	± 20%	2.50 ± 0.30
C3225X5R0J336M/2.00	X5R	6.3V	33,000,000	± 20%	2.00 ± 0.20
C3225X5R0J336M/2.50	X5R	6.3V	33,000,000	± 20%	2.50 ± 0.30
C3225X5R0J476M	X5R	6.3V	47,000,000	± 20%	2.50 ± 0.30
C3225X5R0J686M	X5R	6.3V	68,000,000	± 20%	2.00 ± 0.20
C3225X5R0J107M	X5R	6.3V	100,000,000	± 20%	2.50 ± 0.30
C3225X6S0J476M	X6S	6.3V	47,000,000	± 20%	2.50 ± 0.30
C3225X6S0J107M	X6S	6.3V	100,000,000	± 20%	2.50 ± 0.30
C3225X6S0G107M	X6S	4V	100,000,000	± 20%	2.50 ± 0.30
C3225Y5V1H475Z/1.15	Y5V	50V	4,700,000	+80/-20%	1.15 ± 0.10
C3225Y5V1H475Z/1.60	Y5V	50V	4,700,000	+80/-20%	1.60 ± 0.30
C3225Y5V1H106Z	Y5V	50V	10,000,000	+80/-20%	1.60 ± 0.30
C3225Y5V1E106Z/1.30	Y5V	25V	10,000,000	+80/-20%	1.30 ± 0.15
C3225Y5V1E106Z/1.60	Y5V	25V	10,000,000	+80/-20%	1.60 ± 0.30
C3225Y5V1E226Z	Y5V	25V	22,000,000	+80/-20%	2.00 ± 0.20
C3225Y5V1C106Z/1.15	Y5V	16V	10,000,000	+80/-20%	1.15 ± 0.10
C3225Y5V1C106Z/1.60	Y5V	16V	10,000,000	+80/-20%	1.60 ± 0.30
C3225Y5V1C226Z/1.30	Y5V	16V	22,000,000	+80/-20%	1.30 ± 0.15
	Y5V	16V	22,000,000	+80/-20%	2.00 ± 0.20
C3225Y5V1C476Z	Y5V	16V	47,000,000	+80/-20%	2.30 ± 0.20
C3225Y5V1A226Z/1.15	Y5V	10V	22,000,000	+80/-20%	1.15 ± 0.10
			,		

MULTILAYER CERAMIC CHIP CAPACITORS



C3225 [EIA CC1210]

Class 2 (Temperature Stable)

Temperature Characteristics: Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C3225Y5V1A476Z	Y5V	10V	47,000,000	+80/-20%	2.00 ± 0.20
C3225Y5V0J107Z	Y5V	6.3V	100,000,000	+80/-20%	2.50 ± 0.30

⇔TDK

MULTILAYER CERAMIC CHIP CAPACITORS



C4532 [EIA CC1812]

Capacitance Range Chart

Temperature Characteristics: COG (0 ± 30ppm/^oC) Rated Voltage: 50V (1H)

Capacitanas	Con		COG
Capacitance (pF)	Cap Code	Tolerance	1H (50V)
47,000	473	J: ± 5%	
68,000	683		
100,000	104		
150,000	154		
220,000	224		

Capacitance Range Chart

Temperature Characteristics: X7R (±15%), X5R (±15%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J)

Conceltance	Canacitanaa Can			X7R			X	5R	
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
1,000,000	105	K: ± 10%							
1,500,000	155	M: ± 20%							
2,200,000	225								
3,300,000	335								
4,700,000	475								
6,800,000	685								
10,000,000	106								
15,000,000	156								
22,000,000	226								
33,000,000	336								
47,000,000	476								
68,000,000	686								
100,000,000	107								

Canacitanaa	Con		Y5V				
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)	
10,000,000	106	Z: +80/-20%					
22,000,000	226						
47,000,000	476						
100,000,000	107						

Standard Thickness

1.60 mm 2.00 mm 2.30 mm 2.50 mm 2.50 mm 2.50 mm 3.20 mm

• Standard capacitance and thickness is shown. Please refer to Capacitance Range Table for additional capacitance values and thicknesses.



Capacitance Range Table

C4532 [EIA CC1812]

Class 1 (Temperature Compensating)

Temperature Characteristics: COG (-55 to 125°C, 0±30 ppm/°C)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C4532C0G1H473J	COG	50V	47,000	± 5%	1.60 ± 0.30
C4532C0G1H683J	COG	50V	68,000	± 5%	1.60 ± 0.30
C4532C0G1H104J	COG	50V	100,000	± 5%	2.00 ± 0.20
C4532C0G1H154J	COG	50V	150,000	± 5%	2.50 ± 0.30
C4532C0G1H224J	COG	50V	220,000	± 5%	3.20 ± 0.30

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X5R (-55 to +85°C, ±15%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C4532X7R1H105K	X7R	50V	1,000,000	± 10%	1.60 ± 0.30
C4532X7R1H105M	X7R	50V	1,000,000	± 20%	1.60 ± 0.30
C4532X7R1H155K/1.60	X7R	50V	1,500,000	± 10%	1.60 ± 0.30
C4532X7R1H155M/1.60	X7R	50V	1,500,000	± 20%	1.60 ± 0.30
C4532X7R1H225K	X7R	50V	2,200,000	± 10%	1.60 ± 0.30
C4532X7R1H225M	X7R	50V	2,200,000	± 20%	1.60 ± 0.30
C4532X7R1H335K	X7R	50V	3,300,000	± 10%	2.00 ± 0.20
C4532X7R1H335M	X7R	50V	3,300,000	± 20%	2.00 ± 0.20
C4532X7R1H475K/2.00	X7R	50V	4,700,000	± 10%	2.00 ± 0.20
C4532X7R1H475M/2.00	X7R	50V	4,700,000	± 20%	2.00 ± 0.20
C4532X7R1H685K	X7R	50V	6,800,000	± 10%	2.50 ± 0.30
C4532X7R1H685M	X7R	50V	6,800,000	± 20%	2.50 ± 0.30
C4532X7R1E475M/2.00	X7R	25V	4,700,000	± 20%	2.00 ± 0.20
C4532X7R1E106K	X7R	25V	10,000,000	± 10%	2.50 ± 0.30
C4532X7R1E106M	X7R	25V	10,000,000	± 20%	2.50 ± 0.30
C4532X7R1E156M/2.80	X7R	25V	15,000,000	± 20%	2.80 ± 0.30
C4532X7R1E226M	X7R	25V	22,000,000	± 20%	2.50 ± 0.30
C4532X7R1C106K	X7R	16V	10,000,000	± 10%	2.30 ± 0.20
C4532X7R1C106M	X7R	16V	10,000,000	± 20%	2.30 ± 0.20
C4532X7R1C226M/2.00	X7R	16V	22,000,000	± 20%	2.00 ± 0.20
C4532X7R1C226M/2.30	X7R	16V	22,000,000	± 20%	2.30 ± 0.20
C4532X7R1C336M	X7R	16V	33,000,000	± 20%	2.50 ± 0.30
C4532X5R1E106K	X5R	25V	10,000,000	± 10%	2.50 ± 0.30
C4532X5R1E106M	X5R	25V	10,000,000	± 20%	2.50 ± 0.30
C4532X5R1E156M/2.80	X5R	25V	15,000,000	± 20%	2.80 ± 0.30
C4532X5R1E226M	X5R	25V	22,000,000	± 20%	2.50 ± 0.30
C4532X5R1C226M/2.00	X5R	16V	22,000,000	± 20%	2.00 ± 0.20
C4532X5R1C226M/2.30	X5R	16V	22,000,000	± 20%	2.30 ± 0.20
C4532X5R1C336M	X5R	16V	33,000,000	± 20%	2.50 ± 0.30
C4532X5R1A226M	X5R	10V	22,000,000	± 20%	2.30 ± 0.20
C4532X5R1A336M	X5R	10V	33,000,000	± 20%	2.30 ± 0.20
C4532X5R1A476M	X5R	10V	47,000,000	± 20%	2.80 ± 0.30
C4532X5R1A107M	X5R	10V	100,000,000	± 20%	2.80 ± 0.30
C4532X5R0J476M	X5R	6.3V	47,000,000	± 20%	2.50 ± 0.30
C4532X5R0J686M	X5R	6.3V	68,000,000	± 20%	2.80 ± 0.30

TDK MLCC US Catalog

MULTILAYER CERAMIC CHIP CAPACITORS



C4532 [EIA CC1812]

Class 2 (Temperature Stable)

Temperature Characteristics: X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C4532X5R0J107M	X5R	6.3V	100,000,000	± 20%	2.80 ± 0.30
C4532Y5V1H106Z	Y5V	50V	10,000,000	+80/-20%	2.00 ± 0.20
C4532Y5V1E226Z	Y5V	25V	22,000,000	+80/-20%	2.00 ± 0.20
C4532Y5V1C476Z	Y5V	16V	47,000,000	+80/-20%	2.50 ± 0.30
C4532Y5V1A107Z	Y5V	10V	100,000,000	+80/-20%	2.50 ± 0.30

MULTILAYER CERAMIC CHIP CAPACITORS



C5750 [EIA CC2220]

Capacitance Range Chart

Temperature Characteristics: X7R (± 15%), X5R (± 15%), Y5V (+22/-82%) Rated Voltage: 50V (1H), 25V (1E), 16V (1C), 10V (1A), 6.3V (0J)

Canacitanaa	Can			X7R				X5R		
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1H (50V)	1E (25V)	1C (16V)	1A (10V)	0J (6.3V)
4,700,000	475	K: ± 10%								
6,800,000	685	M: ± 20%								
10,000,000	106									
15,000,000	156									
22,000,000	226									
33,000,000	336									
47,000,000	476									
68,000,000	686]								
100,000,000	107									

Canacitanaa	Con		Y5V						
Capacitance (pF)	Cap Code	Tolerance	1H (50V)	1E (25V)	1C (16V)	1A (10V)			
10,000,000	106	Z: +80/-20%							
22,000,000	226								
47,000,000	476								
100,000,000	107								

 Standard Thickness

 2.00 mm
 2.30 mm
 2.50 mm
 2.80 mm





Capacitance Range Table

C5750 [EIA CC2220]

Class 2 (Temperature Stable)

Temperature Characteristics: X7R (-55 to +125°C, ±15%), X5R (-55 to +85°C, ±15%), Y5V(-30 to +85°C, +22/-82%)

TDK Part Number (Ordering Code)	Temperature Characteristics	Rated Voltage	Capacitance (pF)	Capacitance Tolerance	Thickness (mm)
C5750X7R1H475K/2.00	X7R	50V	4,700,000	± 10%	2.00 ± 0.20
C5750X7R1H475M/2.00	X7R	50V	4,700,000	± 20%	2.00 ± 0.20
C5750X7R1H475M/2.80	X7R	50V	4,700,000	± 20%	2.80 ± 0.20
C5750X7R1H685K	X7R	50V	6,800,000	± 10%	2.50 ± 0.30
C5750X7R1H685M	X7R	50V	6,800,000	± 20%	2.50 ± 0.30
C5750X7R1H106K	X7R	50V	10,000,000	± 10%	2.30 ± 0.20
C5750X7R1H106M	X7R	50V	10,000,000	± 20%	2.30 ± 0.20
C5750X7R1E106M	X7R	25V	10,000,000	± 20%	2.00 ± 0.20
C5750X7R1E156M	X7R	25V	15,000,000	± 20%	2.30 ± 0.20
C5750X7R1E226M	X7R	25V	22,000,000	± 20%	2.50 ± 0.30
C5750X7R1C226M	X7R	16V	22,000,000	± 20%	2.80 ± 0.20
C5750X7R1C476M	X7R	16V	47,000,000	± 20%	2.30 ± 0.20
C5750X5R1H106K	X5R	50V	10,000,000	± 10%	2.30 ± 0.20
C5750X5R1H106M	X5R	50V	10,000,000	± 20%	2.30 ± 0.20
C5750X5R1E226M	X5R	25V	22,000,000	± 20%	2.30 ± 0.20
C5750X5R1C336M	X5R	16V	33,000,000	± 20%	2.00 ± 0.20
C5750X5R1C476M	X5R	16V	47,000,000	± 20%	2.30 ± 0.20
C5750X5R1A686M	X5R	10V	68,000,000	± 20%	2.30 ± 0.20
C5750X5R1A107M	X5R	10V	100,000,000	± 20%	2.80 ± 0.20
C5750X5R0J107M	X5R	6.3V	100,000,000	± 20%	2.80 ± 0.20
C5750Y5V1H226Z	Y5V	50V	22,000,000	+80/-20%	2.00 ± 0.20
C5750Y5V1E476Z	Y5V	25V	47,000,000	+80/-20%	2.00 ± 0.20
C5750Y5V1C107Z	Y5V	16V	100,000,000	+80/-20%	2.50 ± 0.30
C5750Y5V1A107Z	Y5V	10V	100,000,000	+80/-20%	2.50 ± 0.30

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performance	Test or I	Test or Inspection Method					
1	External Appearance	No defects which may affect performance.	Inspect with magnifying glass (3 $ imes$), in case of C0603 type, with magnifying glass (10 $ imes$).						
2	Insulation Resistance	10,000MΩ or 500MΩ•μF min. (As for the capacitors of rated voltage 16, 10 and 6.3V DC, 10,000 MΩ or 100MΩ•μF min.,) whichever smaller.	Apply rated voltage for 60s. As for the rated voltage 630V DC, apply 500V DC.						
3	Voltage Proof	Withstand test voltage without	Class	Apply voltage					
		insulation breakdown or other damage.	Class 1	$3 \times$ rated volta	ge				
			Class 2	2.5 imes rated voltage					
					be applied for 1 ot exceed 50mA				
4	Capacitance	Within the specified tolerance.	Class	Rated Capacitance	Measuring Frequency	Measuring voltage			

lass	Capacitance	Frequency	voltage
Class 1 ⊢	C ≤ 1000pF	1MHz±10%	05 51
	C >1000pF	1kHz±10%	0.5 - 5 V _{rms}
	0.440.5		$0.5\pm0.2V_{rms}$
ass 2	C S TOUF	TKHZ±10%	1.0±0.2V _{rms}
	C > 10uF	120Hz±20%	$0.5\pm0.2V_{rms}$
as	s 1 s 2	$Capacitance$ s 1 $C \le 1000 pF$ $C > 1000 pF$ $C < 100 F$	$\begin{array}{c c c c c c c c c c c c c c c c c c c $

5	Q	Rated	Capacitance	Q	See No.4 in this table for measuring condition.
	(Class 1)	30pF a	and over	1,000 min.	
		Under	30pF	400+20×C min.	
			C : R	ated capacitance	(pF)
6	Dissipation Factor	T.C.	Rated Voltage	D.F.	See No.4 in this table for measuring condition.
	(Class 2)	X5R	-	0.03 max.	
		X7R		0.05 max.	
				0.75 max.	
				0.1 max.	
				0.125 max.	
				0.15 max.	
		Y5V	50VDC	0.05 max.	
			25VDC	0.075 max.	
			16VDC	0.10 max.	
			10VDC	0.125 max.	
			6.3VDC	0.20 max.	

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performance	Test or Inspection Method			
7	Temperature Characteristics of Capacitance (Class 1)	T.C.Temperature CoefficientCOG $0 \pm 30 \text{ (ppm/°C)}$ Capacitance driftWithin $\pm 0.2\%$ or $\pm 0.05 \text{pF}$, whichever larger.	Temperature coefficient shall be calculated based on values at 25°C and 85°C temperature. Measuring temperature below 20°C shall be -10°C and -25°C.			
8	Temperature Characteristics of Capacitance (Class 2)	No Voltage Applied X5R: ± 15% X7R: ± 15% X6S: ± 22% X7S: ± 22% X7T: +22/-33% Y5V: + 22/-82%	$\begin{array}{c} \mbox{Capacitance shall be measured by the steps shown in the following table after thermal equilibrium is obtained for each step. \\ \end{tabular} \Delta C \mbox{ be calculated ref. STEP 3 reading} \\ \hline \hline \begin{tabular}{ c c c c c } \hline Step & Temperature (°C) \\ \hline 1 & Reference temp. \pm 2 \\ \hline 2 & Min. operating temp. \pm 2 \\ \hline 3 & Reference temp. \pm 2 \\ \hline 4 & Max. operating temp. \pm 2 \\ \hline 4 & Max. operating temp. \pm 2 \\ \hline \end{array} \\ \hline \begin{tabular}{ c c c c } \hline Temperature (°C) & Temperature (°C) \\ \hline \end{tabular} \end{array}$			
9	Robustness of Terminations	No sign of termination coming off, breakage of ceramic, or other abnormal signs.	Reflow solder the capacitor on P.C. board (shown in Appendix 1a or Appendix 1b) and apply a pushing force of 2N (C0603, C1005) or 5N (C1608, C2012, C3216, C3225, C4532, C5750) for $10 \pm 1s$.			
10	Bending	No mechanical damage.	Reflow solder the capacitor on P.C. board (shown in Appendix 2a or Appendix 2b) and bend it for 1mm. $50 \xrightarrow{20}{F}$			

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performar	nce		Test or Inspection Method		
11	Solderability	New solder termination.		over 75% of	Completely soak both terminations in solder at $235\pm5^{\circ}$ C for 2 ± 0.5 s.		
		but not cond Ceramic sur be exposed	may have pinholes or rough spots ot concentrated in one spot. mic surface of A sections shall not sposed due to melting or shifting of nation material.		Solder: H63A (JIS Z 3282) Flux: Isopropyl alcohol (JIS K 8839) Rosin (JIS K 5902) 25% solid solution.		
12	Resistance to so External appearance	No cracks a	are allowed and terminations overed at least 60% with new		Completely soak both terminations in solder at 260±5°C for 5±1s. Preheating condition Temp.: 150±10°C Time: 1 to 2min.		
	Capacitance		COG Ca wh	ange from the lue before test pacitance drift within 2.5% or \pm 0.25pF, ichever larger.	Flux: Isopropyl alcohol (JIS K 8839) Rosin (JIS K 5902) 25% solid solution. Solder: H63A (JIS Z 3282)		
		x	(7R ±	7.5 % 7.5 % 20 %	Leave the capacitor in ambient conditions for 6 to 24h (Class 1) or $24\pm 2h$ (Class 2) before measurement.		
	Q (Class 1)	Rated Capa C ≥ 30pF C < 30pF		Q 1,000 min. 400+20×C min. d capacitance (pF)	-		
	D.F. (Class 2) Meet the initial spec. Insulation Meet the initial spec. Resistance Meet the initial spec.			-			
	Voltage Proof	age No insulation breakdown or other			-		

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performa	ance		Test or Inspection Method				
13	Vibration External	No moobo	No mechanical damage.			Reflow solder the capacitor on P.C. board (shown in Appendix 1a or Appendix 1b) before testing.			
	appearance	NO MECHA	inical ua	nage.	Vibrate the capacitor with amplitude of 1.5mm P-P – changing the frequencies from 10Hz to 55Hz and bac				
	Capacitance	Characteristics Change from the value before test			to 10Hz	after 1min. Repeat this for dicular directions.			
		Class 1	C0G	\pm 2.5% or \pm 0.25pF, whichever larger.	_ po.po				
		Class 2	X5R	± 7.5 %	-				
			X7R	± 7.5 %					
			Y5V	± 20 %	_				
	Q (Class 1)	Rated Capacitan	се	Q	=				
		C ≥ 30pF		1,000 min.					
		C < 30pF		400+20×C min.	_				
			C : R	ated capacitance (pF)					
	D.F. (Class 2)	Meet the i	nitial spe	ec.	_				
14	Temperature cyc	cle			Reflow	solder the capacitor on P.C	. board (shown in		
	External appearance	No mecha	inical dai	mage.	Append Expose	Appendix 1a or Appendix 1b) before testing. Expose the capacitor in the condition step1 through step 4 and repeat 5 times consecutively.			
	Capacitance	Characteristics		Change from the value before test	Leave t	he capacitor in ambient con	ditions for 6 to 24h		
		Class 1	Class 1 C0G ±2.5% or ±0.25pF, whichever larger.		(Class 1) or $24\pm 2h$ (Class 2) before measurement.				
		Class 2	X5R	± 15 %	Step	Temperature (°C)	Time (min.)		
			X7R	± 15 %	1	Min. operating temp. ±3	30 ± 3		
			Y5V	± 20 %	2	Reference Temp.	2-5		
					3	Max. operating temp. ± 2	30 ± 2		
	Q (Class 1)	Rated Capacitan	се	Q	4	Reference Temp.	2 - 5		
		C ≥ 30pF		1,000 min.	_				
		C < 30pF		400+20×C min.	_				
			C : R	ated capacitance (pF)	_				
	D.F. (Class 2)	Meet the i	Meet the initial spec.						
	Insulation Resistance	Meet the i	nitial spe	ec.					
	Voltage Proof	No insulat damage.	ion brea	kdown or other	_				

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performa	Performance		Test or Inspection Method
15	Moisture Resist	ance (Steady	State)		Reflow solder the capacitor on P.C. board (shown in Appendix 1a or Appendix 1b) before testing.
	External appearance	No mecha	inical da	mage.	Leave at temperature 40 \pm 2°C, 90 to 95%RH for 500
	Capacitance	Characteristics		Change from the value before test	 +24,0h. Leave the capacitor in ambient conditions for 6 to 24h
		Class 1		\pm 5% or \pm 0.5pF, whichever larger.	(Class 1) or 24 \pm 2h (Class 2) before measurement.
		Class 2	X5R	± 25 %	
			X7R	± 25 %	
			Y5V	± 30 %	
	-	Rated Capacita	ance	Q	_
	()	C ≥ 30pF 10pF ≤ C < 30pF		350 min.	
				275+5/2×C min.	
		C <10pF 200+10×C min.			
		C : Rated capacitance (pF)			
	D.F.	Character	istics		_
	(Class 2)	X5R: 2009	% of initia	al spec. max.	
		X7R: 2009	% of initia	al spec. max	
		Y5V: 150%	% of initia	al spec. max	
	Insulation	1,000MΩ	or 50MΩ	•µF min.	_
	Resistance	(As for the	e capacit	ors of rated voltage	
		•		C, 1,000 MΩ or	
		10MΩ•μF	min.,) wl	hichever smaller.	

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

No.	ltem	Performa	ance		Test or Inspection Method
16	Moisture Resis	tance			Reflow solder the capacitor on P.C. board (shown in
	External	No mecha	inical da	mage.	Appendix 1a or Appendix 1b) before testing.
	appearance				Apply the rated voltage at temperature $40\pm2^{\circ}$ C and 90 - to 95%RH for 500 +24.0h.
	Capacitance	Characteristics		Change from the value before test	Charge/discharge current shall not exceed 50mA.
		Class 1	C0G	\pm 7.5% or \pm 0.75pF, whichever larger.	Leave the capacitor in ambient conditions for 6 to 24h (Class 1) or $24\pm 2h$ (Class 2) before measurement.
		Class 2	X5R	± 25 %	
			X7R	\pm 25 %	Voltage conditioning (only for Class 2):
			Y5V	\pm 30 % *(\pm 40 %)	Voltage treat the capacitor under testing temperature
		* Inside () is applied to Y5V 6.3V product.			and voltage for 1 hour.
					Leave the capacitor in ambient conditions for 24 \pm 2h
	Q (Class 1)	Rated CapacitanceQC ≥ 30pF200 min.		Q	before measurement. Use this measurement for initial value.
				200 min.	
		C < 30pF	:	100+10/3×C min.	
			C : R	ated capacitance (pF)	
	D.F.	Character	istics		-
	(Class 2)	X5R: 2009	% of initi	al spec. max.	
		X7R: 2009	% of initi	al spec. max	
		Y5V: 150%	% of initi	al spec. max	
	Insulation Resistance	500MΩor smaller.	25ΜΩ•μ	F min., whichever	-
		•	16.3V D	tors of rated voltage iC, 500 MΩ or	

MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

C Series – General Application

No.	ltem	Performance		Test or Inspection Method
17	Life			Reflow solder the capacitor on P.C. board (shown in Appendix 1a or Appendix 1b) before testing.
	External appearance	No mechanical	damage.	Apply voltage at $125\pm2^{\circ}$ C for 1,000 +48, 0h.
	Capacitance	Characteristic	S Change from the value before test	 Applied voltage is 1xRV. Some items may be tested at higher voltage (1.2x, 1.5x or 2xRV).
		Class 1 COC	\pm 3% or ±0.3pF, whichever larger.	Charge/discharge current shall not exceed 50mA.
		Class 2 X5F X7F		Leave the capacitors in ambient condition for 6 to 24h (Class 1) or 24 \pm 2h (Class 2) before measurement.
		Y5\	′ ± 30 % *(± 40 %)	Voltage conditioning (only for class 2) Voltage treat the
		* Inside () is applied to Y5V 6.3V product.		capacitor under testing temperature and voltage for 1 hour.
	Q (Class 1)	Rated Capacitance	Q	 Leave the capacitor in ambient conditions for 24±2h before measurement.
		C ≥ 30pF	350 min.	Use this measurement for initial value.
		10pF ≤ C < 30pF	275+5/2×C min.	
		C < 10pF	200+10×C min.	
		C : Rated capacitance (pF)		
	D.F. (Class 2)		nitial spec. max. nitial spec. max nitial spec. max	-
	Insulation Resistance	smaller. (As for the capa	MΩ•µF min. , whichever acitors of rated voltage / DC, 1,000 MΩ or)	_


*As for the initial measurement of capacitors (Class2) on number 8,12,13,14 and 15, leave capacitor at 150 –10, 0°C for 1 hour and measure the value after leaving capacitor for $24\pm 2h$ in ambient conditions.


MULTILAYER CERAMIC CHIP CAPACITORS



General Specifications

C Series – General Application







Material: Glass Epoxy (As per JIS C6484 GE4)

P.C. Board thickness:	Appendix-2a	0.8	mm
	Appendix-1a,	1b, 2b	1.6mm



Copper (thickness 0.035mm) Solder resist






Case	Code	Dimensions (mm)			
JIS	EIA	а	b	с	
C0603	CC0201	0.3	0.8	0.3	
C1005	CC0402	0.4	1.5	0.5	
C1608	CC0603	1.0	3.0	1.2	
C2012	CC0805	1.2	4.0	1.65	
C3216	CC1206	2.2	5.0	2.0	
C3225	CC1210	2.2	5.0	2.9	
C4532	CC1812	3.5	7.0	3.7	
C5750	CC2220	4.5	8.0	5.6	



<mark> 谷TD</mark>K



Recommended Soldering Land Pattern



Wave Solderi	ng		Unit: mm
Туре	C1608	C2012	C3216
Symbol	[CC0603]	[CC0805]	[CC1206]
А	0.7 - 1.0	1.0 - 1.3	2.1 - 2.5
В	0.8 - 1.0	1.0 - 1.2	1.1 - 1.3
С	0.6 - 0.8	0.8 - 1.1	1.0 - 1.3

Reflow Soldering

Reflow Solde	ring			Unit: mm
Туре	C0603	C1005	C1608	C2012
Symbol	[CC0201]	[CC0402]	[CC0603]	[CC0805]
А	0.25 - 0.35	0.3 - 0.5	0.6 - 0.8	0.9 - 1.2
В	0.2 - 0.3	0.35 - 0.45	0.6 - 0.8	0.7 - 0.9
С	0.25 - 0.35	0.4 - 0.6	0.6 - 0.8	0.9 - 1.2

Reflow Soldering


Unit: mm
C5750
10000001

04500

Туре	C3216	03225	C4532	C5750
Symbol	[CC1206]	[CC1210]	[CC1812]	[CC2220]
А	2.0 - 2.4	2.0 - 2.4	3.1 - 3.7	4.1 - 4.8
В	1.0 - 1.2	1.0 - 1.2	1.2 - 1.4	1.2 - 1.4
С	1.1 - 1.6	1.9 - 2.5	2.4 - 3.2	4.0 - 5.0


Recommended Solder Amount


. . .



C Series – General Application

Recommended Soldering Profile





Recommended soldering duration

Temp./	Wave S	oldering	Reflow Soldering		
Dura.	Peak temp	Duration	Peak temp	Duration	
Solder	(°C)	(sec.)	(°C)	(sec.)	
Sn-Pb Solder	250 max.	3 max.	230 max.	20 max.	
Lead-Free Solder	260 max.	5 max.	260 max.	10 max.	

Recommended solder compositions

Sn-37Pb (Sn-Pb solder)

Sn-3.0Ag-0.5Cu (Lead Free Solder)

Preheating Condition

Soldering	Case Size - JIS (EIA)	Temp. (°C)
Wave soldering	C1608(CC0603), C2012(CC0805), C3216(CC1206)	∆T ≤ 150
Reflow	C0603(CC0201), C1005(CC0402), C1608(CC0603), C2012(CC0805), C3216(CC1206)	∆T ≤ 150
soldering	C3225(CC1210), C4532(CC1812), C5750(CC2220)	∆T ≤ 130
Manual	C0603(CC0201), C1005(CC0402), C1608(CC0603), C2012(CC0805), C3216(CC1206)	∆T ≤ 150
soldering	C3225(CC1210), C4532(CC1812), C5750(CC2220)	∆T ≤ 130

TDK MLCC US Catalog


②TDK

MULTILAYER CERAMIC CHIP CAPACITORS




C Series – General Application

Carrier Tape Configuration



• Peel Back Force (Top Tape)



• Carrier tape shall be flexible enough to be wound around a minimum radius of 30mm with components in tape.

 \bullet The missing of components shall be less than 0.1%

· Components shall not stick to the cover tape.

• The cover tape shall not protrude beyond the edges of the carrier tape not shall cover the sprocket holes.

· Chip Quantity Per Reel and Structure of Reel (Paper & Plastic)


	Case	e Code	Chip	Taping	Chip qua	ntity (pcs.)
	JIS	EIA	Thickness	Material	φ178mm (7") reel	φ330mm (13") reel
Paper Carrier Tape & Reel	C0402	CC01005	0.20 mm	Paper	20,000	-
Top cover tape	C0603	CC0201	0.30 mm	Paper	15,000	-
\bigcirc	C1005	CC0402	0.50 mm	Paper	10,000	50,000
Pitch hole	C1608	CC0603	0.80 mm	Paper	4,000	10,000
			0.60 mm	Paper/Plastic	4,000	20,000
	C2012	CC0805	0.85 mm	r apen/r lastic	4,000	10,000
			1.25 mm	Plastic	2,000	10,000
			0.60 mm	Paper	4,000	
			0.85 mm	Paper/Plastic	4,000	10,000
	C3216	CC1206	1.15 mm			10,000
Paper carrier tape			1.30 mm	Plastic	2,000	
Bottom cover tape			1.60 mm			8,000
			1.15 mm		2,000	10,000
			1.25 mm			
			1.30 mm		2,000	8,000
Plastic Carrier Tape & Reel	C3225	CC1210	1.60 mm	Plastic		
Top cover tape			2.00 mm			
			2.30 mm		1,000	5,000
$() () \land $			2.50 mm			
Pitch hole			1.60 mm		1,000	
			2.00 mm		1,000	3,000
	C4532	CC1812	2.30 mm	Plastic		3,000
	04552	001012	2.50 mm	Flaslic	500	
			2.80 mm		500	2,000
l Disetis corrier tons			3.20 mm			2,000
Plastic carrier tape			2.00 mm			
	C5750	CC2220	2.30 mm	Plastic	500	3,000
	05750	002220	2.50 mm	FIASUL	500	
			2.80 mm			2,000

②TDK

MULTILAYER CERAMIC CHIP CAPACITORS




Shape & Dimensions



Case	Code	Dimensions (mm)																																																							
JIS	EIA	L	L W T			G																																																			
C0402	CC01005	0.40	0.20	0.20	0.10	0.13 min.																																																			
C0603	CC0201	0.60	0.30	0.30	0.15	0.20 min.																																																			
C1005	CC0402	1.00	0.50	0.50	0.25	0.35 min.																																																			
04000	000000	4.00	0.00	0.50	0.30	0.50 min																																																			
C1608	CC0603	1.60	0.80	0.80	0.20 min.	0.50 min.																																																			
				0.60																																																					
00040	12 CC0805 2.00 1.20 0.80	0.00 min	0.50 min																																																						
C2012	CC0805	2.00	1.20	0.85	0.20 min.	0.50 min.																																																			
				1.25																																																					
				0.60																																																					
				0.85																																																					
C3216	CC1206	3.20	1.60	1.15	0.20 min.	1.00 min.																																																			
				1.30																																																					
				1.60																																																					
				1.15	0.20 min.	1.00 min																																																			
	CC1210	210 3.20	3.20 2.50	1.25	0.30 min.																																																				
				1.30																																																					
C3225				1.60																																																					
						2.00	0.20 min.																																																		
																				2.30	0.00 min																																				
				2.50	0.30 min.																																																				
				1.30	0.30 min.																																																				
				1.60																																																					
				2.00	0.20 min																																																				
C4532	CC1812	4.50	3.20	2.30		2.00 min																																																			
				2.50																																																					
				2.80	0.30 min.																																																				
				3.20																																																					
				1.60																																																					
				2.00																																																					
C5750	CC2220	5.70	5.70	5.70	5.70	5.70	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	2.30	0.20 min.	2.00 min.
			0.0	2.50																																																					
				2.80																																																					

C Series – General Application

Inside Structure & Material System



No.	NAME	MATERIAL	
		Class 1	Class 2
(1)	Ceramic Dielectric	CaZrO₃	BaTiO ₃
(2)	Internal Electrode	Nickel (Ni)	
(3)		Coppe	er (Cu)
(4)	Termination	Nickel (Ni)	
(5)		Tin	(Sn)

Environmental Information

TDK Corporation established internal product environmental assurance standards that include the six hazardous substances banned by the EU RoHS Directive¹ enforced on July 1, 2006 along with additional substances independently banned by TDK and has successfully completed making general purpose electronic components conform to the RoHS Directive².

- Abbreviation for Restriction on Hazardous Substances, which refers to the regulation EU Directive 2002/95/EC on hazardous substances by the European Union (EU) effective from July 1, 2006. The Directive bans the use of six specific hazardous substances in electric and electronic devices and products handled within the EU. The six substances are lead, mercury, cadmium, hexavalent chromium, PBB (polybrominated biphenyls), and PBDE (polybrominated diphenyl ethers).
- This means that, in conformity with the EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.
- For REACH (SVHC : 15 substances according to ECHA / October 2008) : All TDK MLCC do not contain these 15 substances.
- For European Directive 2000/53/CE and 2005/673/CE : Cadmium, Hexavalent Chromium, Mercury, Lead are not contained in all TDK MLCC.
- For European Directive 2003/11/CE : Pentabromodiphenylether, Octabromodiphenyl-ether are not contained in all TDK MLCC.