

**Solutions** 

# Renewable Energy

# Renewable Energy Solutions for



Photovoltaic parks

Photovoltaic small business, commercial and tracking systems

Photovoltaic residential systems

Off-grid systems

#### **ABOUT CARLO GAVAZZI**

Carlo Gavazzi Automation is an international group active in designing, manufacturing and marketing electronic equipment targeted at the global markets of industrial and building automation.

Our history is full of firsts and our products are installed in a huge number of applications all over the world. With more than 80 years of successful operation, our experience is unparalleled.

We have our headquarters in Europe and numerous offices around the world.

Our R&D competence centres and production sites are located in Denmark, Italy, Lithuania, Malta and the People's Republic of China.

We operate worldwide through 22 of our own sales companies and also selected representatives in more than 65 countries, from the United States in the West to the Pacific Rim in the East.

Our core competence in automation spans three product lines: Sensors, Switches and Controls.

Our wide array of products includes sensors, monitoring relays, timers, energy management system, solid state relays, safety devices and fieldbus systems.

We focus our expertise on offering state-of-the-art product solutions in selected market segments.

Our customers include original equipment manufacturers of packaging machines, plastic injection moulding machines, food and beverage production machines, conveying and material handling equipment, door and entrance control systems, lifts and escalators, as well as heating, ventilation and airconditioning devices.





## DESIGNED TO MEET MARKET REQUIREMENTS

The increasing demand for energy, the availability and cost of oil and issues of pollution make alternative sources of renewable energy essential.

Sun and wind energy can be transformed into electricity that can be used directly or fed into the grid according to national regulations.

Renewable energy, in combination with energy efficiency, is the basis for sustainable development and respect for the environment in which we all live.

Carlo Gavazzi's wide expertise is focused on developing and offering

a package of products and devices for the Renewable Energy market, specifically photovoltaic power plants.

The growing development of cost effective solar energy technology has great potential to benefit our world. Solar technologies diversify the energy supply, reduce our dependence on fossil fuels, improve air quality and offset greenhouse gas emissions.


Carlo Gavazzi offers complete and modular solutions to monitor and control the efficiency of photovoltaic plants.

Our PV monitoring solution consists of Eos-Array, Eos-Web devices, depending upon the requirements and complexity of the photovoltaic plant.

The Eos-Array and Eos-Array Lite are modular systems, providing efficient local string control to the PV plant.

The Eos-Web is a web-server suitable for controlling and supervising small to medium installations as a stand-alone solution.

# Renewable Energy Photovoltaic parks



Web servers and dataloggers	Solar monitoring solutions	Surge arresters	Current transformers
VMU-C PV	Eos-Array	DSF	CTD
	•	DSB	TADK
		DSC	

In terms of scale and accessibility, solar parks represent the most economical option as regards planning and construction. Carlo Gavazzi products ensure an important contribution to the maximum capacity utilization of the solar electricity produced in photovoltaic power plants - both fixed

plants or plants with tracking systems, with 1 or 2 axes.

To complement photovoltaic modules, Carlo Gavazzi provides many components for a photovoltaic installation, especially for surge protection and plant monitoring.


Systems and devices to monitor and

control the efficiency of photovoltaic parks are essential to ensure that the solar investment is a solid and efficient one. The Eos-Web is the ideal solution for installations up to 1 MW.

The Eos-Web is a web server gathering data from string monitoring units such as the Eos-Array, inverters and







3-phase energy analysers	Interface protections	Environmental sensors	Pyranometers	Anemometers Wind vanes
EM26 96 EM24 DIN	PI-DIN	PVS-1 TEMPSOL IKE2000	PVS-2A	DWS-V DWS-D
		IKEZUUU		

energy meters. All plant information is available simply by using the PC web browser and any Internet connection. The Eos-Array is a comprehensive string control system, suitable for being integrated into both Eos-Web based solutions and standard SCADA software packages.

Based on glass optical fibre, the SIUFO is the solution for reliable communication where a traditional RS485 network cannot guarantee the correct level of immunity from electromagnetic emissions from inverters, substations or power wiring. Carlo Gavazzi's flexible and modular

PV monitoring architecture allows all the needs of investors, PV plant installers and maintenance services to be satisfied. Carlo Gavazzi application engineers and product specialists with solid expertise provide complete support, starting from project planning up to start up.



# Photovoltaic small business, commercial and tracking



Surge arresters	Solar monitoring solutions	Web server modules	Current transformers
DSF	Eos-Array	VMU-C	CTD
DSB	-	VMU-D	TADK
DSC			

Carlo Gavazzi provides everything for PV plant monitoring.

Eos-Array and Eos-Array Lite are systems composed of individual modular elements interacting with one another, providing efficient local control to the solar plant and ensuring effective information management in medium or high power plants.

Carlo Gavazzi provides the Eos-Web, where the VMU-C unit is a local web-based data management system which gathers measurements and status information from one or more inverters to your PC or to a centralised cloud monitoring solution based on the Eos-Server. With some rented roofs, wired internet is not available, but VMU-D

solves this problem by using diffuse mobile communication.

Carlo Gavazzi energy meters and analysers measure the energy produced and provided to the grid or locally consumed.

These meters can be supplied with MID certification (Annex D).

The energy produced at low voltage by a PV plant can be measured with a MID approved meter such as the EM210, EM24 or EM26.

When supplying energy to the grid, it is necessary to use a protection device installed between the generator and the power grid in order to grant the required voltage and/or frequency control.

Carlo Gavazzi's interface protections

are the most compact solutions currently available on the market.

DPC72 and PI-DIN protection add a control function to frequency derivative and event recording and are equipped with a large display for local information readout and a serial port for remote readout.

The surge arresters for direct and indirect lightning discharge complete the Carlo Gavazzi portfolio for the photovoltaic market.



### systems



3-phase			
energy	analysers		

EM271 / EM210 EM24 DIN EM26 96

#### **Energy storage systems**

PV energy is generated during the day, while the user generally consumes it during the evening. To minimise the flow between the plant and the grid, it is worth having an energy storage system on site.

In order to evaluate the amount of energy going through the battery system compared to the quantity sent to the grid, it is necessary to measure the flow in both these 2 directions. The information gathered allows the evaluation of the efficiency and payback of the system, but it is also useful to know the charging status of the battery pack.

Carlo Gavazzi offers two solutions for

# Interface protections

DPC72DM PI-DIN DPC02

# Environmental sensors

PVS-1 PVS-2A TEMPSOL

the energy storage systems for new plants and for retrofitted.

The CPA is the ideal solution for new renewable energy plants and storage systems, thanks to its smart mounting system and a comprehensive set of measurable variables, such as voltage, power, energy, frequency, power factor and THD, available through RS485/Modbus communication.

The EM271 and the relevant TCDxM split core current sensing units are frequently used in energy storage systems both new and retrofitted.

The EM271 is able to measure 2 loads in a single meter, allowing for time and space savings.

# Contactless power analysers

CPA300-V CPA300 CPA050



# Photovoltaic residential systems



Solar monitoring solutions

Web server modules

1-phase energy meters

3-phase energy analysers

Touch screens /
Data loggers

**Eos-Array Lite** 

**VMU-C PV** 

EM10 DIN EM11 DIN EM111/EM112 EM340/EM330 EM271/EM210 EM23 EM24 **SmartHUB** 

PV plants in residential areas are mostly grid connected installations.

Modules are set on roofs and the energy produced by the PV modules is delivered to the inverters and then fed into the public grid. Carlo Gavazzi offers a wide range of devices and components for the configuration of the electrical solar plant. Separate interface protection can be achieved with our wide range of monitoring relays such as the PI-DIN, DPC and DPC02, according to national norm requirements.

For energy metering you can use the EM1xx single-phase energy meter series or the EM2xx and EM3xx series for 3-phase PV residential system applications, all with LCD data display.


The real-time energy usage measurements, made via our touch screen and data logger SmartHUB, will lead to more efficiency in energy consumption needs, resulting in significant energy savings. The system reads and logs the energy consumption of the whole installation or of a single load. Data can be accessed anytime by means of a web-server/web-app and shown as instantaneous values, or in the form of graphs and/or diagrams.

For protection against surges and overvoltages it is possible to use the DSB or DSF surge arresters for both DC and AC lines. In the case of direct lightning discharge protection, the DSC series can be used.





# **Off-grid systems**



Surge arresters	Surge arresters	3-phase energy analysers	Anemometers Wind vanes	Digital modular indicators
DSC	DSB	EM23 DIN/EM24 DIN	DWS-V	UDM60
	DSF	EM210/EM330	DWS-D	
		EM340		




In remote areas renewable energy systems are gaining popularity, using stand-alone, off-grid plants with or without battery storage.

Carlo Gavazzi provides some additional components that can play an important role in such installations. DSC surge arresters provide protection for PV installations where an LPS (Lightning Protection System) is installed, hence subject to direct lightning strikes. This device is Type 1 and Type 2 approved.

DSB and DSF surge arresters can be used either on wind turbines or on PV installations. They are available for DC and AC networks and are Type 2, suitable for indirect lightning protection.

Wind speed and direction are extremely parameters. important Accurate measurements are necessary to keep the wind turbine structure under control. The Carlo Gavazzi anemometer DWS-V, with opto electronic detection, measures speed from 2 to 30 m/s. The sensor is designed with a dust and humidity seal, which makes the sensor impervious to all weather conditions. The micro-processor-based digital panel meter (UDM60), with its dual 6-dgt LCD indicator, displays the wind speed by measuring the input from the anemometer, while the energy produced is measured by a 3-phase energy analyser (EM23, EM24, EM210, EM330 or EM340).

# Renewable Energy The diagrams



#### VMU-C PV into a Photovoltaic Monitoring architecture

The VMU-C PV is the core solution for effective Photovoltaic Monitoring in applications of all sizes.


It collects measurements from Eos-Array string control units, energy meters and inverters; it stores information (variables and alarms) in its local database and displays it through its web-based graphical user interface.

The whole system set-up and operation is possible via the VMU-C's web interface, without any external software.

The VMU-C PV can exchange data with other systems by means of standard FTP/HTTP communication.







#### VMU-C PV's benefits at a glance

- No crash or compatibility problems due to different operative systems, different languages, libraries, etc.
- Improved IT security
- On-site database

- Application-focused software embedded inside industrial grade hardware: no need for a dedicated PC for monitoring
- Modular solution for additional inputs/ outputs
- Polling device, data-logger and Ethernet gateway in a single compact unit
- Optional modular modem for wireless Ethernet connections



# Renewable Energy Our product range

Solar monitoring solutions

Web servers and dataloggers

USB dongle connection modules



#### **Eos-Array / Eos-Array Lite**

- Modular local monitoring system for PV plant
- Up to 16 DIN module configuration
- Eos-ArraySoft, freeware configuration software
- Eos-Array can manage in addition to VMU-M unit up to: 1 VMU-P, up to 15 VMU-S and up to 7 VMU-O for a total of maximum 15 units



- The Eos-Array solution can be composed of: VMU-M the master unit and data logger; VMU-S the string controller; VMU-P the environment variable unit and VMU-O the I/O unit
- Eos-Array Lite is the answer to those photovoltaic applications where a less sophisticated monitoring solution is needed



#### VMU-C PV (Eos-Web)

- Dimensions: 2 DIN modules
- Micro PC with web server and web service capability
- Data and event logging capability
- Internal 4GB memory and 16GB SDHC card back-up memory (on request)
- Variables shown as graphs and numbers in formatted tables
- All data exports on HTML format compatible with Excel or other spread sheets
- Management up to 11 Eos-Array, 64 inverters + energy meters

#### **MAIN FEATURES**

- Efficiency calculation and control on different levels: string, BOS and Performance ratio and Yield indices
- Alarms control with automatic e-mailing and SMS management by means of VMU-D



#### VMU-D

- Dimensions: 2 DIN modules
- Compatible with Carlo Gavazzi approved 3G/4G USB modems
- Power supply:24 VDC (+/- 20%)
- Suitable for use with VMU-C and VMU-Y

#### **MAIN FEATURES**

- 3G or 4G Mobile Internet connectivity
- SMS alerting
- SMS commands

# Touch screens / Data loggers

## 1-phase energy meters

# 1-phase energy analysers



#### **SmartHUB**

- Energy data logging from meters and PV inverters
- Colour touch screen 7" (BTM-T7) and 4.3" (BTM-T4)
- Remote access through web browsers
- Alarms management



#### EM10 DIN / EM11 DIN

- Dimensions: 1 DIN module
- Single-phase energy meters with direct connection
- Current input up to 32 A
- Class 1 (kWh) acc. to EN62053-1
- Pulse open collector output



#### EM111

- Dimensions: 1 DIN module
- Backlit touch LCD
- Measurement of voltage, current, power, power factor and frequency
- Measuring inputs: 120 VAC, 230 VAC, 45 A
- Bi-directional energy metering, 7 digits, cl. B (EN50470)

#### **MAIN FEATURES**

- Wide screen display, 64 K colours
- 2 Ethernet port with integrated switch
- SD memory card slot
- USB host port
- Multistandard Modbus RTU serial communication port (selectable: RS485, RS422 or RS232)

#### **MAIN FEATURES**

- Direct measurement in a very compact housing to save space
- Suitable for measuring generated energy
- MID Annex D certification available
- CE, UL

- Self-powered
- Pulse output or as an alternative: RS485 Modbus, M-Bus
- Sealable terminal covers
- MID Annex D certification available (230 V)
- CE, UL (120 V)



## Our product range

1-phase energy analysers

3-phase energy analysers

3-phase energy meters



#### EM112

- Dimensions: 2 DIN modules
- Backlit touch LCD
- Measurement of voltage, current, power, power factor and frequency
- Measuring inputs: 120 VAC, 230 VAC, 100 A
- Bi-directional energy metering, 8 digits, cl. B (EN50470)



#### EM26 96

- Dimensions: 96 x 96 mm housing, only 45 mm behind the panel
- 3-phase energy meters with CT/VT connection
- Primary current input: 5 A
- Class 1 (kWh) acc. to EN62053-1
- Modbus communication port



#### EM23 DIN

- Dimensions: 4 DIN modules
- 3-phase energy meters with direct connection
- Current input for direct connection up to 65A
- Class 1 (kWh) acc. to EN62053-1
- Pulse open collector output
- Modbus communication port

#### **MAIN FEATURES**

- Self-powered
- Pulse output or as an alternative: RS485 Modbus, M-Bus
- Sealable terminal covers
- MID Annex D certification available (230 V)
- CE, UL (120 V)

#### **MAIN FEATURES**

- Energy analyser in a very compact housing to save space
- Suitable for measuring generated and consumed energy
- MID Annex D certification available

#### **MAIN FEATURES**

- Direct measurement in a very compact housing to save space
- MID Annex D certification available

# 3-phase energy analysers

## 3-phase energy analysers

# 3-phase energy analysers



#### EM24 DIN

- Dimensions: 4 DIN modules
- 3-phase energy analysers with direct connection or by CT
- Current input for direct connection up to 65A or external
- CT connection
- Class 1 (kWh) acc. to EN62053-1
- Pulse open collector output
- Modbus or M-bus communication port

#### EM330

- Dimensions: 3 DIN modules
- Backlit touch LCD
- Measurement of voltage, current, power, power factor and frequency
- Bi-directional energy metering on 2 8-digit counters, cl. B (EN50470)
- Measuring inputs: 3 x 230 (400) VAC, 5 A
- Auxiliary power supply: 90 to 260 VAC/DC

# 1100

#### EM340

- Dimensions: 3 DIN modules
- Backlit touch LCD
- Measurement of voltage, current, power, power factor and frequency
- Bi-directional energy metering on 2 8-digit counters, cl. B (EN50470)
- Measuring inputs: 3 x 230 (400) VAC, 65 A
- Power supply: self-powered

#### **MAIN FEATURES**

- Direct or external CT measurement in a very compact housing to save space
- Suitable for measuring generated and consumed energy
- MID Annex D certification available

#### **MAIN FEATURES**

- Pulse output or as an alternative: RS485 Modbus, M-Bus
- Sealable terminal covers
  - CE approved

- Pulse output or as an alternative: RS485 Modbus, M-Bus
- Sealable terminal covers
- CE approved and MID Annex D certification available

# Renewable Energy Our product range

3-phase energy analysers

Quick-fit 3-phase energy analysers

Current transformers



#### **EM210**

- Dimensions: 4 DIN modules or 72x72mm
- Installation: DIN-rail or panel mounting in a single product
- 3-phase energy meters with CT/VT connection
- Measurement of voltage, current, power, power factor and frequency
- Self-powered (MID version: 230 Vac power supply)
- Pulse output
- RS485 Modbus RTU, high speed (up to 115kbps)

#### **MAIN FEATURES**

- CE, cULus
- MID Annex D certification available
- Sealable terminal covers
- Very compact housing to save space



#### **EM271 + TCDM**

- Dimensions: 4-DIN rail module or 72 x 72 mm housing
- Two 3-phase energy analysers with sum function
- Current measurement by triple CT, split-core with RJ plug
- Equivalent to class 1 (kWh)
- Two pulse open collectors and serial RS485 outputs



#### CTD /TADK

- CTD: currents from 40 to 4000 A
- TADK2: 1-250 A
- Removable panel fixing clips
- DIN rail and panel mounting facility (TAD...)
- Double screw terminals (CTD)
- Sealable covers
- Case: ABS, self-extinguishing level UL 94 V-0
- Accuracy class: 0.5

#### **MAIN FEATURES**

- Save 90% of the installation time
- Voltage and serial bus daisy chain connection
- Fast and error-proof CT connection with CT ratio selfrecognition

#### **MAIN FEATURES**

- Wound primary (TADK2) / solid core or split-core (CTD)
- Compliance with EN60044-1 regulations
- Removable DIN rail mounting holder

Contactless power analysers

Contactless power analysers

Contactless power analysers



#### **CPA050**

- Dimensions: 63 x 46 x 25 mm (without connectors);
   DIN rail and panel mounting
- Power analyser
- 1-phase AC( from 1 to 400 Hz) or DC
- Power supply from 9 to 30 VDC



#### **CPA300**

- Dimensions: 99 x 89 x 30 mm (without connectors);
   DIN rail and panel mounting
- Power analyser
- 1-phase AC( from 1 to 400 Hz) or DC
- Power supply from 9 to 30 VDC



#### **CPA300-V**

- Dimensions: 99 x 89 x 30 mm (without connectors);
   DIN rail and panel mounting
- Current transducer for PV installations up to 1500 VDC
- 1-phase AC( from 1 to 400 Hz) or DC
- Power supply from 9 to 30 VDC

#### MAIN FEATURES

- Contactless Hall effect sensing for current (15 mm hole diameter)
- True RMS AC and DC monitoring
- Voltage range: 800 VAC, 1000 VDC
- Current range: 50 AAC, 50 ADC

#### **MAIN FEATURES**

- Contactless Hall effect sensing for current (33 mm hole diameter)
- True RMS AC and DC monitoring
- Voltage range: 800 VAC, 1000 VDC
- Current range: 300 AAC, 400 ADC

- Contactless Hall effect sensing for current
- Current range: 300 AAC, 400 ADC
- Modbus RS485 and analog output



## Our product range

Interface Interface Interface protections protections protections



#### PI-DIN

- Dimensions: 90 x 71x 66 mm
- Interface protection monitoring relay for 1-phase or 3-phase systems with or without neutral
- Voltage and frequency protection
- 4 inputs (CEI-021) or 2 inputs (VDE4105), 2 outputs
- Measure V, Hz
- Auxiliary power supply 230 VAC or 24 VDC
- Data logger with 10 last events logging



#### DPC02DM...B005

- Dimensions: 45 x 80 x 99.5 mm
- DIN rail mounting
- Power: 208 to 240 VAC or 380 to 415 VAC
- Protection degree: IP20
- Output: programmable relays 2 SPDT N.E. or 1 DPDT
   N.E.



#### DPC72DM

- Dimensions: 90 x 71 x 65 mm, 4 DIN module
- DIN rail mounting sealable housing
- Values and intervention time programming
- Serial port RS485 Modbus RTU
- Protection degree: IP50
- Output: 1 DPDT N.E.

#### **MAIN FEATURES**

- Settings, menù and logger navigation by means of front joystick
- Password protected settings, Dual Function Alarm LED
- Certified according to Italian CEI 0-21 2012-06 and V1:2012-12 and German VDE-AR-N-4105:2011-0
- · Anti-islanding on VDE model

#### **MAIN FEATURES**

 One-phase and three-phase relays for monitoring maximum and minimum voltage and frequency, phase sequence and phase failure. It checks that frequency and voltage are within the limits set by the utility

#### **MAIN FEATURES**

- One-phase and three-phase relays for monitoring maximum and minimum voltage and frequency, phase sequence and phase failure. It checks that frequency and voltage are within the limits set by the utility
- Record of the last 10 events (date, time and reason for the event)

Surge	Surge	Surge
arresters	arresters	arresters



#### **DSC**

- Dimensions: 90 x 72 x 70 mm
- Class I and II
- Protective element: High Energy MOV
- High surge discharge rating: limp = 12.5 kA per pole
- Housing: compact design



#### DSB / DSF

- Dimensions: 90 x 36 x 72 mm
- Class II
- Available for PV and AC installations
- Models for communication lines
- Optional remote monitoring
- For DIN rail mounting



#### DSB51XXDP

- Dimensions: 90 x 12 x 71.5 mm DIN-rail housing
- 15 VDC nominal voltage
- 10 kA Inom, 20 kA Imax
- Rated spark overvoltage 184V to 276V
- C1/C2/C3 according to IEC 61643-21

#### **MAIN FEATURES**

- Specifically designed for PV installations with or without LPS (Lightning Protection System)
- Location of use: photovoltaic system PV module side

#### **MAIN FEATURES**

- NO backup fuse required
- Appr. Acc. to IEC61643-11 and UTE C61-740-51
- Complies with prEN50539-11

- Designed for Dupline® communication lines
- Three stage topology with dual GDT
- Socket with replaceable cartridge

# Renewable Energy Our product range

DIN rail DC/DC converters

Switching power supplies

Digital modular indicators



#### DCC 24151K-D

- DIN rail mounting
- Ultra wide input: 100 ~ 1000 VDC
- 24VDC output 15W
- High efficiency up to 80%
- Wide temperature range -40 to +70° C
- Output over voltage and short circuit protection
- Reverse input protection



#### **SPM**

- DIN rail housing
- Universal input 90-264 VAC / 120- 370 VDC
- Single phase and battery charger versions available
- Approvals/Marks: UL, cUL listed and TÜV/CE approved



#### UDM60 / UDM40 / USC

- Dimensions: 48 x 96 x 105 mm
- Modular Controller for pulse signals (UDM60)
- Dual 6-DGT
- 0.001% RDG basic accuracy
- NPN, PNP, NAMUR, TTL, Pick-up, free of voltage contacts and AC signal inputs
- Multi-input modular instrument (UDM40, USC)
- 4-DGT three colour LED
- 0.1% RDG basic accuracy
- Dual rate, speed, frequency and period measurement (0.001 Hz to 50 kHz)

#### **MAIN FEATURES**

- Widely used in Photovoltaic power generation with high voltage inverters
- It provides stable operating voltage to low voltage DC equipment

#### **MAIN FEATURES**

- Operating temperature w/o derating -25°C to +60°C
- Short circuit and Overload protection
- High efficiency (up to 89%)

#### **MAIN FEATURES**

 Digital panelmeter for current, voltage, temperature, resistance, rate, frequency, speed and period measurements

## Temperature sensors

## Irradiation sensors

#### **Pyranometers**



#### TEMPSOL / IKE20001K

- Temperature Pt100 or Pt1000 (TEMPSOL)
- Temperature Pt1000 (IKE20001K)
- $\pm 0.3^{\circ}$ C connection type
- 2 wire connection type



#### PVS-1

- Dimensions: 57 x 48 x 15 mm (not including clamp)
- Sensor type: crystalline silicon cell
- No need for external power supply (self-powered)
- Long lasting 3% accuracy, thanks to a special antiageing treatment
- Calibration process according to IEC 60904-2 and 60904-4
- Two available versions: 4-20 mA output / 0-80 mV output



#### **PVS-2A**

- Dimensions: 162 x 215 x 40 mm (not including clamp)
- 2nd class thermopile pyranometer
- 4-20 mA output for reliable connections
- Calibration certificate according to ISO 9847

#### **MAIN FEATURES**

- Specifically design to measure the temperature of PV panels (TEMPSOL)
- For air temperature measurement in PV plants (IKE20001k)

#### **MAIN FEATURES**

- Long life rugged aluminium case
- UV resistant resin encapsulation
- Fast installation, thanks to the clamping system designed to easily fit the photovoltaic module's frame

- Compact and rugged IP67 aluminium case
- Compliant with WMO (World Meteorological Organization) for environmental monitoring
- Compliant with ISO9060 and IEC17025 for photovoltaic monitoring



## Our product range

Anemometers /	Accessory	Accessory
Wind vanes	modules	modules



#### DWS-D / DWS-V

- Rotor size: 145 mm
- PNP & NPN open collector output in one unit
- Rotor: black painted stainless steel
- Wind vane for relative wind direction (0 and 90 degree internals -DWS-D-DAC13) (+/-7 degree of wind direction, left/right wind indication DWS-D-DDC13)
- Anemometer with opto-electronic detection (DWSV...)
- Measuring range 2 to 30 m/s
- Current source output 10 to 28 VDC supply

#### **MAIN FEATURES**

- Opto-electronic detection
- All inputs and outputs are protected against reverse polarity and transients
- Dust sealed stainless steel ball bearing



#### **SIUFO**

- 4-DIN size; DIN-rail mounting
- SIUF01: RS485 to single loop fibre optic conversion
- SIUFO2: RS485 to double loop fibre optic conversion
- Power supply from 12 to 18VAC or from 10 to 24VDC



#### VMU-O AT/VMU-AT

- Eos-Array standard expansion I/O module (VMU-O AT)
- Plastic optical fiber sensor (VMU-AT)
- Up to 3 VMU-AT modules per VMU-O AT
- Up to 1 VMU-O AT per Eos-Array

#### **MAIN FEATURES**

- Modbus/Jbus(RTU) compliant
- Wire to optical fiber and optical fiber to wire conversion
- Status LED
- Compatible with Multimode Optical fiber
- Up to 160 transceivers on the same bus
- Up to 247 Modbus addresses, automatically managed
- Baudrate and RS485 parameters selectable by dipswitches

- Plastic optical fiber loops (up to 200 m) to protect PV modules
- Plug'n play set-up (optical fiber cutter included)
- Anti-theft alarm events integrated in the Eos-Array and VMU-C PV solutions
- 3 digital inputs, 1 relay output (VMU-0 AT)
- 1 optical fiber loop, digital output (VMU-AT)

# **Notes**



#### **OUR SALES NETWORK IN EUROPE**

#### AUSTRIA

Carlo Gavazzi GmbH Ketzergasse 374, A-1230 Wien Tel: +43 1 888 4112 Fax: +43 1 889 10 53 office@carlogavazzi.at

#### BELGIUM

Carlo Gavazzi NV/SA Mechelsesteenweg 311, B-1800 Vilvoorde Tel: +32 2 257 4120 Fax: +32 2 257 41 25 sales@carlogavazzi.be

#### DENMARK

Carlo Gavazzi Handel A/S Over Hadstenvej 40, DK-8370 Hadsten Tel: +45 89 60 6100 Fax: +45 86 98 15 30 handel@gavazzi.dk

#### FINLAND

Carlo Gavazzi OY AB Ahventie, 4 B FI-02170 Espoo Tel: +358 9 756 2000 myynti@gavazzi.fi

#### FRANC

Carlo Gavazzi Sarl
Zac de Paris Nord II, 69, rue de la Belle Etoile,
F-95956 Roissy CDG Cedex
Tel: +33 1 49 38 98 60
Fax: +33 1 48 63 27 43
french.team@carlogavazzi.fr

#### GERMANY

Carlo Gavazzi GmbH Pfnorstr. 10-14 D-64293 Darmstadt Tel: +49 6151 81000 Fax: +49 6151 81 00 40 info@gavazzi.de

#### **GREAT BRITAIN**

Carlo Gavazzi UK Ltd 4.4 Frimley Business Park, Frimley, Camberley, Surrey GU16 7SG Tel: +44 1 276 854 110 Fax: +44 1 276 682 140 sales@carlogavazzi.co.uk

#### ITALY

Carlo Gavazzi SpA Via Milano 13, I-20020 Lainate Tel: +39 02 931 761 Fax: +39 02 931 763 01 info@gavazziacbu.it

#### **NETHERLANDS**

Carlo Gavazzi BV Wijkermeerweg 23, NL-1948 NT Beverwijk Tel: +31 251 22 9345 Fax: +31 251 22 60 55 info@carlogavazzi.nl

#### NORWAY

Carlo Gavazzi AS Melkeveien 13, N-3919 Porsgrunn Tel: +47 35 93 0800 Fax: +47 35 93 08 01 post@gavazzi.no

#### PORTUGAL

Carlo Gavazzi Lda Rua dos Jerónimos 38-B, P-1400-212 Lisboa Tel: +351 21 361 7060 Fax: +351 21 362 13 73 carlogavazzi@carlogavazzi.pt

#### SPAIN

Carlo Gavazzi SA Avda. Iparraguirre, 80-82, E-48940 Leioa (Bizkaia) Fel: +34 94 480 4037 Fax: +34 94 431 6081 gavazzi@gavazzi.es

#### **SWEDEN**

Carlo Gavazzi AB V:a Kyrkogatan 1, S-652 24 Karlstad Tel: +46 54 85 1125 Fax: +46 54 85 11 77 info@carlogavazzi.se

#### **SWITZERLAND**

Carlo Gavazzi AG Verkauf Schweiz/Vente Suisse Sumpfstrasse 3, CH-6312 Steinhausen Tel: +41 41 747 4535 Fax: +41 41 740 45 40 info@carlogavazzi.ch

#### **OUR SALES NETWORK IN THE AMERICAS**

#### USA

Carlo Gavazzi Inc. 750 Hastings Lane, Buffalo Grove, IL 60089, USA Tel: +1 847 465 6100 Fax: +1 847 465 7373

sales@carlogavazzi.com

#### CANADA

Carlo Gavazzi Inc. 2660 Meadowvale Boulevard, Mississauga, ON L5N 6M6, Canada Tel: +1 905 542 0979 Fax: +1 905 542 22 48 gavazzi@carlogavazzi.com

#### MEXICO

Carlo Gavazzi Mexico S.A. de C.V. Calle la Montoña no. 28, Fracc. Los Pastores Naucalpan de Juárez, EDOMEX CP 53340 Tel & Fax: +52.55.5373.7042 mexicosales@carlogavazzi.com

#### RD A 711

Carlo Gavazzi Automação Ltda.Av. Francisco Matarazzo, 1752 Conj 2108 - Barra Funda - São Paulo/SP Tel: +55 11 3052 0832 Fax: +55 11 3057 1753 info@carlogavazzi.com.br

#### **OUR SALES NETWORK IN ASIA AND PACIFIC**

#### SINGAPORE

Carlo Gavazzi Automation Singapore Pte. Ltd 61 Tai Seng Avenue #05-06 Print Media Hub @ Paya Lebar iPark Singapore 534167 Tel: +65 67 466 990 Fay: +65 67 461 980

Fax: +65 67 461 980 info@carlogavazzi.com.sg

#### MALAYSIA

MALTA

Carlo Gavazzi Automation (M) SDN. BHD. D12-06-G, Block D12, Pusat Perdagangan Dana 1, Jalan PJU 1A/46, 47301 Petaling Jaya, Selangor, Malaysia.

Tel: +60 3 7842 7299 Fax: +60 3 7842 7399 sales@gavazzi-asia.com

#### CHINA

Carlo Gavazzi Automation (China) Co. Ltd. Unit 2308, 23/F., News Building, Block 1,1002 Middle Shennan Zhong Road, Shenzhen, China Tel: +86 755 83699500

#### Tel: +86 755 83699500 Fax: +86 755 83699300 sales@carlogavazzi.cn

#### HONG KONG

Carlo Gavazzi Automation Hong Kong Ltd. Unit 3 12/F Crown Industrial Bldg., 106 How Ming St., Kwun Tong, Kowloon, Hong Kong Tel: +852 23041228 Fax: +852 23443689

#### **OUR COMPETENCE CENTRES AND PRODUCTION SITES**

#### DENMARK

Carlo Gavazzi Industri A/S Hadsten

#### CHINA

Carlo Gavazzi Automation (Kunshan) Co., Ltd. Kunshan

Carlo Gavazzi Ltd Zejtun

#### ITALY

Carlo Gavazzi Controls SpA Belluno

#### LITHUANIA

Uab Carlo Gavazzi Industri Kaunas Kaunas

#### **HEADQUARTERS**

Carlo Gavazzi Automation SpA Via Milano, 13 I-20020 - Lainate (MI) - ITALY Tel: +39 02 931 761 info@gavazziautomation.com



CARLO GAVAZZI Automation Components

Energy to Components!

www.gavazziautomation.com

