

Amphenol

High Speed Interconnects




I/O Products

Now you're connected

Amphenol High Speed Interconnects

THE COMPANY

Amphenol is a global provider of interconnect solutions to the designers and manufacturers of worldwide networking systems. With our design creativity and cost effectiveness, Amphenol leads the way in interconnect development for internet equipment, infrastructure, enterprise networks, and appliances. Whether industry standard or specific designs are required, Amphenol provides customers with products capable of performing at the leading edge of today's high speed technology. Our expertise in understanding and supporting our customers' various design needs has earned Amphenol a reputation of excellence and quality among the world's leading users of high speed components.





HIGH SPEED CONNECTORS

Amphenol offers a full range of high speed connectors with data rates ranging from 1 Gbps to 240 Gbps and beyond, meeting our customers' various high speed connector requirements. Products include the ExpressPort™ Series (SFP+, QSFP+, CXP), SFP, QSFP, Mini-SAS, Mini-SAS HD, XFP, CFP2, and CFP4.

BENEFITS

- Increased platform density for scaling improved performance in a defined physical space
- Servers that can scale I/O and processing power independently
- Racks of servers that can be managed as one autonomous unit
- Servers that can share I/O resources
- True "plug-and-play" I/O connectivity
- Extensive range of SFP/IPF connector and cage solutions to support Fiber Channel, Infiniband, Ethernet, and Gigabit technology
- Next generation ExpressPort™ connectors provide premium level performance for SFP+, CXP, and QSFP+ interfaces
- Data speeds of ExpressPort™ connectors can reach up to 40 Gbps per channel

Table of Contents

ExpressPort SFP+ Series				
	UE76 Series	1xN Connector	4	
	UE77 Series	1xN Cage	4	
	UE86 Series	2xN Combo	6	
SFP Series				
	UE75 Series	1xN Connector	8	
	U77 Series	1xN Cage	8	
	UE78/UE86 Series	2xN Combo	10	
ExpressPort QSFP+ / E-Series / H-Series / QSFP Series				
	FS1 Series	1xN Connector	12	
	U90 Series	1xN Cage	12	
	U90 Series	2xN Combo	14	
CXP Series				
	U91 Series	CXP Combo	16	
Mini-SAS				
	FS1 Series	Connector	18	
	FSX Series	Cage	18	
Mini-SAS HD				
	U92 Series	HD Combo	20	
XFP Series				
	UE75 Series	Connector	22	
	U79 Series	Cage	22	
CFP2 / CFP4				
	U99 Series	Connector	24	
	U98 Series	Cage	24	


ExpressPort™ SFP+ 1xN




UE76-A20-3010T

Amphenol's ExpressPort™ SFP+ 1xN connector, when combined with the ExpressPort™ SFP+ cage, provides data transfer speeds of up to 25 Gbps. The design of the ExpressPort™ SFP+ connector minimizes impedance discontinuities and reflections at high data rates, and provides a 10 to 20 dB improvement in Near-End Crosstalk.


Amphenol's unique ExpressPort™ SFP+ cage construction features EMI shielding available in the form of metal spring fingers or elastomeric gaskets. These cages also eliminate ventilation holes near the front of the cage to prevent potential catch points for the mating module EMI springs. Additional features available include lightpipes (which can be purchased with cages or separately), heat sinks, and other custom features.



U77-A441M-2081



U77-C1419-2001



U77-C261M-2081

Specification Highlights

The interconnect system is comprised of a cage assembly which is used with 20-position SFP+ connectors complying with SFF-8081 and SFF-8083. Ganged cages comply with industry standard SFF-8433.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Industry Standard EIA-364

Mechanical Characteristics

- Accepts Multiple Transceivers per SFF-8431
- Compliant Press-Fit Pins or Solder Tails (for 1x1 Cages)
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 3.3 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max

Packaging

- Tape and Reel Packaging: Connector or 1x1 Cage
- Tray Packaging: Cage of all Sizes
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel or Tin
 - o Light Pipe: Optical Grade Polycarbonate
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Gold or Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -55°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations (Rows x Ports per Row)

- | | |
|-------|-------|
| • 1x1 | • 1x2 |
| • 1x3 | • 1x4 |
| • 1x6 | |

Options

- Dust Cover
- Round Light Pipe
- Heat Sink
- EMI Shielding
 - o Metal Spring Fingers
 - o Conductive Elastomeric Gasket



U77-C461M-2081



UE76-A20-3000

Ordering Information


ExpressPort™ SFP+ Connector

UE76 - A 20 - X X X X X	
UE76	SERIES DESIGNATION (RoHS)
A	STYLE A - R/A Single Surface Mount Connector
20	NUMBER OF POSITIONS 20 - 20 Positions
X	CONTACT PLATING 2 - 30 μ" Gold Plating on Mating Area; Gold Flash on Termination 3 - 30 μ" Gold Plating on Mating Area; Matte Tin Plating on Termination 5 - 15 μ" Gold Plating on Mating Area; Gold Flash on Termination 6 - 15 μ" Gold Plating on Mating Area; Matte Tin Plating on Termination
	PACKAGING J - Tape and Reel Packaging (480 per Reel) T - Tape and Reel Packaging (500 per Reel)
	LUBRICANT OPTION 0 - Non Lubricated 1 - Lubricant Added
	OPTION 2 0 - Standard 1 - Resonance Cancellation Features
	OPTION 1 0 - Standard 6 - 25 Gbps

ExpressPort™ SFP+ Cage

U77 - X X X X X - X X X X	
U77	SERIES DESIGNATION (RoHS)
X	STYLE A - One Row C - One Row Cage; Light Pipe Combo (on Top) E - One Row Cage; Heat Sink Combo (Fin) F - One Row Cage; 1 degree Angle (1x1 Only)
X	NUMBER OF PORTS IN ROW 1 - Single in Row 2 - Inline 1x2 3 - Inline 1x3 4 - Inline 1x4 6 - Inline 1x6
X	CHASSIS GROUNDING 3 - Metal Spring Fingers (No Bottom Latch Cover) 4 - Elastomeric Gasket 6 - Metal Spring Fingers (1 Piece Design Bottom Latch Cover)
X	HEAT SINK / LIGHT PIPE OPTION 1 - No Heat Sink / Light Pipe Option 2 - Heat Sink Option 3 - Light Pipe Option (for 1xN Cage Only)
	PACKAGING 1 - Tray Packaging (ACC Re-Packed) T - Tape and Reel Packaging (for 1x1 Only)
	OPTION 1 0 - Standard 7 - Cage with Extra Bottom Spring Fingers, No Bottom Mid G-Pins 8 - Cage with Half-Moon Mid G-Pins 9 - Cage with Extra Bottom Spring Fingers and Half Moon Mid G-Pins
	DUST COVER OPTION 0 - Without Dust Cover D - With Dust Cover (Shipped Loose)
	PLATING 1 - Bright Tin (for Wave Solder) 2 - Nickel 3 - Matte Tin (for Reflow 245 degrees)
	PCB MOUNTING OPTION X - Various Options Available Consult Sales or Website for Details

ExpressPort™ SFP+ 2xN



UE86-D2527-20321

Amphenol's ExpressPort™ SFP+ 2xN Combo provides data transfer speeds of up to 25 Gbps per port. ExpressPort™ SFP+ 2xN Combos consist of an integrated stacked connector system and a cage with compliant press-fit pins.

Amphenol's unique ExpressPort™ SFP+ cage construction features EMI shielding available in the form of an elastomeric gasket or metal spring fingers. These cages also eliminate ventilation holes near the front of the cage to prevent potential catch points for the mating module EMI springs.



UE86-K8427-20321



UE86-D1427-10321



UE86-D4627-10321

Specification Highlights

The interconnect system is comprised of a 2-row stacked, 20-position, 0.8 mm pitch SFP+ connector and cage assembly as one unit with all press-fit construction.

General Characteristics

- RoHS Compliant
- Press-fit Cage and Connector Combo for min 1.57 +/- 10% mm (0.0625") PCB Thickness
- Industry Standard EIA-364

Mechanical Characteristics

- Card Entry Slot Accepts 1.0 mm Thick Integrated Circuit Cards
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 3.3 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max

Packaging

- Tray Packaging: Cage and Connector Assembly
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel or Tin
 - o Light Pipe: Optical Grade Polycarbonate
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -55°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations (Rows x Ports per Row)

- | | |
|-------|-------|
| • 2x1 | • 2x2 |
| • 2x4 | • 2x5 |
| • 2x6 | • 2x8 |

Options

- Dust Cover
- Light Pipe
 - o 4 Light Pipes per 2x1
 - o 2 Inner Light Pipes per 2x1
 - o 2 Outer Light Pipes per 2x1
- EMI Shielding
 - o Metal Spring Fingers
 - o Conductive Elastomeric Gasket



UE86-K2427-10321



UE86-K442C-20321

Ordering Information

ExpressPort™ SFP+ 2xN Combo (Cage / Connector)

UE86 SERIES DESIGNATION

UE86 - RoHS SFP+ Cage and Connector (Lead Free)

X

STYLE

B - 2xN, No Light Pipe
D - 2xN, Small Light Pipe Openings
K - 2xN, Large Light Pipe Openings
L - 2xN, Low Profile Combo (No Light Pipe)

X

NUMBER OF PORTS IN ROW

1 - 2x1
2 - 2x2
4 - 2x4
5 - 2x5
6 - 2x6
8 - 2x8

X

CHASSIS GROUNDING

4 - Elastomeric Gasket
5 - Elastomeric Gasket, Bottom Mylar Tape
6 - Metal Spring Fingers

X

MOUNTING TYPE: CONNECTOR

2 - Standard Press Fit Pins (12 Gbps)
5 - Small Press Fit Pins for High Speed Termination (16 Gbps)

UE86 - X X X X X - X X X X 1

PACKAGING

1 - Tray Packaging (Stacked)

1

PLATING OPTION: CAGE

1 - Bright Tin
2 - Nickel
3 - Matte Tin

X

PLATING OPTION: CONNECTOR

X - Various Options Available
Consult Sales or Website for Details

X

DUST COVER OPTION

0 - Without Dust Cover
D - With Dust Cover (Shipped Loose)

X

LIGHT PIPE OPTION

0 - No Light Pipe
1 - 4 Light Pipes per 2x1
2 - 2 Inner Light Pipes per 2x1
3 - 2 Outer Light Pipes per 2x1

X

MOUNTING TYPE: CAGE

7 - Standard 2xN Cage
C - Enhanced EMI Cage

X




Amphenol's SFP interconnect system consists of a 20-position connector enclosed in a metal cage mounted to a host PCB.


Amphenol's single port SFP connectors are rated up to 6 Gbps. The connector accepts multiple transceivers per INF-8074i and combines, transmits, and receives functions in a low cost, compact, and flexible format. The cages have a two-piece construction with enhanced transceiver mating tabs available in a press-fit version or a solder tail version. Longer and shorter pins are available as custom options. Single row versions (1xN) consist of SMT connectors used with a separate single row cage (press-fit or solder tail).



U77-A2114-2001



U77-A4114-2001



U77-A4113-0100

Specification Highlights

The interconnect system is comprised of a cage assembly which is used with 20-position SFP connectors complying with MSA Agreement INF-8074i.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Industry Standard EIA-364

Mechanical Characteristics

- Accepts Multiple Transceivers per INF-8074i
- Compliant Press-Fit Pins or Solder Tails (1x1 Cages)
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 3.3 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max
- Spring Fingers for Superior EMI Grounding

Packaging

- Tape and Reel Packaging: Connector or Cage
- Tray Packaging: Cage of all Sizes
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel or Tin
 - o Light Pipe: Optical Grade Polycarbonate
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
 - o EMI Ground Tabs: Stainless Steel
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Gold or Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -55°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations (Rows x Ports per Row)

- | | |
|-------|-------|
| • 1x1 | • 1x2 |
| • 1x4 | • 1x6 |

Options

- Dust Cover
- Light Pipe
- Heat Sink (Standard Fin for Final Cage Combo)
- Enhanced EMI Performance Cage



U77-C6114-2011



U77-E1128-2001

Ordering Information

SFP Connector

UE75 - A 20 - X 0 0 X X

UE75 SERIES DESIGNATION (RoHS)

A

STYLE

A - R/A Single Surface Mount Connector

20

NUMBER OF POSITIONS

20 - 20 Positions

X

CONTACT PLATING

2 - 30 μ " Gold Plating on Mating Area; Gold Flash on Termination
3 - 30 μ " Gold Plating on Mating Area; Matte Tin Plating on Termination
5 - 15 μ " Gold Plating on Mating Area; Gold Flash on Termination
6 - 15 μ " Gold Plating on Mating Area; Matte Tin Plating on Termination

PACKAGING

J - Tape and Reel Packaging (480 per Reel)
T - Tape and Reel Packaging (500 per Reel)

LUBRICANT OPTION

0 - Non Lubricated
1 - Lubricant Added

0 - Standard

OPTION 1

0 - Standard

SFP Cage

U77 - X X X X X - X X X X

U77 SERIES DESIGNATION

X

STYLE

A - One Row
C - One Row Cage; Light Pipe Combo (on Top)
E - One Row Cage; Heat Sink Combo
F - One Row Cage; 1 degree Angle (For 1x1 Only)

X

NUMBER OF PORTS IN ROW

1 - Single in Row
2 - Inline 1x2
4 - Inline 1x4
6 - Inline 1x6

X

CHASSIS GROUNDING

1 - Metal Grounding Tabs
2 - Inner and Outer Flexible Spring Fingers

X

HEAT SINK / LIGHT PIPE OPTION

1 - No Heat Sink / Light Pipe
2 - Heat Sink
3 - Light Pipe (for 1xN Cage Only)

PACKAGING

1 - Tray Packaging (ACC Re-Packed)
T - Tape and Reel Packaging (for 1x1 Only)

OPTION 1

0 - Standard
1 - Cage With Light Pipe on Top
8 - Cage with Half Moon Mid G-Pins

DUST COVER OPTION

0 - Without Dust Cover
D - With Dust Cover (Shipped Loose)

PLATING

1 - Bright Tin (for Wave Solder)
2 - Nickel
3 - Matte Tin (for Reflow 245 degrees)


PCB MOUNTING OPTION

X - Various Options Available
Consult Sales or Website for Details


SFP 2xN

Amphenol's SFP interconnect system consists of a 20-position connector enclosed in a metal cage mounted to a host PCB.


Amphenol's stacked SFP combos are rated up to 6 Gbps. The connector accepts multiple transceivers per INF-8074i and combines, transmits, and receives functions in a low cost, compact, and flexible format. The cages have a two-piece construction with enhanced transceiver mating tabs available in a press-fit version or a solder tail version. Longer and shorter pins are available as custom options. Stacked versions (2xN) consist of a 2-row cage with integrated 2-row connectors.



UE78-B8126-00321



UE78-L1126-00321



UE78-B2127-00321

Specification Highlights

The interconnect system is comprised of a cage assembly which is used with 20-position SFP connectors complying with MSA Agreement INF-8074i.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Industry Standard EIA-364

Mechanical Characteristics

- Accepts Multiple Transceivers per INF-8074i
- Compliant Press-Fit Pins or Solder Tails (1x1 Cages)
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 3.3 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max
- Spring Fingers for Superior EMI Grounding

Packaging

- Tape and Reel Packaging: Connector or Cage
- Tray Packaging: Cage of all Sizes
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel or Tin
 - o Light Pipe: Optical Grade Polycarbonate
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
 - o EMI Ground Tabs: Stainless Steel
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Gold or Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -55°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations (Rows x Ports per Row)

- | | |
|-------|-------|
| • 2x1 | • 2x2 |
| • 2x4 | • 2x5 |
| • 2x6 | • 2x8 |

Options

- Dust Cover
- Light Pipe
- Heat Sink (Standard Fin for Final Cage Combo)
- Enhanced EMI Performance Cage



UE86-K2127-10321



UE78-B4127-00321

Ordering Information

SFP 2xN Combo (Cage / Connector)

UEXX - X X X 2 X - X X X X 1

UEXX

SERIES DESIGNATION

- UE78 - Standard SFP Cage and Connector (RoHS)
- UE86 - Standard SFP Cage and Connector with Light Pipes (RoHS)

X

STYLE

- B - Stacked Connector and Cage Combo (UE78 Series)
- D - 2xN, Small Light Pipe Openings (UE86 Series)
- K - 2xN, Large Light Pipe Openings (UE86 Series)
- L - 2xN, Low Profile Combo (No Light Pipe) (UE78 Series)

X

NUMBER OF PORTS IN ROW

- 1 - 2x1
- 2 - 2x2
- 4 - 2x4
- 5 - 2x5
- 6 - 2x6
- 8 - 2x8

X

EMI SHIELDING

- 1 - Standard
- 2 - Bottom Mylar Tape, No Mid Ground Pins
- 3 - No Mid Ground Pins

2

- 2 - Standard

PACKAGING

- 1 - Tray Packaging (Stacked)

PLATING OPTION: CAGE

- 1 - Bright Tin (for Wave Soldering)
- 2 - Nickel
- 3 - Matte Tin (for SMT Soldering)

PLATING OPTION: CONNECTOR

- X - Various Options Available
- Consult Sales or Website for Details

DUST COVER OPTION


- 0 - Without Dust Cover
- D - With Dust Cover (Shipped Loose)

HEAT SINK / LIGHT PIPE OPTION


- 0 - No Heat Sink or Light Pipe
- X - Various Options Available
- Consult Sales or Website for Details

PCB MOUNTING OPTION

- 7 - Standard
- X - Various Customer Specific Options Available
- Consult Sales or Website for Details



UE78 Series Footprint



UE86 Series Footprint

ExpressPort™ QSFP+ / QSFP



U90-C101-3000

The ExpressPort™ QSFP+/QSFP interconnect system is comprised of a 38-position 0.8 mm pitch SMT connector, and a press-fit cage designed to comply with the Quad Small Form-factor Pluggable (QSFP) Transceiver intended for external connections. High speed serial interconnect applications include clusters, servers, and storage devices.

The ExpressPort™ QSFP+ E-Series and H-Series connector families are rated to 28 Gbps and 40 Gbps respectively per channel (4x28), featuring a stamped and formed contact design providing improved mechanical durability. This connector features an integrated grounding structure and resonance dampening features for superior crosstalk performance. The contact design is optimized for a smooth impedance profile resulting in improved SI performance.

Specification Highlights

The QSFP interconnect system is comprised of a press-fit cage assembly which is used with 38-position connectors complying with QSFP Transceiver Specifications.

Mechanical Characteristics

- Cage is Keyed According to QSFP MSA
 - QSFP+: SFF-8436
 - E-Series: SFF-8672
 - H-Series: TBD
- Durability: 250 Mating Cycles min
- Connector Insertion Force: 40 N max
- Connector Withdrawal Force: 30 N max

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 30 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max

Packaging

- Tape and Reel Packaging: Connector or 1x1 Cage
- Tray Packaging: Cage of all Sizes
- Bulk Packaging: Dust Cover

Temperature Rating

- Operating Temperature: -40°C to +85°C
- Storage Temperature: -40°C to +85°C

Configurations (Rows x Ports per Row)

- 1x1 • 1x2 • 1x3 • 1x4 • 1x6

Options

- Dust Cover
- Light Pipe
 - Round 1.4 mm
 - Square 2.6x2.6 mm
- Heat Sink
- Cage Design
 - Through or Behind the Bezel

Materials

- Cage
 - Base Material: Copper Alloy
 - Plating: Nickel or Tin
 - Light Pipe: Optical Grade Polycarbonate
 - Heat Sink: Aluminum Alloy
 - Heat Sink Clip: Stainless Steel
 - Dust Cover: Thermoplastic
- Connector
 - Contact Base Material: Copper Alloy
 - Contact Plating: Gold on Mating Area, Matte Tin on Terminations and Grounding Tabs
 - Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Signal Integrity Characteristics

QSFP, ExpressPort™ QSFP+

- Return Loss: -12 dB
- Near-End Isolation: -30 dB (frequencies up to 3 GHz)
- Insertion Loss: -1 dB max
- Rise Time for Impedance Measurement: 35 ps
- Within Pair Skew: 1 ps
- NEXT: $\leq$ 2%

ExpressPort™ QSFP+ E-Series Connector

- Return Loss: -12 dB max (frequencies up to 14 GHz)
- Insertion Loss: 1.4 dB max (frequencies up to 14 GHz)
- Common Mode Conversion: -24 dB max (up to 14 GHz)
- Integrated Crosstalk Noise: 3 mV rms
- Assumes 3 Nearest-Neighbour (most detrimental) Aggressor Parameters and Receiver Parameters:
 - Near- and Far-End Aggressors' Peak Differential Amplitude: 600 mV
 - Near- & Far-End Aggressors' 20-80% Risetime: 9.6 ps
 - 3 dB Reference Receiver Bandwidth: 18.75 GHz
 - Range of Integration: 10 MHz to 40 GHz
 - MDNEXT: 1 mV rms; MDFEXT: 2.8 mV rms

ExpressPort™ QSFP+ H-Series Connector

- Return Loss: < -20 dB to 12GHz, -12 dB to 20GHz
- Near End Isolation: -40 to 20 GHz
- Insertion Loss: -1 dB up to 20GHz
- Differential Impedance: 100 +/- 5 Ω at 35 ps
- Within pair skew: <1 ps



U90-G351-101A



FS1-R38-2000

Ordering Information

Connectors:

QSFP

ExpressPort™ QSFP+

ExpressPort™ QSFP+ E-Series

ExpressPort™ QSFP+ H-Series

FS1 SERIES DESIGNATION (RoHS)

X38 R38 - 38 Position Connector (QSFP 10G, ExpressPort™ QSFP+ 12G+ & 16G)
E38 - 38 Position Connector (ExpressPort™ QSFP+ E-Series 28G)
H38 - 38 Position Connector (ExpressPort™ QSFP+ H-Series 40G)

X PLATING

2 - 30 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination
3 - 15 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination

0 0 - Standard

FS1-X38-X0XX-XX

SPECIAL

QSFP+ (12 Gbps and Up)

00 - No Resonance Dampening, No Hold Down Tabs

01 - No Resonance Dampening, Hold Down Tabs

QSFP+ (16 Gbps)

10 - Resonance Dampening, No Hold Down Tabs

11 - Resonance Dampening, Hold Down Tabs

E-Series (28 Gbps) / H-Series (40 Gbps)

10 - Resonance Dampening, No Hold Down Tabs

OPTIONS

00 - QSFP Connector

0A - Connector with Hold Down Tabs

A2 - QSFP+ Connector

M0 - E-Series Connector

HX - H-Series Connector

Cages:

QSFP

ExpressPort™ QSFP+

U90 SERIES DESIGNATION (RoHS)

X STYLE

A - One Row Cage 0°, Through the Bezel (No Light Pipe)
C - One Row Cage 1°, Through the Bezel (1x1 Only, No Light Pipe)
D - One Row Cage 0°, Hybrid with Elastomeric Gasket
G - One Row Cage 0°, Behind the Bezel
H - One Row Cage 0°, Through the Bezel with Optional Light Pipe
K - One Row Cage 0°, Through the Bezel with No Heat Sink Opening
L - One Row Cage 0°, No Pins on Back Wall
P - One Row Cage 0°, Behind the Bezel with Low Profile Heat Sink and Clip
R - One Row Cage 0°, Through the Bezel with Low Profile Heat Sink
T - One Row Cage 0°, Through the Bezel with Low Profile Heat Sink and Clip and Optional Light Pipe

X NUMBER OF PORTS IN ROW

1 - 1x1
3 - 1x3
4 - 1x4
6 - 1x6

X HEAT SINK OPTION

1 - No Heat Sink or Clip Shipped
2 - Fin Style (Black Oxide) Heat Sink and Clip (H = 6.5 mm)
3 - Fin Style (Black Oxide) Heat Sink and Clip (H = 4.2 mm)
4 - Fin Style (Black Oxide) Heat Sink and Clip (H = 13.5 mm)
5 - Pin Style (Nickel Plated) Heat Sink and Clip (H = 6.5 mm)
6 - Pin Style (Nickel Plated) Heat Sink and Clip (H = 4.2 mm)
7 - Pin Style (Nickel Plated) Heat Sink and Clip (H = 13.5 mm)
D - Pin-Fin Style (Black Oxide) Heat Sink and Clip (H = 6.5 mm)
E - Pin-Fin Style (Black Oxide) Heat Sink and Clip (H = 4.2 mm)
F - Pin-Fin Style (Black Oxide) Heat Sink and Clip (H = 13.5 mm)
N - Pin-Fin Style (Nickel Plated) Heat Sink and Clip (H = 6.5 mm)
P - Pin-Fin Style (Nickel Plated) Heat Sink and Clip (H = 4.2 mm)
R - Pin-Fin Style (Nickel Plated) Heat Sink and Clip (H = 13.5 mm)

U90-XX-X1-1XX-X

PACKAGING

1 - Tray Packaging

T - Tape and Reel Packaging (1x1 Only)

A - Tray Packaging Heat Sink and Clip
or Light Pipe Shipped Assembled

LIGHT PIPE OPTION

0 - Without Light Pipe

1 - Round 1.4 mm Outlet Light Pipe,
No EMI gasket

3 - Square 2.6x2.6 mm Outlet Light Pipe,
No EMI gasket

DUST COVER OPTION

0 - Without Dust Cover

D - With Dust Cover (Shipped Loose)

PLATING

1 - Nickel

APPLICATION

1 - Press Fit Pins (2.5 mm Long)

Telephone: (416)-291-4401

Website: www.amphenol-highspeed.com
All specifications are subject to change without notice.

Email: sales@amphenol-highspeed.com

ExpressPort™ QSFP+ (Stacked)

The QSFP+ Stacked Combo interconnect system consists of a 2-row, 38 position, 0.8 mm pitch connector designed to be compatible with the Quad Small Form-factor Pluggable (QSFP) Transceiver Specifications. The connector system is capable of data rates up to 25 Gbps per channel (four channels) and is intended for external connections (38 positions per port). High speed serial interconnect applications include clusters, servers, and storage devices.



U90-B105-2061-120



U90-B105-2061-120
(front view)

Specification Highlights

The interconnect system is comprised of a 2-row, 38-position, 0.8 mm pitch connector and cage assembly as one unit complying with SFF-8436.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Press-fit Cage and Connector Combo for min 1.57 mm (0.0625") PCB thickness

Mechanical Characteristics

- Durability: 250 Mating Cycles min
- Insertion Force: 40 N max
- Withdrawal Force: 30 N max

Electrical Characteristics

- Operating Voltage: 30 V
- Operating Current: 0.5 A
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 80 m Ω max

Packaging

- Tray Packaging: Cage of all Sizes

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel
 - o Light Pipe: Optical Grade Polycarbonate
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Matte Tin on Terminations and Grounding Tabs
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating


- Operating Temperature: -40°C to +85°C
- Storage Temperature: -40°C to +85°C

Configurations (Rows x Ports per Row)

- 2x1
- 2x2
- 2x3
- 2x4
- 2x6

Options

- Dust Cover
- Heat Sink
- Light Pipe
- EMI Shielding





Amphenol's CXP connector comes in a one-piece press-fit assembly system with twelve channels of up to 20 Gbps, resulting in 240 Gbps of total bandwidth – the fastest and most dense I/O on the market today. This allows our CXP to go beyond the 100 Gigabit Ethernet IEEE 802.3ba and the Infiniband CXP12x QDR standards. It also enables pluggable copper or optical cables to increase the flexibility of system-level hardware for end users. The CXP interconnect system is ideal for network switches, routers, servers, and storage devices.



U91-A121-100A-10


U91-A121-100A-10
(bottom view)


U91-A1A1-100A-10

Specification Highlights

The CXP interconnect system is comprised of an 84 position, 2-row press-fit connector, and a cage assembly as one unit complying with SFF-8642.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Industry Standard EIA-364

Mechanical Characteristics

- Insertion Force for an MSA Compliant Transceiver: 150 N max
- Unmating Force: 50 N max
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 30 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min

Packaging

- Tray Packaging: Cage and Connector Assembly
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Zinc Alloy
 - o Plating: Nickel
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Cage Cover: Stainless Steel
 - o Mounting Screw: AISI 1010 Steel
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -40°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations

- 1x1
- Custom Solutions Available

Options

- Dust Cover
- Heat Sink
- EMI Shielding
 - o Conductive Elastomeric Gasket
 - o Metal Spring Fingers
- Keying
 - o Key #1 (Left) InfiniBand™
 - o Key #2 (Right) Ethernet



Dust Cover

Ordering Information

CXP Combo

(Cage / Connector)

U91-X1XX-1XXX-3X

U91 SERIES DESIGNATION (RoHS)

X

STYLE

- A - One Row 0°, Standard Footprint
- D - One Row 0°, Enhanced Footprint
- E - One Row 0°, Long Connector, Belly-to-Belly Application
- F - One Row 0°, Short Connector, Belly-to-Belly Application

1

NUMBER OF PORTS IN ROW

- 1 - 1x1

X

HEAT SINK OPTION

- 1 - No Heat Sink or Clip Shipped
- 2 - Square Pin (Black Oxide) Heat Sink, and Clip
- 5 - Round Pin (Black Oxide) Heat Sink, and Clip
- A - Square Pin (Nickel Plated) Heat Sink, and Clip
- D - Round Pin (Nickel Plated) Heat Sink, and Clip
- G - Square Pin (Chromate Passivation) Heat Sink, and Clip
- K - Round Pin (Chromate Passivation) Heat Sink, and Clip

X

KEYING

- 0 - No Key
- 1 - Key #1 (Left) InfiniBand™
- 2 - Key #2 (Right) Ethernet

1

CAGE PLATING

- 1 - Nickel

MOUNTING SCREWS

- 0 - No Screws
- 1 - With Mounting Screws (Standard Length of M2 x 0.4, 6 mm long)

CONTACT PLATING

- 3 - Mating Area Plating 0.76 µm Gold Over 1.27 µm to 3.81 µm of Nickel; Press Fit Tail Area Plating 0.381 µm to 1.52 µm of Matte Tin Over 1.27 µm to 3.81 µm of Nickel

PACKAGING

- 1 - Tray Packaging
- A - Tray Packaging: Heat Sink and Clip Shipped Assembled

LIGHT PIPE OPTION

- 0 - Without Light Pipe
- X - Various Options Available
Consult Sales or Website for Details

DUST COVER OPTION


- 0 - Without Dust Cover
- D - With Dust Cover (Shipped Loose)



FS2-SF2-16C1

The Mini-SAS external I/O connector system consists of a die-cast metal cage and a Compact MultiLane SMT Connector, featuring proven “cut edge” style contacts. Providing four serial send/receive channels per port, this connector system is designed to satisfy the needs for gigabit serial data transmission applications with signal speeds across the connector interface of 6 Gbps per channel.

The cage is mounted separately to the body so that the stress imposed by insertion and removal of the cable plug does not affect the signal/body solder joints. The connector is available with unique solder hold-down tabs designed to provide additional mechanical robustness in demanding applications.



FS1-SF4-14E1



FS2-S02-14F1



FS1-S02-14E2-LP

Specification Highlights

The Mini-SAS interconnect system is comprised of a cage assembly which is used with 26-position, 0.8mm pitch connectors complying with SFF-8086 and SFF-8088.

Mechanical Characteristics

- Co-Planarity Specification: 0.1 mm
- Connector Insertion Force: 55.5 N max
- Connector Withdrawal Force: 49.0 N max
- Durability: 250 Mating Cycles min
- Reverse Keying for Active Copper Cables per SAS 2.0

Electrical Characteristics

- Operating Voltage: 30 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 80 m Ω max
- Near-End Isolation: -40 dB (frequencies up to 3 GHz)
- Insertion Loss: 1.0 dB max (frequencies up to 1.6 GHz)
- Rise Time for Impedance Measurement: 50 ps
- Within Pair Skew: 5 ps

Packaging

- Tape and Reel Packaging: Connector
- Tray Packaging: Cage
- Bulk Packaging: Mounting Screw or Dust Cover

Materials

- Cage
 - o Base Material: Zinc Alloy
 - o Plating: Nickel
 - o Mounting Screw: AISI 1010 Steel
 - o Light Pipe: Optical Grade Polycarbonate
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -55°C to +85°C
- Storage Temperature: -55°C to +85°C

Configurations (Rows x Ports per Row)

- 1x1
- 1x2
- 1x4

Options

- Dust Cover
- Light Pipe
- EMI Shielding
 - o Conductive Elastomeric Gasket
 - o Soft Shield Foam Gasket
 - o Stainless Steel Gasket
- Cage Inclination from Printed Circuit Board
 - o 0 degree Angle
 - o 1 degree Angle (PCI Applications)
- Keying



FS1-R26-2000



FS2-SF1-12C1

Ordering Information

Mini-SAS Connector

FS1 - R26 - X 0 0 X

FS1 SERIES DESIGNATION (RoHS)

R26 STYLE
R26 - 26 position connector

X PLATING
2 - 30 μ " Gold in Mating Area; 100 μ " Matte Tin on Tails over Nickel Underplate
3 - 15 μ " Gold in Mating Area; 100 μ " Matte Tin on Tails over Nickel Underplate

OPTIONS

0 - Standard Connector
1 - Connector with Hold Down Tabs

0 - Standard

0 - Standard

Mini-SAS Cage

FSX - S XX - 1 X XX - XX

FSX SERIES DESIGNATION
FS1 - Standard
FS2 - With SAS 2.0 Guide Keyway
FSA - With SAS 2.1 Guide Keyway

S S - Shell

XX SIZE
01 - 1x, 1 degree
F1 - 1x, 0 degree
02 - 2x, 1 degree
F2 - 2x, 0 degree
F4 - 4x, 0 degree

1 PLATING
1 - Nickel (RoHS)

X KEYING
0 - No Key
1 - Key #1
4 - Key #4 Universal SAS Port
7 - Key #7
24 - Key #2 and #4 (SAS Out)
46 - Key #4 and #6 (SAS In)
D22 - Left Port Key #2 & #4 / Right Port Key #2 & #4
D66 - Left Port Key #4 & #6 / Right Port Key #4 & #6
D26 - Left Port Key #2 & #4 / Right Port Key #4 & #6
D62 - Left Port Key #4 & #6 / Right Port Key #2 & #4


LIGHT PIPE OPTION

Blank - No Light Pipe
LP - 2 Barrel Light Pipes (1 Light Pipe per Port)

OPTIONS

C1 - Conductive Elastomer Gasket, 8 mm Long Mounting Screw, No Lock Washer
C2 - Conductive Elastomer Gasket, No Mounting Screw
C3 - Conductive Elastomer Gasket, 10 mm Long Mounting Screw with Lock Washer
E1 - Stainless Steel Gasket, 8 mm Long Mounting Screw, No Lock Washer
E2 - Stainless Steel Gasket, No Mounting Screw
E3 - Stainless Steel Gasket, 10 mm Long Mounting Screw with Lock Washer
F1 - Foam Gasket, 8 mm Long Mounting Screw, No Lock Washer
F2 - Foam Gasket, No Mounting Screw
F3 - Foam Gasket, 10 mm Long Mounting Screw with Lock Washer

Mini-SAS HD




U92-A150-1D0A-10

Amphenol's Mini-SAS High Density Interconnect is the next generation SAS system, with 4x, 8x, and 16x cable-plugging options to provide faster data transmission and more bandwidth for end users. The Mini-SAS HD connector system has a 2-row, right-angle connector with 12 Gbps per channel. Each connector handles 4 lanes of data for up to 48 Gbps of total bandwidth. Ganged options are also available up to a 1x4 configuration for up to 192 Gbps of total bandwidth. This connector will mate with active copper and optical cable assemblies, as well as active pluggable modules for extended-length applications in data centers. Main applications for Mini-SAS HD include HBA Servers, storage devices, switches, and rack-mounted computers.



U92-A110-1001-10



U92-A210-1001-10



U92-A410-1001-30

Specification Highlights

The Mini-SAS HD interconnect system is comprised of a 36-position, 2-row press-fit connector, and a stamped and formed cage assembly as one unit complying with SFF-8644.

General Characteristics

- RoHS Compliant
- Industry Standard Footprint
- Industry Standard EIA-364

Mechanical Characteristics

- Durability: 250 Mating Cycles min

Electrical Characteristics

- Hot Swappable
- Operating Voltage: 30 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 10 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- EMI Spring Fingers for Superior EMI Performance

Packaging

- Tray Packaging: Cage and Connector Assembly
- Bulk Packaging: Dust Cover or Mounting Screw

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
 - o Mounting Screw: AISI 1010 Steel
 - o EMI Spring Finger: Copper Alloy with Nickel Plating
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -40°C to +85°C
- Storage Temperature: -55°C to +105°C

Configurations (Rows x Ports per Row)

- 1x1
- 1x2
- 1x4

Options

- Dust Cover
- Heat Sink
- Light Pipe



U92-A410-1001-20

Ordering Information

Mini-SAS HD Combo (Cage / Connector)

U92-A X X X - 1 X X X - 3 X

U92 SERIES DESIGNATION (RoHS)

A

STYLE

A - One Row Cage 0 degrees

X

NUMBER OF PORTS IN ROW

1 - 1x1
2 - 1x2
4 - 1x4

X

HEAT SINK OPTION

1 - No Heat Sink or Clip Shipped
2 - Fin Style (Black Oxide) Heat Sink and Clip
5 - Pin Style (Nickel Plated) Heat Sink and Clip
A - Fin Style (Nickel Plated) Heat Sink and Clip
D - Pin-Fin Style (Black Oxide) Heat Sink and Clip
G - Pin Style (Black Oxide) Heat Sink and Clip
K - Pin Style (Chromate Passivation) Heat Sink and Clip
N - Pin-Fin Style (Nickel Plated) Heat Sink and Clip

X

EMI Shielding

0 - Standard EMI Fingers
1 - Extended EMI Fingers

1

CAGE PLATING

1 - Nickel

MOUNTING SCREWS

0 - No Screws
1 - Mounting Screws (Standard Length of
M2 x 0.4, 4.3 mm Long)

CONTACT PLATING

3 - Mating Area Plating 0.76 µm Gold Over 1.27 µm to
3.81 µm of Nickel; Press Fit Tail Area Plating
0.381 µm to 1.52 µm of Matte Tin Over 1.27 µm to
3.81 µm of Nickel

PACKAGING

1 - Tray Packaging
T - Tape and Reel Packaging
A - Tray Packaging Heat Sink and Clip or Light Pipe
Shipped Assembled

LIGHT PIPE OPTION


0 - Standard
2 - 2 Round Light Pipes Per Port, on Top of the Cage

DUST COVER OPTION


0 - Without Dust Cover
D - With Dust Cover (Shipped Loose)

The XFP interconnect system is capable of a 10 Gbps data rate and is intended for external I/O connections. High speed serial interconnect applications include clusters, servers, and storage devices. Its single row cage configuration requires less space and is a lower cost alternative to parallel-optics VSR. XFP also requires less than one-third the power and physical space of an MSA interconnect with parallel interface. It has a single footprint for all links, and is hot-pluggable.

The ExpressPort™ XFP+ Connector is designed to extend performance to 14 Gbps. Several EMI shielding options such as an elastomeric gasket or mylar tape are also available.



U79-A1G1-2001



U79-A141-2D01

Specification Highlights

The XFP interconnect system is comprised of a press-fit cage assembly which is used with 30-position, 0.8 mm pitch SMT connectors complying with INF-8077i.

Mechanical Characteristics

- Insertion Force: 40 N max (Cage and Connector)
- Withdrawal Force: 30 N max (Cage and Connector)
- Cage Retention: 180 N min (Latch Strength)
- Durability: 250 Mating Cycles min

Electrical Characteristics

- Operating Voltage: 30 V
- Operating Current: 0.5 A
- Differential Impedance: 100 Ω +/- 5 Ω
- DWV: 300 V AC
- Insulation Resistance: 1000 M Ω min
- Contact Resistance: 70 m Ω max
- Near-End Isolation: -40 dB
- Insertion Loss: 1.0 dB max

Packaging

- Tape and Reel Packaging: Connector or Cage
- Tray Packaging: Cage
- Bulk Packaging: Dust Cover

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Plating: Nickel
 - o Front Flange: Zinc Alloy
 - o Heat Sink: Aluminum Alloy
 - o Heat Sink Clip: Stainless Steel
 - o Dust Cover: Thermoplastic
- Connector
 - o Contact Base Material: Copper Alloy
 - o Contact Plating: Gold on Mating Area, Gold or Matte Tin on Termination
 - o Housings: Glass Reinforced, Lead-Free Solder Reflow Process Compatible Thermoplastic, UL94V-0 Rated

Temperature Rating

- Operating Temperature: -40°C to +85°C
- Storage Temperature: -40°C to +85°C

Options

- Heat Sink
- Dust Cover
- EMI Shielding
 - o Conductive Elastomeric Gasket at Back of Cage
 - o Mylar Tape

XFP Connector


UE7X	SERIES DESIGNATION (RoHS) UE75 - Standard XFP Connector UE76 - ExpressPort™ XFP+ Connector	A	STYLE A - R/A Single Surface Mount Connector	30	NUMBER OF POSITIONS 30 - 30 Positions (Single XFP)	X	CONTACT PLATING 2 - 30 μ" Gold Plating on Mating Area; Gold Flash on Termination 3 - 30 μ" Gold Plating on Mating Area; Matte Tin Plating on Termination 5 - 15 μ" Gold Plating on Mating Area; Gold Flash on Termination 6 - 15 μ" Gold Plating on Mating Area; Matte Tin Plating on Termination	0	PACKAGING T - Tape and Reel Packaging (500 per Reel)	T	X	LUBRICANT OPTION 0 - Non Lubricated 1 - Lubricant Added	0	OPTION 1 0 - Standard	0
-------------	---	----------	--	-----------	--	----------	--	----------	--	----------	----------	--	----------	---------------------------------	----------

XFP Cage


U79	SERIES DESIGNATION	A	STYLE A - 1 Row	1	NUMBER OF PORTS IN ROW 1 - Single in Row	X	HEAT SINK OPTION 0 - No Heat Sink, Only Clip is Shipped 1 - No Heat Sink or Clip Shipped 2 - Standard Height Fin Heat Sink (7 mm) and Clip 3 - PCI Height Fin Heat Sink (4.2 mm) and Clip 4 - Tall Fin Heat Sink (13.5 mm) and Clip G - 45° Standard Height Fin Heat Sink (7mm) and Clip	2	PACKAGING 1 - Tray Packaging (Heat Sink and Clip Shipped Separately) T - Tape and Reel (Heat Sink and Clip Shipped Separately) B - Tray Packaging (Clip Shipped Assembled to Cage)	X	X	OPTION 1 0 - Standard 1 - High Conductivity Rear Lower EMI Gasket 2 - Mylar Tape Attached to Bottom Cage Wall	X	DUST COVER OPTION 0 - Without Dust Cover D - With Dust Cover (Shipped Loose)	X	PLATING 2 - Nickel	2
------------	---------------------------	----------	---------------------------	----------	--	----------	---	----------	--	----------	----------	---	----------	---	----------	------------------------------	----------

CFP2 / CFP4

The CFP2 and CFP4 (surface mount receptacle connector) are considered as a candidate of future generation of multi hundred Gbps system. Both are 0.6mm pitch with the CFP2 having 104 positions and the CFP4 having 56 positions. They are rated for 28 Gbps per channel with resonance dampening for improved signal integrity. Both the CFP2 and CFP4 have a plug connector on the mating interface that improves accuracy and aids in achieving high speed performance.



CFP2



CFP4

Specification Highlights

The CFP2 and CFP4 interconnect systems are comprised of insert molding assemblies for top side contacts and press-fit cage assemblies.

Current Mechanical Characteristics

	CFP2	CFP4
• RSS Tolerance	0.19mmMin	
• Host Depth (mm)	84.5	67
• Host Height (mm)	12.9	10
• Ports in 365(445)mm Faceplate	8(10)	16(19)
• Max Insertion Force with Heat-sink:	6N	
• Max Insertion Force without Heat-sink:	4.5N	
• Max Withdrawal Force with Heat-sink:	5.4N	4.0N
• Max Withdrawal Force without Heat-sink:	3.9N	2.5N

Materials

- Cage
 - o Base Material: Copper Alloy
 - o Heat Sink: Aluminum Alloy

Options

- Heat Sink
- Dust Cover
- Connector Cover
- EMI Gasket

Electrical Characteristics

- Operating Voltage: 3.3 V

CFP2/CFP4 Host Connector

U99 SERIES DESIGNATION

X STYLE

B - CFP2 Connector
C - CFP4 Connector

XXX NUMBER OF POSITIONS

104 - CFP2 Connector
056 - CFP4 Connector (To be Tooled)

PACKAGING

T - Tape and Reel Packaging

OPTION 2

0 - Standard

OPTION 1

0 - Standard

CONTACT PLATING

2 - 30 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination

3 - 15 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination

CFP2/CFP4 Plug Connector

U56 SERIES DESIGNATION

X STYLE

B - CFP2 Connector
C - CFP4 Connector

XXX NUMBER OF POSITIONS

104 - CFP2 Connector
056 - CFP4 Connector (To be Tooled)

PACKAGING

T - Tape and Reel Packaging

OPTION 2

0 - Standard

OPTION 1

0 - Standard

CONTACT PLATING

2 - 30 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination

3 - 15 µ" Gold Plating on Mating Area; Matte Tin Plating on Termination

CFP2/CFP4 Cage

U98 SERIES DESIGNATION

X STYLE

B - CFP2 single row
C - CFP4 single row

X NUMBER OF PORT IN ROW

1 - Nx1 ports
2 - Nx2 ports
3 - Nx3 ports (To be Tooled)
4 - Nx4 ports (To be Tooled)
6 - Nx6 ports (To be Tooled)

X HEAT SINK OPTION

1 - No Heat Sink and No Clip Shipped
2 - Fin Style (Black Oxide) Heat Sink and Clip (H=10.75mm)

*Other custom heat sink options are available.

PACKAGING

1 - Tray Packaging
A - Tray Packaging; Heat Sink and Clip or Light Pipe Shipped Assembled

CONNECTOR COVER

0 - With Connector Cover and Kickout Springs
C - With Connector Cover, no Kickout Springs

OPTIONAL DUST COVER

0 - Without Dust Cover
D - With Dust Cover (Ship Loose)

PLATING

1 - Nickel
2 - Matte Tin

APPLICATION

1 - Press Fit Pins - 2.5 mm Long

Notes





Amphenol

High Speed Interconnects

For more information about any of our products, please contact your local Amphenol Sales Representative at:

North America

Phone: +1-416-291-4401

Fax: +1-416-292-0647

Email: cages@amphenol-highspeed.com

www.amphenol-highspeed.com

Europe

Phone: +31-30-635-8000

Fax: +31-30-637-7034

Email: customerservice@amphenol-nl.com

Asia

Phone: +852-2699-2663

Fax: +852-2691-1774

Email: enquiry@amphenol.com.hk

World Headquarters

Phone: +1-203-265-8900

Fax: +1-203-268-8516

Email: info@amphenolacp.com

www.amphenol.com

CONTACT US

Now you're connected