


# Electromechanical Relays Selection Guide

Latching



JAN



Non-Latching



RF



Commercial



Established  
Reliability


Surface-Mount



Environmental



Attenuated



**TELEDYNE  
RELAYS**

A Teledyne Technologies Company



RoHS or Non-RoHS:  
Your Choice!



# Switching Solutions

Teledyne Relays has been the world's innovative leader in the manufacture of ultraminiature, hermetically sealed, electromechanical and solid-state switching products for more than 40 years. The company's comprehensive product line meets a wide range of requirements for defense and aerospace, industrial, commercial, medical and RF & wireless applications.

## Business Focus

- MIL QPL & COTS Solid-State Relays
- MIL QPL & COTS Electromechanical Relays
- HiRel (Space) Electromechanical Relays
- RF & Microwave Relays & Coaxial Switches
- Industrial Solid-State Relays
- Switching Matrices

## Markets


- Commercial & Military Aviation
- Defense & Aerospace
- Telecom/Communications (Wireless)
- Instrumentation & Test
- Industrial Power & Motion Control
- Medical Applications

## Product Assurance

Under an aggressive Total Quality Management (TQM) program, Teledyne Relays has embraced a "continuous improvement" culture. With recognized certifications such as AS/EN/JISQ 9100 - Revision B and ISO 9001:9002, DSCC MIL-STD-790 and Boeing D6-82479 Appendix A, Teledyne Relays has become a primary supplier of switching solutions with the highest quality and reliability to industry leaders around the world.

## Technical Service & Customer Support

Teledyne Relays provides easy access to technical service and customer support. Our websites make it easy to find technical information, buy products and even get e-mail responses within 24 hours. Switching solutions are only a mouse click away at [www.teledynerelays.com](http://www.teledynerelays.com) or at [teledyne-europe.com](http://teledyne-europe.com). Information about coax switches is available at [www.teledynecoax.com](http://www.teledynecoax.com).



Teledyne Relays offer superior signal integrity up to 12 Gbps. See the RF relays section in our website.

# Table of Contents

| RF RELAYS                       |  |      |
|---------------------------------|--|------|
| Series                          | Description  | Page |
| <b>RF100/RF103</b>              | High Repeatability, Broadband Centigrad® Relays, Non-Latching DPDT | 4    |
| <b>GRF172</b>                   | Surface-Mount Centigrad® RF Relays, Non-Latching DPDT              | 4    |
| <b>RF300/RF303</b>              | High Repeatability, Broadband TO-5 Relays, Non-Latching DPDT       | 5    |
| <b>RF312</b>                    | High Repeatability, Broadband TO-5 Relays, Non-Latching DPDT       | 6    |
| <b>RF311/RF331</b>              | High Repeatability, Broadband TO-5 Relays, Non-Latching SPDT       | 7    |
| <b>GRF342</b>                   | Surface-Mount TO-5 RF Relays, Magnetic-Latching DPDT               | 7    |
| <b>RF180</b>                    | Broadband RF Relays, Magnetic-Latching DPDT                        | 8    |
| <b>RF341</b>                    | Broadband TO-5 RF Relays, Magnetic-Latching SPDT                   | 8    |
| <b>RF310/RF313</b>              | High Repeatability TO-5 Relays, Normally Closed, Bypass            | 9    |
| <b>RF320/RF323</b>              | High Repeatability TO-5 Relays, Normally Open, Bypass              | 9    |
| <b>A150</b>                     | Broadband Attenuator RF Relay                                      | 10   |
| <b>A152</b>                     | Broadband Attenuator RF Relay                                      | 10   |
| COMMERCIAL RELAYS               |  |      |
| <b>122C</b>                     | Centigrad® Relays (CMOS Compatible), Magnetic-Latching DPDT        | 11   |
| <b>172</b>                      | Centigrad® Relays, Non-Latching DPDT                               | 11   |
| <b>712</b>                      | TO-5 Relays, Non-Latching DPDT                                     | 12   |
| <b>722</b>                      | TO-5 Relays, Magnetic-Latching DPDT                                | 12   |
| <b>732</b>                      | TO-5 Relays, Non-Latching Sensitive DPDT                           | 13   |
| COMMERCIAL SURFACE-MOUNT RELAYS |  |      |
| <b>S114</b>                     | Surface-Mount Centigrad® Relays, Non-Latching DPDT                 | 14   |
| <b>S134</b>                     | Surface-Mount Centigrad® Relays, Non-Latching Sensitive DPDT       | 14   |
| <b>S172</b>                     | Surface-Mount Centigrad® Relays, Non-Latching DPDT                 | 15   |
| <b>S422</b>                     | Surface-Mount TO-5 Relays, Magnetic-Latching DPDT                  | 15   |
| ESTABLISHED RELIABILITY RELAYS  |  |      |
| <b>ER114</b>                    | Centigrad® Relays, Non-Latching DPDT                               | 16   |
| <b>ER116C</b>                   | Centigrad® Relays (CMOS Compatible), Non-Latching DPDT             | 16   |
| <b>ER134</b>                    | Centigrad® Relays, Non-Latching Sensitive DPDT                     | 17   |
| <b>ER136C</b>                   | Centigrad® Relays (CMOS Compatible), Non-Latching Sensitive DPDT   | 17   |

See specific series for additional features and options

Continued on next page

# Table of Contents

| ESTABLISHED RELIABILITY RELAYS (continued) |  |      |
|--|--|------|
| Series                                     | Description  | Page |
| <b>ER411</b>                               | TO-5 Relays, Non-Latching SPDT                                   | 18   |
| <b>ER431</b>                               | TO-5 Relays, Non-Latching Sensitive SPDT                         | 18   |
| <b>ER412</b>                               | TO-5 Relays, Non-Latching DPDT                                   | 19   |
| <b>ER432</b>                               | TO-5 Relays, Non-Latching Sensitive DPDT                         | 19   |
| <b>255</b>                                 | Half-Size Crystal Can, Magnetic-Latching DPDT                    | 20   |
| <b>ER421</b>                               | TO-5 Relays, Magnetic-Latching SPDT                              | 20   |
| <b>ER420</b>                               | TO-5 Relays, Magnetic-Latching DPDT                              | 21   |
| <b>ER422</b>                               | TO-5 Relays, Magnetic-Latching DPDT                              | 21   |
| MILITARY QUALIFIED (JAN) RELAYS            |  |      |
| <b>J114</b>                                | Centigrad® Relays, Non-Latching DPDT                             | 22   |
| <b>J116C</b>                               | Centigrad® Relays (CMOS Compatible), Non-Latching DPDT           | 22   |
| <b>J134</b>                                | Centigrad® Relays, Non-Latching Sensitive DPDT                   | 23   |
| <b>J136C</b>                               | Centigrad® Relays (CMOS Compatible), Non-Latching Sensitive DPDT | 23   |
| <b>J411</b>                                | TO-5 Relays, Non-Latching SPDT                                   | 24   |
| <b>J431</b>                                | TO-5 Relays, Non-Latching Sensitive SPDT                         | 24   |
| <b>J412</b>                                | TO-5 Relays, Non-Latching DPDT                                   | 25   |
| <b>J432</b>                                | TO-5 Relays, Non-Latching Sensitive DPDT                         | 25   |
| <b>J255</b>                                | Half-Size Crystal Can, Magnetic-Latching DPDT                    | 26   |
| <b>J421</b>                                | TO-5 Relays, Magnetic-Latching SPDT                              | 26   |
| <b>J420</b>                                | TO-5 Relays, Magnetic-Latching DPDT                              | 27   |
| <b>J422</b>                                | TO-5 Relays, Magnetic-Latching DPDT                              | 27   |
| HIGH-PERFORMANCE RELAYS                    |  |      |
| <b>412H/432H</b>                           | High-Temperature (200°C) TO-5 Relays, Non-Latching DPDT          | 28   |
| <b>422H</b>                                | High-Temperature (200°C) TO-5 Relays, Magnetic-Latching DPDT     | 28   |
| <b>412K</b>                                | High-Shock TO-5 Relays, Non-Latching DPDT                        | 29   |
| <b>422K</b>                                | High-Shock TO-5 Relays, Magnetic-Latching DPDT                   | 29   |
| <b>412V/432V</b>                           | High-Vibration TO-5 Relays, Non-Latching DPDT                    | 30   |

See specific series for additional features and options










Continued on next page



# Table of Contents

| APPENDIX                                  |       |
|---|-------|
| Description                               | Page  |
| Signal Integrity Eye Diagrams             | 31-38 |
| RoHS and Reach Certificate of Compliance  | 39    |
| Part Numbering System                     | 40-41 |
| Spacer Pad Options                        | 42    |
| Spreader Pad Options                      | 43    |
| Ground Pin Options                        | 44    |
| Established Reliability Program           | 45-46 |
| Teledyne Relays HI-REL Program            | 47    |
| Authorized Distributors                   | 48    |
| Authorized North American Representatives | 49    |

Teledyne Relays offers a variety of options to customize and meet your specific design needs.

|   |   |   |
|---|---|---|
|  <p><b>GRF Option</b><br/>TO-5 Relays with straight butt pins for surface-mount applications<br/>* RF Relays Only</p>                          |  <p><b>SGRF Option</b><br/>TO-5 Relays with Gull-Wing (J-Lead) pins for surface-mount applications<br/>* RF Relays Only</p>    |  <p><b>GRF Option</b><br/>Centigrad® Relays with straight butt pins for surface-mount applications<br/>* RF Relays Only</p>                      |
|  <p><b>SGRF Option</b><br/>TO-5 Relays with Gull-Wing (J-Lead) pins for surface-mount applications<br/>* RF Relays Only</p>                    |  <p><b>SRF Option</b><br/>Relays with Gull-Wing (J-Lead) pins for surface-mount applications<br/>* RF Relays Only</p>          |  <p><b>/S Option</b><br/>Relays with 0.187" trimmed leads<br/>See Appendix: Part Numbering System</p>  |
|  <p><b>Spacer Pad Option</b><br/>Relays with polyester film pad to space between PCB and Relay Header<br/>See Appendix: Spacer Pad Options</p> |  <p><b>Spreader Pad Option</b><br/>Relays with Diallyl Phthalate pad to spread pins<br/>See Appendix: Spreader Pad Options</p> |  <p><b>/Q, /R Option</b><br/>Relays with solder dipped leads. Pb/Sn (60/40) or RoHS solder available<br/>See Appendix: Part Numbering System</p> |

See specific series for additional features and options

## RF RELAYS






### Series RF100/RF103 Electromechanical Relays


The RF100 and RF103 Centigrad® relays are designed to provide improved RF signal repeatability over the frequency range.

The GRF100 and GRF103 Centigrad® relays feature a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

The SGRF100 and SGRF103 Centigrad® relays extend performance advantages over similar RF devices that simply offer formed leads for surface mounting.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type                    | Part No.   | Nominal Coil  |                | Typical RF Performance |            |                    |                       |                           |
|-------------------------------|--|---------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|
|                               |  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |
| DPDT Non-Latching             |  |               |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |
| Coil Type                     |  |               |                |                        |            |                    |                       |                           |
| 100 = Standard Coil           |  <b>RF100</b>     | 5             | 50             | DC-1                   | 1.1 : 1    | 35                 | 25                    | 0.2                       |
| 103 = Sensitive Coil          |  | 12            | 390            | 1-2                    | 1.5 : 1    | 30                 | 20                    | 0.5                       |
| Mounting                      |  |               |                |                        |            |                    |                       |                           |
| RF = Thru-hole                |  <b>GRF100</b>   | 5             | 50             | DC-1                   | 1.1 : 1    | 45                 | 30                    | 0.2                       |
| GRF = Surface-Mount (Stub)    |  | 12            | 390            | 1-3                    | 1.2 : 1    | 40                 | 25                    | 0.3                       |
| SGRF = Surface-Mount (J-Lead) |  <b>SGRF100</b> | 5             | 100            | 3-4                    | 1.3 : 1    | 35                 | 25                    | 0.6                       |
|                               |  | 12            | 800            | 4-6                    | 2.2 : 1    | 30                 | 25                    | 1.2                       |
| Temperature                   |  |               |                |                        |            |                    |                       |                           |
| Storage: -65°C to +125°C      |  <b>SGRF103</b> | 5             | 50             | DC-1                   | 1.2 : 1    | 35                 | 30                    | 0.2                       |
| Operating: -55°C to +85°C     |  | 12            | 390            | 1-3                    | 1.3 : 1    | 30                 | 30                    | 0.7                       |
|                               |  <b>SGRF103</b> | 5             | 100            | 3-4                    | 1.4 : 1    | 25                 | 25                    | 0.8                       |
|                               |  | 12            | 800            | 4-6                    | 1.8 : 1    | 25                 | 25                    | 1.0                       |





### Series GRF172 Electromechanical Relays

The GRF172 Centigrad® relay is a hermetically sealed, armature relay for 2.5GHz RF applications. Its low profile height .330" (8.38 mm) and .100" (2.54 mm) grid spaced terminals make it an ideal choice where extreme packaging density and/or close PC board spacing are required. The GRF172 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability. The GRF172 extends performance advantages over similar RF devices that simply offer formed leads for surface mounting.


The Series GRF172D has an internal discrete silicon diode for coil suppression.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  | Part No.  | Nominal Coil  |                | Typical RF Performance |            |                    |                       |                           |
|---|---|---------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|
|   |   | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |
| DPDT Non-Latching                                 |   |               |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |
| Coil Type   |   |               |                |                        |            |                    |                       |                           |
| 172 = Standard Coil                               |  <b>GRF172</b> | 5             | 50             | DC-1                   | 1.1 : 1    | 45                 | 30                    | 0.2                       |
|   |   | 12            | 390            | 1-2                    | 1.2 : 1    | 40                 | 25                    | 0.3                       |
|   |   | 26            | 100            | 2-2.5                  | 1.2 : 1    | 40                 | 25                    | 0.3                       |
| Diode Option                                      |   |               |                |                        |            |                    |                       |                           |
| D = Internal diode for coil transient suppression |   |               |                |                        |            |                    |                       |                           |
| Mounting  |   |               |                |                        |            |                    |                       |                           |
| GRF = Surface-Mount (Stub)                        |   |               |                |                        |            |                    |                       |                           |
| Temperature                                       |   |               |                |                        |            |                    |                       |                           |
| Storage: -65°C to +125°C                          |   |               |                |                        |            |                    |                       |                           |
| Operating: -55°C to +85°C                         |   |               |                |                        |            |                    |                       |                           |



GRF172



GRF172D

Schematics as viewed from terminals

## RF RELAYS





### Series RF300/RF303 Electromechanical Relays

The RF300 and RF303 TO-5 relays are designed to provide improved RF signal repeatability over the frequency range.


The GRF300 and GRF303 TO-5 relays feature a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

The SGRF300 and SGRF303 TO-5 relays extend performance advantages over similar RF devices that simply offer formed leads for surface mounting.


- Excellent Signal integrity up to 10Gbps+
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  | Part No.  | Nominal Coil    |                | Typical RF Performance |            |                    |                       |                           |     |
|---|---|-----------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|-----|
|   |   | Voltage (Vdc)   | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |     |
|   |   |                 |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |     |
| DPDT Non-Latching   |   |                 |                |                        |            |                    |                       |                           |     |
| <b>Coil Type</b>  |   |                 |                |                        |            |                    |                       |                           |     |
| 300 = Standard Coil   |   |                 |                |                        |            |                    |                       |                           |     |
| 303 = Sensitive Coil  |   |                 |                |                        |            |                    |                       |                           |     |
| <b>Diode Option</b>   |   |                 |                |                        |            |                    |                       |                           |     |
| D = Internal diode for coil transient suppression                                   |   |                 |                |                        |            |                    |                       |                           |     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |   |                 |                |                        |            |                    |                       |                           |     |
| <b>Mounting</b>   |   |                 |                |                        |            |                    |                       |                           |     |
| RF = Thru-hole  |   |                 |                |                        |            |                    |                       |                           |     |
| GRF = Surface-Mount (Stub)  |   |                 |                |                        |            |                    |                       |                           |     |
| SGRF = Surface-Mount (J-Lead)   |   |                 |                |                        |            |                    |                       |                           |     |
| SRF = Surface Mount (J-Lead)  |   |                 |                |                        |            |                    |                       |                           |     |
| <b>Temperature</b>  |   |                 |                |                        |            |                    |                       |                           |     |
| Storage: -65°C to +125°C  |   |                 |                |                        |            |                    |                       |                           |     |
| Operating: -55°C to +85°C   |   |                 |                |                        |            |                    |                       |                           |     |
|   |    | <b>RF300</b>    | 5              | 50                     | DC-1       | 1.1 : 1            | 30                    | 25                        | 0.2 |
|   |   | <b>RF300D</b>   | 12             | 390                    | 1-2        | 1.1 : 1            | 25                    | 20                        | 0.3 |
|   |   | <b>RF303</b>    | 5              | 100                    | 2-3        | 1.2 : 1            | 25                    | 20                        | 0.4 |
|   |   | <b>RF303D</b>   | 12             | 850                    |            |                    |                       |                           |     |
|   |   | <b>GRF300</b>   | 5              | 50                     | DC-1       | 1.1 : 1            | 40                    | 30                        | 0.2 |
|   |   | <b>GRF300D</b>  | 12             | 390                    | 1-3        | 1.1 : 1            | 40                    | 30                        | 0.2 |
|   |   | <b>GRF303</b>   | 5              | 100                    | 3-4        | 1.3 : 1            | 30                    | 30                        | 0.6 |
|   |   | <b>GRF303D</b>  | 12             | 850                    | 4-6        | 1.6 : 1            | 25                    | 25                        | 1.0 |
|   |  | <b>SGRF300</b>  | 5              | 50                     | DC-1       | 1.2 : 1            | 40                    | 30                        | 0.2 |
|   |   | <b>SGRF300D</b> | 12             | 390                    | 1-3        | 1.2 : 1            | 40                    | 30                        | 0.4 |
|   |   | <b>SGRF303</b>  | 5              | 100                    | 3-4        | 1.2 : 1            | 20                    | 25                        | 0.8 |
|   |   | <b>SGRF303D</b> | 12             | 850                    | 4-6        | 1.8 : 1            | 10                    | 20                        | 1.0 |
|   |  | <b>SRF300</b>   | 5              | 50                     | DC-1       | 1.1 : 1            | 25                    | 25                        | 0.5 |
|   |   | <b>SRF300D</b>  | 12             | 390                    | 1-3        | 1.5 : 1            | 25                    | 25                        | 0.5 |
|   |   | <b>SRF303</b>   | 5              | 100                    | 3-4        | 2.0 : 1            | 15                    | 15                        | 3.0 |
|   |   | <b>SRF303D</b>  | 12             | 850                    | 4-6        | 2.5 : 1            | 10                    | 10                        | 4.0 |


For RF300DD & RF303DD values please see Datasheet



300  
303



300D  
303D



300DD  
303DD

Schematics as viewed from terminals

## RF RELAYS


### Series RF312 Electromechanical Relays




The RF312 is designed to improve upon the RF300/RF303 relay's high frequency performance. The RF312 offers monotonic insertion loss over to 8GHz. This improvement in RF insertion loss over the frequency range, makes these relays highly suitable for use in attenuator and other RF circuits.

The GRF312 is designed to improve upon the GRF300/GRF303 relay's high frequency performance. The GRF312 TO-5 relay features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

- Excellent Signal integrity up to 12Gbps+
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type                    |
|-------------------------------|
| DPDT Non-Latching             |
| Coil Type                     |
| 312 = Standard Coil           |
| Mounting                      |
| RF = Thru-hole                |
| GRF = Surface-Mount (Stub)    |
| SGRF = Surface-Mount (J-Lead) |
| Temperature                   |
| Storage: -65°C to +125°C      |
| Operating: -55°C to +85°C     |



| Part No.   | Nominal Coil  |                | Typical RF Performance |            |                    |                       |                           |
|--|---------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |
|  |               |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |
|  <b>RF312</b>     | 5             | 50             | DC-2                   | 1.2 : 1    | 30                 | 20                    | 0.2                       |
|  |               |                | 2-4                    | 1.2 : 1    | 25                 | 20                    | 0.4                       |
|  | 12            | 390            | 4-6                    | 1.3 : 1    | 25                 | 20                    | 0.6                       |
|  |               |                | 6-8                    | 1.4 : 1    | 20                 | 20                    | 0.8                       |
|  <b>GRF312</b>   | 5             | 50             | DC-2                   | 1.4 : 1    | 40                 | 30                    | 0.3                       |
|  |               |                | 2-4                    | 1.4 : 1    | 40                 | 30                    | 0.5                       |
|  | 12            | 390            | 4-6                    | 1.5 : 1    | 35                 | 30                    | 1.0                       |
|  |               |                | 6-8                    | 1.5 : 1    | 35                 | 30                    | 1.5                       |
|  <b>SGRF312</b> | 5             | 50             | DC-2                   | 1.2 : 1    | 40                 | 30                    | 0.2                       |
|  |               |                | 2-4                    | 1.2 : 1    | 35                 | 30                    | 0.5                       |
|  | 12            | 390            | 4-6                    | 1.3 : 1    | 30                 | 25                    | 1.0                       |
|  |               |                | 6-8                    | 1.5 : 1    | 30                 | 25                    | 1.5                       |

Schematics as viewed from terminals

## RF RELAYS


### Series RF311/RF331 Electromechanical Relays




The RF311/RF331 relays are designed to provide improved RF signal repeatability over the frequency range. These relays are highly suitable for use in attenuator and other RF circuits.

The GRF311 offers monotonic insertion loss to 8GHz. This improvement in RF insertion loss over the frequency range makes these relays highly suitable for use in attenuator and other RF circuits. The GRF311 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| SPDT Non-Latching                                     |
| Coil Type   |
| 311 = Standard Coil<br>331 = Sensitive Coil           |
| Mounting  |
| RF = Thru-hole<br>GRF = Surface-Mount (Stub)          |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |




| Part No.   | Nominal Coil  |                | Typical RF Performance |            |                                      |                           |
|--|---------------|----------------|------------------------|------------|--------------------------------------|---------------------------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation Across Contacts (dB) (min) | Insertion Loss (dB) (max) |
|  <b>RF311</b>   | 5             | 63             | DC-2                   | 1.3 : 1    | 25                                   | 0.2                       |
|  | 12            | 500            | 2-4                    | 1.6 : 1    | 20                                   | 0.4                       |
|  | 26            | 2000           | 4-6                    | 1.6 : 1    | 20                                   | 0.6                       |
|  |               |                | 6-8                    | 1.6 : 1    | 15                                   | 0.8                       |
|  <b>GRF311</b> | 5             | 63             | DC-2                   | 1.2 : 1    | 30                                   | 0.3                       |
|  | 12            | 500            | 2-4                    | 1.5 : 1    | 25                                   | 0.5                       |
|  | 26            | 2000           | 4-6                    | 1.5 : 1    | 25                                   | 0.7                       |
|  |               |                | 6-8                    | 1.6 : 1    | 20                                   | 1.0                       |
|  <b>RF331</b> | 5             | 125            | DC-2                   | 1.3 : 1    | 25                                   | 0.2                       |
|  | 12            | 1025           | 2-4                    | 1.6 : 1    | 20                                   | 0.4                       |
|  | 26            | 4000           | 4-6                    | 1.6 : 1    | 20                                   | 0.6                       |
|  |               |                | 6-8                    | 1.6 : 1    | 15                                   | 0.8                       |

### Series GRF342 Electromechanical Relays


The Series GRF342 relay is a hermetically sealed, RF relay designed from inception for surface mount applications. This magnetic-latching relay features extremely low internal circuit losses for exceptional time and frequency domain response characteristics through and beyond the UHF spectrum and into the S band. The GRF342 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides an RF ground interface that results in improved high-frequency performance as well as parametric repeatability. The GRF342 extends performance advantages over similar RF devices that simply offer formed leads for surface mounting.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| DPDT Magnetic-Latching                                |
| Coil Type   |
| 342 = Standard Coil                                   |
| Mounting  |
| GRF = Surface-Mount (Stub)                            |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |

| Part No.  | Nominal Coil  |                | Typical RF Performance |            |                    |                       |                           |
|---|---------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|
|   | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |
|   |               |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |
|  <b>GRF342</b> | 5             | 50             | DC-2                   | 1.1 : 1    | 40                 | 35                    | 0.3                       |
|   | 12            | 390            | 2-4                    | 1.2 : 1    | 30                 | 30                    | 0.4                       |
|   |               |                | 4-6                    | 1.4 : 1    | 25                 | 25                    | 0.8                       |

Schematics as viewed from terminals



GRF342

SCHEMATIC  
(Coil A Last Energized)

## RF RELAYS



### Series RF180 Electromechanical Relays


The Series RF180 relay is a hermetically sealed, magnetic-latching relay featuring extremely low intercontact capacitance for exceptional RF performance over the full UHF spectrum. Its low profile height and .100" (2.54 mm) grid spaced terminals make it ideal for applications where extreme packaging density and/or close PC board spacing are required.

The GRF180 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact and pole-to-pole isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| DPDT Magnetic-Latching                                |
| Coil Type   |
| 180 = Standard Coil                                   |
| Mounting  |
| RF = Thru-hole<br>GRF = Surface-Mount (Stub)          |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |

| Part No.   | Nominal Coil  |                | Typical RF Performance |            |                    |                       |                           |
|--|---------------|----------------|------------------------|------------|--------------------|-----------------------|---------------------------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation (dB)     |                       | Insertion Loss (dB) (max) |
|  |               |                |                        |            | Pole to Pole (min) | Across Contacts (min) |                           |
|  <b>RF180</b>   | 5             | 61             | DC-2                   | 1.3 : 1    | 50                 | 30                    | 0.2                       |
|  | 12            | 500            | 2-4                    | 1.3 : 1    | 45                 | 30                    | 0.3                       |
|  | 26            | 2000           | 4-6                    | 2.0 : 1    | 30                 | 25                    | 1.5                       |
|  <b>GRF180</b> | 5             | 61             | DC-2                   | 1.2 : 1    | 50                 | 35                    | 0.2                       |
|  | 12            | 500            | 2-4                    | 1.3 : 1    | 35                 | 30                    | 0.4                       |
|  | 26            | 2000           | 4-6                    | 2.0 : 1    | 25                 | 30                    | 1.5                       |



180

SCHEMATIC  
(Coil B Last Energized)



### Series RF341 Electromechanical Relays


The RF341 series relay is an ultraminiature, hermetically sealed, magnetic-latching relay featuring extremely low intercontact capacitance for exceptional RF performance well into the C band. Its low profile and small size make it ideal for applications where extreme packaging density and/or close PC board spacing are required. Due to its minimal mass, many relays may be used to configure replacements for bulkier switching solutions at substantial savings in weight. The RF341 design has been optimized by increasing the distance between the set/reset contacts. This design improvement makes these unique relays the perfect choice for use in RF attenuators, RF switching matrices and other RF applications requiring high isolation, low insertion loss and low VSWR.

The GRF341 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.

- Excellent Signal integrity up to 10Gbps
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| SPDT Magnetic-Latching                                |
| Coil Type   |
| 341 = Standard Coil                                   |
| Mounting  |
| RF = Thru-hole<br>GRF = Surface-Mount (Stub)          |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |

| Part No.  | Nominal Coil  |                | Typical RF Performance |            |                                      |                           |
|---|---------------|----------------|------------------------|------------|--------------------------------------|---------------------------|
|   | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR (max) | Isolation Across Contacts (dB) (min) | Insertion Loss (dB) (max) |
|  <b>RF341</b>  | 5             | 61             | DC-2                   | 1.2 : 1    | 30                                   | 0.5                       |
|   | 12            | 500            | 2-4                    | 1.2 : 1    | 25                                   | 0.8                       |
|   | 26            | 2000           | 4-6                    | 1.4 : 1    | 20                                   | 2.0                       |
|  <b>GRF341</b> | 5             | 61             | DC-2                   | 1.2 : 1    | 35                                   | 0.3                       |
|   | 12            | 500            | 2-4                    | 1.3 : 1    | 30                                   | 0.7                       |
|   | 26            | 2000           | 4-6                    | 1.4 : 1    | 25                                   | 1.5                       |



341

SCHEMATIC  
(Coil A Last Energized)

Schematics as viewed from terminals




## RF RELAYS

### Series RF310/RF313 Electromechanical Relays



The ultraminiature RF310 and RF313 relays are designed with an internal bypass (through path), when the coil is de-energized, to provide low insertion loss and VSWR through the bypass and simplicity of design for the user. Relays have improved RF insertion loss repeatability over the frequency range from DC to 3 GHz. Highly suitable for use in attenuator, linear amplifier and other RF circuits.

- N.C. bypass configuration
- Repeatability insertion loss
- Broad Bandwidth
- Metal Enclosure for EMI shielding
- Ground pin option to improve ground case RF grounding
- High isolation between control and signal path

| Relay Type                |
|---------------------------|
| Normally Closed Bypass    |
| Coil Type                 |
| 310 = Standard Coil       |
| 313 = Sensitive Coil      |
| Mounting                  |
| RF = Thru-hole            |
| Temperature               |
| Storage: -65°C to +125°C  |
| Operating: -55°C to +85°C |



RF310  
RF313


| Part No.   | Nominal Coil  |                | Typical RF Performance |            |              |                |              |                     |              |
|--|---------------|----------------|------------------------|------------|--------------|----------------|--------------|---------------------|--------------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR       |              | Isolation (dB) |              | Insertion Loss (dB) |              |
|  |               |                |                        | N.O. (max) | Bypass (max) | N.O. (min)     | Bypass (min) | N.O. (max)          | Bypass (max) |
|  <b>RF310</b> | 5             | 50             | DC-1                   | 1.2 : 1    | 1.3 : 1      | 35             | 25           | 0.2                 | 0.3          |
|  | 12            | 390            | 1-2                    | 1.2 : 1    | 1.3 : 1      | 25             | 25           | 0.3                 | 0.4          |
|  |               |                | 2-3                    | 1.4 : 1    | 1.3 : 1      | 25             | 20           | 0.4                 | 0.5          |
|  <b>RF313</b> | 5             | 100            | DC-1                   | 1.2 : 1    | 1.3 : 1      | 35             | 25           | 0.2                 | 0.3          |
|  | 12            | 850            | 1-2                    | 1.2 : 1    | 1.3 : 1      | 25             | 25           | 0.3                 | 0.4          |
|  |               |                | 2-3                    | 1.5 : 1    | 1.3 : 1      | 25             | 20           | 0.5                 | 0.4          |

### Series RF320/RF323 Electromechanical Relays



The ultraminiature RF320 and RF323 relays are designed with an internal bypass (through path), when the coil is energized, to provide low insertion loss and VSWR through the bypass and simplicity of design for the user. The RF320 and RF323 relays have improved RF insertion loss repeatability over the frequency range from DC to 3 GHz. Highly suitable for use in attenuator, linear amplifier and other RF circuits.

- N.O. bypass configuration
- Repeatability insertion loss
- Broad Bandwidth
- Metal Enclosure for EMI shielding
- Ground pin option to improve ground case RF grounding
- High isolation between control and signal path

| Relay Type                |
|---------------------------|
| Normally Open Bypass      |
| Coil Type                 |
| 320 = Standard Coil       |
| 323 = Sensitive Coil      |
| Mounting                  |
| RF = Thru-hole            |
| Temperature               |
| Storage: -65°C to +125°C  |
| Operating: -55°C to +85°C |



RF320  
RF323

| Part No.   | Nominal Coil  |                | Typical RF Performance |            |              |                |              |                     |              |
|--|---------------|----------------|------------------------|------------|--------------|----------------|--------------|---------------------|--------------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR       |              | Isolation (dB) |              | Insertion Loss (dB) |              |
|  |               |                |                        | N.C. (max) | Bypass (max) | N.C. (min)     | Bypass (min) | N.C. (max)          | Bypass (max) |
|  <b>RF320</b> | 5             | 50             | DC-1                   | 1.2 : 1    | 1.4 : 1      | 30             | 25           | 0.2                 | 0.4          |
|  | 12            | 390            | 1-2                    | 1.2 : 1    | 1.4 : 1      | 30             | 20           | 0.3                 | 0.4          |
|  |               |                | 2-3                    | 1.4 : 1    | 1.4 : 1      | 25             | 20           | 0.4                 | 0.6          |
|  <b>RF323</b> | 5             | 100            | DC-1                   | 1.2 : 1    | 1.4 : 1      | 30             | 25           | 0.2                 | 0.4          |
|  | 12            | 850            | 1-2                    | 1.2 : 1    | 1.4 : 1      | 30             | 20           | 0.3                 | 0.4          |
|  |               |                | 2-3                    | 1.4 : 1    | 1.4 : 1      | 25             | 20           | 0.4                 | 0.5          |

Schematics as viewed from terminals

## RF RELAYS

### Series A150 Electromechanical Relays


The Series A150 ultraminiature Attenuator Relays are designed for attenuating RF signals in 50-ohm systems over a frequency range from DC to 3 GHz. Their low profile and small grid spacing makes them ideal for use when packaging density is a prime consideration. The A150 relays eliminate the need for additional external resistors.

These single section, switchable attenuator relays have internal matched thin film attenuator pads in "L," "T" or "Pi" configurations, as applicable. Relays are available in fixed increments of 1, 2, 3, 4, 5, 6, 8, 10, 16 and 20 dB, which can be used singly or in combination to achieve the attenuation levels desired.

The GA150 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.



- Excellent phase linearity
- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| RF Attenuator   |
| Coil Type   |
| A150 = Standard Coil                                  |
| Mounting  |
| A = Thru-hole<br>GA = Surface-Mount (Stub)            |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |



150

SCHEMATIC  
(Bottom View)

| Part No.   | Nominal Coil  |                | Typical RF Performance |                        |                  |                     |      |
|--|---------------|----------------|------------------------|------------------------|------------------|---------------------|------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR                   |                  | Insertion Loss (dB) |      |
|  |               |                |                        | Attenuated Path (Typ.) | Thru Path (Max.) | Typ.                | Max. |
|  <b>A150</b>    | 5             | 50             | DC-1                   | 1.20 : 1               | 1.10 : 1         | 0.1                 | 0.25 |
|  | 12            | 390            | 1-2                    | 1.30 : 1               | 1.20 : 1         | 0.2                 | 0.35 |
|  | 15            | 610            | 2-3                    | 1.40 : 1               | 1.25 : 1         | 0.3                 | 0.55 |
|  | 26            | 1560           |                        |                        |                  |                     |      |
|  <b>GA150</b> | 5             | 50             | DC-1                   | 1.20 : 1               | 1.20 : 1         | 0.1                 | 0.25 |
|  | 12            | 390            | 1-2                    | 1.20 : 1               | 1.20 : 1         | 0.2                 | 0.35 |
|  | 15            | 610            | 2-3                    | 1.20 : 1               | 1.30 : 1         | 0.3                 | 0.45 |
|  | 26            | 1560           |                        |                        |                  |                     |      |

### Series A152 Electromechanical Relays


The Series A152 highly repeatable ultraminiature attenuator relays are designed for attenuating RF signals in 50-ohm systems over a frequency range from DC to 5 GHz. Their low profile and small grid spacing makes them ideal for use when packaging density is a prime consideration. The A152 relays eliminate the need for additional external resistors/attenuators.

These single section, switchable attenuator relays have an internal matched thin film attenuator pad in a "Pi" configuration. Relays are available in a fixed increment of 20 dB. (Other values available)

The GA152 features a unique ground shield that isolates and shields each lead to ensure excellent contact-to-contact isolation. This ground shield provides a ground interface that results in improved high-frequency performance as well as parametric repeatability.



- Hermetically Sealed
- High Resistance to ESD
- Metal Enclosure for EMI shielding
- High Repeatability
- Broader bandwidth
- Through-hole or surface-mount configurations

| Relay Type  |
|---|
| RF Attenuator   |
| Coil Type   |
| A152 = Standard Coil                                  |
| Mounting  |
| A = Thru-hole<br>GA = Surface-Mount (Stub)            |
| Temperature   |
| Storage: -65°C to +125°C<br>Operating: -55°C to +85°C |



152

SCHEMATIC  
(Bottom View)

| Part No.   | Nominal Coil  |                | Typical RF Performance |                        |                  |                     |      |
|--|---------------|----------------|------------------------|------------------------|------------------|---------------------|------|
|  | Voltage (Vdc) | Resistance (Ω) | Frequency (GHz)        | VSWR                   |                  | Insertion Loss (dB) |      |
|  |               |                |                        | Attenuated Path (Typ.) | Thru Path (Max.) | Typ.                | Max. |
|  <b>A152</b>  | 5             | 50             | DC-1                   | 1.20 : 1               | 1.10 : 1         | 0.1                 | 0.25 |
|  | 12            | 390            | 1-2                    | 1.30 : 1               | 1.20 : 1         | 0.2                 | 0.35 |
|  | 15            | 610            | 2-3                    | 1.40 : 1               | 1.25 : 1         | 0.3                 | 0.55 |
|  | 26            | 1560           | 3-5                    |                        |                  | See Datasheet       |      |
|  <b>GA152</b> | 5             | 50             | DC-1                   | 1.20 : 1               | 1.20 : 1         | 0.1                 | 0.25 |
|  | 12            | 390            | 1-2                    | 1.20 : 1               | 1.20 : 1         | 0.2                 | 0.35 |
|  | 15            | 610            | 2-3                    | 1.20 : 1               | 1.30 : 1         | 0.3                 | 0.45 |
|  | 26            | 1560           | 3-5                    | 1.40 : 1               | 1.70 : 1         | 0.4                 | 0.55 |

## COMMERCIAL RELAYS

### Series 122C Electromechanical Relays

The 122C Centigrad® magnetic-latching relay is an ultraminiature, hermetically sealed, armature relay capable of being directly driven by most IC logic families. Its low profile height and .100" (2.54 mm) grid spaced terminals, which precludes the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required.


The basic operating function and internal structure are similar to Teledyne's TO-5, 422 relay series. The 122C is capable of meeting Teledyne Relays' T2R® requirements.


The Series 122C relay has internal silicon diodes for coil suppression, Zener diodes to protect the MOSFET gate inputs, and N-channel enhancement-mode MOSFET chips, which enable direct relay interfacing with most microprocessor and IC logic families (CMOS, TTL and MOS).

The 122C magnetic-latching relay is ideally suited for applications where coil operating power must be minimized. The relays can be operated with a short-duration pulse. After the contacts have transferred, no external coil power is required.

The magnetic-latching feature of the Series 122C relay provides a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  | Part No.   | Nominal Coil  |                   |       |                      | Contact Load Rating |                                     |
|---|--|---------------|-------------------|-------|----------------------|---------------------|-------------------------------------|
|   |  | Voltage (Vdc) | Coil Current (mA) |       | Operating Power (mW) |                     | Latch and Reset Voltage (Vdc) (Max) |
| DPDT Magnetic-Latching                                  |  <b>122C</b> | 5             | 82.2              | 114.9 | 505                  | 3.5                 | Resistive: 1A/28Vdc                 |
| CMOS Feature  |  | 6             | 41.6              | 57.0  | 296                  | 4.5                 | Inductive: 200mA/28Vdc (320mH)      |
| Internal power MOSFET driver and diode coil suppression |  | 9             | 27.4              | 37.2  | 288                  | 6.8                 | Lamp: 100mA/28Vdc                   |
| Vibration   |  | 12            | 20.5              | 27.8  | 287                  | 9.0                 | Low Level: 10 to 50 uA/10 to 50 mV  |
| Shock   |  | 18            | 13.7              | 18.2  | 286                  | 13.5                |                                     |
|   |  | 26            | 11.4              | 15.2  | 351                  | 18.0                |                                     |
| Acceleration  |  |               |                   |       |                      |                     |                                     |
| 50 g's  |  |               |                   |       |                      |                     |                                     |
| Temperature   |  |               |                   |       |                      |                     |                                     |
| Storage: -65°C to +125°C                                |  |               |                   |       |                      |                     |                                     |
| Operating: -55°C to +85°C                               |  |               |                   |       |                      |                     |                                     |

SCHMATIC  
(Coil A Last Energized)


### Series 172 Electromechanical Relays



The 172 Centigrad® relay is an ultraminiature, hermetically sealed, armature relay for commercial applications. Its low profile height .280" (7.11 mm) and .100" (2.54 mm) grid spaced terminals, which preclude the need for spreader pads, make it an ideal choice where extreme packaging density and/or close PC board spacing are required.

The Series 172 relay has an internal discrete silicon diode for coil transient suppression.

By virtue of its inherently low intercontact capacitance and contact circuit losses, the 172 relay is an excellent subminiature RF switch for frequencies well into the UHF spectrum. Applications include telecommunications, test instruments, mobile communications, attenuators, and automatic test equipment.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  | Part No.  | Nominal Coil  |                |                    |                      | Contact Load Rating                |
|---|---|---------------|----------------|--------------------|----------------------|------------------------------------|
|   |   | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | Operating Power (mW) |                                    |
| DPDT Non-Latching                                 |  <b>172</b><br><b>172D</b> | 3             | 39             | 2.25               | 235                  | Resistive: 1A/28Vdc                |
| Diode Options                                     |   | 5             | 64             | 3.8                | 405                  | Inductive: 200mA/28Vdc (320mH)     |
| D = Internal diode for coil transient suppression |   | 12            | 400            | 9.0                | 360                  | Lamp: 100mA/28Vdc                  |
| Vibration   |   | 26            | 1600           | 18.0               | 440                  | Low Level: 10 to 50 uA/10 to 50 mV |
| Shock   |   |               |                |                    |                      |                                    |
| 30 g's 6 msec, half-sine                          |   |               |                |                    |                      |                                    |
| Temperature                                       |   |               |                |                    |                      |                                    |
| Storage: -65°C to +125°C                          |   |               |                |                    |                      |                                    |
| Operating: -55°C to +85°C                         |   |               |                |                    |                      |                                    |

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage

## COMMERCIAL RELAYS


### Series 712 Electromechanical Relays


The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, the Series 712 relays are some of the most versatile ultraminiature relays available because of their small size and low coil power dissipation.

The Series 712D relay has an internal discrete silicon diode for coil transient suppression. The hybrid Series 712TN relay has an internal silicon diode and transistor driver. The integrated packaging of the relay with its associated semiconductor devices greatly reduces PC board floor space requirements as well as component installation costs.


By virtue of its inherently low intercontact capacitance and contact circuit losses, the 712 has proven to be excellent ultraminiature RF switch for frequency ranges well into the UHF spectrum. A typical RF application for the TO-5 relay is in handheld radio transceivers, wherein the combined features of good RF performance, small size, low coil power dissipation and high reliability make it a preferred method of Transmit-Receive switching.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type   |  | Part No.   | Nominal Coil  |                |                    |                                       | Contact Load Rating  |
|--|--|--|---------------|----------------|--------------------|---------------------------------------|--|
| DPDT Non-Latching  |  |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | Base Current to Turn On (712 TN only) |  |
| Diode Options  |  |  | 5             | 50             | 3.6                | 3.00                                  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| D = Internal diode for coil transient suppression                    |  |  | 6             | 98             | 4.2                | 2.04                                  |  |
| TN = Internal transistor driver and coil transient suppression diode |  |  | 9             | 220            | 6.5                | 1.36                                  |  |
| Vibration  |  |  | 12            | 390            | 8.4                | 1.03                                  |  |
| Shock  |  |  | 18            | 880            | 13.0               | 0.68                                  |  |
| 10 g's to 500 Hz   |  | 26   | 1560          | 17.0           | 0.50               |                                       |  |
| Temperature  |  |  |               |                |                    |                                       |  |
| Storage: -65°C to +125°C   |  |  |               |                |                    |                                       |  |
| Operating: -55°C to +85°C  |  |  |               |                |                    |                                       |  |



712



712D



712TN

Schematics as viewed from terminals


### Series 722 Electromechanical Relays


The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, the 722 relay has become one of the most versatile ultraminiature relays available because of its small size and low coil power dissipation.

The Series 722D relay has discrete silicon diodes for coil transient suppression.


The Series 722 magnetic-latching relays are ideally suited for applications where coil power dissipation must be minimized. The relays can be operated with a short duration pulse and after the contacts have transferred, no external coil power is required. The magnetic-latching feature of the Series 722 provides a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.  | Nominal Coil  |                |                           | Contact Load Rating  |
|---|--|---|---------------|----------------|---------------------------|--|
| DPDT Magnetic-Latching                            |  |   | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |  |
| Diode Options                                     |  |  | 5             | 61             | 3.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| D = Internal diode for coil transient suppression |  |   | 6             | 120            | 4.5                       |  |
| Vibration   |  |   | 9             | 280            | 6.8                       |  |
| Shock   |  |   | 12            | 500            | 9.0                       |  |
| 10 g's to 500 Hz                                  |  |   | 18            | 1130           | 13.5                      |  |
| Temperature                                       |  | 26  | 2000          | 18.0           |                           |  |
| Storage: -65°C to +125°C                          |  |   |               |                |                           |  |
| Operating: -55°C to +85°C                         |  |   |               |                |                           |  |



722



722D

SCHEMATIC  
(Coil A Last Energized)  
(Bottom View)

SCHEMATIC  
(Coil A Last Energized)  
(Bottom View)


## COMMERCIAL RELAYS


### Series 732 Electromechanical Relays

The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, the Series 732 relay is one of the most versatile ultraminiature relays available because of their small size and low coil power dissipation. The sensitive 732 relay has a high resistance coil, thus requiring extremely low operating power (200 mW typical). The advantages of reduced heat dissipation and power supply demands are a plus. The Series 732D relay has an internal discrete silicon diode for coil transient suppression. The hybrid Series 732TN relay has an internal silicon diode and transistor driver. The integrated packaging of the relay with its associated semiconductor devices greatly reduces PC board floor space requirements as well as component installation costs.


By virtue of its inherently low intercontact capacitance and contact circuit losses, the 732 has proven to be excellent ultraminiature RF switch for frequency ranges well into the UHF spectrum. A typical RF application for the TO-5 relay is in handheld radio transceivers, wherein the combined features of good RF performance, small size, low coil power dissipation and high reliability make it a preferred method of Transmit-Receive switching.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type   |                          | Part No.   | Nominal Coil  |                |                    |                                       | Contact Load Rating  |
|--|--------------------------|--|---------------|----------------|--------------------|---------------------------------------|--|
| DPDT Non-Latching Coil   |                          |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | Base Current to Turn On (712 TN only) |  |
| Diode Options  |                          |  | 5             | 100            | 3.5                | 1.50                                  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| D = Internal diode for coil transient suppression                    |                          |  | 6             | 200            | 4.5                | 1.00                                  |  |
| TN = Internal transistor driver and coil transient suppression diode |                          |  | 9             | 400            | 6.8                | 0.75                                  |  |
| Vibration  | Shock                    |  | 12            | 850            | 9.0                | 0.47                                  |  |
| 10 g's to 500 Hz   | 30 g's 6 msec, half-sine |  | 18            | 1600           | 13.5               | 0.38                                  |  |
| Temperature  |                          | 26   | 3300          | 18.0           | 0.24               |                                       |  |
| Storage: -65°C to +125°C   |                          |  |               |                |                    |                                       |  |
| Operating: -55°C to +85°C  |                          |  |               |                |                    |                                       |  |



732



732D



732TN

Schematics as viewed from terminals

## COMMERCIAL SURFACE-MOUNT RELAYS

### Series S114 & S134 Electromechanical Relays





The Series S114 Surface Mount Centigrad® Relay is an ultraminiature, hermetically sealed, armature relay. The low profile height .360" (9.14 mm) and .100" (2.54 mm) lead spacing make it ideal for applications where extreme packaging density and/or close PC board spacing are required. The specially formed leads are pre-tinned to make the relays ideal for most types of surface mount solder reflow processes.


The basic design and internal construction are identical to the Series 114 & 134 Centigrad® relays, and are capable of meeting Teledyne Relays' T2R® requirements.

The S114D and S114DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection.


The sensitive S134 surface mount Centigrad® Relay has a high resistance coil, thus requiring extremely low operating power (200 mW typical). The advantages of reduced heat dissipation and power supply demands are a plus.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  | Part No.  | Nominal Coil                |                               |  |   | Contact Load Rating                          |  |  |
|---|---|-----------------------------|-------------------------------|--|---|--|--|--|
|   |   | Voltage (Vdc)               | Resistance (Ω)                | P.U.V (Vdc) (max.)                       | D.O.V (Vdc) min. max.                     |  |  |  |
| DPDT Non-Latching   |   |                             |                               |  |   |  |  |  |
| Coil Type   |   |                             |                               |  |   |  |  |  |
| S114 = Standard Coil  |   |                             |                               |  |   | Resistive: 1A/28Vdc                          |  |  |
| S134 = Sensitive Coil   |   |                             |                               |  |   | Inductive: 200mA/28Vdc (320mH)               |  |  |
| Diode Options   |   |                             |                               |  |   | Lamp: 100mA/28Vdc                            |  |  |
| D = Internal diode for coil transient suppression                                   |   |                             |                               |  |   | Low Level: 10 to 50 uA/10 to 50 mV           |  |  |
| DD = Internal diode for coil transient suppression and polarity reversal protection |   |                             |                               |  |   |  |  |  |
| Vibration   |   |                             |                               |  |   |  |  |  |
| Shock   |   |                             |                               |  |   |  |  |  |
| 30 g's to 3000 Hz   |   |                             |                               |  |   |  |  |  |
| 75 g's 6 msec, half-sine  |   |                             |                               |  |   |  |  |  |
| Acceleration  |   |                             |                               |  |   |  |  |  |
| 50 g's  |   |                             |                               |  |   |  |  |  |
| Temperature   |   |                             |                               |  |   |  |  |  |
| Storage: -65°C to +125°C  |   |                             |                               |  |   |  |  |  |
| Operating: -55°C to +85°C   |   |                             |                               |  |   |  |  |  |
|   |    | <b>S114</b><br><b>S114D</b> | 5<br>6<br>9<br>12<br>18<br>26 | 50<br>98<br>220<br>390<br>880<br>1560    | 3.5<br>4.5<br>6.8<br>9.0<br>13.5<br>18.0  | 0.14<br>0.18<br>0.35<br>0.41<br>0.59<br>0.89 | 2.3<br>3.2<br>4.9<br>6.5<br>10.0<br>13.0 |  |
|   |  | <b>S114DD</b>               | 5<br>6<br>9<br>12<br>18<br>26 | 39<br>78<br>220<br>390<br>880<br>1560    | 4.0<br>5.0<br>7.8<br>10.0<br>14.5<br>19.0 | 0.6<br>0.7<br>0.8<br>0.9<br>1.1<br>1.4       | 2.8<br>3.4<br>5.3<br>6.5<br>10.0<br>13.0 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |  | <b>S134</b><br><b>S134D</b> | 5<br>6<br>9<br>12<br>18<br>26 | 100<br>200<br>400<br>800<br>1600<br>3200 | 3.5<br>4.5<br>6.8<br>9.0<br>13.5<br>18.0  | 0.12<br>0.18<br>0.35<br>0.41<br>0.59<br>0.89 | 2.5<br>3.2<br>4.9<br>6.5<br>10.0<br>13.0 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |  | <b>S134DD</b>               | 5<br>6<br>9<br>12<br>18<br>26 | 64<br>125<br>400<br>800<br>1600<br>3200  | 3.7<br>4.8<br>8.0<br>11.0<br>14.5<br>19.0 | 0.7<br>0.8<br>0.9<br>1.0<br>1.1<br>1.3       | 2.6<br>3.0<br>4.5<br>5.8<br>9.0<br>13.0  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |



S114  
S134



S114D  
S134D



S114DD  
S134DD

Schematics as viewed from terminals




## COMMERCIAL SURFACE-MOUNT RELAYS


### Series S172 Electromechanical Relays

The S172 surface mount Centigrad® relay is an ultraminiature, hermetically sealed, armature relay for commercial applications. Its low profile height .470" (11.94 mm) and .100" (2.54 mm) grid spaced terminals make it an ideal choice where extreme packaging density and/or close PC board spacing are required. The specially formed surface-mount leads are pre-tinned to make the relays ideal for all types of surface-mount solder reflow processes.


The basic design and internal structure are similar to Teledyne's DPDT 114 Centigrad® relay. (see page 16) The S172D relay has an internal discrete silicon diode for coil transient suppression.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.  | Nominal Coil  |                |                    |                      | Contact Load Rating                |                                |
|---|--|---|---------------|----------------|--------------------|----------------------|------------------------------------|--------------------------------|
| DPDT Non-Latching                                 |  |   | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | Operating Power (mW) |                                    |                                |
| <b>Diode Options</b>                              |  |  | 5             | 64             | 3.8                | 405                  | Resistive: 1A/28Vdc                |                                |
| D = Internal diode for coil transient suppression |  |   | S172          | 12             | 400                | 9.0                  | 360                                | Inductive: 200mA/28Vdc (320mH) |
| <b>Vibration</b>                                  |  |   | S172D         | 26             | 1600               | 18.0                 | 440                                | Lamp: 100mA/28Vdc              |
| <b>Shock</b>                                      |  |   |               |                |                    |                      | Low Level: 10 to 50 uA/10 to 50 mV |                                |
| 10 g's to 500 Hz                                  |  |   |               |                |                    |                      |                                    |                                |
| 30 g's 6 msec, half-sine                          |  |   |               |                |                    |                      |                                    |                                |
| <b>Temperature</b>                                |  |   |               |                |                    |                      |                                    |                                |
| Storage: -65°C to +125°C                          |  |   |               |                |                    |                      |                                    |                                |
| Operating: -55°C to +85°C                         |  |   |               |                |                    |                      |                                    |                                |



S172



S172D


### Series S422 Electromechanical Relays


The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board surface mounting, its small size and low coil power dissipation make the S422 relay one of the most versatile ultraminiature relays available.

The Series S422D and S422DD utilize discrete diodes for coil suppression and polarity reversal protection. The Series S422 magnetic-latching relays are ideally suited for applications where power dissipation must be minimized. The relays can be operated with a short duration pulse. After the contacts have transferred, no external holding power is required.




The magnetic-latching feature of the Series S422 relays provide a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.  | Nominal Coil  |                |                           | Contact Load Rating |                                    |
|---|--|---|---------------|----------------|---------------------------|---------------------|------------------------------------|
| DPDT Magnetic-Latching  |  |   | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |                     |                                    |
| <b>Diode Options</b>  |  |  | 5             | 61             | 3.5                       | Resistive: 1A/28Vdc |                                    |
| D = Internal diode for coil transient suppression                                   |  |   | S422          | 6              | 120                       | 4.5                 | Inductive: 200mA/28Vdc (320mH)     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   | S422D         | 9              | 280                       | 6.8                 | Lamp: 100mA/28Vdc                  |
| <b>Vibration</b>  |  |   | S422D         | 12             | 500                       | 9.0                 | Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Shock</b>  |  |   | S422D         | 18             | 1130                      | 13.5                |                                    |
| 10 g's to 500 Hz  |  |   | 26            | 2000           | 18.0                      |                     |                                    |
| 30 g's 6 msec, half-sine  |  |   |               |                |                           |                     |                                    |
| <b>Temperature</b>  |  |   |               |                |                           |                     |                                    |
| Storage: -65°C to +125°C  |  |   |               |                |                           |                     |                                    |
| Operating: -55°C to +85°C   |  |   |               |                |                           |                     |                                    |



S422DD



Schematics as viewed from terminals

SCHEMATIC  
(Coil A Last Energized)

SCHEMATIC  
(Coil A Last Energized)

SCHEMATIC  
(Coil A Last Energized)

## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS



### Series ER114 Electromechanical Relays

The Series ER114 Centigrad® relay is an ultraminiature, hermetically sealed, armature relay. Its low profile height .275" (7 mm) and .100" (2.54 mm) grid spaced terminals, which precludes the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required. The basic design and internal construction are similar to the standard Teledyne DPDT TO-5 relay (e.g., Series ER412).

The Series ER114D and ER114DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection.

By virtue of its inherently low intercontact capacitance and contact circuit losses, the ER114 relay has proven to be an excellent ultraminiature RF switch for frequency ranges well into the UHF spectrum. A typical RF application for the ER114 relay is in handheld radio transceivers, wherein the combined features of good RF performance, small size, low coil power dissipation and high reliability make it a preferred method of Transmit-Receive switching.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |                          | Part No.   | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|--------------------------|--|---------------|----------------|--------------------|-------------|---------------------|--|
| DPDT Non-Latching   |                          |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Diode Options   |                          |  |               |                |                    | min.        |                     | max.   |
| D = Internal diode for coil transient suppression                                   |                          |  <b>ER114</b>     | 5             | 50             | 3.5                | 0.14        | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| DD = Internal diode for coil transient suppression and polarity reversal protection |                          |  | 6             | 98             | 4.5                | 0.18        | 3.2                 |  |
| Vibration   |                          |  | 9             | 220            | 6.8                | 0.35        | 4.9                 |  |
| Shock   |                          |  | 12            | 390            | 9.0                | 0.41        | 6.5                 |  |
| Temperature   |                          |  | 18            | 880            | 13.5               | 0.59        | 10.0                |  |
| 30 g's to 3000 Hz   | 75 g's 6 msec, half-sine | 26   | 1560          | 18.0           | 0.89               | 13.0        |                     |  |
| Acceleration  |                          |  <b>ER114DD</b> | 5             | 39             | 4.0                | 0.6         | 2.8                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Operating & Storage: -65°C to +125°C  |                          |  | 6             | 78             | 5.0                | 0.7         | 3.4                 |  |
| 50 g's  |                          |  | 9             | 220            | 7.8                | 0.8         | 5.3                 |  |
|   |                          |  | 12            | 390            | 10.0               | 0.9         | 6.5                 |  |
|   |                          |  | 18            | 880            | 14.5               | 1.1         | 10.0                |  |
|   |                          | 26   | 1560          | 19.0           | 1.4                | 13.0        |                     |  |


### Series ER116C Electromechanical Relays

The ER116C Centigrad® relay is an ultraminiature, hermetically sealed, armature relay capable of being directly driven by most IC logic families. Its low profile height and .100" (2.54 mm) grid spaced terminals, which preclude the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required.


The Series ER116C utilizes an internal silicon diode for coil suppression, a Zener diode to protect the MOSFET gate input, and an N-channel enhancement mode MOSFET chip, which enables direct relay interfacing with most Microprocessor and IC logic families (CMOS, TTL and MOS).

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration


| Relay Type  |  | Part No.  | Nominal Coil  |                   |       |                      | Contact Load Rating |  |
|---|--|---|---------------|-------------------|-------|----------------------|---------------------|--|
| DPDT Non-Latching   |  |   | Voltage (Vdc) | Coil Current (mA) |       | Operating Power (mW) |                     | P.U.V (Vdc) (max.)   |
| CMOS Feature  |  |   |               | Min.              | Max.  |                      |                     |  |
| Internal power MOSFET driver, Zener diode gate protection, and diode coil suppression |  |  <b>ER116C</b> | 5             | 96.5              | 132.3 | 641                  | 4.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Vibration   |  |   | 6             | 60.3              | 83.9  | 462                  | 4.9                 |  |
| Shock   |  |   | 9             | 33.1              | 47.1  | 368                  | 7.3                 |  |
| Temperature   |  |   | 12            | 24.9              | 36.1  | 369                  | 9.8                 |  |
| 50 g's  |  |   | 18            | 16.1              | 24.1  | 368                  | 14.6                |  |
| Operating & Storage: -65°C to +125°C  |  |   | 26            | 12.9              | 19.9  | 450                  | 19.5                |  |




ER114



ER114D



ER114DD



ER116C

P.U.V = Pick-Up Voltage

Schematics as viewed from terminals

## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS



### Series ER134 Electromechanical Relays

The ER134 sensitive Centigrad® relay retains the same features as the ER114 standard Centigrad® relay with only a minimal increase in profile height .375" (9.53 mm). Its .100" (2.54 mm) grid spaced terminals, which preclude the need for spreader pads, and its low profile make the ER134 relay ideal for applications where high packaging density is important.

The Series ER134D and ER134DD have internal discrete silicon diodes for coil suppression and polarity reversal protection.

The sensitive ER134 Centigrad® relay has a high resistance coil, thus requiring extremely low operating power (200 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.  | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|--|---|---------------|----------------|--------------------|-------------|---------------------|--|
| DPDT Non-Latching   |  |   | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Diode Options   |  |   |               |                |                    | min.        |                     | max.   |
| D = Internal diode for coil transient suppression                                   |  |  <b>ER134</b><br><b>ER134D</b> | 5             | 100            | 3.5                | 0.12        | 2.5                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   | 6             | 200            | 4.5                | 0.18        | 3.2                 |  |
| Vibration   |  |   | 9             | 400            | 6.8                | 0.35        | 4.9                 |  |
| Shock   |  |   | 12            | 800            | 9.0                | 0.41        | 6.5                 |  |
| 30 g's to 3000 Hz   |  |   | 18            | 1600           | 13.5               | 0.59        | 10.0                |  |
| 75 g's 6 msec, half-sine  |  | 26  | 3200          | 18.0           | 0.89               | 13.0        |                     |  |
| Acceleration  |  |  <b>ER134DD</b>               | 5             | 64             | 3.7                | 0.7         | 2.6                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Temperature   |  |   | 6             | 125            | 4.8                | 0.8         | 3.0                 |  |
| 50 g's  |  |   | 9             | 400            | 8.0                | 0.9         | 4.5                 |  |
| Operating & Storage: -65°C to +125°C  |  |   | 12            | 800            | 11.0               | 1.0         | 5.8                 |  |
|   |  |   | 18            | 1600           | 14.5               | 1.1         | 9.0                 |  |
|   |  | 26  | 3200          | 19.0           | 1.3                | 13.0        |                     |  |


### Series ER136C Electromechanical Relays


The sensitive ER136C Centigrad® relay is an ultraminiature, hermetically sealed, armature relay capable of being directly driven by most IC logic families. Its low profile height and .100" (2.54 mm) grid spaced terminals, which precludes the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required.

The sensitive ER136C Centigrad® relay has a high resistance coil, thus requiring extremely low operating power (200 mW, typical). The advantages of reduced heat dissipation and power supply demands are a plus.


The sensitive Series ER136C utilizes an internal silicon diode for coil suppression, a Zener diode to protect the MOSFET gate input, and an N-channel enhancement-mode MOSFET chip that enables direct relay interfacing with most microprocessor and IC logic families (CMOS, TTL and MOS).

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration


| Relay Type  |  | Part No.  | Nominal Coil  |                   |      |                      | Contact Load Rating |  |
|---|--|---|---------------|-------------------|------|----------------------|---------------------|--|
| DPDT Non-Latching   |  |   | Voltage (Vdc) | Coil Current (mA) |      | Operating Power (mW) |                     | P.U.V (Vdc) (max.)   |
| CMOS Feature  |  |   |               | Min.              | Max. |                      |                     |  |
| Internal power MOSFET driver, Zener diode gate protection, and diode coil suppression |  |  <b>ER136C</b> | 5             | 43.0              | 56.0 | 250                  | 4.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Vibration   |  |   | 6             | 27.0              | 33.0 | 180                  | 4.9                 |  |
| Shock   |  |   | 9             | 17.8              | 26.4 | 203                  | 7.3                 |  |
| 30 g's to 3000 Hz   |  |   | 12            | 11.3              | 17.7 | 180                  | 9.8                 |  |
| 75 g's 6 msec, half-sine  |  |   | 18            | 8.4               | 13.8 | 203                  | 14.6                |  |
| Acceleration  |  |   | 26            | 5.8               | 10.2 | 219                  | 19.5                |  |
| Temperature   |  |   |               |                   |      |                      |                     |  |
| 50 g's  |  |   |               |                   |      |                      |                     |  |
| Operating & Storage: -65°C to +125°C  |  |   |               |                   |      |                      |                     |  |




ER134



ER134D



ER134DD



ER136C

PIN 1: + SUPPLY  
PIN 9: - SUPPLY  
PIN 10: GATE

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage

## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS

### Series ER411 & ER431 Electromechanical Relays







The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed specifically for high-density PC board mounting, its small size and low coil power dissipation make the ER411 relay one of the most versatile ultraminiature relays available.


The Series ER411D and ER411DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid ER411T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

The sensitive ER431 relay has a high resistance coil, thus requiring extremely low operating power (150 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.


The Series ER431D and ER431DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid ER431T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by minimizing the number of external components needed to drive the relay.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |  | Part No.  | Nominal Coil  |  |                    |             | Contact Load Rating |  |  |     |
|---|--|---|---------------|--|--------------------|-------------|---------------------|--|--|-----|
| SPDT Non-Latching   |  |   | Voltage (Vdc) | Resistance (Ω)   | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |  |     |
| Coil Type   |  |   |               |  |                    | min.        |                     | max.   |  |     |
| ER411 = Standard Coil   |  |  <b>ER411</b>                   | 5             | 63   | 3.7                | 0.15        | 2.4                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |  |     |
| ER431 = Sensitive Coil  |  |   | 6             | 125  | 4.5                | 0.18        | 2.8                 |  |  |     |
| Diode Options   |  |   | 9             | 280  | 6.8                | 0.35        | 4.2                 |  |  |     |
| D = Internal diode for coil transient suppression                                   |  |   | 12            | 500  | 9.0                | 0.40        | 5.6                 |  |  |     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   | 18            | 1130   | 13.5               | 0.58        | 8.4                 |  |  |     |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26  | 2000          | 18.0   | 0.89               | 10.4        |                     |  |  |     |
| Vibration   |  | Shock   |               |  <b>ER411DD</b> |                    |             |                     |  |  |     |
| 30 g's to 3000 Hz   |  | 75 g's 6 msec, half-sine  |               |  |                    |             |                     |  |  |     |
| Acceleration  |  | Temperature   |               |  |                    |             |                     |  |  |     |
| 50 g's  |  | Operating & Storage: -65°C to +125°C  |               |  <b>ER411T</b>  |                    |             |                     |  |  |     |
| ER411 = Standard Coil   |  | 5   | 63            |  |                    |             |                     | 3.9  | 0.15   | 2.4 |
| ER431 = Sensitive Coil  |  | 6   | 125           |  |                    |             |                     | 5.2  | 0.18   | 2.8 |
| Diode Options   |  | 9   | 280           |  |                    |             |                     | 7.8  | 0.35   | 4.2 |
| D = Internal diode for coil transient suppression                                   |  | 12  | 500           |  |                    |             |                     | 10.0   | 0.40   | 5.6 |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  | 18  | 1130          | 14.5   | 0.58               | 8.4         |                     |  |  |     |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26  | 2000          | 19.0   | 0.89               | 10.4        |                     |  |  |     |
| ER411 = Standard Coil   |  |  <b>ER431</b><br><b>ER431D</b> |               | 5  | 125                | 3.7         | 0.15                | 2.0  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |     |
| ER431 = Sensitive Coil  |  |   |               | 6  | 255                | 4.5         | 0.18                | 2.8  |  |     |
| Diode Options   |  |   |               | 9  | 630                | 6.8         | 0.35                | 4.2  |  |     |
| D = Internal diode for coil transient suppression                                   |  |   |               | 12   | 1025               | 9.0         | 0.41                | 5.6  |  |     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   |               | 18   | 2300               | 13.5        | 0.58                | 8.4  |  |     |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26  | 4000          | 18.0   | 0.89               | 10.4        |                     |  |  |     |
| ER411 = Standard Coil   |  |  <b>ER431DD</b>                |               | 5  | 100                | 4.5         | 0.15                | 2.4  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |     |
| ER431 = Sensitive Coil  |  |   |               | 6  | 200                | 5.5         | 0.18                | 2.8  |  |     |
| Diode Options   |  |   |               | 9  | 630                | 7.8         | 0.35                | 4.2  |  |     |
| D = Internal diode for coil transient suppression                                   |  |   |               | 12   | 1025               | 10.0        | 0.40                | 5.6  |  |     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   |               | 18   | 2300               | 14.5        | 0.58                | 8.4  |  |     |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26  | 4000          | 19.0   | 0.89               | 10.4        |                     |  |  |     |
| ER411 = Standard Coil   |  |  <b>ER431T</b>                 |               | 5  | 125                | 3.6         | 0.15                | 2.0  | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |     |
| ER431 = Sensitive Coil  |  |   |               | 6  | 255                | 4.8         | 0.18                | 2.8  |  |     |
| Diode Options   |  |   |               | 9  | 630                | 7.8         | 0.35                | 4.2  |  |     |
| D = Internal diode for coil transient suppression                                   |  |   |               | 12   | 1025               | 10.0        | 0.41                | 5.6  |  |     |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |   |               | 18   | 2300               | 14.5        | 0.58                | 8.4  |  |     |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26  | 4000          | 19.0   | 0.89               | 10.4        |                     |  |  |     |




ER411  
ER431



ER411D  
ER431D



ER411DD  
ER431DD



ER411T  
ER431T

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage

## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS

### Series ER412 & ER432 Electromechanical Relays







The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed specifically for high-density PC board mounting, its small size and low coil power dissipation make the ER412 relay one of the most versatile ultraminiature relays available.


The Series ER412D and ER412DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid ER412T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

The sensitive ER432 relay has a high resistance coil, thus requiring extremely low operating power (200 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.


The Series ER432D and ER432DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid ER432T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by minimizing the number of external components needed to drive the relay.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |                                      | Part No.  | Nominal Coil  |   |                    |  | Contact Load Rating |  |
|---|--------------------------------------|---|---------------|---|--------------------|--|---------------------|--|
| DPDT Non-Latching   |                                      |   | Voltage (Vdc) | Resistance (Ω)  | P.U.V (Vdc) (max.) | D.O.V (Vdc)  |                     |  |
| Coil Type   |                                      |   |               |   |                    | min.   |                     | max.   |
| ER412 = Standard Coil   |                                      |  <b>ER412</b> | 5             | 50  | 3.5                | 0.14   | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 uA |
| ER432 = Sensitive Coil  |                                      |   | 6             | 98  | 4.5                | 0.18   | 3.2                 |  |
| Diode Options   |                                      |   | 9             | 220   | 6.8                | 0.35   | 4.9                 |  |
| D = Internal diode for coil transient suppression                                   |                                      |   | 12            | 390   | 9.0                | 0.41   | 6.5                 |  |
| DD = Internal diode for coil transient suppression and polarity reversal protection |                                      |   | 18            | 880   | 13.5               | 0.59   | 10.0                |  |
| T = Internal transistor drive and coil transient suppression diode                  |                                      |   | 26            | 1560  | 18.0               | 0.89   | 13.0                |  |
| Vibration   |                                      | Shock   |               |  <b>ER412DD</b>                |                    | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 uA |                     |  |
| 30 g's to 3000 Hz   | 75 g's 6 msec, half-sine             | 5   | 39            |   |                    | 3.9  | 0.6                 | 2.8  |
| Acceleration  |                                      | Temperature   |               |  <b>ER412T</b>                 |                    | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |                     |  |
| 50 g's  | Operating & Storage: -65°C to +125°C | 6   | 78            |   |                    | 5.2  | 0.7                 | 3.4  |
|   |                                      | 9   | 220           |   |                    | 6.8  | 0.35                | 4.9  |
|   |                                      | 12  | 390           |   |                    | 9.0  | 0.41                | 6.5  |
|   |                                      | 18  | 880           |   |                    | 13.5   | 0.59                | 10.0   |
|   |                                      | 26  | 1560          |   |                    | 18.0   | 0.89                | 13.0   |
|   |                                      |   |               |  <b>ER432</b><br><b>ER432D</b> |                    | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |                     |  |
|   |                                      | 5   | 100           |   |                    | 3.5  | 0.14                | 2.5  |
|   |                                      | 6   | 200           |   |                    | 4.5  | 0.18                | 3.2  |
|   |                                      | 9   | 400           |   |                    | 6.8  | 0.35                | 4.9  |
|   |                                      | 12  | 850           |   |                    | 9.0  | 0.41                | 6.5  |
|   |                                      | 18  | 1600          |   |                    | 13.5   | 0.59                | 10.0   |
|   |                                      |   |               |  <b>ER432DD</b>                |                    | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |                     |  |
|   |                                      | 5   | 64            |   |                    | 3.7  | 0.7                 | 2.6  |
|   |                                      | 6   | 125           |   |                    | 4.8  | 0.8                 | 3.0  |
|   |                                      | 9   | 400           |   |                    | 8.0  | 0.9                 | 4.5  |
|   |                                      | 12  | 850           |   |                    | 11.0   | 1.0                 | 5.8  |
|   |                                      | 18  | 1600          |   |                    | 14.5   | 1.1                 | 9.0  |
|   |                                      |   |               |  <b>ER432T</b>                 |                    | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |                     |  |
|   |                                      | 5   | 100           |   |                    | 3.6  | 0.14                | 2.5  |
|   |                                      | 6   | 200           |   |                    | 4.8  | 0.18                | 3.2  |
|   |                                      | 9   | 400           |   |                    | 7.8  | 0.35                | 4.9  |
|   |                                      | 12  | 850           |   |                    | 11.0   | 0.41                | 6.5  |
|   |                                      | 18  | 1600          |   |                    | 14.5   | 0.59                | 10.0   |
|   |                                      | 26  | 3300          | 19.0  | 0.89               | 13.0   |                     |  |




ER412  
ER432



ER412D  
ER432D



ER412DD  
ER432DD



ER412T  
ER432T

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage



## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS

### Series 255, 256, 257, 258 Electromechanical Relays

The Series 255 is an industry-standard, half-size, latching crystal can relay. It has a wide range of switching capabilities ranging from low level to 2 amps. The Series J255/255 latching relay configuration is double-pole double-throw (DPDT), so the relay offers excellent switching density and versatility.









Half-Size Crystal Can Features:

- Low level to 2 amps
- Wide range of switching capabilities
- Smallest relay package capable of switching 2 amps
- Modernized assembly process
- Lead-free (gold-plated wire lead only)

- All welded construction
- Wire leads, gold-plated or solder-coated
- Matched seal for superior hermeticity
- Gold-plated contact assembly
- Modernized assembly process
- Advanced cleaning techniques

| Relay Type                                  | Part No. | Nominal Coil  |                |                           |      | Contact Load Rating  |
|---|----------|---------------|----------------|---------------------------|------|--|
|   |          | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |      |  |
|   |          |               |                | Min.                      | Max. |  |
| DPDT Magnetic-Latching                      |          |               |                |                           |      |  |
| <b>Vibration</b>                            |          |               |                |                           |      |  |
| 30G, 10-2500 Hz<br>(Sinusoidal)             |          |               |                |                           |      | Resistive: 2A/28Vdc<br>Inductive: 0.75A/28Vdc (320mH)<br>Intermediate Current: 0.1A/28Vdc<br>Lamp: 0.16A/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Shock</b>                                |          |               |                |                           |      |  |
| 100G, 6 msec half-sine<br>(Specified Pulse) |          |               |                |                           |      |  |
| <b>Temperature</b>                          |          |               |                |                           |      |  |
| Operating & Storage:<br>-65°C to +125°C     |          |               |                |                           |      |  |

|   |  |   |  |  |   |   |  |
|---|--|---|--|--|---|---|--|
|  | <b>255</b><br> <p>SCHMATIC<br/>(Coil X Last Energized)<br/>(Bottom View)</p> |  | <b>256</b><br> <p>SCHMATIC<br/>(Coil X Last Energized)<br/>(Bottom View)</p> |  | <b>257</b><br> <p>SCHMATIC<br/>(Coil X Last Energized)<br/>(Bottom View)</p> |  | <b>258</b><br> <p>SCHMATIC<br/>(Coil Y Last Energized)<br/>(Bottom View)</p> |
|---|--|---|--|--|---|---|--|




### Series ER421 Electromechanical Relays

The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, its small size and low coil power dissipation make the ER421 relay one of the most versatile ultraminiature relays available.

The Series ER421D and ER421DD utilize discrete silicon diodes for coil suppression and polarity reversal protection.

The Series ER421 magnetic-latching relays are ideally suited for applications where coil power dissipation must be minimized. The relays can be operated with a short duration pulse. After the contacts have transferred, no external holding power is required. The magnetic-latching feature of the Series ER421 provides a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  | Part No.   | Nominal Coil  |                |                           | Contact Load Rating  |
|---|--|---------------|----------------|---------------------------|--|
|   |  | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |  |
|   |  |               |                |                           |  |
| SPDT Magnetic-Latching  |  |               |                |                           |  |
| <b>Diode Options</b>  |  |               |                |                           |  |
| D = Internal diode for coil transient suppression                                   |  <b>ER421</b>   | 5             | 61             | 3.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  | 6             | 120            | 4.5                       |  |
|   |  | 9             | 280            | 6.8                       |  |
|   |  | 12            | 500            | 9.0                       |  |
|   |  | 18            | 1130           | 13.5                      |  |
| <b>Vibration</b>  |  <b>ER421D</b>  | 5             | 61             | 3.7                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Shock</b>  |  | 6             | 120            | 4.5                       |  |
| 30 g's<br>to 3000 Hz  |  | 9             | 280            | 6.8                       |  |
| 100 g's 6 msec<br>half-sine   |  | 12            | 500            | 9.0                       |  |
|   |  | 18            | 1130           | 13.5                      |  |
| <b>Acceleration</b>   |  <b>ER421DD</b> | 5             | 48             | 4.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Temperature</b>  |  | 6             | 97             | 5.5                       |  |
| 50 g's  |  | 9             | 280            | 7.8                       |  |
| Operating & Storage:<br>-65°C to +125°C   |  | 12            | 500            | 10.0                      |  |
|   |  | 18            | 1130           | 14.5                      |  |
|   | 26   | 2000          | 19.0           |                           |  |

\*See Schematics on Page 21



## ESTABLISHED RELIABILITY T<sup>2</sup>R RELAYS



### Series ER420 & ER422 Electromechanical Relays


The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, its small size and low coil power dissipation make the ER420 & ER422 relays some of the most versatile ultraminiature relays available.

The Series ER420D/ER422D and ER420DD/ER422DD utilize discrete silicon diodes for coil suppression and polarity reversal protection.


The Series ER420/ER422 magnetic-latching relays are ideally suited for applications where coil power dissipation must be minimized. The relays can be operated with a short duration pulse. After the contacts have transferred, no external holding power is required. The magnetic-latching feature of the Series ER420/ER422 relays provide a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |                      | Part No.   | Nominal Coil  |                |                           | Contact Load Rating  |      |
|---|----------------------|--|---------------|----------------|---------------------------|--|------|
| DPDT Magnetic-Latching  |                      |  | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |  |      |
| Grounding Options   |                      |   | 5             | 61             | 3.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |      |
| 420 = Individual  |                      |  | ER420         | 6              | 120                       |  | 4.5  |
| 422 = Common  |                      |  | ER422         | 9              | 280                       |  | 6.8  |
| Diode Options   |                      |  | ER420D        | 12             | 500                       |  | 9.0  |
| D = Internal diode for coil transient suppression                                   |                      |  | ER422D        | 18             | 1130                      |  | 13.5 |
| DD = Internal diode for coil transient suppression and polarity reversal protection |                      |  |               | 26             | 2000                      |  | 18.0 |
| Vibration   | Shock                |  | 5             | 48             | 4.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |      |
| 30 g's  | 100 g's 6 msec,      |  | ER420DD       | 6              | 97                        |  | 5.5  |
| to 3000 Hz  | half-sine            |  | ER422DD       | 9              | 280                       |  | 7.8  |
| Acceleration  | Temperature          |  |               | 12             | 500                       |  | 10.0 |
| 50 g's  | Operating & Storage: |  |               | 18             | 1130                      |  | 14.5 |
|   | -65°C to +125°C      |  |               | 26             | 2000                      |  | 19.0 |



ER420




ER420D




ER420DD


Schematics Shown with Coil A Last Energized  
Schematics as viewed from terminals




ER421




ER421D




ER421DD



ER422



ER422D



ER422DD

## MILITARY QUALIFIED (JAN) RELAYS




### Series J114 Electromechanical Relays

The Series J114 Centigrad® relay is an ultraminiature, hermetically sealed, armature relay. Its low profile height .275" (7 mm) and .100" (2.54 mm) grid spaced terminals, which precludes the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required. The basic design and internal construction are similar to the standard Teledyne DPDT TO-5 relay (e.g., Series J412).

The Series J114D and J114DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection.

By virtue of its inherently low intercontact capacitance and contact circuit losses, the J114 relay has proven to be an excellent ultraminiature RF switch for frequency ranges well into the UHF spectrum. A typical RF application for the J114 relay is in handheld radio transceivers, wherein the combined features of good RF performance, small size, low coil power dissipation and high reliability make it a preferred method of Transmit-Receive switching.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |                                      | Part No.   | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|--------------------------------------|--|---------------|----------------|--------------------|-------------|---------------------|--|
| DPDT Non-Latching   |                                      |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Diode Options   |                                      |  |               |                |                    | min.        | max.                |  |
| D = Internal diode for coil transient suppression                                   |                                      |  <b>J114</b><br>(M39016/17)     | 5             | 50             | 3.5                | 0.14        | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc                                       |
| DD = Internal diode for coil transient suppression and polarity reversal protection |                                      |  | 6             | 98             | 4.5                | 0.18        | 3.2                 |  |
| Vibration   |                                      |  <b>J114D</b><br>(M39016/18)  | 9             | 220            | 6.8                | 0.35        | 4.9                 | Low Level: 10 to 50 uA/10 to 50 mV   |
| Shock   |                                      |  | 12            | 390            | 9.0                | 0.41        | 6.5                 |  |
| Acceleration  |                                      |  <b>J114DD</b><br>(M39016/18) | 18            | 880            | 13.5               | 0.59        | 10.0                | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Temperature   |                                      |  | 26            | 1560           | 18.0               | 0.89        | 13.0                |  |
| 30 g's to 3000 Hz   | 75 g's 6 msec, half-sine             |  | 5             | 39             | 4.0                | 0.6         | 2.8                 |  |
| 50 g's  | Operating & Storage: -65°C to +125°C |  | 6             | 78             | 5.0                | 0.7         | 3.4                 |  |
|   |                                      |  | 9             | 220            | 7.8                | 0.8         | 5.3                 |  |
|   |                                      |  | 12            | 390            | 10.0               | 0.9         | 6.5                 |  |
|   |                                      |  | 18            | 880            | 14.5               | 1.1         | 10.0                |  |
|   |                                      |  | 26            | 1560           | 19.0               | 1.4         | 13.0                |  |


### Series J116C Electromechanical Relays

The J116C Centigrad® relay is an ultraminiature, hermetically sealed, armature relay capable of being directly driven by most IC logic families. Its low profile height and .100" (2.54 mm) grid spaced terminals, which preclude the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required.

The Series J116C utilizes an internal silicon diode for coil suppression, a Zener diode to protect the MOSFET gate input, and an N-channel enhancement mode MOSFET chip, which enables direct relay interfacing with most Microprocessor and IC logic families (CMOS, TTL and MOS).

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration

| Relay Type  |  | Part No.   | Nominal Coil  |                   |       |                      | Contact Load Rating |  |
|---|--|--|---------------|-------------------|-------|----------------------|---------------------|--|
| DPDT Non-Latching   |  |  | Voltage (Vdc) | Coil Current (mA) |       | Operating Power (mW) |                     | P.U.V (Vdc) (max.)   |
| CMOS Feature  |  |  |               |                   |       |                      |                     |  |
| Internal power MOSFET driver, Zener diode gate protection, and diode coil suppression |  |  <b>J116C</b><br>(M28776/6) | 5             | 96.5              | 132.3 | 641                  | 4.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Vibration   |  |  | 6             | 60.3              | 83.9  | 462                  | 4.9                 |  |
| Shock   |  |  | 9             | 33.1              | 47.1  | 368                  | 7.3                 |  |
| Acceleration  |  |  | 12            | 24.9              | 36.1  | 369                  | 9.8                 |  |
| Temperature   |  |  | 18            | 16.1              | 24.1  | 368                  | 14.6                |  |
|   |  |  | 26            | 12.9              | 19.9  | 450                  | 19.5                |  |



P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage

Schematics as viewed from terminals

## MILITARY QUALIFIED (JAN) RELAYS



### Series J134 Electromechanical Relays

The J134 sensitive Centigrad® relay retains the same features as the J114 standard Centigrad® relay with only a minimal increase in profile height .375" (9.53 mm). Its .100" (2.54 mm) grid spaced terminals, which preclude the need for spreader pads, and its low profile make the J134 relay ideal for applications where high packaging density is important.

The Series J134D and J134DD have internal discrete silicon diodes for coil suppression and polarity reversal protection.

The sensitive J134 Centigrad® relay has a high resistance coil, thus requiring extremely low operating power (200 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.   | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|--|--|---------------|----------------|--------------------|-------------|---------------------|--|
| DPDT Non-Latching   |  |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Diode Options   |  |  |               |                |                    |             |                     |  |
| D = Internal diode for coil transient suppression                                   |  |  <p><b>J134</b><br/>(M39016/41)</p> <p><b>J134D</b><br/>(M39016/42)</p> | 5             | 100            | 3.5                | 0.12        | 2.5                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |  | 6             | 200            | 4.5                | 0.18        | 3.2                 |  |
| Vibration   |  |  | 9             | 400            | 6.8                | 0.35        | 4.9                 |  |
| Shock   |  |  | 12            | 800            | 9.0                | 0.41        | 6.5                 |  |
| 30 g's to 3000 Hz   |  |  | 18            | 1600           | 13.5               | 0.59        | 10.0                |  |
| 75 g's 6 msec, half-sine  |  |  | 26            | 3200           | 18.0               | 0.89        | 13.0                |  |
| Acceleration  |  |  <p><b>J134DD</b><br/>(M39016/43)</p>                                  | 5             | 64             | 3.7                | 0.7         | 2.6                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Temperature   |  |  | 6             | 125            | 4.8                | 0.8         | 3.0                 |  |
| Operating & Storage: -65°C to +125°C  |  |  | 9             | 400            | 8.0                | 0.9         | 4.5                 |  |
| 50 g's  |  |  | 12            | 800            | 11.0               | 1.0         | 5.8                 |  |
|   |  |  | 18            | 1600           | 14.5               | 1.1         | 9.0                 |  |
|   |  |  | 26            | 3200           | 19.0               | 1.3         | 13.0                |  |


### Series J136C Electromechanical Relays

The sensitive J136C Centigrad® relay is an ultraminiature, hermetically sealed, armature relay capable of being directly driven by most IC logic families. Its low profile height and .100" (2.54 mm) grid spaced terminals, which precludes the need for spreader pads, make it ideal for applications where extreme packaging density and/or close PC board spacing are required.


The sensitive J136C Centigrad® relay has a high resistance coil, thus requiring extremely low operating power (200 mW, typical). The advantages of reduced heat dissipation and power supply demands are a plus.

The sensitive Series J136C utilizes an internal silicon diode for coil suppression, a Zener diode to protect the MOSFET gate input, and an N-channel enhancement-mode MOSFET chip that enables direct relay interfacing with most microprocessor and IC logic families (CMOS, TTL and MOS).


- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.   | Nominal Coil  |                   |      |                      | Contact Load Rating |  |
|---|--|--|---------------|-------------------|------|----------------------|---------------------|--|
| DPDT Non-Latching   |  |  | Voltage (Vdc) | Coil Current (mA) |      | Operating Power (mW) |                     | P.U.V (Vdc) (max.)   |
| CMOS Feature  |  |  |               |                   |      |                      |                     |  |
| Internal power MOSFET driver, Zener diode gate protection, and diode coil suppression |  |  <p><b>J136C</b><br/>(M28776/7)</p> | 5             | 43.0              | 56.0 | 250                  | 4.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Vibration   |  |  | 6             | 27.0              | 33.0 | 180                  | 4.9                 |  |
| Shock   |  |  | 9             | 17.8              | 26.4 | 203                  | 7.3                 |  |
| 30 g's to 3000 Hz   |  |  | 12            | 11.3              | 17.7 | 180                  | 9.8                 |  |
| 75 g's 6 msec, half-sine  |  |  | 18            | 8.4               | 13.8 | 203                  | 14.6                |  |
| Acceleration  |  |  | 26            | 5.8               | 10.2 | 219                  | 19.5                |  |
| Temperature   |  |  |               |                   |      |                      |                     |  |
| Operating & Storage: -65°C to +125°C  |  |  |               |                   |      |                      |                     |  |
| 50 g's  |  |  |               |                   |      |                      |                     |  |


Schematics as viewed from terminals




J134



J134D



J134DD



J136C

PIN 1: + SUPPLY  
PIN 9: - SUPPLY  
PIN 10: GATE

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage

## MILITARY QUALIFIED (JAN) RELAYS

### Series J411 & J431 Electromechanical Relays









The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed specifically for high-density PC board mounting, its small size and low coil power dissipation make the J411 relay one of the most versatile ultraminiature relays available.


The Series J411D and J411DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid J411T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

The sensitive J431 relay has a high resistance coil, thus requiring extremely low operating power (150 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.


The Series J431D and J431DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid J431T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  |           | Part No.   | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|-----------|--|---------------|----------------|--------------------|-------------|---------------------|--|
| SPDT Non-Latching   | Coil Type |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Diode Options   |           |  |               |                | min.               | max.        |                     |  |
| J411 = Standard Coil  |           |  <b>J411</b><br>(M39016/7)     | 5             | 63             | 3.7                | 0.15        | 2.4                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| J431 = Sensitive Coil   |           |  | 6             | 125            | 4.5                | 0.18        | 2.8                 |  |
|   |           |  | 9             | 280            | 6.8                | 0.35        | 4.2                 |  |
| D = Internal diode for coil transient suppression                                   |           |  <b>J411D</b><br>(M39016/23)  | 12            | 500            | 9.0                | 0.40        | 5.6                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| DD = Internal diode for coil transient suppression and polarity reversal protection |           |  | 18            | 1130           | 13.5               | 0.58        | 8.4                 |  |
| T = Internal transistor drive and coil transient suppression diode                  |           |  | 26            | 2000           | 18.0               | 0.89        | 10.4                |  |
|   |           |  | 5             | 50             | 4.5                | 0.15        | 2.4                 |  |
| Vibration   |           |  <b>J411DD</b><br>(M39016/24) | 6             | 98             | 5.5                | 0.18        | 2.8                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Shock   |           |  | 9             | 280            | 7.8                | 0.35        | 4.2                 |  |
| 30 g's to 3000 Hz   |           |  | 12            | 500            | 10.0               | 0.40        | 5.6                 |  |
| 75 g's 6 msec, half-sine  |           |  | 18            | 1130           | 14.5               | 0.58        | 8.4                 |  |
|   |           |  | 26            | 2000           | 19.0               | 0.89        | 10.4                |  |
| Acceleration  |           |  <b>J411T</b><br>(M28776/5)   | 5             | 63             | 3.9                | 0.15        | 2.4                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Temperature   |           |  | 6             | 125            | 5.2                | 0.18        | 2.8                 |  |
| 50 g's  |           |  | 9             | 280            | 7.8                | 0.35        | 4.2                 |  |
| Operating & Storage: -65°C to +125°C  |           |  | 12            | 500            | 10.0               | 0.40        | 5.6                 |  |
|   |           |  | 18            | 1130           | 14.5               | 0.58        | 8.4                 |  |
|   |           |  | 26            | 2000           | 19.0               | 0.89        | 10.4                |  |
|   |           |  <b>J431</b><br>(M39016/10)   | 5             | 125            | 3.7                | 0.15        | 2.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |           |  | 6             | 255            | 4.5                | 0.18        | 2.8                 |  |
|   |           |  | 9             | 630            | 6.8                | 0.35        | 4.2                 |  |
|   |           |  | 12            | 1025           | 9.0                | 0.41        | 5.6                 |  |
|   |           |  | 18            | 2300           | 13.5               | 0.58        | 8.4                 |  |
|   |           |  <b>J431D</b><br>(M39016/25)  | 26            | 4000           | 18.0               | 0.89        | 10.4                | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |           |  | 5             | 100            | 4.5                | 0.15        | 2.4                 |  |
|   |           |  | 6             | 200            | 5.5                | 0.18        | 2.8                 |  |
|   |           |  | 9             | 630            | 7.8                | 0.35        | 4.2                 |  |
|   |           |  <b>J431DD</b><br>(M39016/26) | 12            | 1025           | 10.0               | 0.40        | 5.6                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |           |  | 18            | 2300           | 14.5               | 0.58        | 8.4                 |  |
|   |           |  | 26            | 4000           | 19.0               | 0.89        | 10.4                |  |
|   |           |  <b>J431T</b><br>(M28776/4)   | 5             | 125            | 3.6                | 0.15        | 2.0                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |           |  | 6             | 255            | 4.8                | 0.18        | 2.8                 |  |
|   |           |  | 9             | 630            | 7.8                | 0.35        | 4.2                 |  |
|   |           |  | 12            | 1025           | 10.0               | 0.41        | 5.6                 |  |
|   |           |  | 18            | 2300           | 14.5               | 0.58        | 8.4                 |  |
|   |           |  | 26            | 4000           | 19.0               | 0.89        | 10.4                |  |




J411  
J431



J411D  
J431D



J411DD  
J431DD



J411T  
J431T

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage

Schematics as viewed from terminals

## MILITARY QUALIFIED (JAN) RELAYS

### Series J412 & J432 Electromechanical Relays







The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed specifically for high-density PC board mounting, its small size and low coil power dissipation make the J412 relay one of the most versatile ultraminiature relays available.


The Series J412D and J412DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid J412T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

The sensitive J432 relay has a high resistance coil, thus requiring extremely low operating power (200 mw typical). The advantages of reduced heat dissipation and power supply demands are a plus.

The Series J432D and J432DD relays have internal discrete silicon diodes for coil suppression and polarity reversal protection. The hybrid J432T relay features an internal silicon suppression diode and transistor driver. This hybrid package reduces required PC board floor space by reducing the number of external components needed to drive the relay.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  |  | Part No.   | Nominal Coil  |                |                    |             | Contact Load Rating |  |
|---|--|--|---------------|----------------|--------------------|-------------|---------------------|--|
| DPDT Non-Latching   |  |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |                     |  |
| Coil Type   |  |  |               |                |                    | min.        |                     | max.   |
| J412 = Standard Coil  |  |  <b>J412</b><br>(M39016/9)     | 5             | 50             | 3.5                | 0.14        | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 uA |
| J432 = Sensitive Coil   |  |  | 6             | 98             | 4.5                | 0.18        | 3.2                 |  |
| Diode Options   |  |  | 9             | 220            | 6.8                | 0.35        | 4.9                 |  |
| D = Internal diode for coil transient suppression                                   |  |  | 12            | 390            | 9.0                | 0.41        | 6.5                 |  |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  |  | 18            | 880            | 13.5               | 0.59        | 10.0                |  |
| T = Internal transistor drive and coil transient suppression diode                  |  | 26   | 1560          | 18.0           | 0.89               | 13.0        |                     |  |
| Vibration   |  |  <b>J412DD</b><br>(M39016/20) | 5             | 39             | 3.9                | 0.6         | 2.8                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 uA |
| Shock   |  |  | 6             | 78             | 5.2                | 0.7         | 3.4                 |  |
| 30 g's to 3000 Hz   |  |  | 9             | 220            | 7.8                | 0.8         | 5.3                 |  |
| 75 g's 6 msec, half-sine  |  |  | 12            | 390            | 10.0               | 0.9         | 6.5                 |  |
| Acceleration  |  |  | 18            | 880            | 14.5               | 1.1         | 10.0                |  |
| Temperature   |  | 26   | 1560          | 19.0           | 1.4                | 13.0        |                     |  |
| 50 g's  |  |  <b>J412T</b><br>(M28776/1)   | 5             | 50             | 3.5                | 0.14        | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Operating & Storage: -65°C to +125°C  |  |  | 6             | 98             | 4.5                | 0.18        | 3.2                 |  |
|   |  |  | 9             | 220            | 6.8                | 0.35        | 4.9                 |  |
|   |  |  | 12            | 390            | 9.0                | 0.41        | 6.5                 |  |
|   |  |  | 18            | 880            | 13.5               | 0.59        | 10.0                |  |
|   |  | 26   | 1560          | 18.0           | 0.89               | 13.0        |                     |  |
|   |  |  <b>J432</b><br>(M39016/11)   | 5             | 100            | 3.5                | 0.14        | 2.5                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |  |  | 6             | 200            | 4.5                | 0.18        | 3.2                 |  |
|   |  |  | 9             | 400            | 6.8                | 0.35        | 4.9                 |  |
|   |  |  | 12            | 850            | 9.0                | 0.41        | 6.5                 |  |
|   |  |  | 18            | 1600           | 13.5               | 0.59        | 10.0                |  |
|   |  | 26   | 3300          | 18.0           | 0.89               | 13.0        |                     |  |
|   |  |  <b>J432DD</b><br>(M39016/21) | 5             | 64             | 3.7                | 0.7         | 2.6                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |  |  | 6             | 125            | 4.8                | 0.8         | 3.0                 |  |
|   |  |  | 9             | 400            | 8.0                | 0.9         | 4.5                 |  |
|   |  |  | 12            | 850            | 11.0               | 1.0         | 5.8                 |  |
|   |  |  | 18            | 1600           | 14.5               | 1.1         | 9.0                 |  |
|   |  | 26   | 3300          | 19.0           | 1.3                | 13.0        |                     |  |
|   |  |  <b>J432T</b><br>(M28776/3)   | 5             | 100            | 3.6                | 0.14        | 2.5                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
|   |  |  | 6             | 200            | 4.8                | 0.18        | 3.2                 |  |
|   |  |  | 9             | 400            | 7.8                | 0.35        | 4.9                 |  |
|   |  |  | 12            | 850            | 11.0               | 0.41        | 6.5                 |  |
|   |  |  | 18            | 1600           | 14.5               | 0.59        | 10.0                |  |
|   |  | 26   | 3300          | 19.0           | 0.89               | 13.0        |                     |  |



Schematics as viewed from terminals

P.U.V = Pick-Up Voltage  
D.O.V = Drop-Out Voltage



## MILITARY QUALIFIED (JAN) RELAYS


### Series J255 Electromechanical Relays


The Series J255 is an industry-standard, half-size, latching crystal can relay. It has a wide range of switching capabilities ranging from low level to 2 amps. The Series J255 latching relay configuration is double-pole double-throw (DPDT), so the relay offers excellent switching density and versatility.

Half-Size Crystal Can Features:

- All welded construction
- Wire leads, gold-plated or solder-coated
- Matched seal for superior hermeticity
- Gold-plated contact assembly
- Modernized assembly process
- Advanced cleaning techniques

- Low level to 2 amps
- Wide range of switching capabilities
- Smallest relay package capable of switching 2 amps
- Modernized assembly process
- Qualified to MIL-PRF39016/45
- Lead-free (gold-plated wire lead only)

| Relay Type                               | Part No.   | Nominal Coil  |                |                           |      | Contact Load Rating  |
|--|--|---------------|----------------|---------------------------|------|--|
|  |  | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |      |  |
|  |  |               |                | Min.                      | Max. |  |
| DPDT Magnetic-Latching                   |  <b>J255</b><br>(M39016/45) | 5             | 45             | 1.0                       | 3.8  | Resistive: 2A/28Vdc<br>Inductive: 0.75A/28Vdc (320mH)<br>Intermediate Current: 0.1A/28Vdc<br>Lamp: 0.16A/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Vibration                                |  | 6             | 63             | 1.3                       | 4.5  |  |
| 30G, 10-2500 Hz (Sinusoidal)             |  | 12            | 254            | 2.6                       | 9.0  |  |
| Shock                                    |  | 26            | 1000           | 5.2                       | 18.0 |  |
| 100G, 6 msec half-sine (Specified Pulse) |  |               |                |                           |      |  |
| Temperature                              |  |               |                |                           |      |  |
| Operating & Storage: -65°C to +125°C     |  |               |                |                           |      |  |






### Series J421 Electromechanical Relays

The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, its small size and low coil power dissipation make the J421 relay one of the most versatile ultraminiature relays available.

The Series J421D and J421DD utilize discrete silicon diodes for coil suppression and polarity reversal protection.

The Series J421 magnetic-latching relays are ideally suited for applications where coil power dissipation must be minimized. The relays can be operated with a short duration pulse. After the contacts have transferred, no external holding power is required. The magnetic-latching feature of the Series J421 provides a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  | Part No.   | Nominal Coil  |                |                           | Contact Load Rating  |
|---|--|---------------|----------------|---------------------------|--|
|   |  | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |  |
|   |  |               |                |                           |  |
| SPDT Magnetic-Latching  |  <b>J421</b><br>(M39016/8)    | 5             | 61             | 3.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Diode Options   |  | 6             | 120            | 4.5                       |  |
| D = Internal diode for coil transient suppression                                   |  | 9             | 280            | 6.8                       |  |
| DD = Internal diode for coil transient suppression and polarity reversal protection |  | 12            | 500            | 9.0                       |  |
|   |  | 18            | 1130           | 13.5                      |  |
| Vibration   |  <b>J421D</b><br>(M39016/27)  | 5             | 61             | 3.7                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Shock   |  | 6             | 120            | 4.5                       |  |
| 30 g's to 3000 Hz   |  | 9             | 280            | 6.8                       |  |
| 100 g's 6 msec half-sine  |  | 12            | 500            | 9.0                       |  |
|   |  | 18            | 1130           | 13.5                      |  |
| Acceleration  |  <b>J421DD</b><br>(M39016/28) | 5             | 48             | 4.5                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| Temperature   |  | 6             | 97             | 5.5                       |  |
| 50 g's  |  | 9             | 280            | 7.8                       |  |
| Operating & Storage: -65°C to +125°C  |  | 12            | 500            | 10.0                      |  |
|   |  | 18            | 1130           | 14.5                      |  |
|   | 26   | 2000          | 19.0           |                           |  |

\*See Schematics on Page 27

MILITARY QUALIFIED (JAN)



## MILITARY QUALIFIED (JAN) RELAYS

### Series J420 & J422 Electromechanical Relays


The magnetic-latching TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, its small size and low coil power dissipation make the J420 & J422 relays some of the most versatile ultraminiature relays available.

The Series J420D/J422D and J420DD/J422DD utilize discrete silicon diodes for coil suppression and polarity reversal protection.


The Series J420/J422 magnetic-latching relays are ideally suited for applications where coil power dissipation must be minimized. The relays can be operated with a short duration pulse. After the contacts have transferred, no external holding power is required. The magnetic-latching feature of the Series J420/J422 relays provide a "memory" capability, since the relays will not reset upon removal of coil power.

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  | Part No. | Nominal Coil                         |                |                           | Contact Load Rating                |
|---|----------|--------------------------------------|----------------|---------------------------|------------------------------------|
|   |          | Voltage (Vdc)                        | Resistance (Ω) | Set & Reset Voltage (Vdc) |                                    |
| DPDT Magnetic-Latching  |          |                                      |                |                           |                                    |
| <b>Grounding Options</b>  |          |                                      |                |                           |                                    |
| J420 = Individual   |          |                                      |                |                           | Resistive: 1A/28Vdc                |
| J422 = Common   |          |                                      |                |                           | Inductive: 200mA/28Vdc (320mH)     |
|   |          |                                      |                |                           | Lamp: 100mA/28Vdc                  |
|   |          |                                      |                |                           | Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Diode Options</b>  |          |                                      |                |                           |                                    |
| D = Internal diode for coil transient suppression                                   |          |                                      |                |                           |                                    |
| DD = Internal diode for coil transient suppression and polarity reversal protection |          |                                      |                |                           |                                    |
| <b>Vibration</b>  |          | <b>Shock</b>                         |                |                           |                                    |
| 30 g's to 3000 Hz   |          | 100 g's 6 msec. half-sine            |                |                           |                                    |
| <b>Acceleration</b>   |          | <b>Temperature</b>                   |                |                           |                                    |
| 50 g's  |          | Operating & Storage: -65°C to +125°C |                |                           |                                    |




J420




J420D




J420DD




J421




J421D




J421DD



J422



J422D



J422DD

Schematics Shown with Coil A Last Energized  
Schematics as viewed from terminals

## HIGH-PERFORMANCE RELAYS

### Series 412H, 422H & 432H Electromechanical Relays - High Temperature



The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, these TO-5 relays are some of the most versatile ultraminiature relays available because of their small size and low coil power dissipation.

The H Series high-temperature TO-5 relays are designed for reliable operation in elevated ambient temperatures up to 200°C. Special material selection and processing provide assurance of freedom from contact contamination and mechanical malfunctioning that might otherwise be caused by ultra high ambient temperature conditions.


Typical applications:


- Oil exploration (down-hole) instrumentation
- High-Temperature industrial and process control instrumentation

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type                      | Part No.   | Nominal Coil  |                |                    |                       | Contact Load Rating                |  |
|---------------------------------|--|---------------|----------------|--------------------|-----------------------|------------------------------------|--|
|                                 |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) min. max. |                                    |  |
| 412H = DPDT Non-Latching        |  <b>412H</b>  | 5             | 50             | 4.7                | 0.14                  | 2.4                                | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| 432H = DPDT Non-Latching        |  | 6             | 98             | 5.9                | 0.18                  | 3.4                                |  |
| 422H = DPDT Magnetic-Latching   |  | 9             | 220            | 9.0                | 0.35                  | 5.1                                |  |
| <b>Coil Type</b>                |  | 12            | 390            | 11.9               | 0.41                  | 6.8                                |  |
| 412H = Standard Coil            |  | 18            | 880            | 17.8               | 0.59                  | 10.2                               |  |
| 422H = Standard Coil            |  <b>432H</b> | 26            | 1560           | 24.0               | 0.89                  | 13.5                               | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| 432H = Sensitive Coil           |  | 5             | 100            | 4.7                | 0.14                  | 2.4                                |  |
| <b>Vibration</b>                |  | 6             | 200            | 5.9                | 0.18                  | 3.4                                |  |
| 30 g's to 3000 Hz               |  | 9             | 400            | 9.0                | 0.35                  | 5.1                                |  |
| <b>Shock</b>                    |  | 12            | 850            | 11.9               | 0.41                  | 6.8                                |  |
| 412H = 75 g's 6 msec, half-sine | 18   | 1600          | 17.8           | 0.59               | 10.2                  | Low Level: 10 to 50 uA/10 to 50 mV |  |
| 432H = 75 g's 6 msec, half-sine | 26   | 3300          | 24.0           | 0.89               | 13.5                  |                                    |  |
| 422H = 100 g's                  |  |               |                |                    |                       |                                    |  |

| Acceleration         | Part No.  | Nominal Coil  |                |                           | Contact Load Rating  |
|----------------------|---|---------------|----------------|---------------------------|--|
|                      |   | Voltage (Vdc) | Resistance (Ω) | Set & Reset Voltage (Vdc) |  |
| 50 g's               |  <b>422H</b> | 5             | 61             | 4.7                       | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| <b>Temperature</b>   |   | 6             | 120            | 5.9                       |  |
| Operating & Storage: |   | 9             | 280            | 9.0                       |  |
| -65°C to +200°C      |   | 12            | 500            | 11.9                      |  |
|                      |   | 18            | 1130           | 17.8                      |  |
|                      |   | 26            | 2000           | 24.0                      |  |



412H  
432H



SCHEMATIC  
(Coil A Last Energized)  
422H

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage

D.O.V = Drop-Out Voltage

## HIGH-PERFORMANCE RELAYS

### Series 412K & 422K Electromechanical Relays - High Shock



The TO-5 relay, originally conceived and developed by Teledyne, has become one of the industry standards for low-level switching from dry circuit to 1 ampere. Designed for high-density PC board mounting, its small size and low coil power dissipation make the TO-5 relay one of the most versatile subminiature relays available.


The K Series high-shock TO-5 relays are designed to withstand shock levels up to 4000 g's, .5 msec duration. Special material selection and construction details provide assurance that critical elements of the relay structure and mechanism will not be permanently displaced or damaged as a result of extremely high g level shocks.

Typical applications:


- Commercial avionics aircraft control
- Commercial aircraft control systems
- Transportation systems (rail/truck)

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities

| Relay Type  | Part No.   | Nominal Coil  |                |                    |                       | Contact Load Rating |                                    |
|---|--|---------------|----------------|--------------------|-----------------------|---------------------|------------------------------------|
|   |  | Voltage (Vdc) | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) min. max. |                     |                                    |
| 412K = DPDT Non-Latching<br>422K = DPDT Magnetic-Latching   |  412K   | 5             | 50             | 4.3                | 0.14                  | 2.5                 | Resistive: 1A/28Vdc                |
| <b>Vibration</b>  |  | 6             | 80             | 5.2                | 0.18                  | 3.2                 | Inductive: 200mA/28Vdc (320mH)     |
| 30 g's to 3000 Hz   |  | 9             | 160            | 7.6                | 0.35                  | 4.9                 | Lamp: 100mA/28Vdc                  |
| <b>Shock</b>  |  | 12            | 300            | 10.0               | 0.41                  | 6.5                 | Low Level: 10 to 50 uA/10 to 50 mV |
| 412K = 75 g's 6 msec, half-sine<br>4000 g's, 0.5 msec axial plane, half-sine<br>1000 g's, 0.5 msec side planes, half-sine |  | 18            | 600            | 14.3               | 0.59                  | 10.0                |                                    |
| 422K = 100 g's 6 msec, half-sine<br>2100 g's, 0.5 msec axial plane, half-sine<br>750 g's, 0.5 msec side planes, half-sine |  422K | 5             | 61             | 3.5                |                       |                     | Resistive: 1A/28Vdc                |
| <b>Acceleration</b>   |  | 6             | 120            | 4.5                |                       |                     | Inductive: 200mA/28Vdc (320mH)     |
| 50 g's  |  | 9             | 280            | 6.8                |                       |                     | Lamp: 100mA/28Vdc                  |
| <b>Temperature</b>  |  | 12            | 500            | 9.0                |                       |                     | Low Level: 10 to 50 uA/10 to 50 mV |
| Operating & Storage:<br>-65°C to +125°C   |  | 18            | 1130           | 13.5               |                       |                     |                                    |
|   | 26   | 2000          | 18.0           |                    |                       |                     |                                    |



412K



SCHEMATIC  
(Coil A Last Energized)

422K

Schematics as viewed from terminals

P.U.V = Pick-Up Voltage

D.O.V = Drop-Out Voltage

## HIGH-PERFORMANCE RELAYS

### Series 412V & 432V Electromechanical Relays - High Vibration




The 412V and 432V TO-5 relays, originally conceived and developed by Teledyne, have become the industry standards for low level switching from dry circuit to 1 ampere in high-vibration environments. Designed for high-density PC board mounting, these TO-5 relays are some of the most versatile ultraminiature relay available because of their small size and low coil power dissipation.


The V Series high-vibration relays are designed to withstand vibration levels of 250 to 380 g's at the frequencies noted, when tested on a resonant beam for 10 to 20 seconds, in the axis parallel to contact motion (x-axis), or 100 g's 10-2000 Hz for 20 minutes in the x-axis. A unique magnetic circuit prevents contact opening (chatter) in excess of 10 microseconds under vibration or shock conditions.

Typical applications:


- Avionics aircraft control
- Aircraft control systems
- Transportation systems (rail/truck)

- All welded construction
- Unique uni-frame design providing high magnetic efficiency and mechanical rigidity
- High force/mass ratio for resistance to shock and vibration
- Precious metal alloy contact material with gold plating assures excellent high current and dry circuit switching capabilities


| Relay Type  | Part No. | Nominal Coil  |                |                    |             |      | Contact Load Rating |  |
|---|----------|---|----------------|--------------------|-------------|------|---------------------|--|
|   |          | Voltage (Vdc)   | Resistance (Ω) | P.U.V (Vdc) (max.) | D.O.V (Vdc) |      |                     |  |
| Coil Type   |          |   |                |                    | min.        |      | max.                |  |
| DPDT Non-Latching   |          |   |                |                    |             |      |                     |  |
| Coil Type   |          |   |                |                    |             |      |                     |  |
| 412V = Standard Coil  |          |    | 5              | 50                 | 4.6         | 0.14 | 2.3                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| 432V = Sensitive Coil   |          |   | 6              | 70                 | 5.5         | 0.18 | 3.2                 |  |
| Diode Options   |          |   | 9              | 155                | 8.2         | 0.35 | 4.9                 |  |
| D = Internal diode for coil transient suppression                                   |          |   | 12             | 235                | 11.0        | 0.41 | 6.5                 |  |
| DD = Internal diode for coil transient suppression and polarity reversal protection |          | 18  | 610            | 16.5               | 0.59        | 10.0 |                     |  |
| Vibration   |          | 26  | 1130           | 22.0               | 0.89        | 13.0 |                     |  |
| 250 g's at 140 ±5 Hz  |          |   | 5              | 33                 | 4.6         | 0.6  | 2.8                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| 350 g's at 170 ±5 Hz  |          |   | 6              | 44                 | 5.5         | 0.7  | 3.4                 |  |
| 380 g's at 200 ±5 Hz  |          |   | 9              | 125                | 8.2         | 0.8  | 5.3                 |  |
|   |          |   | 12             | 215                | 11.0        | 0.9  | 6.5                 |  |
| Shock   |          | 18  | 470            | 16.5               | 1.1         | 10.0 |                     |  |
| 150 g's 11 msec, half-sine  |          | 26  | 1050           | 22.0               | 1.4         | 13.0 |                     |  |
| Acceleration  |          |  | 5              | 80                 | 4.6         | 0.14 | 2.5                 | Resistive: 1A/28Vdc<br>Inductive: 200mA/28Vdc (320mH)<br>Lamp: 100mA/28Vdc<br>Low Level: 10 to 50 uA/10 to 50 mV |
| 50 g's  |          |   | 6              | 120                | 5.5         | 0.18 | 3.2                 |  |
| Temperature   |          |   | 9              | 240                | 8.2         | 0.35 | 4.9                 |  |
| Operating & Storage: -65°C to +125°C  |          |   | 12             | 480                | 11.0        | 0.41 | 6.5                 |  |
|   |          | 18  | 950            | 16.5               | 0.59        | 10.0 |                     |  |
|   |          | 26  | 1900           | 22.0               | 0.89        | 13.0 |                     |  |



412V  
432V



412DV  
432DV



412DDV

Schematics as viewed from terminals


P.U.V = Pick-Up Voltage

D.O.V = Drop-Out Voltage

## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES RF100

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 233.7 mV   | 88.88 ps  | 13.01 | 9.33 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 217.1 mV   | 88.05 ps  | 11.55 | 8.44 ps               |


### SERIES GRF100

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 242.5 mV   | 90.09 ps  | 14.20 | 8.44 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 263.6 mV   | 87.29 ps  | 20.23 | 9.78 ps               |


### SERIES SGRF100

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 251.5 mV   | 92.04 ps  | 15.11 | 8.00 ps               |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 261.2 mV   | 87.64 ps  | 18.20 | 8.44 ps               |



## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES GRF172

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 246.1 mV   | 92.45 ps  | 14.59 | 6.22 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 268.2 mV   | 90.87 ps  | 21.62 | 7.56 ps               |


### SERIES RF300/RF303

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 254.7 mV   | 90.38 ps  | 18.52 | 8.44 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 250.9 mV   | 88.21 ps  | 16.84 | 8.00 ps               |


### SERIES GRF300/GRF303

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 237.6 mV   | 90.08 ps  | 14.19 | 9.33 ps               |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 255.2 mV   | 88.93 ps  | 17.74 | 8.89 ps               |

## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES SGRF300/SGRF303

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 233.3 mV   | 89.08 ps  | 13.18 | 7.56 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 243.1 mV   | 90.29 ps  | 15.21 | 7.56 ps               |


### SERIES SRF300/SRF303

Normally Closed



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 137.9 mV   | 85.83 ps  | 6.31 | 13.33 ps              |


Normally Open



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 72.8 mV    | 88.1 ps   | 4.31 | 8.00 ps               |


### SERIES RF312

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 266.5 mV   | 89.21 ps  | 19.44 | 9.78 ps               |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>P-P</sub> |
|------------|-----------|-------|-----------------------|
| 264.3 mV   | 89.07 ps  | 19.13 | 8.00 ps               |

## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES GRF312

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 266.5 mV   | 91.09 ps  | 20.75 | 6.22 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 239.6 mV   | 92.77 ps  | 14.52 | 5.78 ps               |


### SERIES SGRF312

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 240.7 mV   | 91.44 ps  | 15.49 | 8.44 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 237.1 mV   | 89.08 ps  | 13.72 | 8.00 ps               |


### SERIES RF311/RF331

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 266.5 mV   | 89.21 ps  | 19.44 | 9.78 ps               |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 264.3 mV   | 89.07 ps  | 19.13 | 8.00 ps               |



## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES GRF311

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 260.0 mV   | 92.32 ps  | 17.98 | 6.67 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 267.2 mV   | 90.99 ps  | 20.84 | 7.11 ps               |


### SERIES GRF342

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 252.9 mV   | 90.74 ps  | 16.53 | 8.44 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 253.1 mV   | 87.31 ps  | 17.57 | 9.78 ps               |


### SERIES RF180

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 240.5 mV   | 88.16 ps  | 13.86 | 10.67 ps              |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 235.8 mV   | 87.22 ps  | 12.75 | 10.22 ps              |

## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES RF341

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 260.9 mV   | 88.26 ps  | 18.39 | 8.44 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 271.5 mV   | 86.41 ps  | 21.35 | 8.89 ps               |


### SERIES GRF341

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 256.2 mV   | 87.70 ps  | 17.15 | 8.89 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 259.9 mV   | 88.39 ps  | 17.59 | 8.00 ps               |


### SERIES RF310/RF313

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 246.1 mV   | 92.45 ps  | 14.59 | 6.22 ps               |

Normally Open




| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 268.2 mV   | 90.87 ps  | 21.62 | 7.56 ps               |



## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES RF320/RF323

Normally Closed



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 246.1 mV   | 92.45 ps  | 14.59 | 6.22 ps               |


Normally Open



| Eye Height | Eye Width | SNR   | Jitter <sub>p-p</sub> |
|------------|-----------|-------|-----------------------|
| 268.2 mV   | 90.87 ps  | 21.62 | 7.56 ps               |


### SERIES A150

Attenuated Path



| Eye Height | Eye Width | SNR  | Jitter <sub>p-p</sub> |
|------------|-----------|------|-----------------------|
| 45.59 mV   | 64.18 ps  | 5.70 | 28.00 ps              |


Thru Path



| Eye Height | Eye Width | SNR  | Jitter <sub>p-p</sub> |
|------------|-----------|------|-----------------------|
| 130.2 mV   | 72.87 ps  | 5.29 | 20.89 ps              |


### SERIES GA150

Attenuated Path



| Eye Height | Eye Width | SNR  | Jitter <sub>p-p</sub> |
|------------|-----------|------|-----------------------|
| 62.10 mV   | 83.23 ps  | 7.14 | 12.89 ps              |

Thru Path




| Eye Height | Eye Width | SNR  | Jitter <sub>p-p</sub> |
|------------|-----------|------|-----------------------|
| 130.3 mV   | 78.38 ps  | 5.30 | 19.56 ps              |

## APPENDIX: SIGNAL INTEGRITY EYE DIAGRAMS


### SERIES A152

Attenuated Path



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 45.10 mV   | 78.94 ps  | 5.57 | 18.67 ps              |


Thru Path



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 124.5 mV   | 73.90 ps  | 5.23 | 22.22 ps              |


### SERIES GA152

Attenuated Path



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 67.99 mV   | 82.70 ps  | 7.85 | 13.78 ps              |

Thru Path



| Eye Height | Eye Width | SNR  | Jitter <sub>P-P</sub> |
|------------|-----------|------|-----------------------|
| 122.9 mV   | 76.21 ps  | 5.07 | 21.78 ps              |

### PATTERN GENERATOR SETTINGS

- 10 Gbps Random Pulse Pattern Generator
- $2^{31} - 1$  PRBS signal
- PRBS output of 300mV<sub>P-P</sub> (nominal)
- RF PCB effect (negligible) not removed from measurement
- Data shown is typical of both poles

# RoHS and REACH CERTIFICATE OF COMPLIANCE

## RoHS

It is hereby stated and certified that Teledyne Relays complies with the Restrictions on Hazardous Substances (RoHS) Directives to the extent herein:

Teledyne Relays does not use any of the Restricted Substances specified by the RoHS Directives (listed below) as components in TO-5 and Centigrad® Electromechanical Relay products, nor are these substances employed during any electromechanical relay manufacturing process:

*Lead*

*Mercury*

*Cadmium*

*Hexavalent Chromium*

*Polybrominated Biphenyls (PBB's)*

*Polybrominated Diphenyl Ethers (PBDE's)*

However, upon request from the Customer, relay leads may be coated with solder, which contains 60% tin and 40% lead.

## REACH

It is hereby stated and certified that Teledyne Relays complies with the Registration Evaluation Authorization and Restriction of Chemicals (REACH) Directives to the extent stated herein:

Teledyne Relays is a manufacturer of articles. Teledyne Relays has taken the initiative to review the (39) substances that are under consideration for treatment as Substances of Very High Concern (SVHC) candidates. Teledyne Relays confirmed that our relays do not contain any of the listed substances in concentration >0.1% weight per supplied article, substance or preparation weight.



RoHS or Non-RoHS:  
Your Choice!




**TELEDYNE  
RELAYS**

A Teledyne Technologies Company


For Additional Information please E-Mail us at: [relays@teledyne.com](mailto:relays@teledyne.com)

## APPENDIX: TELEDYNE RELAYS PART NUMBERING SYSTEM


### RF Attenuator Relays




### RF Relays (Except Attenuator Relays)



### T<sup>2</sup>R Established Reliability Relays



### Military Qualified (JAN) Relays



General Note: Parts ordered without suffix may be supplied with Solder-Coated or Gold-Plated leads


<sup>1</sup> Parts ordered with Solder-Coated leads will have (Sn60/Pb40)

<sup>2</sup> Parts ordered with RoHS Solder-Coated leads will have (Sn99.3/Cu0.7)


<sup>3</sup> Not Applicable to GRF relays

## APPENDIX: TELEDYNE RELAYS PART NUMBERING SYSTEM


### Commercial Surface Mount Relays



### Commercial Relays, (Except Surface Mount Relays)



### High Performance Relays











General Note: Parts ordered without suffix may be supplied with Solder-Coated or Gold-Plated leads.  
1 Parts ordered with Solder-Coated leads will have (Sn60/Pb40)  
2 Parts ordered with RoHS Solder-Coated leads will have (Sn99.3/Cu0.7)

**If you don't see what you're looking for  
in this Selection Guide, contact us!**



## APPENDIX: Spacer Pads

| Pad designation and bottom view dimensions   | Height  | For use with the following:  | Dim. H Max.  |
|--|---|--|--------------|
|  <p>"M4" Pad for TO-5</p>         |    | ER412, ER412D, ER412DD   | .295 (7.49)  |
|  |   | 712, 712D, 712TN, RF300, RF310, RF320  | .300 (7.62)  |
|  |   | ER420, ER422D, ER420DD, 421, ER421D, ER421DD, ER422, ER422D, ER422DD, 722, 722D, RF341 | .305 (7.75)  |
|  |   | ER431T, ER432T, ER432, ER432D, ER432DD   | .400 (10.16) |
|  |   | 732, 732D, 732TN, RF303, RF313, RF323  | .410 (10.41) |
|  |   | RF312  | .350 (8.89)  |
|  <p>"M4" Pad for TO-5</p>        |   | ER411, ER411D, ER411DD, ER411T   | .295 (7.49)  |
|  |   | ER431, ER431D, ER431DD   | .400 (10.16) |
|  |   | RF311  | .300 (7.62)  |
|  |   | RF331  | .410 (10.41) |
|  <p>"M4" Pad for Centigrid®</p> |  | 172, 172D  | .305 (7.75)  |
|  |   | ER114, ER114D, ER114DD, J114, J114D, J114DD  | .300 (7.62)  |
|  |   | ER134, ER134D, ER134DD, J134, J134D, J134DD  | .400 (10.16) |
|  |   | RF100  | .315 (8.00)  |
|  |   | RF103  | .420 (10.67) |
|  <p>"M9" Pad for Centigrid®</p> |  | 122C, A152   | .320 (8.13)  |
|  |   | ER116C, J116C  | .300 (7.62)  |
|  |   | ER136C, J136C  | .400 (10.16) |
|  |   | RF180  | .325 (8.25)  |
|  |   | A150   | .305 (7.75)  |

**Notes:**

1. Spacer pad material: Polyester film.
2. To specify an "M4" or "M9" spacer pad, refer to the mounting variants portion of the part numbering example in the applicable datasheet.
3. Dimensions are in inches (mm).
4. Unless otherwise specified, tolerance is  $\pm .010$ " (.25 mm).
5. Add 10 m $\Omega$  to the contact resistance shown in the datasheet.
6. Add 0.01 oz. (0.25 g) to the weight of the relay assembly shown in the datasheet.


## APPENDIX: Spreader Pads

| Pad designation and bottom view dimensions                  | Height | For use with the following:   | Dim. H Max.  |
|---|--------|---|--------------|
| <p style="text-align: center;"><b>"M" Pad 5/ 6/</b></p>     |        | ER411T, J411T, ER412, ER412D<br>ER412DD, J412, J412D, J412DD<br>ER412T, J412T                                       | .388 (9.86)  |
|   |        | 712, 712D, 712TN  | .393 (9.99)  |
|   |        | ER431T, J431T, ER432, ER432D<br>ER432DD, J432, J432D, J432DD<br>ER432T, J432T                                       | .493 (12.52) |
|   |        | 732, 732D, 732TN  | .503 (12.78) |
|   |        | ER420, J420, ER420D, J420D<br>ER420DD, J420DD, ER421, J421<br>ER421D, J421D, ER421DD<br>J422D, ER422DD, J422DD, 722 | .398 (10.11) |
| <p style="text-align: center;"><b>"M2" Pad 7/ 8/</b></p>    |        | ER411T<br>ER412, ER412D, ER412DD<br>J412, J412D, J412DD   | .441 (11.20) |
|   |        | 712, 712D   | .451 (11.46) |
|   |        | ER421, ER421D, ER421DD<br>722, 732D   | .451 (11.46) |
|   |        | ER431T<br>ER432, ER432D, ER432DD  | .546 (13.87) |
|   |        | 732, 732D   | .556 (14.12) |
| <p style="text-align: center;"><b>"M3" Pad 5/ 6/ 9/</b></p> |        | ER411, ER411D, ER411DD, ER411TX<br>ER412X, ER412DX, ER412DDX<br>ER412TX   | .388 (9.86)  |
|   |        | 712X, 712DX, 712TNX   | .393 (9.99)  |
|   |        | ER420X, ER420DX, ER420DDX<br>ER421X, ER421DX, ER421DDX<br>ER422X, ER422DX<br>ER422DDX, 722X, 722DDX                 | .398 (10.11) |
|   |        | ER431, ER431D, ER431DD<br>ER431TX<br>ER432X, ER432DX, ER432DDX<br>ER432TX   | .493 (12.52) |
|   |        | 732X, 732DX, 732TNX   | .503 (12.78) |

**Notes:**


1. Spreader pad material: Diallyl Phthalate.
2. To specify an "M", "M2" or "M3" spreader pad, refer to the mounting variants portion of the part number example in the applicable datasheet.
3. Dimensions are in inches (mm).
4. Unless otherwise specified, tolerance is  $\pm .010$ " (0.25 mm).
- 5/. Add 25 m $\Omega$  to the contact resistance shown in the datasheet.
- 6/. Add .01 oz. (0.25 g) to the weight of the relay assembly shown in the datasheet.
- 7/. Add 50 m $\Omega$  to the contact resistance shown in the datasheet.
- 8/. Add 0.025 oz (0.71 g) to the weight of the relay assembly shown in the datasheet.
- 9/. M3 pad to be used only when the relay has a center pin (e.g. ER411M3-12A, 722XM3-26.)

## APPENDIX: Ground Pin Positions




### TO-5 Relays:

ER411T, ER412, ER412T, ER420, ER421, ER422, ER431T, ER432, ER432T, 712, 712TN, 400H, 400K, 400V, RF300, RF303, RF341, RF312, RF310, RF313, RF320, RF323




### TO-5 Relays:

ER411, ER431, RF311, RF331



### Centigrad® Relays:

RF180, ER116C, 122C, ER136C



### Centigrad® Relays:

RF100, RF103, ER114, ER134, 172

- Indicates ground pin position
- Indicates glass insulated lead position
- ⊙ Indicates ground pin or lead position depending on relay type

### NOTES

1. Terminal views shown
2. Dimensions are in inches (mm)
3. Tolerances:  $\pm .010$  ( $\pm .25$ ) unless otherwise specified
4. Ground pin positions are within .015 (0.38) dia. of true position
5. Ground pin head dia., 0.035 (0.89) ref: height 0.010 (0.25) ref.
6. Lead dia. 0.017 (0.43) nom.

## APPENDIX: Teledyne Relays T<sup>2</sup>R Program

Teledyne Relays' **T<sup>2</sup>R** program was developed to provide the JAN relay user an alternate means of specifying and procuring established reliability relays. The form, fit and function of a **T<sup>2</sup>R** relay is the same as that of its JAN counterpart. **T<sup>2</sup>R** program requirements differ in certain regimens/tests found in both MIL-PRF-28776 and MIL-PRF-39016 that add cost but no value to the relay.

This program parallels the military specifications in most aspects. The components that make up such a program are intricate and varied. Furthermore, there are additional options of high value for design, manufacturability and operation of high reliability assemblies. The following page presents a table that compares the 100% screening performed on JAN relays and **T<sup>2</sup>R** relays prior to shipment.

Other significant highlights of the **T<sup>2</sup>R** program include:

- Two unique screening levels
- The ability to define lead finish
- Spacer pad options which may not be available in military specifications
- Ground pin options which may not be available in military specifications
- Reduced lead time
- Reduced cost

The program is fully defined for both general product requirements and detailed product requirements in the following Teledyne Relays specifications:

TR-R-1  
TR-STD-1  
TR-STD-2  
TR-ERL-1  
TR-R-1/XXX  
TR Supplement

Copies of these documents are available from Teledyne Relays. We suggest that users check with Teledyne Relays from time to time to assure that they have the latest issue.

## Can't Find What You Need?

Check out our full line of relays and switches. Order literature online at <http://www.teledynere relays.com/lit-request.asp>



## APPENDIX: Teledyne Relays T<sup>2</sup>R Program

| INSPECTION   | Screening Levels                                 |  |                                     |                                     |
|--|--|--|-------------------------------------|-------------------------------------|
|  | <b>T<sup>2</sup>R A Level</b><br>1.5%/10K Cycles | <b>T<sup>2</sup>R B Level</b><br>.75%/10K Cycles | <b>JAN L Level</b><br>3%/10K Cycles | <b>JAN M Level</b><br>1%/10K Cycles |
| <b>Subgroup 1</b>  |  |  |                                     |                                     |
| Screening, Internal Moisture AQL <sup>1</sup>                                  | ✓  | ✓  | ✓                                   | ✓                                   |
| Vibration (Sinusoidal) AQL <sup>1</sup>  |  |  | ✓                                   |                                     |
| Vibration (Sinusoidal) 100%  |  | ✓  |                                     | ✓                                   |
| Screening, Burn-In (Hybrids only)  |  |  | ✓                                   | ✓                                   |
| Screening, Run-In (Room Temperature)   | ✓  |  |                                     |                                     |
| Screening, Run-In (+125°C and -65°C)   |  | ✓  | ✓                                   | ✓                                   |
| <b>Subgroup 2</b>  |  |  |                                     |                                     |
| Coil Resistance or Coil Current  | ✓  | ✓  | ✓                                   | ✓                                   |
| Insulation Resistance  | ✓  | ✓  | ✓                                   | ✓                                   |
| Dielectric Withstanding Voltage  | ✓  | ✓  | ✓                                   | ✓                                   |
| Static Contact Resistance  | ✓  | ✓  | ✓                                   | ✓                                   |
| Pickup and Dropout or Set and Reset Voltage                                    | ✓  | ✓  | ✓                                   | ✓                                   |
| Operate and Release or Set and Reset Time                                      | ✓  | ✓  | ✓                                   | ✓                                   |
| Hold Voltage   |  |  | ✓                                   | ✓                                   |
| Turn-On and Turn-Off Time (Hybrids only)                                       | ✓  | ✓  | ✓                                   | ✓                                   |
| Contact Bounce Time  | ✓  |  | ✓                                   |                                     |
| Contact Stabilization Time   |  | ✓  |                                     | ✓                                   |
| Turn-On Current (T Hybrids only)   | ✓  | ✓  | ✓                                   | ✓                                   |
| Turn-On Voltage (C Hybrids only)   | ✓  | ✓  | ✓                                   | ✓                                   |
| Turn-Off Voltage (Hybrids only)  | ✓  | ✓  | ✓                                   | ✓                                   |
| Coil Transient Suppression (D, DD and Hybrids only)                            | ✓  | ✓  | ✓                                   | ✓                                   |
| Diode Blocking Integrity (DD only)   | ✓  | ✓  | ✓                                   | ✓                                   |
| Zener Voltage (C Hybrid only)  | ✓  | ✓  | ✓                                   | ✓                                   |
| Neutral Screen (Latching Relays only)  | ✓  | ✓  | ✓                                   | ✓                                   |
| Break Before Make Verification   |  |  | ✓                                   | ✓                                   |
| Contact Simultaneity   |  |  | ✓                                   | ✓                                   |
| <b>Subgroup 3</b>  |  |  |                                     |                                     |
| Solderability 2 Samples per Daily Solderability Inspection Lot                 | ✓  | ✓  | ✓                                   | ✓                                   |
| Leak Test  | ✓  | ✓  | ✓                                   | ✓                                   |
| External Visual and Mechanical Inspection 2/Lot for Dimension and Weight Check | ✓  | ✓  | ✓                                   | ✓                                   |

<sup>1</sup> AQL = Acceptable Quality Level



## Teledyne Relays HI-REL Program

# Teledyne Relays: Because in deep space there is no acceptable failure rate

Teledyne Relays has a long history of supplying High Reliability relays for use in space bound vehicles. From the earliest deep space probes, such as Voyager I, now nearing 21 billion miles out in space, to the next generation of probes scheduled for the future, Teledyne Relays continues to be the preeminent supplier of Hi-Reliability relays to the space market.


### Teledyne Relays Hi-Reliability Specification:

#### TR-HIREL-1

- Eliminates the need for customers to develop and maintain specifications.
- Manufacturing and Quality Assurance requirements are fully defined and documented.
- Meets the general requirements of both ESA/SCC and NASA/GSFC documents.
- Offers options for 100% Group A screening
- Offers options for 3 levels of Lot Acceptance Testing (LAT).

### Teledyne Screening Document 0-40-837

NASA approved screening regimen based on NASA/GSFC S-311-P.754



### RELAY TYPES

- TO-5 Magnetic-Latching Relays
- TO-5 Non-Latching Relays
- TO-5 Magnetic-Latching, High-Shock Relays
- TO-5 Non-Latching, High-Shock Relays
- TO-5 Non-Latching, High-Vibration Relays

### HI-REL SCREENING CAPABILITIES

- 100% Open Electrical Inspection
- 100% Precap Inspection
- Fully Automated Small Particle Inspection (Millipore Clean)
- Asynchronous Miss Test
- Coil Continuity
- Sine Vibration
- Random Vibration
- High/Low Run In
- (Miss Test)  $-65\text{ }^{\circ}\text{C} \pm 125\text{ }^{\circ}\text{C}$
- Radiographic Inspection
- Mechanical Shock Test
- Thermal Shock Test
- Acceleration
- Radiographic Inspection (X-ray)
- Mechanical Shock Test
- Thermal Shock Test
- Acceleration
- Load Banks for a Variety of Life Test Load
- Serialized Printed Electrical Data
- Continuous Life Testing
- Environmental Testing
- Vertical Integration

For information or answers to your questions, please visit our website.

## APPENDIX: Authorized Distributors

### NORTH AMERICA

#### ALLIED ELECTRONICS

Tel: (800) 433-5700  
www.alliedelec.com/search.asp

#### ASAP ELECTRONICS

Tel: (800) 477-1272  
www.asapelectronics.com

#### AVNET

Tel: (800) 772-8638  
www.em.avnet.com

#### MASTER DISTRIBUTORS

Tel: (888) 473-5297  
www.onlinecomponents.com

#### MOUSER ELECTRONICS

Tel: (800) 346-6873  
www.mouser.com

#### RICHARDSON ELECTRONICS

Tel: (800) 737-6937  
www.rell.com

#### SHERBURN ELECTRONICS

Tel: (800) 366-3066  
www.sherburn.com

### BELGIUM & LUXEMBOURG

#### Nijkerk Electronics B.V.

Tel: +32 (0) 3 544 7066  
E-mail: alain.huysmans@nijkerk.be  
www.nijkerk-ne.com

### CHINA & HONG KONG

#### Fiaco Microelectronics

Beijing Office  
Tel: 86-10-6503-2171  
E-mail: beijing@fiaco.com

#### Bright Toward Industrial Co., Ltd.

Beijing Office  
Tel: 86-10-8200-4979  
E-mail: linden\_wang@toward.com.cn

### CZECH REPUBLIC

#### Amtek spol. s.r.o.

Tel: +420 547 125 555  
E-mail: amtek@amtek.cz  
www.amtek.cz

### DENMARK

#### ARROW Denmark A/S

Tel: +45 (0) 70102211  
E-mail: jbh@arrownordic.com  
www.arrowne.com

### ESTONIA

#### ARROW Estonia

Tel: +372 6 774250  
E-mail: estonia@arrownordic.com  
www.arrowne.com

### FINLAND

#### ARROW Finland Oy

Tel: +358 9 3212 831  
www.arrowne.com

### FRANCE

#### ARROW France

Tel: +33 1 4978 4960  
E-mail: ralves@arrowfrance.com

### GERMANY

#### Adelco Elektronik GmbH

Tel: +49 (0) 4106 61040  
E-mail: adelco@t-online.de  
www.adelco-elektronik.de

#### Hot Electronic GmbH

Tel: +49 (0) 89 666 2836  
E-mail: info@hot-electronic.de  
www.hot-electronic.de

#### MRC Components oHG

Tel: +49 (0) 8161 98480  
E-mail: info@mrccomponents.de  
www.mrccomponents.de

#### Zettler electronics GmbH

Tel: +49 (0) 89 800 97-0  
E-mail: office@zettlerelectronics.com  
www.zettlerelectronics.com

### INDIA

#### Specsynergy Technologies, Inc.

San Jose, CA (Main Office)  
Tel: (408) 954-8474 x105  
E-mail: karthik@spectraus.com

#### Specsynergy Technologies, Inc.

New Delhi Office  
Tel: 91 11 25860 752  
E-mail: malik@specsynergytech.com

### ISRAEL

#### STG International Ltd.

Tel: +972 (0) 3 733 1400  
E-mail: davidb@stggroup.co.il  
www.stggroup.co.il

### ITALY

#### SINCRON s.r.l.

Tel: +39 02 95384218  
E-mail: ermanno.baschieri@sincron.it  
www.sincron.it

### JAPAN

#### Comcraft Corporation Tokyo

Tel: 81-3-3395-5553  
E-mail: trcsales@comcraft.co.jp  
www.comcraft.co.jp

#### Comcraft Corporation Osaka

Tel: 81-6-6396-7722  
E-mail: trcsales@comcraft.co.jp  
www.comcraft.co.jp

### KOREA

#### Electro-Comm USA

Tel: (818) 848-7790  
E-mail: briansong@anyeparts.com  
www.anyeparts.com

#### Electro-Comm SEOUL

Tel: 82-31-713-4216  
E-mail: tony\_jang@anyeparts.com  
www.anyeparts.com

### LATVIA

#### ARROW Latvia

Tel: +371 7311490  
E-mail: latvia@arrownordic.com  
www.arrowne.com

### LITHUANIA

#### ARROW Lithuania

Tel: +370-37-759015  
E-mail: lithuania@arrownordic.com  
www.arrowne.com

### MALAYSIA

#### Device Electronics PTE, Ltd.

Tel: (603) 7880 8626/8636  
E-mail: ngthomas@devicelect.com

### NETHERLANDS

#### Nijkerk Electronics B.V.

Tel: +32 (0) 3 544 7066  
E-mail: alain.huysmans@nijkerk.be  
www.nijkerk-ne.com

### NORWAY

#### ARROW Norway A/S

Tel: +47 (0) 21306532  
E-mail: stondevoidshagen@arrownordic.com  
www.arrowne.com

### RUSSIA

#### Petersburg Electronic Company JSC

Tel: +7 812 4488 777  
E-mail: dkizha@pec.spb.ru  
www.pec.spb.ru

### SINGAPORE

#### Device Electronics PTE, Ltd.

Tel: 65-288 6455  
E-mail: ngthomas@devicelect.com

### SOUTH AFRICA

#### RF Design

Tel:  
National Smart Call: 0861 753 357  
Cape Town: +27 (0) 21 555 8400  
Gauteng: +27 (0) 11 695 2200  
Durban: +27 (0) 31 266 4534  
www.rfdesign.co.za

### SWEDEN

#### ARROW Sweden

Tel: +46 8 56265500  
E-mail: aekstrom-wiroth@arrownordic.com  
www.arrowne.com

#### MicroComp Nordic AB

Tel: +46 8 607 3910  
E-mail: info@microcomp-nordic.se  
www.mcnaab.se

#### OEM Electronics

Tel: +46 75 242 4562  
E-mail: ulf.nygren@oemelectronics.se  
www.oemelectronics.se

### SWITZERLAND

#### ENA AG

Tel: +41 56 6342834  
E-mail: rolf.hochstrasser@ena.ch  
www.ena.ch

### TAIWAN

#### Bright Toward Industrial Co., Ltd.

Tel: +886-2-822-76000  
E-mail: philip@relays.com.tw  
www.relays.com.tw

### UNITED KINGDOM

#### Advanced Power Components plc

Tel: +44 (0) 1480 226603  
E-mail: angiep@apc-plc.co.uk  
www.apc-plc.co.uk

#### Arrow Electronics UK Ltd.

Tel: +44 (0) 1279 626 777  
www.arrowne.com


#### Willow Technologies Ltd.

Tel: +44 (0) 1342 835 234  
E-mail: sales@willow.co.uk  
www.willow.co.uk

#### 2001 Electronic Components Ltd.

Tel: +44 (0) 1438 742 001  
E-mail: sales@2001elec.co.uk  
www.2001elec.co.uk

## APPENDIX: Authorized North American Representatives



### REPRESENTATIVES

#### Cain Technology

*Southern California*  
2629 Townsgate Road, Suite 200  
Westlake Village, CA 91361  
Tel: 805-496-5702  
Fax: 805-496-6702  
www.caintech.com

#### Cee-Jay Micro Ltd.

*Eastern Canada*  
155 Terence Matthews Crescent  
Unit 2  
Kanata, Ontario  
Canada K2M 2A8  
Tel: 613-599-5626  
www.cjmicro.com

#### CentraMark Technical Sales Associates

*TX, OK and LA*  
3333 Naaman School Road  
Garland, TX 75040  
Tel: 972-414-8188  
Fax: 972-414-6788  
www.cmatex.com

#### Comp-Tech Sales

*Northern New Jersey, Metro New York, Long Island*  
232 Boulevard, Suite 11  
Hasbrouck Heights, NJ 07604  
Tel: (201) 288-7400  
Fax: (201) 288-7583  
www.comp-techsales.com

#### Eagle Sales Corporation

*MD, VA, WA DC, Eastern PA, Southern NJ*  
3545 Ellicott Mills Drive, Suite 202  
Ellicott City, MD 21043  
Tel: (410) 203-2317  
Fax: (410) 203-2318  
www.eaglesales.net

#### EK & Associates, Inc.

*IL, WI*  
887 E. Wilmette Road, Suite J  
Paltine, IL 60074  
Tel: 847-776-1758  
Fax: 847-776-8221  
www.ekrep.com

#### Electronic Representatives, Inc.

*IN, OH, MI, KY, West PA*  
6801 Lake Plaza Drive, Suite D402  
Indianapolis, IN 46220  
Tel: (317) 915-1414  
Fax: (317) 915-1216  
www.electronicreps.com

#### Essig & Associates, Inc.

*Iowa*  
809 N. Compton Drive  
Hiawatha, IA 52233  
Tel: (319) 363-8703  
Fax: (319) 363-7224  
www.essigassoc.com

#### HHP Associates, Inc.

*Florida*  
1355 S. International Pkwy, Suite 2471  
Lake Mary, FL 32746  
Tel: 407-829-8792  
Fax: 407-829-8798  
www.hhpai.com

#### Jay Stone & Associates

*Northern California*  
2109 O'Toole Avenue, Suite M  
San Jose, CA 95131  
Tel: 408-428-2500  
Fax: 407-428-9000  
www.jsarep.com

#### The MacInnis Company

*ME, NH, RI, CT, MA, VT*  
375 Vanderbilt Avenue  
Norwood, MA 02062  
Tel: (781) 762-8090  
Fax: (781) 762-5059  
www.macinnis-company.com

#### MINK Associates

*NE, KA, MO*  
10100 Santa Fe, Suite 311  
Overland Park, KS 66212  
Tel: (913) 341-8309  
Fax: (913) 341-2605  
www.minkassoc.com

#### Precision Marketing Incorporated

*MS, AL, TN, GA, NC and SC*  
5497 Wiles Road, Suite 204  
Coconut Creek, FL 33073  
Tel: (954) 752-1700  
Fax: (954) 973-6335  
www.precision-marketing.com

#### RPI-Apex Associates, Inc.

*Upstate New York (excluding Long Island)*  
54 Andover Street  
Andover, MA 01810  
Tel: 978-475-7055  
Fax: 978-475-4749  
www.rpi-apex.com

#### Sea-Port Tech Sales

*WA, OR, ID, Western Canada*  
3630 130th Ave. NE  
Bellevue, WA 98005  
Tel: (425) 702-8300  
Fax: (425) 702-8388  
www.seaporttech.com

#### Synergy Sales Representatives, Inc.

*MN, ND, SD*  
5401 Gamble Drive, Suite #105  
St. Louis Park, MN 55416  
Tel: (952) 544-1686  
Fax: (952) 545-2935  
www.synergyreps.com

#### Westrep Arizona

*AZ, NM, Clark County, NV & El Paso, TX*  
6105 S. Ash Avenue, Suite A8  
Tempe, AZ 85283  
Tel: (480) 820-9932  
Fax: (480) 820-9962  
www.westrepaz.com

**HEADQUARTERS**

12525 Daphne Ave.  
Hawthorne, CA 90250  
Phone: (323) 777-0077 or (800) 284-7007  
Fax: (323) 241-1287  
E-mail: [relays@teledyne.com](mailto:relays@teledyne.com)

**[www.teledyne.com](http://www.teledyne.com)**  
**(800) 284-7007**

**EUROPE**

9-13 Napier Road  
Wardpark North  
Cumbernauld G68 OEF  
Scotland UK  
Phone: +44 (0) 1236 453 124  
Fax: +44 (0) 1236 780 651  
E-mail: [sales\\_europe@teledyne.com](mailto:sales_europe@teledyne.com)

**[www.teledyne-europe.com](http://www.teledyne-europe.com)**  
**+44 (0) 1236 453 124**



**TELEDYNE  
RELAYS**

A Teledyne Technologies Company